

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332179-930

Luminaire Tested: **S123DIW-S775D1535U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332179-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1535U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6924.3 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		60	60	60		45	45	45	37
1	95	91	87	83	86	82	79	76	67	64	62		52	51	50		39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52		46	43	41		34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43		41	38	35		31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37		36	33	30		27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32		32	29	26		25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28		29	25	23		22	20	18	14
7	56	44	36	31	51	40	33	29	33	28	24		27	23	20		20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21		24	20	18		19	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19		22	19	16		17	15	13	10
10	45	33	26	21	41	31	24	20	25	20	17		21	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.4
10°-20°	264.1	3.8
20°-30°	390.1	5.6
30°-40°	455.7	6.6
40°-50°	458.1	6.6
50°-60°	402.4	5.8
60°-70°	299.8	4.3
70°-80°	170.8	2.5
80°-90°	53.7	0.8
90°-100°	102.0	1.5
100°-110°	305.2	4.4
110°-120°	519.0	7.5
120°-130°	682.7	9.9
130°-140°	767.4	11.1
140°-150°	754.3	10.9
150°-160°	635.0	9.2
160°-170°	422.7	6.1
170°-180°	148.0	2.1
0°-30°	747.7	10.8
0°-40°	1203.3	17.4
0°-60°	2063.8	29.8
0°-90°	2588.1	37.4
90°-120°	926.2	13.4
90°-150°	3130.5	45.2
90°-180°	4336.0	62.6
0°-180°	6924.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	14	30	34	37	7
95°	73	81	91	96	96	82
105°	277	280	290	290	293	296
115°	522	526	524	525	524	517
125°	765	768	766	761	756	682
135°	992	999	998	994	991	764
145°	1204	1206	1210	1208	1204	752
155°	1378	1378	1379	1384	1376	634
165°	1501	1498	1498	1504	1496	423
175°	1561	1557	1556	1563	1555	148
180°	1565	1565	1565	1565	1565	



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	18.0	18.1	18.2	18.3	18.3	18.7	19.2	19.8	20.4	21.0	21.0
90°	1.2	4.0	6.7	9.5	12.1	15.3	18.8	22.4	25.9	29.5	30.6
92.5°	29.8	31.6	33.4	35.3	37.2	39.1	41.2	43.1	45.2	47.2	48.1
95°	72.6	74.4	76.4	78.3	80.2	82.3	84.4	86.6	88.8	91.0	92.0
97.5°	128.8	130.3	131.7	133.1	134.5	136.0	137.6	139.2	140.8	142.4	143.7
100°	167.2	168.8	170.5	172.1	173.7	175.3	176.6	178.0	179.4	180.8	181.6
102.5°	211.5	212.5	213.4	214.4	215.4	216.8	218.6	220.4	222.2	224.0	224.9
105°	276.6	277.2	277.7	278.3	278.8	280.3	282.7	285.2	287.7	290.2	290.2
107.5°	352.4	352.7	353.0	353.4	353.7	354.3	355.3	356.3	357.3	358.2	359.1
110°	399.6	400.1	400.6	401.2	401.8	402.3	402.8	403.4	403.9	404.5	405.6



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.7	449.1	449.4	449.7	450.0	450.3	450.4	450.5	450.6	450.7	452.0
115°	522.5	523.3	524.2	525.0	525.8	525.9	525.4	524.8	524.3	523.7	524.0
117.5°	596.8	597.3	597.9	598.4	598.9	598.8	598.2	597.5	596.7	596.1	596.0
120°	643.0	644.7	646.3	647.9	649.5	649.7	648.3	646.9	645.6	644.2	643.9
122.5°	691.2	692.4	693.6	694.8	696.0	696.3	695.5	694.8	694.1	693.4	692.7
125°	764.7	765.5	766.4	767.2	768.0	768.1	767.6	767.0	766.5	766.0	764.8
127.5°	832.6	834.3	836.1	837.8	839.6	840.2	839.5	838.9	838.4	837.7	836.2
130°	877.8	880.0	882.2	884.4	886.6	887.2	886.4	885.6	884.8	883.9	882.9
132.5°	923.1	925.2	927.4	929.6	931.8	932.6	932.0	931.4	930.7	930.2	928.9
135°	992.1	993.8	995.4	997.0	998.7	999.4	999.1	998.8	998.6	998.3	997.2
137.5°	1056.1	1057.4	1058.8	1060.2	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3
140°	1100.3	1101.7	1103.1	1104.4	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4
142.5°	1140.7	1142.0	1143.4	1144.8	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8
145°	1203.6	1204.2	1204.7	1205.3	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5
147.5°	1258.7	1259.6	1260.6	1261.7	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6
150°	1297.1	1297.6	1298.1	1298.7	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0
152.5°	1328.5	1329.3	1330.1	1330.8	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9
155°	1378.2	1378.2	1378.2	1378.2	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5
157.5°	1420.5	1420.2	1419.8	1419.5	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1
160°	1447.1	1446.5	1445.9	1445.4	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9
162.5°	1470.6	1469.9	1469.1	1468.4	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6
165°	1501.1	1500.3	1499.5	1498.7	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1
167.5°	1525.5	1524.4	1523.3	1522.2	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2
170°	1539.2	1538.1	1537.1	1535.9	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3
172.5°	1550.0	1549.0	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9
175°	1561.4	1560.3	1559.2	1558.1	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1
177.5°	1566.0	1565.2	1564.3	1563.4	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	21.0	21.1	21.2	21.3	21.4	21.5	21.6	21.7
90°	31.7	32.8	33.9	34.7	35.2	35.8	36.4	36.9
92.5°	48.9	49.8	50.7	51.0	50.6	50.3	50.0	49.7
95°	93.2	94.2	95.3	95.9	95.9	95.9	95.9	95.9
97.5°	144.9	146.1	147.4	148.0	147.9	147.7	147.7	147.6
100°	182.4	183.2	184.0	184.7	185.2	185.8	186.3	186.9
102.5°	225.7	226.5	227.3	227.6	227.6	227.4	227.3	227.2
105°	290.2	290.2	290.2	290.4	291.0	291.6	292.0	292.6
107.5°	360.0	360.9	361.7	362.0	361.7	361.3	361.0	360.7
110°	406.7	407.7	408.9	409.1	408.5	408.1	407.5	406.9



TEST NUMBER: P332179-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	453.3	454.6	455.9	456.6	456.5	456.3	456.2	456.1
115°	524.3	524.6	524.8	524.8	524.6	524.3	524.0	523.7
117.5°	595.9	595.9	595.8	595.4	594.6	593.9	593.1	592.3
120°	643.7	643.4	643.1	642.7	642.2	641.6	641.1	640.5
122.5°	691.9	691.3	690.6	689.8	689.1	688.3	687.5	686.7
125°	763.8	762.6	761.6	760.4	759.4	758.3	757.2	756.1
127.5°	834.7	833.2	831.6	830.2	829.0	827.7	826.5	825.2
130°	881.7	880.7	879.6	878.1	876.2	874.2	872.4	870.4
132.5°	927.6	926.3	925.0	923.6	922.1	920.6	919.1	917.6
135°	996.1	995.0	993.9	993.1	992.5	992.0	991.5	990.9
137.5°	1063.2	1062.0	1060.9	1059.7	1058.7	1057.7	1056.6	1055.6
140°	1107.2	1106.9	1106.6	1105.5	1103.6	1101.7	1099.8	1097.9
142.5°	1148.5	1148.2	1147.9	1147.0	1145.6	1144.1	1142.6	1141.2
145°	1209.2	1208.9	1208.7	1207.9	1206.9	1205.8	1204.7	1203.6
147.5°	1266.6	1266.6	1266.6	1265.8	1264.1	1262.5	1260.8	1259.1
150°	1302.0	1302.0	1302.0	1301.1	1299.5	1297.9	1296.2	1294.6
152.5°	1334.3	1334.7	1335.2	1334.7	1333.3	1331.9	1330.4	1329.0
155°	1381.6	1382.7	1383.8	1383.4	1381.4	1379.6	1377.6	1375.7
157.5°	1422.3	1423.4	1424.6	1424.4	1422.9	1421.3	1419.8	1418.3
160°	1447.3	1448.7	1450.0	1450.2	1449.1	1448.0	1446.9	1445.8
162.5°	1470.9	1472.3	1473.7	1473.5	1471.7	1470.0	1468.2	1466.5
165°	1500.7	1502.4	1504.0	1503.9	1501.9	1500.1	1498.1	1496.2
167.5°	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5
170°	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3
172.5°	1548.5	1550.2	1551.9	1551.8	1549.9	1548.0	1546.1	1544.2
175°	1559.7	1561.4	1563.0	1562.8	1561.0	1559.0	1557.1	1555.3
177.5°	1564.7	1566.0	1567.3	1567.2	1565.7	1564.2	1562.7	1561.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0

(END OF REPORT)