

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332157-930

Luminaire Tested: **S123DIW-S775D755U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332157-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D755U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4795.6 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	74	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	25	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	1.8
10°-20°	278.3	5.8
20°-30°	467.0	9.7
30°-40°	528.8	11.0
40°-50°	474.2	9.9
50°-60°	382.7	8.0
60°-70°	266.7	5.6
70°-80°	140.2	2.9
80°-90°	36.6	0.8
90°-100°	50.2	1.0
100°-110°	150.2	3.1
110°-120°	255.5	5.3
120°-130°	336.1	7.0
130°-140°	377.7	7.9
140°-150°	371.3	7.7
150°-160°	312.6	6.5
160°-170°	208.1	4.3
170°-180°	72.9	1.5
0°-30°	832.1	17.4
0°-40°	1360.9	28.4
0°-60°	2217.8	46.2
0°-90°	2661.2	55.5
90°-120°	455.9	9.5
90°-150°	1540.9	32.1
90°-180°	2134.0	44.5
0°-180°	4795.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	18	1	18	1	18	10
95°	47	36	47	36	47	48
105°	144	136	144	136	144	153
115°	258	257	258	257	258	255
125°	372	376	372	376	372	333
135°	488	488	488	488	488	375
145°	592	592	592	592	592	370
155°	677	678	677	678	677	312
165°	736	739	736	739	736	208
175°	766	768	766	768	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	13.9	13.1	13.5	13.7	13.3	13.6	13.8	14.0	14.3	14.5	14.5
90°	18.2	17.9	17.6	17.4	17.0	16.7	16.1	15.6	15.1	14.5	12.8
92.5°	24.5	24.6	24.8	24.9	25.1	24.9	24.5	24.1	23.6	23.2	22.3
95°	47.2	47.2	47.2	47.2	47.2	47.0	46.4	45.8	45.3	44.8	43.7
97.5°	72.6	72.6	72.7	72.8	72.8	72.6	71.9	71.3	70.7	70.1	69.3
100°	92.0	91.7	91.5	91.2	90.9	90.6	90.2	89.8	89.4	88.9	88.3
102.5°	111.9	111.9	111.9	112.0	112.0	111.9	111.5	111.0	110.6	110.2	109.3
105°	144.1	143.7	143.5	143.2	142.9	142.8	142.8	142.8	142.8	142.8	141.6
107.5°	177.6	177.7	177.9	178.1	178.2	178.1	177.7	177.2	176.8	176.3	175.9
110°	200.3	200.6	200.8	201.1	201.4	201.2	200.7	200.2	199.7	199.1	198.9



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.5	224.5	224.6	224.7	224.7	224.5	223.8	223.1	222.5	221.8	221.8
115°	257.8	258.0	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8	258.0
117.5°	291.6	292.0	292.3	292.7	293.1	293.3	293.3	293.3	293.3	293.3	293.8
120°	315.3	315.5	315.8	316.1	316.3	316.6	316.7	316.8	317.0	317.1	317.8
122.5°	338.0	338.4	338.8	339.2	339.6	339.9	340.2	340.6	341.0	341.3	341.7
125°	372.2	372.7	373.2	373.8	374.3	374.9	375.4	375.9	376.5	377.0	377.2
127.5°	406.2	406.8	407.4	408.1	408.6	409.4	410.1	410.8	411.6	412.4	412.6
130°	428.4	429.4	430.3	431.3	432.2	432.9	433.5	434.1	434.6	435.1	435.5
132.5°	451.7	452.4	453.1	453.9	454.6	455.3	455.9	456.6	457.2	457.9	458.1
135°	487.7	488.0	488.3	488.5	488.9	489.3	489.8	490.3	490.8	491.4	491.5
137.5°	519.6	520.1	520.6	521.1	521.6	522.2	522.7	523.3	523.8	524.4	524.1
140°	540.4	541.4	542.3	543.2	544.1	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.7	562.4	563.1	563.9	564.6	565.0	565.2	565.3	565.4	565.6	565.3
145°	592.5	593.0	593.5	594.0	594.6	594.9	595.1	595.2	595.3	595.5	595.1
147.5°	619.8	620.6	621.4	622.2	623.1	623.5	623.5	623.5	623.5	623.5	623.1
150°	637.2	638.1	638.9	639.6	640.4	640.8	640.8	640.8	640.8	640.8	640.6
152.5°	654.2	654.8	655.6	656.2	657.0	657.2	657.0	656.8	656.6	656.3	656.2
155°	677.2	678.1	679.1	680.0	680.9	681.1	680.6	680.0	679.6	679.0	678.8
157.5°	698.1	698.9	699.6	700.3	701.1	701.2	700.7	700.1	699.5	699.0	698.9
160°	711.7	712.2	712.7	713.3	713.8	713.7	713.1	712.4	711.8	711.0	711.0
162.5°	721.8	722.7	723.6	724.4	725.3	725.4	724.7	724.0	723.3	722.7	722.6
165°	736.5	737.4	738.3	739.3	740.2	740.3	739.5	738.7	737.8	737.0	737.0
167.5°	748.9	749.7	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9	748.9
170°	755.2	756.2	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2	755.2
172.5°	760.1	761.0	762.0	762.9	763.9	763.9	763.0	762.2	761.4	760.5	760.5
175°	765.5	766.5	767.4	768.3	769.3	769.3	768.5	767.8	767.0	766.1	766.1
177.5°	768.4	769.2	769.9	770.7	771.4	771.5	770.9	770.2	769.6	768.9	768.9
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	14.8	14.8	13.5	11.8	10.8	9.5	9.3	8.3	7.9	8.2	8.1
90°	11.0	9.3	7.5	6.0	4.6	3.3	2.0	0.6	2.0	3.3	4.6
92.5°	21.3	20.2	19.2	18.3	17.4	16.5	15.6	14.7	15.6	16.5	17.4
95°	42.6	41.6	40.4	39.5	38.6	37.6	36.6	35.7	36.6	37.6	38.6
97.5°	68.5	67.8	66.9	66.2	65.6	64.8	64.1	63.4	64.1	64.8	65.6
100°	87.6	86.9	86.3	85.5	84.7	83.9	83.1	82.3	83.1	83.9	84.7
102.5°	108.5	107.6	106.7	106.0	105.5	105.1	104.6	104.1	104.6	105.1	105.5
105°	140.4	139.2	137.9	137.2	137.0	136.7	136.4	136.2	136.4	136.7	137.0
107.5°	175.4	174.9	174.4	174.1	173.9	173.7	173.6	173.4	173.6	173.7	173.9
110°	198.5	198.3	198.0	197.7	197.5	197.2	197.0	196.7	197.0	197.2	197.5





TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	221.8	221.7	221.6	221.5	221.4	221.2	221.0	220.9	221.0	221.2	221.4
115°	258.4	258.6	258.9	258.8	258.4	258.0	257.6	257.2	257.6	258.0	258.4
117.5°	294.1	294.4	294.8	294.8	294.6	294.2	294.0	293.8	294.0	294.2	294.6
120°	318.5	319.1	319.8	319.8	318.9	318.1	317.3	316.5	317.3	318.1	318.9
122.5°	342.0	342.3	342.7	342.6	342.0	341.4	340.8	340.2	340.8	341.4	342.0
125°	377.6	377.8	378.1	378.1	377.6	377.2	376.8	376.4	376.8	377.2	377.6
127.5°	412.9	413.3	413.5	413.3	412.4	411.6	410.7	409.8	410.7	411.6	412.4
130°	435.9	436.3	436.8	436.3	435.3	434.2	433.2	432.1	433.2	434.2	435.3
132.5°	458.4	458.8	459.0	458.7	457.5	456.5	455.4	454.4	455.4	456.5	457.5
135°	491.6	491.8	492.0	491.5	490.8	490.0	489.2	488.4	489.2	490.0	490.8
137.5°	523.7	523.3	523.0	522.5	521.9	521.1	520.5	519.8	520.5	521.1	521.9
140°	544.9	544.9	544.7	544.3	543.6	543.0	542.3	541.6	542.3	543.0	543.6
142.5°	565.1	564.8	564.6	564.1	563.5	562.8	562.1	561.5	562.1	562.8	563.5
145°	594.7	594.3	593.9	593.5	593.2	593.0	592.7	592.5	592.7	593.0	593.2
147.5°	622.6	622.3	621.9	621.5	621.0	620.5	620.0	619.5	620.0	620.5	621.0
150°	640.3	640.0	639.8	639.5	639.3	639.0	638.7	638.5	638.7	639.0	639.3
152.5°	656.0	655.8	655.7	655.4	655.1	654.7	654.3	654.0	654.3	654.7	655.1
155°	678.7	678.6	678.4	678.4	678.4	678.4	678.4	678.4	678.4	678.4	678.4
157.5°	698.7	698.6	698.5	698.5	698.7	698.9	699.0	699.2	699.0	698.9	698.7
160°	711.0	711.0	711.0	711.2	711.4	711.8	712.0	712.2	712.0	711.8	711.4
162.5°	722.4	722.4	722.3	722.4	722.8	723.1	723.5	723.9	723.5	723.1	722.8
165°	737.0	737.0	737.0	737.3	737.7	738.1	738.5	738.9	738.5	738.1	737.7
167.5°	748.7	748.6	748.5	748.7	749.3	749.8	750.3	750.9	750.3	749.8	749.3
170°	755.2	755.2	755.2	755.5	756.0	756.6	757.1	757.7	757.1	756.6	756.0
172.5°	760.5	760.5	760.5	760.8	761.3	761.9	762.5	763.0	762.5	761.9	761.3
175°	766.1	766.1	766.1	766.4	767.0	767.4	768.0	768.5	768.0	767.4	767.0
177.5°	768.9	768.9	768.9	769.2	769.6	770.0	770.4	770.9	770.4	770.0	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	8.0	8.6	8.7	9.4	9.4	10.1	10.2	9.6	9.7	10.8	9.5
90°	6.0	7.5	9.3	11.0	12.8	14.5	15.1	15.6	16.1	16.7	17.0
92.5°	18.3	19.2	20.2	21.3	22.3	23.2	23.6	24.1	24.5	24.9	25.1
95°	39.5	40.4	41.6	42.6	43.7	44.8	45.3	45.8	46.4	47.0	47.2
97.5°	66.2	66.9	67.8	68.5	69.3	70.1	70.7	71.3	71.9	72.6	72.8
100°	85.5	86.3	86.9	87.6	88.3	88.9	89.4	89.8	90.2	90.6	90.9
102.5°	106.0	106.7	107.6	108.5	109.3	110.2	110.6	111.0	111.5	111.9	112.0
105°	137.2	137.9	139.2	140.4	141.6	142.8	142.8	142.8	142.8	142.8	142.9
107.5°	174.1	174.4	174.9	175.4	175.9	176.3	176.8	177.2	177.7	178.1	178.2
110°	197.7	198.0	198.3	198.5	198.9	199.1	199.7	200.2	200.7	201.2	201.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	221.5	221.6	221.7	221.8	221.8	221.8	222.5	223.1	223.8	224.5	224.7
115°	258.8	258.9	258.6	258.4	258.0	257.8	258.0	258.0	258.2	258.4	258.4
117.5°	294.8	294.8	294.4	294.1	293.8	293.3	293.3	293.3	293.3	293.3	293.1
120°	319.8	319.8	319.1	318.5	317.8	317.1	317.0	316.8	316.7	316.6	316.3
122.5°	342.6	342.7	342.3	342.0	341.7	341.3	341.0	340.6	340.2	339.9	339.6
125°	378.1	378.1	377.8	377.6	377.2	377.0	376.5	375.9	375.4	374.9	374.3
127.5°	413.3	413.5	413.3	412.9	412.6	412.4	411.6	410.8	410.1	409.4	408.6
130°	436.3	436.8	436.3	435.9	435.5	435.1	434.6	434.1	433.5	432.9	432.2
132.5°	458.7	459.0	458.8	458.4	458.1	457.9	457.2	456.6	455.9	455.3	454.6
135°	491.5	492.0	491.8	491.6	491.5	491.4	490.8	490.3	489.8	489.3	488.9
137.5°	522.5	523.0	523.3	523.7	524.1	524.4	523.8	523.3	522.7	522.2	521.6
140°	544.3	544.7	544.9	544.9	545.1	545.3	545.1	544.9	544.9	544.7	544.1
142.5°	564.1	564.6	564.8	565.1	565.3	565.6	565.4	565.3	565.2	565.0	564.6
145°	593.5	593.9	594.3	594.7	595.1	595.5	595.3	595.2	595.1	594.9	594.6
147.5°	621.5	621.9	622.3	622.6	623.1	623.5	623.5	623.5	623.5	623.5	623.1
150°	639.5	639.8	640.0	640.3	640.6	640.8	640.8	640.8	640.8	640.8	640.4
152.5°	655.4	655.7	655.8	656.0	656.2	656.3	656.6	656.8	657.0	657.2	657.0
155°	678.4	678.4	678.6	678.7	678.8	679.0	679.6	680.0	680.6	681.1	680.9
157.5°	698.5	698.5	698.6	698.7	698.9	699.0	699.5	700.1	700.7	701.2	701.1
160°	711.2	711.0	711.0	711.0	711.0	711.0	711.8	712.4	713.1	713.7	713.8
162.5°	722.4	722.3	722.4	722.4	722.6	722.7	723.3	724.0	724.7	725.4	725.3
165°	737.3	737.0	737.0	737.0	737.0	737.0	737.8	738.7	739.5	740.3	740.2
167.5°	748.7	748.5	748.6	748.7	748.9	748.9	749.7	750.6	751.5	752.3	752.3
170°	755.5	755.2	755.2	755.2	755.2	755.2	756.2	757.1	758.1	759.0	759.0
172.5°	760.8	760.5	760.5	760.5	760.5	760.5	761.4	762.2	763.0	763.9	763.9
175°	766.4	766.1	766.1	766.1	766.1	766.1	767.0	767.8	768.5	769.3	769.3
177.5°	769.2	768.9	768.9	768.9	768.9	768.9	769.6	770.2	770.9	771.5	771.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	9.6	9.7	9.4	9.1	9.4	9.7	9.6	9.5	10.8	9.7	9.6
90°	17.4	17.6	17.9	18.2	17.9	17.6	17.4	17.0	16.7	16.1	15.6
92.5°	24.9	24.8	24.6	24.5	24.6	24.8	24.9	25.1	24.9	24.5	24.1
95°	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.0	46.4	45.8
97.5°	72.8	72.7	72.6	72.6	72.6	72.7	72.8	72.8	72.6	71.9	71.3
100°	91.2	91.5	91.7	92.0	91.7	91.5	91.2	90.9	90.6	90.2	89.8
102.5°	112.0	111.9	111.9	111.9	111.9	111.9	112.0	112.0	111.9	111.5	111.0
105°	143.2	143.5	143.7	144.1	143.7	143.5	143.2	142.9	142.8	142.8	142.8
107.5°	178.1	177.9	177.7	177.6	177.7	177.9	178.1	178.2	178.1	177.7	177.2
110°	201.1	200.8	200.6	200.3	200.6	200.8	201.1	201.4	201.2	200.7	200.2



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	224.7	224.6	224.5	224.5	224.5	224.6	224.7	224.7	224.5	223.8	223.1
115°	258.2	258.0	258.0	257.8	258.0	258.0	258.2	258.4	258.4	258.2	258.0
117.5°	292.7	292.3	292.0	291.6	292.0	292.3	292.7	293.1	293.3	293.3	293.3
120°	316.1	315.8	315.5	315.3	315.5	315.8	316.1	316.3	316.6	316.7	316.8
122.5°	339.2	338.8	338.4	338.0	338.4	338.8	339.2	339.6	339.9	340.2	340.6
125°	373.8	373.2	372.7	372.2	372.7	373.2	373.8	374.3	374.9	375.4	375.9
127.5°	408.1	407.4	406.8	406.2	406.8	407.4	408.1	408.6	409.4	410.1	410.8
130°	431.3	430.3	429.4	428.4	429.4	430.3	431.3	432.2	432.9	433.5	434.1
132.5°	453.9	453.1	452.4	451.7	452.4	453.1	453.9	454.6	455.3	455.9	456.6
135°	488.5	488.3	488.0	487.7	488.0	488.3	488.5	488.9	489.3	489.8	490.3
137.5°	521.1	520.6	520.1	519.6	520.1	520.6	521.1	521.6	522.2	522.7	523.3
140°	543.2	542.3	541.4	540.4	541.4	542.3	543.2	544.1	544.7	544.9	544.9
142.5°	563.9	563.1	562.4	561.7	562.4	563.1	563.9	564.6	565.0	565.2	565.3
145°	594.0	593.5	593.0	592.5	593.0	593.5	594.0	594.6	594.9	595.1	595.2
147.5°	622.2	621.4	620.6	619.8	620.6	621.4	622.2	623.1	623.5	623.5	623.5
150°	639.6	638.9	638.1	637.2	638.1	638.9	639.6	640.4	640.8	640.8	640.8
152.5°	656.2	655.6	654.8	654.2	654.8	655.6	656.2	657.0	657.2	657.0	656.8
155°	680.0	679.1	678.1	677.2	678.1	679.1	680.0	680.9	681.1	680.6	680.0
157.5°	700.3	699.6	698.9	698.1	698.9	699.6	700.3	701.1	701.2	700.7	700.1
160°	713.3	712.7	712.2	711.7	712.2	712.7	713.3	713.8	713.7	713.1	712.4
162.5°	724.4	723.6	722.7	721.8	722.7	723.6	724.4	725.3	725.4	724.7	724.0
165°	739.3	738.3	737.4	736.5	737.4	738.3	739.3	740.2	740.3	739.5	738.7
167.5°	751.5	750.6	749.7	748.9	749.7	750.6	751.5	752.3	752.3	751.5	750.6
170°	758.1	757.1	756.2	755.2	756.2	757.1	758.1	759.0	759.0	758.1	757.1
172.5°	762.9	762.0	761.0	760.1	761.0	762.0	762.9	763.9	763.9	763.0	762.2
175°	768.3	767.4	766.5	765.5	766.5	767.4	768.3	769.3	769.3	768.5	767.8
177.5°	770.7	769.9	769.2	768.4	769.2	769.9	770.7	771.4	771.5	770.9	770.2
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	10.2	10.1	9.4	9.4	8.7	8.6	8.0	8.1	8.2	7.9	8.3
90°	15.1	14.5	12.8	11.0	9.3	7.5	6.0	4.6	3.3	2.0	0.6
92.5°	23.6	23.2	22.3	21.3	20.2	19.2	18.3	17.4	16.5	15.6	14.7
95°	45.3	44.8	43.7	42.6	41.6	40.4	39.5	38.6	37.6	36.6	35.7
97.5°	70.7	70.1	69.3	68.5	67.8	66.9	66.2	65.6	64.8	64.1	63.4
100°	89.4	88.9	88.3	87.6	86.9	86.3	85.5	84.7	83.9	83.1	82.3
102.5°	110.6	110.2	109.3	108.5	107.6	106.7	106.0	105.5	105.1	104.6	104.1
105°	142.8	142.8	141.6	140.4	139.2	137.9	137.2	137.0	136.7	136.4	136.2
107.5°	176.8	176.3	175.9	175.4	174.9	174.4	174.1	173.9	173.7	173.6	173.4
110°	199.7	199.1	198.9	198.5	198.3	198.0	197.7	197.5	197.2	197.0	196.7



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.5	221.8	221.8	221.8	221.7	221.6	221.5	221.4	221.2	221.0	220.9
115°	258.0	257.8	258.0	258.4	258.6	258.9	258.8	258.4	258.0	257.6	257.2
117.5°	293.3	293.3	293.8	294.1	294.4	294.8	294.8	294.6	294.2	294.0	293.8
120°	317.0	317.1	317.8	318.5	319.1	319.8	319.8	318.9	318.1	317.3	316.5
122.5°	341.0	341.3	341.7	342.0	342.3	342.7	342.6	342.0	341.4	340.8	340.2
125°	376.5	377.0	377.2	377.6	377.8	378.1	378.1	377.6	377.2	376.8	376.4
127.5°	411.6	412.4	412.6	412.9	413.3	413.5	413.3	412.4	411.6	410.7	409.8
130°	434.6	435.1	435.5	435.9	436.3	436.8	436.3	435.3	434.2	433.2	432.1
132.5°	457.2	457.9	458.1	458.4	458.8	459.0	458.7	457.5	456.5	455.4	454.4
135°	490.8	491.4	491.5	491.6	491.8	492.0	491.5	490.8	490.0	489.2	488.4
137.5°	523.8	524.4	524.1	523.7	523.3	523.0	522.5	521.9	521.1	520.5	519.8
140°	545.1	545.3	545.1	544.9	544.9	544.7	544.3	543.6	543.0	542.3	541.6
142.5°	565.4	565.6	565.3	565.1	564.8	564.6	564.1	563.5	562.8	562.1	561.5
145°	595.3	595.5	595.1	594.7	594.3	593.9	593.5	593.2	593.0	592.7	592.5
147.5°	623.5	623.5	623.1	622.6	622.3	621.9	621.5	621.0	620.5	620.0	619.5
150°	640.8	640.8	640.6	640.3	640.0	639.8	639.5	639.3	639.0	638.7	638.5
152.5°	656.6	656.3	656.2	656.0	655.8	655.7	655.4	655.1	654.7	654.3	654.0
155°	679.6	679.0	678.8	678.7	678.6	678.4	678.4	678.4	678.4	678.4	678.4
157.5°	699.5	699.0	698.9	698.7	698.6	698.5	698.5	698.7	698.9	699.0	699.2
160°	711.8	711.0	711.0	711.0	711.0	711.0	711.2	711.4	711.8	712.0	712.2
162.5°	723.3	722.7	722.6	722.4	722.4	722.3	722.4	722.8	723.1	723.5	723.9
165°	737.8	737.0	737.0	737.0	737.0	737.0	737.3	737.7	738.1	738.5	738.9
167.5°	749.7	748.9	748.9	748.7	748.6	748.5	748.7	749.3	749.8	750.3	750.9
170°	756.2	755.2	755.2	755.2	755.2	755.2	755.5	756.0	756.6	757.1	757.7
172.5°	761.4	760.5	760.5	760.5	760.5	760.5	760.8	761.3	761.9	762.5	763.0
175°	767.0	766.1	766.1	766.1	766.1	766.1	766.4	767.0	767.4	768.0	768.5
177.5°	769.6	768.9	768.9	768.9	768.9	768.9	769.2	769.6	770.0	770.4	770.9
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.3	9.5	10.8	11.8	13.5	14.8	14.8	14.5	14.5	14.3	14.0
90°	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1	15.6
92.5°	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6	24.1
95°	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3	45.8
97.5°	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7	71.3
100°	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4	89.8
102.5°	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6	111.0
105°	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8	142.8
107.5°	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8	177.2
110°	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7	200.2





TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5	223.1
115°	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0	258.0
117.5°	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3	293.3
120°	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0	316.8
122.5°	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0	340.6
125°	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5	375.9
127.5°	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6	410.8
130°	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6	434.1
132.5°	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2	456.6
135°	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8	490.3
137.5°	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8	523.3
140°	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1	544.9
142.5°	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4	565.3
145°	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3	595.2
147.5°	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5	623.5
150°	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8	640.8
152.5°	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6	656.8
155°	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6	680.0
157.5°	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5	700.1
160°	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8	712.4
162.5°	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3	724.0
165°	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8	738.7
167.5°	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7	750.6
170°	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2	757.1
172.5°	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4	762.2
175°	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0	767.8
177.5°	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6	770.2
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	13.8	13.6	13.3	13.7	13.5	13.1	13.9
90°	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332157-930

CATALOG NUMBER: S123DIW-S775D755U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)