

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332457-930

Luminaire Tested: **S123RDIW-S1000D755U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332457-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5227.6 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	84	78	76	74	67	66	64	58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.5
10°-20°	357.5	6.8
20°-30°	514.7	9.8
30°-40°	579.8	11.1
40°-50°	554.7	10.6
50°-60°	454.2	8.7
60°-70°	306.5	5.9
70°-80°	154.2	2.9
80°-90°	43.1	0.8
90°-100°	50.2	1.0
100°-110°	150.2	2.9
110°-120°	255.5	4.9
120°-130°	336.1	6.4
130°-140°	377.7	7.2
140°-150°	371.3	7.1
150°-160°	312.6	6.0
160°-170°	208.1	4.0
170°-180°	72.9	1.4
0°-30°	1000.7	19.1
0°-40°	1580.5	30.2
0°-60°	2589.5	49.5
0°-90°	3093.2	59.2
90°-120°	455.9	8.7
90°-150°	1540.9	29.5
90°-180°	2134.0	40.8
0°-180°	5227.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	7	14	17	18	5
95°	36	40	45	47	47	40
105°	136	138	143	143	144	146
115°	257	259	258	258	258	254
125°	376	378	377	375	372	336
135°	488	492	491	489	488	376
145°	592	594	596	595	592	370
155°	678	678	679	681	677	312
165°	739	737	737	740	736	208
175°	768	766	766	769	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.5	17.6	15.7	13.9	13.0	13.4	13.8	14.1	14.4	14.3
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1
92.5°	14.7	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6
95°	35.7	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3
97.5°	63.4	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7
100°	82.3	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4
102.5°	104.1	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6
105°	136.2	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8
107.5°	173.4	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8
110°	196.7	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5
115°	257.2	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0
117.5°	293.8	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3
120°	316.5	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0
122.5°	340.2	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0
125°	376.4	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5
127.5°	409.8	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6
130°	432.1	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6
132.5°	454.4	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2
135°	488.4	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8
137.5°	519.8	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8
140°	541.6	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.5	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4
145°	592.5	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3
147.5°	619.5	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5
150°	638.5	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8
152.5°	654.0	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6
155°	678.4	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6
157.5°	699.2	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5
160°	712.2	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8
162.5°	723.9	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3
165°	738.9	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8
167.5°	750.9	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7
170°	757.7	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2
172.5°	763.0	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4
175°	768.5	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0
177.5°	770.9	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	14.3	14.2	14.1	13.9	13.9	13.7	13.5	13.4
90°	15.6	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.1	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	45.8	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.3	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	89.8	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.0	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.2	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.2	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332457-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.8	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.6	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.9	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.8	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	434.1	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	456.6	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	490.3	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	523.3	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.3	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.2	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	656.8	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.0	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.1	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	712.4	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.0	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	738.7	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	762.2	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	767.8	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.2	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)