

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332473-930

Luminaire Tested: **S123RDIW-S1165D460U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332473-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D460U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4874.3 lumens  
Efficiency: N/A  
Efficacy: 93.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	62	59	57	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49	46
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42	40
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33	31
7	63	50	42	37	60	48	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27	25
9	55	42	35	29	52	41	33	29	38	31	27	35	29	26	32	27	24	22
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.4	3.0
10°-20°	412.9	8.5
20°-30°	594.5	12.2
30°-40°	669.6	13.7
40°-50°	640.6	13.1
50°-60°	524.6	10.8
60°-70°	354.0	7.3
70°-80°	178.1	3.7
80°-90°	48.5	1.0
90°-100°	30.6	0.6
100°-110°	91.7	1.9
110°-120°	156.0	3.2
120°-130°	205.2	4.2
130°-140°	230.6	4.7
140°-150°	226.7	4.7
150°-160°	190.8	3.9
160°-170°	127.0	2.6
170°-180°	44.5	0.9
0°-30°	1155.7	23.7
0°-40°	1825.4	37.4
0°-60°	2990.6	61.4
0°-90°	3571.2	73.3
90°-120°	278.3	5.7
90°-150°	940.8	19.3
90°-180°	1303.0	26.7
0°-180°	4874.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	0	4	9	10	11	5
95°	22	24	27	29	29	24
105°	83	84	87	87	88	89
115°	157	158	157	158	157	155
125°	230	231	230	229	227	205
135°	298	300	300	299	298	230
145°	362	362	364	363	362	226
155°	414	414	415	416	413	191
165°	451	450	450	452	450	127
175°	469	468	468	470	467	45
180°	470	470	470	470	470	



TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.7	22.3	20.0	17.7	15.3	14.3	14.4	14.7	14.9	15.1	14.9
90°	0.4	1.2	2.0	2.9	3.7	4.6	5.6	6.8	7.8	8.9	9.2
92.5°	9.0	9.5	10.0	10.6	11.2	11.7	12.4	13.0	13.6	14.2	14.4
95°	21.8	22.3	22.9	23.6	24.1	24.7	25.4	26.0	26.7	27.3	27.6
97.5°	38.7	39.1	39.5	40.0	40.4	40.8	41.3	41.8	42.3	42.8	43.1
100°	50.2	50.7	51.2	51.7	52.2	52.7	53.1	53.5	53.9	54.3	54.5
102.5°	63.5	63.8	64.2	64.4	64.7	65.1	65.7	66.2	66.8	67.3	67.6
105°	83.2	83.3	83.5	83.6	83.8	84.2	85.0	85.7	86.4	87.2	87.2
107.5°	105.9	106.0	106.1	106.2	106.3	106.5	106.8	107.0	107.4	107.7	107.9
110°	120.1	120.3	120.4	120.6	120.7	120.9	121.1	121.2	121.4	121.6	121.9



TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.9	134.9	135.1	135.2	135.3	135.3	135.3	135.4	135.4	135.4	135.8
115°	157.0	157.3	157.5	157.8	158.0	158.1	157.9	157.8	157.6	157.4	157.5
117.5°	179.4	179.5	179.7	179.9	180.0	179.9	179.8	179.5	179.4	179.1	179.1
120°	193.2	193.7	194.2	194.7	195.2	195.3	194.9	194.4	194.0	193.6	193.6
122.5°	207.7	208.1	208.5	208.8	209.1	209.2	209.0	208.8	208.6	208.4	208.1
125°	229.8	230.1	230.3	230.6	230.8	230.8	230.6	230.5	230.3	230.2	229.8
127.5°	250.2	250.7	251.3	251.8	252.3	252.5	252.3	252.1	251.9	251.8	251.3
130°	263.8	264.5	265.1	265.8	266.4	266.6	266.4	266.1	265.9	265.6	265.3
132.5°	277.4	278.0	278.8	279.4	280.1	280.3	280.1	279.9	279.7	279.6	279.2
135°	298.2	298.6	299.1	299.6	300.1	300.4	300.3	300.2	300.1	300.0	299.7
137.5°	317.4	317.8	318.2	318.6	319.0	319.4	319.5	319.8	320.0	320.2	319.8
140°	330.7	331.1	331.5	331.9	332.3	332.6	332.6	332.7	332.8	332.9	332.8
142.5°	342.8	343.2	343.6	344.1	344.5	344.7	344.9	345.0	345.2	345.3	345.2
145°	361.7	361.9	362.1	362.2	362.4	362.6	362.8	363.1	363.3	363.5	363.5
147.5°	378.3	378.5	378.9	379.1	379.4	379.7	379.9	380.2	380.4	380.7	380.7
150°	389.8	390.0	390.1	390.3	390.4	390.6	390.8	390.9	391.1	391.3	391.3
152.5°	399.3	399.5	399.7	399.9	400.1	400.3	400.4	400.6	400.6	400.7	400.9
155°	414.2	414.2	414.2	414.2	414.2	414.3	414.3	414.4	414.5	414.6	414.9
157.5°	426.9	426.8	426.7	426.6	426.5	426.5	426.6	426.6	426.6	426.7	427.1
160°	434.9	434.7	434.6	434.4	434.2	434.1	434.1	434.1	434.1	434.1	434.6
162.5°	442.0	441.7	441.5	441.2	441.1	441.0	441.0	441.1	441.2	441.2	441.6
165°	451.1	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.5
167.5°	458.4	458.1	457.8	457.5	457.1	457.0	457.1	457.1	457.2	457.2	457.8
170°	462.6	462.3	461.9	461.6	461.3	461.1	461.1	461.1	461.1	461.1	461.7
172.5°	465.9	465.5	465.2	464.9	464.5	464.3	464.3	464.3	464.3	464.3	464.9
175°	469.2	468.9	468.6	468.2	467.9	467.7	467.7	467.7	467.7	467.7	468.2
177.5°	470.7	470.3	470.1	469.9	469.6	469.4	469.4	469.4	469.4	469.4	469.9
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3



TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	14.8	14.6	14.4	14.3	14.1	13.9	13.7	13.5
90°	9.5	9.9	10.2	10.4	10.6	10.8	10.9	11.1
92.5°	14.7	15.0	15.2	15.3	15.2	15.1	15.0	14.9
95°	28.0	28.3	28.6	28.8	28.8	28.8	28.8	28.8
97.5°	43.5	43.9	44.3	44.4	44.4	44.4	44.4	44.4
100°	54.8	55.0	55.3	55.5	55.7	55.8	56.0	56.2
102.5°	67.8	68.1	68.3	68.4	68.4	68.3	68.3	68.2
105°	87.2	87.2	87.2	87.2	87.5	87.6	87.8	88.0
107.5°	108.2	108.4	108.7	108.8	108.7	108.6	108.5	108.4
110°	122.2	122.5	122.9	122.9	122.8	122.6	122.5	122.3





TEST NUMBER: P332473-930

CATALOG NUMBER: S123RDIW-S1165D460U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	136.2	136.6	137.1	137.2	137.1	137.1	137.1	137.1
115°	157.6	157.7	157.8	157.8	157.7	157.6	157.5	157.4
117.5°	179.1	179.0	179.0	179.0	178.7	178.5	178.2	178.0
120°	193.5	193.4	193.3	193.1	193.0	192.8	192.7	192.5
122.5°	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.4
125°	229.5	229.2	228.9	228.5	228.2	227.9	227.6	227.2
127.5°	250.9	250.4	249.9	249.5	249.2	248.7	248.3	248.0
130°	265.0	264.6	264.3	263.9	263.3	262.8	262.2	261.5
132.5°	278.8	278.3	277.9	277.5	277.1	276.6	276.2	275.7
135°	299.4	299.1	298.7	298.5	298.3	298.2	298.0	297.8
137.5°	319.5	319.2	318.8	318.5	318.1	317.9	317.6	317.2
140°	332.7	332.6	332.6	332.2	331.7	331.1	330.5	330.0
142.5°	345.1	345.0	345.0	344.7	344.3	343.8	343.4	342.9
145°	363.4	363.3	363.2	363.1	362.7	362.4	362.1	361.7
147.5°	380.7	380.7	380.7	380.4	379.9	379.4	378.9	378.4
150°	391.3	391.3	391.3	391.0	390.5	390.0	389.6	389.1
152.5°	401.0	401.1	401.3	401.1	400.7	400.2	399.8	399.4
155°	415.2	415.6	415.9	415.7	415.2	414.6	414.0	413.4
157.5°	427.5	427.8	428.1	428.0	427.6	427.1	426.6	426.2
160°	435.0	435.4	435.8	435.8	435.5	435.1	434.8	434.5
162.5°	442.1	442.5	442.9	442.8	442.3	441.7	441.2	440.7
165°	451.0	451.5	452.0	451.9	451.3	450.8	450.2	449.6
167.5°	458.3	458.8	459.3	459.3	458.8	458.3	457.8	457.2
170°	462.3	462.8	463.4	463.4	462.8	462.3	461.7	461.1
172.5°	465.4	465.9	466.4	466.4	465.8	465.2	464.6	464.1
175°	468.7	469.2	469.7	469.7	469.1	468.6	468.0	467.4
177.5°	470.3	470.7	471.0	471.0	470.5	470.1	469.6	469.1
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3

(END OF REPORT)