

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332477-930

Luminaire Tested: **S123RDIW-S1165D755U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332477-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5706.4 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	51	49	45
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43	39
4	78	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32	30
6	66	54	46	40	62	51	44	38	45	39	35	40	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	2.6
10°-20°	412.9	7.2
20°-30°	594.5	10.4
30°-40°	669.6	11.7
40°-50°	640.6	11.2
50°-60°	524.6	9.2
60°-70°	354.0	6.2
70°-80°	178.1	3.1
80°-90°	49.4	0.9
90°-100°	50.2	0.9
100°-110°	150.2	2.6
110°-120°	255.5	4.5
120°-130°	336.1	5.9
130°-140°	377.7	6.6
140°-150°	371.3	6.5
150°-160°	312.6	5.5
160°-170°	208.1	3.6
170°-180°	72.9	1.3
0°-30°	1155.7	20.3
0°-40°	1825.4	32.0
0°-60°	2990.6	52.4
0°-90°	3572.1	62.6
90°-120°	455.9	8.0
90°-150°	1540.9	27.0
90°-180°	2134.0	37.4
0°-180°	5706.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	1	7	14	17	18	6
95°	36	40	45	47	47	40
105°	136	138	143	143	144	146
115°	257	259	258	258	258	254
125°	376	378	377	375	372	336
135°	488	492	491	489	488	376
145°	592	594	596	595	592	370
155°	678	678	679	681	677	312
165°	739	737	737	740	736	208
175°	768	766	766	769	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.7	22.5	20.2	18.0	15.8	14.8	15.2	15.6	15.9	16.2	16.1
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1
92.5°	14.7	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6
95°	35.7	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3
97.5°	63.4	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7
100°	82.3	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4
102.5°	104.1	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6
105°	136.2	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8
107.5°	173.4	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8
110°	196.7	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5
115°	257.2	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0
117.5°	293.8	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3
120°	316.5	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0
122.5°	340.2	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0
125°	376.4	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5
127.5°	409.8	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6
130°	432.1	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6
132.5°	454.4	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2
135°	488.4	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8
137.5°	519.8	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8
140°	541.6	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.5	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4
145°	592.5	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3
147.5°	619.5	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5
150°	638.5	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8
152.5°	654.0	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6
155°	678.4	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6
157.5°	699.2	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5
160°	712.2	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8
162.5°	723.9	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3
165°	738.9	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8
167.5°	750.9	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7
170°	757.7	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2
172.5°	763.0	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4
175°	768.5	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0
177.5°	770.9	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	16.0	15.9	15.7	15.6	15.4	15.2	15.1	14.9
90°	15.6	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.1	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	45.8	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.3	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	89.8	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.0	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.2	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.2	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332477-930

CATALOG NUMBER: S123RDIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.8	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.6	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.9	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.8	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	434.1	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	456.6	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	490.3	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	523.3	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.3	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.2	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	656.8	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.0	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.1	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	712.4	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.0	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	738.7	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	762.2	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	767.8	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.2	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)