

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332423-930

Luminaire Tested: **S123RDIW-S560D1320U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332423-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1320U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5549.8 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33			33
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	35	35	28			28
2	86	79	73	69	77	72	67	63	57	54	51	44	42	40	32	31	30	24			24
3	79	70	63	58	71	63	57	53	51	47	43	40	37	34	29	27	26	21			21
4	72	62	55	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18			18
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16			16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14			14
7	56	45	37	32	51	41	34	30	33	28	25	26	23	20	20	17	16	13			13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12			12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	14	13	11			11
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7851	7851	7851	7851
5°	9360	7886	6944	7886
10°	11687	7840	6274	7840
15°	13718	7759	5721	7759
20°	15309	7640	5251	7640
25°	15064	7514	4962	7514
30°	10828	7398	4666	7398
35°	7230	7247	4473	7247
40°	5327	7065	4274	7065
45°	4468	6745	4078	6745
50°	3944	6328	3806	6328
55°	3459	5849	3434	5849
60°	3078	5393	3147	5393
65°	2705	4898	2929	4898
70°	2121	4463	2675	4463
75°	1871	3897	2441	3897
80°	1630	3310	2399	3310
85°	1309	2655	2544	2655



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	1.3
10°-20°	224.1	4.0
20°-30°	352.1	6.3
30°-40°	367.3	6.6
40°-50°	314.4	5.7
50°-60°	239.6	4.3
60°-70°	153.6	2.8
70°-80°	73.9	1.3
80°-90°	23.5	0.4
90°-100°	87.7	1.6
100°-110°	262.5	4.7
110°-120°	446.4	8.0
120°-130°	587.2	10.6
130°-140°	660.0	11.9
140°-150°	648.8	11.7
150°-160°	546.2	9.8
160°-170°	363.6	6.6
170°-180°	127.3	2.3
0°-30°	647.9	11.7
0°-40°	1015.3	18.3
0°-60°	1569.3	28.3
0°-90°	1820.3	32.8
90°-120°	796.6	14.4
90°-150°	2692.5	48.5
90°-180°	3730.0	67.2
0°-180°	5549.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	729	729	729	729	729	
5°	866	730	643	730	866	89
15°	1231	696	513	696	1231	349
25°	1268	633	418	633	1268	545
35°	550	552	340	552	550	361
45°	294	443	268	443	294	231
55°	184	312	183	312	184	167
65°	106	192	115	192	106	104
75°	45	94	59	94	45	48
85°	11	22	21	22	11	13
90°	32	1	32	1	32	16
95°	82	62	82	62	82	85
105°	252	238	252	238	252	267
115°	450	449	450	449	450	446
125°	650	658	650	658	650	581
135°	852	853	852	853	852	655
145°	1035	1035	1035	1035	1035	646
155°	1183	1185	1183	1185	1183	545
165°	1287	1291	1287	1291	1287	363
175°	1338	1343	1338	1343	1338	127
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	776.9	778.0	774.7	774.2	770.5	769.5	769.5	764.2	760.9	756.7	754.2
5°	866.3	871.2	868.8	863.2	853.8	851.6	845.6	836.3	825.7	812.5	806.3
7.5°	977.8	984.6	981.9	973.3	963.5	955.5	938.8	923.2	901.5	882.4	866.0
10°	1069.3	1062.0	1056.5	1048.0	1038.9	1024.3	1006.8	982.8	955.0	933.1	908.7
12.5°	1137.7	1136.5	1129.4	1120.7	1107.9	1094.0	1072.4	1043.2	1010.9	979.3	951.5
15°	1231.0	1232.9	1228.2	1219.1	1201.0	1176.3	1143.9	1131.7	1085.5	1051.1	1016.8
17.5°	1295.6	1295.2	1294.5	1282.0	1263.6	1245.9	1215.9	1183.8	1142.0	1093.6	1047.3
20°	1336.5	1333.4	1334.1	1320.0	1306.3	1286.0	1256.6	1210.1	1175.7	1119.8	1072.0
22.5°	1335.5	1334.9	1337.3	1332.4	1322.5	1306.9	1283.9	1244.6	1200.7	1144.3	1090.5
25°	1268.4	1266.0	1280.7	1284.7	1300.6	1303.4	1296.6	1275.0	1233.5	1175.4	1108.9
27.5°	1061.6	1060.2	1087.4	1121.5	1164.8	1198.4	1230.9	1246.5	1233.5	1191.9	1125.3
30°	871.2	900.6	914.4	963.7	1018.6	1084.2	1141.7	1196.3	1209.7	1191.6	1137.0
32.5°	723.3	748.9	760.4	802.8	854.0	930.8	1017.0	1094.4	1149.1	1162.9	1130.0
35°	550.2	550.6	576.7	595.5	642.9	721.9	805.7	909.3	1012.4	1090.5	1098.6
37.5°	439.0	440.6	456.5	475.2	510.8	552.5	626.2	712.4	831.4	951.3	1021.6
40°	379.1	381.9	393.8	412.2	437.8	469.4	526.8	608.0	707.3	840.7	949.7
42.5°	340.6	345.2	351.3	365.5	381.3	410.9	457.4	520.1	610.3	736.5	862.2
45°	293.5	296.0	300.7	307.3	321.6	342.3	373.5	415.6	490.6	592.1	718.0
47.5°	258.9	257.6	262.5	267.9	277.4	291.5	312.4	346.8	400.3	481.7	588.5
50°	235.5	235.1	238.6	242.6	251.7	262.0	279.2	305.1	347.6	415.0	512.7
52.5°	213.4	214.7	217.1	222.2	228.7	237.0	252.4	271.1	307.6	365.8	447.3
55°	184.3	185.2	188.6	191.4	196.1	204.6	214.3	229.8	254.8	295.4	362.6
57.5°	159.5	159.1	162.4	163.1	168.4	175.2	182.7	194.9	213.0	243.1	288.4
60°	143.0	142.1	144.9	147.1	149.9	155.5	161.8	173.7	188.0	210.2	248.9
62.5°	128.0	127.6	129.6	131.8	134.1	139.3	144.6	153.6	165.0	183.7	214.4
65°	106.2	107.1	108.0	109.0	110.2	113.3	118.4	124.6	132.4	145.5	167.7
67.5°	83.4	84.4	84.7	86.6	89.3	91.2	94.3	99.9	105.3	116.3	129.0
70°	67.4	67.1	67.4	68.4	71.8	75.3	79.3	83.4	86.8	94.7	105.3
72.5°	58.0	57.4	58.2	58.4	60.1	61.0	63.6	67.4	71.8	77.1	84.8
75°	45.0	45.0	45.0	45.0	46.2	46.9	47.8	48.8	50.3	52.7	58.4
77.5°	33.3	33.3	33.8	34.0	34.3	34.7	35.2	36.2	36.7	38.1	40.4
80°	26.3	26.6	26.3	26.6	26.6	27.1	27.5	28.5	28.7	30.3	31.2
82.5°	19.7	19.6	19.7	20.1	20.1	20.7	20.7	21.4	21.5	22.3	23.2
85°	10.6	10.0	10.6	10.3	10.9	10.3	10.6	11.3	11.3	11.6	12.8
87.5°	8.8	9.2	8.6	8.8	8.7	8.8	8.6	8.5	8.7	8.3	8.0
90°	31.7	31.2	30.8	30.3	29.8	29.1	28.2	27.2	26.3	25.4	22.3
92.5°	42.7	43.0	43.3	43.5	43.9	43.6	42.9	42.1	41.3	40.6	38.9
95°	82.5	82.5	82.5	82.5	82.5	82.0	81.0	80.1	79.2	78.3	76.4
97.5°	126.9	127.0	127.1	127.2	127.3	126.8	125.7	124.6	123.5	122.5	121.1
100°	160.7	160.3	159.8	159.3	158.8	158.2	157.5	156.9	156.1	155.5	154.3
102.5°	195.4	195.5	195.6	195.7	195.8	195.5	194.8	194.0	193.4	192.7	191.1
105°	251.7	251.2	250.7	250.3	249.8	249.6	249.6	249.6	249.6	249.6	247.4
107.5°	310.2	310.5	310.8	311.1	311.4	311.1	310.4	309.7	308.9	308.1	307.3
110°	350.0	350.5	351.0	351.4	351.9	351.6	350.7	349.8	348.9	347.9	347.4



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	392.3	392.4	392.5	392.6	392.6	392.2	391.0	389.9	388.8	387.7	387.6
115°	450.5	450.7	450.9	451.2	451.4	451.4	451.2	450.9	450.7	450.5	450.9
117.5°	509.5	510.1	510.8	511.4	512.1	512.4	512.5	512.6	512.6	512.7	513.2
120°	550.9	551.4	551.9	552.4	552.8	553.2	553.4	553.6	553.8	554.1	555.3
122.5°	590.7	591.3	592.0	592.6	593.3	593.9	594.5	595.2	595.7	596.4	597.0
125°	650.3	651.3	652.2	653.1	654.1	655.0	656.0	656.9	657.9	658.8	659.3
127.5°	709.7	710.9	711.9	713.0	714.0	715.3	716.6	717.9	719.2	720.6	721.1
130°	748.7	750.3	752.0	753.6	755.2	756.5	757.5	758.4	759.4	760.3	761.0
132.5°	789.3	790.5	791.8	793.0	794.3	795.6	796.6	797.8	798.9	800.1	800.5
135°	852.3	852.7	853.2	853.7	854.2	854.8	855.8	856.7	857.7	858.6	858.8
137.5°	907.9	908.8	909.7	910.6	911.5	912.4	913.4	914.4	915.3	916.4	915.7
140°	944.3	945.9	947.5	949.3	950.9	951.8	952.0	952.3	952.5	952.8	952.5
142.5°	981.5	982.8	984.1	985.3	986.6	987.3	987.6	987.8	988.1	988.3	987.8
145°	1035.2	1036.2	1037.1	1038.0	1039.0	1039.6	1039.8	1040.0	1040.2	1040.5	1039.8
147.5°	1083.0	1084.4	1085.8	1087.3	1088.7	1089.3	1089.3	1089.3	1089.3	1089.3	1088.7
150°	1113.5	1114.8	1116.3	1117.7	1119.1	1119.8	1119.8	1119.8	1119.8	1119.8	1119.3
152.5°	1143.0	1144.3	1145.5	1146.7	1147.9	1148.3	1148.0	1147.6	1147.3	1146.9	1146.6
155°	1183.2	1184.9	1186.6	1188.2	1189.8	1190.2	1189.3	1188.3	1187.4	1186.4	1186.2
157.5°	1219.9	1221.2	1222.5	1223.8	1225.1	1225.3	1224.3	1223.3	1222.3	1221.3	1221.2
160°	1243.5	1244.5	1245.5	1246.3	1247.3	1247.2	1246.0	1244.8	1243.7	1242.4	1242.4
162.5°	1261.3	1262.8	1264.3	1265.8	1267.3	1267.5	1266.3	1265.1	1264.0	1262.7	1262.6
165°	1286.9	1288.5	1290.2	1291.8	1293.5	1293.6	1292.2	1290.8	1289.3	1287.9	1287.9
167.5°	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6	1308.5
170°	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6	1319.6
172.5°	1328.1	1329.8	1331.4	1333.1	1334.7	1334.8	1333.3	1331.9	1330.4	1328.9	1328.9
175°	1337.7	1339.3	1340.9	1342.6	1344.2	1344.3	1343.0	1341.5	1340.1	1338.7	1338.7
177.5°	1342.7	1344.0	1345.3	1346.6	1348.0	1348.1	1347.0	1345.8	1344.7	1343.5	1343.5
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	753.2	752.4	748.9	744.9	739.7	736.2	733.4	732.0	727.5	721.9	718.2
5°	799.7	790.4	780.4	768.2	756.9	745.4	738.3	729.8	719.5	707.9	699.8
7.5°	849.5	831.2	811.4	791.0	770.8	752.7	736.7	723.0	706.6	690.1	678.4
10°	887.8	861.0	833.2	804.7	778.8	754.5	735.7	717.3	697.7	678.6	664.2
12.5°	922.5	887.2	855.2	820.2	787.1	758.0	731.0	709.3	685.7	665.4	649.0
15°	966.5	930.3	891.5	838.5	794.4	757.6	724.8	696.3	667.6	642.7	626.7
17.5°	1007.5	953.1	901.1	856.7	799.6	753.5	713.5	679.5	648.0	621.5	601.9
20°	1024.6	971.8	915.3	858.8	802.6	751.1	704.5	667.0	634.2	604.2	586.1
22.5°	1034.8	975.0	915.5	854.8	795.1	741.5	695.5	654.3	618.7	590.3	567.9
25°	1046.8	975.5	910.0	850.0	789.1	731.0	676.4	632.7	594.3	563.9	540.2
27.5°	1054.6	970.9	893.3	826.7	764.9	707.1	657.0	610.7	571.7	539.6	514.2
30°	1056.1	967.1	880.6	808.5	745.7	692.6	639.5	595.2	554.0	519.9	496.2
32.5°	1058.1	957.9	863.4	786.8	722.5	669.9	621.8	579.4	537.2	503.7	479.5
35°	1049.9	952.8	837.2	749.2	684.9	633.9	590.5	551.5	510.0	477.4	452.8
37.5°	1014.4	932.5	810.1	706.8	639.5	592.4	557.0	523.0	484.9	449.9	426.6
40°	978.7	912.5	789.1	681.1	610.8	562.4	530.5	502.8	465.9	433.1	408.1
42.5°	925.4	885.3	769.2	654.1	578.3	531.7	504.8	478.7	446.5	413.1	389.6
45°	827.9	833.2	728.2	611.1	533.4	486.5	461.2	443.1	414.4	386.9	362.9
47.5°	705.4	755.0	680.2	565.3	486.0	442.0	419.9	404.1	384.7	357.8	335.8
50°	625.5	696.3	641.7	534.6	456.2	412.5	390.7	377.9	361.0	339.7	318.9
52.5°	551.8	627.9	595.3	500.3	424.0	384.0	362.6	352.1	338.8	318.8	299.9
55°	450.0	527.1	519.6	448.7	375.7	339.7	323.5	311.7	302.6	287.6	272.6
57.5°	363.9	437.1	441.0	391.3	333.0	297.6	283.6	274.7	268.7	257.5	243.6
60°	309.8	376.9	390.0	352.5	302.6	271.3	257.6	250.5	245.7	236.7	226.1
62.5°	264.8	322.0	336.8	309.8	273.4	244.1	233.4	226.5	223.3	215.5	206.1
65°	202.7	250.1	264.5	249.5	230.5	207.0	198.3	192.3	189.6	185.2	178.3
67.5°	152.4	187.0	202.8	192.2	185.3	170.5	164.9	161.8	159.2	156.3	150.5
70°	122.4	148.1	164.3	161.4	155.8	148.1	144.0	141.8	139.3	136.8	131.8
72.5°	98.4	116.0	131.3	132.7	128.1	126.5	122.9	122.1	120.5	117.6	114.8
75°	65.3	77.5	88.1	92.1	94.0	95.6	94.0	93.7	93.4	90.9	89.3
77.5°	42.8	49.3	56.0	62.9	65.9	68.0	68.5	69.6	68.8	67.5	66.8
80°	32.8	34.3	39.1	45.0	49.7	51.5	52.7	53.4	53.1	52.7	51.5
82.5°	23.8	25.1	27.3	31.5	35.4	38.6	39.3	39.1	39.9	40.0	39.1
85°	12.8	13.1	13.8	14.3	16.6	20.0	21.0	21.5	22.2	22.2	20.3
87.5°	7.8	7.0	6.8	6.4	6.6	6.4	7.4	8.2	8.9	8.4	8.9
90°	19.2	16.2	13.1	10.4	8.1	5.8	3.4	1.1	3.4	5.8	8.1
92.5°	37.1	35.4	33.7	32.0	30.4	28.8	27.1	25.6	27.1	28.8	30.4
95°	74.5	72.6	70.8	69.0	67.3	65.7	64.0	62.4	64.0	65.7	67.3
97.5°	119.7	118.4	117.0	115.7	114.5	113.2	112.0	110.8	112.0	113.2	114.5
100°	153.1	151.9	150.7	149.4	148.1	146.6	145.2	143.8	145.2	146.6	148.1
102.5°	189.6	188.0	186.5	185.2	184.4	183.6	182.7	181.9	182.7	183.6	184.4
105°	245.3	243.2	241.1	239.8	239.3	238.9	238.4	237.9	238.4	238.9	239.3
107.5°	306.5	305.6	304.8	304.2	303.9	303.6	303.4	303.0	303.4	303.6	303.9
110°	347.0	346.5	346.0	345.5	345.0	344.6	344.1	343.6	344.1	344.6	345.0



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.4	387.3	387.3	387.1	386.8	386.5	386.2	386.0	386.2	386.5	386.8
115°	451.4	451.8	452.3	452.2	451.5	450.8	450.1	449.4	450.1	450.8	451.5
117.5°	513.9	514.5	515.1	515.2	514.7	514.2	513.7	513.3	513.7	514.2	514.7
120°	556.4	557.6	558.8	558.6	557.3	555.9	554.4	553.0	554.4	555.9	557.3
122.5°	597.6	598.2	598.8	598.6	597.6	596.6	595.5	594.5	595.5	596.6	597.6
125°	659.7	660.1	660.6	660.6	659.8	659.1	658.4	657.7	658.4	659.1	659.8
127.5°	721.5	722.1	722.6	722.1	720.6	719.1	717.6	716.1	717.6	719.1	720.6
130°	761.7	762.4	763.1	762.5	760.7	758.8	756.8	755.0	756.8	758.8	760.7
132.5°	801.1	801.6	802.1	801.4	799.6	797.7	795.8	793.9	795.8	797.7	799.6
135°	859.1	859.3	859.6	859.0	857.5	856.1	854.8	853.4	854.8	856.1	857.5
137.5°	915.2	914.5	914.0	913.1	911.8	910.7	909.5	908.3	909.5	910.7	911.8
140°	952.3	952.0	951.8	951.1	949.9	948.8	947.5	946.4	947.5	948.8	949.9
142.5°	987.4	987.0	986.6	985.8	984.6	983.4	982.3	981.0	982.3	983.4	984.6
145°	1039.1	1038.4	1037.7	1037.1	1036.7	1036.2	1035.7	1035.2	1035.7	1036.2	1036.7
147.5°	1088.0	1087.4	1086.7	1086.0	1085.2	1084.3	1083.5	1082.6	1083.5	1084.3	1085.2
150°	1118.8	1118.4	1117.9	1117.4	1117.0	1116.6	1116.1	1115.6	1116.1	1116.6	1117.0
152.5°	1146.3	1146.1	1145.7	1145.3	1144.6	1143.9	1143.3	1142.6	1143.3	1143.9	1144.6
155°	1185.9	1185.7	1185.5	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4
157.5°	1220.9	1220.7	1220.6	1220.6	1220.9	1221.2	1221.5	1221.7	1221.5	1221.2	1220.9
160°	1242.4	1242.4	1242.4	1242.7	1243.2	1243.7	1244.1	1244.6	1244.1	1243.7	1243.2
162.5°	1262.4	1262.2	1262.0	1262.2	1262.9	1263.6	1264.2	1264.9	1264.2	1263.6	1262.9
165°	1287.9	1287.9	1287.9	1288.3	1289.0	1289.7	1290.4	1291.1	1290.4	1289.7	1289.0
167.5°	1308.3	1308.1	1307.9	1308.3	1309.2	1310.2	1311.1	1312.1	1311.1	1310.2	1309.2
170°	1319.6	1319.6	1319.6	1320.1	1321.1	1322.0	1323.0	1323.9	1323.0	1322.0	1321.1
172.5°	1328.9	1328.9	1328.9	1329.4	1330.4	1331.3	1332.3	1333.2	1332.3	1331.3	1330.4
175°	1338.7	1338.7	1338.7	1339.1	1340.1	1341.1	1342.0	1343.0	1342.0	1341.1	1340.1
177.5°	1343.5	1343.5	1343.5	1343.9	1344.7	1345.4	1346.2	1347.0	1346.2	1345.4	1344.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	717.0	713.7	711.5	706.5	703.3	699.8	696.3	698.5	698.2	698.0	698.0
5°	692.9	685.7	679.2	670.7	665.4	658.9	653.9	653.3	654.5	650.1	647.7
7.5°	669.1	659.3	650.0	640.7	630.8	622.9	618.0	615.7	612.5	609.8	607.0
10°	652.3	640.8	631.7	620.2	609.6	600.2	594.3	590.2	588.0	585.8	581.8
12.5°	635.1	623.8	612.2	599.2	589.1	578.2	573.8	569.2	565.0	562.6	557.0
15°	609.8	595.2	583.0	569.2	558.1	547.4	541.2	532.1	530.8	527.7	522.1
17.5°	584.6	568.7	551.9	541.7	529.0	518.0	508.4	505.4	496.4	493.1	488.2
20°	564.6	549.9	537.1	523.7	505.2	495.0	487.5	483.4	476.2	471.8	468.7
22.5°	547.4	532.4	517.6	502.0	486.7	475.2	469.7	463.4	459.5	453.4	450.0
25°	522.8	506.5	488.7	471.8	460.9	452.2	443.4	437.8	432.2	429.3	423.1
27.5°	494.2	477.2	460.6	447.8	434.3	425.7	417.8	412.8	406.0	401.3	397.9
30°	478.4	458.4	444.1	432.5	415.3	407.2	401.3	395.0	390.0	385.1	381.6
32.5°	460.2	441.9	428.3	414.0	400.8	392.0	384.3	378.8	374.5	369.8	366.4
35°	431.5	416.3	402.2	387.8	378.1	369.1	360.0	355.4	351.3	346.9	343.8
37.5°	405.7	391.4	378.1	364.4	352.5	345.0	337.8	334.2	328.7	325.8	322.6
40°	389.7	375.7	361.3	348.2	335.7	330.1	323.5	318.2	313.2	311.0	307.6
42.5°	372.3	358.2	346.1	331.9	321.7	314.1	308.0	302.2	298.5	295.3	293.3
45°	346.3	333.8	322.0	307.9	298.2	291.6	284.8	279.5	276.1	273.9	270.4
47.5°	321.1	308.7	296.6	284.4	275.0	267.5	260.7	256.9	252.4	249.7	247.4
50°	302.9	291.6	278.8	267.6	258.3	250.8	245.2	240.4	236.4	232.9	231.4
52.5°	286.2	274.2	263.1	252.7	242.8	234.2	229.2	224.2	221.2	217.2	215.4
55°	258.5	247.0	237.7	227.3	217.7	210.5	204.2	199.8	196.7	192.3	189.9
57.5°	232.6	222.3	211.1	202.2	192.2	186.1	180.9	175.0	171.2	167.8	165.3
60°	215.2	203.3	193.6	185.2	176.4	168.6	164.0	159.2	155.2	151.7	149.6
62.5°	196.9	186.5	177.4	168.2	160.2	153.4	148.0	144.0	140.5	138.3	136.1
65°	168.9	160.9	151.5	144.0	136.5	131.5	127.1	123.7	121.2	119.6	117.7
67.5°	143.2	135.3	127.2	119.8	114.8	111.0	108.1	105.2	104.0	101.9	100.7
70°	126.5	118.4	111.2	105.6	100.5	97.8	95.9	93.7	92.5	89.9	88.7
72.5°	108.3	102.4	97.2	92.5	88.5	86.0	83.6	81.0	78.9	76.2	74.9
75°	85.3	80.0	75.9	72.7	70.3	66.9	63.4	60.6	59.7	58.7	58.4
77.5°	63.1	59.8	56.8	54.2	51.1	48.6	47.9	47.2	47.0	46.6	46.6
80°	49.7	46.6	44.4	41.3	39.4	39.4	39.4	38.7	39.1	39.1	39.1
82.5°	36.9	34.0	32.9	31.7	31.4	31.6	31.6	31.7	31.6	32.0	31.8
85°	19.1	19.3	20.0	19.6	20.0	20.0	20.6	20.3	20.6	20.0	20.6
87.5°	9.0	10.4	11.3	12.1	13.0	13.3	13.8	13.9	14.3	14.6	14.7
90°	10.4	13.1	16.2	19.2	22.3	25.4	26.3	27.2	28.2	29.1	29.8
92.5°	32.0	33.7	35.4	37.1	38.9	40.6	41.3	42.1	42.9	43.6	43.9
95°	69.0	70.8	72.6	74.5	76.4	78.3	79.2	80.1	81.0	82.0	82.5
97.5°	115.7	117.0	118.4	119.7	121.1	122.5	123.5	124.6	125.7	126.8	127.3
100°	149.4	150.7	151.9	153.1	154.3	155.5	156.1	156.9	157.5	158.2	158.8
102.5°	185.2	186.5	188.0	189.6	191.1	192.7	193.4	194.0	194.8	195.5	195.8
105°	239.8	241.1	243.2	245.3	247.4	249.6	249.6	249.6	249.6	249.6	249.8
107.5°	304.2	304.8	305.6	306.5	307.3	308.1	308.9	309.7	310.4	311.1	311.4
110°	345.5	346.0	346.5	347.0	347.4	347.9	348.9	349.8	350.7	351.6	351.9



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	387.1	387.3	387.3	387.4	387.6	387.7	388.8	389.9	391.0	392.2	392.6
115°	452.2	452.3	451.8	451.4	450.9	450.5	450.7	450.9	451.2	451.4	451.4
117.5°	515.2	515.1	514.5	513.9	513.2	512.7	512.6	512.6	512.5	512.4	512.1
120°	558.6	558.8	557.6	556.4	555.3	554.1	553.8	553.6	553.4	553.2	552.8
122.5°	598.6	598.8	598.2	597.6	597.0	596.4	595.7	595.2	594.5	593.9	593.3
125°	660.6	660.6	660.1	659.7	659.3	658.8	657.9	656.9	656.0	655.0	654.1
127.5°	722.1	722.6	722.1	721.5	721.1	720.6	719.2	717.9	716.6	715.3	714.0
130°	762.5	763.1	762.4	761.7	761.0	760.3	759.4	758.4	757.5	756.5	755.2
132.5°	801.4	802.1	801.6	801.1	800.5	800.1	798.9	797.8	796.6	795.6	794.3
135°	859.0	859.6	859.3	859.1	858.8	858.6	857.7	856.7	855.8	854.8	854.2
137.5°	913.1	914.0	914.5	915.2	915.7	916.4	915.3	914.4	913.4	912.4	911.5
140°	951.1	951.8	952.0	952.3	952.5	952.8	952.5	952.3	952.0	951.8	950.9
142.5°	985.8	986.6	987.0	987.4	987.8	988.3	988.1	987.8	987.6	987.3	986.6
145°	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2	1040.0	1039.8	1039.6	1039.0
147.5°	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3	1089.3	1089.3	1089.3	1088.7
150°	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8	1119.8	1119.8	1119.8	1119.1
152.5°	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3	1147.6	1148.0	1148.3	1147.9
155°	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4	1188.3	1189.3	1190.2	1189.8
157.5°	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3	1223.3	1224.3	1225.3	1225.1
160°	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7	1244.8	1246.0	1247.2	1247.3
162.5°	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0	1265.1	1266.3	1267.5	1267.3
165°	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3	1290.8	1292.2	1293.6	1293.5
167.5°	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5
170°	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2
172.5°	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4	1331.9	1333.3	1334.8	1334.7
175°	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1	1341.5	1343.0	1344.3	1344.2
177.5°	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7	1345.8	1347.0	1348.1	1348.0
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	695.0	694.7	695.0	694.0	695.0	694.7	695.0	698.0	698.0	698.2	698.5
5°	646.7	646.4	645.5	642.7	645.5	646.4	646.7	647.7	650.1	654.5	653.3
7.5°	604.5	604.1	601.4	601.4	601.4	604.1	604.5	607.0	609.8	612.5	615.7
10°	579.6	579.9	576.2	574.0	576.2	579.9	579.6	581.8	585.8	588.0	590.2
12.5°	555.4	553.9	550.9	548.5	550.9	553.9	555.4	557.0	562.6	565.0	569.2
15°	523.3	520.2	512.7	513.4	512.7	520.2	523.3	522.1	527.7	530.8	532.1
17.5°	485.7	483.4	483.3	478.9	483.3	483.4	485.7	488.2	493.1	496.4	505.4
20°	463.7	462.2	462.8	458.4	462.8	462.2	463.7	468.7	471.8	476.2	483.4
22.5°	446.5	444.9	442.3	440.9	442.3	444.9	446.5	450.0	453.4	459.5	463.4
25°	421.3	418.7	416.3	417.8	416.3	418.7	421.3	423.1	429.3	432.2	437.8
27.5°	396.0	394.1	391.7	391.3	391.7	394.1	396.0	397.9	401.3	406.0	412.8
30°	380.0	378.1	376.9	375.4	376.9	378.1	380.0	381.6	385.1	390.0	395.0
32.5°	363.8	363.5	361.2	360.9	361.2	363.5	363.8	366.4	369.8	374.5	378.8
35°	342.6	340.7	340.1	340.4	340.1	340.7	342.6	343.8	346.9	351.3	355.4
37.5°	322.4	319.9	318.8	317.6	318.8	319.9	322.4	322.6	325.8	328.7	334.2
40°	307.9	305.4	304.8	304.2	304.8	305.4	307.9	307.6	311.0	313.2	318.2
42.5°	291.6	290.7	290.3	289.2	290.3	290.7	291.6	293.3	295.3	298.5	302.2
45°	269.5	269.2	267.3	267.9	267.3	269.2	269.5	270.4	273.9	276.1	279.5
47.5°	246.1	244.8	243.4	244.3	243.4	244.8	246.1	247.4	249.7	252.4	256.9
50°	230.2	229.5	226.7	227.3	226.7	229.5	230.2	231.4	232.9	236.4	240.4
52.5°	214.2	211.8	210.8	210.3	210.8	211.8	214.2	215.4	217.2	221.2	224.2
55°	187.7	184.8	183.6	183.0	183.6	184.8	187.7	189.9	192.3	196.7	199.8
57.5°	161.7	160.9	160.0	160.6	160.0	160.9	161.7	165.3	167.8	171.2	175.0
60°	146.4	146.4	146.4	146.2	146.4	146.4	146.4	149.6	151.7	155.2	159.2
62.5°	134.7	134.0	133.7	134.1	133.7	134.0	134.7	136.1	138.3	140.5	144.0
65°	116.8	116.5	115.2	115.0	115.2	116.5	116.8	117.7	119.6	121.2	123.7
67.5°	99.9	98.7	98.4	97.9	98.4	98.7	99.9	100.7	101.9	104.0	105.2
70°	87.2	86.5	84.6	85.0	84.6	86.5	87.2	88.7	89.9	92.5	93.7
72.5°	73.4	72.7	72.4	71.9	72.4	72.7	73.4	74.9	76.2	78.9	81.0
75°	58.0	57.8	57.5	58.7	57.5	57.8	58.0	58.4	58.7	59.7	60.6
77.5°	46.6	46.6	46.7	46.2	46.7	46.6	46.6	46.6	46.6	47.0	47.2
80°	39.1	39.1	38.7	38.7	38.7	39.1	39.1	39.1	39.1	39.1	38.7
82.5°	31.3	31.6	31.7	31.2	31.7	31.6	31.3	31.8	32.0	31.6	31.7
85°	20.6	20.3	21.0	20.6	21.0	20.3	20.6	20.6	20.0	20.6	20.3
87.5°	15.3	14.9	15.0	15.3	15.0	14.9	15.3	14.7	14.6	14.3	13.9
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	29.1	28.2	27.2
92.5°	43.5	43.3	43.0	42.7	43.0	43.3	43.5	43.9	43.6	42.9	42.1
95°	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.0	81.0	80.1
97.5°	127.2	127.1	127.0	126.9	127.0	127.1	127.2	127.3	126.8	125.7	124.6
100°	159.3	159.8	160.3	160.7	160.3	159.8	159.3	158.8	158.2	157.5	156.9
102.5°	195.7	195.6	195.5	195.4	195.5	195.6	195.7	195.8	195.5	194.8	194.0
105°	250.3	250.7	251.2	251.7	251.2	250.7	250.3	249.8	249.6	249.6	249.6
107.5°	311.1	310.8	310.5	310.2	310.5	310.8	311.1	311.4	311.1	310.4	309.7
110°	351.4	351.0	350.5	350.0	350.5	351.0	351.4	351.9	351.6	350.7	349.8



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	392.6	392.5	392.4	392.3	392.4	392.5	392.6	392.6	392.2	391.0	389.9
115°	451.2	450.9	450.7	450.5	450.7	450.9	451.2	451.4	451.4	451.2	450.9
117.5°	511.4	510.8	510.1	509.5	510.1	510.8	511.4	512.1	512.4	512.5	512.6
120°	552.4	551.9	551.4	550.9	551.4	551.9	552.4	552.8	553.2	553.4	553.6
122.5°	592.6	592.0	591.3	590.7	591.3	592.0	592.6	593.3	593.9	594.5	595.2
125°	653.1	652.2	651.3	650.3	651.3	652.2	653.1	654.1	655.0	656.0	656.9
127.5°	713.0	711.9	710.9	709.7	710.9	711.9	713.0	714.0	715.3	716.6	717.9
130°	753.6	752.0	750.3	748.7	750.3	752.0	753.6	755.2	756.5	757.5	758.4
132.5°	793.0	791.8	790.5	789.3	790.5	791.8	793.0	794.3	795.6	796.6	797.8
135°	853.7	853.2	852.7	852.3	852.7	853.2	853.7	854.2	854.8	855.8	856.7
137.5°	910.6	909.7	908.8	907.9	908.8	909.7	910.6	911.5	912.4	913.4	914.4
140°	949.3	947.5	945.9	944.3	945.9	947.5	949.3	950.9	951.8	952.0	952.3
142.5°	985.3	984.1	982.8	981.5	982.8	984.1	985.3	986.6	987.3	987.6	987.8
145°	1038.0	1037.1	1036.2	1035.2	1036.2	1037.1	1038.0	1039.0	1039.6	1039.8	1040.0
147.5°	1087.3	1085.8	1084.4	1083.0	1084.4	1085.8	1087.3	1088.7	1089.3	1089.3	1089.3
150°	1117.7	1116.3	1114.8	1113.5	1114.8	1116.3	1117.7	1119.1	1119.8	1119.8	1119.8
152.5°	1146.7	1145.5	1144.3	1143.0	1144.3	1145.5	1146.7	1147.9	1148.3	1148.0	1147.6
155°	1188.2	1186.6	1184.9	1183.2	1184.9	1186.6	1188.2	1189.8	1190.2	1189.3	1188.3
157.5°	1223.8	1222.5	1221.2	1219.9	1221.2	1222.5	1223.8	1225.1	1225.3	1224.3	1223.3
160°	1246.3	1245.5	1244.5	1243.5	1244.5	1245.5	1246.3	1247.3	1247.2	1246.0	1244.8
162.5°	1265.8	1264.3	1262.8	1261.3	1262.8	1264.3	1265.8	1267.3	1267.5	1266.3	1265.1
165°	1291.8	1290.2	1288.5	1286.9	1288.5	1290.2	1291.8	1293.5	1293.6	1292.2	1290.8
167.5°	1313.0	1311.6	1310.1	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6
170°	1324.6	1323.0	1321.3	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0
172.5°	1333.1	1331.4	1329.8	1328.1	1329.8	1331.4	1333.1	1334.7	1334.8	1333.3	1331.9
175°	1342.6	1340.9	1339.3	1337.7	1339.3	1340.9	1342.6	1344.2	1344.3	1343.0	1341.5
177.5°	1346.6	1345.3	1344.0	1342.7	1344.0	1345.3	1346.6	1348.0	1348.1	1347.0	1345.8
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	696.3	699.8	703.3	706.5	711.5	713.7	717.0	718.2	721.9	727.5	732.0
5°	653.9	658.9	665.4	670.7	679.2	685.7	692.9	699.8	707.9	719.5	729.8
7.5°	618.0	622.9	630.8	640.7	650.0	659.3	669.1	678.4	690.1	706.6	723.0
10°	594.3	600.2	609.6	620.2	631.7	640.8	652.3	664.2	678.6	697.7	717.3
12.5°	573.8	578.2	589.1	599.2	612.2	623.8	635.1	649.0	665.4	685.7	709.3
15°	541.2	547.4	558.1	569.2	583.0	595.2	609.8	626.7	642.7	667.6	696.3
17.5°	508.4	518.0	529.0	541.7	551.9	568.7	584.6	601.9	621.5	648.0	679.5
20°	487.5	495.0	505.2	523.7	537.1	549.9	564.6	586.1	604.2	634.2	667.0
22.5°	469.7	475.2	486.7	502.0	517.6	532.4	547.4	567.9	590.3	618.7	654.3
25°	443.4	452.2	460.9	471.8	488.7	506.5	522.8	540.2	563.9	594.3	632.7
27.5°	417.8	425.7	434.3	447.8	460.6	477.2	494.2	514.2	539.6	571.7	610.7
30°	401.3	407.2	415.3	432.5	444.1	458.4	478.4	496.2	519.9	554.0	595.2
32.5°	384.3	392.0	400.8	414.0	428.3	441.9	460.2	479.5	503.7	537.2	579.4
35°	360.0	369.1	378.1	387.8	402.2	416.3	431.5	452.8	477.4	510.0	551.5
37.5°	337.8	345.0	352.5	364.4	378.1	391.4	405.7	426.6	449.9	484.9	523.0
40°	323.5	330.1	335.7	348.2	361.3	375.7	389.7	408.1	433.1	465.9	502.8
42.5°	308.0	314.1	321.7	331.9	346.1	358.2	372.3	389.6	413.1	446.5	478.7
45°	284.8	291.6	298.2	307.9	322.0	333.8	346.3	362.9	386.9	414.4	443.1
47.5°	260.7	267.5	275.0	284.4	296.6	308.7	321.1	335.8	357.8	384.7	404.1
50°	245.2	250.8	258.3	267.6	278.8	291.6	302.9	318.9	339.7	361.0	377.9
52.5°	229.2	234.2	242.8	252.7	263.1	274.2	286.2	299.9	318.8	338.8	352.1
55°	204.2	210.5	217.7	227.3	237.7	247.0	258.5	272.6	287.6	302.6	311.7
57.5°	180.9	186.1	192.2	202.2	211.1	222.3	232.6	243.6	257.5	268.7	274.7
60°	164.0	168.6	176.4	185.2	193.6	203.3	215.2	226.1	236.7	245.7	250.5
62.5°	148.0	153.4	160.2	168.2	177.4	186.5	196.9	206.1	215.5	223.3	226.5
65°	127.1	131.5	136.5	144.0	151.5	160.9	168.9	178.3	185.2	189.6	192.3
67.5°	108.1	111.0	114.8	119.8	127.2	135.3	143.2	150.5	156.3	159.2	161.8
70°	95.9	97.8	100.5	105.6	111.2	118.4	126.5	131.8	136.8	139.3	141.8
72.5°	83.6	86.0	88.5	92.5	97.2	102.4	108.3	114.8	117.6	120.5	122.1
75°	63.4	66.9	70.3	72.7	75.9	80.0	85.3	89.3	90.9	93.4	93.7
77.5°	47.9	48.6	51.1	54.2	56.8	59.8	63.1	66.8	67.5	68.8	69.6
80°	39.4	39.4	39.4	41.3	44.4	46.6	49.7	51.5	52.7	53.1	53.4
82.5°	31.6	31.6	31.4	31.7	32.9	34.0	36.9	39.1	40.0	39.9	39.1
85°	20.6	20.0	20.0	19.6	20.0	19.3	19.1	20.3	22.2	22.2	21.5
87.5°	13.8	13.3	13.0	12.1	11.3	10.4	9.0	8.9	8.4	8.9	8.2
90°	26.3	25.4	22.3	19.2	16.2	13.1	10.4	8.1	5.8	3.4	1.1
92.5°	41.3	40.6	38.9	37.1	35.4	33.7	32.0	30.4	28.8	27.1	25.6
95°	79.2	78.3	76.4	74.5	72.6	70.8	69.0	67.3	65.7	64.0	62.4
97.5°	123.5	122.5	121.1	119.7	118.4	117.0	115.7	114.5	113.2	112.0	110.8
100°	156.1	155.5	154.3	153.1	151.9	150.7	149.4	148.1	146.6	145.2	143.8
102.5°	193.4	192.7	191.1	189.6	188.0	186.5	185.2	184.4	183.6	182.7	181.9
105°	249.6	249.6	247.4	245.3	243.2	241.1	239.8	239.3	238.9	238.4	237.9
107.5°	308.9	308.1	307.3	306.5	305.6	304.8	304.2	303.9	303.6	303.4	303.0
110°	348.9	347.9	347.4	347.0	346.5	346.0	345.5	345.0	344.6	344.1	343.6



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.8	387.7	387.6	387.4	387.3	387.3	387.1	386.8	386.5	386.2	386.0
115°	450.7	450.5	450.9	451.4	451.8	452.3	452.2	451.5	450.8	450.1	449.4
117.5°	512.6	512.7	513.2	513.9	514.5	515.1	515.2	514.7	514.2	513.7	513.3
120°	553.8	554.1	555.3	556.4	557.6	558.8	558.6	557.3	555.9	554.4	553.0
122.5°	595.7	596.4	597.0	597.6	598.2	598.8	598.6	597.6	596.6	595.5	594.5
125°	657.9	658.8	659.3	659.7	660.1	660.6	660.6	659.8	659.1	658.4	657.7
127.5°	719.2	720.6	721.1	721.5	722.1	722.6	722.1	720.6	719.1	717.6	716.1
130°	759.4	760.3	761.0	761.7	762.4	763.1	762.5	760.7	758.8	756.8	755.0
132.5°	798.9	800.1	800.5	801.1	801.6	802.1	801.4	799.6	797.7	795.8	793.9
135°	857.7	858.6	858.8	859.1	859.3	859.6	859.0	857.5	856.1	854.8	853.4
137.5°	915.3	916.4	915.7	915.2	914.5	914.0	913.1	911.8	910.7	909.5	908.3
140°	952.5	952.8	952.5	952.3	952.0	951.8	951.1	949.9	948.8	947.5	946.4
142.5°	988.1	988.3	987.8	987.4	987.0	986.6	985.8	984.6	983.4	982.3	981.0
145°	1040.2	1040.5	1039.8	1039.1	1038.4	1037.7	1037.1	1036.7	1036.2	1035.7	1035.2
147.5°	1089.3	1089.3	1088.7	1088.0	1087.4	1086.7	1086.0	1085.2	1084.3	1083.5	1082.6
150°	1119.8	1119.8	1119.3	1118.8	1118.4	1117.9	1117.4	1117.0	1116.6	1116.1	1115.6
152.5°	1147.3	1146.9	1146.6	1146.3	1146.1	1145.7	1145.3	1144.6	1143.9	1143.3	1142.6
155°	1187.4	1186.4	1186.2	1185.9	1185.7	1185.5	1185.4	1185.4	1185.4	1185.4	1185.4
157.5°	1222.3	1221.3	1221.2	1220.9	1220.7	1220.6	1220.6	1220.9	1221.2	1221.5	1221.7
160°	1243.7	1242.4	1242.4	1242.4	1242.4	1242.4	1242.7	1243.2	1243.7	1244.1	1244.6
162.5°	1264.0	1262.7	1262.6	1262.4	1262.2	1262.0	1262.2	1262.9	1263.6	1264.2	1264.9
165°	1289.3	1287.9	1287.9	1287.9	1287.9	1287.9	1288.3	1289.0	1289.7	1290.4	1291.1
167.5°	1310.1	1308.6	1308.5	1308.3	1308.1	1307.9	1308.3	1309.2	1310.2	1311.1	1312.1
170°	1321.3	1319.6	1319.6	1319.6	1319.6	1319.6	1320.1	1321.1	1322.0	1323.0	1323.9
172.5°	1330.4	1328.9	1328.9	1328.9	1328.9	1328.9	1329.4	1330.4	1331.3	1332.3	1333.2
175°	1340.1	1338.7	1338.7	1338.7	1338.7	1338.7	1339.1	1340.1	1341.1	1342.0	1343.0
177.5°	1344.7	1343.5	1343.5	1343.5	1343.5	1343.5	1343.9	1344.7	1345.4	1346.2	1347.0
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	733.4	736.2	739.7	744.9	748.9	752.4	753.2	754.2	756.7	760.9	764.2
5°	738.3	745.4	756.9	768.2	780.4	790.4	799.7	806.3	812.5	825.7	836.3
7.5°	736.7	752.7	770.8	791.0	811.4	831.2	849.5	866.0	882.4	901.5	923.2
10°	735.7	754.5	778.8	804.7	833.2	861.0	887.8	908.7	933.1	955.0	982.8
12.5°	731.0	758.0	787.1	820.2	855.2	887.2	922.5	951.5	979.3	1010.9	1043.2
15°	724.8	757.6	794.4	838.5	891.5	930.3	966.5	1016.8	1051.1	1085.5	1131.7
17.5°	713.5	753.5	799.6	856.7	901.1	953.1	1007.5	1047.3	1093.6	1142.0	1183.8
20°	704.5	751.1	802.6	858.8	915.3	971.8	1024.6	1072.0	1119.8	1175.7	1210.1
22.5°	695.5	741.5	795.1	854.8	915.5	975.0	1034.8	1090.5	1144.3	1200.7	1244.6
25°	676.4	731.0	789.1	850.0	910.0	975.5	1046.8	1108.9	1175.4	1233.5	1275.0
27.5°	657.0	707.1	764.9	826.7	893.3	970.9	1054.6	1125.3	1191.9	1233.5	1246.5
30°	639.5	692.6	745.7	808.5	880.6	967.1	1056.1	1137.0	1191.6	1209.7	1196.3
32.5°	621.8	669.9	722.5	786.8	863.4	957.9	1058.1	1130.0	1162.9	1149.1	1094.4
35°	590.5	633.9	684.9	749.2	837.2	952.8	1049.9	1098.6	1090.5	1012.4	909.3
37.5°	557.0	592.4	639.5	706.8	810.1	932.5	1014.4	1021.6	951.3	831.4	712.4
40°	530.5	562.4	610.8	681.1	789.1	912.5	978.7	949.7	840.7	707.3	608.0
42.5°	504.8	531.7	578.3	654.1	769.2	885.3	925.4	862.2	736.5	610.3	520.1
45°	461.2	486.5	533.4	611.1	728.2	833.2	827.9	718.0	592.1	490.6	415.6
47.5°	419.9	442.0	486.0	565.3	680.2	755.0	705.4	588.5	481.7	400.3	346.8
50°	390.7	412.5	456.2	534.6	641.7	696.3	625.5	512.7	415.0	347.6	305.1
52.5°	362.6	384.0	424.0	500.3	595.3	627.9	551.8	447.3	365.8	307.6	271.1
55°	323.5	339.7	375.7	448.7	519.6	527.1	450.0	362.6	295.4	254.8	229.8
57.5°	283.6	297.6	333.0	391.3	441.0	437.1	363.9	288.4	243.1	213.0	194.9
60°	257.6	271.3	302.6	352.5	390.0	376.9	309.8	248.9	210.2	188.0	173.7
62.5°	233.4	244.1	273.4	309.8	336.8	322.0	264.8	214.4	183.7	165.0	153.6
65°	198.3	207.0	230.5	249.5	264.5	250.1	202.7	167.7	145.5	132.4	124.6
67.5°	164.9	170.5	185.3	192.2	202.8	187.0	152.4	129.0	116.3	105.3	99.9
70°	144.0	148.1	155.8	161.4	164.3	148.1	122.4	105.3	94.7	86.8	83.4
72.5°	122.9	126.5	128.1	132.7	131.3	116.0	98.4	84.8	77.1	71.8	67.4
75°	94.0	95.6	94.0	92.1	88.1	77.5	65.3	58.4	52.7	50.3	48.8
77.5°	68.5	68.0	65.9	62.9	56.0	49.3	42.8	40.4	38.1	36.7	36.2
80°	52.7	51.5	49.7	45.0	39.1	34.3	32.8	31.2	30.3	28.7	28.5
82.5°	39.3	38.6	35.4	31.5	27.3	25.1	23.8	23.2	22.3	21.5	21.4
85°	21.0	20.0	16.6	14.3	13.8	13.1	12.8	12.8	11.6	11.3	11.3
87.5°	7.4	6.4	6.6	6.4	6.8	7.0	7.8	8.0	8.3	8.7	8.5
90°	3.4	5.8	8.1	10.4	13.1	16.2	19.2	22.3	25.4	26.3	27.2
92.5°	27.1	28.8	30.4	32.0	33.7	35.4	37.1	38.9	40.6	41.3	42.1
95°	64.0	65.7	67.3	69.0	70.8	72.6	74.5	76.4	78.3	79.2	80.1
97.5°	112.0	113.2	114.5	115.7	117.0	118.4	119.7	121.1	122.5	123.5	124.6
100°	145.2	146.6	148.1	149.4	150.7	151.9	153.1	154.3	155.5	156.1	156.9
102.5°	182.7	183.6	184.4	185.2	186.5	188.0	189.6	191.1	192.7	193.4	194.0
105°	238.4	238.9	239.3	239.8	241.1	243.2	245.3	247.4	249.6	249.6	249.6
107.5°	303.4	303.6	303.9	304.2	304.8	305.6	306.5	307.3	308.1	308.9	309.7
110°	344.1	344.6	345.0	345.5	346.0	346.5	347.0	347.4	347.9	348.9	349.8



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	386.2	386.5	386.8	387.1	387.3	387.3	387.4	387.6	387.7	388.8	389.9
115°	450.1	450.8	451.5	452.2	452.3	451.8	451.4	450.9	450.5	450.7	450.9
117.5°	513.7	514.2	514.7	515.2	515.1	514.5	513.9	513.2	512.7	512.6	512.6
120°	554.4	555.9	557.3	558.6	558.8	557.6	556.4	555.3	554.1	553.8	553.6
122.5°	595.5	596.6	597.6	598.6	598.8	598.2	597.6	597.0	596.4	595.7	595.2
125°	658.4	659.1	659.8	660.6	660.6	660.1	659.7	659.3	658.8	657.9	656.9
127.5°	717.6	719.1	720.6	722.1	722.6	722.1	721.5	721.1	720.6	719.2	717.9
130°	756.8	758.8	760.7	762.5	763.1	762.4	761.7	761.0	760.3	759.4	758.4
132.5°	795.8	797.7	799.6	801.4	802.1	801.6	801.1	800.5	800.1	798.9	797.8
135°	854.8	856.1	857.5	859.0	859.6	859.3	859.1	858.8	858.6	857.7	856.7
137.5°	909.5	910.7	911.8	913.1	914.0	914.5	915.2	915.7	916.4	915.3	914.4
140°	947.5	948.8	949.9	951.1	951.8	952.0	952.3	952.5	952.8	952.5	952.3
142.5°	982.3	983.4	984.6	985.8	986.6	987.0	987.4	987.8	988.3	988.1	987.8
145°	1035.7	1036.2	1036.7	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2	1040.0
147.5°	1083.5	1084.3	1085.2	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3	1089.3
150°	1116.1	1116.6	1117.0	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8	1119.8
152.5°	1143.3	1143.9	1144.6	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3	1147.6
155°	1185.4	1185.4	1185.4	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4	1188.3
157.5°	1221.5	1221.2	1220.9	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3	1223.3
160°	1244.1	1243.7	1243.2	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7	1244.8
162.5°	1264.2	1263.6	1262.9	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0	1265.1
165°	1290.4	1289.7	1289.0	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3	1290.8
167.5°	1311.1	1310.2	1309.2	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1	1311.6
170°	1323.0	1322.0	1321.1	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3	1323.0
172.5°	1332.3	1331.3	1330.4	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4	1331.9
175°	1342.0	1341.1	1340.1	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1	1341.5
177.5°	1346.2	1345.4	1344.7	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7	1345.8
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	769.5	769.5	770.5	774.2	774.7	778.0	776.9
5°	845.6	851.6	853.8	863.2	868.8	871.2	866.3
7.5°	938.8	955.5	963.5	973.3	981.9	984.6	977.8
10°	1006.8	1024.3	1038.9	1048.0	1056.5	1062.0	1069.3
12.5°	1072.4	1094.0	1107.9	1120.7	1129.4	1136.5	1137.7
15°	1143.9	1176.3	1201.0	1219.1	1228.2	1232.9	1231.0
17.5°	1215.9	1245.9	1263.6	1282.0	1294.5	1295.2	1295.6
20°	1256.6	1286.0	1306.3	1320.0	1334.1	1333.4	1336.5
22.5°	1283.9	1306.9	1322.5	1332.4	1337.3	1334.9	1335.5
25°	1296.6	1303.4	1300.6	1284.7	1280.7	1266.0	1268.4
27.5°	1230.9	1198.4	1164.8	1121.5	1087.4	1060.2	1061.6
30°	1141.7	1084.2	1018.6	963.7	914.4	900.6	871.2
32.5°	1017.0	930.8	854.0	802.8	760.4	748.9	723.3
35°	805.7	721.9	642.9	595.5	576.7	550.6	550.2
37.5°	626.2	552.5	510.8	475.2	456.5	440.6	439.0
40°	526.8	469.4	437.8	412.2	393.8	381.9	379.1
42.5°	457.4	410.9	381.3	365.5	351.3	345.2	340.6
45°	373.5	342.3	321.6	307.3	300.7	296.0	293.5
47.5°	312.4	291.5	277.4	267.9	262.5	257.6	258.9
50°	279.2	262.0	251.7	242.6	238.6	235.1	235.5
52.5°	252.4	237.0	228.7	222.2	217.1	214.7	213.4
55°	214.3	204.6	196.1	191.4	188.6	185.2	184.3
57.5°	182.7	175.2	168.4	163.1	162.4	159.1	159.5
60°	161.8	155.5	149.9	147.1	144.9	142.1	143.0
62.5°	144.6	139.3	134.1	131.8	129.6	127.6	128.0
65°	118.4	113.3	110.2	109.0	108.0	107.1	106.2
67.5°	94.3	91.2	89.3	86.6	84.7	84.4	83.4
70°	79.3	75.3	71.8	68.4	67.4	67.1	67.4
72.5°	63.6	61.0	60.1	58.4	58.2	57.4	58.0
75°	47.8	46.9	46.2	45.0	45.0	45.0	45.0
77.5°	35.2	34.7	34.3	34.0	33.8	33.3	33.3
80°	27.5	27.1	26.6	26.6	26.3	26.6	26.3
82.5°	20.7	20.7	20.1	20.1	19.7	19.6	19.7
85°	10.6	10.3	10.9	10.3	10.6	10.0	10.6
87.5°	8.6	8.8	8.7	8.8	8.6	9.2	8.8
90°	28.2	29.1	29.8	30.3	30.8	31.2	31.7
92.5°	42.9	43.6	43.9	43.5	43.3	43.0	42.7
95°	81.0	82.0	82.5	82.5	82.5	82.5	82.5
97.5°	125.7	126.8	127.3	127.2	127.1	127.0	126.9
100°	157.5	158.2	158.8	159.3	159.8	160.3	160.7
102.5°	194.8	195.5	195.8	195.7	195.6	195.5	195.4
105°	249.6	249.6	249.8	250.3	250.7	251.2	251.7
107.5°	310.4	311.1	311.4	311.1	310.8	310.5	310.2
110°	350.7	351.6	351.9	351.4	351.0	350.5	350.0



TEST NUMBER: P332423-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	391.0	392.2	392.6	392.6	392.5	392.4	392.3
115°	451.2	451.4	451.4	451.2	450.9	450.7	450.5
117.5°	512.5	512.4	512.1	511.4	510.8	510.1	509.5
120°	553.4	553.2	552.8	552.4	551.9	551.4	550.9
122.5°	594.5	593.9	593.3	592.6	592.0	591.3	590.7
125°	656.0	655.0	654.1	653.1	652.2	651.3	650.3
127.5°	716.6	715.3	714.0	713.0	711.9	710.9	709.7
130°	757.5	756.5	755.2	753.6	752.0	750.3	748.7
132.5°	796.6	795.6	794.3	793.0	791.8	790.5	789.3
135°	855.8	854.8	854.2	853.7	853.2	852.7	852.3
137.5°	913.4	912.4	911.5	910.6	909.7	908.8	907.9
140°	952.0	951.8	950.9	949.3	947.5	945.9	944.3
142.5°	987.6	987.3	986.6	985.3	984.1	982.8	981.5
145°	1039.8	1039.6	1039.0	1038.0	1037.1	1036.2	1035.2
147.5°	1089.3	1089.3	1088.7	1087.3	1085.8	1084.4	1083.0
150°	1119.8	1119.8	1119.1	1117.7	1116.3	1114.8	1113.5
152.5°	1148.0	1148.3	1147.9	1146.7	1145.5	1144.3	1143.0
155°	1189.3	1190.2	1189.8	1188.2	1186.6	1184.9	1183.2
157.5°	1224.3	1225.3	1225.1	1223.8	1222.5	1221.2	1219.9
160°	1246.0	1247.2	1247.3	1246.3	1245.5	1244.5	1243.5
162.5°	1266.3	1267.5	1267.3	1265.8	1264.3	1262.8	1261.3
165°	1292.2	1293.6	1293.5	1291.8	1290.2	1288.5	1286.9
167.5°	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6
170°	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6
172.5°	1333.3	1334.8	1334.7	1333.1	1331.4	1329.8	1328.1
175°	1343.0	1344.3	1344.2	1342.6	1340.9	1339.3	1337.7
177.5°	1347.0	1348.1	1348.0	1346.6	1345.3	1344.0	1342.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1

(END OF REPORT)