

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332447-930

Luminaire Tested: **S123RDIW-S775D1535U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332447-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1535U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6823.5 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	31	30	28	23				
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	28	26	24	20				
5	67	56	48	43	61	51	44	39	42	37	33	34	30	27	26	23	22	18				
6	62	50	43	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12				
10	46	34	28	23	42	32	26	21	27	22	18	22	18	16	17	14	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.1	1.4
10°-20°	306.3	4.5
20°-30°	481.3	7.1
30°-40°	502.1	7.4
40°-50°	429.7	6.3
50°-60°	327.5	4.8
60°-70°	209.9	3.1
70°-80°	101.0	1.5
80°-90°	31.4	0.5
90°-100°	102.0	1.5
100°-110°	305.2	4.5
110°-120°	519.0	7.6
120°-130°	682.7	10.0
130°-140°	767.4	11.2
140°-150°	754.3	11.1
150°-160°	635.0	9.3
160°-170°	422.7	6.2
170°-180°	148.0	2.2
0°-30°	885.7	13.0
0°-40°	1387.8	20.3
0°-60°	2145.0	31.4
0°-90°	2487.3	36.5
90°-120°	926.2	13.6
90°-150°	3130.5	45.9
90°-180°	4336.0	63.5
0°-180°	6823.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	18
90°	37	1	37	1	37	18
95°	96	73	96	73	96	98
105°	293	277	293	277	293	310
115°	524	522	524	522	524	519
125°	756	765	756	765	756	676
135°	991	992	991	992	991	762
145°	1204	1204	1204	1204	1204	751
155°	1376	1378	1376	1378	1376	633
165°	1496	1501	1496	1501	1496	422
175°	1555	1561	1555	1561	1555	148
180°	1565	1565	1565	1565	1565	



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	10.8	11.3	10.6	10.8	10.7	10.8	10.7	10.4	10.9	10.4	9.9
90°	36.9	36.4	35.8	35.2	34.7	33.9	32.8	31.7	30.6	29.5	25.9
92.5°	49.7	50.0	50.3	50.6	51.0	50.7	49.8	48.9	48.1	47.2	45.2
95°	95.9	95.9	95.9	95.9	95.9	95.3	94.2	93.2	92.0	91.0	88.8
97.5°	147.6	147.7	147.7	147.9	148.0	147.4	146.1	144.9	143.7	142.4	140.8
100°	186.9	186.3	185.8	185.2	184.7	184.0	183.2	182.4	181.6	180.8	179.4
102.5°	227.2	227.3	227.4	227.6	227.6	227.3	226.5	225.7	224.9	224.0	222.2
105°	292.6	292.0	291.6	291.0	290.4	290.2	290.2	290.2	290.2	290.2	287.7
107.5°	360.7	361.0	361.3	361.7	362.0	361.7	360.9	360.0	359.1	358.2	357.3
110°	406.9	407.5	408.1	408.5	409.1	408.9	407.7	406.7	405.6	404.5	403.9



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.1	456.2	456.3	456.5	456.6	455.9	454.6	453.3	452.0	450.7	450.6
115°	523.7	524.0	524.3	524.6	524.8	524.8	524.6	524.3	524.0	523.7	524.3
117.5°	592.3	593.1	593.9	594.6	595.4	595.8	595.9	595.9	596.0	596.1	596.7
120°	640.5	641.1	641.6	642.2	642.7	643.1	643.4	643.7	643.9	644.2	645.6
122.5°	686.7	687.5	688.3	689.1	689.8	690.6	691.3	691.9	692.7	693.4	694.1
125°	756.1	757.2	758.3	759.4	760.4	761.6	762.6	763.8	764.8	766.0	766.5
127.5°	825.2	826.5	827.7	829.0	830.2	831.6	833.2	834.7	836.2	837.7	838.4
130°	870.4	872.4	874.2	876.2	878.1	879.6	880.7	881.7	882.9	883.9	884.8
132.5°	917.6	919.1	920.6	922.1	923.6	925.0	926.3	927.6	928.9	930.2	930.7
135°	990.9	991.5	992.0	992.5	993.1	993.9	995.0	996.1	997.2	998.3	998.6
137.5°	1055.6	1056.6	1057.7	1058.7	1059.7	1060.9	1062.0	1063.2	1064.3	1065.4	1064.7
140°	1097.9	1099.8	1101.7	1103.6	1105.5	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4
142.5°	1141.2	1142.6	1144.1	1145.6	1147.0	1147.9	1148.2	1148.5	1148.8	1149.0	1148.5
145°	1203.6	1204.7	1205.8	1206.9	1207.9	1208.7	1208.9	1209.2	1209.5	1209.7	1208.9
147.5°	1259.1	1260.8	1262.5	1264.1	1265.8	1266.6	1266.6	1266.6	1266.6	1266.6	1265.8
150°	1294.6	1296.2	1297.9	1299.5	1301.1	1302.0	1302.0	1302.0	1302.0	1302.0	1301.4
152.5°	1329.0	1330.4	1331.9	1333.3	1334.7	1335.2	1334.7	1334.3	1333.9	1333.4	1333.1
155°	1375.7	1377.6	1379.6	1381.4	1383.4	1383.8	1382.7	1381.6	1380.5	1379.4	1379.2
157.5°	1418.3	1419.8	1421.3	1422.9	1424.4	1424.6	1423.4	1422.3	1421.1	1420.0	1419.8
160°	1445.8	1446.9	1448.0	1449.1	1450.2	1450.0	1448.7	1447.3	1445.9	1444.5	1444.5
162.5°	1466.5	1468.2	1470.0	1471.7	1473.5	1473.7	1472.3	1470.9	1469.6	1468.2	1467.9
165°	1496.2	1498.1	1500.1	1501.9	1503.9	1504.0	1502.4	1500.7	1499.1	1497.5	1497.5
167.5°	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5	1521.3
170°	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3	1534.3
172.5°	1544.2	1546.1	1548.0	1549.9	1551.8	1551.9	1550.2	1548.5	1546.9	1545.2	1545.2
175°	1555.3	1557.1	1559.0	1561.0	1562.8	1563.0	1561.4	1559.7	1558.1	1556.5	1556.5
177.5°	1561.1	1562.7	1564.2	1565.7	1567.2	1567.3	1566.0	1564.7	1563.4	1562.1	1562.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	9.9	8.9	8.9	8.2	8.7	8.5	10.0	11.2	12.1	11.3	11.8
90°	22.4	18.8	15.3	12.1	9.5	6.7	4.0	1.2	4.0	6.7	9.5
92.5°	43.1	41.2	39.1	37.2	35.3	33.4	31.6	29.8	31.6	33.4	35.3
95°	86.6	84.4	82.3	80.2	78.3	76.4	74.4	72.6	74.4	76.4	78.3
97.5°	139.2	137.6	136.0	134.5	133.1	131.7	130.3	128.8	130.3	131.7	133.1
100°	178.0	176.6	175.3	173.7	172.1	170.5	168.8	167.2	168.8	170.5	172.1
102.5°	220.4	218.6	216.8	215.4	214.4	213.4	212.5	211.5	212.5	213.4	214.4
105°	285.2	282.7	280.3	278.8	278.3	277.7	277.2	276.6	277.2	277.7	278.3
107.5°	356.3	355.3	354.3	353.7	353.4	353.0	352.7	352.4	352.7	353.0	353.4
110°	403.4	402.8	402.3	401.8	401.2	400.6	400.1	399.6	400.1	400.6	401.2





TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	450.5	450.4	450.3	450.0	449.7	449.4	449.1	448.7	449.1	449.4	449.7
115°	524.8	525.4	525.9	525.8	525.0	524.2	523.3	522.5	523.3	524.2	525.0
117.5°	597.5	598.2	598.8	598.9	598.4	597.9	597.3	596.8	597.3	597.9	598.4
120°	646.9	648.3	649.7	649.5	647.9	646.3	644.7	643.0	644.7	646.3	647.9
122.5°	694.8	695.5	696.3	696.0	694.8	693.6	692.4	691.2	692.4	693.6	694.8
125°	767.0	767.6	768.1	768.0	767.2	766.4	765.5	764.7	765.5	766.4	767.2
127.5°	838.9	839.5	840.2	839.6	837.8	836.1	834.3	832.6	834.3	836.1	837.8
130°	885.6	886.4	887.2	886.6	884.4	882.2	880.0	877.8	880.0	882.2	884.4
132.5°	931.4	932.0	932.6	931.8	929.6	927.4	925.2	923.1	925.2	927.4	929.6
135°	998.8	999.1	999.4	998.7	997.0	995.4	993.8	992.1	993.8	995.4	997.0
137.5°	1064.0	1063.3	1062.6	1061.5	1060.2	1058.8	1057.4	1056.1	1057.4	1058.8	1060.2
140°	1107.2	1106.9	1106.6	1105.8	1104.4	1103.1	1101.7	1100.3	1101.7	1103.1	1104.4
142.5°	1148.0	1147.5	1147.0	1146.1	1144.8	1143.4	1142.0	1140.7	1142.0	1143.4	1144.8
145°	1208.1	1207.3	1206.5	1205.8	1205.3	1204.7	1204.2	1203.6	1204.2	1204.7	1205.3
147.5°	1265.0	1264.3	1263.5	1262.7	1261.7	1260.6	1259.6	1258.7	1259.6	1260.6	1261.7
150°	1300.9	1300.3	1299.8	1299.3	1298.7	1298.1	1297.6	1297.1	1297.6	1298.1	1298.7
152.5°	1332.8	1332.4	1332.1	1331.5	1330.8	1330.1	1329.3	1328.5	1329.3	1330.1	1330.8
155°	1378.8	1378.6	1378.3	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2
157.5°	1419.5	1419.4	1419.1	1419.2	1419.5	1419.8	1420.2	1420.5	1420.2	1419.8	1419.5
160°	1444.5	1444.5	1444.5	1444.9	1445.4	1445.9	1446.5	1447.1	1446.5	1445.9	1445.4
162.5°	1467.8	1467.5	1467.3	1467.6	1468.4	1469.1	1469.9	1470.6	1469.9	1469.1	1468.4
165°	1497.5	1497.5	1497.5	1497.9	1498.7	1499.5	1500.3	1501.1	1500.3	1499.5	1498.7
167.5°	1521.1	1520.9	1520.7	1521.1	1522.2	1523.3	1524.4	1525.5	1524.4	1523.3	1522.2
170°	1534.3	1534.3	1534.3	1534.9	1535.9	1537.1	1538.1	1539.2	1538.1	1537.1	1535.9
172.5°	1545.2	1545.2	1545.2	1545.7	1546.8	1547.8	1549.0	1550.0	1549.0	1547.8	1546.8
175°	1556.5	1556.5	1556.5	1557.0	1558.1	1559.2	1560.3	1561.4	1560.3	1559.2	1558.1
177.5°	1562.1	1562.1	1562.1	1562.5	1563.4	1564.3	1565.2	1566.0	1565.2	1564.3	1563.4
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	12.0	13.6	14.7	15.7	16.8	17.2	17.7	17.9	18.5	18.8	18.9
90°	12.1	15.3	18.8	22.4	25.9	29.5	30.6	31.7	32.8	33.9	34.7
92.5°	37.2	39.1	41.2	43.1	45.2	47.2	48.1	48.9	49.8	50.7	51.0
95°	80.2	82.3	84.4	86.6	88.8	91.0	92.0	93.2	94.2	95.3	95.9
97.5°	134.5	136.0	137.6	139.2	140.8	142.4	143.7	144.9	146.1	147.4	148.0
100°	173.7	175.3	176.6	178.0	179.4	180.8	181.6	182.4	183.2	184.0	184.7
102.5°	215.4	216.8	218.6	220.4	222.2	224.0	224.9	225.7	226.5	227.3	227.6
105°	278.8	280.3	282.7	285.2	287.7	290.2	290.2	290.2	290.2	290.2	290.4
107.5°	353.7	354.3	355.3	356.3	357.3	358.2	359.1	360.0	360.9	361.7	362.0
110°	401.8	402.3	402.8	403.4	403.9	404.5	405.6	406.7	407.7	408.9	409.1



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.0	450.3	450.4	450.5	450.6	450.7	452.0	453.3	454.6	455.9	456.6
115°	525.8	525.9	525.4	524.8	524.3	523.7	524.0	524.3	524.6	524.8	524.8
117.5°	598.9	598.8	598.2	597.5	596.7	596.1	596.0	595.9	595.9	595.8	595.4
120°	649.5	649.7	648.3	646.9	645.6	644.2	643.9	643.7	643.4	643.1	642.7
122.5°	696.0	696.3	695.5	694.8	694.1	693.4	692.7	691.9	691.3	690.6	689.8
125°	768.0	768.1	767.6	767.0	766.5	766.0	764.8	763.8	762.6	761.6	760.4
127.5°	839.6	840.2	839.5	838.9	838.4	837.7	836.2	834.7	833.2	831.6	830.2
130°	886.6	887.2	886.4	885.6	884.8	883.9	882.9	881.7	880.7	879.6	878.1
132.5°	931.8	932.6	932.0	931.4	930.7	930.2	928.9	927.6	926.3	925.0	923.6
135°	998.7	999.4	999.1	998.8	998.6	998.3	997.2	996.1	995.0	993.9	993.1
137.5°	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3	1063.2	1062.0	1060.9	1059.7
140°	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4	1107.2	1106.9	1106.6	1105.5
142.5°	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8	1148.5	1148.2	1147.9	1147.0
145°	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5	1209.2	1208.9	1208.7	1207.9
147.5°	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6	1266.6	1266.6	1266.6	1265.8
150°	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0	1302.0	1302.0	1302.0	1301.1
152.5°	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9	1334.3	1334.7	1335.2	1334.7
155°	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5	1381.6	1382.7	1383.8	1383.4
157.5°	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1	1422.3	1423.4	1424.6	1424.4
160°	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9	1447.3	1448.7	1450.0	1450.2
162.5°	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6	1470.9	1472.3	1473.7	1473.5
165°	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1	1500.7	1502.4	1504.0	1503.9
167.5°	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3
170°	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0
172.5°	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9	1548.5	1550.2	1551.9	1551.8
175°	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1	1559.7	1561.4	1563.0	1562.8
177.5°	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4	1564.7	1566.0	1567.3	1567.2
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	19.6	19.1	19.2	19.6	19.2	19.1	19.6	18.9	18.8	18.5	17.9
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.9	32.8	31.7
92.5°	50.6	50.3	50.0	49.7	50.0	50.3	50.6	51.0	50.7	49.8	48.9
95°	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.3	94.2	93.2
97.5°	147.9	147.7	147.7	147.6	147.7	147.7	147.9	148.0	147.4	146.1	144.9
100°	185.2	185.8	186.3	186.9	186.3	185.8	185.2	184.7	184.0	183.2	182.4
102.5°	227.6	227.4	227.3	227.2	227.3	227.4	227.6	227.6	227.3	226.5	225.7
105°	291.0	291.6	292.0	292.6	292.0	291.6	291.0	290.4	290.2	290.2	290.2
107.5°	361.7	361.3	361.0	360.7	361.0	361.3	361.7	362.0	361.7	360.9	360.0
110°	408.5	408.1	407.5	406.9	407.5	408.1	408.5	409.1	408.9	407.7	406.7



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	456.5	456.3	456.2	456.1	456.2	456.3	456.5	456.6	455.9	454.6	453.3
115°	524.6	524.3	524.0	523.7	524.0	524.3	524.6	524.8	524.8	524.6	524.3
117.5°	594.6	593.9	593.1	592.3	593.1	593.9	594.6	595.4	595.8	595.9	595.9
120°	642.2	641.6	641.1	640.5	641.1	641.6	642.2	642.7	643.1	643.4	643.7
122.5°	689.1	688.3	687.5	686.7	687.5	688.3	689.1	689.8	690.6	691.3	691.9
125°	759.4	758.3	757.2	756.1	757.2	758.3	759.4	760.4	761.6	762.6	763.8
127.5°	829.0	827.7	826.5	825.2	826.5	827.7	829.0	830.2	831.6	833.2	834.7
130°	876.2	874.2	872.4	870.4	872.4	874.2	876.2	878.1	879.6	880.7	881.7
132.5°	922.1	920.6	919.1	917.6	919.1	920.6	922.1	923.6	925.0	926.3	927.6
135°	992.5	992.0	991.5	990.9	991.5	992.0	992.5	993.1	993.9	995.0	996.1
137.5°	1058.7	1057.7	1056.6	1055.6	1056.6	1057.7	1058.7	1059.7	1060.9	1062.0	1063.2
140°	1103.6	1101.7	1099.8	1097.9	1099.8	1101.7	1103.6	1105.5	1106.6	1106.9	1107.2
142.5°	1145.6	1144.1	1142.6	1141.2	1142.6	1144.1	1145.6	1147.0	1147.9	1148.2	1148.5
145°	1206.9	1205.8	1204.7	1203.6	1204.7	1205.8	1206.9	1207.9	1208.7	1208.9	1209.2
147.5°	1264.1	1262.5	1260.8	1259.1	1260.8	1262.5	1264.1	1265.8	1266.6	1266.6	1266.6
150°	1299.5	1297.9	1296.2	1294.6	1296.2	1297.9	1299.5	1301.1	1302.0	1302.0	1302.0
152.5°	1333.3	1331.9	1330.4	1329.0	1330.4	1331.9	1333.3	1334.7	1335.2	1334.7	1334.3
155°	1381.4	1379.6	1377.6	1375.7	1377.6	1379.6	1381.4	1383.4	1383.8	1382.7	1381.6
157.5°	1422.9	1421.3	1419.8	1418.3	1419.8	1421.3	1422.9	1424.4	1424.6	1423.4	1422.3
160°	1449.1	1448.0	1446.9	1445.8	1446.9	1448.0	1449.1	1450.2	1450.0	1448.7	1447.3
162.5°	1471.7	1470.0	1468.2	1466.5	1468.2	1470.0	1471.7	1473.5	1473.7	1472.3	1470.9
165°	1501.9	1500.1	1498.1	1496.2	1498.1	1500.1	1501.9	1503.9	1504.0	1502.4	1500.7
167.5°	1526.6	1524.9	1523.2	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9
170°	1540.1	1538.1	1536.3	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1
172.5°	1549.9	1548.0	1546.1	1544.2	1546.1	1548.0	1549.9	1551.8	1551.9	1550.2	1548.5
175°	1561.0	1559.0	1557.1	1555.3	1557.1	1559.0	1561.0	1562.8	1563.0	1561.4	1559.7
177.5°	1565.7	1564.2	1562.7	1561.1	1562.7	1564.2	1565.7	1567.2	1567.3	1566.0	1564.7
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	17.7	17.2	16.8	15.7	14.7	13.6	12.0	11.8	11.3	12.1	11.2
90°	30.6	29.5	25.9	22.4	18.8	15.3	12.1	9.5	6.7	4.0	1.2
92.5°	48.1	47.2	45.2	43.1	41.2	39.1	37.2	35.3	33.4	31.6	29.8
95°	92.0	91.0	88.8	86.6	84.4	82.3	80.2	78.3	76.4	74.4	72.6
97.5°	143.7	142.4	140.8	139.2	137.6	136.0	134.5	133.1	131.7	130.3	128.8
100°	181.6	180.8	179.4	178.0	176.6	175.3	173.7	172.1	170.5	168.8	167.2
102.5°	224.9	224.0	222.2	220.4	218.6	216.8	215.4	214.4	213.4	212.5	211.5
105°	290.2	290.2	287.7	285.2	282.7	280.3	278.8	278.3	277.7	277.2	276.6
107.5°	359.1	358.2	357.3	356.3	355.3	354.3	353.7	353.4	353.0	352.7	352.4
110°	405.6	404.5	403.9	403.4	402.8	402.3	401.8	401.2	400.6	400.1	399.6



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.0	450.7	450.6	450.5	450.4	450.3	450.0	449.7	449.4	449.1	448.7
115°	524.0	523.7	524.3	524.8	525.4	525.9	525.8	525.0	524.2	523.3	522.5
117.5°	596.0	596.1	596.7	597.5	598.2	598.8	598.9	598.4	597.9	597.3	596.8
120°	643.9	644.2	645.6	646.9	648.3	649.7	649.5	647.9	646.3	644.7	643.0
122.5°	692.7	693.4	694.1	694.8	695.5	696.3	696.0	694.8	693.6	692.4	691.2
125°	764.8	766.0	766.5	767.0	767.6	768.1	768.0	767.2	766.4	765.5	764.7
127.5°	836.2	837.7	838.4	838.9	839.5	840.2	839.6	837.8	836.1	834.3	832.6
130°	882.9	883.9	884.8	885.6	886.4	887.2	886.6	884.4	882.2	880.0	877.8
132.5°	928.9	930.2	930.7	931.4	932.0	932.6	931.8	929.6	927.4	925.2	923.1
135°	997.2	998.3	998.6	998.8	999.1	999.4	998.7	997.0	995.4	993.8	992.1
137.5°	1064.3	1065.4	1064.7	1064.0	1063.3	1062.6	1061.5	1060.2	1058.8	1057.4	1056.1
140°	1107.4	1107.7	1107.4	1107.2	1106.9	1106.6	1105.8	1104.4	1103.1	1101.7	1100.3
142.5°	1148.8	1149.0	1148.5	1148.0	1147.5	1147.0	1146.1	1144.8	1143.4	1142.0	1140.7
145°	1209.5	1209.7	1208.9	1208.1	1207.3	1206.5	1205.8	1205.3	1204.7	1204.2	1203.6
147.5°	1266.6	1266.6	1265.8	1265.0	1264.3	1263.5	1262.7	1261.7	1260.6	1259.6	1258.7
150°	1302.0	1302.0	1301.4	1300.9	1300.3	1299.8	1299.3	1298.7	1298.1	1297.6	1297.1
152.5°	1333.9	1333.4	1333.1	1332.8	1332.4	1332.1	1331.5	1330.8	1330.1	1329.3	1328.5
155°	1380.5	1379.4	1379.2	1378.8	1378.6	1378.3	1378.2	1378.2	1378.2	1378.2	1378.2
157.5°	1421.1	1420.0	1419.8	1419.5	1419.4	1419.1	1419.2	1419.5	1419.8	1420.2	1420.5
160°	1445.9	1444.5	1444.5	1444.5	1444.5	1444.5	1444.9	1445.4	1445.9	1446.5	1447.1
162.5°	1469.6	1468.2	1467.9	1467.8	1467.5	1467.3	1467.6	1468.4	1469.1	1469.9	1470.6
165°	1499.1	1497.5	1497.5	1497.5	1497.5	1497.5	1497.9	1498.7	1499.5	1500.3	1501.1
167.5°	1523.2	1521.5	1521.3	1521.1	1520.9	1520.7	1521.1	1522.2	1523.3	1524.4	1525.5
170°	1536.3	1534.3	1534.3	1534.3	1534.3	1534.3	1534.9	1535.9	1537.1	1538.1	1539.2
172.5°	1546.9	1545.2	1545.2	1545.2	1545.2	1545.2	1545.7	1546.8	1547.8	1549.0	1550.0
175°	1558.1	1556.5	1556.5	1556.5	1556.5	1556.5	1557.0	1558.1	1559.2	1560.3	1561.4
177.5°	1563.4	1562.1	1562.1	1562.1	1562.1	1562.1	1562.5	1563.4	1564.3	1565.2	1566.0
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	10.0	8.5	8.7	8.2	8.9	8.9	9.9	9.9	10.4	10.9	10.4
90°	4.0	6.7	9.5	12.1	15.3	18.8	22.4	25.9	29.5	30.6	31.7
92.5°	31.6	33.4	35.3	37.2	39.1	41.2	43.1	45.2	47.2	48.1	48.9
95°	74.4	76.4	78.3	80.2	82.3	84.4	86.6	88.8	91.0	92.0	93.2
97.5°	130.3	131.7	133.1	134.5	136.0	137.6	139.2	140.8	142.4	143.7	144.9
100°	168.8	170.5	172.1	173.7	175.3	176.6	178.0	179.4	180.8	181.6	182.4
102.5°	212.5	213.4	214.4	215.4	216.8	218.6	220.4	222.2	224.0	224.9	225.7
105°	277.2	277.7	278.3	278.8	280.3	282.7	285.2	287.7	290.2	290.2	290.2
107.5°	352.7	353.0	353.4	353.7	354.3	355.3	356.3	357.3	358.2	359.1	360.0
110°	400.1	400.6	401.2	401.8	402.3	402.8	403.4	403.9	404.5	405.6	406.7





TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	449.1	449.4	449.7	450.0	450.3	450.4	450.5	450.6	450.7	452.0	453.3
115°	523.3	524.2	525.0	525.8	525.9	525.4	524.8	524.3	523.7	524.0	524.3
117.5°	597.3	597.9	598.4	598.9	598.8	598.2	597.5	596.7	596.1	596.0	595.9
120°	644.7	646.3	647.9	649.5	649.7	648.3	646.9	645.6	644.2	643.9	643.7
122.5°	692.4	693.6	694.8	696.0	696.3	695.5	694.8	694.1	693.4	692.7	691.9
125°	765.5	766.4	767.2	768.0	768.1	767.6	767.0	766.5	766.0	764.8	763.8
127.5°	834.3	836.1	837.8	839.6	840.2	839.5	838.9	838.4	837.7	836.2	834.7
130°	880.0	882.2	884.4	886.6	887.2	886.4	885.6	884.8	883.9	882.9	881.7
132.5°	925.2	927.4	929.6	931.8	932.6	932.0	931.4	930.7	930.2	928.9	927.6
135°	993.8	995.4	997.0	998.7	999.4	999.1	998.8	998.6	998.3	997.2	996.1
137.5°	1057.4	1058.8	1060.2	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3	1063.2
140°	1101.7	1103.1	1104.4	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4	1107.2
142.5°	1142.0	1143.4	1144.8	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8	1148.5
145°	1204.2	1204.7	1205.3	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5	1209.2
147.5°	1259.6	1260.6	1261.7	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6	1266.6
150°	1297.6	1298.1	1298.7	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0	1302.0
152.5°	1329.3	1330.1	1330.8	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9	1334.3
155°	1378.2	1378.2	1378.2	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5	1381.6
157.5°	1420.2	1419.8	1419.5	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1	1422.3
160°	1446.5	1445.9	1445.4	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9	1447.3
162.5°	1469.9	1469.1	1468.4	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6	1470.9
165°	1500.3	1499.5	1498.7	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1	1500.7
167.5°	1524.4	1523.3	1522.2	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2	1524.9
170°	1538.1	1537.1	1535.9	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3	1538.1
172.5°	1549.0	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9	1548.5
175°	1560.3	1559.2	1558.1	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1	1559.7
177.5°	1565.2	1564.3	1563.4	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4	1564.7
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	10.7	10.8	10.7	10.8	10.6	11.3	10.8
90°	32.8	33.9	34.7	35.2	35.8	36.4	36.9
92.5°	49.8	50.7	51.0	50.6	50.3	50.0	49.7
95°	94.2	95.3	95.9	95.9	95.9	95.9	95.9
97.5°	146.1	147.4	148.0	147.9	147.7	147.7	147.6
100°	183.2	184.0	184.7	185.2	185.8	186.3	186.9
102.5°	226.5	227.3	227.6	227.6	227.4	227.3	227.2
105°	290.2	290.2	290.4	291.0	291.6	292.0	292.6
107.5°	360.9	361.7	362.0	361.7	361.3	361.0	360.7
110°	407.7	408.9	409.1	408.5	408.1	407.5	406.9



TEST NUMBER: P332447-930

CATALOG NUMBER: S123RDIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.6	455.9	456.6	456.5	456.3	456.2	456.1
115°	524.6	524.8	524.8	524.6	524.3	524.0	523.7
117.5°	595.9	595.8	595.4	594.6	593.9	593.1	592.3
120°	643.4	643.1	642.7	642.2	641.6	641.1	640.5
122.5°	691.3	690.6	689.8	689.1	688.3	687.5	686.7
125°	762.6	761.6	760.4	759.4	758.3	757.2	756.1
127.5°	833.2	831.6	830.2	829.0	827.7	826.5	825.2
130°	880.7	879.6	878.1	876.2	874.2	872.4	870.4
132.5°	926.3	925.0	923.6	922.1	920.6	919.1	917.6
135°	995.0	993.9	993.1	992.5	992.0	991.5	990.9
137.5°	1062.0	1060.9	1059.7	1058.7	1057.7	1056.6	1055.6
140°	1106.9	1106.6	1105.5	1103.6	1101.7	1099.8	1097.9
142.5°	1148.2	1147.9	1147.0	1145.6	1144.1	1142.6	1141.2
145°	1208.9	1208.7	1207.9	1206.9	1205.8	1204.7	1203.6
147.5°	1266.6	1266.6	1265.8	1264.1	1262.5	1260.8	1259.1
150°	1302.0	1302.0	1301.1	1299.5	1297.9	1296.2	1294.6
152.5°	1334.7	1335.2	1334.7	1333.3	1331.9	1330.4	1329.0
155°	1382.7	1383.8	1383.4	1381.4	1379.6	1377.6	1375.7
157.5°	1423.4	1424.6	1424.4	1422.9	1421.3	1419.8	1418.3
160°	1448.7	1450.0	1450.2	1449.1	1448.0	1446.9	1445.8
162.5°	1472.3	1473.7	1473.5	1471.7	1470.0	1468.2	1466.5
165°	1502.4	1504.0	1503.9	1501.9	1500.1	1498.1	1496.2
167.5°	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5
170°	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3
172.5°	1550.2	1551.9	1551.8	1549.9	1548.0	1546.1	1544.2
175°	1561.4	1563.0	1562.8	1561.0	1559.0	1557.1	1555.3
177.5°	1566.0	1567.3	1567.2	1565.7	1564.2	1562.7	1561.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0

(END OF REPORT)