

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332163

Luminaire Tested: **S123DIW-S775D1030U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332163
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1030U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6838.4 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48					48			
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46					41				
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39					35				
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34					29				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29					25				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	25					22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22					20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20					17				
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18					16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16					14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15					13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.6
10°-20°	341.3	5.0
20°-30°	572.8	8.4
30°-40°	648.6	9.5
40°-50°	581.7	8.5
50°-60°	469.4	6.9
60°-70°	327.1	4.8
70°-80°	171.9	2.5
80°-90°	45.9	0.7
90°-100°	84.0	1.2
100°-110°	251.5	3.7
110°-120°	427.7	6.3
120°-130°	562.6	8.2
130°-140°	632.3	9.2
140°-150°	621.6	9.1
150°-160°	523.3	7.7
160°-170°	348.3	5.1
170°-180°	122.0	1.8
0°-30°	1020.6	14.9
0°-40°	1669.2	24.4
0°-60°	2720.2	39.8
0°-90°	3265.1	47.7
90°-120°	763.2	11.2
90°-150°	2579.7	37.7
90°-180°	3573.0	52.2
0°-180°	6838.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	42
90°	30	1	30	1	30	16
95°	79	60	79	60	79	81
105°	241	228	241	228	241	256
115°	432	431	432	431	432	427
125°	623	630	623	630	623	557
135°	817	818	817	818	817	628
145°	992	992	992	992	992	619
155°	1134	1136	1134	1136	1134	522
165°	1233	1237	1233	1237	1233	348
175°	1282	1287	1282	1287	1282	122
180°	1290	1290	1290	1290	1290	



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	18.6	17.7	18.0	18.4	17.9	18.1	18.4	18.6	18.9	19.1	18.9
90°	30.4	29.9	29.5	29.0	28.6	27.9	27.0	26.1	25.2	24.3	21.4
92.5°	40.9	41.2	41.5	41.7	42.0	41.8	41.1	40.3	39.6	38.9	37.2
95°	79.0	79.0	79.0	79.0	79.0	78.6	77.7	76.8	75.9	75.0	73.2
97.5°	121.6	121.7	121.8	121.8	121.9	121.5	120.4	119.4	118.4	117.3	116.0
100°	154.0	153.5	153.1	152.6	152.2	151.6	151.0	150.3	149.6	148.9	147.8
102.5°	187.2	187.3	187.4	187.5	187.6	187.3	186.6	185.9	185.3	184.6	183.1
105°	241.1	240.7	240.2	239.8	239.3	239.1	239.1	239.1	239.1	239.1	237.1
107.5°	297.2	297.5	297.8	298.1	298.3	298.1	297.4	296.7	295.9	295.2	294.4
110°	335.3	335.8	336.2	336.7	337.1	336.9	336.0	335.1	334.2	333.3	332.9



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.9	376.0	376.0	376.1	376.2	375.7	374.6	373.6	372.5	371.4	371.3
115°	431.6	431.8	432.0	432.3	432.5	432.5	432.3	432.0	431.8	431.6	432.0
117.5°	488.1	488.7	489.4	490.0	490.6	491.0	491.0	491.1	491.1	491.2	491.7
120°	527.8	528.3	528.7	529.2	529.6	530.0	530.2	530.4	530.6	530.9	532.0
122.5°	565.9	566.6	567.2	567.8	568.4	569.1	569.6	570.2	570.8	571.4	572.0
125°	623.1	624.0	624.9	625.8	626.7	627.6	628.5	629.4	630.3	631.2	631.6
127.5°	680.0	681.0	682.1	683.1	684.1	685.3	686.6	687.8	689.1	690.3	690.8
130°	717.3	718.9	720.4	722.0	723.6	724.8	725.7	726.6	727.5	728.4	729.1
132.5°	756.2	757.4	758.6	759.8	761.1	762.2	763.3	764.4	765.4	766.5	767.0
135°	816.6	817.0	817.5	817.9	818.4	819.0	819.9	820.8	821.7	822.6	822.9
137.5°	869.9	870.7	871.6	872.4	873.3	874.2	875.1	876.1	877.0	878.0	877.4
140°	904.7	906.3	907.9	909.4	911.0	911.9	912.1	912.4	912.6	912.8	912.6
142.5°	940.4	941.6	942.8	944.0	945.2	946.0	946.2	946.4	946.6	946.9	946.5
145°	991.8	992.7	993.6	994.5	995.4	996.0	996.2	996.5	996.7	996.9	996.2
147.5°	1037.6	1039.0	1040.3	1041.7	1043.0	1043.7	1043.7	1043.7	1043.7	1043.7	1043.1
150°	1066.8	1068.2	1069.5	1070.9	1072.2	1072.9	1072.9	1072.9	1072.9	1072.9	1072.4
152.5°	1095.2	1096.3	1097.5	1098.7	1099.9	1100.3	1099.9	1099.5	1099.2	1098.8	1098.6
155°	1133.7	1135.3	1136.8	1138.4	1140.0	1140.3	1139.4	1138.5	1137.6	1136.7	1136.5
157.5°	1168.7	1170.0	1171.3	1172.5	1173.8	1173.9	1173.0	1172.0	1171.1	1170.1	1170.0
160°	1191.4	1192.3	1193.2	1194.1	1195.0	1194.9	1193.8	1192.7	1191.5	1190.4	1190.4
162.5°	1208.4	1209.9	1211.3	1212.8	1214.2	1214.4	1213.2	1212.1	1211.0	1209.9	1209.7
165°	1233.0	1234.5	1236.1	1237.7	1239.3	1239.4	1238.0	1236.7	1235.3	1234.0	1234.0
167.5°	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8	1253.7
170°	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4	1264.4
172.5°	1272.5	1274.0	1275.6	1277.2	1278.8	1278.9	1277.5	1276.1	1274.7	1273.3	1273.3
175°	1281.6	1283.2	1284.7	1286.3	1287.9	1288.0	1286.7	1285.3	1284.0	1282.6	1282.6
177.5°	1286.5	1287.7	1289.0	1290.2	1291.5	1291.6	1290.5	1289.4	1288.3	1287.3	1287.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	19.2	19.0	17.2	15.0	13.7	12.0	11.5	10.3	9.9	10.3	10.3
90°	18.5	15.5	12.6	10.0	7.8	5.5	3.3	1.0	3.3	5.5	7.8
92.5°	35.6	33.9	32.2	30.6	29.1	27.6	26.0	24.5	26.0	27.6	29.1
95°	71.4	69.6	67.8	66.1	64.5	62.9	61.3	59.8	61.3	62.9	64.5
97.5°	114.7	113.4	112.1	110.9	109.7	108.5	107.3	106.2	107.3	108.5	109.7
100°	146.7	145.6	144.4	143.2	141.8	140.5	139.1	137.8	139.1	140.5	141.8
102.5°	181.6	180.1	178.6	177.5	176.7	175.9	175.1	174.3	175.1	175.9	176.7
105°	235.0	233.0	231.0	229.8	229.3	228.9	228.4	228.0	228.4	228.9	229.3
107.5°	293.6	292.8	292.0	291.4	291.2	290.9	290.6	290.4	290.6	290.9	291.2
110°	332.4	332.0	331.5	331.1	330.6	330.2	329.7	329.3	329.7	330.2	330.6



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	371.2	371.1	371.0	370.9	370.6	370.3	370.1	369.8	370.1	370.3	370.6
115°	432.5	432.9	433.4	433.3	432.6	431.9	431.2	430.6	431.2	431.9	432.6
117.5°	492.3	492.9	493.5	493.6	493.1	492.7	492.2	491.8	492.2	492.7	493.1
120°	533.1	534.2	535.4	535.3	533.9	532.6	531.2	529.9	531.2	532.6	533.9
122.5°	572.6	573.2	573.7	573.5	572.5	571.6	570.6	569.6	570.6	571.6	572.5
125°	632.1	632.5	633.0	632.9	632.2	631.5	630.8	630.2	630.8	631.5	632.2
127.5°	691.3	691.8	692.3	691.8	690.4	689.0	687.5	686.1	687.5	689.0	690.4
130°	729.8	730.5	731.1	730.6	728.8	727.0	725.2	723.4	725.2	727.0	728.8
132.5°	767.5	768.0	768.5	767.9	766.1	764.2	762.4	760.6	762.4	764.2	766.1
135°	823.1	823.3	823.5	823.0	821.6	820.3	818.9	817.6	818.9	820.3	821.6
137.5°	876.8	876.2	875.6	874.8	873.6	872.5	871.4	870.3	871.4	872.5	873.6
140°	912.4	912.1	911.9	911.2	910.1	909.0	907.9	906.7	907.9	909.0	910.1
142.5°	946.0	945.6	945.2	944.5	943.3	942.2	941.1	940.0	941.1	942.2	943.3
145°	995.6	994.9	994.2	993.6	993.2	992.7	992.3	991.8	992.3	992.7	993.2
147.5°	1042.5	1041.8	1041.2	1040.5	1039.7	1038.8	1038.0	1037.2	1038.0	1038.8	1039.7
150°	1072.0	1071.5	1071.1	1070.6	1070.2	1069.7	1069.3	1068.8	1069.3	1069.7	1070.2
152.5°	1098.3	1098.0	1097.7	1097.3	1096.7	1096.0	1095.4	1094.8	1095.4	1096.0	1096.7
155°	1136.3	1136.0	1135.8	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7
157.5°	1169.8	1169.6	1169.4	1169.5	1169.7	1170.0	1170.3	1170.6	1170.3	1170.0	1169.7
160°	1190.4	1190.4	1190.4	1190.6	1191.1	1191.5	1192.0	1192.4	1192.0	1191.5	1191.1
162.5°	1209.5	1209.3	1209.1	1209.4	1210.0	1210.6	1211.3	1211.9	1211.3	1210.6	1210.0
165°	1234.0	1234.0	1234.0	1234.3	1235.0	1235.7	1236.3	1237.0	1236.3	1235.7	1235.0
167.5°	1253.5	1253.3	1253.1	1253.5	1254.4	1255.3	1256.2	1257.1	1256.2	1255.3	1254.4
170°	1264.4	1264.4	1264.4	1264.8	1265.7	1266.6	1267.5	1268.4	1267.5	1266.6	1265.7
172.5°	1273.3	1273.3	1273.3	1273.7	1274.6	1275.5	1276.4	1277.3	1276.4	1275.5	1274.6
175°	1282.6	1282.6	1282.6	1283.1	1284.0	1284.9	1285.8	1286.7	1285.8	1284.9	1284.0
177.5°	1287.3	1287.3	1287.3	1287.6	1288.3	1289.1	1289.8	1290.5	1289.8	1289.1	1288.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	10.4	11.3	11.5	12.5	12.7	13.7	13.8	13.2	13.4	14.8	13.3
90°	10.0	12.6	15.5	18.5	21.4	24.3	25.2	26.1	27.0	27.9	28.6
92.5°	30.6	32.2	33.9	35.6	37.2	38.9	39.6	40.3	41.1	41.8	42.0
95°	66.1	67.8	69.6	71.4	73.2	75.0	75.9	76.8	77.7	78.6	79.0
97.5°	110.9	112.1	113.4	114.7	116.0	117.3	118.4	119.4	120.4	121.5	121.9
100°	143.2	144.4	145.6	146.7	147.8	148.9	149.6	150.3	151.0	151.6	152.2
102.5°	177.5	178.6	180.1	181.6	183.1	184.6	185.3	185.9	186.6	187.3	187.6
105°	229.8	231.0	233.0	235.0	237.1	239.1	239.1	239.1	239.1	239.1	239.3
107.5°	291.4	292.0	292.8	293.6	294.4	295.2	295.9	296.7	297.4	298.1	298.3
110°	331.1	331.5	332.0	332.4	332.9	333.3	334.2	335.1	336.0	336.9	337.1



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	370.9	371.0	371.1	371.2	371.3	371.4	372.5	373.6	374.6	375.7	376.2
115°	433.3	433.4	432.9	432.5	432.0	431.6	431.8	432.0	432.3	432.5	432.5
117.5°	493.6	493.5	492.9	492.3	491.7	491.2	491.1	491.1	491.0	491.0	490.6
120°	535.3	535.4	534.2	533.1	532.0	530.9	530.6	530.4	530.2	530.0	529.6
122.5°	573.5	573.7	573.2	572.6	572.0	571.4	570.8	570.2	569.6	569.1	568.4
125°	632.9	633.0	632.5	632.1	631.6	631.2	630.3	629.4	628.5	627.6	626.7
127.5°	691.8	692.3	691.8	691.3	690.8	690.3	689.1	687.8	686.6	685.3	684.1
130°	730.6	731.1	730.5	729.8	729.1	728.4	727.5	726.6	725.7	724.8	723.6
132.5°	767.9	768.5	768.0	767.5	767.0	766.5	765.4	764.4	763.3	762.2	761.1
135°	823.0	823.5	823.3	823.1	822.9	822.6	821.7	820.8	819.9	819.0	818.4
137.5°	874.8	875.6	876.2	876.8	877.4	878.0	877.0	876.1	875.1	874.2	873.3
140°	911.2	911.9	912.1	912.4	912.6	912.8	912.6	912.4	912.1	911.9	911.0
142.5°	944.5	945.2	945.6	946.0	946.5	946.9	946.6	946.4	946.2	946.0	945.2
145°	993.6	994.2	994.9	995.6	996.2	996.9	996.7	996.5	996.2	996.0	995.4
147.5°	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7	1043.7	1043.7	1043.7	1043.0
150°	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9	1072.9	1072.9	1072.9	1072.2
152.5°	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2	1099.5	1099.9	1100.3	1099.9
155°	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6	1138.5	1139.4	1140.3	1140.0
157.5°	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1	1172.0	1173.0	1173.9	1173.8
160°	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5	1192.7	1193.8	1194.9	1195.0
162.5°	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0	1212.1	1213.2	1214.4	1214.2
165°	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3	1236.7	1238.0	1239.4	1239.3
167.5°	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4
170°	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7
172.5°	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7	1276.1	1277.5	1278.9	1278.8
175°	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0	1285.3	1286.7	1288.0	1287.9
177.5°	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3	1289.4	1290.5	1291.6	1291.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	13.3	13.4	13.1	12.8	13.1	13.4	13.3	13.3	14.8	13.4	13.2
90°	29.0	29.5	29.9	30.4	29.9	29.5	29.0	28.6	27.9	27.0	26.1
92.5°	41.7	41.5	41.2	40.9	41.2	41.5	41.7	42.0	41.8	41.1	40.3
95°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	78.6	77.7	76.8
97.5°	121.8	121.8	121.7	121.6	121.7	121.8	121.8	121.9	121.5	120.4	119.4
100°	152.6	153.1	153.5	154.0	153.5	153.1	152.6	152.2	151.6	151.0	150.3
102.5°	187.5	187.4	187.3	187.2	187.3	187.4	187.5	187.6	187.3	186.6	185.9
105°	239.8	240.2	240.7	241.1	240.7	240.2	239.8	239.3	239.1	239.1	239.1
107.5°	298.1	297.8	297.5	297.2	297.5	297.8	298.1	298.3	298.1	297.4	296.7
110°	336.7	336.2	335.8	335.3	335.8	336.2	336.7	337.1	336.9	336.0	335.1



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	376.1	376.0	376.0	375.9	376.0	376.0	376.1	376.2	375.7	374.6	373.6
115°	432.3	432.0	431.8	431.6	431.8	432.0	432.3	432.5	432.5	432.3	432.0
117.5°	490.0	489.4	488.7	488.1	488.7	489.4	490.0	490.6	491.0	491.0	491.1
120°	529.2	528.7	528.3	527.8	528.3	528.7	529.2	529.6	530.0	530.2	530.4
122.5°	567.8	567.2	566.6	565.9	566.6	567.2	567.8	568.4	569.1	569.6	570.2
125°	625.8	624.9	624.0	623.1	624.0	624.9	625.8	626.7	627.6	628.5	629.4
127.5°	683.1	682.1	681.0	680.0	681.0	682.1	683.1	684.1	685.3	686.6	687.8
130°	722.0	720.4	718.9	717.3	718.9	720.4	722.0	723.6	724.8	725.7	726.6
132.5°	759.8	758.6	757.4	756.2	757.4	758.6	759.8	761.1	762.2	763.3	764.4
135°	817.9	817.5	817.0	816.6	817.0	817.5	817.9	818.4	819.0	819.9	820.8
137.5°	872.4	871.6	870.7	869.9	870.7	871.6	872.4	873.3	874.2	875.1	876.1
140°	909.4	907.9	906.3	904.7	906.3	907.9	909.4	911.0	911.9	912.1	912.4
142.5°	944.0	942.8	941.6	940.4	941.6	942.8	944.0	945.2	946.0	946.2	946.4
145°	994.5	993.6	992.7	991.8	992.7	993.6	994.5	995.4	996.0	996.2	996.5
147.5°	1041.7	1040.3	1039.0	1037.6	1039.0	1040.3	1041.7	1043.0	1043.7	1043.7	1043.7
150°	1070.9	1069.5	1068.2	1066.8	1068.2	1069.5	1070.9	1072.2	1072.9	1072.9	1072.9
152.5°	1098.7	1097.5	1096.3	1095.2	1096.3	1097.5	1098.7	1099.9	1100.3	1099.9	1099.5
155°	1138.4	1136.8	1135.3	1133.7	1135.3	1136.8	1138.4	1140.0	1140.3	1139.4	1138.5
157.5°	1172.5	1171.3	1170.0	1168.7	1170.0	1171.3	1172.5	1173.8	1173.9	1173.0	1172.0
160°	1194.1	1193.2	1192.3	1191.4	1192.3	1193.2	1194.1	1195.0	1194.9	1193.8	1192.7
162.5°	1212.8	1211.3	1209.9	1208.4	1209.9	1211.3	1212.8	1214.2	1214.4	1213.2	1212.1
165°	1237.7	1236.1	1234.5	1233.0	1234.5	1236.1	1237.7	1239.3	1239.4	1238.0	1236.7
167.5°	1258.0	1256.6	1255.2	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6
170°	1269.1	1267.5	1265.9	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5
172.5°	1277.2	1275.6	1274.0	1272.5	1274.0	1275.6	1277.2	1278.8	1278.9	1277.5	1276.1
175°	1286.3	1284.7	1283.2	1281.6	1283.2	1284.7	1286.3	1287.9	1288.0	1286.7	1285.3
177.5°	1290.2	1289.0	1287.7	1286.5	1287.7	1289.0	1290.2	1291.5	1291.6	1290.5	1289.4
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	13.8	13.7	12.7	12.5	11.5	11.3	10.4	10.3	10.3	9.9	10.3
90°	25.2	24.3	21.4	18.5	15.5	12.6	10.0	7.8	5.5	3.3	1.0
92.5°	39.6	38.9	37.2	35.6	33.9	32.2	30.6	29.1	27.6	26.0	24.5
95°	75.9	75.0	73.2	71.4	69.6	67.8	66.1	64.5	62.9	61.3	59.8
97.5°	118.4	117.3	116.0	114.7	113.4	112.1	110.9	109.7	108.5	107.3	106.2
100°	149.6	148.9	147.8	146.7	145.6	144.4	143.2	141.8	140.5	139.1	137.8
102.5°	185.3	184.6	183.1	181.6	180.1	178.6	177.5	176.7	175.9	175.1	174.3
105°	239.1	239.1	237.1	235.0	233.0	231.0	229.8	229.3	228.9	228.4	228.0
107.5°	295.9	295.2	294.4	293.6	292.8	292.0	291.4	291.2	290.9	290.6	290.4
110°	334.2	333.3	332.9	332.4	332.0	331.5	331.1	330.6	330.2	329.7	329.3



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	372.5	371.4	371.3	371.2	371.1	371.0	370.9	370.6	370.3	370.1	369.8
115°	431.8	431.6	432.0	432.5	432.9	433.4	433.3	432.6	431.9	431.2	430.6
117.5°	491.1	491.2	491.7	492.3	492.9	493.5	493.6	493.1	492.7	492.2	491.8
120°	530.6	530.9	532.0	533.1	534.2	535.4	535.3	533.9	532.6	531.2	529.9
122.5°	570.8	571.4	572.0	572.6	573.2	573.7	573.5	572.5	571.6	570.6	569.6
125°	630.3	631.2	631.6	632.1	632.5	633.0	632.9	632.2	631.5	630.8	630.2
127.5°	689.1	690.3	690.8	691.3	691.8	692.3	691.8	690.4	689.0	687.5	686.1
130°	727.5	728.4	729.1	729.8	730.5	731.1	730.6	728.8	727.0	725.2	723.4
132.5°	765.4	766.5	767.0	767.5	768.0	768.5	767.9	766.1	764.2	762.4	760.6
135°	821.7	822.6	822.9	823.1	823.3	823.5	823.0	821.6	820.3	818.9	817.6
137.5°	877.0	878.0	877.4	876.8	876.2	875.6	874.8	873.6	872.5	871.4	870.3
140°	912.6	912.8	912.6	912.4	912.1	911.9	911.2	910.1	909.0	907.9	906.7
142.5°	946.6	946.9	946.5	946.0	945.6	945.2	944.5	943.3	942.2	941.1	940.0
145°	996.7	996.9	996.2	995.6	994.9	994.2	993.6	993.2	992.7	992.3	991.8
147.5°	1043.7	1043.7	1043.1	1042.5	1041.8	1041.2	1040.5	1039.7	1038.8	1038.0	1037.2
150°	1072.9	1072.9	1072.4	1072.0	1071.5	1071.1	1070.6	1070.2	1069.7	1069.3	1068.8
152.5°	1099.2	1098.8	1098.6	1098.3	1098.0	1097.7	1097.3	1096.7	1096.0	1095.4	1094.8
155°	1137.6	1136.7	1136.5	1136.3	1136.0	1135.8	1135.7	1135.7	1135.7	1135.7	1135.7
157.5°	1171.1	1170.1	1170.0	1169.8	1169.6	1169.4	1169.5	1169.7	1170.0	1170.3	1170.6
160°	1191.5	1190.4	1190.4	1190.4	1190.4	1190.4	1190.6	1191.1	1191.5	1192.0	1192.4
162.5°	1211.0	1209.9	1209.7	1209.5	1209.3	1209.1	1209.4	1210.0	1210.6	1211.3	1211.9
165°	1235.3	1234.0	1234.0	1234.0	1234.0	1234.0	1234.3	1235.0	1235.7	1236.3	1237.0
167.5°	1255.2	1253.8	1253.7	1253.5	1253.3	1253.1	1253.5	1254.4	1255.3	1256.2	1257.1
170°	1265.9	1264.4	1264.4	1264.4	1264.4	1264.4	1264.8	1265.7	1266.6	1267.5	1268.4
172.5°	1274.7	1273.3	1273.3	1273.3	1273.3	1273.3	1273.7	1274.6	1275.5	1276.4	1277.3
175°	1284.0	1282.6	1282.6	1282.6	1282.6	1282.6	1283.1	1284.0	1284.9	1285.8	1286.7
177.5°	1288.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.6	1288.3	1289.1	1289.8	1290.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.5	12.0	13.7	15.0	17.2	19.0	19.2	18.9	19.1	18.9	18.6
90°	3.3	5.5	7.8	10.0	12.6	15.5	18.5	21.4	24.3	25.2	26.1
92.5°	26.0	27.6	29.1	30.6	32.2	33.9	35.6	37.2	38.9	39.6	40.3
95°	61.3	62.9	64.5	66.1	67.8	69.6	71.4	73.2	75.0	75.9	76.8
97.5°	107.3	108.5	109.7	110.9	112.1	113.4	114.7	116.0	117.3	118.4	119.4
100°	139.1	140.5	141.8	143.2	144.4	145.6	146.7	147.8	148.9	149.6	150.3
102.5°	175.1	175.9	176.7	177.5	178.6	180.1	181.6	183.1	184.6	185.3	185.9
105°	228.4	228.9	229.3	229.8	231.0	233.0	235.0	237.1	239.1	239.1	239.1
107.5°	290.6	290.9	291.2	291.4	292.0	292.8	293.6	294.4	295.2	295.9	296.7
110°	329.7	330.2	330.6	331.1	331.5	332.0	332.4	332.9	333.3	334.2	335.1



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	370.1	370.3	370.6	370.9	371.0	371.1	371.2	371.3	371.4	372.5	373.6
115°	431.2	431.9	432.6	433.3	433.4	432.9	432.5	432.0	431.6	431.8	432.0
117.5°	492.2	492.7	493.1	493.6	493.5	492.9	492.3	491.7	491.2	491.1	491.1
120°	531.2	532.6	533.9	535.3	535.4	534.2	533.1	532.0	530.9	530.6	530.4
122.5°	570.6	571.6	572.5	573.5	573.7	573.2	572.6	572.0	571.4	570.8	570.2
125°	630.8	631.5	632.2	632.9	633.0	632.5	632.1	631.6	631.2	630.3	629.4
127.5°	687.5	689.0	690.4	691.8	692.3	691.8	691.3	690.8	690.3	689.1	687.8
130°	725.2	727.0	728.8	730.6	731.1	730.5	729.8	729.1	728.4	727.5	726.6
132.5°	762.4	764.2	766.1	767.9	768.5	768.0	767.5	767.0	766.5	765.4	764.4
135°	818.9	820.3	821.6	823.0	823.5	823.3	823.1	822.9	822.6	821.7	820.8
137.5°	871.4	872.5	873.6	874.8	875.6	876.2	876.8	877.4	878.0	877.0	876.1
140°	907.9	909.0	910.1	911.2	911.9	912.1	912.4	912.6	912.8	912.6	912.4
142.5°	941.1	942.2	943.3	944.5	945.2	945.6	946.0	946.5	946.9	946.6	946.4
145°	992.3	992.7	993.2	993.6	994.2	994.9	995.6	996.2	996.9	996.7	996.5
147.5°	1038.0	1038.8	1039.7	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7	1043.7
150°	1069.3	1069.7	1070.2	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9	1072.9
152.5°	1095.4	1096.0	1096.7	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2	1099.5
155°	1135.7	1135.7	1135.7	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6	1138.5
157.5°	1170.3	1170.0	1169.7	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1	1172.0
160°	1192.0	1191.5	1191.1	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5	1192.7
162.5°	1211.3	1210.6	1210.0	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0	1212.1
165°	1236.3	1235.7	1235.0	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3	1236.7
167.5°	1256.2	1255.3	1254.4	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2	1256.6
170°	1267.5	1266.6	1265.7	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9	1267.5
172.5°	1276.4	1275.5	1274.6	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7	1276.1
175°	1285.8	1284.9	1284.0	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0	1285.3
177.5°	1289.8	1289.1	1288.3	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3	1289.4
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	18.4	18.1	17.9	18.4	18.0	17.7	18.6
90°	27.0	27.9	28.6	29.0	29.5	29.9	30.4
92.5°	41.1	41.8	42.0	41.7	41.5	41.2	40.9
95°	77.7	78.6	79.0	79.0	79.0	79.0	79.0
97.5°	120.4	121.5	121.9	121.8	121.8	121.7	121.6
100°	151.0	151.6	152.2	152.6	153.1	153.5	154.0
102.5°	186.6	187.3	187.6	187.5	187.4	187.3	187.2
105°	239.1	239.1	239.3	239.8	240.2	240.7	241.1
107.5°	297.4	298.1	298.3	298.1	297.8	297.5	297.2
110°	336.0	336.9	337.1	336.7	336.2	335.8	335.3



TEST NUMBER: P332163

CATALOG NUMBER: S123DIW-S775D1030U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.6	375.7	376.2	376.1	376.0	376.0	375.9
115°	432.3	432.5	432.5	432.3	432.0	431.8	431.6
117.5°	491.0	491.0	490.6	490.0	489.4	488.7	488.1
120°	530.2	530.0	529.6	529.2	528.7	528.3	527.8
122.5°	569.6	569.1	568.4	567.8	567.2	566.6	565.9
125°	628.5	627.6	626.7	625.8	624.9	624.0	623.1
127.5°	686.6	685.3	684.1	683.1	682.1	681.0	680.0
130°	725.7	724.8	723.6	722.0	720.4	718.9	717.3
132.5°	763.3	762.2	761.1	759.8	758.6	757.4	756.2
135°	819.9	819.0	818.4	817.9	817.5	817.0	816.6
137.5°	875.1	874.2	873.3	872.4	871.6	870.7	869.9
140°	912.1	911.9	911.0	909.4	907.9	906.3	904.7
142.5°	946.2	946.0	945.2	944.0	942.8	941.6	940.4
145°	996.2	996.0	995.4	994.5	993.6	992.7	991.8
147.5°	1043.7	1043.7	1043.0	1041.7	1040.3	1039.0	1037.6
150°	1072.9	1072.9	1072.2	1070.9	1069.5	1068.2	1066.8
152.5°	1099.9	1100.3	1099.9	1098.7	1097.5	1096.3	1095.2
155°	1139.4	1140.3	1140.0	1138.4	1136.8	1135.3	1133.7
157.5°	1173.0	1173.9	1173.8	1172.5	1171.3	1170.0	1168.7
160°	1193.8	1194.9	1195.0	1194.1	1193.2	1192.3	1191.4
162.5°	1213.2	1214.4	1214.2	1212.8	1211.3	1209.9	1208.4
165°	1238.0	1239.4	1239.3	1237.7	1236.1	1234.5	1233.0
167.5°	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8
170°	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4
172.5°	1277.5	1278.9	1278.8	1277.2	1275.6	1274.0	1272.5
175°	1286.7	1288.0	1287.9	1286.3	1284.7	1283.2	1281.6
177.5°	1290.5	1291.6	1291.5	1290.2	1289.0	1287.7	1286.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7

(END OF REPORT)