

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332432

Luminaire Tested: **S123RDIW-S775D460U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332432  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D460U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4762.4 lumens  
Efficiency: N/A  
Efficacy: 126.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	101	96	93	89	94	90	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	60	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	37	32	27	33	29	25	29	26	23	21
9	53	41	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	35	29	24	32	26	22	28	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	2.5
10°-20°	337.3	7.1
20°-30°	485.7	10.2
30°-40°	547.1	11.5
40°-50°	523.4	11.0
50°-60°	428.6	9.0
60°-70°	289.2	6.1
70°-80°	145.5	3.1
80°-90°	40.2	0.8
90°-100°	22.0	0.5
100°-110°	104.8	2.2
110°-120°	251.7	5.3
120°-130°	320.5	6.7
130°-140°	342.4	7.2
140°-150°	320.2	6.7
150°-160°	258.3	5.4
160°-170°	166.7	3.5
170°-180°	57.5	1.2
0°-30°	944.3	19.8
0°-40°	1491.4	31.3
0°-60°	2443.4	51.3
0°-90°	2918.3	61.3
90°-120°	378.5	7.9
90°-150°	1361.6	28.6
90°-180°	1844.0	38.7
0°-180°	4762.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	0	5	11	13	14	4
95°	27	10	14	17	17	34
105°	134	136	98	23	20	142
115°	251	254	258	262	264	248
125°	354	358	359	360	361	316
135°	441	443	445	446	445	339
145°	509	512	513	513	514	318
155°	560	559	560	562	559	258
165°	591	590	589	592	590	167
175°	605	603	603	606	602	58
180°	605	605	605	605	605	



TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.2	18.3	16.5	14.6	12.8	12.0	12.3	12.5	12.8	13.0	12.9
90°	0.4	1.4	2.4	3.4	4.4	5.6	6.9	8.2	9.5	10.8	11.2
92.5°	8.4	8.1	7.8	7.5	7.2	7.6	8.6	9.5	10.5	11.5	12.1
95°	27.4	23.3	19.2	15.1	11.0	9.5	10.6	11.7	12.8	13.9	14.6
97.5°	55.1	53.2	51.4	49.6	47.7	43.2	36.0	28.8	21.7	14.5	15.3
100°	75.9	77.9	79.9	81.9	83.9	77.1	61.6	46.0	30.4	14.8	15.6
102.5°	99.6	101.1	102.5	104.0	105.4	97.6	80.6	63.6	46.6	29.6	27.1
105°	133.9	135.0	136.1	137.2	138.3	134.3	125.3	116.4	107.4	98.4	80.7
107.5°	170.0	170.9	171.8	172.6	173.5	174.7	176.1	177.5	178.9	180.3	167.4
110°	194.1	194.9	195.7	196.5	197.3	198.2	199.3	200.4	201.5	202.6	199.3



TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.1	217.8	218.5	219.2	220.0	220.9	222.0	223.1	224.2	225.3	225.3
115°	251.1	251.7	252.3	252.9	253.5	254.3	255.2	256.1	257.0	257.9	258.9
117.5°	284.1	284.9	285.6	286.3	287.1	287.7	288.1	288.6	289.1	289.5	290.3
120°	304.6	305.5	306.4	307.3	308.2	308.8	309.1	309.4	309.7	310.0	310.8
122.5°	325.5	326.2	326.9	327.7	328.4	329.0	329.4	329.7	330.1	330.5	331.0
125°	354.0	354.8	355.6	356.4	357.2	357.8	358.2	358.6	359.0	359.4	359.6
127.5°	381.7	382.5	383.3	384.1	384.9	385.5	386.0	386.5	387.0	387.5	387.8
130°	399.0	399.8	400.6	401.4	402.2	402.8	403.2	403.6	404.0	404.3	404.7
132.5°	415.5	416.3	417.1	417.9	418.7	419.2	419.6	419.9	420.2	420.5	420.9
135°	440.7	441.3	441.9	442.5	443.1	443.6	444.0	444.4	444.8	445.2	445.5
137.5°	462.3	463.1	463.8	464.6	465.3	465.8	466.1	466.3	466.5	466.7	467.2
140°	476.7	477.3	477.9	478.5	479.1	479.5	479.8	480.1	480.4	480.7	481.1
142.5°	490.0	490.6	491.2	491.8	492.4	492.8	493.1	493.4	493.7	494.0	494.3
145°	508.6	509.3	510.0	510.7	511.4	511.8	512.0	512.2	512.4	512.6	512.8
147.5°	526.1	526.6	527.0	527.5	527.9	528.3	528.5	528.7	528.9	529.1	529.3
150°	536.9	537.2	537.5	537.8	538.1	538.3	538.5	538.7	538.9	539.1	539.3
152.5°	546.6	546.7	546.9	547.0	547.2	547.3	547.4	547.5	547.6	547.8	548.1
155°	560.2	560.0	559.8	559.7	559.5	559.4	559.5	559.6	559.7	559.8	560.3
157.5°	570.9	570.8	570.8	570.8	570.8	570.7	570.6	570.5	570.4	570.3	570.9
160°	577.3	577.2	577.1	577.0	576.9	576.8	576.7	576.6	576.5	576.4	577.0
162.5°	583.4	583.2	582.9	582.7	582.4	582.2	582.1	582.0	581.9	581.8	582.5
165°	590.8	590.5	590.2	589.9	589.6	589.4	589.3	589.2	589.1	589.0	589.8
167.5°	596.6	596.2	595.8	595.4	595.0	594.8	594.8	594.8	594.8	594.8	595.6
170°	599.8	599.4	599.0	598.6	598.2	598.0	598.0	598.0	598.0	598.0	598.8
172.5°	601.9	601.5	601.0	600.5	600.0	599.8	599.9	600.0	600.1	600.1	600.9
175°	604.7	604.2	603.7	603.2	602.7	602.5	602.6	602.7	602.8	602.9	603.6
177.5°	605.4	605.0	604.6	604.2	603.8	603.7	603.8	603.8	603.9	604.0	604.6
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7



TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	12.8	12.7	12.6	12.5	12.3	12.2	12.1	11.9
90°	11.6	12.0	12.4	12.7	12.9	13.1	13.3	13.5
92.5°	12.8	13.4	14.1	14.4	14.6	14.7	14.8	14.9
95°	15.3	16.0	16.7	17.1	17.1	17.1	17.1	17.1
97.5°	16.1	16.9	17.7	18.1	18.2	18.3	18.4	18.5
100°	16.4	17.2	18.0	18.5	18.6	18.7	18.8	18.9
102.5°	24.6	22.1	19.7	18.5	18.7	18.9	19.0	19.2
105°	63.0	45.4	27.7	19.0	19.2	19.4	19.6	19.8
107.5°	154.4	141.5	128.5	115.4	102.0	88.7	75.4	62.1
110°	196.0	192.7	189.4	180.7	166.4	152.1	137.8	123.6





TEST NUMBER: P332432

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.4	225.4	225.5	224.0	221.0	218.0	215.0	212.0
115°	259.9	260.9	261.9	262.6	263.0	263.4	263.8	264.2
117.5°	291.1	291.9	292.7	293.1	293.2	293.3	293.4	293.5
120°	311.6	312.4	313.2	313.6	313.6	313.6	313.6	313.6
122.5°	331.6	332.2	332.7	333.0	333.1	333.2	333.3	333.4
125°	359.8	360.0	360.2	360.4	360.6	360.8	361.0	361.2
127.5°	388.1	388.4	388.7	388.8	388.6	388.4	388.2	388.0
130°	405.1	405.5	405.9	406.0	405.8	405.6	405.4	405.2
132.5°	421.3	421.7	422.1	422.2	421.9	421.6	421.3	421.1
135°	445.8	446.1	446.4	446.4	446.1	445.8	445.5	445.2
137.5°	467.7	468.1	468.6	468.8	468.6	468.4	468.2	468.0
140°	481.5	481.9	482.3	482.4	482.2	482.0	481.8	481.6
142.5°	494.7	495.0	495.3	495.3	495.0	494.8	494.5	494.2
145°	513.0	513.2	513.4	513.5	513.5	513.5	513.5	513.5
147.5°	529.5	529.7	529.9	529.7	529.3	528.8	528.4	527.9
150°	539.5	539.7	539.9	539.9	539.6	539.3	539.0	538.7
152.5°	548.5	548.8	549.2	549.1	548.7	548.2	547.8	547.3
155°	560.8	561.3	561.8	561.7	561.1	560.5	559.9	559.4
157.5°	571.5	572.1	572.7	572.6	571.8	571.1	570.3	569.5
160°	577.6	578.2	578.8	578.8	578.1	577.4	576.7	576.0
162.5°	583.2	583.9	584.5	584.6	583.9	583.3	582.7	582.1
165°	590.6	591.4	592.2	592.2	591.5	590.9	590.2	589.5
167.5°	596.4	597.1	597.9	597.9	597.1	596.4	595.6	594.8
170°	599.6	600.4	601.2	601.2	600.4	599.6	598.8	598.0
172.5°	601.7	602.5	603.3	603.3	602.4	601.5	600.7	599.8
175°	604.3	605.0	605.7	605.7	604.9	604.1	603.3	602.5
177.5°	605.3	605.9	606.6	606.5	605.7	604.9	604.1	603.3
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7

(END OF REPORT)