

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332126-935

Luminaire Tested: **S123DIW-S560D755U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332126-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D755U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4657.3 lumens  
Efficiency: N/A  
Efficacy: 123.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.0	1.4
10°-20°	215.0	4.6
20°-30°	360.8	7.7
30°-40°	408.6	8.8
40°-50°	366.4	7.9
50°-60°	295.7	6.3
60°-70°	206.0	4.4
70°-80°	108.3	2.3
80°-90°	28.9	0.6
90°-100°	31.0	0.7
100°-110°	147.8	3.2
110°-120°	355.0	7.6
120°-130°	452.0	9.7
130°-140°	482.9	10.4
140°-150°	451.6	9.7
150°-160°	364.3	7.8
160°-170°	235.1	5.0
170°-180°	81.0	1.7
0°-30°	642.9	13.8
0°-40°	1051.4	22.6
0°-60°	1713.5	36.8
0°-90°	2056.7	44.2
90°-120°	533.7	11.5
90°-150°	1920.2	41.2
90°-180°	2601.0	55.8
0°-180°	4657.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	26
90°	19	1	19	1	19	10
95°	24	39	24	39	24	20
105°	28	189	28	189	28	64
115°	373	354	373	354	373	344
125°	509	499	509	499	509	455
135°	628	622	628	622	628	484
145°	724	717	724	717	724	452
155°	789	790	789	790	789	364
165°	831	833	831	833	831	235
175°	850	853	850	853	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	11.7	11.1	11.4	11.5	11.2	11.4	11.5	11.7	11.9	12.0	11.9
90°	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4	15.8	15.2	13.3
92.5°	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0	17.1	16.2	14.8
95°	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6	20.7	19.6	18.1
97.5°	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6	21.5	20.4	30.6
100°	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2	22.0	20.9	42.9
102.5°	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7	38.2	41.7	65.7
105°	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9	113.8	138.8	151.4
107.5°	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7	236.0	254.3	252.4
110°	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5	281.1	285.8	284.2



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9	317.8	317.7	316.2
115°	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5	365.1	363.7	362.4
117.5°	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5	409.4	408.3	407.6
120°	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5	438.3	437.1	436.8
122.5°	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6	466.8	466.1	465.5
125°	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4	507.1	506.9	506.3
127.5°	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3	546.8	546.4	545.7
130°	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4	570.8	570.2	569.6
132.5°	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2	593.6	593.1	592.5
135°	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8	627.3
137.5°	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5	658.8	658.1	657.9
140°	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1	678.5	678.0	677.5
142.5°	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6	697.2	696.7	696.3
145°	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5	723.2	722.9	722.6
147.5°	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7	746.4	746.1	745.8
150°	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9	760.6	760.3	760.0
152.5°	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4	772.9	772.5	772.3
155°	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8	790.1	789.5	789.3
157.5°	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0	805.1	804.3	804.4
160°	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6	813.7	812.9	813.0
162.5°	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4	821.5	820.4	820.6
165°	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8	831.7	830.6	830.8
167.5°	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7	838.7
170°	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3	843.3
172.5°	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6	847.5	846.4	846.2
175°	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2	851.3	850.2	850.2
177.5°	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6	852.6	851.8	851.7
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	12.1	12.0	10.8	9.5	8.6	7.6	7.2	6.5	6.2	6.5	6.5
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6	2.1	3.4	4.8
92.5°	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8	11.4	11.0	10.6
95°	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7	32.9	27.1	21.4
97.5°	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7	75.1	72.5	69.9
100°	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1	109.9	112.7	115.5
102.5°	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5	142.6	144.6	146.6
105°	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8	190.4	191.9	193.5
107.5°	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7	241.0	242.2	243.5
110°	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7	274.8	276.0	277.1





TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2	307.1	308.2	309.2
115°	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1	355.0	355.9	356.7
117.5°	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7	401.7	402.8	403.8
120°	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6	430.8	432.1	433.3
122.5°	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0	460.0	461.1	462.1
125°	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3	500.4	501.5	502.7
127.5°	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3	539.4	540.5	541.7
130°	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6	563.8	564.9	566.0
132.5°	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9	587.0	588.1	589.3
135°	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6	622.4	623.2	624.1
137.5°	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9	653.0	654.1	655.1
140°	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2	673.0	673.9	674.8
142.5°	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0	691.8	692.7	693.5
145°	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2	718.2	719.2	720.1
147.5°	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9	742.5	743.2	743.8
150°	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2	757.5	757.9	758.4
152.5°	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8	771.0	771.2	771.4
155°	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1	789.8	789.5	789.2
157.5°	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0	805.0	804.9	804.9
160°	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2	814.0	813.9	813.7
162.5°	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8	822.4	822.0	821.7
165°	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2	832.8	832.3	831.9
167.5°	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3	840.7	840.2	839.6
170°	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8	845.2	844.7	844.1
172.5°	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9	848.2	847.5	846.9
175°	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8	852.0	851.4	850.7
177.5°	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8	853.3	852.6	852.1
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	6.5	7.1	7.2	7.8	7.9	8.6	8.7	8.3	8.4	9.3	8.4
90°	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4	16.9	17.5	17.9
92.5°	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0	18.9	19.8	20.3
95°	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6	22.6	23.6	24.1
97.5°	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6	23.8	24.9	25.6
100°	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2	24.3	25.4	26.1
102.5°	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7	31.3	27.7	26.1
105°	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9	64.0	39.1	26.8
107.5°	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7	199.5	181.2	162.7
110°	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5	271.8	267.2	254.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9	318.0	318.1	315.9
115°	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5	367.9	369.3	370.3
117.5°	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5	411.6	412.8	413.4
120°	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5	440.6	441.7	442.2
122.5°	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6	468.4	469.2	469.7
125°	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4	507.7	508.0	508.2
127.5°	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3	547.8	548.2	548.3
130°	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4	571.9	572.5	572.7
132.5°	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2	594.7	595.3	595.4
135°	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7	629.1	629.6	629.6
137.5°	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5	660.2	660.9	661.1
140°	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1	679.6	680.2	680.4
142.5°	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6	698.0	698.4	698.5
145°	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5	723.8	724.0	724.2
147.5°	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7	746.9	747.3	747.0
150°	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9	761.1	761.4	761.4
152.5°	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4	774.0	774.5	774.4
155°	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8	791.5	792.3	792.2
157.5°	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0	806.8	807.6	807.5
160°	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6	815.5	816.2	816.2
162.5°	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4	823.4	824.3	824.3
165°	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8	834.0	835.1	835.2
167.5°	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9	842.1	843.3	843.3
170°	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5	846.7	847.8	847.8
172.5°	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6	849.7	850.8	850.8
175°	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2	853.3	854.2	854.1
177.5°	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6	854.5	855.4	855.2
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	8.4	8.4	8.3	8.0	8.3	8.4	8.4	8.4	9.3	8.4	8.3
90°	18.2	18.4	18.7	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4
92.5°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0
95°	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6
97.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6
100°	26.2	26.3	26.4	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2
102.5°	26.3	26.6	26.9	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7
105°	27.0	27.3	27.6	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9
107.5°	143.9	125.1	106.3	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7
110°	234.6	214.5	194.3	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.7	307.5	303.2	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9
115°	370.8	371.4	372.0	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5
117.5°	413.5	413.6	413.7	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5
120°	442.2	442.2	442.2	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5
122.5°	469.8	469.8	470.0	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6
125°	508.6	508.9	509.1	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4
127.5°	548.0	547.7	547.4	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3
130°	572.3	572.0	571.8	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4
132.5°	595.0	594.6	594.2	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2
135°	629.1	628.7	628.3	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7
137.5°	660.8	660.5	660.2	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5
140°	680.0	679.8	679.5	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1
142.5°	698.1	697.8	697.3	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6
145°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5
147.5°	746.4	745.7	745.1	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7
150°	761.0	760.5	760.1	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9
152.5°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4
155°	791.3	790.5	789.6	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8
157.5°	806.4	805.3	804.3	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0
160°	815.2	814.2	813.2	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6
162.5°	823.5	822.6	821.7	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4
165°	834.2	833.2	832.2	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8
167.5°	842.1	840.9	839.8	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9
170°	846.7	845.5	844.4	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5
172.5°	849.5	848.3	847.1	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6
175°	853.0	851.9	850.8	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2
177.5°	854.1	853.0	851.9	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	8.7	8.6	7.9	7.8	7.2	7.1	6.5	6.5	6.5	6.2	6.5
90°	15.8	15.2	13.3	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6
92.5°	17.1	16.2	14.8	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8
95°	20.7	19.6	18.1	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7
97.5°	21.5	20.4	30.6	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7
100°	22.0	20.9	42.9	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1
102.5°	38.2	41.7	65.7	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5
105°	113.8	138.8	151.4	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8
107.5°	236.0	254.3	252.4	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7
110°	281.1	285.8	284.2	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.8	317.7	316.2	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2
115°	365.1	363.7	362.4	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1
117.5°	409.4	408.3	407.6	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7
120°	438.3	437.1	436.8	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6
122.5°	466.8	466.1	465.5	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0
125°	507.1	506.9	506.3	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3
127.5°	546.8	546.4	545.7	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3
130°	570.8	570.2	569.6	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6
132.5°	593.6	593.1	592.5	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9
135°	628.3	627.8	627.3	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6
137.5°	658.8	658.1	657.9	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9
140°	678.5	678.0	677.5	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2
142.5°	697.2	696.7	696.3	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0
145°	723.2	722.9	722.6	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2
147.5°	746.4	746.1	745.8	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9
150°	760.6	760.3	760.0	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2
152.5°	772.9	772.5	772.3	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8
155°	790.1	789.5	789.3	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1
157.5°	805.1	804.3	804.4	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0
160°	813.7	812.9	813.0	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2
162.5°	821.5	820.4	820.6	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8
165°	831.7	830.6	830.8	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2
167.5°	839.8	838.7	838.7	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3
170°	844.4	843.3	843.3	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8
172.5°	847.5	846.4	846.2	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9
175°	851.3	850.2	850.2	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8
177.5°	852.6	851.8	851.7	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.2	7.6	8.6	9.5	10.8	12.0	12.1	11.9	12.0	11.9	11.7
90°	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4
92.5°	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0
95°	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6
97.5°	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6
100°	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2
102.5°	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7
105°	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9
107.5°	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7
110°	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5





TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9
115°	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5
117.5°	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5
120°	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5
122.5°	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6
125°	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4
127.5°	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3
130°	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4
132.5°	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2
135°	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7
137.5°	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5
140°	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1
142.5°	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6
145°	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5
147.5°	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7
150°	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9
152.5°	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4
155°	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8
157.5°	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0
160°	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6
162.5°	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4
165°	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8
167.5°	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9
170°	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5
172.5°	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6
175°	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2
177.5°	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	11.5	11.4	11.2	11.5	11.4	11.1	11.7
90°	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332126-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)