

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332163-935

Luminaire Tested: **S123DIW-S775D1030U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332163-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1030U935-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5887.8 lumens  
Efficiency: N/A  
Efficacy: 111.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48	48	48	48	48	48		
	1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41		
	2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	35	35		
	3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34	29	29	29	29	29	29		
	4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25	25	25		
	5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	25	22	22	22	22	22	22		
	6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22	20	20	20	20	20	20		
	7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17	17	17	17	17	17		
	8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16	16	16	16	16	16		
	9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14	14	14	14	14	14		
	10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13	13	13	13		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.6	1.6
10°-20°	293.9	5.0
20°-30°	493.2	8.4
30°-40°	558.5	9.5
40°-50°	500.8	8.5
50°-60°	404.1	6.9
60°-70°	281.6	4.8
70°-80°	148.0	2.5
80°-90°	39.5	0.7
90°-100°	72.4	1.2
100°-110°	216.5	3.7
110°-120°	368.3	6.3
120°-130°	484.4	8.2
130°-140°	544.4	9.2
140°-150°	535.2	9.1
150°-160°	450.5	7.7
160°-170°	299.9	5.1
170°-180°	105.0	1.8
0°-30°	878.7	14.9
0°-40°	1437.2	24.4
0°-60°	2342.1	39.8
0°-90°	2811.2	47.7
90°-120°	657.1	11.2
90°-150°	2221.1	37.7
90°-180°	3077.0	52.3
0°-180°	5887.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	26	1	26	1	26	14
95°	68	52	68	52	68	70
105°	208	196	208	196	208	220
115°	372	371	372	371	372	368
125°	536	543	536	543	536	480
135°	703	704	703	704	703	541
145°	854	854	854	854	854	533
155°	976	978	976	978	976	449
165°	1062	1065	1062	1065	1062	299
175°	1104	1108	1104	1108	1104	105
180°	1110	1110	1110	1110	1110	



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	16.0	15.2	15.5	15.8	15.4	15.6	15.8	16.0	16.3	16.4	16.3
90°	26.2	25.7	25.4	25.0	24.6	24.0	23.2	22.5	21.7	20.9	18.4
92.5°	35.2	35.5	35.7	35.9	36.2	36.0	35.4	34.7	34.1	33.5	32.0
95°	68.0	68.0	68.0	68.0	68.0	67.7	66.9	66.1	65.3	64.6	63.0
97.5°	104.7	104.8	104.9	104.9	105.0	104.6	103.7	102.8	101.9	101.0	99.9
100°	132.6	132.2	131.8	131.4	131.0	130.5	130.0	129.4	128.8	128.2	127.3
102.5°	161.2	161.3	161.4	161.4	161.5	161.3	160.7	160.1	159.5	158.9	157.6
105°	207.6	207.2	206.8	206.5	206.0	205.9	205.9	205.9	205.9	205.9	204.1
107.5°	255.9	256.1	256.4	256.7	256.8	256.7	256.1	255.5	254.8	254.2	253.5
110°	288.7	289.1	289.5	289.9	290.2	290.1	289.3	288.5	287.7	287.0	286.6



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.6	323.7	323.7	323.8	323.9	323.5	322.5	321.7	320.7	319.8	319.7
115°	371.6	371.8	372.0	372.2	372.4	372.4	372.2	372.0	371.8	371.6	372.0
117.5°	420.3	420.8	421.4	421.9	422.4	422.8	422.8	422.8	422.8	422.9	423.4
120°	454.4	454.9	455.2	455.6	456.0	456.3	456.5	456.7	456.8	457.1	458.1
122.5°	487.2	487.8	488.4	488.9	489.4	490.0	490.4	490.9	491.5	492.0	492.5
125°	536.5	537.3	538.0	538.8	539.6	540.4	541.1	541.9	542.7	543.5	543.8
127.5°	585.5	586.3	587.3	588.1	589.0	590.0	591.2	592.2	593.3	594.3	594.8
130°	617.6	619.0	620.3	621.6	623.0	624.1	624.8	625.6	626.4	627.2	627.8
132.5°	651.1	652.1	653.2	654.2	655.3	656.3	657.2	658.1	659.0	660.0	660.4
135°	703.1	703.4	703.9	704.2	704.6	705.2	705.9	706.7	707.5	708.3	708.5
137.5°	749.0	749.7	750.4	751.1	751.9	752.7	753.5	754.3	755.1	756.0	755.4
140°	778.9	780.3	781.7	783.0	784.4	785.1	785.3	785.6	785.7	785.9	785.7
142.5°	809.7	810.7	811.8	812.8	813.8	814.5	814.7	814.9	815.0	815.3	814.9
145°	853.9	854.7	855.5	856.3	857.0	857.6	857.7	858.0	858.2	858.3	857.7
147.5°	893.4	894.6	895.7	896.9	898.0	898.6	898.6	898.6	898.6	898.6	898.1
150°	918.5	919.7	920.8	922.0	923.2	923.8	923.8	923.8	923.8	923.8	923.3
152.5°	943.0	943.9	944.9	946.0	947.0	947.4	947.0	946.7	946.4	946.1	945.9
155°	976.1	977.5	978.8	980.2	981.5	981.8	981.0	980.2	979.5	978.7	978.5
157.5°	1006.3	1007.4	1008.5	1009.5	1010.6	1010.7	1010.0	1009.1	1008.3	1007.5	1007.4
160°	1025.8	1026.6	1027.3	1028.1	1028.9	1028.8	1027.9	1026.9	1025.9	1024.9	1024.9
162.5°	1040.4	1041.7	1042.9	1044.2	1045.4	1045.6	1044.6	1043.6	1042.7	1041.7	1041.6
165°	1061.6	1062.9	1064.3	1065.7	1067.0	1067.1	1065.9	1064.8	1063.6	1062.5	1062.5
167.5°	1079.5	1080.7	1081.9	1083.1	1084.3	1084.3	1083.1	1081.9	1080.7	1079.5	1079.4
170°	1088.6	1089.9	1091.3	1092.7	1094.1	1094.1	1092.7	1091.3	1089.9	1088.6	1088.6
172.5°	1095.6	1096.9	1098.3	1099.7	1101.0	1101.1	1099.9	1098.7	1097.5	1096.3	1096.3
175°	1103.5	1104.8	1106.1	1107.5	1108.9	1109.0	1107.8	1106.6	1105.5	1104.3	1104.3
177.5°	1107.7	1108.7	1109.8	1110.9	1112.0	1112.1	1111.1	1110.2	1109.2	1108.4	1108.4
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	16.5	16.4	14.8	12.9	11.8	10.3	9.9	8.9	8.5	8.9	8.9
90°	15.9	13.3	10.8	8.6	6.7	4.7	2.8	0.9	2.8	4.7	6.7
92.5°	30.7	29.2	27.7	26.3	25.1	23.8	22.4	21.1	22.4	23.8	25.1
95°	61.5	59.9	58.4	56.9	55.5	54.2	52.8	51.5	52.8	54.2	55.5
97.5°	98.8	97.6	96.5	95.5	94.5	93.4	92.4	91.4	92.4	93.4	94.5
100°	126.3	125.4	124.3	123.3	122.1	121.0	119.8	118.6	119.8	121.0	122.1
102.5°	156.4	155.1	153.8	152.8	152.1	151.4	150.8	150.1	150.8	151.4	152.1
105°	202.3	200.6	198.9	197.9	197.4	197.1	196.7	196.3	196.7	197.1	197.4
107.5°	252.8	252.1	251.4	250.9	250.7	250.5	250.2	250.0	250.2	250.5	250.7
110°	286.2	285.9	285.4	285.1	284.6	284.3	283.9	283.5	283.9	284.3	284.6





TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	319.6	319.5	319.4	319.3	319.1	318.8	318.7	318.4	318.7	318.8	319.1
115°	372.4	372.7	373.2	373.1	372.5	371.9	371.3	370.7	371.3	371.9	372.5
117.5°	423.9	424.4	424.9	425.0	424.6	424.2	423.8	423.4	423.8	424.2	424.6
120°	459.0	459.9	461.0	460.9	459.7	458.6	457.4	456.2	457.4	458.6	459.7
122.5°	493.0	493.5	494.0	493.8	492.9	492.1	491.3	490.4	491.3	492.1	492.9
125°	544.2	544.6	545.0	544.9	544.3	543.7	543.1	542.6	543.1	543.7	544.3
127.5°	595.2	595.6	596.1	595.6	594.4	593.2	591.9	590.7	591.9	593.2	594.4
130°	628.4	629.0	629.5	629.0	627.5	625.9	624.4	622.8	624.4	625.9	627.5
132.5°	660.8	661.2	661.7	661.2	659.6	658.0	656.4	654.9	656.4	658.0	659.6
135°	708.7	708.9	709.0	708.6	707.4	706.3	705.1	704.0	705.1	706.3	707.4
137.5°	754.9	754.4	753.9	753.2	752.2	751.2	750.3	749.3	750.3	751.2	752.2
140°	785.6	785.3	785.1	784.5	783.6	782.6	781.7	780.7	781.7	782.6	783.6
142.5°	814.5	814.2	813.8	813.2	812.2	811.2	810.3	809.3	810.3	811.2	812.2
145°	857.2	856.6	856.0	855.5	855.1	854.7	854.4	853.9	854.4	854.7	855.1
147.5°	897.6	897.0	896.5	895.9	895.2	894.4	893.7	893.0	893.7	894.4	895.2
150°	923.0	922.6	922.2	921.8	921.4	921.0	920.7	920.2	920.7	921.0	921.4
152.5°	945.6	945.4	945.1	944.8	944.3	943.7	943.1	942.6	943.1	943.7	944.3
155°	978.4	978.1	977.9	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8
157.5°	1007.2	1007.0	1006.9	1006.9	1007.1	1007.4	1007.6	1007.9	1007.6	1007.4	1007.1
160°	1024.9	1024.9	1024.9	1025.1	1025.5	1025.9	1026.3	1026.7	1026.3	1025.9	1025.5
162.5°	1041.4	1041.2	1041.0	1041.3	1041.8	1042.3	1042.9	1043.4	1042.9	1042.3	1041.8
165°	1062.5	1062.5	1062.5	1062.7	1063.3	1063.9	1064.5	1065.1	1064.5	1063.9	1063.3
167.5°	1079.3	1079.1	1078.9	1079.3	1080.0	1080.8	1081.6	1082.4	1081.6	1080.8	1080.0
170°	1088.6	1088.6	1088.6	1089.0	1089.8	1090.5	1091.3	1092.1	1091.3	1090.5	1089.8
172.5°	1096.3	1096.3	1096.3	1096.7	1097.4	1098.2	1099.0	1099.8	1099.0	1098.2	1097.4
175°	1104.3	1104.3	1104.3	1104.7	1105.5	1106.3	1107.1	1107.8	1107.1	1106.3	1105.5
177.5°	1108.4	1108.4	1108.4	1108.6	1109.2	1109.9	1110.5	1111.1	1110.5	1109.9	1109.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	9.0	9.7	9.9	10.8	10.9	11.8	11.9	11.4	11.5	12.7	11.5
90°	8.6	10.8	13.3	15.9	18.4	20.9	21.7	22.5	23.2	24.0	24.6
92.5°	26.3	27.7	29.2	30.7	32.0	33.5	34.1	34.7	35.4	36.0	36.2
95°	56.9	58.4	59.9	61.5	63.0	64.6	65.3	66.1	66.9	67.7	68.0
97.5°	95.5	96.5	97.6	98.8	99.9	101.0	101.9	102.8	103.7	104.6	105.0
100°	123.3	124.3	125.4	126.3	127.3	128.2	128.8	129.4	130.0	130.5	131.0
102.5°	152.8	153.8	155.1	156.4	157.6	158.9	159.5	160.1	160.7	161.3	161.5
105°	197.9	198.9	200.6	202.3	204.1	205.9	205.9	205.9	205.9	205.9	206.0
107.5°	250.9	251.4	252.1	252.8	253.5	254.2	254.8	255.5	256.1	256.7	256.8
110°	285.1	285.4	285.9	286.2	286.6	287.0	287.7	288.5	289.3	290.1	290.2



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	319.3	319.4	319.5	319.6	319.7	319.8	320.7	321.7	322.5	323.5	323.9
115°	373.1	373.2	372.7	372.4	372.0	371.6	371.8	372.0	372.2	372.4	372.4
117.5°	425.0	424.9	424.4	423.9	423.4	422.9	422.8	422.8	422.8	422.8	422.4
120°	460.9	461.0	459.9	459.0	458.1	457.1	456.8	456.7	456.5	456.3	456.0
122.5°	493.8	494.0	493.5	493.0	492.5	492.0	491.5	490.9	490.4	490.0	489.4
125°	544.9	545.0	544.6	544.2	543.8	543.5	542.7	541.9	541.1	540.4	539.6
127.5°	595.6	596.1	595.6	595.2	594.8	594.3	593.3	592.2	591.2	590.0	589.0
130°	629.0	629.5	629.0	628.4	627.8	627.2	626.4	625.6	624.8	624.1	623.0
132.5°	661.2	661.7	661.2	660.8	660.4	660.0	659.0	658.1	657.2	656.3	655.3
135°	708.6	709.0	708.9	708.7	708.5	708.3	707.5	706.7	705.9	705.2	704.6
137.5°	753.2	753.9	754.4	754.9	755.4	756.0	755.1	754.3	753.5	752.7	751.9
140°	784.5	785.1	785.3	785.6	785.7	785.9	785.7	785.6	785.3	785.1	784.4
142.5°	813.2	813.8	814.2	814.5	814.9	815.3	815.0	814.9	814.7	814.5	813.8
145°	855.5	856.0	856.6	857.2	857.7	858.3	858.2	858.0	857.7	857.6	857.0
147.5°	895.9	896.5	897.0	897.6	898.1	898.6	898.6	898.6	898.6	898.6	898.0
150°	921.8	922.2	922.6	923.0	923.3	923.8	923.8	923.8	923.8	923.8	923.2
152.5°	944.8	945.1	945.4	945.6	945.9	946.1	946.4	946.7	947.0	947.4	947.0
155°	977.8	977.9	978.1	978.4	978.5	978.7	979.5	980.2	981.0	981.8	981.5
157.5°	1006.9	1006.9	1007.0	1007.2	1007.4	1007.5	1008.3	1009.1	1010.0	1010.7	1010.6
160°	1025.1	1024.9	1024.9	1024.9	1024.9	1024.9	1025.9	1026.9	1027.9	1028.8	1028.9
162.5°	1041.3	1041.0	1041.2	1041.4	1041.6	1041.7	1042.7	1043.6	1044.6	1045.6	1045.4
165°	1062.7	1062.5	1062.5	1062.5	1062.5	1062.5	1063.6	1064.8	1065.9	1067.1	1067.0
167.5°	1079.3	1078.9	1079.1	1079.3	1079.4	1079.5	1080.7	1081.9	1083.1	1084.3	1084.3
170°	1089.0	1088.6	1088.6	1088.6	1088.6	1088.6	1089.9	1091.3	1092.7	1094.1	1094.1
172.5°	1096.7	1096.3	1096.3	1096.3	1096.3	1096.3	1097.5	1098.7	1099.9	1101.1	1101.0
175°	1104.7	1104.3	1104.3	1104.3	1104.3	1104.3	1105.5	1106.6	1107.8	1109.0	1108.9
177.5°	1108.6	1108.4	1108.4	1108.4	1108.4	1108.4	1109.2	1110.2	1111.1	1112.1	1112.0
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	11.5	11.5	11.3	11.0	11.3	11.5	11.5	11.5	12.7	11.5	11.4
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	24.0	23.2	22.5
92.5°	35.9	35.7	35.5	35.2	35.5	35.7	35.9	36.2	36.0	35.4	34.7
95°	68.0	68.0	68.0	68.0	68.0	68.0	68.0	68.0	67.7	66.9	66.1
97.5°	104.9	104.9	104.8	104.7	104.8	104.9	104.9	105.0	104.6	103.7	102.8
100°	131.4	131.8	132.2	132.6	132.2	131.8	131.4	131.0	130.5	130.0	129.4
102.5°	161.4	161.4	161.3	161.2	161.3	161.4	161.4	161.5	161.3	160.7	160.1
105°	206.5	206.8	207.2	207.6	207.2	206.8	206.5	206.0	205.9	205.9	205.9
107.5°	256.7	256.4	256.1	255.9	256.1	256.4	256.7	256.8	256.7	256.1	255.5
110°	289.9	289.5	289.1	288.7	289.1	289.5	289.9	290.2	290.1	289.3	288.5



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	323.8	323.7	323.7	323.6	323.7	323.7	323.8	323.9	323.5	322.5	321.7
115°	372.2	372.0	371.8	371.6	371.8	372.0	372.2	372.4	372.4	372.2	372.0
117.5°	421.9	421.4	420.8	420.3	420.8	421.4	421.9	422.4	422.8	422.8	422.8
120°	455.6	455.2	454.9	454.4	454.9	455.2	455.6	456.0	456.3	456.5	456.7
122.5°	488.9	488.4	487.8	487.2	487.8	488.4	488.9	489.4	490.0	490.4	490.9
125°	538.8	538.0	537.3	536.5	537.3	538.0	538.8	539.6	540.4	541.1	541.9
127.5°	588.1	587.3	586.3	585.5	586.3	587.3	588.1	589.0	590.0	591.2	592.2
130°	621.6	620.3	619.0	617.6	619.0	620.3	621.6	623.0	624.1	624.8	625.6
132.5°	654.2	653.2	652.1	651.1	652.1	653.2	654.2	655.3	656.3	657.2	658.1
135°	704.2	703.9	703.4	703.1	703.4	703.9	704.2	704.6	705.2	705.9	706.7
137.5°	751.1	750.4	749.7	749.0	749.7	750.4	751.1	751.9	752.7	753.5	754.3
140°	783.0	781.7	780.3	778.9	780.3	781.7	783.0	784.4	785.1	785.3	785.6
142.5°	812.8	811.8	810.7	809.7	810.7	811.8	812.8	813.8	814.5	814.7	814.9
145°	856.3	855.5	854.7	853.9	854.7	855.5	856.3	857.0	857.6	857.7	858.0
147.5°	896.9	895.7	894.6	893.4	894.6	895.7	896.9	898.0	898.6	898.6	898.6
150°	922.0	920.8	919.7	918.5	919.7	920.8	922.0	923.2	923.8	923.8	923.8
152.5°	946.0	944.9	943.9	943.0	943.9	944.9	946.0	947.0	947.4	947.0	946.7
155°	980.2	978.8	977.5	976.1	977.5	978.8	980.2	981.5	981.8	981.0	980.2
157.5°	1009.5	1008.5	1007.4	1006.3	1007.4	1008.5	1009.5	1010.6	1010.7	1010.0	1009.1
160°	1028.1	1027.3	1026.6	1025.8	1026.6	1027.3	1028.1	1028.9	1028.8	1027.9	1026.9
162.5°	1044.2	1042.9	1041.7	1040.4	1041.7	1042.9	1044.2	1045.4	1045.6	1044.6	1043.6
165°	1065.7	1064.3	1062.9	1061.6	1062.9	1064.3	1065.7	1067.0	1067.1	1065.9	1064.8
167.5°	1083.1	1081.9	1080.7	1079.5	1080.7	1081.9	1083.1	1084.3	1084.3	1083.1	1081.9
170°	1092.7	1091.3	1089.9	1088.6	1089.9	1091.3	1092.7	1094.1	1094.1	1092.7	1091.3
172.5°	1099.7	1098.3	1096.9	1095.6	1096.9	1098.3	1099.7	1101.0	1101.1	1099.9	1098.7
175°	1107.5	1106.1	1104.8	1103.5	1104.8	1106.1	1107.5	1108.9	1109.0	1107.8	1106.6
177.5°	1110.9	1109.8	1108.7	1107.7	1108.7	1109.8	1110.9	1112.0	1112.1	1111.1	1110.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	11.9	11.8	10.9	10.8	9.9	9.7	9.0	8.9	8.9	8.5	8.9
90°	21.7	20.9	18.4	15.9	13.3	10.8	8.6	6.7	4.7	2.8	0.9
92.5°	34.1	33.5	32.0	30.7	29.2	27.7	26.3	25.1	23.8	22.4	21.1
95°	65.3	64.6	63.0	61.5	59.9	58.4	56.9	55.5	54.2	52.8	51.5
97.5°	101.9	101.0	99.9	98.8	97.6	96.5	95.5	94.5	93.4	92.4	91.4
100°	128.8	128.2	127.3	126.3	125.4	124.3	123.3	122.1	121.0	119.8	118.6
102.5°	159.5	158.9	157.6	156.4	155.1	153.8	152.8	152.1	151.4	150.8	150.1
105°	205.9	205.9	204.1	202.3	200.6	198.9	197.9	197.4	197.1	196.7	196.3
107.5°	254.8	254.2	253.5	252.8	252.1	251.4	250.9	250.7	250.5	250.2	250.0
110°	287.7	287.0	286.6	286.2	285.9	285.4	285.1	284.6	284.3	283.9	283.5



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	320.7	319.8	319.7	319.6	319.5	319.4	319.3	319.1	318.8	318.7	318.4
115°	371.8	371.6	372.0	372.4	372.7	373.2	373.1	372.5	371.9	371.3	370.7
117.5°	422.8	422.9	423.4	423.9	424.4	424.9	425.0	424.6	424.2	423.8	423.4
120°	456.8	457.1	458.1	459.0	459.9	461.0	460.9	459.7	458.6	457.4	456.2
122.5°	491.5	492.0	492.5	493.0	493.5	494.0	493.8	492.9	492.1	491.3	490.4
125°	542.7	543.5	543.8	544.2	544.6	545.0	544.9	544.3	543.7	543.1	542.6
127.5°	593.3	594.3	594.8	595.2	595.6	596.1	595.6	594.4	593.2	591.9	590.7
130°	626.4	627.2	627.8	628.4	629.0	629.5	629.0	627.5	625.9	624.4	622.8
132.5°	659.0	660.0	660.4	660.8	661.2	661.7	661.2	659.6	658.0	656.4	654.9
135°	707.5	708.3	708.5	708.7	708.9	709.0	708.6	707.4	706.3	705.1	704.0
137.5°	755.1	756.0	755.4	754.9	754.4	753.9	753.2	752.2	751.2	750.3	749.3
140°	785.7	785.9	785.7	785.6	785.3	785.1	784.5	783.6	782.6	781.7	780.7
142.5°	815.0	815.3	814.9	814.5	814.2	813.8	813.2	812.2	811.2	810.3	809.3
145°	858.2	858.3	857.7	857.2	856.6	856.0	855.5	855.1	854.7	854.4	853.9
147.5°	898.6	898.6	898.1	897.6	897.0	896.5	895.9	895.2	894.4	893.7	893.0
150°	923.8	923.8	923.3	923.0	922.6	922.2	921.8	921.4	921.0	920.7	920.2
152.5°	946.4	946.1	945.9	945.6	945.4	945.1	944.8	944.3	943.7	943.1	942.6
155°	979.5	978.7	978.5	978.4	978.1	977.9	977.8	977.8	977.8	977.8	977.8
157.5°	1008.3	1007.5	1007.4	1007.2	1007.0	1006.9	1006.9	1007.1	1007.4	1007.6	1007.9
160°	1025.9	1024.9	1024.9	1024.9	1024.9	1024.9	1025.1	1025.5	1025.9	1026.3	1026.7
162.5°	1042.7	1041.7	1041.6	1041.4	1041.2	1041.0	1041.3	1041.8	1042.3	1042.9	1043.4
165°	1063.6	1062.5	1062.5	1062.5	1062.5	1062.5	1062.7	1063.3	1063.9	1064.5	1065.1
167.5°	1080.7	1079.5	1079.4	1079.3	1079.1	1078.9	1079.3	1080.0	1080.8	1081.6	1082.4
170°	1089.9	1088.6	1088.6	1088.6	1088.6	1088.6	1089.0	1089.8	1090.5	1091.3	1092.1
172.5°	1097.5	1096.3	1096.3	1096.3	1096.3	1096.3	1096.7	1097.4	1098.2	1099.0	1099.8
175°	1105.5	1104.3	1104.3	1104.3	1104.3	1104.3	1104.7	1105.5	1106.3	1107.1	1107.8
177.5°	1109.2	1108.4	1108.4	1108.4	1108.4	1108.4	1108.6	1109.2	1109.9	1110.5	1111.1
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	9.9	10.3	11.8	12.9	14.8	16.4	16.5	16.3	16.4	16.3	16.0
90°	2.8	4.7	6.7	8.6	10.8	13.3	15.9	18.4	20.9	21.7	22.5
92.5°	22.4	23.8	25.1	26.3	27.7	29.2	30.7	32.0	33.5	34.1	34.7
95°	52.8	54.2	55.5	56.9	58.4	59.9	61.5	63.0	64.6	65.3	66.1
97.5°	92.4	93.4	94.5	95.5	96.5	97.6	98.8	99.9	101.0	101.9	102.8
100°	119.8	121.0	122.1	123.3	124.3	125.4	126.3	127.3	128.2	128.8	129.4
102.5°	150.8	151.4	152.1	152.8	153.8	155.1	156.4	157.6	158.9	159.5	160.1
105°	196.7	197.1	197.4	197.9	198.9	200.6	202.3	204.1	205.9	205.9	205.9
107.5°	250.2	250.5	250.7	250.9	251.4	252.1	252.8	253.5	254.2	254.8	255.5
110°	283.9	284.3	284.6	285.1	285.4	285.9	286.2	286.6	287.0	287.7	288.5





TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.7	318.8	319.1	319.3	319.4	319.5	319.6	319.7	319.8	320.7	321.7
115°	371.3	371.9	372.5	373.1	373.2	372.7	372.4	372.0	371.6	371.8	372.0
117.5°	423.8	424.2	424.6	425.0	424.9	424.4	423.9	423.4	422.9	422.8	422.8
120°	457.4	458.6	459.7	460.9	461.0	459.9	459.0	458.1	457.1	456.8	456.7
122.5°	491.3	492.1	492.9	493.8	494.0	493.5	493.0	492.5	492.0	491.5	490.9
125°	543.1	543.7	544.3	544.9	545.0	544.6	544.2	543.8	543.5	542.7	541.9
127.5°	591.9	593.2	594.4	595.6	596.1	595.6	595.2	594.8	594.3	593.3	592.2
130°	624.4	625.9	627.5	629.0	629.5	629.0	628.4	627.8	627.2	626.4	625.6
132.5°	656.4	658.0	659.6	661.2	661.7	661.2	660.8	660.4	660.0	659.0	658.1
135°	705.1	706.3	707.4	708.6	709.0	708.9	708.7	708.5	708.3	707.5	706.7
137.5°	750.3	751.2	752.2	753.2	753.9	754.4	754.9	755.4	756.0	755.1	754.3
140°	781.7	782.6	783.6	784.5	785.1	785.3	785.6	785.7	785.9	785.7	785.6
142.5°	810.3	811.2	812.2	813.2	813.8	814.2	814.5	814.9	815.3	815.0	814.9
145°	854.4	854.7	855.1	855.5	856.0	856.6	857.2	857.7	858.3	858.2	858.0
147.5°	893.7	894.4	895.2	895.9	896.5	897.0	897.6	898.1	898.6	898.6	898.6
150°	920.7	921.0	921.4	921.8	922.2	922.6	923.0	923.3	923.8	923.8	923.8
152.5°	943.1	943.7	944.3	944.8	945.1	945.4	945.6	945.9	946.1	946.4	946.7
155°	977.8	977.8	977.8	977.8	977.9	978.1	978.4	978.5	978.7	979.5	980.2
157.5°	1007.6	1007.4	1007.1	1006.9	1006.9	1007.0	1007.2	1007.4	1007.5	1008.3	1009.1
160°	1026.3	1025.9	1025.5	1025.1	1024.9	1024.9	1024.9	1024.9	1024.9	1025.9	1026.9
162.5°	1042.9	1042.3	1041.8	1041.3	1041.0	1041.2	1041.4	1041.6	1041.7	1042.7	1043.6
165°	1064.5	1063.9	1063.3	1062.7	1062.5	1062.5	1062.5	1062.5	1062.5	1063.6	1064.8
167.5°	1081.6	1080.8	1080.0	1079.3	1078.9	1079.1	1079.3	1079.4	1079.5	1080.7	1081.9
170°	1091.3	1090.5	1089.8	1089.0	1088.6	1088.6	1088.6	1088.6	1088.6	1089.9	1091.3
172.5°	1099.0	1098.2	1097.4	1096.7	1096.3	1096.3	1096.3	1096.3	1096.3	1097.5	1098.7
175°	1107.1	1106.3	1105.5	1104.7	1104.3	1104.3	1104.3	1104.3	1104.3	1105.5	1106.6
177.5°	1110.5	1109.9	1109.2	1108.6	1108.4	1108.4	1108.4	1108.4	1108.4	1109.2	1110.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	15.8	15.6	15.4	15.8	15.5	15.2	16.0
90°	23.2	24.0	24.6	25.0	25.4	25.7	26.2
92.5°	35.4	36.0	36.2	35.9	35.7	35.5	35.2
95°	66.9	67.7	68.0	68.0	68.0	68.0	68.0
97.5°	103.7	104.6	105.0	104.9	104.9	104.8	104.7
100°	130.0	130.5	131.0	131.4	131.8	132.2	132.6
102.5°	160.7	161.3	161.5	161.4	161.4	161.3	161.2
105°	205.9	205.9	206.0	206.5	206.8	207.2	207.6
107.5°	256.1	256.7	256.8	256.7	256.4	256.1	255.9
110°	289.3	290.1	290.2	289.9	289.5	289.1	288.7



TEST NUMBER: P332163-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	322.5	323.5	323.9	323.8	323.7	323.7	323.6
115°	372.2	372.4	372.4	372.2	372.0	371.8	371.6
117.5°	422.8	422.8	422.4	421.9	421.4	420.8	420.3
120°	456.5	456.3	456.0	455.6	455.2	454.9	454.4
122.5°	490.4	490.0	489.4	488.9	488.4	487.8	487.2
125°	541.1	540.4	539.6	538.8	538.0	537.3	536.5
127.5°	591.2	590.0	589.0	588.1	587.3	586.3	585.5
130°	624.8	624.1	623.0	621.6	620.3	619.0	617.6
132.5°	657.2	656.3	655.3	654.2	653.2	652.1	651.1
135°	705.9	705.2	704.6	704.2	703.9	703.4	703.1
137.5°	753.5	752.7	751.9	751.1	750.4	749.7	749.0
140°	785.3	785.1	784.4	783.0	781.7	780.3	778.9
142.5°	814.7	814.5	813.8	812.8	811.8	810.7	809.7
145°	857.7	857.6	857.0	856.3	855.5	854.7	853.9
147.5°	898.6	898.6	898.0	896.9	895.7	894.6	893.4
150°	923.8	923.8	923.2	922.0	920.8	919.7	918.5
152.5°	947.0	947.4	947.0	946.0	944.9	943.9	943.0
155°	981.0	981.8	981.5	980.2	978.8	977.5	976.1
157.5°	1010.0	1010.7	1010.6	1009.5	1008.5	1007.4	1006.3
160°	1027.9	1028.8	1028.9	1028.1	1027.3	1026.6	1025.8
162.5°	1044.6	1045.6	1045.4	1044.2	1042.9	1041.7	1040.4
165°	1065.9	1067.1	1067.0	1065.7	1064.3	1062.9	1061.6
167.5°	1083.1	1084.3	1084.3	1083.1	1081.9	1080.7	1079.5
170°	1092.7	1094.1	1094.1	1092.7	1091.3	1089.9	1088.6
172.5°	1099.9	1101.1	1101.0	1099.7	1098.3	1096.9	1095.6
175°	1107.8	1109.0	1108.9	1107.5	1106.1	1104.8	1103.5
177.5°	1111.1	1112.1	1112.0	1110.9	1109.8	1108.7	1107.7
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4

(END OF REPORT)