

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332169-935

Luminaire Tested: **S123DIW-S775D1320U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332169-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1320U935-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6750.8 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.6	1.4
10°-20°	293.9	4.4
20°-30°	493.2	7.3
30°-40°	558.5	8.3
40°-50°	500.8	7.4
50°-60°	404.1	6.0
60°-70°	281.6	4.2
70°-80°	148.0	2.2
80°-90°	40.4	0.6
90°-100°	92.6	1.4
100°-110°	277.2	4.1
110°-120°	471.4	7.0
120°-130°	620.1	9.2
130°-140°	697.0	10.3
140°-150°	685.1	10.1
150°-160°	576.8	8.5
160°-170°	383.9	5.7
170°-180°	134.4	2.0
0°-30°	878.7	13.0
0°-40°	1437.2	21.3
0°-60°	2342.1	34.7
0°-90°	2812.2	41.7
90°-120°	841.3	12.5
90°-150°	2843.5	42.1
90°-180°	3939.0	58.3
0°-180°	6750.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	34	1	34	1	34	18
95°	87	66	87	66	87	89
105°	266	251	266	251	266	282
115°	476	475	476	475	476	471
125°	687	695	687	695	687	614
135°	900	901	900	901	900	692
145°	1093	1093	1093	1093	1093	682
155°	1250	1252	1250	1252	1250	575
165°	1359	1364	1359	1364	1359	383
175°	1413	1418	1413	1418	1413	134
180°	1422	1422	1422	1422	1422	



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	17.5	16.7	17.0	17.2	16.8	17.0	17.1	17.3	17.5	17.7	17.3
90°	33.5	33.0	32.5	32.0	31.5	30.7	29.8	28.8	27.8	26.8	23.6
92.5°	45.1	45.4	45.7	46.0	46.3	46.1	45.3	44.4	43.7	42.9	41.1
95°	87.1	87.1	87.1	87.1	87.1	86.6	85.6	84.6	83.6	82.7	80.7
97.5°	134.0	134.1	134.2	134.3	134.4	133.9	132.8	131.6	130.4	129.3	127.9
100°	169.7	169.3	168.8	168.2	167.7	167.1	166.3	165.7	164.9	164.2	162.9
102.5°	206.4	206.5	206.6	206.6	206.7	206.5	205.7	204.9	204.2	203.5	201.8
105°	265.8	265.3	264.8	264.3	263.8	263.6	263.6	263.6	263.6	263.6	261.3
107.5°	327.6	328.0	328.2	328.6	328.8	328.6	327.8	327.0	326.2	325.4	324.5
110°	369.6	370.1	370.7	371.1	371.6	371.3	370.4	369.4	368.4	367.4	366.9



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	414.3	414.4	414.5	414.6	414.7	414.1	412.9	411.7	410.6	409.4	409.3
115°	475.7	476.0	476.2	476.5	476.7	476.7	476.5	476.2	476.0	475.7	476.2
117.5°	538.0	538.7	539.4	540.1	540.8	541.1	541.2	541.3	541.3	541.4	542.0
120°	581.8	582.3	582.8	583.3	583.8	584.2	584.4	584.6	584.9	585.1	586.4
122.5°	623.8	624.5	625.2	625.9	626.5	627.2	627.8	628.5	629.1	629.8	630.4
125°	686.7	687.8	688.7	689.7	690.8	691.7	692.8	693.7	694.7	695.7	696.2
127.5°	749.5	750.7	751.8	752.9	754.1	755.4	756.7	758.1	759.5	761.0	761.5
130°	790.7	792.4	794.1	795.8	797.5	798.9	800.0	800.9	801.9	802.9	803.7
132.5°	833.5	834.8	836.2	837.5	838.9	840.2	841.3	842.5	843.7	844.9	845.4
135°	900.1	900.5	901.0	901.6	902.1	902.8	903.8	904.7	905.8	906.7	907.0
137.5°	958.8	959.8	960.7	961.7	962.6	963.5	964.6	965.6	966.6	967.8	967.1
140°	997.2	998.9	1000.7	1002.5	1004.2	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9
142.5°	1036.6	1037.8	1039.2	1040.5	1041.9	1042.7	1042.9	1043.2	1043.4	1043.7	1043.2
145°	1093.2	1094.2	1095.2	1096.2	1097.3	1097.9	1098.1	1098.3	1098.5	1098.8	1098.1
147.5°	1143.8	1145.2	1146.7	1148.2	1149.7	1150.4	1150.4	1150.4	1150.4	1150.4	1149.7
150°	1175.9	1177.3	1178.9	1180.3	1181.8	1182.6	1182.6	1182.6	1182.6	1182.6	1182.1
152.5°	1207.1	1208.4	1209.7	1211.0	1212.3	1212.7	1212.4	1211.9	1211.6	1211.2	1210.9
155°	1249.6	1251.3	1253.1	1254.8	1256.5	1256.9	1255.9	1254.9	1254.0	1252.9	1252.7
157.5°	1288.2	1289.6	1291.0	1292.4	1293.7	1294.0	1292.9	1291.8	1290.8	1289.8	1289.6
160°	1313.2	1314.2	1315.3	1316.2	1317.2	1317.1	1315.9	1314.6	1313.4	1312.1	1312.1
162.5°	1332.0	1333.6	1335.2	1336.8	1338.3	1338.5	1337.3	1336.0	1334.8	1333.5	1333.3
165°	1359.0	1360.7	1362.5	1364.3	1366.0	1366.1	1364.6	1363.1	1361.6	1360.1	1360.1
167.5°	1382.0	1383.5	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0	1381.8
170°	1393.6	1395.3	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6	1393.6
172.5°	1402.6	1404.3	1406.0	1407.8	1409.5	1409.6	1408.1	1406.5	1405.0	1403.4	1403.4
175°	1412.6	1414.4	1416.1	1417.8	1419.5	1419.7	1418.2	1416.7	1415.2	1413.8	1413.8
177.5°	1418.0	1419.4	1420.7	1422.1	1423.6	1423.7	1422.5	1421.3	1420.0	1418.8	1418.8
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	17.4	17.1	15.4	13.3	12.1	10.6	10.1	8.9	8.6	9.1	9.3
90°	20.3	17.1	13.9	11.0	8.5	6.1	3.6	1.1	3.6	6.1	8.5
92.5°	39.2	37.4	35.6	33.8	32.1	30.4	28.7	27.0	28.7	30.4	32.1
95°	78.7	76.7	74.7	72.8	71.1	69.4	67.6	65.9	67.6	69.4	71.1
97.5°	126.4	125.0	123.6	122.2	120.9	119.6	118.3	117.0	118.3	119.6	120.9
100°	161.7	160.4	159.2	157.8	156.4	154.8	153.3	151.9	153.3	154.8	156.4
102.5°	200.2	198.5	196.9	195.6	194.8	193.9	193.0	192.1	193.0	193.9	194.8
105°	259.1	256.8	254.6	253.2	252.7	252.3	251.8	251.2	251.8	252.3	252.7
107.5°	323.6	322.7	321.8	321.2	321.0	320.6	320.4	320.0	320.4	320.6	321.0
110°	366.4	365.9	365.4	364.9	364.4	363.9	363.4	362.9	363.4	363.9	364.4





TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	409.1	409.1	409.0	408.8	408.5	408.2	407.9	407.6	407.9	408.2	408.5
115°	476.7	477.2	477.7	477.6	476.8	476.0	475.4	474.6	475.4	476.0	476.8
117.5°	542.7	543.3	544.0	544.1	543.5	543.0	542.5	542.1	542.5	543.0	543.5
120°	587.6	588.8	590.1	590.0	588.5	587.0	585.5	584.0	585.5	587.0	588.5
122.5°	631.1	631.7	632.4	632.1	631.1	630.0	628.9	627.8	628.9	630.0	631.1
125°	696.7	697.2	697.7	697.6	696.8	696.0	695.3	694.6	695.3	696.0	696.8
127.5°	762.0	762.6	763.1	762.6	761.0	759.4	757.9	756.2	757.9	759.4	761.0
130°	804.4	805.1	805.9	805.3	803.3	801.3	799.3	797.3	799.3	801.3	803.3
132.5°	846.0	846.5	847.1	846.4	844.4	842.4	840.4	838.4	840.4	842.4	844.4
135°	907.2	907.5	907.8	907.1	905.6	904.1	902.7	901.2	902.7	904.1	905.6
137.5°	966.5	965.8	965.2	964.2	962.9	961.7	960.4	959.2	960.4	961.7	962.9
140°	1005.6	1005.4	1005.1	1004.4	1003.2	1001.9	1000.7	999.4	1000.7	1001.9	1003.2
142.5°	1042.8	1042.3	1041.9	1041.0	1039.8	1038.5	1037.3	1036.0	1037.3	1038.5	1039.8
145°	1097.3	1096.6	1095.9	1095.2	1094.8	1094.2	1093.7	1093.2	1093.7	1094.2	1094.8
147.5°	1149.0	1148.3	1147.6	1146.9	1146.0	1145.0	1144.2	1143.2	1144.2	1145.0	1146.0
150°	1181.6	1181.1	1180.6	1180.1	1179.6	1179.1	1178.6	1178.1	1178.6	1179.1	1179.6
152.5°	1210.6	1210.3	1210.0	1209.4	1208.8	1208.1	1207.4	1206.7	1207.4	1208.1	1208.8
155°	1252.4	1252.2	1252.0	1251.8	1251.8	1251.8	1251.8	1251.8	1251.8	1251.8	1251.8
157.5°	1289.3	1289.2	1289.0	1289.0	1289.3	1289.6	1290.0	1290.2	1290.0	1289.6	1289.3
160°	1312.1	1312.1	1312.1	1312.3	1312.9	1313.4	1313.9	1314.3	1313.9	1313.4	1312.9
162.5°	1333.2	1333.0	1332.7	1333.0	1333.7	1334.4	1335.1	1335.8	1335.1	1334.4	1333.7
165°	1360.1	1360.1	1360.1	1360.6	1361.2	1362.0	1362.7	1363.5	1362.7	1362.0	1361.2
167.5°	1381.6	1381.4	1381.2	1381.6	1382.6	1383.6	1384.6	1385.6	1384.6	1383.6	1382.6
170°	1393.6	1393.6	1393.6	1394.1	1395.2	1396.1	1397.1	1398.1	1397.1	1396.1	1395.2
172.5°	1403.4	1403.4	1403.4	1403.9	1405.0	1405.9	1407.0	1407.9	1407.0	1405.9	1405.0
175°	1413.8	1413.8	1413.8	1414.2	1415.2	1416.3	1417.2	1418.2	1417.2	1416.3	1415.2
177.5°	1418.8	1418.8	1418.8	1419.3	1420.0	1420.8	1421.7	1422.5	1421.7	1420.8	1420.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	9.4	10.3	10.7	11.6	12.0	12.9	13.2	12.6	12.8	14.1	12.8
90°	11.0	13.9	17.1	20.3	23.6	26.8	27.8	28.8	29.8	30.7	31.5
92.5°	33.8	35.6	37.4	39.2	41.1	42.9	43.7	44.4	45.3	46.1	46.3
95°	72.8	74.7	76.7	78.7	80.7	82.7	83.6	84.6	85.6	86.6	87.1
97.5°	122.2	123.6	125.0	126.4	127.9	129.3	130.4	131.6	132.8	133.9	134.4
100°	157.8	159.2	160.4	161.7	162.9	164.2	164.9	165.7	166.3	167.1	167.7
102.5°	195.6	196.9	198.5	200.2	201.8	203.5	204.2	204.9	205.7	206.5	206.7
105°	253.2	254.6	256.8	259.1	261.3	263.6	263.6	263.6	263.6	263.6	263.8
107.5°	321.2	321.8	322.7	323.6	324.5	325.4	326.2	327.0	327.8	328.6	328.8
110°	364.9	365.4	365.9	366.4	366.9	367.4	368.4	369.4	370.4	371.3	371.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	408.8	409.0	409.1	409.1	409.3	409.4	410.6	411.7	412.9	414.1	414.7
115°	477.6	477.7	477.2	476.7	476.2	475.7	476.0	476.2	476.5	476.7	476.7
117.5°	544.1	544.0	543.3	542.7	542.0	541.4	541.3	541.3	541.2	541.1	540.8
120°	590.0	590.1	588.8	587.6	586.4	585.1	584.9	584.6	584.4	584.2	583.8
122.5°	632.1	632.4	631.7	631.1	630.4	629.8	629.1	628.5	627.8	627.2	626.5
125°	697.6	697.7	697.2	696.7	696.2	695.7	694.7	693.7	692.8	691.7	690.8
127.5°	762.6	763.1	762.6	762.0	761.5	761.0	759.5	758.1	756.7	755.4	754.1
130°	805.3	805.9	805.1	804.4	803.7	802.9	801.9	800.9	800.0	798.9	797.5
132.5°	846.4	847.1	846.5	846.0	845.4	844.9	843.7	842.5	841.3	840.2	838.9
135°	907.1	907.8	907.5	907.2	907.0	906.7	905.8	904.7	903.8	902.8	902.1
137.5°	964.2	965.2	965.8	966.5	967.1	967.8	966.6	965.6	964.6	963.5	962.6
140°	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9	1005.6	1005.4	1005.1	1004.2
142.5°	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4	1043.2	1042.9	1042.7	1041.9
145°	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5	1098.3	1098.1	1097.9	1097.3
147.5°	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4	1150.4	1150.4	1150.4	1149.7
150°	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6	1182.6	1182.6	1182.6	1181.8
152.5°	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6	1211.9	1212.4	1212.7	1212.3
155°	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0	1254.9	1255.9	1256.9	1256.5
157.5°	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8	1291.8	1292.9	1294.0	1293.7
160°	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4	1314.6	1315.9	1317.1	1317.2
162.5°	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8	1336.0	1337.3	1338.5	1338.3
165°	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6	1363.1	1364.6	1366.1	1366.0
167.5°	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5	1385.1	1386.6	1388.2	1388.2
170°	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3	1397.1	1398.9	1400.6	1400.6
172.5°	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0	1406.5	1408.1	1409.6	1409.5
175°	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2	1416.7	1418.2	1419.7	1419.5
177.5°	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0	1421.3	1422.5	1423.7	1423.6
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	12.9	13.0	12.7	12.5	12.7	13.0	12.9	12.8	14.1	12.8	12.6
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.7	29.8	28.8
92.5°	46.0	45.7	45.4	45.1	45.4	45.7	46.0	46.3	46.1	45.3	44.4
95°	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	86.6	85.6	84.6
97.5°	134.3	134.2	134.1	134.0	134.1	134.2	134.3	134.4	133.9	132.8	131.6
100°	168.2	168.8	169.3	169.7	169.3	168.8	168.2	167.7	167.1	166.3	165.7
102.5°	206.6	206.6	206.5	206.4	206.5	206.6	206.6	206.7	206.5	205.7	204.9
105°	264.3	264.8	265.3	265.8	265.3	264.8	264.3	263.8	263.6	263.6	263.6
107.5°	328.6	328.2	328.0	327.6	328.0	328.2	328.6	328.8	328.6	327.8	327.0
110°	371.1	370.7	370.1	369.6	370.1	370.7	371.1	371.6	371.3	370.4	369.4



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	414.6	414.5	414.4	414.3	414.4	414.5	414.6	414.7	414.1	412.9	411.7
115°	476.5	476.2	476.0	475.7	476.0	476.2	476.5	476.7	476.7	476.5	476.2
117.5°	540.1	539.4	538.7	538.0	538.7	539.4	540.1	540.8	541.1	541.2	541.3
120°	583.3	582.8	582.3	581.8	582.3	582.8	583.3	583.8	584.2	584.4	584.6
122.5°	625.9	625.2	624.5	623.8	624.5	625.2	625.9	626.5	627.2	627.8	628.5
125°	689.7	688.7	687.8	686.7	687.8	688.7	689.7	690.8	691.7	692.8	693.7
127.5°	752.9	751.8	750.7	749.5	750.7	751.8	752.9	754.1	755.4	756.7	758.1
130°	795.8	794.1	792.4	790.7	792.4	794.1	795.8	797.5	798.9	800.0	800.9
132.5°	837.5	836.2	834.8	833.5	834.8	836.2	837.5	838.9	840.2	841.3	842.5
135°	901.6	901.0	900.5	900.1	900.5	901.0	901.6	902.1	902.8	903.8	904.7
137.5°	961.7	960.7	959.8	958.8	959.8	960.7	961.7	962.6	963.5	964.6	965.6
140°	1002.5	1000.7	998.9	997.2	998.9	1000.7	1002.5	1004.2	1005.1	1005.4	1005.6
142.5°	1040.5	1039.2	1037.8	1036.6	1037.8	1039.2	1040.5	1041.9	1042.7	1042.9	1043.2
145°	1096.2	1095.2	1094.2	1093.2	1094.2	1095.2	1096.2	1097.3	1097.9	1098.1	1098.3
147.5°	1148.2	1146.7	1145.2	1143.8	1145.2	1146.7	1148.2	1149.7	1150.4	1150.4	1150.4
150°	1180.3	1178.9	1177.3	1175.9	1177.3	1178.9	1180.3	1181.8	1182.6	1182.6	1182.6
152.5°	1211.0	1209.7	1208.4	1207.1	1208.4	1209.7	1211.0	1212.3	1212.7	1212.4	1211.9
155°	1254.8	1253.1	1251.3	1249.6	1251.3	1253.1	1254.8	1256.5	1256.9	1255.9	1254.9
157.5°	1292.4	1291.0	1289.6	1288.2	1289.6	1291.0	1292.4	1293.7	1294.0	1292.9	1291.8
160°	1316.2	1315.3	1314.2	1313.2	1314.2	1315.3	1316.2	1317.2	1317.1	1315.9	1314.6
162.5°	1336.8	1335.2	1333.6	1332.0	1333.6	1335.2	1336.8	1338.3	1338.5	1337.3	1336.0
165°	1364.3	1362.5	1360.7	1359.0	1360.7	1362.5	1364.3	1366.0	1366.1	1364.6	1363.1
167.5°	1386.6	1385.1	1383.5	1382.0	1383.5	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1
170°	1398.9	1397.1	1395.3	1393.6	1395.3	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1
172.5°	1407.8	1406.0	1404.3	1402.6	1404.3	1406.0	1407.8	1409.5	1409.6	1408.1	1406.5
175°	1417.8	1416.1	1414.4	1412.6	1414.4	1416.1	1417.8	1419.5	1419.7	1418.2	1416.7
177.5°	1422.1	1420.7	1419.4	1418.0	1419.4	1420.7	1422.1	1423.6	1423.7	1422.5	1421.3
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	13.2	12.9	12.0	11.6	10.7	10.3	9.4	9.3	9.1	8.6	8.9
90°	27.8	26.8	23.6	20.3	17.1	13.9	11.0	8.5	6.1	3.6	1.1
92.5°	43.7	42.9	41.1	39.2	37.4	35.6	33.8	32.1	30.4	28.7	27.0
95°	83.6	82.7	80.7	78.7	76.7	74.7	72.8	71.1	69.4	67.6	65.9
97.5°	130.4	129.3	127.9	126.4	125.0	123.6	122.2	120.9	119.6	118.3	117.0
100°	164.9	164.2	162.9	161.7	160.4	159.2	157.8	156.4	154.8	153.3	151.9
102.5°	204.2	203.5	201.8	200.2	198.5	196.9	195.6	194.8	193.9	193.0	192.1
105°	263.6	263.6	261.3	259.1	256.8	254.6	253.2	252.7	252.3	251.8	251.2
107.5°	326.2	325.4	324.5	323.6	322.7	321.8	321.2	321.0	320.6	320.4	320.0
110°	368.4	367.4	366.9	366.4	365.9	365.4	364.9	364.4	363.9	363.4	362.9



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	410.6	409.4	409.3	409.1	409.1	409.0	408.8	408.5	408.2	407.9	407.6
115°	476.0	475.7	476.2	476.7	477.2	477.7	477.6	476.8	476.0	475.4	474.6
117.5°	541.3	541.4	542.0	542.7	543.3	544.0	544.1	543.5	543.0	542.5	542.1
120°	584.9	585.1	586.4	587.6	588.8	590.1	590.0	588.5	587.0	585.5	584.0
122.5°	629.1	629.8	630.4	631.1	631.7	632.4	632.1	631.1	630.0	628.9	627.8
125°	694.7	695.7	696.2	696.7	697.2	697.7	697.6	696.8	696.0	695.3	694.6
127.5°	759.5	761.0	761.5	762.0	762.6	763.1	762.6	761.0	759.4	757.9	756.2
130°	801.9	802.9	803.7	804.4	805.1	805.9	805.3	803.3	801.3	799.3	797.3
132.5°	843.7	844.9	845.4	846.0	846.5	847.1	846.4	844.4	842.4	840.4	838.4
135°	905.8	906.7	907.0	907.2	907.5	907.8	907.1	905.6	904.1	902.7	901.2
137.5°	966.6	967.8	967.1	966.5	965.8	965.2	964.2	962.9	961.7	960.4	959.2
140°	1005.9	1006.2	1005.9	1005.6	1005.4	1005.1	1004.4	1003.2	1001.9	1000.7	999.4
142.5°	1043.4	1043.7	1043.2	1042.8	1042.3	1041.9	1041.0	1039.8	1038.5	1037.3	1036.0
145°	1098.5	1098.8	1098.1	1097.3	1096.6	1095.9	1095.2	1094.8	1094.2	1093.7	1093.2
147.5°	1150.4	1150.4	1149.7	1149.0	1148.3	1147.6	1146.9	1146.0	1145.0	1144.2	1143.2
150°	1182.6	1182.6	1182.1	1181.6	1181.1	1180.6	1180.1	1179.6	1179.1	1178.6	1178.1
152.5°	1211.6	1211.2	1210.9	1210.6	1210.3	1210.0	1209.4	1208.8	1208.1	1207.4	1206.7
155°	1254.0	1252.9	1252.7	1252.4	1252.2	1252.0	1251.8	1251.8	1251.8	1251.8	1251.8
157.5°	1290.8	1289.8	1289.6	1289.3	1289.2	1289.0	1289.0	1289.3	1289.6	1290.0	1290.2
160°	1313.4	1312.1	1312.1	1312.1	1312.1	1312.1	1312.3	1312.9	1313.4	1313.9	1314.3
162.5°	1334.8	1333.5	1333.3	1333.2	1333.0	1332.7	1333.0	1333.7	1334.4	1335.1	1335.8
165°	1361.6	1360.1	1360.1	1360.1	1360.1	1360.1	1360.6	1361.2	1362.0	1362.7	1363.5
167.5°	1383.5	1382.0	1381.8	1381.6	1381.4	1381.2	1381.6	1382.6	1383.6	1384.6	1385.6
170°	1395.3	1393.6	1393.6	1393.6	1393.6	1393.6	1394.1	1395.2	1396.1	1397.1	1398.1
172.5°	1405.0	1403.4	1403.4	1403.4	1403.4	1403.4	1403.9	1405.0	1405.9	1407.0	1407.9
175°	1415.2	1413.8	1413.8	1413.8	1413.8	1413.8	1414.2	1415.2	1416.3	1417.2	1418.2
177.5°	1420.0	1418.8	1418.8	1418.8	1418.8	1418.8	1419.3	1420.0	1420.8	1421.7	1422.5
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	10.1	10.6	12.1	13.3	15.4	17.1	17.4	17.3	17.7	17.5	17.3
90°	3.6	6.1	8.5	11.0	13.9	17.1	20.3	23.6	26.8	27.8	28.8
92.5°	28.7	30.4	32.1	33.8	35.6	37.4	39.2	41.1	42.9	43.7	44.4
95°	67.6	69.4	71.1	72.8	74.7	76.7	78.7	80.7	82.7	83.6	84.6
97.5°	118.3	119.6	120.9	122.2	123.6	125.0	126.4	127.9	129.3	130.4	131.6
100°	153.3	154.8	156.4	157.8	159.2	160.4	161.7	162.9	164.2	164.9	165.7
102.5°	193.0	193.9	194.8	195.6	196.9	198.5	200.2	201.8	203.5	204.2	204.9
105°	251.8	252.3	252.7	253.2	254.6	256.8	259.1	261.3	263.6	263.6	263.6
107.5°	320.4	320.6	321.0	321.2	321.8	322.7	323.6	324.5	325.4	326.2	327.0
110°	363.4	363.9	364.4	364.9	365.4	365.9	366.4	366.9	367.4	368.4	369.4





TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	407.9	408.2	408.5	408.8	409.0	409.1	409.1	409.3	409.4	410.6	411.7
115°	475.4	476.0	476.8	477.6	477.7	477.2	476.7	476.2	475.7	476.0	476.2
117.5°	542.5	543.0	543.5	544.1	544.0	543.3	542.7	542.0	541.4	541.3	541.3
120°	585.5	587.0	588.5	590.0	590.1	588.8	587.6	586.4	585.1	584.9	584.6
122.5°	628.9	630.0	631.1	632.1	632.4	631.7	631.1	630.4	629.8	629.1	628.5
125°	695.3	696.0	696.8	697.6	697.7	697.2	696.7	696.2	695.7	694.7	693.7
127.5°	757.9	759.4	761.0	762.6	763.1	762.6	762.0	761.5	761.0	759.5	758.1
130°	799.3	801.3	803.3	805.3	805.9	805.1	804.4	803.7	802.9	801.9	800.9
132.5°	840.4	842.4	844.4	846.4	847.1	846.5	846.0	845.4	844.9	843.7	842.5
135°	902.7	904.1	905.6	907.1	907.8	907.5	907.2	907.0	906.7	905.8	904.7
137.5°	960.4	961.7	962.9	964.2	965.2	965.8	966.5	967.1	967.8	966.6	965.6
140°	1000.7	1001.9	1003.2	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9	1005.6
142.5°	1037.3	1038.5	1039.8	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4	1043.2
145°	1093.7	1094.2	1094.8	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5	1098.3
147.5°	1144.2	1145.0	1146.0	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4	1150.4
150°	1178.6	1179.1	1179.6	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6	1182.6
152.5°	1207.4	1208.1	1208.8	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6	1211.9
155°	1251.8	1251.8	1251.8	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0	1254.9
157.5°	1290.0	1289.6	1289.3	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8	1291.8
160°	1313.9	1313.4	1312.9	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4	1314.6
162.5°	1335.1	1334.4	1333.7	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8	1336.0
165°	1362.7	1362.0	1361.2	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6	1363.1
167.5°	1384.6	1383.6	1382.6	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5	1385.1
170°	1397.1	1396.1	1395.2	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3	1397.1
172.5°	1407.0	1405.9	1405.0	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0	1406.5
175°	1417.2	1416.3	1415.2	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2	1416.7
177.5°	1421.7	1420.8	1420.0	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0	1421.3
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	17.1	17.0	16.8	17.2	17.0	16.7	17.5
90°	29.8	30.7	31.5	32.0	32.5	33.0	33.5
92.5°	45.3	46.1	46.3	46.0	45.7	45.4	45.1
95°	85.6	86.6	87.1	87.1	87.1	87.1	87.1
97.5°	132.8	133.9	134.4	134.3	134.2	134.1	134.0
100°	166.3	167.1	167.7	168.2	168.8	169.3	169.7
102.5°	205.7	206.5	206.7	206.6	206.6	206.5	206.4
105°	263.6	263.6	263.8	264.3	264.8	265.3	265.8
107.5°	327.8	328.6	328.8	328.6	328.2	328.0	327.6
110°	370.4	371.3	371.6	371.1	370.7	370.1	369.6



TEST NUMBER: P332169-935

CATALOG NUMBER: S123DIW-S775D1320U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	412.9	414.1	414.7	414.6	414.5	414.4	414.3
115°	476.5	476.7	476.7	476.5	476.2	476.0	475.7
117.5°	541.2	541.1	540.8	540.1	539.4	538.7	538.0
120°	584.4	584.2	583.8	583.3	582.8	582.3	581.8
122.5°	627.8	627.2	626.5	625.9	625.2	624.5	623.8
125°	692.8	691.7	690.8	689.7	688.7	687.8	686.7
127.5°	756.7	755.4	754.1	752.9	751.8	750.7	749.5
130°	800.0	798.9	797.5	795.8	794.1	792.4	790.7
132.5°	841.3	840.2	838.9	837.5	836.2	834.8	833.5
135°	903.8	902.8	902.1	901.6	901.0	900.5	900.1
137.5°	964.6	963.5	962.6	961.7	960.7	959.8	958.8
140°	1005.4	1005.1	1004.2	1002.5	1000.7	998.9	997.2
142.5°	1042.9	1042.7	1041.9	1040.5	1039.2	1037.8	1036.6
145°	1098.1	1097.9	1097.3	1096.2	1095.2	1094.2	1093.2
147.5°	1150.4	1150.4	1149.7	1148.2	1146.7	1145.2	1143.8
150°	1182.6	1182.6	1181.8	1180.3	1178.9	1177.3	1175.9
152.5°	1212.4	1212.7	1212.3	1211.0	1209.7	1208.4	1207.1
155°	1255.9	1256.9	1256.5	1254.8	1253.1	1251.3	1249.6
157.5°	1292.9	1294.0	1293.7	1292.4	1291.0	1289.6	1288.2
160°	1315.9	1317.1	1317.2	1316.2	1315.3	1314.2	1313.2
162.5°	1337.3	1338.5	1338.3	1336.8	1335.2	1333.6	1332.0
165°	1364.6	1366.1	1366.0	1364.3	1362.5	1360.7	1359.0
167.5°	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0
170°	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6
172.5°	1408.1	1409.6	1409.5	1407.8	1406.0	1404.3	1402.6
175°	1418.2	1419.7	1419.5	1417.8	1416.1	1414.4	1412.6
177.5°	1422.5	1423.7	1423.6	1422.1	1420.7	1419.4	1418.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6

(END OF REPORT)