

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332473-935

Luminaire Tested: **S123RDIW-S1165D460U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332473-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D460U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5147.5 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	62	59	57	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49	46
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42	40
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33	31
7	63	50	42	37	60	48	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27	25
9	55	42	35	29	52	41	33	29	38	31	27	35	29	26	32	27	24	22
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	3.0
10°-20°	436.0	8.5
20°-30°	627.8	12.2
30°-40°	707.2	13.7
40°-50°	676.5	13.1
50°-60°	554.0	10.8
60°-70°	373.8	7.3
70°-80°	188.1	3.7
80°-90°	51.2	1.0
90°-100°	32.4	0.6
100°-110°	96.8	1.9
110°-120°	164.7	3.2
120°-130°	216.7	4.2
130°-140°	243.5	4.7
140°-150°	239.4	4.7
150°-160°	201.5	3.9
160°-170°	134.2	2.6
170°-180°	47.0	0.9
0°-30°	1220.5	23.7
0°-40°	1927.7	37.4
0°-60°	3158.3	61.4
0°-90°	3771.3	73.3
90°-120°	293.9	5.7
90°-150°	993.5	19.3
90°-180°	1376.0	26.7
0°-180°	5147.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	0	4	9	11	12	5
95°	23	26	29	30	30	26
105°	88	89	92	92	93	94
115°	166	167	166	167	166	164
125°	243	244	243	242	240	216
135°	315	317	317	315	314	243
145°	382	383	384	384	382	239
155°	437	437	438	439	437	201
165°	476	475	475	477	475	134
175°	496	494	494	496	494	47
180°	497	497	497	497	497	



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.1	23.6	21.1	18.7	16.2	15.1	15.2	15.5	15.8	15.9	15.8
90°	0.4	1.3	2.2	3.0	3.9	4.8	5.9	7.1	8.3	9.4	9.7
92.5°	9.5	10.1	10.6	11.2	11.8	12.4	13.1	13.7	14.4	15.0	15.2
95°	23.0	23.6	24.2	24.9	25.5	26.1	26.8	27.5	28.2	28.8	29.2
97.5°	40.9	41.3	41.8	42.3	42.7	43.1	43.7	44.2	44.7	45.2	45.5
100°	53.0	53.6	54.1	54.6	55.1	55.6	56.1	56.5	56.9	57.3	57.6
102.5°	67.1	67.4	67.8	68.0	68.4	68.8	69.4	69.9	70.5	71.1	71.4
105°	87.8	88.0	88.2	88.3	88.5	88.9	89.7	90.5	91.3	92.0	92.0
107.5°	111.8	111.9	112.0	112.1	112.3	112.4	112.8	113.0	113.4	113.7	114.0
110°	126.8	127.0	127.2	127.3	127.5	127.7	127.9	128.0	128.2	128.4	128.7



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.4	142.5	142.7	142.8	142.8	142.9	142.9	143.0	143.0	143.0	143.4
115°	165.8	166.1	166.3	166.6	166.9	166.9	166.8	166.6	166.4	166.3	166.3
117.5°	189.4	189.6	189.8	189.9	190.1	190.0	189.9	189.6	189.4	189.2	189.2
120°	204.1	204.6	205.1	205.6	206.1	206.2	205.8	205.3	204.9	204.5	204.4
122.5°	219.4	219.7	220.2	220.5	220.8	220.9	220.8	220.5	220.3	220.1	219.8
125°	242.7	243.0	243.2	243.5	243.7	243.7	243.6	243.4	243.2	243.1	242.7
127.5°	264.2	264.8	265.4	265.9	266.5	266.7	266.5	266.2	266.0	265.9	265.4
130°	278.6	279.3	280.0	280.7	281.4	281.5	281.3	281.0	280.8	280.5	280.2
132.5°	292.9	293.6	294.4	295.1	295.8	296.0	295.8	295.6	295.4	295.2	294.8
135°	314.9	315.4	315.9	316.4	316.9	317.2	317.1	317.0	316.9	316.8	316.5
137.5°	335.2	335.6	336.0	336.5	336.9	337.3	337.4	337.7	337.9	338.1	337.8
140°	349.2	349.7	350.1	350.5	350.9	351.2	351.3	351.4	351.5	351.5	351.5
142.5°	362.1	362.5	362.9	363.3	363.8	364.0	364.2	364.4	364.5	364.6	364.5
145°	382.0	382.2	382.4	382.5	382.7	382.9	383.1	383.4	383.7	383.9	383.8
147.5°	399.5	399.8	400.1	400.4	400.7	401.0	401.2	401.5	401.7	402.0	402.0
150°	411.6	411.8	412.0	412.2	412.3	412.5	412.7	412.8	413.0	413.2	413.2
152.5°	421.6	421.9	422.1	422.3	422.6	422.8	422.8	423.0	423.1	423.2	423.4
155°	437.4	437.4	437.4	437.4	437.4	437.5	437.6	437.6	437.7	437.8	438.2
157.5°	450.8	450.7	450.6	450.5	450.4	450.4	450.5	450.6	450.6	450.6	451.0
160°	459.3	459.1	458.9	458.7	458.6	458.5	458.5	458.5	458.5	458.5	458.9
162.5°	466.7	466.5	466.2	466.0	465.8	465.7	465.7	465.8	465.9	466.0	466.4
165°	476.4	476.1	475.9	475.6	475.4	475.3	475.3	475.3	475.3	475.3	475.8
167.5°	484.1	483.8	483.5	483.1	482.8	482.6	482.7	482.8	482.8	482.8	483.5
170°	488.5	488.2	487.8	487.5	487.2	487.0	487.0	487.0	487.0	487.0	487.6
172.5°	492.0	491.6	491.3	490.9	490.5	490.3	490.3	490.3	490.3	490.3	490.9
175°	495.5	495.2	494.8	494.5	494.1	494.0	494.0	494.0	494.0	494.0	494.5
177.5°	497.1	496.7	496.5	496.2	495.9	495.8	495.8	495.8	495.8	495.8	496.2
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	15.6	15.4	15.2	15.1	14.9	14.6	14.5	14.3
90°	10.1	10.4	10.8	11.0	11.2	11.4	11.5	11.7
92.5°	15.5	15.8	16.1	16.2	16.1	15.9	15.8	15.8
95°	29.5	29.9	30.2	30.4	30.4	30.4	30.4	30.4
97.5°	46.0	46.4	46.8	46.9	46.9	46.9	46.8	46.8
100°	57.9	58.1	58.4	58.6	58.8	59.0	59.2	59.3
102.5°	71.6	71.9	72.2	72.2	72.2	72.2	72.2	72.1
105°	92.0	92.0	92.0	92.1	92.4	92.6	92.7	92.9
107.5°	114.3	114.5	114.8	114.9	114.8	114.7	114.6	114.5
110°	129.1	129.4	129.8	129.8	129.7	129.5	129.3	129.2



TEST NUMBER: P332473-935

CATALOG NUMBER: S123RDIW-S1165D460U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	143.9	144.3	144.7	144.9	144.8	144.8	144.8	144.7
115°	166.4	166.5	166.6	166.6	166.5	166.4	166.3	166.3
117.5°	189.2	189.1	189.1	189.0	188.7	188.5	188.2	188.0
120°	204.3	204.2	204.1	204.0	203.8	203.6	203.5	203.3
122.5°	219.6	219.4	219.1	219.0	218.7	218.4	218.2	217.9
125°	242.4	242.0	241.7	241.3	241.0	240.6	240.3	240.0
127.5°	264.9	264.4	263.9	263.5	263.1	262.7	262.3	261.9
130°	279.8	279.5	279.1	278.7	278.1	277.5	276.9	276.2
132.5°	294.4	293.9	293.5	293.1	292.7	292.1	291.7	291.2
135°	316.2	315.8	315.5	315.2	315.0	314.9	314.7	314.5
137.5°	337.4	337.1	336.7	336.3	336.0	335.7	335.4	335.0
140°	351.4	351.3	351.2	350.9	350.3	349.7	349.0	348.4
142.5°	364.5	364.4	364.3	364.0	363.6	363.1	362.7	362.1
145°	383.7	383.7	383.6	383.4	383.1	382.7	382.4	382.0
147.5°	402.0	402.0	402.0	401.7	401.2	400.6	400.1	399.6
150°	413.2	413.2	413.2	412.9	412.4	411.9	411.4	410.9
152.5°	423.4	423.6	423.8	423.6	423.2	422.7	422.2	421.8
155°	438.5	438.9	439.2	439.0	438.4	437.8	437.2	436.6
157.5°	451.4	451.8	452.1	452.0	451.6	451.1	450.6	450.1
160°	459.3	459.8	460.2	460.2	459.9	459.5	459.2	458.8
162.5°	466.8	467.3	467.7	467.6	467.1	466.5	466.0	465.4
165°	476.3	476.8	477.3	477.3	476.6	476.0	475.4	474.8
167.5°	484.0	484.5	485.0	485.0	484.5	484.0	483.5	482.8
170°	488.2	488.8	489.4	489.4	488.8	488.2	487.6	487.0
172.5°	491.5	492.0	492.5	492.5	491.9	491.3	490.7	490.1
175°	495.0	495.5	496.0	496.0	495.4	494.8	494.2	493.6
177.5°	496.6	497.1	497.4	497.4	496.9	496.5	495.9	495.4
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7

(END OF REPORT)