

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332415-840

Luminaire Tested: **S123RDIW-S560D755U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332415-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D755U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4896.3 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40
2	89	82	76	71	82	76	71	66	64	60	57	52	50	48	42	40	39	34
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	38	36	34	32	30	26
5	69	58	50	44	63	54	47	42	45	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.8
10°-20°	277.6	5.7
20°-30°	436.1	8.9
30°-40°	455.0	9.3
40°-50°	389.4	8.0
50°-60°	296.8	6.1
60°-70°	190.2	3.9
70°-80°	91.5	1.9
80°-90°	27.0	0.6
90°-100°	62.2	1.3
100°-110°	186.1	3.8
110°-120°	316.4	6.5
120°-130°	416.2	8.5
130°-140°	467.8	9.6
140°-150°	459.9	9.4
150°-160°	387.1	7.9
160°-170°	257.7	5.3
170°-180°	90.2	1.8
0°-30°	802.6	16.4
0°-40°	1257.6	25.7
0°-60°	1943.7	39.7
0°-90°	2252.5	46.0
90°-120°	564.7	11.5
90°-150°	1908.6	39.0
90°-180°	2644.0	54.0
0°-180°	4896.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	22	1	22	1	22	11
95°	58	44	58	44	58	60
105°	178	169	178	169	178	189
115°	319	319	319	319	319	316
125°	461	466	461	466	461	412
135°	604	605	604	605	604	464
145°	734	734	734	734	734	458
155°	839	840	839	840	839	386
165°	912	915	912	915	912	257
175°	948	952	948	952	948	90
180°	954	954	954	954	954	



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	7.6	8.2	7.5	7.7	7.7	7.9	7.7	7.6	8.1	7.6	7.5
90°	22.5	22.1	21.8	21.5	21.1	20.7	20.0	19.3	18.7	18.0	15.9
92.5°	30.3	30.5	30.7	30.9	31.1	30.9	30.4	29.9	29.3	28.8	27.6
95°	58.5	58.5	58.5	58.5	58.5	58.2	57.5	56.8	56.1	55.4	54.1
97.5°	90.0	90.0	90.1	90.2	90.2	89.9	89.1	88.4	87.6	86.8	85.8
100°	113.9	113.6	113.3	112.9	112.6	112.2	111.7	111.2	110.7	110.2	109.4
102.5°	138.6	138.6	138.7	138.8	138.8	138.6	138.0	137.5	137.0	136.5	135.4
105°	178.4	178.0	177.7	177.4	177.0	176.9	176.9	176.9	176.9	176.9	175.4
107.5°	219.9	220.2	220.4	220.6	220.8	220.6	220.0	219.4	218.9	218.4	217.8
110°	248.1	248.4	248.7	249.1	249.4	249.2	248.6	247.9	247.3	246.6	246.3



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.1	278.1	278.2	278.3	278.3	278.0	277.2	276.4	275.6	274.8	274.7
115°	319.3	319.5	319.6	319.8	320.0	320.0	319.8	319.6	319.5	319.3	319.6
117.5°	361.1	361.6	362.0	362.5	363.0	363.2	363.2	363.3	363.3	363.3	363.9
120°	390.5	390.8	391.2	391.5	391.8	392.1	392.2	392.4	392.6	392.7	393.6
122.5°	418.7	419.2	419.6	420.1	420.6	421.0	421.4	421.9	422.3	422.7	423.2
125°	461.0	461.6	462.3	463.0	463.6	464.3	464.9	465.6	466.4	467.0	467.3
127.5°	503.1	503.9	504.6	505.4	506.1	507.1	508.0	508.9	509.8	510.8	511.1
130°	530.7	531.9	533.0	534.2	535.3	536.2	536.9	537.7	538.3	539.0	539.5
132.5°	559.5	560.4	561.3	562.2	563.1	563.9	564.7	565.5	566.3	567.1	567.4
135°	604.1	604.5	604.8	605.1	605.5	606.0	606.6	607.3	607.9	608.6	608.8
137.5°	643.6	644.2	644.8	645.5	646.1	646.8	647.4	648.1	648.8	649.5	649.1
140°	669.3	670.6	671.7	672.9	674.0	674.7	674.9	675.0	675.2	675.4	675.2
142.5°	695.7	696.6	697.5	698.4	699.3	699.8	700.0	700.2	700.3	700.5	700.2
145°	733.9	734.5	735.2	735.8	736.5	736.9	737.1	737.2	737.4	737.6	737.1
147.5°	767.7	768.7	769.7	770.7	771.7	772.2	772.2	772.2	772.2	772.2	771.7
150°	789.3	790.3	791.3	792.2	793.2	793.8	793.8	793.8	793.8	793.8	793.5
152.5°	810.3	811.1	812.0	812.8	813.7	814.1	813.7	813.5	813.2	812.9	812.7
155°	838.8	839.9	841.1	842.2	843.4	843.6	843.0	842.3	841.7	841.0	840.8
157.5°	864.6	865.7	866.6	867.5	868.4	868.6	867.9	867.2	866.5	865.8	865.7
160°	881.5	882.1	882.8	883.5	884.1	884.0	883.2	882.4	881.6	880.7	880.7
162.5°	894.0	895.1	896.3	897.3	898.4	898.5	897.7	896.8	896.0	895.1	895.0
165°	912.2	913.4	914.5	915.7	916.9	917.0	915.9	914.9	913.9	912.9	912.9
167.5°	927.7	928.7	929.7	930.8	931.8	931.8	930.8	929.7	928.7	927.7	927.6
170°	935.4	936.6	937.8	939.0	940.1	940.1	939.0	937.8	936.6	935.4	935.4
172.5°	941.5	942.6	943.8	944.9	946.1	946.1	945.1	944.1	943.1	942.0	942.0
175°	948.2	949.4	950.5	951.7	952.9	952.9	951.9	951.0	950.0	949.0	949.0
177.5°	951.8	952.7	953.6	954.6	955.5	955.6	954.8	954.0	953.2	952.4	952.4
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	7.7	7.0	7.2	6.8	7.4	7.3	8.9	10.1	10.7	9.8	10.1
90°	13.6	11.5	9.3	7.4	5.8	4.0	2.4	0.7	2.4	4.0	5.8
92.5°	26.4	25.0	23.8	22.6	21.5	20.4	19.3	18.2	19.3	20.4	21.5
95°	52.8	51.5	50.1	48.9	47.8	46.6	45.3	44.2	45.3	46.6	47.8
97.5°	84.8	83.9	82.9	82.0	81.2	80.3	79.4	78.6	79.4	80.3	81.2
100°	108.6	107.7	106.8	105.9	104.9	103.9	102.9	101.9	102.9	103.9	104.9
102.5°	134.4	133.3	132.2	131.3	130.7	130.2	129.6	129.0	129.6	130.2	130.7
105°	173.9	172.4	170.9	170.0	169.7	169.4	169.0	168.6	169.0	169.4	169.7
107.5°	217.2	216.6	216.0	215.6	215.4	215.2	215.0	214.8	215.0	215.2	215.4
110°	245.9	245.6	245.3	244.9	244.6	244.3	244.0	243.6	244.0	244.3	244.6



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	274.7	274.6	274.5	274.4	274.2	274.0	273.8	273.6	273.8	274.0	274.2
115°	320.0	320.3	320.6	320.5	320.0	319.5	319.0	318.6	319.0	319.5	320.0
117.5°	364.3	364.7	365.2	365.2	364.9	364.5	364.2	363.9	364.2	364.5	364.9
120°	394.5	395.3	396.1	396.1	395.1	394.0	393.0	392.0	393.0	394.0	395.1
122.5°	423.6	424.0	424.4	424.3	423.6	422.8	422.1	421.4	422.1	422.8	423.6
125°	467.7	468.0	468.3	468.3	467.8	467.3	466.8	466.3	466.8	467.3	467.8
127.5°	511.5	511.9	512.2	511.9	510.8	509.8	508.7	507.6	508.7	509.8	510.8
130°	540.0	540.5	541.0	540.5	539.2	537.9	536.5	535.2	536.5	537.9	539.2
132.5°	567.8	568.3	568.6	568.2	566.7	565.4	564.1	562.8	564.1	565.4	566.7
135°	608.9	609.2	609.4	608.8	607.9	606.9	605.9	604.9	605.9	606.9	607.9
137.5°	648.7	648.2	647.8	647.2	646.4	645.5	644.7	643.9	644.7	645.5	646.4
140°	675.0	674.9	674.7	674.2	673.4	672.6	671.7	670.9	671.7	672.6	673.4
142.5°	699.9	699.6	699.3	698.7	697.9	697.1	696.3	695.5	696.3	697.1	697.9
145°	736.6	736.1	735.6	735.2	734.8	734.5	734.2	733.9	734.2	734.5	734.8
147.5°	771.2	770.8	770.3	769.8	769.2	768.6	768.0	767.4	768.0	768.6	769.2
150°	793.1	792.7	792.4	792.1	791.8	791.4	791.1	790.8	791.1	791.4	791.8
152.5°	812.5	812.3	812.1	811.8	811.4	810.9	810.4	810.0	810.4	810.9	811.4
155°	840.7	840.5	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3
157.5°	865.5	865.4	865.3	865.3	865.5	865.7	865.9	866.1	865.9	865.7	865.5
160°	880.7	880.7	880.7	880.9	881.2	881.6	881.9	882.2	881.9	881.6	881.2
162.5°	894.8	894.7	894.6	894.7	895.2	895.6	896.2	896.7	896.2	895.6	895.2
165°	912.9	912.9	912.9	913.2	913.7	914.2	914.7	915.2	914.7	914.2	913.7
167.5°	927.4	927.3	927.2	927.4	928.1	928.8	929.4	930.1	929.4	928.8	928.1
170°	935.4	935.4	935.4	935.7	936.4	937.2	937.8	938.5	937.8	937.2	936.4
172.5°	942.0	942.0	942.0	942.4	943.0	943.7	944.4	945.0	944.4	943.7	943.0
175°	949.0	949.0	949.0	949.3	950.0	950.6	951.3	951.9	951.3	950.6	950.0
177.5°	952.4	952.4	952.4	952.7	953.2	953.7	954.2	954.8	954.2	953.7	953.2
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	10.1	11.4	12.2	12.9	13.7	13.8	14.2	14.3	14.8	14.9	15.0
90°	7.4	9.3	11.5	13.6	15.9	18.0	18.7	19.3	20.0	20.7	21.1
92.5°	22.6	23.8	25.0	26.4	27.6	28.8	29.3	29.9	30.4	30.9	31.1
95°	48.9	50.1	51.5	52.8	54.1	55.4	56.1	56.8	57.5	58.2	58.5
97.5°	82.0	82.9	83.9	84.8	85.8	86.8	87.6	88.4	89.1	89.9	90.2
100°	105.9	106.8	107.7	108.6	109.4	110.2	110.7	111.2	111.7	112.2	112.6
102.5°	131.3	132.2	133.3	134.4	135.4	136.5	137.0	137.5	138.0	138.6	138.8
105°	170.0	170.9	172.4	173.9	175.4	176.9	176.9	176.9	176.9	176.9	177.0
107.5°	215.6	216.0	216.6	217.2	217.8	218.4	218.9	219.4	220.0	220.6	220.8
110°	244.9	245.3	245.6	245.9	246.3	246.6	247.3	247.9	248.6	249.2	249.4



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	274.4	274.5	274.6	274.7	274.7	274.8	275.6	276.4	277.2	278.0	278.3
115°	320.5	320.6	320.3	320.0	319.6	319.3	319.5	319.6	319.8	320.0	320.0
117.5°	365.2	365.2	364.7	364.3	363.9	363.3	363.3	363.3	363.2	363.2	363.0
120°	396.1	396.1	395.3	394.5	393.6	392.7	392.6	392.4	392.2	392.1	391.8
122.5°	424.3	424.4	424.0	423.6	423.2	422.7	422.3	421.9	421.4	421.0	420.6
125°	468.3	468.3	468.0	467.7	467.3	467.0	466.4	465.6	464.9	464.3	463.6
127.5°	511.9	512.2	511.9	511.5	511.1	510.8	509.8	508.9	508.0	507.1	506.1
130°	540.5	541.0	540.5	540.0	539.5	539.0	538.3	537.7	536.9	536.2	535.3
132.5°	568.2	568.6	568.3	567.8	567.4	567.1	566.3	565.5	564.7	563.9	563.1
135°	608.8	609.4	609.2	608.9	608.8	608.6	607.9	607.3	606.6	606.0	605.5
137.5°	647.2	647.8	648.2	648.7	649.1	649.5	648.8	648.1	647.4	646.8	646.1
140°	674.2	674.7	674.9	675.0	675.2	675.4	675.2	675.0	674.9	674.7	674.0
142.5°	698.7	699.3	699.6	699.9	700.2	700.5	700.3	700.2	700.0	699.8	699.3
145°	735.2	735.6	736.1	736.6	737.1	737.6	737.4	737.2	737.1	736.9	736.5
147.5°	769.8	770.3	770.8	771.2	771.7	772.2	772.2	772.2	772.2	772.2	771.7
150°	792.1	792.4	792.7	793.1	793.5	793.8	793.8	793.8	793.8	793.8	793.2
152.5°	811.8	812.1	812.3	812.5	812.7	812.9	813.2	813.5	813.7	814.1	813.7
155°	840.3	840.3	840.5	840.7	840.8	841.0	841.7	842.3	843.0	843.6	843.4
157.5°	865.3	865.3	865.4	865.5	865.7	865.8	866.5	867.2	867.9	868.6	868.4
160°	880.9	880.7	880.7	880.7	880.7	880.7	881.6	882.4	883.2	884.0	884.1
162.5°	894.7	894.6	894.7	894.8	895.0	895.1	896.0	896.8	897.7	898.5	898.4
165°	913.2	912.9	912.9	912.9	912.9	912.9	913.9	914.9	915.9	917.0	916.9
167.5°	927.4	927.2	927.3	927.4	927.6	927.7	928.7	929.7	930.8	931.8	931.8
170°	935.7	935.4	935.4	935.4	935.4	935.4	936.6	937.8	939.0	940.1	940.1
172.5°	942.4	942.0	942.0	942.0	942.0	942.0	943.1	944.1	945.1	946.1	946.1
175°	949.3	949.0	949.0	949.0	949.0	949.0	950.0	951.0	951.9	952.9	952.9
177.5°	952.7	952.4	952.4	952.4	952.4	952.4	953.2	954.0	954.8	955.6	955.5
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	15.8	15.1	15.2	15.7	15.2	15.1	15.8	15.0	14.9	14.8	14.3
90°	21.5	21.8	22.1	22.5	22.1	21.8	21.5	21.1	20.7	20.0	19.3
92.5°	30.9	30.7	30.5	30.3	30.5	30.7	30.9	31.1	30.9	30.4	29.9
95°	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.2	57.5	56.8
97.5°	90.2	90.1	90.0	90.0	90.0	90.1	90.2	90.2	89.9	89.1	88.4
100°	112.9	113.3	113.6	113.9	113.6	113.3	112.9	112.6	112.2	111.7	111.2
102.5°	138.8	138.7	138.6	138.6	138.6	138.7	138.8	138.8	138.6	138.0	137.5
105°	177.4	177.7	178.0	178.4	178.0	177.7	177.4	177.0	176.9	176.9	176.9
107.5°	220.6	220.4	220.2	219.9	220.2	220.4	220.6	220.8	220.6	220.0	219.4
110°	249.1	248.7	248.4	248.1	248.4	248.7	249.1	249.4	249.2	248.6	247.9



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	278.3	278.2	278.1	278.1	278.1	278.2	278.3	278.3	278.0	277.2	276.4
115°	319.8	319.6	319.5	319.3	319.5	319.6	319.8	320.0	320.0	319.8	319.6
117.5°	362.5	362.0	361.6	361.1	361.6	362.0	362.5	363.0	363.2	363.2	363.3
120°	391.5	391.2	390.8	390.5	390.8	391.2	391.5	391.8	392.1	392.2	392.4
122.5°	420.1	419.6	419.2	418.7	419.2	419.6	420.1	420.6	421.0	421.4	421.9
125°	463.0	462.3	461.6	461.0	461.6	462.3	463.0	463.6	464.3	464.9	465.6
127.5°	505.4	504.6	503.9	503.1	503.9	504.6	505.4	506.1	507.1	508.0	508.9
130°	534.2	533.0	531.9	530.7	531.9	533.0	534.2	535.3	536.2	536.9	537.7
132.5°	562.2	561.3	560.4	559.5	560.4	561.3	562.2	563.1	563.9	564.7	565.5
135°	605.1	604.8	604.5	604.1	604.5	604.8	605.1	605.5	606.0	606.6	607.3
137.5°	645.5	644.8	644.2	643.6	644.2	644.8	645.5	646.1	646.8	647.4	648.1
140°	672.9	671.7	670.6	669.3	670.6	671.7	672.9	674.0	674.7	674.9	675.0
142.5°	698.4	697.5	696.6	695.7	696.6	697.5	698.4	699.3	699.8	700.0	700.2
145°	735.8	735.2	734.5	733.9	734.5	735.2	735.8	736.5	736.9	737.1	737.2
147.5°	770.7	769.7	768.7	767.7	768.7	769.7	770.7	771.7	772.2	772.2	772.2
150°	792.2	791.3	790.3	789.3	790.3	791.3	792.2	793.2	793.8	793.8	793.8
152.5°	812.8	812.0	811.1	810.3	811.1	812.0	812.8	813.7	814.1	813.7	813.5
155°	842.2	841.1	839.9	838.8	839.9	841.1	842.2	843.4	843.6	843.0	842.3
157.5°	867.5	866.6	865.7	864.6	865.7	866.6	867.5	868.4	868.6	867.9	867.2
160°	883.5	882.8	882.1	881.5	882.1	882.8	883.5	884.1	884.0	883.2	882.4
162.5°	897.3	896.3	895.1	894.0	895.1	896.3	897.3	898.4	898.5	897.7	896.8
165°	915.7	914.5	913.4	912.2	913.4	914.5	915.7	916.9	917.0	915.9	914.9
167.5°	930.8	929.7	928.7	927.7	928.7	929.7	930.8	931.8	931.8	930.8	929.7
170°	939.0	937.8	936.6	935.4	936.6	937.8	939.0	940.1	940.1	939.0	937.8
172.5°	944.9	943.8	942.6	941.5	942.6	943.8	944.9	946.1	946.1	945.1	944.1
175°	951.7	950.5	949.4	948.2	949.4	950.5	951.7	952.9	952.9	951.9	951.0
177.5°	954.6	953.6	952.7	951.8	952.7	953.6	954.6	955.5	955.6	954.8	954.0
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	14.2	13.8	13.7	12.9	12.2	11.4	10.1	10.1	9.8	10.7	10.1
90°	18.7	18.0	15.9	13.6	11.5	9.3	7.4	5.8	4.0	2.4	0.7
92.5°	29.3	28.8	27.6	26.4	25.0	23.8	22.6	21.5	20.4	19.3	18.2
95°	56.1	55.4	54.1	52.8	51.5	50.1	48.9	47.8	46.6	45.3	44.2
97.5°	87.6	86.8	85.8	84.8	83.9	82.9	82.0	81.2	80.3	79.4	78.6
100°	110.7	110.2	109.4	108.6	107.7	106.8	105.9	104.9	103.9	102.9	101.9
102.5°	137.0	136.5	135.4	134.4	133.3	132.2	131.3	130.7	130.2	129.6	129.0
105°	176.9	176.9	175.4	173.9	172.4	170.9	170.0	169.7	169.4	169.0	168.6
107.5°	218.9	218.4	217.8	217.2	216.6	216.0	215.6	215.4	215.2	215.0	214.8
110°	247.3	246.6	246.3	245.9	245.6	245.3	244.9	244.6	244.3	244.0	243.6



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.6	274.8	274.7	274.7	274.6	274.5	274.4	274.2	274.0	273.8	273.6
115°	319.5	319.3	319.6	320.0	320.3	320.6	320.5	320.0	319.5	319.0	318.6
117.5°	363.3	363.3	363.9	364.3	364.7	365.2	365.2	364.9	364.5	364.2	363.9
120°	392.6	392.7	393.6	394.5	395.3	396.1	396.1	395.1	394.0	393.0	392.0
122.5°	422.3	422.7	423.2	423.6	424.0	424.4	424.3	423.6	422.8	422.1	421.4
125°	466.4	467.0	467.3	467.7	468.0	468.3	468.3	467.8	467.3	466.8	466.3
127.5°	509.8	510.8	511.1	511.5	511.9	512.2	511.9	510.8	509.8	508.7	507.6
130°	538.3	539.0	539.5	540.0	540.5	541.0	540.5	539.2	537.9	536.5	535.2
132.5°	566.3	567.1	567.4	567.8	568.3	568.6	568.2	566.7	565.4	564.1	562.8
135°	607.9	608.6	608.8	608.9	609.2	609.4	608.8	607.9	606.9	605.9	604.9
137.5°	648.8	649.5	649.1	648.7	648.2	647.8	647.2	646.4	645.5	644.7	643.9
140°	675.2	675.4	675.2	675.0	674.9	674.7	674.2	673.4	672.6	671.7	670.9
142.5°	700.3	700.5	700.2	699.9	699.6	699.3	698.7	697.9	697.1	696.3	695.5
145°	737.4	737.6	737.1	736.6	736.1	735.6	735.2	734.8	734.5	734.2	733.9
147.5°	772.2	772.2	771.7	771.2	770.8	770.3	769.8	769.2	768.6	768.0	767.4
150°	793.8	793.8	793.5	793.1	792.7	792.4	792.1	791.8	791.4	791.1	790.8
152.5°	813.2	812.9	812.7	812.5	812.3	812.1	811.8	811.4	810.9	810.4	810.0
155°	841.7	841.0	840.8	840.7	840.5	840.3	840.3	840.3	840.3	840.3	840.3
157.5°	866.5	865.8	865.7	865.5	865.4	865.3	865.3	865.5	865.7	865.9	866.1
160°	881.6	880.7	880.7	880.7	880.7	880.7	880.9	881.2	881.6	881.9	882.2
162.5°	896.0	895.1	895.0	894.8	894.7	894.6	894.7	895.2	895.6	896.2	896.7
165°	913.9	912.9	912.9	912.9	912.9	912.9	913.2	913.7	914.2	914.7	915.2
167.5°	928.7	927.7	927.6	927.4	927.3	927.2	927.4	928.1	928.8	929.4	930.1
170°	936.6	935.4	935.4	935.4	935.4	935.4	935.7	936.4	937.2	937.8	938.5
172.5°	943.1	942.0	942.0	942.0	942.0	942.0	942.4	943.0	943.7	944.4	945.0
175°	950.0	949.0	949.0	949.0	949.0	949.0	949.3	950.0	950.6	951.3	951.9
177.5°	953.2	952.4	952.4	952.4	952.4	952.4	952.7	953.2	953.7	954.2	954.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	8.9	7.3	7.4	6.8	7.2	7.0	7.7	7.5	7.6	8.1	7.6
90°	2.4	4.0	5.8	7.4	9.3	11.5	13.6	15.9	18.0	18.7	19.3
92.5°	19.3	20.4	21.5	22.6	23.8	25.0	26.4	27.6	28.8	29.3	29.9
95°	45.3	46.6	47.8	48.9	50.1	51.5	52.8	54.1	55.4	56.1	56.8
97.5°	79.4	80.3	81.2	82.0	82.9	83.9	84.8	85.8	86.8	87.6	88.4
100°	102.9	103.9	104.9	105.9	106.8	107.7	108.6	109.4	110.2	110.7	111.2
102.5°	129.6	130.2	130.7	131.3	132.2	133.3	134.4	135.4	136.5	137.0	137.5
105°	169.0	169.4	169.7	170.0	170.9	172.4	173.9	175.4	176.9	176.9	176.9
107.5°	215.0	215.2	215.4	215.6	216.0	216.6	217.2	217.8	218.4	218.9	219.4
110°	244.0	244.3	244.6	244.9	245.3	245.6	245.9	246.3	246.6	247.3	247.9



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	273.8	274.0	274.2	274.4	274.5	274.6	274.7	274.7	274.8	275.6	276.4
115°	319.0	319.5	320.0	320.5	320.6	320.3	320.0	319.6	319.3	319.5	319.6
117.5°	364.2	364.5	364.9	365.2	365.2	364.7	364.3	363.9	363.3	363.3	363.3
120°	393.0	394.0	395.1	396.1	396.1	395.3	394.5	393.6	392.7	392.6	392.4
122.5°	422.1	422.8	423.6	424.3	424.4	424.0	423.6	423.2	422.7	422.3	421.9
125°	466.8	467.3	467.8	468.3	468.3	468.0	467.7	467.3	467.0	466.4	465.6
127.5°	508.7	509.8	510.8	511.9	512.2	511.9	511.5	511.1	510.8	509.8	508.9
130°	536.5	537.9	539.2	540.5	541.0	540.5	540.0	539.5	539.0	538.3	537.7
132.5°	564.1	565.4	566.7	568.2	568.6	568.3	567.8	567.4	567.1	566.3	565.5
135°	605.9	606.9	607.9	608.8	609.4	609.2	608.9	608.8	608.6	607.9	607.3
137.5°	644.7	645.5	646.4	647.2	647.8	648.2	648.7	649.1	649.5	648.8	648.1
140°	671.7	672.6	673.4	674.2	674.7	674.9	675.0	675.2	675.4	675.2	675.0
142.5°	696.3	697.1	697.9	698.7	699.3	699.6	699.9	700.2	700.5	700.3	700.2
145°	734.2	734.5	734.8	735.2	735.6	736.1	736.6	737.1	737.6	737.4	737.2
147.5°	768.0	768.6	769.2	769.8	770.3	770.8	771.2	771.7	772.2	772.2	772.2
150°	791.1	791.4	791.8	792.1	792.4	792.7	793.1	793.5	793.8	793.8	793.8
152.5°	810.4	810.9	811.4	811.8	812.1	812.3	812.5	812.7	812.9	813.2	813.5
155°	840.3	840.3	840.3	840.3	840.3	840.5	840.7	840.8	841.0	841.7	842.3
157.5°	865.9	865.7	865.5	865.3	865.3	865.4	865.5	865.7	865.8	866.5	867.2
160°	881.9	881.6	881.2	880.9	880.7	880.7	880.7	880.7	880.7	881.6	882.4
162.5°	896.2	895.6	895.2	894.7	894.6	894.7	894.8	895.0	895.1	896.0	896.8
165°	914.7	914.2	913.7	913.2	912.9	912.9	912.9	912.9	912.9	913.9	914.9
167.5°	929.4	928.8	928.1	927.4	927.2	927.3	927.4	927.6	927.7	928.7	929.7
170°	937.8	937.2	936.4	935.7	935.4	935.4	935.4	935.4	935.4	936.6	937.8
172.5°	944.4	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.1	944.1
175°	951.3	950.6	950.0	949.3	949.0	949.0	949.0	949.0	949.0	950.0	951.0
177.5°	954.2	953.7	953.2	952.7	952.4	952.4	952.4	952.4	952.4	953.2	954.0
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	7.7	7.9	7.7	7.7	7.5	8.2	7.6
90°	20.0	20.7	21.1	21.5	21.8	22.1	22.5
92.5°	30.4	30.9	31.1	30.9	30.7	30.5	30.3
95°	57.5	58.2	58.5	58.5	58.5	58.5	58.5
97.5°	89.1	89.9	90.2	90.2	90.1	90.0	90.0
100°	111.7	112.2	112.6	112.9	113.3	113.6	113.9
102.5°	138.0	138.6	138.8	138.8	138.7	138.6	138.6
105°	176.9	176.9	177.0	177.4	177.7	178.0	178.4
107.5°	220.0	220.6	220.8	220.6	220.4	220.2	219.9
110°	248.6	249.2	249.4	249.1	248.7	248.4	248.1



TEST NUMBER: P332415-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	277.2	278.0	278.3	278.3	278.2	278.1	278.1
115°	319.8	320.0	320.0	319.8	319.6	319.5	319.3
117.5°	363.2	363.2	363.0	362.5	362.0	361.6	361.1
120°	392.2	392.1	391.8	391.5	391.2	390.8	390.5
122.5°	421.4	421.0	420.6	420.1	419.6	419.2	418.7
125°	464.9	464.3	463.6	463.0	462.3	461.6	461.0
127.5°	508.0	507.1	506.1	505.4	504.6	503.9	503.1
130°	536.9	536.2	535.3	534.2	533.0	531.9	530.7
132.5°	564.7	563.9	563.1	562.2	561.3	560.4	559.5
135°	606.6	606.0	605.5	605.1	604.8	604.5	604.1
137.5°	647.4	646.8	646.1	645.5	644.8	644.2	643.6
140°	674.9	674.7	674.0	672.9	671.7	670.6	669.3
142.5°	700.0	699.8	699.3	698.4	697.5	696.6	695.7
145°	737.1	736.9	736.5	735.8	735.2	734.5	733.9
147.5°	772.2	772.2	771.7	770.7	769.7	768.7	767.7
150°	793.8	793.8	793.2	792.2	791.3	790.3	789.3
152.5°	813.7	814.1	813.7	812.8	812.0	811.1	810.3
155°	843.0	843.6	843.4	842.2	841.1	839.9	838.8
157.5°	867.9	868.6	868.4	867.5	866.6	865.7	864.6
160°	883.2	884.0	884.1	883.5	882.8	882.1	881.5
162.5°	897.7	898.5	898.4	897.3	896.3	895.1	894.0
165°	915.9	917.0	916.9	915.7	914.5	913.4	912.2
167.5°	930.8	931.8	931.8	930.8	929.7	928.7	927.7
170°	939.0	940.1	940.1	939.0	937.8	936.6	935.4
172.5°	945.1	946.1	946.1	944.9	943.8	942.6	941.5
175°	951.9	952.9	952.9	951.7	950.5	949.4	948.2
177.5°	954.8	955.6	955.5	954.6	953.6	952.7	951.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2

(END OF REPORT)