

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332167-940

Luminaire Tested: **S123DIW-S775D1030U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332167-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1030U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6015.3 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45				39	
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38				33	
3	81	71	64	58	74	66	59	54	55	50	46	46	42	39	37	34	32				28	
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24				21	
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21				18	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19				16	
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17				14	
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	21	18	15				13	
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.3	1.7
10°-20°	288.8	4.8
20°-30°	426.6	7.1
30°-40°	498.4	8.3
40°-50°	501.0	8.3
50°-60°	440.1	7.3
60°-70°	327.9	5.5
70°-80°	186.8	3.1
80°-90°	57.0	0.9
90°-100°	74.9	1.2
100°-110°	224.2	3.7
110°-120°	381.4	6.3
120°-130°	501.7	8.3
130°-140°	563.9	9.4
140°-150°	554.3	9.2
150°-160°	466.6	7.8
160°-170°	310.6	5.2
170°-180°	108.8	1.8
0°-30°	817.7	13.6
0°-40°	1316.1	21.9
0°-60°	2257.3	37.5
0°-90°	2829.0	47.0
90°-120°	680.6	11.3
90°-150°	2300.3	38.2
90°-180°	3186.0	53.0
0°-180°	6015.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	10	22	25	27	6
95°	53	60	67	70	70	60
105°	203	205	213	213	215	218
115°	384	386	385	386	385	380
125°	562	564	563	559	556	501
135°	729	734	734	730	728	562
145°	884	886	889	888	884	552
155°	1013	1013	1014	1017	1011	466
165°	1103	1100	1100	1105	1100	311
175°	1147	1144	1144	1148	1143	109
180°	1150	1150	1150	1150	1150	



TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.6	19.5	19.4	19.4	19.2	19.4	19.7	20.1	20.4	20.8	20.8
90°	0.9	2.9	4.9	7.0	8.9	11.2	13.8	16.5	19.1	21.7	22.5
92.5°	21.8	23.2	24.6	25.9	27.3	28.7	30.2	31.7	33.2	34.7	35.3
95°	53.3	54.7	56.1	57.5	58.9	60.5	62.1	63.7	65.3	66.9	67.7
97.5°	94.7	95.7	96.8	97.8	98.9	100.0	101.1	102.3	103.4	104.6	105.6
100°	122.9	124.0	125.3	126.4	127.7	128.8	129.8	130.8	131.8	132.8	133.4
102.5°	155.4	156.1	156.9	157.6	158.3	159.3	160.6	161.9	163.3	164.6	165.2
105°	203.3	203.7	204.1	204.5	204.9	206.0	207.8	209.6	211.4	213.2	213.2
107.5°	259.0	259.1	259.4	259.7	259.8	260.4	261.1	261.8	262.5	263.2	263.9
110°	293.6	294.0	294.4	294.8	295.2	295.6	296.0	296.4	296.9	297.2	298.0



TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.8	330.0	330.2	330.5	330.7	330.8	330.9	331.0	331.1	331.2	332.2
115°	384.0	384.5	385.1	385.8	386.4	386.5	386.0	385.7	385.2	384.9	385.0
117.5°	438.5	438.9	439.3	439.7	440.1	440.1	439.5	439.0	438.5	438.0	437.9
120°	472.5	473.7	474.9	476.1	477.3	477.4	476.4	475.4	474.4	473.4	473.1
122.5°	507.9	508.8	509.7	510.5	511.4	511.6	511.1	510.6	510.1	509.5	509.0
125°	562.0	562.5	563.1	563.7	564.4	564.5	564.0	563.7	563.2	562.8	562.0
127.5°	611.8	613.1	614.4	615.6	616.9	617.3	616.9	616.4	616.0	615.5	614.5
130°	645.1	646.7	648.3	649.9	651.5	651.9	651.4	650.8	650.1	649.5	648.7
132.5°	678.2	679.8	681.4	683.1	684.7	685.3	684.8	684.4	683.9	683.5	682.5
135°	729.1	730.2	731.5	732.6	733.9	734.3	734.1	734.0	733.8	733.5	732.7
137.5°	776.1	777.0	778.0	779.0	780.1	780.8	781.3	781.9	782.4	782.9	782.0
140°	808.5	809.6	810.6	811.5	812.5	813.2	813.3	813.6	813.8	814.0	813.8
142.5°	838.2	839.2	840.2	841.2	842.2	842.8	843.2	843.6	844.0	844.4	844.1
145°	884.4	884.8	885.2	885.6	886.0	886.5	887.2	887.8	888.3	888.9	888.8
147.5°	924.9	925.6	926.3	927.1	927.8	928.4	929.0	929.6	930.1	930.7	930.7
150°	953.1	953.5	953.9	954.3	954.7	955.1	955.5	955.9	956.3	956.7	956.7
152.5°	976.2	976.8	977.3	977.9	978.5	978.8	979.1	979.4	979.6	979.8	980.2
155°	1012.7	1012.7	1012.7	1012.7	1012.7	1012.8	1013.0	1013.3	1013.4	1013.6	1014.4
157.5°	1043.8	1043.6	1043.3	1043.0	1042.9	1042.8	1042.9	1043.1	1043.3	1043.4	1044.3
160°	1063.3	1062.9	1062.5	1062.1	1061.7	1061.5	1061.5	1061.5	1061.5	1061.5	1062.5
162.5°	1080.7	1080.1	1079.5	1079.0	1078.4	1078.2	1078.3	1078.5	1078.7	1078.9	1079.9
165°	1103.0	1102.4	1101.9	1101.3	1100.6	1100.4	1100.4	1100.4	1100.4	1100.4	1101.5
167.5°	1121.0	1120.2	1119.4	1118.6	1117.8	1117.4	1117.6	1117.8	1117.9	1118.0	1119.3
170°	1131.0	1130.2	1129.4	1128.6	1127.8	1127.5	1127.5	1127.5	1127.5	1127.5	1128.8
172.5°	1139.0	1138.2	1137.4	1136.6	1135.8	1135.4	1135.4	1135.4	1135.4	1135.4	1136.7
175°	1147.4	1146.6	1145.8	1145.0	1144.2	1143.7	1143.7	1143.7	1143.7	1143.7	1145.0
177.5°	1150.8	1150.1	1149.5	1148.8	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1148.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	20.8	20.8	20.8	20.8	20.9	21.0	21.0	21.1
90°	23.3	24.1	24.9	25.5	25.9	26.3	26.7	27.1
92.5°	35.9	36.6	37.3	37.5	37.2	37.0	36.7	36.5
95°	68.5	69.3	70.1	70.4	70.4	70.4	70.4	70.4
97.5°	106.5	107.4	108.3	108.7	108.6	108.6	108.5	108.4
100°	134.0	134.6	135.2	135.7	136.1	136.5	136.9	137.3
102.5°	165.8	166.4	167.0	167.3	167.2	167.1	167.0	166.9
105°	213.2	213.2	213.2	213.4	213.8	214.2	214.6	215.0
107.5°	264.6	265.2	265.8	266.0	265.8	265.6	265.3	265.0
110°	298.8	299.6	300.4	300.6	300.2	299.8	299.4	299.0





TEST NUMBER: P332167-940

CATALOG NUMBER: S123DIW-S775D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	333.1	334.0	335.0	335.5	335.4	335.3	335.3	335.2
115°	385.2	385.5	385.7	385.7	385.5	385.2	385.0	384.9
117.5°	437.9	437.8	437.8	437.5	436.9	436.4	435.8	435.2
120°	473.0	472.8	472.6	472.3	471.9	471.4	471.1	470.6
122.5°	508.5	507.9	507.5	506.8	506.3	505.8	505.2	504.6
125°	561.2	560.4	559.6	558.8	558.0	557.2	556.4	555.6
127.5°	613.3	612.2	611.1	610.0	609.1	608.2	607.3	606.4
130°	647.9	647.1	646.3	645.2	643.8	642.4	641.1	639.6
132.5°	681.6	680.6	679.7	678.7	677.5	676.5	675.4	674.3
135°	731.9	731.1	730.3	729.8	729.3	729.0	728.5	728.2
137.5°	781.2	780.3	779.5	778.7	777.9	777.2	776.4	775.7
140°	813.6	813.3	813.2	812.3	810.9	809.6	808.2	806.7
142.5°	843.9	843.7	843.6	842.8	841.8	840.7	839.6	838.6
145°	888.6	888.3	888.1	887.6	886.8	886.0	885.2	884.4
147.5°	930.7	930.7	930.7	930.1	928.9	927.6	926.5	925.2
150°	956.7	956.7	956.7	956.1	954.9	953.7	952.5	951.3
152.5°	980.4	980.8	981.1	980.8	979.7	978.7	977.6	976.6
155°	1015.2	1016.0	1016.8	1016.6	1015.1	1013.7	1012.4	1010.9
157.5°	1045.1	1046.0	1046.8	1046.7	1045.5	1044.5	1043.3	1042.1
160°	1063.5	1064.5	1065.5	1065.6	1064.8	1064.0	1063.2	1062.4
162.5°	1080.8	1081.8	1082.9	1082.7	1081.5	1080.1	1078.9	1077.5
165°	1102.8	1103.9	1105.2	1105.1	1103.7	1102.2	1100.8	1099.5
167.5°	1120.5	1121.8	1123.0	1123.0	1121.8	1120.5	1119.3	1118.0
170°	1130.2	1131.7	1133.1	1133.1	1131.7	1130.2	1128.8	1127.5
172.5°	1137.9	1139.2	1140.4	1140.3	1138.9	1137.5	1136.0	1134.7
175°	1146.1	1147.4	1148.5	1148.4	1147.0	1145.6	1144.2	1142.8
177.5°	1149.8	1150.8	1151.7	1151.6	1150.5	1149.4	1148.3	1147.2
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0

(END OF REPORT)