

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332175-940

Luminaire Tested: **S123DIW-S775D1535U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332175-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1535U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7655.8 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	36	34	33	27
3	79	70	63	58	72	64	58	53	52	48	44	42	39	36	32	30	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	39	34	38	32	29	30	26	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12369	10416	9231	10416
10°	15481	10364	8337	10364
15°	18988	10280	7762	10280
20°	22620	10149	7391	10149
25°	24018	9991	7308	9991
30°	20586	9875	7346	9875
35°	14318	9711	7423	9711
40°	10784	9517	7399	9517
45°	8954	9232	7305	9232
50°	8020	8646	7239	8646
55°	7499	8015	7148	8015
60°	7035	7356	7076	7356
65°	6612	6706	6849	6706
70°	6200	5964	6521	5964
75°	5552	5224	5976	5224
80°	4866	4283	5151	4283
85°	3816	3112	3458	3112



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	1.2
10°-20°	304.3	4.0
20°-30°	510.8	6.7
30°-40°	578.4	7.6
40°-50°	518.7	6.8
50°-60°	418.6	5.5
60°-70°	291.7	3.8
70°-80°	153.3	2.0
80°-90°	42.6	0.6
90°-100°	111.5	1.5
100°-110°	333.8	4.4
110°-120°	567.7	7.4
120°-130°	746.7	9.8
130°-140°	839.3	11.0
140°-150°	825.0	10.8
150°-160°	694.5	9.1
160°-170°	462.3	6.0
170°-180°	161.9	2.1
0°-30°	910.1	11.9
0°-40°	1488.4	19.4
0°-60°	2425.7	31.7
0°-90°	2913.2	38.1
90°-120°	1013.0	13.2
90°-150°	3423.9	44.7
90°-180°	4743.0	62.0
0°-180°	7655.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	964	964	964	964	964	
5°	1145	964	854	964	1145	119
15°	1704	922	696	922	1704	492
25°	2022	841	615	841	2022	887
35°	1090	739	565	739	1090	708
45°	588	606	480	606	588	465
55°	400	427	381	427	400	359
65°	260	263	269	263	260	259
75°	134	126	144	126	134	143
85°	31	25	28	25	31	38
90°	40	1	40	1	40	21
95°	105	79	105	79	105	108
105°	320	303	320	303	320	340
115°	573	572	573	572	573	567
125°	827	836	827	836	827	739
135°	1084	1085	1084	1085	1084	833
145°	1316	1316	1316	1316	1316	822
155°	1505	1507	1505	1507	1505	693
165°	1636	1642	1636	1642	1636	462
175°	1701	1708	1701	1708	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1022.5	1021.8	1019.9	1021.5	1018.4	1014.3	1014.0	1010.2	999.3	998.6	995.7
5°	1144.7	1140.9	1140.5	1140.0	1133.5	1124.6	1107.8	1106.3	1084.0	1072.7	1059.3
7.5°	1302.8	1304.8	1298.0	1292.0	1272.0	1258.8	1240.8	1217.7	1190.3	1162.3	1143.7
10°	1416.4	1431.7	1412.6	1399.5	1387.4	1364.5	1337.9	1304.8	1271.7	1232.9	1203.5
12.5°	1538.1	1545.7	1541.9	1529.6	1510.6	1475.9	1428.7	1392.1	1361.6	1297.1	1271.0
15°	1703.9	1732.4	1714.2	1672.1	1673.1	1639.9	1578.3	1510.6	1474.7	1418.2	1341.2
17.5°	1880.5	1884.1	1876.3	1841.4	1818.0	1772.5	1715.6	1650.7	1577.9	1509.5	1427.8
20°	1974.7	1971.8	1955.5	1937.3	1897.2	1861.7	1799.7	1727.2	1633.9	1566.6	1477.5
22.5°	2026.9	2022.3	2014.6	1999.3	1965.9	1927.8	1872.1	1793.0	1704.1	1611.5	1508.5
25°	2022.3	2028.4	2029.3	2025.1	2013.4	1990.6	1946.7	1883.6	1794.9	1675.9	1568.5
27.5°	1839.3	1847.9	1872.9	1895.0	1919.7	1944.9	1941.5	1910.2	1844.6	1741.9	1610.5
30°	1656.3	1637.6	1683.8	1742.2	1781.9	1851.9	1891.1	1893.5	1856.5	1768.4	1640.4
32.5°	1402.3	1422.9	1443.3	1515.1	1601.9	1680.5	1758.5	1821.4	1828.5	1769.9	1658.0
35°	1089.6	1115.3	1152.6	1189.9	1283.4	1363.6	1500.8	1620.3	1715.6	1728.2	1659.6
37.5°	878.0	890.7	914.4	951.7	1012.8	1108.0	1214.2	1365.3	1503.2	1605.9	1610.3
40°	767.5	771.2	797.8	826.3	875.7	954.2	1049.9	1183.4	1348.6	1492.0	1551.8
42.5°	684.6	692.8	704.1	731.4	770.8	829.8	918.8	1029.1	1180.6	1345.6	1462.5
45°	588.2	597.5	604.6	622.8	650.8	690.5	752.5	853.4	968.7	1139.1	1296.4
47.5°	524.5	525.3	530.5	544.2	563.3	593.1	636.9	701.8	807.6	945.7	1107.3
50°	478.9	486.4	488.3	499.0	514.0	535.9	572.3	627.4	714.3	835.6	984.1
52.5°	446.8	449.1	454.3	462.1	475.1	492.2	523.8	566.9	635.1	738.5	875.0
55°	399.6	399.6	404.7	410.8	418.3	433.6	454.7	486.4	538.2	618.6	731.6
57.5°	355.9	358.2	361.9	363.7	370.1	380.3	397.8	422.0	460.6	522.4	612.2
60°	326.8	331.0	330.6	334.2	339.8	347.8	362.7	382.4	416.9	466.4	542.0
62.5°	301.4	301.1	301.0	305.5	311.1	318.7	328.3	345.4	374.7	418.6	483.0
65°	259.6	258.6	261.9	264.7	266.5	272.2	279.6	294.5	314.1	346.9	396.8
67.5°	222.4	219.7	221.5	222.4	225.6	230.0	236.9	246.2	261.8	288.0	325.7
70°	197.0	194.7	194.2	195.1	198.0	201.2	206.3	215.2	229.7	250.7	278.2
72.5°	170.9	169.2	169.2	171.2	172.5	174.7	178.3	186.5	198.0	213.7	239.4
75°	133.5	133.5	133.5	133.9	135.4	137.2	140.1	144.3	153.1	164.3	181.6
77.5°	100.0	100.0	99.4	99.3	101.4	102.3	102.9	106.8	111.7	119.3	131.9
80°	78.5	76.1	77.0	78.5	79.4	79.8	81.2	82.1	86.4	90.6	99.4
82.5°	58.2	56.3	56.4	58.7	58.9	59.3	60.7	62.0	63.6	67.4	72.1
85°	30.9	30.9	31.3	31.3	31.7	31.3	32.6	33.2	33.2	35.5	38.3
87.5°	19.3	18.4	18.6	18.9	18.5	18.6	18.7	18.9	19.0	19.2	18.7
90°	40.3	39.8	39.1	38.5	38.0	37.1	35.8	34.7	33.4	32.3	28.4
92.5°	54.3	54.7	55.0	55.4	55.7	55.5	54.5	53.5	52.6	51.6	49.4
95°	104.9	104.9	104.9	104.9	104.9	104.2	103.1	101.9	100.7	99.5	97.1
97.5°	161.4	161.5	161.6	161.8	161.8	161.2	159.8	158.5	157.1	155.7	154.0
100°	204.4	203.8	203.2	202.6	202.0	201.3	200.4	199.5	198.6	197.7	196.2
102.5°	248.5	248.6	248.7	248.9	249.0	248.6	247.7	246.8	245.9	245.0	243.0
105°	320.0	319.4	318.9	318.3	317.6	317.4	317.4	317.4	317.4	317.4	314.7
107.5°	394.5	394.8	395.2	395.6	395.9	395.7	394.7	393.8	392.8	391.8	390.7
110°	445.1	445.7	446.3	446.8	447.5	447.2	445.9	444.8	443.6	442.4	441.8



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	498.8	499.0	499.1	499.3	499.4	498.6	497.2	495.8	494.4	492.9	492.8
115°	572.8	573.1	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8	573.5
117.5°	647.8	648.7	649.5	650.3	651.2	651.7	651.8	651.8	651.8	651.9	652.6
120°	700.5	701.2	701.8	702.4	702.9	703.4	703.7	704.0	704.3	704.6	706.1
122.5°	751.1	752.0	752.8	753.7	754.5	755.3	756.1	756.8	757.6	758.4	759.2
125°	827.0	828.1	829.4	830.5	831.7	832.9	834.1	835.4	836.5	837.8	838.3
127.5°	902.5	903.9	905.3	906.7	908.0	909.5	911.2	912.9	914.5	916.2	916.9
130°	952.0	954.1	956.2	958.3	960.4	962.1	963.2	964.4	965.6	966.8	967.7
132.5°	1003.6	1005.2	1006.9	1008.5	1010.1	1011.6	1013.1	1014.5	1015.9	1017.4	1018.0
135°	1083.8	1084.4	1084.9	1085.6	1086.2	1087.1	1088.2	1089.5	1090.7	1091.9	1092.2
137.5°	1154.5	1155.7	1156.8	1157.9	1159.0	1160.3	1161.5	1162.8	1164.0	1165.3	1164.5
140°	1200.8	1202.8	1205.0	1207.0	1209.2	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1248.1	1249.7	1251.3	1252.9	1254.5	1255.5	1255.8	1256.2	1256.4	1256.7	1256.2
145°	1316.4	1317.6	1318.8	1320.0	1321.2	1322.0	1322.2	1322.5	1322.9	1323.1	1322.2
147.5°	1377.2	1378.9	1380.8	1382.6	1384.4	1385.3	1385.3	1385.3	1385.3	1385.3	1384.4
150°	1415.9	1417.7	1419.5	1421.3	1423.1	1424.0	1424.0	1424.0	1424.0	1424.0	1423.3
152.5°	1453.6	1455.1	1456.7	1458.2	1459.8	1460.4	1459.8	1459.4	1458.9	1458.4	1458.0
155°	1504.7	1506.7	1508.9	1510.9	1513.1	1513.5	1512.3	1511.1	1509.9	1508.7	1508.4
157.5°	1551.2	1552.8	1554.5	1556.2	1557.9	1558.1	1556.8	1555.6	1554.3	1553.1	1552.8
160°	1581.3	1582.5	1583.7	1584.9	1586.1	1585.9	1584.5	1583.0	1581.4	1579.9	1579.9
162.5°	1603.9	1605.8	1607.8	1609.6	1611.6	1611.8	1610.3	1608.7	1607.3	1605.8	1605.5
165°	1636.5	1638.5	1640.7	1642.7	1644.8	1644.9	1643.2	1641.4	1639.6	1637.8	1637.8
167.5°	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1	1663.9
170°	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1	1678.1
172.5°	1688.9	1691.0	1693.1	1695.1	1697.3	1697.4	1695.5	1693.6	1691.8	1690.0	1690.0
175°	1701.0	1703.1	1705.1	1707.3	1709.3	1709.5	1707.7	1705.9	1704.1	1702.4	1702.4
177.5°	1707.4	1709.1	1710.7	1712.4	1714.1	1714.2	1712.8	1711.4	1709.9	1708.5	1708.5
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	993.4	990.4	987.4	982.2	977.8	971.3	969.5	967.2	960.6	954.6	950.1
5°	1054.1	1042.9	1026.5	1011.6	999.5	983.1	973.8	964.0	950.0	937.4	927.1
7.5°	1117.6	1095.6	1070.1	1042.7	1017.1	992.5	972.6	954.8	935.2	916.7	902.2
10°	1168.0	1136.2	1100.8	1062.5	1029.8	998.1	971.4	948.2	922.9	901.0	882.8
12.5°	1225.5	1178.5	1129.5	1083.1	1044.4	1000.3	968.1	938.4	909.8	883.4	863.0
15°	1293.6	1233.9	1175.9	1112.0	1053.2	998.1	959.8	922.5	889.3	862.2	836.1
17.5°	1355.6	1287.9	1211.6	1133.8	1062.8	997.6	944.0	901.7	860.2	827.2	801.1
20°	1390.7	1313.7	1227.3	1146.6	1068.1	995.2	936.5	886.0	841.2	806.2	776.8
22.5°	1420.9	1330.8	1241.4	1155.1	1067.7	989.3	922.7	870.8	822.2	787.9	756.6
25°	1452.3	1344.4	1254.8	1153.5	1056.0	974.7	900.0	841.2	792.6	752.5	720.3
27.5°	1479.2	1343.5	1237.2	1128.2	1037.5	956.1	876.3	813.2	761.7	718.1	685.4
30°	1497.1	1345.4	1218.9	1111.1	1019.6	935.5	858.0	794.5	740.4	696.1	665.2
32.5°	1508.3	1344.3	1202.1	1087.2	991.1	916.9	838.2	772.5	716.8	673.2	643.5
35°	1514.8	1336.1	1173.1	1037.8	945.3	873.0	807.2	739.0	680.6	640.0	606.5
37.5°	1501.8	1318.8	1139.5	990.2	888.9	817.7	762.3	704.3	648.5	603.7	574.8
40°	1481.2	1307.6	1113.4	956.5	850.1	781.5	734.3	677.3	622.2	579.8	552.7
42.5°	1442.0	1284.8	1084.6	919.2	809.8	741.1	697.8	650.1	598.0	558.1	531.1
45°	1346.3	1235.2	1041.5	863.2	750.2	679.2	641.0	606.5	559.3	520.5	497.1
47.5°	1213.5	1160.7	979.1	804.1	688.0	619.7	580.0	552.1	517.7	486.4	464.0
50°	1121.3	1099.4	936.9	763.8	646.6	579.8	541.5	516.3	491.6	460.3	439.8
52.5°	1014.9	1028.4	887.6	721.9	604.3	538.7	502.7	482.7	460.2	434.5	416.6
55°	865.0	914.0	802.5	651.7	541.5	478.9	444.9	427.1	414.1	394.9	379.5
57.5°	724.7	787.1	710.4	579.3	479.8	425.9	393.2	373.8	365.4	355.4	343.3
60°	641.4	703.0	644.7	530.7	438.4	387.0	358.0	341.7	333.3	326.3	316.0
62.5°	567.1	629.5	580.4	481.5	397.6	350.0	324.9	308.9	302.3	298.6	289.9
65°	464.9	518.6	486.0	404.7	339.4	297.4	274.5	263.3	257.3	255.8	250.2
67.5°	378.4	419.3	395.5	335.7	284.3	248.0	228.5	219.0	214.4	213.9	209.7
70°	321.6	359.9	341.7	287.6	243.3	214.7	198.0	189.5	186.7	186.3	184.0
72.5°	277.6	304.3	289.8	244.6	210.4	184.5	172.2	163.4	160.2	160.9	159.3
75°	205.4	225.5	217.0	185.8	158.3	141.4	131.2	125.6	122.8	124.2	122.3
77.5°	147.8	160.5	152.9	131.3	114.3	102.1	94.6	91.1	88.6	88.5	87.7
80°	111.6	119.0	114.9	101.7	87.7	77.5	71.4	69.1	67.7	67.2	66.8
82.5°	79.5	85.8	80.9	71.9	62.3	56.2	52.8	49.7	48.7	49.0	48.4
85°	40.1	42.4	40.6	35.0	31.3	28.4	26.6	25.2	24.3	24.7	23.8
87.5°	18.7	18.3	16.4	14.3	12.9	11.1	10.6	9.3	9.1	9.7	9.9
90°	24.5	20.6	16.8	13.3	10.3	7.3	4.4	1.3	4.4	7.3	10.3
92.5°	47.2	45.0	42.8	40.7	38.6	36.6	34.6	32.5	34.6	36.6	38.6
95°	94.7	92.3	90.0	87.7	85.6	83.6	81.4	79.4	81.4	83.6	85.6
97.5°	152.2	150.5	148.7	147.1	145.6	144.0	142.5	140.9	142.5	144.0	145.6
100°	194.7	193.1	191.7	190.0	188.2	186.5	184.7	182.9	184.7	186.5	188.2
102.5°	241.0	239.1	237.1	235.6	234.5	233.4	232.4	231.3	232.4	233.4	234.5
105°	311.9	309.2	306.6	305.0	304.3	303.7	303.2	302.6	303.2	303.7	304.3
107.5°	389.7	388.6	387.5	386.8	386.5	386.1	385.8	385.4	385.8	386.1	386.5
110°	441.2	440.6	440.0	439.4	438.8	438.2	437.7	437.0	437.7	438.2	438.8



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	492.7	492.6	492.5	492.2	491.9	491.5	491.2	490.8	491.2	491.5	491.9
115°	574.0	574.6	575.2	575.1	574.2	573.3	572.4	571.5	572.4	573.3	574.2
117.5°	653.4	654.2	655.0	655.1	654.5	653.9	653.3	652.7	653.3	653.9	654.5
120°	707.6	709.1	710.6	710.4	708.6	706.9	705.1	703.3	705.1	706.9	708.6
122.5°	759.9	760.7	761.5	761.3	759.9	758.6	757.2	756.0	757.2	758.6	759.9
125°	838.9	839.5	840.1	840.0	839.1	838.2	837.2	836.3	837.2	838.2	839.1
127.5°	917.6	918.2	918.9	918.3	916.3	914.4	912.5	910.6	912.5	914.4	916.3
130°	968.6	969.5	970.4	969.6	967.2	964.8	962.5	960.1	962.5	964.8	967.2
132.5°	1018.7	1019.3	1020.0	1019.1	1016.7	1014.3	1011.9	1009.6	1011.9	1014.3	1016.7
135°	1092.4	1092.8	1093.1	1092.3	1090.5	1088.7	1086.9	1085.1	1086.9	1088.7	1090.5
137.5°	1163.7	1163.0	1162.2	1161.0	1159.6	1158.1	1156.5	1155.0	1156.5	1158.1	1159.6
140°	1210.9	1210.7	1210.3	1209.4	1207.9	1206.5	1205.0	1203.5	1205.0	1206.5	1207.9
142.5°	1255.6	1255.1	1254.5	1253.6	1252.1	1250.5	1249.0	1247.6	1249.0	1250.5	1252.1
145°	1321.3	1320.4	1319.6	1318.8	1318.2	1317.6	1317.1	1316.4	1317.1	1317.6	1318.2
147.5°	1383.6	1382.8	1381.9	1381.0	1379.9	1378.8	1377.7	1376.6	1377.7	1378.8	1379.9
150°	1422.8	1422.2	1421.6	1421.0	1420.4	1419.8	1419.2	1418.6	1419.2	1419.8	1420.4
152.5°	1457.7	1457.3	1457.0	1456.3	1455.5	1454.7	1453.8	1453.0	1453.8	1454.7	1455.5
155°	1508.1	1507.8	1507.5	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3
157.5°	1552.6	1552.4	1552.1	1552.2	1552.6	1552.9	1553.3	1553.6	1553.3	1552.9	1552.6
160°	1579.9	1579.9	1579.9	1580.3	1580.8	1581.4	1582.1	1582.7	1582.1	1581.4	1580.8
162.5°	1605.3	1605.1	1604.8	1605.2	1606.0	1606.8	1607.7	1608.5	1607.7	1606.8	1606.0
165°	1637.8	1637.8	1637.8	1638.3	1639.1	1640.0	1640.9	1641.8	1640.9	1640.0	1639.1
167.5°	1663.7	1663.4	1663.2	1663.7	1664.8	1666.1	1667.2	1668.5	1667.2	1666.1	1664.8
170°	1678.1	1678.1	1678.1	1678.7	1679.9	1681.1	1682.3	1683.5	1682.3	1681.1	1679.9
172.5°	1690.0	1690.0	1690.0	1690.6	1691.8	1692.9	1694.2	1695.3	1694.2	1692.9	1691.8
175°	1702.4	1702.4	1702.4	1702.9	1704.1	1705.3	1706.6	1707.7	1706.6	1705.3	1704.1
177.5°	1708.5	1708.5	1708.5	1709.0	1709.9	1710.9	1711.9	1712.8	1711.9	1710.9	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	947.4	944.9	941.1	935.5	931.0	923.9	923.9	925.1	925.1	924.7	923.9
5°	918.7	911.7	903.3	893.5	883.2	873.0	871.1	867.4	864.6	862.7	860.3
7.5°	888.4	875.9	863.7	850.0	837.5	827.2	819.9	814.0	810.1	806.0	803.1
10°	867.8	852.4	837.9	823.5	807.6	795.0	787.1	781.5	777.3	773.6	771.7
12.5°	843.6	825.9	809.9	796.2	778.8	765.9	758.3	755.7	750.7	742.9	738.8
15°	808.1	791.8	772.6	751.6	743.2	727.3	718.5	714.3	711.4	705.3	703.5
17.5°	777.8	756.3	734.9	719.2	703.6	690.7	685.7	680.6	676.8	671.8	670.4
20°	753.5	734.3	714.7	697.9	681.5	667.5	663.3	659.6	655.9	653.5	651.7
22.5°	728.8	709.7	693.4	677.7	660.3	651.1	646.6	642.5	639.8	638.3	636.4
25°	694.2	677.3	659.2	645.2	631.2	625.1	622.2	619.9	618.0	615.7	615.3
27.5°	663.2	644.9	630.1	617.1	607.0	601.9	599.2	598.1	598.5	599.3	599.9
30°	640.0	623.2	611.1	599.9	590.6	585.9	585.4	585.4	587.3	587.7	588.7
32.5°	618.8	604.9	592.8	581.9	574.9	571.7	573.5	573.5	575.0	576.1	577.8
35°	587.7	575.6	566.2	557.0	550.9	552.2	553.2	554.1	556.4	559.3	561.2
37.5°	558.1	547.6	537.9	530.6	527.8	530.3	532.5	534.5	537.3	539.4	541.3
40°	536.8	528.9	519.6	513.0	514.0	515.4	517.3	519.6	521.9	523.3	525.2
42.5°	517.0	508.7	501.7	496.2	497.6	499.4	500.4	501.7	504.4	506.8	508.0
45°	486.9	480.4	473.9	470.6	471.5	472.4	473.3	474.7	477.1	478.9	479.5
47.5°	453.0	448.4	444.1	440.9	442.4	442.0	443.2	446.2	446.9	448.1	450.7
50°	431.3	427.1	422.0	421.1	421.1	421.1	421.5	425.3	425.3	427.1	429.0
52.5°	407.4	404.7	401.4	399.8	399.0	399.0	401.0	402.9	403.6	406.3	408.1
55°	372.0	369.3	366.5	365.1	364.1	365.1	368.8	369.7	372.0	373.4	374.9
57.5°	335.2	333.1	330.8	330.0	329.8	331.1	333.1	335.9	336.5	340.8	343.0
60°	310.9	307.6	305.8	305.8	304.9	309.1	308.1	312.8	313.7	316.5	319.8
62.5°	285.9	281.5	280.7	280.7	282.0	283.3	284.5	286.6	289.1	292.6	295.2
65°	245.6	243.3	246.5	246.0	245.0	247.9	247.9	250.2	253.0	256.3	261.4
67.5°	207.3	206.2	206.4	206.4	207.9	209.5	210.7	212.8	216.2	219.6	222.9
70°	181.6	183.0	180.7	182.5	184.0	184.4	185.3	188.2	191.9	194.2	198.0
72.5°	156.6	156.5	156.8	157.5	158.9	159.7	160.7	163.9	168.0	170.0	172.9
75°	120.5	119.9	121.4	121.4	123.7	124.7	125.6	127.0	130.7	133.5	135.8
77.5°	87.9	88.5	88.2	89.8	89.2	89.3	92.2	93.6	94.0	99.5	100.8
80°	66.3	67.2	67.7	68.1	68.7	67.7	71.0	72.3	72.3	75.6	77.9
82.5°	47.6	48.2	49.4	49.8	49.9	50.9	51.2	52.2	53.3	54.8	57.8
85°	23.8	25.2	25.7	25.2	25.7	24.7	26.1	26.6	27.1	27.1	27.1
87.5°	10.2	11.1	11.6	12.8	13.1	14.3	14.5	14.0	14.3	15.6	14.4
90°	13.3	16.8	20.6	24.5	28.4	32.3	33.4	34.7	35.8	37.1	38.0
92.5°	40.7	42.8	45.0	47.2	49.4	51.6	52.6	53.5	54.5	55.5	55.7
95°	87.7	90.0	92.3	94.7	97.1	99.5	100.7	101.9	103.1	104.2	104.9
97.5°	147.1	148.7	150.5	152.2	154.0	155.7	157.1	158.5	159.8	161.2	161.8
100°	190.0	191.7	193.1	194.7	196.2	197.7	198.6	199.5	200.4	201.3	202.0
102.5°	235.6	237.1	239.1	241.0	243.0	245.0	245.9	246.8	247.7	248.6	249.0
105°	305.0	306.6	309.2	311.9	314.7	317.4	317.4	317.4	317.4	317.4	317.6
107.5°	386.8	387.5	388.6	389.7	390.7	391.8	392.8	393.8	394.7	395.7	395.9
110°	439.4	440.0	440.6	441.2	441.8	442.4	443.6	444.8	445.9	447.2	447.5



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.2	492.5	492.6	492.7	492.8	492.9	494.4	495.8	497.2	498.6	499.4
115°	575.1	575.2	574.6	574.0	573.5	572.8	573.1	573.5	573.7	574.0	574.0
117.5°	655.1	655.0	654.2	653.4	652.6	651.9	651.8	651.8	651.8	651.7	651.2
120°	710.4	710.6	709.1	707.6	706.1	704.6	704.3	704.0	703.7	703.4	702.9
122.5°	761.3	761.5	760.7	759.9	759.2	758.4	757.6	756.8	756.1	755.3	754.5
125°	840.0	840.1	839.5	838.9	838.3	837.8	836.5	835.4	834.1	832.9	831.7
127.5°	918.3	918.9	918.2	917.6	916.9	916.2	914.5	912.9	911.2	909.5	908.0
130°	969.6	970.4	969.5	968.6	967.7	966.8	965.6	964.4	963.2	962.1	960.4
132.5°	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9	1014.5	1013.1	1011.6	1010.1
135°	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7	1089.5	1088.2	1087.1	1086.2
137.5°	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0	1162.8	1161.5	1160.3	1159.0
140°	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2	1210.9	1210.7	1210.3	1209.2
142.5°	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4	1256.2	1255.8	1255.5	1254.5
145°	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9	1322.5	1322.2	1322.0	1321.2
147.5°	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3	1385.3	1385.3	1385.3	1384.4
150°	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0	1424.0	1424.0	1424.0	1423.1
152.5°	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9	1459.4	1459.8	1460.4	1459.8
155°	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9	1511.1	1512.3	1513.5	1513.1
157.5°	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3	1555.6	1556.8	1558.1	1557.9
160°	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4	1583.0	1584.5	1585.9	1586.1
162.5°	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3	1608.7	1610.3	1611.8	1611.6
165°	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6	1641.4	1643.2	1644.9	1644.8
167.5°	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5
170°	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5
172.5°	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8	1693.6	1695.5	1697.4	1697.3
175°	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1	1705.9	1707.7	1709.5	1709.3
177.5°	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9	1711.4	1712.8	1714.2	1714.1
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	921.3	921.0	923.5	921.7	923.5	921.0	921.3	923.9	924.7	925.1	925.1
5°	857.6	859.0	854.3	854.3	854.3	859.0	857.6	860.3	862.7	864.6	867.4
7.5°	800.8	798.7	798.9	796.4	798.9	798.7	800.8	803.1	806.0	810.1	814.0
10°	766.1	763.3	762.3	762.8	762.3	763.3	766.1	771.7	773.6	777.3	781.5
12.5°	737.3	736.7	730.6	730.7	730.6	736.7	737.3	738.8	742.9	750.7	755.7
15°	703.5	694.6	693.7	696.5	693.7	694.6	703.5	703.5	705.3	711.4	714.3
17.5°	669.6	664.9	665.2	663.8	665.2	664.9	669.6	670.4	671.8	676.8	680.6
20°	651.7	648.9	648.5	645.2	648.5	648.9	651.7	651.7	653.5	655.9	659.6
22.5°	635.3	634.4	634.6	631.0	634.6	634.4	635.3	636.4	638.3	639.8	642.5
25°	614.8	617.2	615.3	615.3	615.3	617.2	614.8	615.3	615.7	618.0	619.9
27.5°	601.0	600.9	599.9	599.9	599.9	600.9	601.0	599.9	599.3	598.5	598.1
30°	590.6	590.0	591.0	591.0	591.0	590.0	590.6	588.7	587.7	587.3	585.4
32.5°	580.1	580.8	580.9	581.3	580.9	580.8	580.1	577.8	576.1	575.0	573.5
35°	563.9	564.4	565.8	564.9	565.8	564.4	563.9	561.2	559.3	556.4	554.1
37.5°	542.1	544.2	543.8	544.5	543.8	544.2	542.1	541.3	539.4	537.3	534.5
40°	525.7	527.1	526.6	526.6	526.6	527.1	525.7	525.2	523.3	521.9	519.6
42.5°	508.8	509.9	508.6	507.9	508.6	509.9	508.8	508.0	506.8	504.4	501.7
45°	481.3	480.4	481.8	479.9	481.8	480.4	481.3	479.5	478.9	477.1	474.7
47.5°	450.5	451.4	451.8	453.2	451.8	451.4	450.5	450.7	448.1	446.9	446.2
50°	430.0	432.7	432.7	432.3	432.7	432.7	430.0	429.0	427.1	425.3	425.3
52.5°	409.7	411.1	413.0	412.9	413.0	411.1	409.7	408.1	406.3	403.6	402.9
55°	378.6	379.5	380.5	380.9	380.5	379.5	378.6	374.9	373.4	372.0	369.7
57.5°	346.3	345.9	348.1	348.8	348.1	345.9	346.3	343.0	340.8	336.5	335.9
60°	323.5	323.5	327.3	328.7	327.3	323.5	323.5	319.8	316.5	313.7	312.8
62.5°	299.3	300.8	304.4	302.5	304.4	300.8	299.3	295.2	292.6	289.1	286.6
65°	263.8	267.5	267.1	268.9	267.1	267.5	263.8	261.4	256.3	253.0	250.2
67.5°	226.7	229.0	232.4	232.6	232.4	229.0	226.7	222.9	219.6	216.2	212.8
70°	201.7	204.0	205.9	207.2	205.9	204.0	201.7	198.0	194.2	191.9	188.2
72.5°	177.4	178.6	183.1	181.1	183.1	178.6	177.4	172.9	170.0	168.0	163.9
75°	139.1	142.4	145.2	143.7	145.2	142.4	139.1	135.8	133.5	130.7	127.0
77.5°	102.9	106.1	107.5	106.3	107.5	106.1	102.9	100.8	99.5	94.0	93.6
80°	81.2	80.8	83.6	83.1	83.6	80.8	81.2	77.9	75.6	72.3	72.3
82.5°	59.6	59.1	60.4	60.7	60.4	59.1	59.6	57.8	54.8	53.3	52.2
85°	29.0	30.3	28.4	28.0	28.4	30.3	29.0	27.1	27.1	27.1	26.6
87.5°	14.4	14.5	14.3	14.0	14.3	14.5	14.4	14.4	15.6	14.3	14.0
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	37.1	35.8	34.7
92.5°	55.4	55.0	54.7	54.3	54.7	55.0	55.4	55.7	55.5	54.5	53.5
95°	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.2	103.1	101.9
97.5°	161.8	161.6	161.5	161.4	161.5	161.6	161.8	161.8	161.2	159.8	158.5
100°	202.6	203.2	203.8	204.4	203.8	203.2	202.6	202.0	201.3	200.4	199.5
102.5°	248.9	248.7	248.6	248.5	248.6	248.7	248.9	249.0	248.6	247.7	246.8
105°	318.3	318.9	319.4	320.0	319.4	318.9	318.3	317.6	317.4	317.4	317.4
107.5°	395.6	395.2	394.8	394.5	394.8	395.2	395.6	395.9	395.7	394.7	393.8
110°	446.8	446.3	445.7	445.1	445.7	446.3	446.8	447.5	447.2	445.9	444.8



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	499.3	499.1	499.0	498.8	499.0	499.1	499.3	499.4	498.6	497.2	495.8
115°	573.7	573.5	573.1	572.8	573.1	573.5	573.7	574.0	574.0	573.7	573.5
117.5°	650.3	649.5	648.7	647.8	648.7	649.5	650.3	651.2	651.7	651.8	651.8
120°	702.4	701.8	701.2	700.5	701.2	701.8	702.4	702.9	703.4	703.7	704.0
122.5°	753.7	752.8	752.0	751.1	752.0	752.8	753.7	754.5	755.3	756.1	756.8
125°	830.5	829.4	828.1	827.0	828.1	829.4	830.5	831.7	832.9	834.1	835.4
127.5°	906.7	905.3	903.9	902.5	903.9	905.3	906.7	908.0	909.5	911.2	912.9
130°	958.3	956.2	954.1	952.0	954.1	956.2	958.3	960.4	962.1	963.2	964.4
132.5°	1008.5	1006.9	1005.2	1003.6	1005.2	1006.9	1008.5	1010.1	1011.6	1013.1	1014.5
135°	1085.6	1084.9	1084.4	1083.8	1084.4	1084.9	1085.6	1086.2	1087.1	1088.2	1089.5
137.5°	1157.9	1156.8	1155.7	1154.5	1155.7	1156.8	1157.9	1159.0	1160.3	1161.5	1162.8
140°	1207.0	1205.0	1202.8	1200.8	1202.8	1205.0	1207.0	1209.2	1210.3	1210.7	1210.9
142.5°	1252.9	1251.3	1249.7	1248.1	1249.7	1251.3	1252.9	1254.5	1255.5	1255.8	1256.2
145°	1320.0	1318.8	1317.6	1316.4	1317.6	1318.8	1320.0	1321.2	1322.0	1322.2	1322.5
147.5°	1382.6	1380.8	1378.9	1377.2	1378.9	1380.8	1382.6	1384.4	1385.3	1385.3	1385.3
150°	1421.3	1419.5	1417.7	1415.9	1417.7	1419.5	1421.3	1423.1	1424.0	1424.0	1424.0
152.5°	1458.2	1456.7	1455.1	1453.6	1455.1	1456.7	1458.2	1459.8	1460.4	1459.8	1459.4
155°	1510.9	1508.9	1506.7	1504.7	1506.7	1508.9	1510.9	1513.1	1513.5	1512.3	1511.1
157.5°	1556.2	1554.5	1552.8	1551.2	1552.8	1554.5	1556.2	1557.9	1558.1	1556.8	1555.6
160°	1584.9	1583.7	1582.5	1581.3	1582.5	1583.7	1584.9	1586.1	1585.9	1584.5	1583.0
162.5°	1609.6	1607.8	1605.8	1603.9	1605.8	1607.8	1609.6	1611.6	1611.8	1610.3	1608.7
165°	1642.7	1640.7	1638.5	1636.5	1638.5	1640.7	1642.7	1644.8	1644.9	1643.2	1641.4
167.5°	1669.7	1667.9	1666.0	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9
170°	1684.4	1682.3	1680.3	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3
172.5°	1695.1	1693.1	1691.0	1688.9	1691.0	1693.1	1695.1	1697.3	1697.4	1695.5	1693.6
175°	1707.3	1705.1	1703.1	1701.0	1703.1	1705.1	1707.3	1709.3	1709.5	1707.7	1705.9
177.5°	1712.4	1710.7	1709.1	1707.4	1709.1	1710.7	1712.4	1714.1	1714.2	1712.8	1711.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	923.9	923.9	931.0	935.5	941.1	944.9	947.4	950.1	954.6	960.6	967.2
5°	871.1	873.0	883.2	893.5	903.3	911.7	918.7	927.1	937.4	950.0	964.0
7.5°	819.9	827.2	837.5	850.0	863.7	875.9	888.4	902.2	916.7	935.2	954.8
10°	787.1	795.0	807.6	823.5	837.9	852.4	867.8	882.8	901.0	922.9	948.2
12.5°	758.3	765.9	778.8	796.2	809.9	825.9	843.6	863.0	883.4	909.8	938.4
15°	718.5	727.3	743.2	751.6	772.6	791.8	808.1	836.1	862.2	889.3	922.5
17.5°	685.7	690.7	703.6	719.2	734.9	756.3	777.8	801.1	827.2	860.2	901.7
20°	663.3	667.5	681.5	697.9	714.7	734.3	753.5	776.8	806.2	841.2	886.0
22.5°	646.6	651.1	660.3	677.7	693.4	709.7	728.8	756.6	787.9	822.2	870.8
25°	622.2	625.1	631.2	645.2	659.2	677.3	694.2	720.3	752.5	792.6	841.2
27.5°	599.2	601.9	607.0	617.1	630.1	644.9	663.2	685.4	718.1	761.7	813.2
30°	585.4	585.9	590.6	599.9	611.1	623.2	640.0	665.2	696.1	740.4	794.5
32.5°	573.5	571.7	574.9	581.9	592.8	604.9	618.8	643.5	673.2	716.8	772.5
35°	553.2	552.2	550.9	557.0	566.2	575.6	587.7	606.5	640.0	680.6	739.0
37.5°	532.5	530.3	527.8	530.6	537.9	547.6	558.1	574.8	603.7	648.5	704.3
40°	517.3	515.4	514.0	513.0	519.6	528.9	536.8	552.7	579.8	622.2	677.3
42.5°	500.4	499.4	497.6	496.2	501.7	508.7	517.0	531.1	558.1	598.0	650.1
45°	473.3	472.4	471.5	470.6	473.9	480.4	486.9	497.1	520.5	559.3	606.5
47.5°	443.2	442.0	442.4	440.9	444.1	448.4	453.0	464.0	486.4	517.7	552.1
50°	421.5	421.1	421.1	421.1	422.0	427.1	431.3	439.8	460.3	491.6	516.3
52.5°	401.0	399.0	399.0	399.8	401.4	404.7	407.4	416.6	434.5	460.2	482.7
55°	368.8	365.1	364.1	365.1	366.5	369.3	372.0	379.5	394.9	414.1	427.1
57.5°	333.1	331.1	329.8	330.0	330.8	333.1	335.2	343.3	355.4	365.4	373.8
60°	308.1	309.1	304.9	305.8	305.8	307.6	310.9	316.0	326.3	333.3	341.7
62.5°	284.5	283.3	282.0	280.7	280.7	281.5	285.9	289.9	298.6	302.3	308.9
65°	247.9	247.9	245.0	246.0	246.5	243.3	245.6	250.2	255.8	257.3	263.3
67.5°	210.7	209.5	207.9	206.4	206.4	206.2	207.3	209.7	213.9	214.4	219.0
70°	185.3	184.4	184.0	182.5	180.7	183.0	181.6	184.0	186.3	186.7	189.5
72.5°	160.7	159.7	158.9	157.5	156.8	156.5	156.6	159.3	160.9	160.2	163.4
75°	125.6	124.7	123.7	121.4	121.4	119.9	120.5	122.3	124.2	122.8	125.6
77.5°	92.2	89.3	89.2	89.8	88.2	88.5	87.9	87.7	88.5	88.6	91.1
80°	71.0	67.7	68.7	68.1	67.7	67.2	66.3	66.8	67.2	67.7	69.1
82.5°	51.2	50.9	49.9	49.8	49.4	48.2	47.6	48.4	49.0	48.7	49.7
85°	26.1	24.7	25.7	25.2	25.7	25.2	23.8	23.8	24.7	24.3	25.2
87.5°	14.5	14.3	13.1	12.8	11.6	11.1	10.2	9.9	9.7	9.1	9.3
90°	33.4	32.3	28.4	24.5	20.6	16.8	13.3	10.3	7.3	4.4	1.3
92.5°	52.6	51.6	49.4	47.2	45.0	42.8	40.7	38.6	36.6	34.6	32.5
95°	100.7	99.5	97.1	94.7	92.3	90.0	87.7	85.6	83.6	81.4	79.4
97.5°	157.1	155.7	154.0	152.2	150.5	148.7	147.1	145.6	144.0	142.5	140.9
100°	198.6	197.7	196.2	194.7	193.1	191.7	190.0	188.2	186.5	184.7	182.9
102.5°	245.9	245.0	243.0	241.0	239.1	237.1	235.6	234.5	233.4	232.4	231.3
105°	317.4	317.4	314.7	311.9	309.2	306.6	305.0	304.3	303.7	303.2	302.6
107.5°	392.8	391.8	390.7	389.7	388.6	387.5	386.8	386.5	386.1	385.8	385.4
110°	443.6	442.4	441.8	441.2	440.6	440.0	439.4	438.8	438.2	437.7	437.0



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.4	492.9	492.8	492.7	492.6	492.5	492.2	491.9	491.5	491.2	490.8
115°	573.1	572.8	573.5	574.0	574.6	575.2	575.1	574.2	573.3	572.4	571.5
117.5°	651.8	651.9	652.6	653.4	654.2	655.0	655.1	654.5	653.9	653.3	652.7
120°	704.3	704.6	706.1	707.6	709.1	710.6	710.4	708.6	706.9	705.1	703.3
122.5°	757.6	758.4	759.2	759.9	760.7	761.5	761.3	759.9	758.6	757.2	756.0
125°	836.5	837.8	838.3	838.9	839.5	840.1	840.0	839.1	838.2	837.2	836.3
127.5°	914.5	916.2	916.9	917.6	918.2	918.9	918.3	916.3	914.4	912.5	910.6
130°	965.6	966.8	967.7	968.6	969.5	970.4	969.6	967.2	964.8	962.5	960.1
132.5°	1015.9	1017.4	1018.0	1018.7	1019.3	1020.0	1019.1	1016.7	1014.3	1011.9	1009.6
135°	1090.7	1091.9	1092.2	1092.4	1092.8	1093.1	1092.3	1090.5	1088.7	1086.9	1085.1
137.5°	1164.0	1165.3	1164.5	1163.7	1163.0	1162.2	1161.0	1159.6	1158.1	1156.5	1155.0
140°	1211.2	1211.6	1211.2	1210.9	1210.7	1210.3	1209.4	1207.9	1206.5	1205.0	1203.5
142.5°	1256.4	1256.7	1256.2	1255.6	1255.1	1254.5	1253.6	1252.1	1250.5	1249.0	1247.6
145°	1322.9	1323.1	1322.2	1321.3	1320.4	1319.6	1318.8	1318.2	1317.6	1317.1	1316.4
147.5°	1385.3	1385.3	1384.4	1383.6	1382.8	1381.9	1381.0	1379.9	1378.8	1377.7	1376.6
150°	1424.0	1424.0	1423.3	1422.8	1422.2	1421.6	1421.0	1420.4	1419.8	1419.2	1418.6
152.5°	1458.9	1458.4	1458.0	1457.7	1457.3	1457.0	1456.3	1455.5	1454.7	1453.8	1453.0
155°	1509.9	1508.7	1508.4	1508.1	1507.8	1507.5	1507.3	1507.3	1507.3	1507.3	1507.3
157.5°	1554.3	1553.1	1552.8	1552.6	1552.4	1552.1	1552.2	1552.6	1552.9	1553.3	1553.6
160°	1581.4	1579.9	1579.9	1579.9	1579.9	1579.9	1580.3	1580.8	1581.4	1582.1	1582.7
162.5°	1607.3	1605.8	1605.5	1605.3	1605.1	1604.8	1605.2	1606.0	1606.8	1607.7	1608.5
165°	1639.6	1637.8	1637.8	1637.8	1637.8	1637.8	1638.3	1639.1	1640.0	1640.9	1641.8
167.5°	1666.0	1664.1	1663.9	1663.7	1663.4	1663.2	1663.7	1664.8	1666.1	1667.2	1668.5
170°	1680.3	1678.1	1678.1	1678.1	1678.1	1678.1	1678.7	1679.9	1681.1	1682.3	1683.5
172.5°	1691.8	1690.0	1690.0	1690.0	1690.0	1690.0	1690.6	1691.8	1692.9	1694.2	1695.3
175°	1704.1	1702.4	1702.4	1702.4	1702.4	1702.4	1702.9	1704.1	1705.3	1706.6	1707.7
177.5°	1709.9	1708.5	1708.5	1708.5	1708.5	1708.5	1709.0	1709.9	1710.9	1711.9	1712.8
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	969.5	971.3	977.8	982.2	987.4	990.4	993.4	995.7	998.6	999.3	1010.2
5°	973.8	983.1	999.5	1011.6	1026.5	1042.9	1054.1	1059.3	1072.7	1084.0	1106.3
7.5°	972.6	992.5	1017.1	1042.7	1070.1	1095.6	1117.6	1143.7	1162.3	1190.3	1217.7
10°	971.4	998.1	1029.8	1062.5	1100.8	1136.2	1168.0	1203.5	1232.9	1271.7	1304.8
12.5°	968.1	1000.3	1044.4	1083.1	1129.5	1178.5	1225.5	1271.0	1297.1	1361.6	1392.1
15°	959.8	998.1	1053.2	1112.0	1175.9	1233.9	1293.6	1341.2	1418.2	1474.7	1510.6
17.5°	944.0	997.6	1062.8	1133.8	1211.6	1287.9	1355.6	1427.8	1509.5	1577.9	1650.7
20°	936.5	995.2	1068.1	1146.6	1227.3	1313.7	1390.7	1477.5	1566.6	1633.9	1727.2
22.5°	922.7	989.3	1067.7	1155.1	1241.4	1330.8	1420.9	1508.5	1611.5	1704.1	1793.0
25°	900.0	974.7	1056.0	1153.5	1254.8	1344.4	1452.3	1568.5	1675.9	1794.9	1883.6
27.5°	876.3	956.1	1037.5	1128.2	1237.2	1343.5	1479.2	1610.5	1741.9	1844.6	1910.2
30°	858.0	935.5	1019.6	1111.1	1218.9	1345.4	1497.1	1640.4	1768.4	1856.5	1893.5
32.5°	838.2	916.9	991.1	1087.2	1202.1	1344.3	1508.3	1658.0	1769.9	1828.5	1821.4
35°	807.2	873.0	945.3	1037.8	1173.1	1336.1	1514.8	1659.6	1728.2	1715.6	1620.3
37.5°	762.3	817.7	888.9	990.2	1139.5	1318.8	1501.8	1610.3	1605.9	1503.2	1365.3
40°	734.3	781.5	850.1	956.5	1113.4	1307.6	1481.2	1551.8	1492.0	1348.6	1183.4
42.5°	697.8	741.1	809.8	919.2	1084.6	1284.8	1442.0	1462.5	1345.6	1180.6	1029.1
45°	641.0	679.2	750.2	863.2	1041.5	1235.2	1346.3	1296.4	1139.1	968.7	853.4
47.5°	580.0	619.7	688.0	804.1	979.1	1160.7	1213.5	1107.3	945.7	807.6	701.8
50°	541.5	579.8	646.6	763.8	936.9	1099.4	1121.3	984.1	835.6	714.3	627.4
52.5°	502.7	538.7	604.3	721.9	887.6	1028.4	1014.9	875.0	738.5	635.1	566.9
55°	444.9	478.9	541.5	651.7	802.5	914.0	865.0	731.6	618.6	538.2	486.4
57.5°	393.2	425.9	479.8	579.3	710.4	787.1	724.7	612.2	522.4	460.6	422.0
60°	358.0	387.0	438.4	530.7	644.7	703.0	641.4	542.0	466.4	416.9	382.4
62.5°	324.9	350.0	397.6	481.5	580.4	629.5	567.1	483.0	418.6	374.7	345.4
65°	274.5	297.4	339.4	404.7	486.0	518.6	464.9	396.8	346.9	314.1	294.5
67.5°	228.5	248.0	284.3	335.7	395.5	419.3	378.4	325.7	288.0	261.8	246.2
70°	198.0	214.7	243.3	287.6	341.7	359.9	321.6	278.2	250.7	229.7	215.2
72.5°	172.2	184.5	210.4	244.6	289.8	304.3	277.6	239.4	213.7	198.0	186.5
75°	131.2	141.4	158.3	185.8	217.0	225.5	205.4	181.6	164.3	153.1	144.3
77.5°	94.6	102.1	114.3	131.3	152.9	160.5	147.8	131.9	119.3	111.7	106.8
80°	71.4	77.5	87.7	101.7	114.9	119.0	111.6	99.4	90.6	86.4	82.1
82.5°	52.8	56.2	62.3	71.9	80.9	85.8	79.5	72.1	67.4	63.6	62.0
85°	26.6	28.4	31.3	35.0	40.6	42.4	40.1	38.3	35.5	33.2	33.2
87.5°	10.6	11.1	12.9	14.3	16.4	18.3	18.7	18.7	19.2	19.0	18.9
90°	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4	34.7
92.5°	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6	53.5
95°	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7	101.9
97.5°	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1	158.5
100°	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6	199.5
102.5°	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9	246.8
105°	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4	317.4
107.5°	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8	393.8
110°	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6	444.8



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4	495.8
115°	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1	573.5
117.5°	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8	651.8
120°	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3	704.0
122.5°	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6	756.8
125°	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5	835.4
127.5°	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5	912.9
130°	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6	964.4
132.5°	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9	1014.5
135°	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7	1089.5
137.5°	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0	1162.8
140°	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2	1210.9
142.5°	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4	1256.2
145°	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9	1322.5
147.5°	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3	1385.3
150°	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0	1424.0
152.5°	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9	1459.4
155°	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9	1511.1
157.5°	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3	1555.6
160°	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4	1583.0
162.5°	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3	1608.7
165°	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6	1641.4
167.5°	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0	1667.9
170°	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3	1682.3
172.5°	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8	1693.6
175°	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1	1705.9
177.5°	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9	1711.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1014.0	1014.3	1018.4	1021.5	1019.9	1021.8	1022.5
5°	1107.8	1124.6	1133.5	1140.0	1140.5	1140.9	1144.7
7.5°	1240.8	1258.8	1272.0	1292.0	1298.0	1304.8	1302.8
10°	1337.9	1364.5	1387.4	1399.5	1412.6	1431.7	1416.4
12.5°	1428.7	1475.9	1510.6	1529.6	1541.9	1545.7	1538.1
15°	1578.3	1639.9	1673.1	1672.1	1714.2	1732.4	1703.9
17.5°	1715.6	1772.5	1818.0	1841.4	1876.3	1884.1	1880.5
20°	1799.7	1861.7	1897.2	1937.3	1955.5	1971.8	1974.7
22.5°	1872.1	1927.8	1965.9	1999.3	2014.6	2022.3	2026.9
25°	1946.7	1990.6	2013.4	2025.1	2029.3	2028.4	2022.3
27.5°	1941.5	1944.9	1919.7	1895.0	1872.9	1847.9	1839.3
30°	1891.1	1851.9	1781.9	1742.2	1683.8	1637.6	1656.3
32.5°	1758.5	1680.5	1601.9	1515.1	1443.3	1422.9	1402.3
35°	1500.8	1363.6	1283.4	1189.9	1152.6	1115.3	1089.6
37.5°	1214.2	1108.0	1012.8	951.7	914.4	890.7	878.0
40°	1049.9	954.2	875.7	826.3	797.8	771.2	767.5
42.5°	918.8	829.8	770.8	731.4	704.1	692.8	684.6
45°	752.5	690.5	650.8	622.8	604.6	597.5	588.2
47.5°	636.9	593.1	563.3	544.2	530.5	525.3	524.5
50°	572.3	535.9	514.0	499.0	488.3	486.4	478.9
52.5°	523.8	492.2	475.1	462.1	454.3	449.1	446.8
55°	454.7	433.6	418.3	410.8	404.7	399.6	399.6
57.5°	397.8	380.3	370.1	363.7	361.9	358.2	355.9
60°	362.7	347.8	339.8	334.2	330.6	331.0	326.8
62.5°	328.3	318.7	311.1	305.5	301.0	301.1	301.4
65°	279.6	272.2	266.5	264.7	261.9	258.6	259.6
67.5°	236.9	230.0	225.6	222.4	221.5	219.7	222.4
70°	206.3	201.2	198.0	195.1	194.2	194.7	197.0
72.5°	178.3	174.7	172.5	171.2	169.2	169.2	170.9
75°	140.1	137.2	135.4	133.9	133.5	133.5	133.5
77.5°	102.9	102.3	101.4	99.3	99.4	100.0	100.0
80°	81.2	79.8	79.4	78.5	77.0	76.1	78.5
82.5°	60.7	59.3	58.9	58.7	56.4	56.3	58.2
85°	32.6	31.3	31.7	31.3	31.3	30.9	30.9
87.5°	18.7	18.6	18.5	18.9	18.6	18.4	19.3
90°	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332175-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)