

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332763-927

Luminaire Tested: **S124DIW-S575D1340U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332763-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1340U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6306.3 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	32	30	29	23				
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20				
4	72	61	54	48	64	55	49	44	45	40	36	35	31	29	25	23	21	17				
5	66	54	47	41	59	49	43	38	40	35	31	31	28	25	23	21	19	15				
6	60	49	41	35	54	44	38	33	36	31	27	28	24	22	21	18	17	13				
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	19	16	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10				
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6006	6006	6006	6006
5°	7074	6022	5315	6022
10°	8470	5996	4786	5996
15°	10021	5935	4395	5935
20°	11159	5874	4046	5874
25°	11339	5782	3805	5782
30°	9648	5695	3730	5695
35°	7418	5552	3730	5552
40°	5782	5385	3800	5385
45°	4820	5134	3863	5134
50°	4243	4828	3995	4828
55°	3887	4460	4155	4460
60°	3643	4130	4350	4130
65°	3391	3761	4510	3761
70°	3099	3397	4612	3397
75°	2770	2991	4557	2991
80°	2320	2450	4412	2450
85°	1714	1769	4224	1769



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	1.1
10°-20°	223.4	3.5
20°-30°	354.3	5.6
30°-40°	394.3	6.3
40°-50°	358.9	5.7
50°-60°	293.3	4.7
60°-70°	209.4	3.3
70°-80°	115.3	1.8
80°-90°	35.4	0.6
90°-100°	47.0	0.7
100°-110°	299.6	4.8
110°-120°	573.1	9.1
120°-130°	727.5	11.5
130°-140°	778.4	12.3
140°-150°	727.9	11.5
150°-160°	587.0	9.3
160°-170°	378.6	6.0
170°-180°	130.5	2.1
0°-30°	650.2	10.3
0°-40°	1044.5	16.6
0°-60°	1696.7	26.9
0°-90°	2056.8	32.6
90°-120°	919.7	14.6
90°-150°	3153.4	50.0
90°-180°	4250.0	67.4
0°-180°	6306.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	744	744	744	744	744	
5°	873	743	656	743	873	89
15°	1199	710	526	710	1199	339
25°	1273	649	427	649	1273	561
35°	753	563	378	563	753	478
45°	422	450	338	450	422	333
55°	276	317	295	317	276	249
65°	178	197	236	197	178	176
75°	89	96	146	96	89	94
85°	18	19	46	19	18	23
90°	31	3	31	3	31	14
95°	30	56	30	56	30	24
105°	293	309	293	309	293	255
115°	582	577	582	577	582	576
125°	818	812	818	812	818	728
135°	1014	1007	1014	1007	1014	781
145°	1167	1161	1167	1161	1167	729
155°	1272	1273	1272	1273	1272	587
165°	1337	1343	1337	1343	1337	378
175°	1366	1374	1366	1374	1366	130
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	791.9	791.6	789.2	788.7	787.0	784.7	784.3	780.3	772.4	768.7	767.7
5°	872.9	879.1	871.0	869.5	868.5	858.4	853.2	847.0	832.8	824.5	818.0
7.5°	969.6	970.3	966.8	963.9	956.1	947.2	933.9	919.7	902.9	885.3	872.0
10°	1033.2	1035.6	1031.7	1031.0	1015.3	1005.4	985.7	969.1	949.9	928.7	909.3
12.5°	1100.3	1096.8	1094.7	1081.6	1078.6	1060.7	1037.8	1020.6	991.1	966.6	940.8
15°	1199.0	1192.2	1187.9	1169.7	1160.8	1135.8	1111.4	1092.7	1054.2	1017.5	989.7
17.5°	1257.0	1263.7	1253.7	1246.3	1223.1	1205.6	1180.7	1141.3	1111.1	1065.6	1030.5
20°	1298.9	1299.5	1294.0	1286.2	1268.0	1245.9	1218.7	1175.6	1139.5	1094.2	1046.1
22.5°	1310.2	1310.3	1308.0	1300.8	1287.0	1269.0	1241.7	1205.6	1162.0	1112.7	1064.6
25°	1273.0	1271.8	1274.5	1282.5	1277.3	1271.8	1256.0	1229.2	1188.5	1136.4	1084.7
27.5°	1134.6	1143.1	1158.8	1178.5	1197.5	1212.0	1216.1	1210.6	1185.3	1142.5	1088.3
30°	1035.0	1045.5	1057.2	1077.0	1115.2	1137.0	1161.1	1179.2	1169.1	1134.9	1084.3
32.5°	925.5	928.1	945.5	968.0	1003.0	1045.0	1083.2	1120.1	1132.3	1114.4	1072.2
35°	752.7	757.0	775.8	798.0	840.8	892.3	949.7	1000.8	1043.1	1060.0	1038.4
37.5°	614.3	626.6	639.8	663.7	701.5	747.8	807.4	873.5	936.5	978.7	985.8
40°	548.7	556.3	565.9	584.1	616.2	661.8	712.9	788.8	855.6	916.1	935.8
42.5°	496.9	501.4	507.2	523.6	548.1	593.4	640.2	706.9	774.0	846.3	879.3
45°	422.2	426.9	436.7	446.3	464.8	496.2	539.7	594.5	662.0	731.7	792.7
47.5°	368.4	371.4	377.2	387.5	403.1	423.9	459.2	505.0	567.6	635.3	700.3
50°	337.8	340.2	344.9	354.2	366.1	384.7	413.6	456.5	505.5	573.6	637.4
52.5°	313.6	314.7	318.1	324.3	333.9	349.4	373.2	408.6	454.2	514.9	578.5
55°	276.2	277.4	280.5	285.1	293.4	303.3	321.5	348.0	387.8	440.5	495.6
57.5°	245.3	246.2	248.8	250.6	257.5	265.5	279.4	298.3	328.5	373.2	422.5
60°	225.6	225.0	228.1	229.7	234.2	241.1	251.8	270.0	296.2	332.2	377.6
62.5°	206.4	205.5	208.1	210.2	212.8	218.6	227.4	241.6	262.9	295.6	334.7
65°	177.5	176.3	177.8	180.3	182.8	185.8	192.3	204.9	221.9	245.3	275.2
67.5°	148.5	149.9	150.1	151.3	152.7	156.9	161.4	170.3	182.3	201.1	226.3
70°	131.3	131.6	132.8	132.8	133.8	137.4	141.2	146.4	158.1	175.4	196.1
72.5°	114.1	115.3	114.9	115.8	116.5	119.0	121.7	126.7	136.7	149.5	166.9
75°	88.8	89.7	89.7	90.0	90.9	91.8	94.0	97.7	104.8	114.3	126.4
77.5°	64.7	64.9	65.3	66.4	66.4	67.9	69.5	72.4	76.0	82.5	89.8
80°	49.9	50.5	50.2	50.9	50.9	52.1	52.7	56.4	57.9	62.3	68.1
82.5°	36.6	37.2	37.2	38.0	38.5	38.7	39.6	41.1	42.6	46.5	48.9
85°	18.5	19.1	18.5	19.1	20.0	20.4	21.2	21.5	22.8	23.8	25.9
87.5°	11.6	12.2	12.1	12.3	12.7	12.8	12.8	12.2	12.9	12.9	13.5
90°	30.8	30.3	29.9	29.5	29.0	28.1	26.7	25.3	24.0	22.6	20.8
92.5°	28.4	28.3	28.2	28.1	28.0	27.3	25.9	24.6	23.1	21.8	20.0
95°	29.8	29.5	29.3	29.1	28.9	28.1	26.7	25.3	24.0	22.6	22.3
97.5°	28.8	28.5	28.3	28.1	27.9	27.6	27.6	27.4	27.3	27.1	52.6
100°	28.8	28.5	28.3	28.1	27.9	29.7	33.6	37.5	41.4	45.2	76.7
102.5°	29.6	29.5	29.5	29.5	29.4	50.3	92.2	134.1	175.9	217.9	222.0
105°	292.9	301.0	309.3	317.5	325.7	328.8	326.8	324.7	322.7	320.6	319.4
107.5°	408.1	407.3	406.4	405.5	404.6	403.7	402.7	401.7	400.7	399.7	398.2
110°	458.3	457.6	456.9	456.2	455.5	455.0	454.5	454.1	453.6	453.1	451.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	508.4	507.6	506.7	505.8	504.9	504.5	504.6	504.7	504.9	504.9	504.3
115°	581.5	581.5	581.5	581.5	581.5	581.3	580.9	580.4	580.0	579.5	579.7
117.5°	655.9	656.1	656.2	656.2	656.3	656.4	656.5	656.6	656.7	656.8	656.2
120°	702.8	703.3	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8	703.1
122.5°	748.8	749.3	749.7	750.2	750.7	750.8	750.5	750.2	750.0	749.6	749.3
125°	817.9	817.7	817.5	817.2	817.0	816.5	815.9	815.2	814.4	813.8	814.2
127.5°	878.5	878.7	878.8	879.1	879.2	879.4	879.6	879.7	879.8	880.0	878.9
130°	919.6	919.6	919.6	919.6	919.6	919.5	919.2	919.0	918.9	918.6	917.9
132.5°	957.4	957.6	957.8	958.0	958.1	958.1	957.9	957.7	957.4	957.2	956.3
135°	1014.2	1013.7	1013.2	1012.8	1012.3	1011.9	1011.4	1011.0	1010.5	1010.0	1009.2
137.5°	1062.6	1062.8	1063.0	1063.0	1063.2	1063.0	1062.5	1062.0	1061.5	1061.0	1060.0
140°	1096.4	1096.1	1095.9	1095.7	1095.4	1095.0	1094.3	1093.6	1092.9	1092.3	1091.8
142.5°	1124.3	1124.3	1124.2	1124.2	1124.1	1123.9	1123.3	1122.8	1122.4	1121.8	1121.6
145°	1167.3	1166.8	1166.3	1165.9	1165.5	1165.1	1164.8	1164.6	1164.4	1164.2	1164.2
147.5°	1202.8	1202.5	1202.4	1202.1	1201.9	1201.7	1201.5	1201.3	1201.1	1200.9	1201.2
150°	1225.8	1225.6	1225.3	1225.1	1224.9	1224.8	1224.8	1224.8	1224.8	1224.8	1225.0
152.5°	1245.5	1245.7	1245.8	1245.9	1246.1	1245.9	1245.6	1245.2	1244.9	1244.5	1244.9
155°	1272.1	1272.7	1273.4	1274.1	1274.8	1274.7	1273.7	1272.9	1271.9	1271.1	1271.7
157.5°	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3	1295.1
160°	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1	1309.2
162.5°	1320.6	1322.1	1323.7	1325.2	1326.7	1326.8	1325.5	1324.1	1322.7	1321.4	1321.6
165°	1336.8	1338.9	1340.9	1343.0	1345.0	1345.1	1343.3	1341.5	1339.7	1337.8	1337.8
167.5°	1348.9	1351.2	1353.4	1355.7	1358.0	1358.2	1356.1	1354.2	1352.2	1350.1	1350.3
170°	1356.3	1358.6	1360.9	1363.2	1365.4	1365.6	1363.8	1362.0	1360.2	1358.4	1358.1
172.5°	1360.4	1362.9	1365.3	1367.8	1370.3	1370.6	1368.8	1366.9	1365.1	1363.3	1363.0
175°	1365.6	1368.3	1371.0	1373.8	1376.5	1376.9	1374.8	1372.8	1370.7	1368.7	1368.4
177.5°	1368.8	1371.0	1373.2	1375.4	1377.6	1378.0	1376.5	1375.1	1373.6	1372.1	1371.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	767.9	764.5	762.1	760.1	754.6	751.5	749.0	745.5	741.6	737.4	732.2
5°	811.6	801.1	793.4	781.6	770.6	761.3	751.8	743.1	732.6	721.3	712.9
7.5°	857.4	841.8	821.8	804.5	785.0	768.0	752.9	737.4	721.2	705.5	691.2
10°	886.5	866.4	844.2	818.0	793.4	771.5	751.1	731.4	712.3	693.2	676.8
12.5°	917.7	892.8	860.0	829.3	801.8	772.5	747.9	723.7	700.7	680.6	661.6
15°	959.8	923.8	885.8	844.9	808.5	774.3	740.7	710.1	684.3	657.7	639.3
17.5°	985.6	941.0	897.7	854.8	810.8	767.6	731.4	696.2	663.8	637.5	614.2
20°	1002.7	958.3	904.4	861.5	809.1	764.7	722.8	683.7	649.7	621.7	597.6
22.5°	1017.5	966.1	912.2	855.8	803.7	756.5	710.7	671.3	636.7	607.1	584.1
25°	1025.5	966.6	908.0	851.9	792.7	737.0	695.4	649.1	612.1	581.0	556.3
27.5°	1026.4	963.4	897.1	834.8	773.7	721.8	669.2	627.9	589.5	556.6	532.9
30°	1023.6	958.0	886.8	819.3	758.0	701.5	655.9	610.9	571.7	539.1	514.4
32.5°	1014.9	946.6	873.5	802.0	738.5	683.3	636.2	593.4	555.2	523.1	497.2
35°	990.0	922.5	844.5	770.2	705.2	649.4	606.9	563.4	525.2	494.7	469.8
37.5°	951.0	889.9	810.7	733.8	669.9	613.9	571.7	532.5	498.0	467.0	441.4
40°	917.0	863.3	783.8	708.9	639.8	586.5	547.1	511.0	476.8	447.5	423.2
42.5°	877.7	831.0	757.6	678.3	611.7	558.2	519.8	487.4	455.1	428.1	403.7
45°	807.9	777.1	708.0	634.6	565.3	514.8	478.1	449.7	422.6	396.1	375.7
47.5°	727.5	712.2	654.0	584.4	518.6	468.7	437.0	410.7	387.0	364.5	346.6
50°	673.4	666.1	615.8	548.7	485.8	438.9	406.9	384.4	364.0	344.3	327.3
52.5°	620.2	620.0	574.6	513.1	455.0	409.8	378.0	357.0	339.4	323.3	308.1
55°	538.8	547.4	512.0	457.1	405.0	364.3	335.6	316.9	304.5	291.3	279.9
57.5°	464.0	478.3	449.1	400.8	357.3	319.8	294.9	280.7	267.6	259.6	251.3
60°	415.2	428.7	405.9	365.3	324.2	292.2	268.5	255.8	244.4	238.8	233.0
62.5°	371.8	383.9	366.9	329.2	293.7	262.8	242.8	230.7	223.0	216.9	213.0
65°	309.7	320.0	305.5	278.1	247.5	222.8	206.5	196.9	189.6	187.1	182.8
67.5°	250.4	259.7	251.8	228.5	204.1	185.4	172.6	163.4	159.1	156.9	153.8
70°	215.2	224.4	216.0	195.7	176.9	161.2	149.2	143.9	139.3	138.4	134.1
72.5°	185.3	191.6	183.2	167.4	151.3	138.0	128.7	123.3	120.8	119.1	116.8
75°	139.0	144.6	139.0	126.7	115.3	106.0	98.0	95.9	93.1	92.1	90.6
77.5°	98.4	103.2	98.9	91.3	82.7	75.6	71.3	68.5	67.9	66.3	67.0
80°	75.2	78.3	74.3	69.1	62.3	57.4	54.3	52.7	50.9	50.2	51.5
82.5°	54.0	55.4	53.3	49.8	44.8	41.5	39.5	37.6	37.3	37.4	37.4
85°	28.0	27.7	27.4	24.3	22.8	20.7	19.4	19.1	18.8	19.4	20.0
87.5°	13.2	13.1	12.4	11.0	9.7	8.6	7.8	7.1	7.8	8.6	9.3
90°	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	18.1	16.3	14.5	13.5	13.4	13.2	13.1	12.9	13.1	13.2	13.4
95°	22.2	21.9	21.7	25.4	33.2	41.0	48.7	56.5	48.7	41.0	33.2
97.5°	78.1	103.5	129.0	139.3	134.5	129.7	124.8	120.0	124.8	129.7	134.5
100°	108.2	139.7	171.3	185.0	180.9	176.7	172.6	168.5	172.6	176.7	180.9
102.5°	226.1	230.1	234.2	234.8	231.8	228.8	225.8	222.8	225.8	228.8	231.8
105°	318.3	317.2	316.0	314.7	313.4	312.0	310.6	309.3	310.6	312.0	313.4
107.5°	396.6	395.1	393.5	392.4	391.7	391.0	390.3	389.6	390.3	391.0	391.7
110°	450.4	449.0	447.7	446.6	445.9	445.3	444.6	443.9	444.6	445.3	445.9





TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.7	503.0	502.3	501.5	500.2	499.0	497.7	496.5	497.7	499.0	500.2
115°	580.0	580.2	580.4	580.2	579.5	578.8	578.1	577.4	578.1	578.8	579.5
117.5°	655.8	655.3	654.7	654.0	653.2	652.2	651.3	650.4	651.3	652.2	653.2
120°	703.3	703.5	703.7	703.4	702.5	701.6	700.6	699.7	700.6	701.6	702.5
122.5°	749.0	748.7	748.4	748.0	747.4	746.9	746.3	745.8	746.3	746.9	747.4
125°	814.7	815.2	815.6	815.4	814.4	813.6	812.6	811.7	812.6	813.6	814.4
127.5°	877.8	876.8	875.8	875.1	874.9	874.6	874.4	874.2	874.4	874.6	874.9
130°	917.2	916.6	915.8	915.4	915.1	915.0	914.7	914.5	914.7	915.0	915.1
132.5°	955.5	954.7	953.8	953.1	952.7	952.3	951.9	951.5	951.9	952.3	952.7
135°	1008.2	1007.3	1006.4	1006.1	1006.3	1006.5	1006.7	1006.9	1006.7	1006.5	1006.3
137.5°	1059.0	1058.0	1057.0	1056.5	1056.4	1056.2	1056.1	1056.1	1056.1	1056.2	1056.4
140°	1091.3	1090.8	1090.4	1090.0	1089.5	1089.0	1088.6	1088.1	1088.6	1089.0	1089.5
142.5°	1121.3	1121.0	1120.7	1120.2	1119.4	1118.6	1117.7	1116.9	1117.7	1118.6	1119.4
145°	1164.2	1164.2	1164.2	1163.8	1163.2	1162.4	1161.7	1161.1	1161.7	1162.4	1163.2
147.5°	1201.4	1201.7	1201.9	1201.3	1200.1	1198.8	1197.5	1196.2	1197.5	1198.8	1200.1
150°	1225.3	1225.5	1225.7	1225.3	1224.5	1223.5	1222.7	1221.7	1222.7	1223.5	1224.5
152.5°	1245.3	1245.8	1246.2	1246.0	1245.2	1244.5	1243.8	1243.1	1243.8	1244.5	1245.2
155°	1272.4	1273.1	1273.7	1274.0	1273.7	1273.5	1273.3	1273.1	1273.3	1273.5	1273.7
157.5°	1295.8	1296.6	1297.4	1297.8	1297.9	1298.1	1298.2	1298.4	1298.2	1298.1	1297.9
160°	1309.5	1309.7	1310.0	1310.4	1311.1	1311.8	1312.5	1313.1	1312.5	1311.8	1311.1
162.5°	1321.8	1322.1	1322.3	1322.9	1323.7	1324.6	1325.4	1326.3	1325.4	1324.6	1323.7
165°	1337.8	1337.8	1337.8	1338.4	1339.5	1340.7	1341.8	1343.0	1341.8	1340.7	1339.5
167.5°	1350.4	1350.6	1350.7	1351.4	1352.6	1353.8	1354.9	1356.1	1354.9	1353.8	1352.6
170°	1357.9	1357.6	1357.5	1358.0	1359.4	1360.7	1362.2	1363.5	1362.2	1360.7	1359.4
172.5°	1362.9	1362.6	1362.4	1362.9	1364.3	1365.7	1367.1	1368.4	1367.1	1365.7	1364.3
175°	1368.2	1367.9	1367.7	1368.3	1369.7	1371.0	1372.4	1373.8	1372.4	1371.0	1369.7
177.5°	1371.4	1371.0	1370.6	1371.1	1372.4	1373.6	1375.0	1376.3	1375.0	1373.6	1372.4
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	729.8	727.5	724.3	719.9	716.2	712.3	711.2	709.8	712.7	710.3	709.6
5°	705.8	699.3	691.0	681.5	676.0	667.9	666.4	663.3	660.2	659.9	656.8
7.5°	680.5	671.0	660.1	650.4	641.4	632.6	626.9	625.7	621.1	618.5	615.4
10°	664.2	652.5	639.8	630.7	620.1	610.9	604.4	600.7	597.6	594.2	591.2
12.5°	645.0	632.6	622.1	612.1	599.7	592.6	582.0	575.6	575.0	575.0	567.0
15°	622.6	610.3	594.2	580.1	573.3	559.8	553.9	546.4	541.9	537.3	533.5
17.5°	597.1	581.7	569.2	552.9	540.0	529.2	521.4	517.0	510.1	503.5	498.8
20°	581.0	564.7	551.4	534.2	520.0	506.8	500.3	494.1	488.9	483.3	478.1
22.5°	564.7	547.6	531.5	514.7	501.5	487.5	481.3	472.9	467.9	464.8	459.5
25°	539.1	520.6	502.1	486.1	472.5	460.2	451.9	445.4	439.8	437.4	434.0
27.5°	511.2	492.8	475.0	456.8	441.4	432.5	425.8	420.9	417.7	414.5	412.9
30°	493.5	474.4	455.3	438.3	424.1	415.2	409.0	405.6	403.1	401.6	400.1
32.5°	475.5	456.6	436.5	421.0	408.4	400.4	395.7	392.3	391.1	390.5	390.0
35°	446.6	427.5	409.0	395.1	383.1	380.0	376.0	374.1	373.6	375.7	376.7
37.5°	418.7	400.9	383.9	370.5	362.6	358.1	356.7	356.8	359.0	360.9	363.1
40°	400.7	383.4	367.4	355.7	348.3	345.5	344.9	346.4	348.9	351.1	353.6
42.5°	383.2	366.1	351.6	340.6	335.5	333.0	333.4	334.9	338.3	341.0	344.7
45°	356.0	341.8	327.6	318.7	314.4	315.0	315.0	317.7	321.2	325.2	329.2
47.5°	330.4	316.1	304.4	296.9	294.7	294.1	295.9	299.5	304.4	309.3	315.0
50°	313.1	299.6	289.4	282.7	280.2	281.1	283.6	286.9	292.8	299.0	304.8
52.5°	295.6	283.3	273.9	267.6	265.9	267.5	270.0	275.4	280.5	287.2	294.2
55°	268.5	258.0	250.6	246.0	245.3	246.3	249.1	254.9	262.3	270.6	277.4
57.5°	241.4	232.7	225.9	222.7	223.0	223.9	228.4	235.4	243.3	252.2	260.9
60°	223.2	215.2	209.6	207.2	207.5	209.3	214.8	221.3	231.2	239.8	249.1
62.5°	205.9	198.8	193.5	191.3	190.9	195.0	200.3	207.0	216.9	226.5	236.5
65°	178.2	172.6	168.3	167.1	167.9	171.0	177.8	186.8	195.1	205.3	215.8
67.5°	151.0	146.5	143.5	144.1	145.2	149.7	155.4	163.1	172.5	183.1	193.5
70°	133.8	129.4	127.0	127.3	129.1	134.7	139.7	147.3	157.5	168.3	176.9
72.5°	116.1	113.2	111.0	112.3	114.1	118.0	124.1	131.8	140.8	150.8	159.9
75°	89.0	89.0	87.9	88.8	91.6	95.2	99.9	107.9	116.8	124.8	132.2
77.5°	66.1	65.4	66.2	67.3	68.9	73.3	78.6	84.4	91.0	99.1	105.2
80°	50.5	50.9	52.4	54.3	54.9	58.2	63.8	69.1	74.3	81.0	86.9
82.5°	37.9	38.3	39.1	41.4	42.1	45.7	49.3	54.5	59.3	63.8	68.7
85°	20.7	20.7	22.2	23.1	24.6	27.1	29.3	32.4	36.7	39.8	44.4
87.5°	10.5	10.9	12.3	13.2	14.3	15.8	16.6	19.6	20.9	22.4	24.8
90°	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3	26.7	28.1	29.0
92.5°	13.5	14.5	16.3	18.1	20.0	21.8	23.1	24.6	25.9	27.3	28.0
95°	25.4	21.7	21.9	22.2	22.3	22.6	24.0	25.3	26.7	28.1	28.9
97.5°	139.3	129.0	103.5	78.1	52.6	27.1	27.3	27.4	27.6	27.6	27.9
100°	185.0	171.3	139.7	108.2	76.7	45.2	41.4	37.5	33.6	29.7	27.9
102.5°	234.8	234.2	230.1	226.1	222.0	217.9	175.9	134.1	92.2	50.3	29.4
105°	314.7	316.0	317.2	318.3	319.4	320.6	322.7	324.7	326.8	328.8	325.7
107.5°	392.4	393.5	395.1	396.6	398.2	399.7	400.7	401.7	402.7	403.7	404.6
110°	446.6	447.7	449.0	450.4	451.8	453.1	453.6	454.1	454.5	455.0	455.5



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	501.5	502.3	503.0	503.7	504.3	504.9	504.9	504.7	504.6	504.5	504.9
115°	580.2	580.4	580.2	580.0	579.7	579.5	580.0	580.4	580.9	581.3	581.5
117.5°	654.0	654.7	655.3	655.8	656.2	656.8	656.7	656.6	656.5	656.4	656.3
120°	703.4	703.7	703.5	703.3	703.1	702.8	703.3	703.7	704.2	704.6	704.6
122.5°	748.0	748.4	748.7	749.0	749.3	749.6	750.0	750.2	750.5	750.8	750.7
125°	815.4	815.6	815.2	814.7	814.2	813.8	814.4	815.2	815.9	816.5	817.0
127.5°	875.1	875.8	876.8	877.8	878.9	880.0	879.8	879.7	879.6	879.4	879.2
130°	915.4	915.8	916.6	917.2	917.9	918.6	918.9	919.0	919.2	919.5	919.6
132.5°	953.1	953.8	954.7	955.5	956.3	957.2	957.4	957.7	957.9	958.1	958.1
135°	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5	1011.0	1011.4	1011.9	1012.3
137.5°	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5	1062.0	1062.5	1063.0	1063.2
140°	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9	1093.6	1094.3	1095.0	1095.4
142.5°	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4	1122.8	1123.3	1123.9	1124.1
145°	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4	1164.6	1164.8	1165.1	1165.5
147.5°	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1	1201.3	1201.5	1201.7	1201.9
150°	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8	1224.8	1224.8	1224.8	1224.9
152.5°	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9	1245.2	1245.6	1245.9	1246.1
155°	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9	1272.9	1273.7	1274.7	1274.8
157.5°	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0
160°	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5
162.5°	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7	1324.1	1325.5	1326.8	1326.7
165°	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7	1341.5	1343.3	1345.1	1345.0
167.5°	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2	1354.2	1356.1	1358.2	1358.0
170°	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2	1362.0	1363.8	1365.6	1365.4
172.5°	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1	1366.9	1368.8	1370.6	1370.3
175°	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7	1372.8	1374.8	1376.9	1376.5
177.5°	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6	1375.1	1376.5	1378.0	1377.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	709.0	708.5	706.8	706.5	706.8	708.5	709.0	709.6	710.3	712.7	709.8
5°	655.0	653.5	652.5	655.9	652.5	653.5	655.0	656.8	659.9	660.2	663.3
7.5°	614.3	613.0	610.3	609.4	610.3	613.0	614.3	615.4	618.5	621.1	625.7
10°	588.1	586.8	584.4	583.8	584.4	586.8	588.1	591.2	594.2	597.6	600.7
12.5°	562.9	560.5	560.0	560.6	560.0	560.5	562.9	567.0	575.0	575.0	575.6
15°	529.5	528.3	524.9	525.9	524.9	528.3	529.5	533.5	537.3	541.9	546.4
17.5°	496.6	495.1	491.0	494.6	491.0	495.1	496.6	498.8	503.5	510.1	517.0
20°	475.9	473.4	471.3	471.0	471.3	473.4	475.9	478.1	483.3	488.9	494.1
22.5°	456.1	453.9	453.8	451.7	453.8	453.9	456.1	459.5	464.8	467.9	472.9
25°	431.5	429.4	428.7	427.2	428.7	429.4	431.5	434.0	437.4	439.8	445.4
27.5°	412.6	411.5	410.4	410.9	410.4	411.5	412.6	412.9	414.5	417.7	420.9
30°	401.0	400.7	400.1	400.1	400.1	400.7	401.0	400.1	401.6	403.1	405.6
32.5°	391.4	391.3	391.7	391.7	391.7	391.3	391.4	390.0	390.5	391.1	392.3
35°	377.9	378.8	379.5	378.5	379.5	378.8	377.9	376.7	375.7	373.6	374.1
37.5°	365.7	366.6	367.5	368.5	367.5	366.6	365.7	363.1	360.9	359.0	356.8
40°	356.3	358.5	359.1	360.6	359.1	358.5	356.3	353.6	351.1	348.9	346.4
42.5°	347.5	349.8	351.4	351.7	351.4	349.8	347.5	344.7	341.0	338.3	334.9
45°	333.8	336.3	338.4	338.4	338.4	336.3	333.8	329.2	325.2	321.2	317.7
47.5°	319.7	323.3	325.4	326.0	325.4	323.3	319.7	315.0	309.3	304.4	299.5
50°	310.1	314.4	316.6	318.1	316.6	314.4	310.1	304.8	299.0	292.8	286.9
52.5°	300.7	305.0	307.9	308.7	307.9	305.0	300.7	294.2	287.2	280.5	275.4
55°	284.5	290.7	294.1	295.2	294.1	290.7	284.5	277.4	270.6	262.3	254.9
57.5°	269.2	274.9	278.8	279.7	278.8	274.9	269.2	260.9	252.2	243.3	235.4
60°	257.4	263.6	268.5	269.4	268.5	263.6	257.4	249.1	239.8	231.2	221.3
62.5°	245.3	251.7	256.1	258.6	256.1	251.7	245.3	236.5	226.5	216.9	207.0
65°	224.4	230.8	235.2	236.1	235.2	230.8	224.4	215.8	205.3	195.1	186.8
67.5°	201.6	208.0	210.9	212.7	210.9	208.0	201.6	193.5	183.1	172.5	163.1
70°	185.5	190.8	193.8	195.4	193.8	190.8	185.5	176.9	168.3	157.5	147.3
72.5°	167.3	172.8	176.3	176.7	176.3	172.8	167.3	159.9	150.8	140.8	131.8
75°	139.3	144.3	146.1	146.1	146.1	144.3	139.3	132.2	124.8	116.8	107.9
77.5°	110.3	112.8	115.2	115.7	115.2	112.8	110.3	105.2	99.1	91.0	84.4
80°	91.6	93.1	94.9	94.9	94.9	93.1	91.6	86.9	81.0	74.3	69.1
82.5°	72.3	73.6	75.4	75.2	75.4	73.6	72.3	68.7	63.8	59.3	54.5
85°	43.7	46.6	46.3	45.6	46.3	46.6	43.7	44.4	39.8	36.7	32.4
87.5°	25.6	26.0	26.8	27.4	26.8	26.0	25.6	24.8	22.4	20.9	19.6
90°	29.5	29.9	30.3	30.8	30.3	29.9	29.5	29.0	28.1	26.7	25.3
92.5°	28.1	28.2	28.3	28.4	28.3	28.2	28.1	28.0	27.3	25.9	24.6
95°	29.1	29.3	29.5	29.8	29.5	29.3	29.1	28.9	28.1	26.7	25.3
97.5°	28.1	28.3	28.5	28.8	28.5	28.3	28.1	27.9	27.6	27.6	27.4
100°	28.1	28.3	28.5	28.8	28.5	28.3	28.1	27.9	29.7	33.6	37.5
102.5°	29.5	29.5	29.5	29.6	29.5	29.5	29.5	29.4	50.3	92.2	134.1
105°	317.5	309.3	301.0	292.9	301.0	309.3	317.5	325.7	328.8	326.8	324.7
107.5°	405.5	406.4	407.3	408.1	407.3	406.4	405.5	404.6	403.7	402.7	401.7
110°	456.2	456.9	457.6	458.3	457.6	456.9	456.2	455.5	455.0	454.5	454.1



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	505.8	506.7	507.6	508.4	507.6	506.7	505.8	504.9	504.5	504.6	504.7
115°	581.5	581.5	581.5	581.5	581.5	581.5	581.5	581.5	581.3	580.9	580.4
117.5°	656.2	656.2	656.1	655.9	656.1	656.2	656.2	656.3	656.4	656.5	656.6
120°	704.2	703.7	703.3	702.8	703.3	703.7	704.2	704.6	704.6	704.2	703.7
122.5°	750.2	749.7	749.3	748.8	749.3	749.7	750.2	750.7	750.8	750.5	750.2
125°	817.2	817.5	817.7	817.9	817.7	817.5	817.2	817.0	816.5	815.9	815.2
127.5°	879.1	878.8	878.7	878.5	878.7	878.8	879.1	879.2	879.4	879.6	879.7
130°	919.6	919.6	919.6	919.6	919.6	919.6	919.6	919.6	919.5	919.2	919.0
132.5°	958.0	957.8	957.6	957.4	957.6	957.8	958.0	958.1	958.1	957.9	957.7
135°	1012.8	1013.2	1013.7	1014.2	1013.7	1013.2	1012.8	1012.3	1011.9	1011.4	1011.0
137.5°	1063.0	1063.0	1062.8	1062.6	1062.8	1063.0	1063.0	1063.2	1063.0	1062.5	1062.0
140°	1095.7	1095.9	1096.1	1096.4	1096.1	1095.9	1095.7	1095.4	1095.0	1094.3	1093.6
142.5°	1124.2	1124.2	1124.3	1124.3	1124.3	1124.2	1124.2	1124.1	1123.9	1123.3	1122.8
145°	1165.9	1166.3	1166.8	1167.3	1166.8	1166.3	1165.9	1165.5	1165.1	1164.8	1164.6
147.5°	1202.1	1202.4	1202.5	1202.8	1202.5	1202.4	1202.1	1201.9	1201.7	1201.5	1201.3
150°	1225.1	1225.3	1225.6	1225.8	1225.6	1225.3	1225.1	1224.9	1224.8	1224.8	1224.8
152.5°	1245.9	1245.8	1245.7	1245.5	1245.7	1245.8	1245.9	1246.1	1245.9	1245.6	1245.2
155°	1274.1	1273.4	1272.7	1272.1	1272.7	1273.4	1274.1	1274.8	1274.7	1273.7	1272.9
157.5°	1297.8	1296.6	1295.5	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6
160°	1313.1	1311.8	1310.4	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8
162.5°	1325.2	1323.7	1322.1	1320.6	1322.1	1323.7	1325.2	1326.7	1326.8	1325.5	1324.1
165°	1343.0	1340.9	1338.9	1336.8	1338.9	1340.9	1343.0	1345.0	1345.1	1343.3	1341.5
167.5°	1355.7	1353.4	1351.2	1348.9	1351.2	1353.4	1355.7	1358.0	1358.2	1356.1	1354.2
170°	1363.2	1360.9	1358.6	1356.3	1358.6	1360.9	1363.2	1365.4	1365.6	1363.8	1362.0
172.5°	1367.8	1365.3	1362.9	1360.4	1362.9	1365.3	1367.8	1370.3	1370.6	1368.8	1366.9
175°	1373.8	1371.0	1368.3	1365.6	1368.3	1371.0	1373.8	1376.5	1376.9	1374.8	1372.8
177.5°	1375.4	1373.2	1371.0	1368.8	1371.0	1373.2	1375.4	1377.6	1378.0	1376.5	1375.1
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	711.2	712.3	716.2	719.9	724.3	727.5	729.8	732.2	737.4	741.6	745.5
5°	666.4	667.9	676.0	681.5	691.0	699.3	705.8	712.9	721.3	732.6	743.1
7.5°	626.9	632.6	641.4	650.4	660.1	671.0	680.5	691.2	705.5	721.2	737.4
10°	604.4	610.9	620.1	630.7	639.8	652.5	664.2	676.8	693.2	712.3	731.4
12.5°	582.0	592.6	599.7	612.1	622.1	632.6	645.0	661.6	680.6	700.7	723.7
15°	553.9	559.8	573.3	580.1	594.2	610.3	622.6	639.3	657.7	684.3	710.1
17.5°	521.4	529.2	540.0	552.9	569.2	581.7	597.1	614.2	637.5	663.8	696.2
20°	500.3	506.8	520.0	534.2	551.4	564.7	581.0	597.6	621.7	649.7	683.7
22.5°	481.3	487.5	501.5	514.7	531.5	547.6	564.7	584.1	607.1	636.7	671.3
25°	451.9	460.2	472.5	486.1	502.1	520.6	539.1	556.3	581.0	612.1	649.1
27.5°	425.8	432.5	441.4	456.8	475.0	492.8	511.2	532.9	556.6	589.5	627.9
30°	409.0	415.2	424.1	438.3	455.3	474.4	493.5	514.4	539.1	571.7	610.9
32.5°	395.7	400.4	408.4	421.0	436.5	456.6	475.5	497.2	523.1	555.2	593.4
35°	376.0	380.0	383.1	395.1	409.0	427.5	446.6	469.8	494.7	525.2	563.4
37.5°	356.7	358.1	362.6	370.5	383.9	400.9	418.7	441.4	467.0	498.0	532.5
40°	344.9	345.5	348.3	355.7	367.4	383.4	400.7	423.2	447.5	476.8	511.0
42.5°	333.4	333.0	335.5	340.6	351.6	366.1	383.2	403.7	428.1	455.1	487.4
45°	315.0	315.0	314.4	318.7	327.6	341.8	356.0	375.7	396.1	422.6	449.7
47.5°	295.9	294.1	294.7	296.9	304.4	316.1	330.4	346.6	364.5	387.0	410.7
50°	283.6	281.1	280.2	282.7	289.4	299.6	313.1	327.3	344.3	364.0	384.4
52.5°	270.0	267.5	265.9	267.6	273.9	283.3	295.6	308.1	323.3	339.4	357.0
55°	249.1	246.3	245.3	246.0	250.6	258.0	268.5	279.9	291.3	304.5	316.9
57.5°	228.4	223.9	223.0	222.7	225.9	232.7	241.4	251.3	259.6	267.6	280.7
60°	214.8	209.3	207.5	207.2	209.6	215.2	223.2	233.0	238.8	244.4	255.8
62.5°	200.3	195.0	190.9	191.3	193.5	198.8	205.9	213.0	216.9	223.0	230.7
65°	177.8	171.0	167.9	167.1	168.3	172.6	178.2	182.8	187.1	189.6	196.9
67.5°	155.4	149.7	145.2	144.1	143.5	146.5	151.0	153.8	156.9	159.1	163.4
70°	139.7	134.7	129.1	127.3	127.0	129.4	133.8	134.1	138.4	139.3	143.9
72.5°	124.1	118.0	114.1	112.3	111.0	113.2	116.1	116.8	119.1	120.8	123.3
75°	99.9	95.2	91.6	88.8	87.9	89.0	89.0	90.6	92.1	93.1	95.9
77.5°	78.6	73.3	68.9	67.3	66.2	65.4	66.1	67.0	66.3	67.9	68.5
80°	63.8	58.2	54.9	54.3	52.4	50.9	50.5	51.5	50.2	50.9	52.7
82.5°	49.3	45.7	42.1	41.4	39.1	38.3	37.9	37.4	37.4	37.3	37.6
85°	29.3	27.1	24.6	23.1	22.2	20.7	20.7	20.0	19.4	18.8	19.1
87.5°	16.6	15.8	14.3	13.2	12.3	10.9	10.5	9.3	8.6	7.8	7.1
90°	24.0	22.6	20.8	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1
92.5°	23.1	21.8	20.0	18.1	16.3	14.5	13.5	13.4	13.2	13.1	12.9
95°	24.0	22.6	22.3	22.2	21.9	21.7	25.4	33.2	41.0	48.7	56.5
97.5°	27.3	27.1	52.6	78.1	103.5	129.0	139.3	134.5	129.7	124.8	120.0
100°	41.4	45.2	76.7	108.2	139.7	171.3	185.0	180.9	176.7	172.6	168.5
102.5°	175.9	217.9	222.0	226.1	230.1	234.2	234.8	231.8	228.8	225.8	222.8
105°	322.7	320.6	319.4	318.3	317.2	316.0	314.7	313.4	312.0	310.6	309.3
107.5°	400.7	399.7	398.2	396.6	395.1	393.5	392.4	391.7	391.0	390.3	389.6
110°	453.6	453.1	451.8	450.4	449.0	447.7	446.6	445.9	445.3	444.6	443.9



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	504.9	504.9	504.3	503.7	503.0	502.3	501.5	500.2	499.0	497.7	496.5
115°	580.0	579.5	579.7	580.0	580.2	580.4	580.2	579.5	578.8	578.1	577.4
117.5°	656.7	656.8	656.2	655.8	655.3	654.7	654.0	653.2	652.2	651.3	650.4
120°	703.3	702.8	703.1	703.3	703.5	703.7	703.4	702.5	701.6	700.6	699.7
122.5°	750.0	749.6	749.3	749.0	748.7	748.4	748.0	747.4	746.9	746.3	745.8
125°	814.4	813.8	814.2	814.7	815.2	815.6	815.4	814.4	813.6	812.6	811.7
127.5°	879.8	880.0	878.9	877.8	876.8	875.8	875.1	874.9	874.6	874.4	874.2
130°	918.9	918.6	917.9	917.2	916.6	915.8	915.4	915.1	915.0	914.7	914.5
132.5°	957.4	957.2	956.3	955.5	954.7	953.8	953.1	952.7	952.3	951.9	951.5
135°	1010.5	1010.0	1009.2	1008.2	1007.3	1006.4	1006.1	1006.3	1006.5	1006.7	1006.9
137.5°	1061.5	1061.0	1060.0	1059.0	1058.0	1057.0	1056.5	1056.4	1056.2	1056.1	1056.1
140°	1092.9	1092.3	1091.8	1091.3	1090.8	1090.4	1090.0	1089.5	1089.0	1088.6	1088.1
142.5°	1122.4	1121.8	1121.6	1121.3	1121.0	1120.7	1120.2	1119.4	1118.6	1117.7	1116.9
145°	1164.4	1164.2	1164.2	1164.2	1164.2	1164.2	1163.8	1163.2	1162.4	1161.7	1161.1
147.5°	1201.1	1200.9	1201.2	1201.4	1201.7	1201.9	1201.3	1200.1	1198.8	1197.5	1196.2
150°	1224.8	1224.8	1225.0	1225.3	1225.5	1225.7	1225.3	1224.5	1223.5	1222.7	1221.7
152.5°	1244.9	1244.5	1244.9	1245.3	1245.8	1246.2	1246.0	1245.2	1244.5	1243.8	1243.1
155°	1271.9	1271.1	1271.7	1272.4	1273.1	1273.7	1274.0	1273.7	1273.5	1273.3	1273.1
157.5°	1295.5	1294.3	1295.1	1295.8	1296.6	1297.4	1297.8	1297.9	1298.1	1298.2	1298.4
160°	1310.4	1309.1	1309.2	1309.5	1309.7	1310.0	1310.4	1311.1	1311.8	1312.5	1313.1
162.5°	1322.7	1321.4	1321.6	1321.8	1322.1	1322.3	1322.9	1323.7	1324.6	1325.4	1326.3
165°	1339.7	1337.8	1337.8	1337.8	1337.8	1337.8	1338.4	1339.5	1340.7	1341.8	1343.0
167.5°	1352.2	1350.1	1350.3	1350.4	1350.6	1350.7	1351.4	1352.6	1353.8	1354.9	1356.1
170°	1360.2	1358.4	1358.1	1357.9	1357.6	1357.5	1358.0	1359.4	1360.7	1362.2	1363.5
172.5°	1365.1	1363.3	1363.0	1362.9	1362.6	1362.4	1362.9	1364.3	1365.7	1367.1	1368.4
175°	1370.7	1368.7	1368.4	1368.2	1367.9	1367.7	1368.3	1369.7	1371.0	1372.4	1373.8
177.5°	1373.6	1372.1	1371.7	1371.4	1371.0	1370.6	1371.1	1372.4	1373.6	1375.0	1376.3
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	749.0	751.5	754.6	760.1	762.1	764.5	767.9	767.7	768.7	772.4	780.3
5°	751.8	761.3	770.6	781.6	793.4	801.1	811.6	818.0	824.5	832.8	847.0
7.5°	752.9	768.0	785.0	804.5	821.8	841.8	857.4	872.0	885.3	902.9	919.7
10°	751.1	771.5	793.4	818.0	844.2	866.4	886.5	909.3	928.7	949.9	969.1
12.5°	747.9	772.5	801.8	829.3	860.0	892.8	917.7	940.8	966.6	991.1	1020.6
15°	740.7	774.3	808.5	844.9	885.8	923.8	959.8	989.7	1017.5	1054.2	1092.7
17.5°	731.4	767.6	810.8	854.8	897.7	941.0	985.6	1030.5	1065.6	1111.1	1141.3
20°	722.8	764.7	809.1	861.5	904.4	958.3	1002.7	1046.1	1094.2	1139.5	1175.6
22.5°	710.7	756.5	803.7	855.8	912.2	966.1	1017.5	1064.6	1112.7	1162.0	1205.6
25°	695.4	737.0	792.7	851.9	908.0	966.6	1025.5	1084.7	1136.4	1188.5	1229.2
27.5°	669.2	721.8	773.7	834.8	897.1	963.4	1026.4	1088.3	1142.5	1185.3	1210.6
30°	655.9	701.5	758.0	819.3	886.8	958.0	1023.6	1084.3	1134.9	1169.1	1179.2
32.5°	636.2	683.3	738.5	802.0	873.5	946.6	1014.9	1072.2	1114.4	1132.3	1120.1
35°	606.9	649.4	705.2	770.2	844.5	922.5	990.0	1038.4	1060.0	1043.1	1000.8
37.5°	571.7	613.9	669.9	733.8	810.7	889.9	951.0	985.8	978.7	936.5	873.5
40°	547.1	586.5	639.8	708.9	783.8	863.3	917.0	935.8	916.1	855.6	788.8
42.5°	519.8	558.2	611.7	678.3	757.6	831.0	877.7	879.3	846.3	774.0	706.9
45°	478.1	514.8	565.3	634.6	708.0	777.1	807.9	792.7	731.7	662.0	594.5
47.5°	437.0	468.7	518.6	584.4	654.0	712.2	727.5	700.3	635.3	567.6	505.0
50°	406.9	438.9	485.8	548.7	615.8	666.1	673.4	637.4	573.6	505.5	456.5
52.5°	378.0	409.8	455.0	513.1	574.6	620.0	620.2	578.5	514.9	454.2	408.6
55°	335.6	364.3	405.0	457.1	512.0	547.4	538.8	495.6	440.5	387.8	348.0
57.5°	294.9	319.8	357.3	400.8	449.1	478.3	464.0	422.5	373.2	328.5	298.3
60°	268.5	292.2	324.2	365.3	405.9	428.7	415.2	377.6	332.2	296.2	270.0
62.5°	242.8	262.8	293.7	329.2	366.9	383.9	371.8	334.7	295.6	262.9	241.6
65°	206.5	222.8	247.5	278.1	305.5	320.0	309.7	275.2	245.3	221.9	204.9
67.5°	172.6	185.4	204.1	228.5	251.8	259.7	250.4	226.3	201.1	182.3	170.3
70°	149.2	161.2	176.9	195.7	216.0	224.4	215.2	196.1	175.4	158.1	146.4
72.5°	128.7	138.0	151.3	167.4	183.2	191.6	185.3	166.9	149.5	136.7	126.7
75°	98.0	106.0	115.3	126.7	139.0	144.6	139.0	126.4	114.3	104.8	97.7
77.5°	71.3	75.6	82.7	91.3	98.9	103.2	98.4	89.8	82.5	76.0	72.4
80°	54.3	57.4	62.3	69.1	74.3	78.3	75.2	68.1	62.3	57.9	56.4
82.5°	39.5	41.5	44.8	49.8	53.3	55.4	54.0	48.9	46.5	42.6	41.1
85°	19.4	20.7	22.8	24.3	27.4	27.7	28.0	25.9	23.8	22.8	21.5
87.5°	7.8	8.6	9.7	11.0	12.4	13.1	13.2	13.5	12.9	12.9	12.2
90°	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3
92.5°	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1	24.6
95°	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0	25.3
97.5°	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3	27.4
100°	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4	37.5
102.5°	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9	134.1
105°	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7	324.7
107.5°	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7	401.7
110°	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6	454.1





TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9	504.7
115°	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0	580.4
117.5°	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7	656.6
120°	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3	703.7
122.5°	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0	750.2
125°	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4	815.2
127.5°	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8	879.7
130°	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9	919.0
132.5°	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4	957.7
135°	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5	1011.0
137.5°	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5	1062.0
140°	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9	1093.6
142.5°	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4	1122.8
145°	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4	1164.6
147.5°	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1	1201.3
150°	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8	1224.8
152.5°	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9	1245.2
155°	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9	1272.9
157.5°	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5	1296.6
160°	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4	1311.8
162.5°	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7	1324.1
165°	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7	1341.5
167.5°	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2	1354.2
170°	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2	1362.0
172.5°	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1	1366.9
175°	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7	1372.8
177.5°	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6	1375.1
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	784.3	784.7	787.0	788.7	789.2	791.6	791.9
5°	853.2	858.4	868.5	869.5	871.0	879.1	872.9
7.5°	933.9	947.2	956.1	963.9	966.8	970.3	969.6
10°	985.7	1005.4	1015.3	1031.0	1031.7	1035.6	1033.2
12.5°	1037.8	1060.7	1078.6	1081.6	1094.7	1096.8	1100.3
15°	1111.4	1135.8	1160.8	1169.7	1187.9	1192.2	1199.0
17.5°	1180.7	1205.6	1223.1	1246.3	1253.7	1263.7	1257.0
20°	1218.7	1245.9	1268.0	1286.2	1294.0	1299.5	1298.9
22.5°	1241.7	1269.0	1287.0	1300.8	1308.0	1310.3	1310.2
25°	1256.0	1271.8	1277.3	1282.5	1274.5	1271.8	1273.0
27.5°	1216.1	1212.0	1197.5	1178.5	1158.8	1143.1	1134.6
30°	1161.1	1137.0	1115.2	1077.0	1057.2	1045.5	1035.0
32.5°	1083.2	1045.0	1003.0	968.0	945.5	928.1	925.5
35°	949.7	892.3	840.8	798.0	775.8	757.0	752.7
37.5°	807.4	747.8	701.5	663.7	639.8	626.6	614.3
40°	712.9	661.8	616.2	584.1	565.9	556.3	548.7
42.5°	640.2	593.4	548.1	523.6	507.2	501.4	496.9
45°	539.7	496.2	464.8	446.3	436.7	426.9	422.2
47.5°	459.2	423.9	403.1	387.5	377.2	371.4	368.4
50°	413.6	384.7	366.1	354.2	344.9	340.2	337.8
52.5°	373.2	349.4	333.9	324.3	318.1	314.7	313.6
55°	321.5	303.3	293.4	285.1	280.5	277.4	276.2
57.5°	279.4	265.5	257.5	250.6	248.8	246.2	245.3
60°	251.8	241.1	234.2	229.7	228.1	225.0	225.6
62.5°	227.4	218.6	212.8	210.2	208.1	205.5	206.4
65°	192.3	185.8	182.8	180.3	177.8	176.3	177.5
67.5°	161.4	156.9	152.7	151.3	150.1	149.9	148.5
70°	141.2	137.4	133.8	132.8	132.8	131.6	131.3
72.5°	121.7	119.0	116.5	115.8	114.9	115.3	114.1
75°	94.0	91.8	90.9	90.0	89.7	89.7	88.8
77.5°	69.5	67.9	66.4	66.4	65.3	64.9	64.7
80°	52.7	52.1	50.9	50.9	50.2	50.5	49.9
82.5°	39.6	38.7	38.5	38.0	37.2	37.2	36.6
85°	21.2	20.4	20.0	19.1	18.5	19.1	18.5
87.5°	12.8	12.8	12.7	12.3	12.1	12.2	11.6
90°	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.5	455.0	455.5	456.2	456.9	457.6	458.3



TEST NUMBER: P332763-927

CATALOG NUMBER: S124DIW-S575D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)