

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333020-927

Luminaire Tested: **S124RDIW-S350D770U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333020-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3287.7 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36																				
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31																				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26																				
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23																				
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	28	25	24	20																				
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21	17																				
6	61	50	42	36	55	46	39	34	37	32	29	30	26	23	23	20	18	15																				
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14																				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12																				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11																				
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	16	14	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	1.4
10°-20°	136.0	4.1
20°-30°	212.7	6.5
30°-40°	236.5	7.2
40°-50°	209.8	6.4
50°-60°	163.5	5.0
60°-70°	107.0	3.3
70°-80°	52.6	1.6
80°-90°	15.3	0.5
90°-100°	50.1	1.5
100°-110°	148.5	4.5
110°-120°	252.1	7.7
120°-130°	332.4	10.1
130°-140°	373.3	11.4
140°-150°	366.9	11.2
150°-160°	308.6	9.4
160°-170°	205.3	6.2
170°-180°	71.9	2.2
0°-30°	393.8	12.0
0°-40°	630.3	19.2
0°-60°	1003.6	30.5
0°-90°	1178.5	35.8
90°-120°	450.8	13.7
90°-150°	1523.4	46.3
90°-180°	2109.0	64.1
0°-180°	3287.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	11
90°	18	2	18	2	18	9
95°	46	35	46	35	46	48
105°	144	137	144	137	144	151
115°	254	256	254	256	254	251
125°	370	373	370	373	370	330
135°	482	482	482	482	482	372
145°	586	585	586	585	586	366
155°	670	670	670	670	670	308
165°	728	730	728	730	728	205
175°	756	759	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	6.8	6.7	6.7	6.7	6.7	6.5	6.5	6.7	6.2	6.2	5.9
90°	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5	13.7	12.9	11.9
92.5°	26.1	26.0	25.8	25.7	25.5	25.2	24.7	24.2	23.8	23.3	22.6
95°	46.4	46.4	46.4	46.4	46.4	46.3	45.9	45.5	45.1	44.7	43.8
97.5°	72.8	72.8	72.8	72.8	72.8	72.6	72.1	71.6	71.1	70.7	69.6
100°	91.1	91.1	91.1	91.1	91.1	91.0	90.7	90.5	90.2	90.0	88.8
102.5°	111.9	111.7	111.6	111.5	111.4	111.1	110.8	110.4	110.1	109.7	108.6
105°	143.5	143.1	142.7	142.3	141.9	141.5	141.1	140.7	140.3	139.9	139.4
107.5°	174.3	174.3	174.4	174.4	174.4	174.2	173.8	173.5	173.1	172.8	172.7
110°	196.4	196.0	195.6	195.2	194.8	194.7	195.0	195.3	195.5	195.7	195.9



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.0	218.9	218.8	218.7	218.6	218.6	218.6	218.7	218.8	218.8	219.0
115°	254.0	254.1	254.3	254.4	254.5	254.6	254.8	254.9	255.0	255.2	255.4
117.5°	287.4	287.6	287.9	288.2	288.4	288.8	289.2	289.7	290.1	290.6	290.7
120°	312.8	312.5	312.3	312.0	311.7	312.0	312.6	313.2	313.9	314.6	315.0
122.5°	334.0	334.5	334.9	335.3	335.8	336.3	336.8	337.2	337.6	338.1	338.3
125°	370.4	370.7	370.9	371.2	371.5	371.7	372.0	372.2	372.5	372.7	372.9
127.5°	404.2	404.3	404.6	404.8	405.0	405.2	405.5	405.8	406.0	406.3	406.5
130°	426.3	426.7	427.3	427.9	428.3	428.7	429.0	429.3	429.5	429.8	429.8
132.5°	449.8	450.0	450.2	450.4	450.6	450.8	451.1	451.4	451.6	451.9	452.0
135°	482.1	482.5	482.9	483.3	483.7	484.0	484.3	484.5	484.8	485.1	485.1
137.5°	516.1	516.0	515.9	515.9	515.8	515.9	516.3	516.6	516.9	517.3	517.1
140°	536.8	536.9	537.0	537.2	537.3	537.4	537.6	537.7	537.8	538.0	538.0
142.5°	557.5	557.5	557.5	557.5	557.6	557.6	557.6	557.7	557.7	557.7	557.9
145°	585.6	586.0	586.4	586.8	587.2	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	614.0	614.2	614.3	614.4	614.6	614.7	614.8	614.9	615.0	615.1	615.2
150°	631.4	631.6	631.7	631.8	632.0	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	647.5	647.8	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5	647.5
155°	669.7	670.2	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7	669.8
157.5°	689.5	690.0	690.5	690.9	691.3	691.3	690.9	690.5	690.1	689.8	689.8
160°	700.8	701.5	702.1	702.8	703.5	703.6	703.2	702.8	702.4	702.0	702.1
162.5°	712.6	713.3	713.9	714.5	715.2	715.2	714.5	713.8	713.0	712.3	712.5
165°	727.9	728.4	728.9	729.4	730.0	729.8	729.0	728.3	727.5	726.7	727.0
167.5°	738.8	739.7	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.9	738.9
170°	745.0	745.8	746.8	747.7	748.6	748.7	747.9	747.1	746.3	745.5	745.4
172.5°	750.1	751.0	751.9	752.8	753.8	753.8	752.9	752.0	751.1	750.2	750.2
175°	755.5	756.5	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5	755.7
177.5°	758.4	759.1	760.0	760.8	761.7	761.8	761.0	760.3	759.5	758.8	758.8
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	5.8	5.4	5.5	5.2	5.1	5.5	5.6	5.5	5.3	5.1	5.0
90°	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7	3.2	4.7	6.1
92.5°	21.8	21.1	20.4	19.2	17.5	15.8	14.3	12.6	14.3	15.8	17.5
95°	42.9	41.9	41.0	40.0	38.8	37.6	36.4	35.3	36.4	37.6	38.8
97.5°	68.5	67.5	66.4	65.4	64.4	63.5	62.6	61.6	62.6	63.5	64.4
100°	87.6	86.4	85.2	84.4	83.9	83.3	82.9	82.3	82.9	83.3	83.9
102.5°	107.6	106.5	105.4	104.8	104.6	104.3	104.2	103.9	104.2	104.3	104.6
105°	138.9	138.4	137.8	137.5	137.4	137.3	137.1	137.0	137.1	137.3	137.4
107.5°	172.6	172.5	172.5	172.3	172.1	172.0	171.8	171.7	171.8	172.0	172.1
110°	196.1	196.1	196.3	196.2	196.0	195.7	195.4	195.2	195.4	195.7	196.0



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.3	219.5	219.8	219.8	219.8	219.8	219.7	219.7	219.7	219.8	219.8
115°	255.7	256.0	256.2	256.4	256.4	256.4	256.4	256.4	256.4	256.4	256.4
117.5°	291.0	291.1	291.3	291.4	291.2	291.1	291.0	290.9	291.0	291.1	291.2
120°	315.4	315.8	316.1	316.1	315.5	315.0	314.5	313.9	314.5	315.0	315.5
122.5°	338.4	338.7	338.8	338.8	338.6	338.3	338.2	337.9	338.2	338.3	338.6
125°	373.0	373.1	373.3	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4
127.5°	406.7	406.9	407.1	407.0	406.6	406.2	405.8	405.4	405.8	406.2	406.6
130°	429.8	429.8	429.8	429.6	429.2	428.8	428.4	428.0	428.4	428.8	429.2
132.5°	452.1	452.2	452.3	452.3	451.9	451.6	451.4	451.1	451.4	451.6	451.9
135°	485.1	485.1	485.1	484.7	483.9	483.1	482.3	481.6	482.3	483.1	483.9
137.5°	516.8	516.7	516.4	516.2	515.8	515.4	515.1	514.7	515.1	515.4	515.8
140°	538.0	538.0	538.0	537.8	537.6	537.3	537.0	536.8	537.0	537.3	537.6
142.5°	557.9	558.0	558.2	558.1	557.8	557.5	557.3	557.0	557.3	557.5	557.8
145°	587.7	587.6	587.4	587.1	586.6	586.1	585.5	585.0	585.5	586.1	586.6
147.5°	615.3	615.4	615.5	615.3	614.7	614.0	613.4	612.8	613.4	614.0	614.7
150°	632.1	632.1	632.1	631.8	631.3	630.7	630.2	629.7	630.2	630.7	631.3
152.5°	647.4	647.2	647.1	647.0	646.7	646.3	646.0	645.7	646.0	646.3	646.7
155°	669.9	670.0	670.2	670.3	670.3	670.3	670.3	670.3	670.3	670.3	670.3
157.5°	689.8	689.8	689.9	690.0	690.2	690.5	690.7	690.9	690.7	690.5	690.2
160°	702.3	702.4	702.5	702.7	702.8	702.9	703.1	703.2	703.1	702.9	702.8
162.5°	712.6	712.7	712.9	713.1	713.4	713.8	714.2	714.5	714.2	713.8	713.4
165°	727.2	727.5	727.8	728.1	728.5	728.9	729.3	729.7	729.3	728.9	728.5
167.5°	738.9	738.9	738.8	739.1	739.7	740.2	740.8	741.2	740.8	740.2	739.7
170°	745.3	745.1	745.0	745.3	745.9	746.6	747.2	747.9	747.2	746.6	745.9
172.5°	750.2	750.1	750.1	750.4	750.9	751.5	752.0	752.6	752.0	751.5	750.9
175°	755.7	755.9	756.1	756.5	757.1	757.7	758.4	759.1	758.4	757.7	757.1
177.5°	758.8	758.8	758.8	759.1	759.6	760.1	760.7	761.1	760.7	760.1	759.6
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	5.2	5.4	5.5	5.5	5.9	6.0	6.0	6.2	6.5	6.3	6.5
90°	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5	15.3	16.1	16.6
92.5°	19.2	20.4	21.1	21.8	22.6	23.3	23.8	24.2	24.7	25.2	25.5
95°	40.0	41.0	41.9	42.9	43.8	44.7	45.1	45.5	45.9	46.3	46.4
97.5°	65.4	66.4	67.5	68.5	69.6	70.7	71.1	71.6	72.1	72.6	72.8
100°	84.4	85.2	86.4	87.6	88.8	90.0	90.2	90.5	90.7	91.0	91.1
102.5°	104.8	105.4	106.5	107.6	108.6	109.7	110.1	110.4	110.8	111.1	111.4
105°	137.5	137.8	138.4	138.9	139.4	139.9	140.3	140.7	141.1	141.5	141.9
107.5°	172.3	172.5	172.5	172.6	172.7	172.8	173.1	173.5	173.8	174.2	174.4
110°	196.2	196.3	196.1	196.1	195.9	195.7	195.5	195.3	195.0	194.7	194.8



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.8	219.8	219.5	219.3	219.0	218.8	218.8	218.7	218.6	218.6	218.6
115°	256.4	256.2	256.0	255.7	255.4	255.2	255.0	254.9	254.8	254.6	254.5
117.5°	291.4	291.3	291.1	291.0	290.7	290.6	290.1	289.7	289.2	288.8	288.4
120°	316.1	316.1	315.8	315.4	315.0	314.6	313.9	313.2	312.6	312.0	311.7
122.5°	338.8	338.8	338.7	338.4	338.3	338.1	337.6	337.2	336.8	336.3	335.8
125°	373.4	373.3	373.1	373.0	372.9	372.7	372.5	372.2	372.0	371.7	371.5
127.5°	407.0	407.1	406.9	406.7	406.5	406.3	406.0	405.8	405.5	405.2	405.0
130°	429.6	429.8	429.8	429.8	429.8	429.8	429.5	429.3	429.0	428.7	428.3
132.5°	452.3	452.3	452.2	452.1	452.0	451.9	451.6	451.4	451.1	450.8	450.6
135°	484.7	485.1	485.1	485.1	485.1	485.1	484.8	484.5	484.3	484.0	483.7
137.5°	516.2	516.4	516.7	516.8	517.1	517.3	516.9	516.6	516.3	515.9	515.8
140°	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.7	537.6	537.4	537.3
142.5°	558.1	558.2	558.0	557.9	557.9	557.7	557.7	557.7	557.6	557.6	557.6
145°	587.1	587.4	587.6	587.7	587.8	588.0	587.8	587.7	587.6	587.4	587.2
147.5°	615.3	615.5	615.4	615.3	615.2	615.1	615.0	614.9	614.8	614.7	614.6
150°	631.8	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.0
152.5°	647.0	647.1	647.2	647.4	647.5	647.5	647.8	648.2	648.5	648.8	648.8
155°	670.3	670.2	670.0	669.9	669.8	669.7	670.2	670.7	671.2	671.8	671.8
157.5°	690.0	689.9	689.8	689.8	689.8	689.8	690.1	690.5	690.9	691.3	691.3
160°	702.7	702.5	702.4	702.3	702.1	702.0	702.4	702.8	703.2	703.6	703.5
162.5°	713.1	712.9	712.7	712.6	712.5	712.3	713.0	713.8	714.5	715.2	715.2
165°	728.1	727.8	727.5	727.2	727.0	726.7	727.5	728.3	729.0	729.8	730.0
167.5°	739.1	738.8	738.9	738.9	738.9	738.9	739.7	740.5	741.2	742.0	742.0
170°	745.3	745.0	745.1	745.3	745.4	745.5	746.3	747.1	747.9	748.7	748.6
172.5°	750.4	750.1	750.1	750.2	750.2	750.2	751.1	752.0	752.9	753.8	753.8
175°	756.5	756.1	755.9	755.7	755.7	755.5	756.5	757.3	758.3	759.1	759.1
177.5°	759.1	758.8	758.8	758.8	758.8	758.8	759.5	760.3	761.0	761.8	761.7
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	6.8	6.7	6.7	6.8	6.7	6.7	6.8	6.5	6.3	6.5	6.2
90°	16.9	17.1	17.3	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5
92.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.5	25.2	24.7	24.2
95°	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.3	45.9	45.5
97.5°	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.8	72.6	72.1	71.6
100°	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.0	90.7	90.5
102.5°	111.5	111.6	111.7	111.9	111.7	111.6	111.5	111.4	111.1	110.8	110.4
105°	142.3	142.7	143.1	143.5	143.1	142.7	142.3	141.9	141.5	141.1	140.7
107.5°	174.4	174.4	174.3	174.3	174.3	174.4	174.4	174.4	174.2	173.8	173.5
110°	195.2	195.6	196.0	196.4	196.0	195.6	195.2	194.8	194.7	195.0	195.3



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	218.7	218.8	218.9	219.0	218.9	218.8	218.7	218.6	218.6	218.6	218.7
115°	254.4	254.3	254.1	254.0	254.1	254.3	254.4	254.5	254.6	254.8	254.9
117.5°	288.2	287.9	287.6	287.4	287.6	287.9	288.2	288.4	288.8	289.2	289.7
120°	312.0	312.3	312.5	312.8	312.5	312.3	312.0	311.7	312.0	312.6	313.2
122.5°	335.3	334.9	334.5	334.0	334.5	334.9	335.3	335.8	336.3	336.8	337.2
125°	371.2	370.9	370.7	370.4	370.7	370.9	371.2	371.5	371.7	372.0	372.2
127.5°	404.8	404.6	404.3	404.2	404.3	404.6	404.8	405.0	405.2	405.5	405.8
130°	427.9	427.3	426.7	426.3	426.7	427.3	427.9	428.3	428.7	429.0	429.3
132.5°	450.4	450.2	450.0	449.8	450.0	450.2	450.4	450.6	450.8	451.1	451.4
135°	483.3	482.9	482.5	482.1	482.5	482.9	483.3	483.7	484.0	484.3	484.5
137.5°	515.9	515.9	516.0	516.1	516.0	515.9	515.9	515.8	515.9	516.3	516.6
140°	537.2	537.0	536.9	536.8	536.9	537.0	537.2	537.3	537.4	537.6	537.7
142.5°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.6	557.6	557.6	557.7
145°	586.8	586.4	586.0	585.6	586.0	586.4	586.8	587.2	587.4	587.6	587.7
147.5°	614.4	614.3	614.2	614.0	614.2	614.3	614.4	614.6	614.7	614.8	614.9
150°	631.8	631.7	631.6	631.4	631.6	631.7	631.8	632.0	632.1	632.1	632.1
152.5°	648.5	648.2	647.8	647.5	647.8	648.2	648.5	648.8	648.8	648.5	648.2
155°	671.2	670.7	670.2	669.7	670.2	670.7	671.2	671.8	671.8	671.2	670.7
157.5°	690.9	690.5	690.0	689.5	690.0	690.5	690.9	691.3	691.3	690.9	690.5
160°	702.8	702.1	701.5	700.8	701.5	702.1	702.8	703.5	703.6	703.2	702.8
162.5°	714.5	713.9	713.3	712.6	713.3	713.9	714.5	715.2	715.2	714.5	713.8
165°	729.4	728.9	728.4	727.9	728.4	728.9	729.4	730.0	729.8	729.0	728.3
167.5°	741.2	740.5	739.7	738.8	739.7	740.5	741.2	742.0	742.0	741.2	740.5
170°	747.7	746.8	745.8	745.0	745.8	746.8	747.7	748.6	748.7	747.9	747.1
172.5°	752.8	751.9	751.0	750.1	751.0	751.9	752.8	753.8	753.8	752.9	752.0
175°	758.3	757.3	756.5	755.5	756.5	757.3	758.3	759.1	759.1	758.3	757.3
177.5°	760.8	760.0	759.1	758.4	759.1	760.0	760.8	761.7	761.8	761.0	760.3
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	6.0	6.0	5.9	5.5	5.5	5.4	5.2	5.0	5.1	5.3	5.5
90°	13.7	12.9	11.9	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7
92.5°	23.8	23.3	22.6	21.8	21.1	20.4	19.2	17.5	15.8	14.3	12.6
95°	45.1	44.7	43.8	42.9	41.9	41.0	40.0	38.8	37.6	36.4	35.3
97.5°	71.1	70.7	69.6	68.5	67.5	66.4	65.4	64.4	63.5	62.6	61.6
100°	90.2	90.0	88.8	87.6	86.4	85.2	84.4	83.9	83.3	82.9	82.3
102.5°	110.1	109.7	108.6	107.6	106.5	105.4	104.8	104.6	104.3	104.2	103.9
105°	140.3	139.9	139.4	138.9	138.4	137.8	137.5	137.4	137.3	137.1	137.0
107.5°	173.1	172.8	172.7	172.6	172.5	172.5	172.3	172.1	172.0	171.8	171.7
110°	195.5	195.7	195.9	196.1	196.1	196.3	196.2	196.0	195.7	195.4	195.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	218.8	218.8	219.0	219.3	219.5	219.8	219.8	219.8	219.8	219.7	219.7
115°	255.0	255.2	255.4	255.7	256.0	256.2	256.4	256.4	256.4	256.4	256.4
117.5°	290.1	290.6	290.7	291.0	291.1	291.3	291.4	291.2	291.1	291.0	290.9
120°	313.9	314.6	315.0	315.4	315.8	316.1	316.1	315.5	315.0	314.5	313.9
122.5°	337.6	338.1	338.3	338.4	338.7	338.8	338.8	338.6	338.3	338.2	337.9
125°	372.5	372.7	372.9	373.0	373.1	373.3	373.4	373.4	373.4	373.4	373.4
127.5°	406.0	406.3	406.5	406.7	406.9	407.1	407.0	406.6	406.2	405.8	405.4
130°	429.5	429.8	429.8	429.8	429.8	429.8	429.6	429.2	428.8	428.4	428.0
132.5°	451.6	451.9	452.0	452.1	452.2	452.3	452.3	451.9	451.6	451.4	451.1
135°	484.8	485.1	485.1	485.1	485.1	485.1	484.7	483.9	483.1	482.3	481.6
137.5°	516.9	517.3	517.1	516.8	516.7	516.4	516.2	515.8	515.4	515.1	514.7
140°	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.6	537.3	537.0	536.8
142.5°	557.7	557.7	557.9	557.9	558.0	558.2	558.1	557.8	557.5	557.3	557.0
145°	587.8	588.0	587.8	587.7	587.6	587.4	587.1	586.6	586.1	585.5	585.0
147.5°	615.0	615.1	615.2	615.3	615.4	615.5	615.3	614.7	614.0	613.4	612.8
150°	632.1	632.1	632.1	632.1	632.1	632.1	631.8	631.3	630.7	630.2	629.7
152.5°	647.8	647.5	647.5	647.4	647.2	647.1	647.0	646.7	646.3	646.0	645.7
155°	670.2	669.7	669.8	669.9	670.0	670.2	670.3	670.3	670.3	670.3	670.3
157.5°	690.1	689.8	689.8	689.8	689.8	689.9	690.0	690.2	690.5	690.7	690.9
160°	702.4	702.0	702.1	702.3	702.4	702.5	702.7	702.8	702.9	703.1	703.2
162.5°	713.0	712.3	712.5	712.6	712.7	712.9	713.1	713.4	713.8	714.2	714.5
165°	727.5	726.7	727.0	727.2	727.5	727.8	728.1	728.5	728.9	729.3	729.7
167.5°	739.7	738.9	738.9	738.9	738.9	738.8	739.1	739.7	740.2	740.8	741.2
170°	746.3	745.5	745.4	745.3	745.1	745.0	745.3	745.9	746.6	747.2	747.9
172.5°	751.1	750.2	750.2	750.2	750.1	750.1	750.4	750.9	751.5	752.0	752.6
175°	756.5	755.5	755.7	755.7	755.9	756.1	756.5	757.1	757.7	758.4	759.1
177.5°	759.5	758.8	758.8	758.8	758.8	758.8	759.1	759.6	760.1	760.7	761.1
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	5.6	5.5	5.1	5.2	5.5	5.4	5.8	5.9	6.2	6.2	6.7
90°	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5
92.5°	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8	24.2
95°	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1	45.5
97.5°	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1	71.6
100°	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2	90.5
102.5°	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1	110.4
105°	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3	140.7
107.5°	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1	173.5
110°	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5	195.3



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8	218.7
115°	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0	254.9
117.5°	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1	289.7
120°	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9	313.2
122.5°	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6	337.2
125°	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5	372.2
127.5°	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0	405.8
130°	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5	429.3
132.5°	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6	451.4
135°	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8	484.5
137.5°	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9	516.6
140°	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8	537.7
142.5°	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7	557.7
145°	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8	587.7
147.5°	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0	614.9
150°	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8	648.2
155°	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2	670.7
157.5°	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1	690.5
160°	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4	702.8
162.5°	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0	713.8
165°	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5	728.3
167.5°	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7	740.5
170°	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3	747.1
172.5°	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1	752.0
175°	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5	757.3
177.5°	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5	760.3
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	6.5	6.5	6.7	6.7	6.7	6.7	6.8
90°	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P333020-927

CATALOG NUMBER: S124RDIW-S350D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)