

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333039-927

Luminaire Tested: **S124RDIW-S575D770U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333039-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4368.0 lumens  
Efficiency: N/A  
Efficacy: 116.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	19	17	14	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6176	6176	6176	6176
5°	7164	6195	5476	6195
10°	8475	6167	4887	6167
15°	9789	6110	4199	6110
20°	10899	6032	3797	6032
25°	11251	5955	3526	5955
30°	9849	5862	3361	5862
35°	7666	5723	3263	5723
40°	5750	5564	3209	5564
45°	4539	5310	3181	5310
50°	3832	5016	3090	5016
55°	3340	4694	2923	4694
60°	3006	4359	2588	4359
65°	2649	3998	2225	3998
70°	2386	3623	2009	3623
75°	1999	3213	1712	3213
80°	1692	2738	1604	2738
85°	1426	2140	1426	2140



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	1.7
10°-20°	223.6	5.1
20°-30°	349.7	8.0
30°-40°	388.8	8.9
40°-50°	344.9	7.9
50°-60°	268.8	6.2
60°-70°	176.0	4.0
70°-80°	86.5	2.0
80°-90°	23.6	0.5
90°-100°	26.9	0.6
100°-110°	171.5	3.9
110°-120°	328.0	7.5
120°-130°	416.3	9.5
130°-140°	445.5	10.2
140°-150°	416.6	9.5
150°-160°	335.9	7.7
160°-170°	216.7	5.0
170°-180°	74.7	1.7
0°-30°	647.4	14.8
0°-40°	1036.2	23.7
0°-60°	1649.9	37.8
0°-90°	1936.0	44.3
90°-120°	526.3	12.0
90°-150°	1804.7	41.3
90°-180°	2432.0	55.7
0°-180°	4368.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	765	765	765	765	765	
5°	884	764	676	764	884	89
15°	1171	731	502	731	1171	333
25°	1263	668	396	668	1263	560
35°	778	581	331	581	778	488
45°	398	465	279	465	398	315
55°	237	334	208	334	237	216
65°	139	209	116	209	139	140
75°	64	103	55	103	64	71
85°	15	23	15	23	15	18
90°	18	2	18	2	18	8
95°	17	32	17	32	17	14
105°	168	177	168	177	168	146
115°	333	330	333	330	333	329
125°	468	464	468	464	468	417
135°	580	576	580	576	580	447
145°	668	664	668	664	668	417
155°	728	729	728	729	728	336
165°	765	769	765	769	765	216
175°	782	786	782	786	782	74
180°	786	786	786	786	786	



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	806.9	809.1	806.9	806.7	804.2	803.5	802.5	799.3	793.4	789.9	790.7
5°	884.0	891.7	887.4	886.8	880.0	873.2	868.9	859.0	848.5	841.5	835.6
7.5°	973.1	977.6	974.9	970.5	959.6	953.3	943.3	930.3	911.6	897.1	884.1
10°	1033.8	1037.4	1036.3	1028.3	1020.3	1003.9	994.7	976.4	952.7	933.9	916.3
12.5°	1093.4	1097.4	1086.6	1087.0	1071.7	1058.8	1044.2	1021.4	993.9	969.6	947.7
15°	1171.2	1166.3	1166.3	1160.2	1143.2	1125.3	1110.2	1086.2	1051.6	1022.7	992.2
17.5°	1232.2	1233.9	1231.4	1216.8	1203.5	1185.0	1157.3	1129.3	1097.2	1058.3	1027.1
20°	1268.7	1268.7	1265.9	1256.0	1238.7	1219.0	1189.1	1158.6	1117.9	1078.8	1043.6
22.5°	1283.4	1284.4	1281.2	1273.0	1257.5	1238.3	1212.8	1181.8	1139.9	1095.8	1052.3
25°	1263.1	1268.9	1269.6	1267.4	1262.8	1251.1	1229.2	1197.5	1159.8	1112.1	1065.2
27.5°	1159.7	1167.0	1173.5	1184.2	1198.3	1205.8	1206.7	1190.6	1157.8	1111.8	1064.7
30°	1056.6	1062.7	1082.8	1109.0	1129.3	1147.8	1163.9	1168.2	1149.7	1108.3	1058.8
32.5°	942.1	950.5	970.6	998.8	1032.7	1064.0	1100.0	1118.3	1117.8	1093.1	1047.2
35°	777.9	784.1	802.6	832.2	872.9	919.4	976.4	1020.8	1051.1	1048.8	1020.8
37.5°	627.4	634.4	653.1	677.6	717.1	774.7	829.9	891.0	946.9	978.3	968.8
40°	545.6	545.9	564.0	589.3	626.3	676.5	736.7	804.5	866.7	917.6	927.4
42.5°	480.9	481.0	493.1	520.3	546.9	594.2	651.6	718.9	791.8	850.5	876.6
45°	397.6	400.4	410.3	426.6	447.5	487.6	533.5	596.1	677.8	747.4	790.9
47.5°	336.7	340.8	347.1	360.4	377.1	403.8	441.7	498.0	564.4	641.0	702.9
50°	305.1	305.8	313.8	321.2	335.6	357.0	390.2	437.0	498.1	571.7	640.5
52.5°	278.1	277.9	282.7	292.1	303.9	320.4	347.3	390.0	444.1	510.1	581.1
55°	237.3	238.8	242.6	249.9	258.9	270.6	291.9	323.9	366.5	422.9	487.3
57.5°	206.4	207.2	210.1	213.3	221.4	230.0	245.9	268.2	304.0	350.2	410.3
60°	186.2	186.5	187.4	192.0	198.5	206.5	217.3	236.1	266.3	308.6	356.0
62.5°	166.4	167.0	168.4	171.8	176.8	182.4	193.6	208.7	233.8	269.8	312.6
65°	138.7	139.0	141.2	142.4	146.4	151.3	159.6	169.8	187.1	217.3	249.7
67.5°	115.9	115.9	116.0	117.7	120.5	123.7	128.7	136.9	149.9	168.4	196.9
70°	101.1	101.1	101.7	102.7	104.2	106.9	109.7	115.9	125.5	140.5	162.4
72.5°	87.3	87.5	88.2	88.3	89.1	91.4	93.5	97.4	104.5	115.9	133.6
75°	64.1	65.0	66.5	67.8	69.3	69.1	71.2	73.7	75.8	82.6	92.8
77.5°	47.7	47.2	47.4	48.5	48.6	49.0	50.5	52.4	54.0	57.2	60.8
80°	36.4	36.4	37.3	37.6	37.3	37.6	39.1	40.1	40.7	41.9	45.3
82.5°	27.5	28.0	27.6	28.0	28.2	28.5	29.8	29.9	30.6	31.1	32.5
85°	15.4	15.7	16.0	15.4	15.4	15.4	16.0	16.3	17.0	16.6	17.3
87.5°	9.0	8.6	8.9	8.8	9.0	8.6	8.7	9.0	8.4	8.5	8.3
90°	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5	13.7	12.9	11.9
92.5°	16.2	16.2	16.2	16.1	16.0	15.6	14.8	14.0	13.2	12.4	11.4
95°	17.0	17.0	16.8	16.6	16.6	16.1	15.3	14.5	13.7	12.9	12.8
97.5°	16.5	16.3	16.2	16.1	15.9	15.8	15.8	15.7	15.6	15.5	30.1
100°	16.5	16.3	16.2	16.1	15.9	17.0	19.2	21.5	23.7	25.9	43.9
102.5°	17.0	16.9	16.9	16.9	16.8	28.8	52.8	76.8	100.7	124.7	127.0
105°	167.6	172.3	177.0	181.7	186.4	188.1	187.0	185.8	184.7	183.5	182.8
107.5°	233.5	233.1	232.6	232.1	231.6	231.1	230.4	229.9	229.3	228.7	227.8
110°	262.3	261.9	261.5	261.1	260.7	260.4	260.1	259.8	259.6	259.3	258.6



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.0	290.5	289.9	289.5	289.0	288.8	288.8	288.8	288.9	289.0	288.6
115°	332.8	332.8	332.8	332.8	332.8	332.7	332.4	332.2	331.9	331.6	331.8
117.5°	375.4	375.4	375.5	375.6	375.6	375.7	375.7	375.7	375.8	375.9	375.6
120°	402.2	402.5	402.7	403.0	403.2	403.2	403.0	402.7	402.5	402.2	402.3
122.5°	428.6	428.8	429.0	429.4	429.6	429.7	429.5	429.4	429.2	429.0	428.8
125°	468.1	467.9	467.8	467.7	467.5	467.3	466.9	466.5	466.1	465.7	466.0
127.5°	502.8	502.9	503.0	503.1	503.2	503.3	503.4	503.4	503.5	503.6	503.0
130°	526.2	526.2	526.2	526.2	526.2	526.2	526.1	525.9	525.9	525.7	525.3
132.5°	548.0	548.0	548.1	548.3	548.3	548.3	548.2	548.0	548.0	547.8	547.3
135°	580.4	580.1	579.9	579.6	579.3	579.1	578.8	578.5	578.3	578.1	577.5
137.5°	608.2	608.2	608.3	608.4	608.5	608.3	608.1	607.8	607.4	607.2	606.7
140°	627.4	627.3	627.2	627.0	626.9	626.6	626.2	625.8	625.4	625.1	624.8
142.5°	643.4	643.4	643.3	643.3	643.3	643.2	642.9	642.6	642.3	642.0	641.8
145°	668.0	667.7	667.5	667.2	666.9	666.8	666.6	666.5	666.4	666.2	666.2
147.5°	688.3	688.2	688.1	687.9	687.9	687.7	687.6	687.5	687.4	687.3	687.4
150°	701.5	701.4	701.2	701.2	701.0	700.9	700.9	700.9	700.9	700.9	701.1
152.5°	712.8	712.9	713.0	713.0	713.1	713.0	712.8	712.6	712.4	712.3	712.5
155°	728.0	728.3	728.7	729.1	729.5	729.4	729.0	728.4	727.9	727.4	727.8
157.5°	740.7	741.3	742.0	742.8	743.4	743.4	742.8	742.0	741.3	740.7	741.1
160°	749.2	750.0	750.8	751.5	752.3	752.3	751.5	750.8	750.0	749.2	749.2
162.5°	755.7	756.6	757.5	758.4	759.3	759.3	758.5	757.8	757.0	756.2	756.3
165°	765.0	766.2	767.4	768.6	769.8	769.8	768.7	767.7	766.7	765.6	765.6
167.5°	772.0	773.2	774.6	775.9	777.2	777.3	776.1	775.0	773.8	772.7	772.8
170°	776.2	777.5	778.8	780.1	781.4	781.6	780.5	779.4	778.4	777.4	777.2
172.5°	778.6	780.0	781.4	782.8	784.2	784.3	783.3	782.3	781.3	780.2	780.1
175°	781.5	783.1	784.7	786.2	787.7	788.0	786.8	785.6	784.4	783.2	783.2
177.5°	783.4	784.7	785.8	787.1	788.4	788.6	787.7	787.0	786.1	785.2	785.1
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	788.2	784.7	783.0	779.0	774.4	771.9	769.7	766.5	762.3	757.9	754.6
5°	828.2	820.8	811.5	800.4	790.6	781.0	772.7	764.4	754.9	745.0	735.1
7.5°	869.3	854.7	839.0	820.8	803.1	787.0	772.2	758.0	742.0	727.6	714.5
10°	897.9	878.1	856.3	833.1	810.0	790.0	770.2	752.3	732.6	715.1	700.3
12.5°	921.1	897.9	871.6	842.7	814.9	790.7	768.0	744.7	722.3	703.2	683.5
15°	959.5	927.7	892.3	857.8	821.7	788.8	758.2	731.1	705.5	678.7	659.9
17.5°	986.0	948.2	905.2	863.7	821.1	782.2	747.0	714.7	685.2	657.8	635.4
20°	1001.7	960.1	912.4	865.1	817.4	775.8	737.9	702.1	671.6	642.1	618.9
22.5°	1010.6	964.6	912.4	862.9	813.5	768.4	726.8	689.6	656.3	626.8	601.2
25°	1013.4	964.1	910.8	854.1	799.9	752.1	708.9	668.5	631.5	602.0	574.8
27.5°	1009.5	951.4	896.8	838.6	782.7	732.3	687.0	644.5	607.5	575.8	548.0
30°	1003.5	941.4	882.7	822.4	765.6	717.2	669.5	628.8	590.3	557.3	529.3
32.5°	990.8	929.0	866.0	804.1	746.6	696.8	651.5	610.5	572.7	539.0	509.2
35°	965.4	902.8	834.3	770.9	714.5	662.7	620.1	580.7	544.6	508.6	477.1
37.5°	931.8	868.0	799.9	730.4	673.9	625.0	586.0	549.0	513.7	480.9	446.0
40°	900.3	842.1	771.8	702.7	644.8	597.6	561.6	528.0	492.6	459.9	425.0
42.5°	862.1	812.5	741.5	672.2	615.0	569.5	535.9	503.1	470.9	439.2	402.8
45°	798.3	760.7	694.1	627.6	569.9	524.9	494.1	465.1	436.7	406.5	372.3
47.5°	725.2	699.7	642.3	574.1	520.8	480.3	450.5	426.8	402.8	372.6	342.6
50°	674.4	658.1	602.6	540.3	489.5	452.2	421.7	399.4	379.5	350.5	323.6
52.5°	620.1	611.5	564.6	505.0	455.9	419.4	393.3	373.4	353.1	329.0	303.9
55°	537.6	542.2	502.4	450.9	404.7	373.9	350.1	333.5	316.2	295.9	276.5
57.5°	453.0	470.0	443.3	398.1	354.7	326.3	308.4	294.4	280.0	263.0	246.4
60°	402.5	416.7	401.6	361.9	323.9	297.5	280.8	270.0	255.5	240.1	227.4
62.5°	353.2	368.4	359.4	327.3	292.2	269.3	254.7	244.6	233.9	220.4	207.2
65°	291.3	301.1	296.8	274.6	249.7	230.2	216.7	209.3	199.4	189.6	177.8
67.5°	223.1	242.2	239.6	227.8	206.3	191.1	182.2	175.7	166.7	159.4	151.4
70°	183.4	201.0	200.7	191.1	179.4	165.2	159.1	153.5	145.4	138.4	131.9
72.5°	150.1	166.2	168.6	161.3	153.3	142.5	136.6	132.8	125.0	120.2	114.9
75°	105.1	116.8	119.9	119.9	116.2	110.7	105.4	103.0	97.4	93.1	90.0
77.5°	68.9	76.3	81.1	82.2	82.8	81.0	76.6	74.9	70.7	69.1	66.1
80°	48.7	53.6	59.2	61.0	62.6	61.9	60.1	58.9	54.9	53.3	52.1
82.5°	33.7	36.4	41.0	45.0	44.6	46.2	44.6	43.6	40.6	40.0	38.7
85°	17.6	17.9	18.5	21.2	22.8	23.4	23.8	23.1	22.2	22.2	20.0
87.5°	8.1	7.6	7.9	7.7	7.6	8.3	8.8	8.7	8.3	7.8	7.4
90°	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7	3.2	4.7	6.1
92.5°	10.4	9.3	8.3	7.7	7.6	7.6	7.5	7.4	7.5	7.6	7.6
95°	12.7	12.5	12.4	14.6	19.0	23.4	27.9	32.3	27.9	23.4	19.0
97.5°	44.7	59.3	73.8	79.8	77.0	74.2	71.5	68.7	71.5	74.2	77.0
100°	61.9	80.0	98.0	105.8	103.5	101.2	98.8	96.4	98.8	101.2	103.5
102.5°	129.4	131.7	134.0	134.4	132.7	130.9	129.2	127.5	129.2	130.9	132.7
105°	182.1	181.5	180.9	180.1	179.4	178.6	177.8	177.0	177.8	178.6	179.4
107.5°	227.0	226.1	225.2	224.6	224.2	223.8	223.4	223.0	223.4	223.8	224.2
110°	257.8	257.0	256.2	255.6	255.2	254.8	254.4	254.1	254.4	254.8	255.2





TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.2	287.9	287.5	286.9	286.2	285.6	284.9	284.2	284.9	285.6	286.2
115°	331.9	332.0	332.2	332.0	331.6	331.3	330.9	330.5	330.9	331.3	331.6
117.5°	375.3	375.0	374.7	374.3	373.8	373.3	372.7	372.2	372.7	373.3	373.8
120°	402.5	402.6	402.7	402.5	402.0	401.5	401.0	400.4	401.0	401.5	402.0
122.5°	428.6	428.5	428.3	428.0	427.7	427.4	427.1	426.8	427.1	427.4	427.7
125°	466.3	466.5	466.8	466.6	466.1	465.6	465.1	464.5	465.1	465.6	466.1
127.5°	502.4	501.8	501.2	500.8	500.7	500.6	500.4	500.3	500.4	500.6	500.7
130°	524.9	524.5	524.1	523.9	523.7	523.6	523.5	523.3	523.5	523.6	523.7
132.5°	546.8	546.3	545.8	545.4	545.2	545.0	544.8	544.5	544.8	545.0	545.2
135°	576.9	576.5	575.9	575.8	575.8	576.0	576.2	576.2	576.2	576.0	575.8
137.5°	606.0	605.5	604.9	604.6	604.5	604.5	604.4	604.4	604.4	604.5	604.5
140°	624.6	624.3	624.0	623.8	623.5	623.2	623.0	622.7	623.0	623.2	623.5
142.5°	641.7	641.5	641.4	641.0	640.6	640.2	639.7	639.2	639.7	640.2	640.6
145°	666.2	666.2	666.2	666.1	665.7	665.3	664.9	664.5	664.9	665.3	665.7
147.5°	687.5	687.7	687.8	687.5	686.7	686.0	685.3	684.6	685.3	686.0	686.7
150°	701.2	701.3	701.5	701.2	700.8	700.2	699.7	699.2	699.7	700.2	700.8
152.5°	712.7	712.9	713.1	713.0	712.6	712.3	711.8	711.4	711.8	712.3	712.6
155°	728.2	728.6	729.0	729.1	729.0	728.8	728.7	728.6	728.7	728.8	729.0
157.5°	741.6	742.0	742.4	742.8	742.8	742.9	743.0	743.1	743.0	742.9	742.8
160°	749.4	749.6	749.6	750.0	750.4	750.8	751.1	751.5	751.1	750.8	750.4
162.5°	756.5	756.6	756.7	757.0	757.6	758.0	758.5	759.0	758.5	758.0	757.6
165°	765.6	765.6	765.6	766.0	766.6	767.2	767.9	768.6	767.9	767.2	766.6
167.5°	772.9	772.9	773.0	773.3	774.0	774.8	775.4	776.1	775.4	774.8	774.0
170°	777.1	777.0	776.8	777.2	777.9	778.7	779.5	780.3	779.5	778.7	777.9
172.5°	779.9	779.8	779.7	780.0	780.8	781.6	782.4	783.2	782.4	781.6	780.8
175°	783.0	782.8	782.8	783.1	783.9	784.7	785.4	786.2	785.4	784.7	783.9
177.5°	784.8	784.7	784.4	784.7	785.4	786.2	786.9	787.6	786.9	786.2	785.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	751.2	748.8	745.5	741.8	737.4	733.5	731.7	733.2	734.0	732.0	731.7
5°	728.3	720.6	714.5	705.2	697.8	691.7	687.3	685.5	686.1	681.2	679.9
7.5°	702.6	693.5	683.4	672.4	662.2	653.2	648.4	645.8	640.6	638.3	634.5
10°	686.1	673.8	663.9	650.9	639.3	628.4	623.2	618.9	613.7	611.2	605.9
12.5°	669.1	654.8	644.0	630.5	618.5	605.5	600.6	592.6	584.3	579.2	572.4
15°	645.1	627.9	614.6	598.6	584.4	569.6	556.3	541.5	536.0	524.3	517.5
17.5°	617.0	599.5	583.1	561.7	539.8	521.4	507.2	493.1	484.6	477.1	473.6
20°	598.6	582.6	559.8	534.8	510.4	490.0	478.6	469.4	460.2	455.0	451.2
22.5°	581.1	560.6	534.1	507.2	482.8	466.9	457.2	447.7	440.2	435.2	430.3
25°	551.8	524.9	496.9	466.0	449.4	435.5	425.0	417.3	412.7	406.2	403.8
27.5°	521.6	489.1	458.1	437.4	420.1	407.4	398.3	392.5	386.7	382.5	379.3
30°	498.4	465.4	437.7	418.0	400.4	389.9	382.5	375.7	371.1	367.7	365.3
32.5°	475.5	442.5	419.1	398.0	384.1	373.9	366.0	360.9	357.3	352.9	351.4
35°	442.3	413.0	392.7	373.6	359.4	350.1	344.0	338.7	335.6	334.5	333.5
37.5°	410.4	386.4	364.6	348.9	336.3	329.0	321.7	319.2	317.0	314.8	315.8
40°	390.2	367.7	348.3	331.7	321.5	313.5	309.1	306.1	304.2	304.2	304.2
42.5°	372.7	350.7	331.8	316.9	306.7	299.9	295.1	292.5	291.9	291.6	293.1
45°	345.5	325.2	306.1	293.7	285.1	278.3	275.5	273.4	273.4	274.6	275.0
47.5°	318.6	299.5	284.2	270.4	262.4	258.3	255.8	254.7	254.8	256.0	257.5
50°	302.1	283.3	268.2	255.8	248.4	244.4	242.2	241.6	242.2	242.2	244.4
52.5°	284.1	267.2	252.4	242.0	233.6	229.9	228.7	227.8	228.2	229.2	230.1
55°	257.7	242.6	228.4	218.6	212.4	209.9	207.2	207.5	206.8	207.5	207.5
57.5°	231.2	217.7	204.5	196.6	191.2	187.7	184.7	185.4	184.6	184.4	183.9
60°	214.2	199.4	188.9	181.9	175.7	172.6	169.8	170.5	169.5	168.9	167.7
62.5°	195.7	183.4	173.4	166.6	161.6	158.0	155.3	154.6	152.5	150.4	147.7
65°	168.9	158.8	149.8	143.3	138.7	135.9	133.8	131.9	127.3	122.4	119.9
67.5°	142.8	135.5	127.1	121.7	118.0	114.3	110.2	107.0	102.7	100.0	98.5
70°	126.0	119.0	111.9	106.6	102.7	99.3	94.6	92.4	89.4	88.2	86.6
72.5°	110.0	103.5	96.8	92.1	87.9	85.2	81.6	79.4	78.0	77.6	76.0
75°	85.7	80.5	75.5	71.2	67.8	66.0	64.4	62.9	62.3	59.5	57.9
77.5°	62.5	59.0	56.0	52.9	50.5	49.3	46.3	44.5	43.5	42.1	41.8
80°	48.7	46.3	43.2	41.3	37.9	36.7	35.4	35.2	34.9	34.5	34.2
82.5°	36.6	34.1	31.1	29.9	29.1	28.3	27.6	27.3	26.9	27.1	27.1
85°	18.5	17.3	17.3	17.0	16.6	16.3	16.0	16.0	15.7	16.0	15.7
87.5°	7.7	7.7	7.8	7.6	8.1	8.2	8.2	8.3	8.7	8.4	8.5
90°	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5	15.3	16.1	16.6
92.5°	7.7	8.3	9.3	10.4	11.4	12.4	13.2	14.0	14.8	15.6	16.0
95°	14.6	12.4	12.5	12.7	12.8	12.9	13.7	14.5	15.3	16.1	16.6
97.5°	79.8	73.8	59.3	44.7	30.1	15.5	15.6	15.7	15.8	15.8	15.9
100°	105.8	98.0	80.0	61.9	43.9	25.9	23.7	21.5	19.2	17.0	15.9
102.5°	134.4	134.0	131.7	129.4	127.0	124.7	100.7	76.8	52.8	28.8	16.8
105°	180.1	180.9	181.5	182.1	182.8	183.5	184.7	185.8	187.0	188.1	186.4
107.5°	224.6	225.2	226.1	227.0	227.8	228.7	229.3	229.9	230.4	231.1	231.6
110°	255.6	256.2	257.0	257.8	258.6	259.3	259.6	259.8	260.1	260.4	260.7



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	286.9	287.5	287.9	288.2	288.6	289.0	288.9	288.8	288.8	288.8	289.0
115°	332.0	332.2	332.0	331.9	331.8	331.6	331.9	332.2	332.4	332.7	332.8
117.5°	374.3	374.7	375.0	375.3	375.6	375.9	375.8	375.7	375.7	375.7	375.6
120°	402.5	402.7	402.6	402.5	402.3	402.2	402.5	402.7	403.0	403.2	403.2
122.5°	428.0	428.3	428.5	428.6	428.8	429.0	429.2	429.4	429.5	429.7	429.6
125°	466.6	466.8	466.5	466.3	466.0	465.7	466.1	466.5	466.9	467.3	467.5
127.5°	500.8	501.2	501.8	502.4	503.0	503.6	503.5	503.4	503.4	503.3	503.2
130°	523.9	524.1	524.5	524.9	525.3	525.7	525.9	525.9	526.1	526.2	526.2
132.5°	545.4	545.8	546.3	546.8	547.3	547.8	548.0	548.0	548.2	548.3	548.3
135°	575.8	575.9	576.5	576.9	577.5	578.1	578.3	578.5	578.8	579.1	579.3
137.5°	604.6	604.9	605.5	606.0	606.7	607.2	607.4	607.8	608.1	608.3	608.5
140°	623.8	624.0	624.3	624.6	624.8	625.1	625.4	625.8	626.2	626.6	626.9
142.5°	641.0	641.4	641.5	641.7	641.8	642.0	642.3	642.6	642.9	643.2	643.3
145°	666.1	666.2	666.2	666.2	666.2	666.2	666.4	666.5	666.6	666.8	666.9
147.5°	687.5	687.8	687.7	687.5	687.4	687.3	687.4	687.5	687.6	687.7	687.9
150°	701.2	701.5	701.3	701.2	701.1	700.9	700.9	700.9	700.9	700.9	701.0
152.5°	713.0	713.1	712.9	712.7	712.5	712.3	712.4	712.6	712.8	713.0	713.1
155°	729.1	729.0	728.6	728.2	727.8	727.4	727.9	728.4	729.0	729.4	729.5
157.5°	742.8	742.4	742.0	741.6	741.1	740.7	741.3	742.0	742.8	743.4	743.4
160°	750.0	749.6	749.6	749.4	749.2	749.2	750.0	750.8	751.5	752.3	752.3
162.5°	757.0	756.7	756.6	756.5	756.3	756.2	757.0	757.8	758.5	759.3	759.3
165°	766.0	765.6	765.6	765.6	765.6	765.6	766.7	767.7	768.7	769.8	769.8
167.5°	773.3	773.0	772.9	772.9	772.8	772.7	773.8	775.0	776.1	777.3	777.2
170°	777.2	776.8	777.0	777.1	777.2	777.4	778.4	779.4	780.5	781.6	781.4
172.5°	780.0	779.7	779.8	779.9	780.1	780.2	781.3	782.3	783.3	784.3	784.2
175°	783.1	782.8	782.8	783.0	783.2	783.2	784.4	785.6	786.8	788.0	787.7
177.5°	784.7	784.4	784.7	784.8	785.1	785.2	786.1	787.0	787.7	788.6	788.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	730.2	730.7	729.0	728.5	729.0	730.7	730.2	731.7	732.0	734.0	733.2
5°	677.5	676.8	675.3	675.7	675.3	676.8	677.5	679.9	681.2	686.1	685.5
7.5°	632.3	629.9	630.7	628.1	630.7	629.9	632.3	634.5	638.3	640.6	645.8
10°	604.8	601.3	598.6	596.1	598.6	601.3	604.8	605.9	611.2	613.7	618.9
12.5°	567.0	564.1	560.3	561.1	560.3	564.1	567.0	572.4	579.2	584.3	592.6
15°	513.5	508.9	501.5	502.4	501.5	508.9	513.5	517.5	524.3	536.0	541.5
17.5°	468.2	468.3	464.9	465.6	464.9	468.3	468.2	473.6	477.1	484.6	493.1
20°	444.7	442.6	442.9	442.0	442.9	442.6	444.7	451.2	455.0	460.2	469.4
22.5°	428.5	425.9	423.7	421.8	423.7	425.9	428.5	430.3	435.2	440.2	447.7
25°	401.0	399.2	396.4	395.8	396.4	399.2	401.0	403.8	406.2	412.7	417.3
27.5°	376.8	376.4	375.3	373.9	375.3	376.4	376.8	379.3	382.5	386.7	392.5
30°	362.7	362.2	361.6	360.6	361.6	362.2	362.7	365.3	367.7	371.1	375.7
32.5°	350.2	349.8	349.2	349.3	349.2	349.8	350.2	351.4	352.9	357.3	360.9
35°	332.2	331.9	331.4	331.1	331.4	331.9	332.2	333.5	334.5	335.6	338.7
37.5°	315.5	316.3	315.9	315.8	315.9	316.3	315.5	315.8	314.8	317.0	319.2
40°	303.9	304.2	304.8	304.5	304.8	304.2	303.9	304.2	304.2	304.2	306.1
42.5°	294.3	294.4	295.2	294.1	295.2	294.4	294.3	293.1	291.6	291.9	292.5
45°	277.1	278.9	278.6	278.6	278.6	278.9	277.1	275.0	274.6	273.4	273.4
47.5°	258.3	259.9	260.3	260.2	260.3	259.9	258.3	257.5	256.0	254.8	254.7
50°	246.0	245.3	246.3	246.0	246.3	245.3	246.0	244.4	242.2	242.2	241.6
52.5°	230.9	231.1	231.0	230.7	231.0	231.1	230.9	230.1	229.2	228.2	227.8
55°	207.7	208.0	207.5	207.7	207.5	208.0	207.7	207.5	207.5	206.8	207.5
57.5°	182.6	181.1	181.7	181.0	181.7	181.1	182.6	183.9	184.4	184.6	185.4
60°	164.6	162.2	161.5	160.3	161.5	162.2	164.6	167.7	168.9	169.5	170.5
62.5°	144.3	142.7	140.5	141.6	140.5	142.7	144.3	147.7	150.4	152.5	154.6
65°	117.4	116.2	115.3	116.5	115.3	116.2	117.4	119.9	122.4	127.3	131.9
67.5°	97.2	96.6	96.6	95.9	96.6	96.6	97.2	98.5	100.0	102.7	107.0
70°	86.6	85.7	85.7	85.1	85.7	85.7	86.6	86.6	88.2	89.4	92.4
72.5°	75.7	74.9	75.1	74.7	75.1	74.9	75.7	76.0	77.6	78.0	79.4
75°	56.1	54.6	54.6	54.9	54.6	54.6	56.1	57.9	59.5	62.3	62.9
77.5°	41.8	41.5	42.0	41.4	42.0	41.5	41.8	41.8	42.1	43.5	44.5
80°	34.2	33.9	33.6	34.5	33.6	33.9	34.2	34.2	34.5	34.9	35.2
82.5°	26.5	26.5	26.5	27.6	26.5	26.5	26.5	27.1	27.1	26.9	27.3
85°	16.0	15.4	16.0	15.4	16.0	15.4	16.0	15.7	16.0	15.7	16.0
87.5°	9.0	8.9	8.6	9.0	8.6	8.9	9.0	8.5	8.4	8.7	8.3
90°	16.9	17.1	17.3	17.7	17.3	17.1	16.9	16.6	16.1	15.3	14.5
92.5°	16.1	16.2	16.2	16.2	16.2	16.2	16.1	16.0	15.6	14.8	14.0
95°	16.6	16.8	17.0	17.0	17.0	16.8	16.6	16.6	16.1	15.3	14.5
97.5°	16.1	16.2	16.3	16.5	16.3	16.2	16.1	15.9	15.8	15.8	15.7
100°	16.1	16.2	16.3	16.5	16.3	16.2	16.1	15.9	17.0	19.2	21.5
102.5°	16.9	16.9	16.9	17.0	16.9	16.9	16.9	16.8	28.8	52.8	76.8
105°	181.7	177.0	172.3	167.6	172.3	177.0	181.7	186.4	188.1	187.0	185.8
107.5°	232.1	232.6	233.1	233.5	233.1	232.6	232.1	231.6	231.1	230.4	229.9
110°	261.1	261.5	261.9	262.3	261.9	261.5	261.1	260.7	260.4	260.1	259.8



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	289.5	289.9	290.5	291.0	290.5	289.9	289.5	289.0	288.8	288.8	288.8
115°	332.8	332.8	332.8	332.8	332.8	332.8	332.8	332.8	332.7	332.4	332.2
117.5°	375.6	375.5	375.4	375.4	375.4	375.5	375.6	375.6	375.7	375.7	375.7
120°	403.0	402.7	402.5	402.2	402.5	402.7	403.0	403.2	403.2	403.0	402.7
122.5°	429.4	429.0	428.8	428.6	428.8	429.0	429.4	429.6	429.7	429.5	429.4
125°	467.7	467.8	467.9	468.1	467.9	467.8	467.7	467.5	467.3	466.9	466.5
127.5°	503.1	503.0	502.9	502.8	502.9	503.0	503.1	503.2	503.3	503.4	503.4
130°	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.1	525.9
132.5°	548.3	548.1	548.0	548.0	548.0	548.1	548.3	548.3	548.3	548.2	548.0
135°	579.6	579.9	580.1	580.4	580.1	579.9	579.6	579.3	579.1	578.8	578.5
137.5°	608.4	608.3	608.2	608.2	608.2	608.3	608.4	608.5	608.3	608.1	607.8
140°	627.0	627.2	627.3	627.4	627.3	627.2	627.0	626.9	626.6	626.2	625.8
142.5°	643.3	643.3	643.4	643.4	643.4	643.3	643.3	643.3	643.2	642.9	642.6
145°	667.2	667.5	667.7	668.0	667.7	667.5	667.2	666.9	666.8	666.6	666.5
147.5°	687.9	688.1	688.2	688.3	688.2	688.1	687.9	687.9	687.7	687.6	687.5
150°	701.2	701.2	701.4	701.5	701.4	701.2	701.2	701.0	700.9	700.9	700.9
152.5°	713.0	713.0	712.9	712.8	712.9	713.0	713.0	713.1	713.0	712.8	712.6
155°	729.1	728.7	728.3	728.0	728.3	728.7	729.1	729.5	729.4	729.0	728.4
157.5°	742.8	742.0	741.3	740.7	741.3	742.0	742.8	743.4	743.4	742.8	742.0
160°	751.5	750.8	750.0	749.2	750.0	750.8	751.5	752.3	752.3	751.5	750.8
162.5°	758.4	757.5	756.6	755.7	756.6	757.5	758.4	759.3	759.3	758.5	757.8
165°	768.6	767.4	766.2	765.0	766.2	767.4	768.6	769.8	769.8	768.7	767.7
167.5°	775.9	774.6	773.2	772.0	773.2	774.6	775.9	777.2	777.3	776.1	775.0
170°	780.1	778.8	777.5	776.2	777.5	778.8	780.1	781.4	781.6	780.5	779.4
172.5°	782.8	781.4	780.0	778.6	780.0	781.4	782.8	784.2	784.3	783.3	782.3
175°	786.2	784.7	783.1	781.5	783.1	784.7	786.2	787.7	788.0	786.8	785.6
177.5°	787.1	785.8	784.7	783.4	784.7	785.8	787.1	788.4	788.6	787.7	787.0
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	731.7	733.5	737.4	741.8	745.5	748.8	751.2	754.6	757.9	762.3	766.5
5°	687.3	691.7	697.8	705.2	714.5	720.6	728.3	735.1	745.0	754.9	764.4
7.5°	648.4	653.2	662.2	672.4	683.4	693.5	702.6	714.5	727.6	742.0	758.0
10°	623.2	628.4	639.3	650.9	663.9	673.8	686.1	700.3	715.1	732.6	752.3
12.5°	600.6	605.5	618.5	630.5	644.0	654.8	669.1	683.5	703.2	722.3	744.7
15°	556.3	569.6	584.4	598.6	614.6	627.9	645.1	659.9	678.7	705.5	731.1
17.5°	507.2	521.4	539.8	561.7	583.1	599.5	617.0	635.4	657.8	685.2	714.7
20°	478.6	490.0	510.4	534.8	559.8	582.6	598.6	618.9	642.1	671.6	702.1
22.5°	457.2	466.9	482.8	507.2	534.1	560.6	581.1	601.2	626.8	656.3	689.6
25°	425.0	435.5	449.4	466.0	496.9	524.9	551.8	574.8	602.0	631.5	668.5
27.5°	398.3	407.4	420.1	437.4	458.1	489.1	521.6	548.0	575.8	607.5	644.5
30°	382.5	389.9	400.4	418.0	437.7	465.4	498.4	529.3	557.3	590.3	628.8
32.5°	366.0	373.9	384.1	398.0	419.1	442.5	475.5	509.2	539.0	572.7	610.5
35°	344.0	350.1	359.4	373.6	392.7	413.0	442.3	477.1	508.6	544.6	580.7
37.5°	321.7	329.0	336.3	348.9	364.6	386.4	410.4	446.0	480.9	513.7	549.0
40°	309.1	313.5	321.5	331.7	348.3	367.7	390.2	425.0	459.9	492.6	528.0
42.5°	295.1	299.9	306.7	316.9	331.8	350.7	372.7	402.8	439.2	470.9	503.1
45°	275.5	278.3	285.1	293.7	306.1	325.2	345.5	372.3	406.5	436.7	465.1
47.5°	255.8	258.3	262.4	270.4	284.2	299.5	318.6	342.6	372.6	402.8	426.8
50°	242.2	244.4	248.4	255.8	268.2	283.3	302.1	323.6	350.5	379.5	399.4
52.5°	228.7	229.9	233.6	242.0	252.4	267.2	284.1	303.9	329.0	353.1	373.4
55°	207.2	209.9	212.4	218.6	228.4	242.6	257.7	276.5	295.9	316.2	333.5
57.5°	184.7	187.7	191.2	196.6	204.5	217.7	231.2	246.4	263.0	280.0	294.4
60°	169.8	172.6	175.7	181.9	188.9	199.4	214.2	227.4	240.1	255.5	270.0
62.5°	155.3	158.0	161.6	166.6	173.4	183.4	195.7	207.2	220.4	233.9	244.6
65°	133.8	135.9	138.7	143.3	149.8	158.8	168.9	177.8	189.6	199.4	209.3
67.5°	110.2	114.3	118.0	121.7	127.1	135.5	142.8	151.4	159.4	166.7	175.7
70°	94.6	99.3	102.7	106.6	111.9	119.0	126.0	131.9	138.4	145.4	153.5
72.5°	81.6	85.2	87.9	92.1	96.8	103.5	110.0	114.9	120.2	125.0	132.8
75°	64.4	66.0	67.8	71.2	75.5	80.5	85.7	90.0	93.1	97.4	103.0
77.5°	46.3	49.3	50.5	52.9	56.0	59.0	62.5	66.1	69.1	70.7	74.9
80°	35.4	36.7	37.9	41.3	43.2	46.3	48.7	52.1	53.3	54.9	58.9
82.5°	27.6	28.3	29.1	29.9	31.1	34.1	36.6	38.7	40.0	40.6	43.6
85°	16.0	16.3	16.6	17.0	17.3	17.3	18.5	20.0	22.2	22.2	23.1
87.5°	8.2	8.2	8.1	7.6	7.8	7.7	7.7	7.4	7.8	8.3	8.7
90°	13.7	12.9	11.9	10.9	9.8	8.8	7.5	6.1	4.7	3.2	1.7
92.5°	13.2	12.4	11.4	10.4	9.3	8.3	7.7	7.6	7.6	7.5	7.4
95°	13.7	12.9	12.8	12.7	12.5	12.4	14.6	19.0	23.4	27.9	32.3
97.5°	15.6	15.5	30.1	44.7	59.3	73.8	79.8	77.0	74.2	71.5	68.7
100°	23.7	25.9	43.9	61.9	80.0	98.0	105.8	103.5	101.2	98.8	96.4
102.5°	100.7	124.7	127.0	129.4	131.7	134.0	134.4	132.7	130.9	129.2	127.5
105°	184.7	183.5	182.8	182.1	181.5	180.9	180.1	179.4	178.6	177.8	177.0
107.5°	229.3	228.7	227.8	227.0	226.1	225.2	224.6	224.2	223.8	223.4	223.0
110°	259.6	259.3	258.6	257.8	257.0	256.2	255.6	255.2	254.8	254.4	254.1



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	288.9	289.0	288.6	288.2	287.9	287.5	286.9	286.2	285.6	284.9	284.2
115°	331.9	331.6	331.8	331.9	332.0	332.2	332.0	331.6	331.3	330.9	330.5
117.5°	375.8	375.9	375.6	375.3	375.0	374.7	374.3	373.8	373.3	372.7	372.2
120°	402.5	402.2	402.3	402.5	402.6	402.7	402.5	402.0	401.5	401.0	400.4
122.5°	429.2	429.0	428.8	428.6	428.5	428.3	428.0	427.7	427.4	427.1	426.8
125°	466.1	465.7	466.0	466.3	466.5	466.8	466.6	466.1	465.6	465.1	464.5
127.5°	503.5	503.6	503.0	502.4	501.8	501.2	500.8	500.7	500.6	500.4	500.3
130°	525.9	525.7	525.3	524.9	524.5	524.1	523.9	523.7	523.6	523.5	523.3
132.5°	548.0	547.8	547.3	546.8	546.3	545.8	545.4	545.2	545.0	544.8	544.5
135°	578.3	578.1	577.5	576.9	576.5	575.9	575.8	575.8	576.0	576.2	576.2
137.5°	607.4	607.2	606.7	606.0	605.5	604.9	604.6	604.5	604.5	604.4	604.4
140°	625.4	625.1	624.8	624.6	624.3	624.0	623.8	623.5	623.2	623.0	622.7
142.5°	642.3	642.0	641.8	641.7	641.5	641.4	641.0	640.6	640.2	639.7	639.2
145°	666.4	666.2	666.2	666.2	666.2	666.2	666.1	665.7	665.3	664.9	664.5
147.5°	687.4	687.3	687.4	687.5	687.7	687.8	687.5	686.7	686.0	685.3	684.6
150°	700.9	700.9	701.1	701.2	701.3	701.5	701.2	700.8	700.2	699.7	699.2
152.5°	712.4	712.3	712.5	712.7	712.9	713.1	713.0	712.6	712.3	711.8	711.4
155°	727.9	727.4	727.8	728.2	728.6	729.0	729.1	729.0	728.8	728.7	728.6
157.5°	741.3	740.7	741.1	741.6	742.0	742.4	742.8	742.8	742.9	743.0	743.1
160°	750.0	749.2	749.2	749.4	749.6	749.6	750.0	750.4	750.8	751.1	751.5
162.5°	757.0	756.2	756.3	756.5	756.6	756.7	757.0	757.6	758.0	758.5	759.0
165°	766.7	765.6	765.6	765.6	765.6	765.6	766.0	766.6	767.2	767.9	768.6
167.5°	773.8	772.7	772.8	772.9	772.9	773.0	773.3	774.0	774.8	775.4	776.1
170°	778.4	777.4	777.2	777.1	777.0	776.8	777.2	777.9	778.7	779.5	780.3
172.5°	781.3	780.2	780.1	779.9	779.8	779.7	780.0	780.8	781.6	782.4	783.2
175°	784.4	783.2	783.2	783.0	782.8	782.8	783.1	783.9	784.7	785.4	786.2
177.5°	786.1	785.2	785.1	784.8	784.7	784.4	784.7	785.4	786.2	786.9	787.6
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	769.7	771.9	774.4	779.0	783.0	784.7	788.2	790.7	789.9	793.4	799.3
5°	772.7	781.0	790.6	800.4	811.5	820.8	828.2	835.6	841.5	848.5	859.0
7.5°	772.2	787.0	803.1	820.8	839.0	854.7	869.3	884.1	897.1	911.6	930.3
10°	770.2	790.0	810.0	833.1	856.3	878.1	897.9	916.3	933.9	952.7	976.4
12.5°	768.0	790.7	814.9	842.7	871.6	897.9	921.1	947.7	969.6	993.9	1021.4
15°	758.2	788.8	821.7	857.8	892.3	927.7	959.5	992.2	1022.7	1051.6	1086.2
17.5°	747.0	782.2	821.1	863.7	905.2	948.2	986.0	1027.1	1058.3	1097.2	1129.3
20°	737.9	775.8	817.4	865.1	912.4	960.1	1001.7	1043.6	1078.8	1117.9	1158.6
22.5°	726.8	768.4	813.5	862.9	912.4	964.6	1010.6	1052.3	1095.8	1139.9	1181.8
25°	708.9	752.1	799.9	854.1	910.8	964.1	1013.4	1065.2	1112.1	1159.8	1197.5
27.5°	687.0	732.3	782.7	838.6	896.8	951.4	1009.5	1064.7	1111.8	1157.8	1190.6
30°	669.5	717.2	765.6	822.4	882.7	941.4	1003.5	1058.8	1108.3	1149.7	1168.2
32.5°	651.5	696.8	746.6	804.1	866.0	929.0	990.8	1047.2	1093.1	1117.8	1118.3
35°	620.1	662.7	714.5	770.9	834.3	902.8	965.4	1020.8	1048.8	1051.1	1020.8
37.5°	586.0	625.0	673.9	730.4	799.9	868.0	931.8	968.8	978.3	946.9	891.0
40°	561.6	597.6	644.8	702.7	771.8	842.1	900.3	927.4	917.6	866.7	804.5
42.5°	535.9	569.5	615.0	672.2	741.5	812.5	862.1	876.6	850.5	791.8	718.9
45°	494.1	524.9	569.9	627.6	694.1	760.7	798.3	790.9	747.4	677.8	596.1
47.5°	450.5	480.3	520.8	574.1	642.3	699.7	725.2	702.9	641.0	564.4	498.0
50°	421.7	452.2	489.5	540.3	602.6	658.1	674.4	640.5	571.7	498.1	437.0
52.5°	393.3	419.4	455.9	505.0	564.6	611.5	620.1	581.1	510.1	444.1	390.0
55°	350.1	373.9	404.7	450.9	502.4	542.2	537.6	487.3	422.9	366.5	323.9
57.5°	308.4	326.3	354.7	398.1	443.3	470.0	453.0	410.3	350.2	304.0	268.2
60°	280.8	297.5	323.9	361.9	401.6	416.7	402.5	356.0	308.6	266.3	236.1
62.5°	254.7	269.3	292.2	327.3	359.4	368.4	353.2	312.6	269.8	233.8	208.7
65°	216.7	230.2	249.7	274.6	296.8	301.1	291.3	249.7	217.3	187.1	169.8
67.5°	182.2	191.1	206.3	227.8	239.6	242.2	223.1	196.9	168.4	149.9	136.9
70°	159.1	165.2	179.4	191.1	200.7	201.0	183.4	162.4	140.5	125.5	115.9
72.5°	136.6	142.5	153.3	161.3	168.6	166.2	150.1	133.6	115.9	104.5	97.4
75°	105.4	110.7	116.2	119.9	119.9	116.8	105.1	92.8	82.6	75.8	73.7
77.5°	76.6	81.0	82.8	82.2	81.1	76.3	68.9	60.8	57.2	54.0	52.4
80°	60.1	61.9	62.6	61.0	59.2	53.6	48.7	45.3	41.9	40.7	40.1
82.5°	44.6	46.2	44.6	45.0	41.0	36.4	33.7	32.5	31.1	30.6	29.9
85°	23.8	23.4	22.8	21.2	18.5	17.9	17.6	17.3	16.6	17.0	16.3
87.5°	8.8	8.3	7.6	7.7	7.9	7.6	8.1	8.3	8.5	8.4	9.0
90°	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7	14.5
92.5°	7.5	7.6	7.6	7.7	8.3	9.3	10.4	11.4	12.4	13.2	14.0
95°	27.9	23.4	19.0	14.6	12.4	12.5	12.7	12.8	12.9	13.7	14.5
97.5°	71.5	74.2	77.0	79.8	73.8	59.3	44.7	30.1	15.5	15.6	15.7
100°	98.8	101.2	103.5	105.8	98.0	80.0	61.9	43.9	25.9	23.7	21.5
102.5°	129.2	130.9	132.7	134.4	134.0	131.7	129.4	127.0	124.7	100.7	76.8
105°	177.8	178.6	179.4	180.1	180.9	181.5	182.1	182.8	183.5	184.7	185.8
107.5°	223.4	223.8	224.2	224.6	225.2	226.1	227.0	227.8	228.7	229.3	229.9
110°	254.4	254.8	255.2	255.6	256.2	257.0	257.8	258.6	259.3	259.6	259.8





TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.9	285.6	286.2	286.9	287.5	287.9	288.2	288.6	289.0	288.9	288.8
115°	330.9	331.3	331.6	332.0	332.2	332.0	331.9	331.8	331.6	331.9	332.2
117.5°	372.7	373.3	373.8	374.3	374.7	375.0	375.3	375.6	375.9	375.8	375.7
120°	401.0	401.5	402.0	402.5	402.7	402.6	402.5	402.3	402.2	402.5	402.7
122.5°	427.1	427.4	427.7	428.0	428.3	428.5	428.6	428.8	429.0	429.2	429.4
125°	465.1	465.6	466.1	466.6	466.8	466.5	466.3	466.0	465.7	466.1	466.5
127.5°	500.4	500.6	500.7	500.8	501.2	501.8	502.4	503.0	503.6	503.5	503.4
130°	523.5	523.6	523.7	523.9	524.1	524.5	524.9	525.3	525.7	525.9	525.9
132.5°	544.8	545.0	545.2	545.4	545.8	546.3	546.8	547.3	547.8	548.0	548.0
135°	576.2	576.0	575.8	575.8	575.9	576.5	576.9	577.5	578.1	578.3	578.5
137.5°	604.4	604.5	604.5	604.6	604.9	605.5	606.0	606.7	607.2	607.4	607.8
140°	623.0	623.2	623.5	623.8	624.0	624.3	624.6	624.8	625.1	625.4	625.8
142.5°	639.7	640.2	640.6	641.0	641.4	641.5	641.7	641.8	642.0	642.3	642.6
145°	664.9	665.3	665.7	666.1	666.2	666.2	666.2	666.2	666.2	666.4	666.5
147.5°	685.3	686.0	686.7	687.5	687.8	687.7	687.5	687.4	687.3	687.4	687.5
150°	699.7	700.2	700.8	701.2	701.5	701.3	701.2	701.1	700.9	700.9	700.9
152.5°	711.8	712.3	712.6	713.0	713.1	712.9	712.7	712.5	712.3	712.4	712.6
155°	728.7	728.8	729.0	729.1	729.0	728.6	728.2	727.8	727.4	727.9	728.4
157.5°	743.0	742.9	742.8	742.8	742.4	742.0	741.6	741.1	740.7	741.3	742.0
160°	751.1	750.8	750.4	750.0	749.6	749.6	749.4	749.2	749.2	750.0	750.8
162.5°	758.5	758.0	757.6	757.0	756.7	756.6	756.5	756.3	756.2	757.0	757.8
165°	767.9	767.2	766.6	766.0	765.6	765.6	765.6	765.6	765.6	766.7	767.7
167.5°	775.4	774.8	774.0	773.3	773.0	772.9	772.9	772.8	772.7	773.8	775.0
170°	779.5	778.7	777.9	777.2	776.8	777.0	777.1	777.2	777.4	778.4	779.4
172.5°	782.4	781.6	780.8	780.0	779.7	779.8	779.9	780.1	780.2	781.3	782.3
175°	785.4	784.7	783.9	783.1	782.8	782.8	783.0	783.2	783.2	784.4	785.6
177.5°	786.9	786.2	785.4	784.7	784.4	784.7	784.8	785.1	785.2	786.1	787.0
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2	786.2



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	802.5	803.5	804.2	806.7	806.9	809.1	806.9
5°	868.9	873.2	880.0	886.8	887.4	891.7	884.0
7.5°	943.3	953.3	959.6	970.5	974.9	977.6	973.1
10°	994.7	1003.9	1020.3	1028.3	1036.3	1037.4	1033.8
12.5°	1044.2	1058.8	1071.7	1087.0	1086.6	1097.4	1093.4
15°	1110.2	1125.3	1143.2	1160.2	1166.3	1166.3	1171.2
17.5°	1157.3	1185.0	1203.5	1216.8	1231.4	1233.9	1232.2
20°	1189.1	1219.0	1238.7	1256.0	1265.9	1268.7	1268.7
22.5°	1212.8	1238.3	1257.5	1273.0	1281.2	1284.4	1283.4
25°	1229.2	1251.1	1262.8	1267.4	1269.6	1268.9	1263.1
27.5°	1206.7	1205.8	1198.3	1184.2	1173.5	1167.0	1159.7
30°	1163.9	1147.8	1129.3	1109.0	1082.8	1062.7	1056.6
32.5°	1100.0	1064.0	1032.7	998.8	970.6	950.5	942.1
35°	976.4	919.4	872.9	832.2	802.6	784.1	777.9
37.5°	829.9	774.7	717.1	677.6	653.1	634.4	627.4
40°	736.7	676.5	626.3	589.3	564.0	545.9	545.6
42.5°	651.6	594.2	546.9	520.3	493.1	481.0	480.9
45°	533.5	487.6	447.5	426.6	410.3	400.4	397.6
47.5°	441.7	403.8	377.1	360.4	347.1	340.8	336.7
50°	390.2	357.0	335.6	321.2	313.8	305.8	305.1
52.5°	347.3	320.4	303.9	292.1	282.7	277.9	278.1
55°	291.9	270.6	258.9	249.9	242.6	238.8	237.3
57.5°	245.9	230.0	221.4	213.3	210.1	207.2	206.4
60°	217.3	206.5	198.5	192.0	187.4	186.5	186.2
62.5°	193.6	182.4	176.8	171.8	168.4	167.0	166.4
65°	159.6	151.3	146.4	142.4	141.2	139.0	138.7
67.5°	128.7	123.7	120.5	117.7	116.0	115.9	115.9
70°	109.7	106.9	104.2	102.7	101.7	101.1	101.1
72.5°	93.5	91.4	89.1	88.3	88.2	87.5	87.3
75°	71.2	69.1	69.3	67.8	66.5	65.0	64.1
77.5°	50.5	49.0	48.6	48.5	47.4	47.2	47.7
80°	39.1	37.6	37.3	37.6	37.3	36.4	36.4
82.5°	29.8	28.5	28.2	28.0	27.6	28.0	27.5
85°	16.0	15.4	15.4	15.4	16.0	15.7	15.4
87.5°	8.7	8.6	9.0	8.8	8.9	8.6	9.0
90°	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	14.8	15.6	16.0	16.1	16.2	16.2	16.2
95°	15.3	16.1	16.6	16.6	16.8	17.0	17.0
97.5°	15.8	15.8	15.9	16.1	16.2	16.3	16.5
100°	19.2	17.0	15.9	16.1	16.2	16.3	16.5
102.5°	52.8	28.8	16.8	16.9	16.9	16.9	17.0
105°	187.0	188.1	186.4	181.7	177.0	172.3	167.6
107.5°	230.4	231.1	231.6	232.1	232.6	233.1	233.5
110°	260.1	260.4	260.7	261.1	261.5	261.9	262.3



TEST NUMBER: P333039-927

CATALOG NUMBER: S124RDIW-S575D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	288.8	288.8	289.0	289.5	289.9	290.5	291.0
115°	332.4	332.7	332.8	332.8	332.8	332.8	332.8
117.5°	375.7	375.7	375.6	375.6	375.5	375.4	375.4
120°	403.0	403.2	403.2	403.0	402.7	402.5	402.2
122.5°	429.5	429.7	429.6	429.4	429.0	428.8	428.6
125°	466.9	467.3	467.5	467.7	467.8	467.9	468.1
127.5°	503.4	503.3	503.2	503.1	503.0	502.9	502.8
130°	526.1	526.2	526.2	526.2	526.2	526.2	526.2
132.5°	548.2	548.3	548.3	548.3	548.1	548.0	548.0
135°	578.8	579.1	579.3	579.6	579.9	580.1	580.4
137.5°	608.1	608.3	608.5	608.4	608.3	608.2	608.2
140°	626.2	626.6	626.9	627.0	627.2	627.3	627.4
142.5°	642.9	643.2	643.3	643.3	643.3	643.4	643.4
145°	666.6	666.8	666.9	667.2	667.5	667.7	668.0
147.5°	687.6	687.7	687.9	687.9	688.1	688.2	688.3
150°	700.9	700.9	701.0	701.2	701.2	701.4	701.5
152.5°	712.8	713.0	713.1	713.0	713.0	712.9	712.8
155°	729.0	729.4	729.5	729.1	728.7	728.3	728.0
157.5°	742.8	743.4	743.4	742.8	742.0	741.3	740.7
160°	751.5	752.3	752.3	751.5	750.8	750.0	749.2
162.5°	758.5	759.3	759.3	758.4	757.5	756.6	755.7
165°	768.7	769.8	769.8	768.6	767.4	766.2	765.0
167.5°	776.1	777.3	777.2	775.9	774.6	773.2	772.0
170°	780.5	781.6	781.4	780.1	778.8	777.5	776.2
172.5°	783.3	784.3	784.2	782.8	781.4	780.0	778.6
175°	786.8	788.0	787.7	786.2	784.7	783.1	781.5
177.5°	787.7	788.6	788.4	787.1	785.8	784.7	783.4
180°	786.2	786.2	786.2	786.2	786.2	786.2	786.2

(END OF REPORT)