

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332810-830

Luminaire Tested: **S124DIW-S1020D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332810-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D470U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5707.3 lumens  
Efficiency: N/A  
Efficacy: 123.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.2	2.7
10°-20°	431.5	7.6
20°-30°	635.2	11.1
30°-40°	738.4	12.9
40°-50°	738.4	12.9
50°-60°	645.9	11.3
60°-70°	479.7	8.4
70°-80°	272.5	4.8
80°-90°	80.3	1.4
90°-100°	36.4	0.6
100°-110°	107.9	1.9
110°-120°	183.1	3.2
120°-130°	241.5	4.2
130°-140°	271.2	4.8
140°-150°	266.5	4.7
150°-160°	224.1	3.9
160°-170°	149.1	2.6
170°-180°	52.2	0.9
0°-30°	1219.8	21.4
0°-40°	1958.2	34.3
0°-60°	3342.6	58.6
0°-90°	4175.1	73.2
90°-120°	327.5	5.7
90°-150°	1106.7	19.4
90°-180°	1532.0	26.8
0°-180°	5707.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	1	6	9	12	13	5
95°	26	29	32	34	34	29
105°	100	100	102	103	104	106
115°	186	186	185	185	184	184
125°	271	271	271	270	269	242
135°	350	352	352	352	350	270
145°	425	427	427	427	425	266
155°	487	487	486	488	486	224
165°	530	529	528	530	529	149
175°	551	549	549	552	549	52
180°	552	552	552	552	552	



TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.3	27.3	27.3	27.3	27.2	27.2	27.1	27.1	27.0	26.9	27.1
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	9.1	10.4	11.5	12.7	13.9	14.8	15.4	15.8	16.4	16.9	17.2
95°	25.6	26.5	27.3	28.2	29.0	29.8	30.4	31.1	31.8	32.4	32.7
97.5°	44.8	45.4	46.1	46.8	47.5	48.3	49.0	49.8	50.5	51.4	51.7
100°	59.8	60.1	60.5	60.9	61.4	61.9	62.8	63.6	64.5	65.3	65.5
102.5°	75.5	75.7	75.8	76.0	76.2	76.6	77.4	78.1	78.9	79.7	79.9
105°	99.5	99.6	99.7	99.8	99.9	100.1	100.5	100.9	101.2	101.6	101.9
107.5°	124.7	124.8	125.0	125.1	125.2	125.3	125.4	125.4	125.5	125.5	125.7
110°	141.8	141.9	142.1	142.3	142.5	142.6	142.5	142.4	142.3	142.2	142.0



TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	159.6	159.7	159.7	159.8	159.7	159.5	159.3	159.1	159.0	158.9
115°	186.2	186.2	186.2	186.2	186.2	186.2	186.0	185.8	185.6	185.4	185.3
117.5°	211.3	211.4	211.5	211.6	211.6	211.6	211.5	211.3	211.2	211.0	210.8
120°	228.1	228.5	228.8	229.2	229.6	229.6	229.3	229.0	228.8	228.5	228.0
122.5°	245.5	245.6	245.8	245.9	246.1	246.1	246.0	245.8	245.7	245.6	245.2
125°	271.2	271.2	271.2	271.2	271.2	271.2	271.1	271.0	270.9	270.8	270.6
127.5°	294.5	294.8	295.1	295.4	295.7	295.8	295.6	295.4	295.3	295.1	294.9
130°	310.9	311.2	311.5	311.8	312.1	312.2	312.2	312.2	312.2	312.2	312.0
132.5°	327.6	327.9	328.1	328.3	328.5	328.6	328.5	328.4	328.4	328.3	328.1
135°	349.8	350.3	350.9	351.5	352.0	352.3	352.3	352.3	352.3	352.3	352.1
137.5°	373.9	374.2	374.4	374.7	374.9	375.1	375.3	375.5	375.6	375.8	375.5
140°	389.9	390.1	390.3	390.5	390.7	390.8	390.8	390.8	390.8	390.8	390.7
142.5°	404.6	404.8	405.0	405.2	405.4	405.5	405.4	405.3	405.2	405.1	405.1
145°	425.0	425.4	425.7	426.1	426.5	426.7	426.8	426.9	427.0	427.1	427.0
147.5°	445.2	445.5	446.0	446.5	447.0	447.1	447.0	447.0	447.0	446.9	446.8
150°	457.4	457.8	458.2	458.5	458.9	459.1	459.1	459.1	459.1	459.1	459.1
152.5°	469.0	469.3	469.5	469.8	470.0	470.1	470.1	470.2	470.3	470.4	470.6
155°	486.9	486.9	486.9	486.9	486.9	486.8	486.7	486.6	486.5	486.4	486.8
157.5°	501.9	501.7	501.6	501.4	501.2	501.1	501.1	501.1	501.1	501.1	501.3
160°	510.9	510.8	510.7	510.6	510.5	510.4	510.3	510.2	510.1	510.0	510.3
162.5°	519.1	518.8	518.5	518.3	518.0	517.8	517.7	517.6	517.6	517.5	518.0
165°	530.0	529.7	529.4	529.1	528.9	528.7	528.5	528.3	528.1	527.9	528.5
167.5°	538.5	538.1	537.7	537.3	536.9	536.7	536.7	536.8	536.8	536.8	537.3
170°	543.3	542.8	542.3	541.9	541.4	541.2	541.3	541.4	541.5	541.6	542.2
172.5°	546.7	546.3	545.9	545.5	545.1	544.9	544.9	545.0	545.0	545.0	545.6
175°	551.4	550.9	550.4	550.0	549.5	549.2	549.1	549.0	548.9	548.8	549.5
177.5°	552.9	552.5	552.1	551.8	551.4	551.2	551.2	551.2	551.2	551.2	551.8
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2



TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	27.1	27.2	27.3	27.4	27.4	27.5	27.5	27.6
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	17.6	17.9	18.3	18.5	18.7	18.8	18.9	18.9
95°	33.0	33.3	33.6	33.7	33.7	33.7	33.7	33.7
97.5°	52.0	52.4	52.7	52.9	52.9	52.9	52.9	52.9
100°	65.7	65.9	66.1	66.2	66.2	66.2	66.2	66.2
102.5°	80.2	80.5	80.8	81.0	81.0	81.1	81.2	81.2
105°	102.3	102.5	102.8	103.1	103.4	103.7	104.0	104.2
107.5°	126.0	126.3	126.6	126.7	126.7	126.7	126.6	126.6
110°	141.9	141.7	141.5	141.5	141.8	142.0	142.3	142.6





TEST NUMBER: P332810-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.9	158.8	158.8	158.8	158.9	158.9	159.0	159.0
115°	185.2	185.1	185.0	184.9	184.8	184.7	184.6	184.5
117.5°	210.5	210.1	209.8	209.5	209.3	209.2	209.0	208.8
120°	227.5	227.1	226.6	226.5	226.7	226.9	227.1	227.2
122.5°	245.0	244.6	244.3	243.9	243.6	243.3	242.9	242.6
125°	270.4	270.2	270.0	269.8	269.7	269.5	269.3	269.1
127.5°	294.7	294.5	294.4	294.2	294.1	293.9	293.8	293.6
130°	311.8	311.6	311.4	311.1	310.8	310.4	310.0	309.6
132.5°	327.9	327.7	327.5	327.3	327.2	327.1	326.9	326.8
135°	351.9	351.8	351.6	351.4	351.1	350.8	350.5	350.2
137.5°	375.2	375.0	374.8	374.7	374.8	374.8	374.8	374.9
140°	390.6	390.5	390.4	390.3	390.2	390.1	390.0	389.9
142.5°	405.1	405.1	405.1	405.0	405.0	405.0	405.0	405.0
145°	426.9	426.8	426.7	426.5	426.2	425.9	425.7	425.4
147.5°	446.7	446.6	446.6	446.5	446.4	446.3	446.2	446.1
150°	459.1	459.1	459.1	459.1	459.0	458.9	458.8	458.7
152.5°	470.9	471.1	471.4	471.3	471.1	470.8	470.6	470.3
155°	487.2	487.6	488.0	488.0	487.6	487.2	486.8	486.4
157.5°	501.6	501.9	502.2	502.2	501.9	501.5	501.2	500.9
160°	510.6	510.9	511.1	511.0	510.6	510.1	509.5	509.1
162.5°	518.5	519.1	519.5	519.5	519.1	518.6	518.1	517.6
165°	529.0	529.6	530.2	530.3	529.9	529.5	529.1	528.8
167.5°	537.9	538.5	539.0	539.0	538.5	537.9	537.2	536.7
170°	542.7	543.3	543.8	543.8	543.1	542.4	541.8	541.1
172.5°	546.3	547.0	547.5	547.5	546.9	546.2	545.5	544.9
175°	550.2	550.8	551.5	551.5	550.8	550.2	549.5	548.8
177.5°	552.3	552.8	553.4	553.3	552.7	552.1	551.5	550.9
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2

(END OF REPORT)