

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332840-830

Luminaire Tested: **S124DIW-S1195D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332840-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D470U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6353.9 lumens  
Efficiency: N/A  
Efficacy: 121.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	71	69	67	64
2	94	86	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	72	60	52	45	69	58	50	44	53	46	41	49	43	39	44	40	36	34
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.8
10°-20°	498.4	7.8
20°-30°	733.6	11.5
30°-40°	852.8	13.4
40°-50°	852.8	13.4
50°-60°	746.0	11.7
60°-70°	554.0	8.7
70°-80°	314.7	5.0
80°-90°	92.5	1.5
90°-100°	36.4	0.6
100°-110°	107.9	1.7
110°-120°	183.1	2.9
120°-130°	241.5	3.8
130°-140°	271.2	4.3
140°-150°	266.5	4.2
150°-160°	224.1	3.5
160°-170°	149.1	2.3
170°-180°	52.2	0.8
0°-30°	1408.8	22.2
0°-40°	2261.6	35.6
0°-60°	3860.5	60.8
0°-90°	4821.7	75.9
90°-120°	327.5	5.2
90°-150°	1106.7	17.4
90°-180°	1532.0	24.1
0°-180°	6353.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	1	6	9	12	13	6
95°	26	29	32	34	34	29
105°	100	100	102	103	104	106
115°	186	186	185	185	184	184
125°	271	271	271	270	269	242
135°	350	352	352	352	350	270
145°	425	427	427	427	425	266
155°	487	487	486	488	486	224
165°	530	529	528	530	529	149
175°	551	549	549	552	549	52
180°	552	552	552	552	552	



TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.6	31.5	31.5	31.4	31.3	31.2	31.1	31.0	30.9	30.8	30.9
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	9.1	10.4	11.5	12.7	13.9	14.8	15.4	15.8	16.4	16.9	17.2
95°	25.6	26.5	27.3	28.2	29.0	29.8	30.4	31.1	31.8	32.4	32.7
97.5°	44.8	45.4	46.1	46.8	47.5	48.3	49.0	49.8	50.5	51.4	51.7
100°	59.8	60.1	60.5	60.9	61.4	61.9	62.8	63.6	64.5	65.3	65.5
102.5°	75.5	75.7	75.8	76.0	76.2	76.6	77.4	78.1	78.9	79.7	79.9
105°	99.5	99.6	99.7	99.8	99.9	100.1	100.5	100.9	101.2	101.6	101.9
107.5°	124.7	124.8	125.0	125.1	125.2	125.3	125.4	125.4	125.5	125.5	125.7
110°	141.8	141.9	142.1	142.3	142.5	142.6	142.5	142.4	142.3	142.2	142.0



TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	159.6	159.7	159.7	159.8	159.7	159.5	159.3	159.1	159.0	158.9
115°	186.2	186.2	186.2	186.2	186.2	186.2	186.0	185.8	185.6	185.4	185.3
117.5°	211.3	211.4	211.5	211.6	211.6	211.6	211.5	211.3	211.2	211.0	210.8
120°	228.1	228.5	228.8	229.2	229.6	229.6	229.3	229.0	228.8	228.5	228.0
122.5°	245.5	245.6	245.8	245.9	246.1	246.1	246.0	245.8	245.7	245.6	245.2
125°	271.2	271.2	271.2	271.2	271.2	271.2	271.1	271.0	270.9	270.8	270.6
127.5°	294.5	294.8	295.1	295.4	295.7	295.8	295.6	295.4	295.3	295.1	294.9
130°	310.9	311.2	311.5	311.8	312.1	312.2	312.2	312.2	312.2	312.2	312.0
132.5°	327.6	327.9	328.1	328.3	328.5	328.6	328.5	328.4	328.4	328.3	328.1
135°	349.8	350.3	350.9	351.5	352.0	352.3	352.3	352.3	352.3	352.3	352.1
137.5°	373.9	374.2	374.4	374.7	374.9	375.1	375.3	375.5	375.6	375.8	375.5
140°	389.9	390.1	390.3	390.5	390.7	390.8	390.8	390.8	390.8	390.8	390.7
142.5°	404.6	404.8	405.0	405.2	405.4	405.5	405.4	405.3	405.2	405.1	405.1
145°	425.0	425.4	425.7	426.1	426.5	426.7	426.8	426.9	427.0	427.1	427.0
147.5°	445.2	445.5	446.0	446.5	447.0	447.1	447.0	447.0	447.0	446.9	446.8
150°	457.4	457.8	458.2	458.5	458.9	459.1	459.1	459.1	459.1	459.1	459.1
152.5°	469.0	469.3	469.5	469.8	470.0	470.1	470.1	470.2	470.3	470.4	470.6
155°	486.9	486.9	486.9	486.9	486.9	486.8	486.7	486.6	486.5	486.4	486.8
157.5°	501.9	501.7	501.6	501.4	501.2	501.1	501.1	501.1	501.1	501.1	501.3
160°	510.9	510.8	510.7	510.6	510.5	510.4	510.3	510.2	510.1	510.0	510.3
162.5°	519.1	518.8	518.5	518.3	518.0	517.8	517.7	517.6	517.6	517.5	518.0
165°	530.0	529.7	529.4	529.1	528.9	528.7	528.5	528.3	528.1	527.9	528.5
167.5°	538.5	538.1	537.7	537.3	536.9	536.7	536.7	536.8	536.8	536.8	537.3
170°	543.3	542.8	542.3	541.9	541.4	541.2	541.3	541.4	541.5	541.6	542.2
172.5°	546.7	546.3	545.9	545.5	545.1	544.9	544.9	545.0	545.0	545.0	545.6
175°	551.4	550.9	550.4	550.0	549.5	549.2	549.1	549.0	548.9	548.8	549.5
177.5°	552.9	552.5	552.1	551.8	551.4	551.2	551.2	551.2	551.2	551.2	551.8
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2



TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	31.0	31.1	31.2	31.3	31.4	31.4	31.4	31.5
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	17.6	17.9	18.3	18.5	18.7	18.8	18.9	18.9
95°	33.0	33.3	33.6	33.7	33.7	33.7	33.7	33.7
97.5°	52.0	52.4	52.7	52.9	52.9	52.9	52.9	52.9
100°	65.7	65.9	66.1	66.2	66.2	66.2	66.2	66.2
102.5°	80.2	80.5	80.8	81.0	81.0	81.1	81.2	81.2
105°	102.3	102.5	102.8	103.1	103.4	103.7	104.0	104.2
107.5°	126.0	126.3	126.6	126.7	126.7	126.7	126.6	126.6
110°	141.9	141.7	141.5	141.5	141.8	142.0	142.3	142.6





TEST NUMBER: P332840-830

CATALOG NUMBER: S124DIW-S1195D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.9	158.8	158.8	158.8	158.9	158.9	159.0	159.0
115°	185.2	185.1	185.0	184.9	184.8	184.7	184.6	184.5
117.5°	210.5	210.1	209.8	209.5	209.3	209.2	209.0	208.8
120°	227.5	227.1	226.6	226.5	226.7	226.9	227.1	227.2
122.5°	245.0	244.6	244.3	243.9	243.6	243.3	242.9	242.6
125°	270.4	270.2	270.0	269.8	269.7	269.5	269.3	269.1
127.5°	294.7	294.5	294.4	294.2	294.1	293.9	293.8	293.6
130°	311.8	311.6	311.4	311.1	310.8	310.4	310.0	309.6
132.5°	327.9	327.7	327.5	327.3	327.2	327.1	326.9	326.8
135°	351.9	351.8	351.6	351.4	351.1	350.8	350.5	350.2
137.5°	375.2	375.0	374.8	374.7	374.8	374.8	374.8	374.9
140°	390.6	390.5	390.4	390.3	390.2	390.1	390.0	389.9
142.5°	405.1	405.1	405.1	405.0	405.0	405.0	405.0	405.0
145°	426.9	426.8	426.7	426.5	426.2	425.9	425.7	425.4
147.5°	446.7	446.6	446.6	446.5	446.4	446.3	446.2	446.1
150°	459.1	459.1	459.1	459.1	459.0	458.9	458.8	458.7
152.5°	470.9	471.1	471.4	471.3	471.1	470.8	470.6	470.3
155°	487.2	487.6	488.0	488.0	487.6	487.2	486.8	486.4
157.5°	501.6	501.9	502.2	502.2	501.9	501.5	501.2	500.9
160°	510.6	510.9	511.1	511.0	510.6	510.1	509.5	509.1
162.5°	518.5	519.1	519.5	519.5	519.1	518.6	518.1	517.6
165°	529.0	529.6	530.2	530.3	529.9	529.5	529.1	528.8
167.5°	537.9	538.5	539.0	539.0	538.5	537.9	537.2	536.7
170°	542.7	543.3	543.8	543.8	543.1	542.4	541.8	541.1
172.5°	546.3	547.0	547.5	547.5	546.9	546.2	545.5	544.9
175°	550.2	550.8	551.5	551.5	550.8	550.2	549.5	548.8
177.5°	552.3	552.8	553.4	553.3	552.7	552.1	551.5	550.9
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2

(END OF REPORT)