

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769-830

Luminaire Tested: **S124DIW-S575D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332769-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8326.5 lumens
Efficiency: N/A
Efficacy: 137.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7146	7146	7146	7146
5°	8417	7165	6324	7165
10°	10077	7133	5694	7133
15°	11922	7061	5229	7061
20°	13277	6988	4814	6988
25°	13491	6879	4528	6879
30°	11479	6776	4437	6776
35°	8825	6606	4438	6606
40°	6880	6407	4521	6407
45°	5736	6109	4598	6109
50°	5048	5743	4752	5743
55°	4625	5306	4944	5306
60°	4334	4913	5176	4913
65°	4034	4476	5366	4476
70°	3687	4043	5488	4043
75°	3297	3556	5421	3556
80°	2762	2915	5249	2915
85°	2038	2103	5030	2103



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.0
10°-20°	265.8	3.2
20°-30°	421.5	5.1
30°-40°	469.1	5.6
40°-50°	427.0	5.1
50°-60°	349.0	4.2
60°-70°	249.1	3.0
70°-80°	137.2	1.6
80°-90°	42.9	0.5
90°-100°	65.0	0.8
100°-110°	414.4	5.0
110°-120°	792.8	9.5
120°-130°	1006.4	12.1
130°-140°	1076.8	12.9
140°-150°	1006.9	12.1
150°-160°	812.0	9.8
160°-170°	523.7	6.3
170°-180°	180.5	2.2
0°-30°	773.6	9.3
0°-40°	1242.8	14.9
0°-60°	2018.8	24.2
0°-90°	2448.0	29.4
90°-120°	1272.2	15.3
90°-150°	4362.3	52.4
90°-180°	5879.0	70.6
0°-180°	8326.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	885	885	885	885	885	
5°	1039	884	780	884	1039	106
15°	1426	845	626	845	1426	403
25°	1515	772	508	772	1515	668
35°	896	670	450	670	896	568
45°	502	535	403	535	502	396
55°	329	377	351	377	329	297
65°	211	234	281	234	211	209
75°	106	114	174	114	106	112
85°	22	23	54	23	22	28
90°	43	4	43	4	43	19
95°	41	78	41	78	41	33
105°	405	428	405	428	405	353
115°	805	799	805	799	805	796
125°	1131	1123	1131	1123	1131	1008
135°	1403	1393	1403	1393	1403	1080
145°	1615	1606	1615	1606	1615	1009
155°	1760	1761	1760	1761	1760	811
165°	1849	1858	1849	1858	1849	522
175°	1889	1900	1889	1900	1889	180
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	942.2	941.9	939.0	938.4	936.3	933.7	933.1	928.4	919.0	914.6	913.4
5°	1038.6	1045.9	1036.3	1034.5	1033.4	1021.3	1015.1	1007.8	990.9	981.0	973.3
7.5°	1153.6	1154.4	1150.3	1146.9	1137.6	1127.0	1111.2	1094.3	1074.2	1053.3	1037.6
10°	1229.3	1232.2	1227.5	1226.7	1208.0	1196.3	1172.8	1153.0	1130.2	1104.9	1081.9
12.5°	1309.1	1305.0	1302.5	1286.9	1283.4	1262.0	1234.7	1214.3	1179.2	1150.1	1119.4
15°	1426.5	1418.5	1413.3	1391.8	1381.1	1351.4	1322.4	1300.0	1254.2	1210.6	1177.5
17.5°	1495.5	1503.5	1491.7	1482.8	1455.3	1434.5	1404.9	1357.9	1322.0	1267.8	1226.2
20°	1545.4	1546.1	1539.5	1530.3	1508.7	1482.3	1450.0	1398.7	1355.8	1301.8	1244.6
22.5°	1558.9	1559.1	1556.2	1547.7	1531.3	1509.9	1477.3	1434.5	1382.5	1323.9	1266.7
25°	1514.6	1513.2	1516.5	1526.0	1519.8	1513.2	1494.4	1462.5	1414.1	1352.1	1290.5
27.5°	1350.0	1360.1	1378.8	1402.2	1424.8	1442.0	1446.9	1440.4	1410.3	1359.3	1294.9
30°	1231.4	1244.0	1257.8	1281.4	1326.8	1352.8	1381.5	1403.1	1391.0	1350.3	1290.2
32.5°	1101.2	1104.3	1124.9	1151.7	1193.4	1243.4	1288.7	1332.7	1347.3	1326.0	1275.7
35°	895.5	900.7	923.0	949.4	1000.4	1061.7	1129.9	1190.7	1241.0	1261.2	1235.5
37.5°	730.8	745.6	761.3	789.7	834.6	889.8	960.6	1039.3	1114.3	1164.4	1172.9
40°	652.8	661.9	673.4	694.9	733.1	787.4	848.2	938.5	1018.0	1090.0	1113.4
42.5°	591.2	596.5	603.5	623.0	652.1	706.1	761.7	841.0	921.0	1006.9	1046.2
45°	502.4	507.9	519.6	531.0	553.0	590.4	642.2	707.4	787.7	870.6	943.2
47.5°	438.3	441.9	448.8	461.0	479.7	504.4	546.4	600.9	675.3	755.8	833.2
50°	401.9	404.8	410.4	421.4	435.6	457.7	492.1	543.1	601.4	682.5	758.4
52.5°	373.2	374.4	378.4	385.9	397.3	415.8	444.0	486.2	540.5	612.7	688.2
55°	328.6	330.1	333.8	339.2	349.1	360.9	382.5	414.1	461.4	524.1	589.7
57.5°	291.9	292.9	296.1	298.1	306.3	315.8	332.4	355.0	390.9	444.0	502.7
60°	268.4	267.7	271.4	273.2	278.7	286.8	299.6	321.2	352.4	395.3	449.2
62.5°	245.5	244.5	247.6	250.1	253.2	260.0	270.6	287.5	312.8	351.7	398.2
65°	211.2	209.8	211.6	214.5	217.4	221.1	228.8	243.8	264.0	291.9	327.4
67.5°	176.7	178.3	178.6	180.0	181.7	186.7	192.0	202.6	216.9	239.2	269.3
70°	156.2	156.6	158.1	158.1	159.2	163.5	168.0	174.2	188.1	208.7	233.3
72.5°	135.7	137.2	136.7	137.8	138.6	141.6	144.8	150.7	162.6	177.9	198.6
75°	105.7	106.7	106.7	107.1	108.2	109.2	111.9	116.2	124.7	136.0	150.3
77.5°	77.0	77.2	77.7	79.0	79.0	80.8	82.7	86.1	90.4	98.1	106.9
80°	59.4	60.1	59.8	60.5	60.5	62.0	62.7	67.1	68.9	74.1	81.1
82.5°	43.5	44.3	44.2	45.2	45.8	46.1	47.1	48.9	50.7	55.3	58.2
85°	22.0	22.7	22.0	22.7	23.8	24.2	25.3	25.6	27.1	28.3	30.8
87.5°	15.0	15.7	15.6	15.7	16.2	16.3	16.2	15.6	16.3	16.2	16.9
90°	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1	33.2	31.3	28.7
92.5°	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9	32.0	30.2	27.6
95°	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1	33.2	31.3	30.9
97.5°	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9	37.7	37.5	72.8
100°	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8	57.2	62.6	106.1
102.5°	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5	243.4	301.3	307.0
105°	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1	446.3	443.5	441.9
107.5°	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7	554.3	552.9	550.7
110°	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1	627.5	626.8	624.9



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2	698.3	698.5	697.6
115°	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0	802.3	801.6	802.0
117.5°	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3	908.4	908.5	907.9
120°	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2	972.5
122.5°	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8	1037.5	1037.1	1036.6
125°	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7	1126.7	1125.8	1126.3
127.5°	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9	1217.1	1217.3	1215.8
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4	1271.0	1270.7	1269.8
132.5°	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8	1324.5	1324.2	1323.0
135°	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5	1397.9	1397.2	1396.0
137.5°	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1	1468.4	1467.7	1466.3
140°	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9	1511.9	1510.9	1510.3
142.5°	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3	1552.6	1551.9	1551.5
145°	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1	1610.7	1610.4	1610.4
147.5°	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8	1661.6	1661.3	1661.6
150°	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3	1694.3	1694.3	1694.6
152.5°	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6	1722.1	1721.6	1722.1
155°	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8	1759.5	1758.2	1759.3
157.5°	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4	1791.5
160°	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8	1811.2
162.5°	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7	1829.8	1827.9	1828.2
165°	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7	1853.1	1850.7	1850.7
167.5°	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3	1870.5	1867.7	1867.9
170°	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1	1881.6	1879.1	1878.8
172.5°	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9	1888.4	1885.9	1885.6
175°	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9	1896.1	1893.3	1893.0
177.5°	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1	1900.2	1898.1	1897.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	913.7	909.6	906.7	904.4	897.9	894.1	891.2	887.0	882.3	877.3	871.2
5°	965.6	953.1	944.0	930.0	916.8	905.8	894.5	884.2	871.7	858.2	848.2
7.5°	1020.1	1001.5	977.8	957.2	934.0	913.8	895.8	877.3	858.1	839.4	822.4
10°	1054.7	1030.9	1004.5	973.3	944.0	917.9	893.7	870.2	847.5	824.7	805.3
12.5°	1091.9	1062.2	1023.2	986.7	953.9	919.1	889.9	861.1	833.7	809.8	787.1
15°	1142.0	1099.1	1054.0	1005.2	962.0	921.2	881.3	844.9	814.2	782.6	760.6
17.5°	1172.7	1119.6	1068.1	1017.1	964.7	913.3	870.2	828.4	789.8	758.5	730.8
20°	1193.0	1140.2	1076.0	1025.0	962.6	909.8	860.0	813.4	773.1	739.7	711.1
22.5°	1210.6	1149.5	1085.3	1018.2	956.2	900.1	845.6	798.7	757.5	722.4	694.9
25°	1220.1	1150.1	1080.3	1013.6	943.2	876.8	827.4	772.3	728.3	691.3	661.9
27.5°	1221.2	1146.2	1067.4	993.3	920.6	858.8	796.3	747.1	701.4	662.2	634.0
30°	1217.9	1139.8	1055.1	974.8	901.8	834.6	780.4	726.9	680.2	641.4	612.1
32.5°	1207.6	1126.2	1039.2	954.2	878.6	812.9	757.0	706.1	660.6	622.4	591.5
35°	1177.9	1097.6	1004.8	916.4	839.1	772.7	722.1	670.3	624.9	588.6	558.9
37.5°	1131.5	1058.9	964.6	873.1	797.1	730.5	680.2	633.6	592.6	555.6	525.2
40°	1091.0	1027.2	932.6	843.5	761.3	697.9	650.9	608.0	567.3	532.4	503.5
42.5°	1044.3	988.7	901.4	807.1	727.8	664.1	618.4	579.9	541.5	509.3	480.3
45°	961.2	924.5	842.4	755.1	672.6	612.5	568.8	535.1	502.8	471.3	447.0
47.5°	865.5	847.3	778.2	695.3	617.0	557.7	519.9	488.7	460.4	433.7	412.4
50°	801.3	792.5	732.7	652.8	578.0	522.3	484.1	457.3	433.1	409.6	389.5
52.5°	737.9	737.6	683.7	610.5	541.3	487.6	449.8	424.7	403.8	384.7	366.6
55°	641.0	651.3	609.2	543.8	481.9	433.5	399.4	377.0	362.3	346.6	333.0
57.5°	552.0	569.1	534.3	476.8	425.1	380.5	350.8	334.0	318.4	308.9	299.0
60°	494.0	510.1	483.0	434.6	385.8	347.6	319.4	304.3	290.8	284.2	277.2
62.5°	442.3	456.8	436.6	391.7	349.4	312.7	288.9	274.5	265.3	258.1	253.4
65°	368.5	380.7	363.4	330.8	294.5	265.1	245.7	234.3	225.6	222.6	217.4
67.5°	297.9	309.0	299.6	271.9	242.8	220.6	205.4	194.4	189.3	186.6	183.0
70°	256.0	267.0	257.0	232.9	210.5	191.8	177.5	171.3	165.8	164.7	159.6
72.5°	220.5	228.0	218.0	199.2	180.0	164.2	153.2	146.7	143.7	141.8	139.0
75°	165.4	172.0	165.4	150.7	137.1	126.1	116.6	114.0	110.7	109.6	107.8
77.5°	117.1	122.8	117.7	108.6	98.4	89.9	84.8	81.5	80.8	78.9	79.7
80°	89.4	93.1	88.4	82.2	74.1	68.2	64.6	62.7	60.5	59.8	61.3
82.5°	64.3	65.9	63.4	59.3	53.3	49.4	46.9	44.8	44.4	44.5	44.5
85°	33.4	33.0	32.6	28.9	27.1	24.6	23.1	22.7	22.3	23.1	23.8
87.5°	16.4	16.2	15.4	13.6	12.1	10.5	9.4	8.5	9.4	10.5	11.4
90°	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2	7.7	11.2	14.7
92.5°	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9	18.1	18.3	18.5
95°	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1	67.4	56.7	46.0
97.5°	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0	172.7	179.4	186.2
100°	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1	238.8	244.5	250.2
102.5°	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1	312.4	316.5	320.7
105°	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8	429.7	431.6	433.6
107.5°	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9	540.0	540.9	541.9
110°	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1	615.0	616.0	616.9



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8	688.5	690.2	691.9
115°	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8	799.7	800.7	801.6
117.5°	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8	901.0	902.3	903.5
120°	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0	969.2	970.5	971.8
122.5°	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6	1032.4	1033.1	1033.9
125°	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9	1124.2	1125.4	1126.7
127.5°	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3	1209.7	1209.9	1210.2
130°	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1	1265.4	1265.6	1266.0
132.5°	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2	1316.7	1317.4	1318.0
135°	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0	1392.6	1392.3	1392.0
137.5°	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9	1461.0	1461.1	1461.3
140°	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2	1505.9	1506.6	1507.1
142.5°	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0	1546.1	1547.4	1548.5
145°	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2	1607.1	1608.1	1609.0
147.5°	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8	1656.5	1658.3	1660.1
150°	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1	1691.3	1692.5	1693.8
152.5°	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6	1720.6	1721.6	1722.6
155°	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1	1761.4	1761.7	1762.1
157.5°	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1	1795.9	1795.7	1795.5
160°	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6	1815.6	1814.7	1813.7
162.5°	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8	1833.5	1832.3	1831.2
165°	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8	1856.1	1854.6	1853.0
167.5°	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9	1874.3	1872.6	1871.0
170°	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2	1884.3	1882.4	1880.5
172.5°	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0	1891.1	1889.2	1887.3
175°	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4	1898.5	1896.6	1894.7
177.5°	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8	1902.1	1900.3	1898.5
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	868.3	865.6	861.8	856.5	852.2	847.4	846.2	844.5	848.0	845.1	844.2
5°	839.8	832.1	822.2	810.9	804.3	794.7	792.9	789.2	785.5	785.1	781.5
7.5°	809.6	798.3	785.4	773.8	763.1	752.7	745.8	744.4	739.0	735.8	732.2
10°	790.3	776.4	761.3	750.4	737.8	726.9	719.2	714.7	711.1	707.0	703.4
12.5°	767.4	752.6	740.2	728.3	713.5	705.1	692.5	684.9	684.1	684.2	674.7
15°	740.7	726.1	707.0	690.2	682.1	666.0	659.0	650.2	644.7	639.2	634.8
17.5°	710.4	692.1	677.2	657.8	642.4	629.6	620.4	615.1	606.9	599.1	593.4
20°	691.3	671.8	656.1	635.6	618.7	602.9	595.2	587.9	581.6	575.0	568.8
22.5°	671.9	651.6	632.4	612.4	596.6	580.0	572.6	562.6	556.7	553.0	546.8
25°	641.4	619.4	597.4	578.3	562.2	547.5	537.6	529.9	523.3	520.4	516.3
27.5°	608.2	586.4	565.1	543.5	525.2	514.5	506.6	500.8	497.0	493.1	491.3
30°	587.1	564.4	541.7	521.5	504.6	494.0	486.6	482.6	479.7	477.9	476.0
32.5°	565.7	543.3	519.3	501.0	485.9	476.4	470.8	466.7	465.3	464.7	464.0
35°	531.4	508.7	486.6	470.1	455.8	452.1	447.4	445.2	444.5	447.0	448.2
37.5°	498.1	477.0	456.8	440.8	431.4	426.0	424.4	424.5	427.2	429.4	432.1
40°	476.7	456.2	437.2	423.2	414.4	411.1	410.4	412.2	415.1	417.7	420.7
42.5°	455.9	435.6	418.4	405.3	399.2	396.2	396.6	398.4	402.6	405.7	410.1
45°	423.6	406.7	389.8	379.2	374.1	374.8	374.8	378.1	382.1	386.9	391.6
47.5°	393.1	376.1	362.2	353.3	350.6	350.0	352.0	356.4	362.2	368.1	374.8
50°	372.6	356.5	344.3	336.3	333.4	334.4	337.4	341.4	348.4	355.7	362.7
52.5°	351.8	337.1	325.8	318.4	316.3	318.3	321.2	327.6	333.8	341.7	350.1
55°	319.4	307.0	298.1	292.7	291.9	293.0	296.3	303.3	312.1	322.0	330.1
57.5°	287.2	276.8	268.7	264.9	265.3	266.4	271.7	280.0	289.5	300.0	310.4
60°	265.5	256.0	249.4	246.5	246.9	249.0	255.6	263.3	275.0	285.3	296.3
62.5°	245.0	236.6	230.3	227.6	227.2	232.0	238.3	246.3	258.1	269.5	281.3
65°	212.0	205.4	200.2	198.8	199.8	203.5	211.6	222.3	232.1	244.2	256.7
67.5°	179.6	174.3	170.8	171.4	172.8	178.1	184.9	194.1	205.3	217.8	230.2
70°	159.2	154.0	151.1	151.5	153.6	160.2	166.2	175.3	187.4	200.2	210.5
72.5°	138.1	134.7	132.1	133.6	135.7	140.3	147.6	156.8	167.5	179.4	190.3
75°	105.9	105.9	104.5	105.7	109.0	113.3	118.9	128.4	139.0	148.5	157.3
77.5°	78.6	77.9	78.8	80.1	82.0	87.2	93.5	100.4	108.3	117.9	125.2
80°	60.1	60.5	62.3	64.6	65.3	69.3	75.9	82.2	88.4	96.4	103.4
82.5°	45.1	45.5	46.5	49.3	50.0	54.4	58.6	64.8	70.5	75.9	81.7
85°	24.6	24.6	26.4	27.5	29.3	32.2	34.9	38.5	43.6	47.3	52.8
87.5°	13.0	13.7	15.3	16.4	17.8	19.8	20.7	24.3	25.9	27.7	30.6
90°	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1	36.9	38.8	40.2
92.5°	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9	35.8	37.7	38.7
95°	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1	36.9	38.8	40.0
97.5°	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9	38.1	38.3	38.5
100°	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8	46.5	41.1	38.5
102.5°	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5	127.5	69.7	40.7
105°	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1	452.0	454.9	450.5
107.5°	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7	557.1	558.5	559.8
110°	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1	628.8	629.3	630.2



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2	698.0	698.0	698.5
115°	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0	803.5	804.2	804.6
117.5°	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3	908.1	908.0	908.0
120°	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5	974.1	974.8	974.8
122.5°	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8	1038.2	1038.6	1038.4
125°	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7	1128.6	1129.5	1130.2
127.5°	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9	1216.7	1216.5	1216.3
130°	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4	1271.7	1272.0	1272.1
132.5°	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8	1325.1	1325.4	1325.5
135°	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5	1399.1	1399.8	1400.4
137.5°	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1	1469.8	1470.6	1470.7
140°	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9	1513.8	1514.8	1515.3
142.5°	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3	1554.0	1554.6	1555.0
145°	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1	1611.4	1611.7	1612.2
147.5°	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8	1662.1	1662.4	1662.6
150°	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3	1694.3	1694.3	1694.5
152.5°	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6	1723.1	1723.6	1723.7
155°	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8	1762.1	1763.3	1763.5
157.5°	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0
160°	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4
162.5°	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7	1833.6	1835.5	1835.3
165°	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7	1858.2	1860.8	1860.6
167.5°	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3	1876.0	1878.9	1878.7
170°	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1	1886.7	1889.2	1888.9
172.5°	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9	1893.5	1896.0	1895.5
175°	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9	1901.9	1904.7	1904.2
177.5°	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1	1904.2	1906.2	1905.7
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	843.6	843.0	840.9	840.7	840.9	843.0	843.6	844.2	845.1	848.0	844.5
5°	779.3	777.5	776.4	780.4	776.4	777.5	779.3	781.5	785.1	785.5	789.2
7.5°	730.8	729.3	726.1	725.1	726.1	729.3	730.8	732.2	735.8	739.0	744.4
10°	699.7	698.2	695.3	694.6	695.3	698.2	699.7	703.4	707.0	711.1	714.7
12.5°	669.8	666.8	666.3	667.0	666.3	666.8	669.8	674.7	684.2	684.1	684.9
15°	630.0	628.6	624.5	625.7	624.5	628.6	630.0	634.8	639.2	644.7	650.2
17.5°	590.9	589.1	584.2	588.5	584.2	589.1	590.9	593.4	599.1	606.9	615.1
20°	566.2	563.3	560.7	560.3	560.7	563.3	566.2	568.8	575.0	581.6	587.9
22.5°	542.7	540.1	539.9	537.4	539.9	540.1	542.7	546.8	553.0	556.7	562.6
25°	513.4	510.9	510.1	508.3	510.1	510.9	513.4	516.3	520.4	523.3	529.9
27.5°	490.9	489.7	488.3	488.9	488.3	489.7	490.9	491.3	493.1	497.0	500.8
30°	477.1	476.7	476.0	476.0	476.0	476.7	477.1	476.0	477.9	479.7	482.6
32.5°	465.7	465.6	466.0	466.0	466.0	465.6	465.7	464.0	464.7	465.3	466.7
35°	449.6	450.7	451.5	450.3	451.5	450.7	449.6	448.2	447.0	444.5	445.2
37.5°	435.1	436.2	437.2	438.5	437.2	436.2	435.1	432.1	429.4	427.2	424.5
40°	424.0	426.5	427.3	429.0	427.3	426.5	424.0	420.7	417.7	415.1	412.2
42.5°	413.4	416.2	418.1	418.5	418.1	416.2	413.4	410.1	405.7	402.6	398.4
45°	397.2	400.1	402.7	402.7	402.7	400.1	397.2	391.6	386.9	382.1	378.1
47.5°	380.4	384.7	387.2	387.9	387.2	384.7	380.4	374.8	368.1	362.2	356.4
50°	368.9	374.1	376.6	378.4	376.6	374.1	368.9	362.7	355.7	348.4	341.4
52.5°	357.8	362.9	366.4	367.3	366.4	362.9	357.8	350.1	341.7	333.8	327.6
55°	338.5	345.8	349.9	351.3	349.9	345.8	338.5	330.1	322.0	312.1	303.3
57.5°	320.3	327.1	331.8	332.8	331.8	327.1	320.3	310.4	300.0	289.5	280.0
60°	306.2	313.6	319.4	320.6	319.4	313.6	306.2	296.3	285.3	275.0	263.3
62.5°	291.8	299.4	304.7	307.6	304.7	299.4	291.8	281.3	269.5	258.1	246.3
65°	267.0	274.7	279.8	280.9	279.8	274.7	267.0	256.7	244.2	232.1	222.3
67.5°	239.9	247.5	250.9	253.1	250.9	247.5	239.9	230.2	217.8	205.3	194.1
70°	220.7	227.0	230.6	232.5	230.6	227.0	220.7	210.5	200.2	187.4	175.3
72.5°	199.1	205.6	209.8	210.2	209.8	205.6	199.1	190.3	179.4	167.5	156.8
75°	165.8	171.6	173.8	173.8	173.8	171.6	165.8	157.3	148.5	139.0	128.4
77.5°	131.2	134.2	137.0	137.6	137.0	134.2	131.2	125.2	117.9	108.3	100.4
80°	109.0	110.7	112.9	112.9	112.9	110.7	109.0	103.4	96.4	88.4	82.2
82.5°	86.1	87.6	89.7	89.4	89.7	87.6	86.1	81.7	75.9	70.5	64.8
85°	52.0	55.4	55.0	54.3	55.0	55.4	52.0	52.8	47.3	43.6	38.5
87.5°	31.6	32.0	33.1	33.7	33.1	32.0	31.6	30.6	27.7	25.9	24.3
90°	40.7	41.4	42.0	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1
92.5°	38.8	39.0	39.1	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9
95°	40.2	40.6	40.9	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1
97.5°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9
100°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8
102.5°	40.7	40.8	40.9	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5
105°	439.2	427.8	416.5	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1
107.5°	561.0	562.1	563.4	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7
110°	631.1	632.1	633.0	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	699.7	700.9	702.1	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2
115°	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0
117.5°	907.8	907.7	907.6	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3
120°	974.1	973.5	972.9	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5
122.5°	1037.8	1037.2	1036.5	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8
125°	1130.5	1130.8	1131.1	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7
127.5°	1216.1	1215.8	1215.5	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4
132.5°	1325.2	1324.9	1324.7	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8
135°	1401.0	1401.7	1402.3	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5
137.5°	1470.6	1470.4	1470.2	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1
140°	1515.7	1516.0	1516.3	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9
142.5°	1555.1	1555.2	1555.2	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3
145°	1612.8	1613.4	1614.1	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1
147.5°	1662.9	1663.2	1663.6	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8
150°	1694.8	1695.1	1695.4	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3
152.5°	1723.5	1723.3	1723.2	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6
155°	1762.6	1761.6	1760.7	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8
157.5°	1795.4	1793.7	1792.1	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7
160°	1816.6	1814.7	1812.8	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7
162.5°	1833.2	1831.1	1828.9	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7
165°	1857.8	1854.9	1852.1	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7
167.5°	1875.5	1872.4	1869.2	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3
170°	1885.7	1882.5	1879.4	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1
172.5°	1892.2	1888.8	1885.4	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9
175°	1900.4	1896.6	1892.8	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9
177.5°	1902.7	1899.6	1896.6	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	846.2	847.4	852.2	856.5	861.8	865.6	868.3	871.2	877.3	882.3	887.0
5°	792.9	794.7	804.3	810.9	822.2	832.1	839.8	848.2	858.2	871.7	884.2
7.5°	745.8	752.7	763.1	773.8	785.4	798.3	809.6	822.4	839.4	858.1	877.3
10°	719.2	726.9	737.8	750.4	761.3	776.4	790.3	805.3	824.7	847.5	870.2
12.5°	692.5	705.1	713.5	728.3	740.2	752.6	767.4	787.1	809.8	833.7	861.1
15°	659.0	666.0	682.1	690.2	707.0	726.1	740.7	760.6	782.6	814.2	844.9
17.5°	620.4	629.6	642.4	657.8	677.2	692.1	710.4	730.8	758.5	789.8	828.4
20°	595.2	602.9	618.7	635.6	656.1	671.8	691.3	711.1	739.7	773.1	813.4
22.5°	572.6	580.0	596.6	612.4	632.4	651.6	671.9	694.9	722.4	757.5	798.7
25°	537.6	547.5	562.2	578.3	597.4	619.4	641.4	661.9	691.3	728.3	772.3
27.5°	506.6	514.5	525.2	543.5	565.1	586.4	608.2	634.0	662.2	701.4	747.1
30°	486.6	494.0	504.6	521.5	541.7	564.4	587.1	612.1	641.4	680.2	726.9
32.5°	470.8	476.4	485.9	501.0	519.3	543.3	565.7	591.5	622.4	660.6	706.1
35°	447.4	452.1	455.8	470.1	486.6	508.7	531.4	558.9	588.6	624.9	670.3
37.5°	424.4	426.0	431.4	440.8	456.8	477.0	498.1	525.2	555.6	592.6	633.6
40°	410.4	411.1	414.4	423.2	437.2	456.2	476.7	503.5	532.4	567.3	608.0
42.5°	396.6	396.2	399.2	405.3	418.4	435.6	455.9	480.3	509.3	541.5	579.9
45°	374.8	374.8	374.1	379.2	389.8	406.7	423.6	447.0	471.3	502.8	535.1
47.5°	352.0	350.0	350.6	353.3	362.2	376.1	393.1	412.4	433.7	460.4	488.7
50°	337.4	334.4	333.4	336.3	344.3	356.5	372.6	389.5	409.6	433.1	457.3
52.5°	321.2	318.3	316.3	318.4	325.8	337.1	351.8	366.6	384.7	403.8	424.7
55°	296.3	293.0	291.9	292.7	298.1	307.0	319.4	333.0	346.6	362.3	377.0
57.5°	271.7	266.4	265.3	264.9	268.7	276.8	287.2	299.0	308.9	318.4	334.0
60°	255.6	249.0	246.9	246.5	249.4	256.0	265.5	277.2	284.2	290.8	304.3
62.5°	238.3	232.0	227.2	227.6	230.3	236.6	245.0	253.4	258.1	265.3	274.5
65°	211.6	203.5	199.8	198.8	200.2	205.4	212.0	217.4	222.6	225.6	234.3
67.5°	184.9	178.1	172.8	171.4	170.8	174.3	179.6	183.0	186.6	189.3	194.4
70°	166.2	160.2	153.6	151.5	151.1	154.0	159.2	159.6	164.7	165.8	171.3
72.5°	147.6	140.3	135.7	133.6	132.1	134.7	138.1	139.0	141.8	143.7	146.7
75°	118.9	113.3	109.0	105.7	104.5	105.9	105.9	107.8	109.6	110.7	114.0
77.5°	93.5	87.2	82.0	80.1	78.8	77.9	78.6	79.7	78.9	80.8	81.5
80°	75.9	69.3	65.3	64.6	62.3	60.5	60.1	61.3	59.8	60.5	62.7
82.5°	58.6	54.4	50.0	49.3	46.5	45.5	45.1	44.5	44.5	44.4	44.8
85°	34.9	32.2	29.3	27.5	26.4	24.6	24.6	23.8	23.1	22.3	22.7
87.5°	20.7	19.8	17.8	16.4	15.3	13.7	13.0	11.4	10.5	9.4	8.5
90°	33.2	31.3	28.7	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2
92.5°	32.0	30.2	27.6	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9
95°	33.2	31.3	30.9	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1
97.5°	37.7	37.5	72.8	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0
100°	57.2	62.6	106.1	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1
102.5°	243.4	301.3	307.0	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1
105°	446.3	443.5	441.9	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8
107.5°	554.3	552.9	550.7	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9
110°	627.5	626.8	624.9	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.3	698.5	697.6	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8
115°	802.3	801.6	802.0	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8
117.5°	908.4	908.5	907.9	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8
120°	972.9	972.2	972.5	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0
122.5°	1037.5	1037.1	1036.6	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6
125°	1126.7	1125.8	1126.3	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9
127.5°	1217.1	1217.3	1215.8	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3
130°	1271.0	1270.7	1269.8	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1
132.5°	1324.5	1324.2	1323.0	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2
135°	1397.9	1397.2	1396.0	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0
137.5°	1468.4	1467.7	1466.3	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9
140°	1511.9	1510.9	1510.3	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2
142.5°	1552.6	1551.9	1551.5	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0
145°	1610.7	1610.4	1610.4	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2
147.5°	1661.6	1661.3	1661.6	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8
150°	1694.3	1694.3	1694.6	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1
152.5°	1722.1	1721.6	1722.1	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6
155°	1759.5	1758.2	1759.3	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1
157.5°	1792.1	1790.4	1791.5	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1
160°	1812.8	1810.8	1811.2	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6
162.5°	1829.8	1827.9	1828.2	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8
165°	1853.1	1850.7	1850.7	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8
167.5°	1870.5	1867.7	1867.9	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9
170°	1881.6	1879.1	1878.8	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2
172.5°	1888.4	1885.9	1885.6	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0
175°	1896.1	1893.3	1893.0	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4
177.5°	1900.2	1898.1	1897.6	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	891.2	894.1	897.9	904.4	906.7	909.6	913.7	913.4	914.6	919.0	928.4
5°	894.5	905.8	916.8	930.0	944.0	953.1	965.6	973.3	981.0	990.9	1007.8
7.5°	895.8	913.8	934.0	957.2	977.8	1001.5	1020.1	1037.6	1053.3	1074.2	1094.3
10°	893.7	917.9	944.0	973.3	1004.5	1030.9	1054.7	1081.9	1104.9	1130.2	1153.0
12.5°	889.9	919.1	953.9	986.7	1023.2	1062.2	1091.9	1119.4	1150.1	1179.2	1214.3
15°	881.3	921.2	962.0	1005.2	1054.0	1099.1	1142.0	1177.5	1210.6	1254.2	1300.0
17.5°	870.2	913.3	964.7	1017.1	1068.1	1119.6	1172.7	1226.2	1267.8	1322.0	1357.9
20°	860.0	909.8	962.6	1025.0	1076.0	1140.2	1193.0	1244.6	1301.8	1355.8	1398.7
22.5°	845.6	900.1	956.2	1018.2	1085.3	1149.5	1210.6	1266.7	1323.9	1382.5	1434.5
25°	827.4	876.8	943.2	1013.6	1080.3	1150.1	1220.1	1290.5	1352.1	1414.1	1462.5
27.5°	796.3	858.8	920.6	993.3	1067.4	1146.2	1221.2	1294.9	1359.3	1410.3	1440.4
30°	780.4	834.6	901.8	974.8	1055.1	1139.8	1217.9	1290.2	1350.3	1391.0	1403.1
32.5°	757.0	812.9	878.6	954.2	1039.2	1126.2	1207.6	1275.7	1326.0	1347.3	1332.7
35°	722.1	772.7	839.1	916.4	1004.8	1097.6	1177.9	1235.5	1261.2	1241.0	1190.7
37.5°	680.2	730.5	797.1	873.1	964.6	1058.9	1131.5	1172.9	1164.4	1114.3	1039.3
40°	650.9	697.9	761.3	843.5	932.6	1027.2	1091.0	1113.4	1090.0	1018.0	938.5
42.5°	618.4	664.1	727.8	807.1	901.4	988.7	1044.3	1046.2	1006.9	921.0	841.0
45°	568.8	612.5	672.6	755.1	842.4	924.5	961.2	943.2	870.6	787.7	707.4
47.5°	519.9	557.7	617.0	695.3	778.2	847.3	865.5	833.2	755.8	675.3	600.9
50°	484.1	522.3	578.0	652.8	732.7	792.5	801.3	758.4	682.5	601.4	543.1
52.5°	449.8	487.6	541.3	610.5	683.7	737.6	737.9	688.2	612.7	540.5	486.2
55°	399.4	433.5	481.9	543.8	609.2	651.3	641.0	589.7	524.1	461.4	414.1
57.5°	350.8	380.5	425.1	476.8	534.3	569.1	552.0	502.7	444.0	390.9	355.0
60°	319.4	347.6	385.8	434.6	483.0	510.1	494.0	449.2	395.3	352.4	321.2
62.5°	288.9	312.7	349.4	391.7	436.6	456.8	442.3	398.2	351.7	312.8	287.5
65°	245.7	265.1	294.5	330.8	363.4	380.7	368.5	327.4	291.9	264.0	243.8
67.5°	205.4	220.6	242.8	271.9	299.6	309.0	297.9	269.3	239.2	216.9	202.6
70°	177.5	191.8	210.5	232.9	257.0	267.0	256.0	233.3	208.7	188.1	174.2
72.5°	153.2	164.2	180.0	199.2	218.0	228.0	220.5	198.6	177.9	162.6	150.7
75°	116.6	126.1	137.1	150.7	165.4	172.0	165.4	150.3	136.0	124.7	116.2
77.5°	84.8	89.9	98.4	108.6	117.7	122.8	117.1	106.9	98.1	90.4	86.1
80°	64.6	68.2	74.1	82.2	88.4	93.1	89.4	81.1	74.1	68.9	67.1
82.5°	46.9	49.4	53.3	59.3	63.4	65.9	64.3	58.2	55.3	50.7	48.9
85°	23.1	24.6	27.1	28.9	32.6	33.0	33.4	30.8	28.3	27.1	25.6
87.5°	9.4	10.5	12.1	13.6	15.4	16.2	16.4	16.9	16.2	16.3	15.6
90°	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1
92.5°	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9
95°	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1
97.5°	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9
100°	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8
102.5°	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5
105°	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1
107.5°	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7
110°	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2
115°	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0
117.5°	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3
120°	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5
122.5°	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8
125°	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7
127.5°	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9
130°	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4
132.5°	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8
135°	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5
137.5°	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1
140°	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9
142.5°	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3
145°	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1
147.5°	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8
150°	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3
152.5°	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6
155°	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8
157.5°	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7
160°	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7
162.5°	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7
165°	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7
167.5°	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3
170°	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1
172.5°	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9
175°	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9
177.5°	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	933.1	933.7	936.3	938.4	939.0	941.9	942.2
5°	1015.1	1021.3	1033.4	1034.5	1036.3	1045.9	1038.6
7.5°	1111.2	1127.0	1137.6	1146.9	1150.3	1154.4	1153.6
10°	1172.8	1196.3	1208.0	1226.7	1227.5	1232.2	1229.3
12.5°	1234.7	1262.0	1283.4	1286.9	1302.5	1305.0	1309.1
15°	1322.4	1351.4	1381.1	1391.8	1413.3	1418.5	1426.5
17.5°	1404.9	1434.5	1455.3	1482.8	1491.7	1503.5	1495.5
20°	1450.0	1482.3	1508.7	1530.3	1539.5	1546.1	1545.4
22.5°	1477.3	1509.9	1531.3	1547.7	1556.2	1559.1	1558.9
25°	1494.4	1513.2	1519.8	1526.0	1516.5	1513.2	1514.6
27.5°	1446.9	1442.0	1424.8	1402.2	1378.8	1360.1	1350.0
30°	1381.5	1352.8	1326.8	1281.4	1257.8	1244.0	1231.4
32.5°	1288.7	1243.4	1193.4	1151.7	1124.9	1104.3	1101.2
35°	1129.9	1061.7	1000.4	949.4	923.0	900.7	895.5
37.5°	960.6	889.8	834.6	789.7	761.3	745.6	730.8
40°	848.2	787.4	733.1	694.9	673.4	661.9	652.8
42.5°	761.7	706.1	652.1	623.0	603.5	596.5	591.2
45°	642.2	590.4	553.0	531.0	519.6	507.9	502.4
47.5°	546.4	504.4	479.7	461.0	448.8	441.9	438.3
50°	492.1	457.7	435.6	421.4	410.4	404.8	401.9
52.5°	444.0	415.8	397.3	385.9	378.4	374.4	373.2
55°	382.5	360.9	349.1	339.2	333.8	330.1	328.6
57.5°	332.4	315.8	306.3	298.1	296.1	292.9	291.9
60°	299.6	286.8	278.7	273.2	271.4	267.7	268.4
62.5°	270.6	260.0	253.2	250.1	247.6	244.5	245.5
65°	228.8	221.1	217.4	214.5	211.6	209.8	211.2
67.5°	192.0	186.7	181.7	180.0	178.6	178.3	176.7
70°	168.0	163.5	159.2	158.1	158.1	156.6	156.2
72.5°	144.8	141.6	138.6	137.8	136.7	137.2	135.7
75°	111.9	109.2	108.2	107.1	106.7	106.7	105.7
77.5°	82.7	80.8	79.0	79.0	77.7	77.2	77.0
80°	62.7	62.0	60.5	60.5	59.8	60.1	59.4
82.5°	47.1	46.1	45.8	45.2	44.2	44.3	43.5
85°	25.3	24.2	23.8	22.7	22.0	22.7	22.0
87.5°	16.2	16.3	16.2	15.7	15.6	15.7	15.0
90°	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P332769-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)