

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332751-830

Luminaire Tested: **S124DIW-S575D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332751-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D770U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5338.7 lumens
Efficiency: N/A
Efficacy: 142.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46					46			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39					39			
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33					33			
3	81	72	64	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28					28			
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24					24			
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21					21			
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19					19			
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17					17			
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15					15			
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16	14					14			
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	19	16	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7146	7146	7146	7146
5°	8417	7165	6324	7165
10°	10077	7133	5694	7133
15°	11922	7061	5229	7061
20°	13277	6988	4814	6988
25°	13491	6879	4528	6879
30°	11479	6776	4437	6776
35°	8825	6606	4438	6606
40°	6880	6407	4521	6407
45°	5736	6109	4598	6109
50°	5048	5743	4752	5743
55°	4625	5306	4944	5306
60°	4334	4913	5176	4913
65°	4034	4476	5366	4476
70°	3687	4043	5488	4043
75°	3297	3556	5421	3556
80°	2762	2915	5249	2915
85°	2038	2103	5030	2103



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.6
10°-20°	265.8	5.0
20°-30°	421.5	7.9
30°-40°	469.1	8.8
40°-50°	427.0	8.0
50°-60°	349.0	6.5
60°-70°	249.1	4.7
70°-80°	137.2	2.6
80°-90°	40.1	0.8
90°-100°	32.0	0.6
100°-110°	204.0	3.8
110°-120°	390.2	7.3
120°-130°	495.4	9.3
130°-140°	530.0	9.9
140°-150°	495.6	9.3
150°-160°	399.7	7.5
160°-170°	257.8	4.8
170°-180°	88.8	1.7
0°-30°	773.6	14.5
0°-40°	1242.8	23.3
0°-60°	2018.8	37.8
0°-90°	2445.2	45.8
90°-120°	626.2	11.7
90°-150°	2147.2	40.2
90°-180°	2894.0	54.2
0°-180°	5338.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	885	885	885	885	885	
5°	1039	884	780	884	1039	106
15°	1426	845	626	845	1426	403
25°	1515	772	508	772	1515	668
35°	896	670	450	670	896	568
45°	502	535	403	535	502	396
55°	329	377	351	377	329	297
65°	211	234	281	234	211	209
75°	106	114	174	114	106	112
85°	22	23	54	23	22	27
90°	21	2	21	2	21	10
95°	20	38	20	38	20	16
105°	199	211	199	211	199	174
115°	396	393	396	393	396	392
125°	557	553	557	553	557	496
135°	690	686	690	686	690	532
145°	795	791	795	791	795	497
155°	866	867	866	867	866	399
165°	910	914	910	914	910	257
175°	930	935	930	935	930	89
180°	935	935	935	935	935	



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	942.2	941.9	939.0	938.4	936.3	933.7	933.1	928.4	919.0	914.6	913.4
5°	1038.6	1045.9	1036.3	1034.5	1033.4	1021.3	1015.1	1007.8	990.9	981.0	973.3
7.5°	1153.6	1154.4	1150.3	1146.9	1137.6	1127.0	1111.2	1094.3	1074.2	1053.3	1037.6
10°	1229.3	1232.2	1227.5	1226.7	1208.0	1196.3	1172.8	1153.0	1130.2	1104.9	1081.9
12.5°	1309.1	1305.0	1302.5	1286.9	1283.4	1262.0	1234.7	1214.3	1179.2	1150.1	1119.4
15°	1426.5	1418.5	1413.3	1391.8	1381.1	1351.4	1322.4	1300.0	1254.2	1210.6	1177.5
17.5°	1495.5	1503.5	1491.7	1482.8	1455.3	1434.5	1404.9	1357.9	1322.0	1267.8	1226.2
20°	1545.4	1546.1	1539.5	1530.3	1508.7	1482.3	1450.0	1398.7	1355.8	1301.8	1244.6
22.5°	1558.9	1559.1	1556.2	1547.7	1531.3	1509.9	1477.3	1434.5	1382.5	1323.9	1266.7
25°	1514.6	1513.2	1516.5	1526.0	1519.8	1513.2	1494.4	1462.5	1414.1	1352.1	1290.5
27.5°	1350.0	1360.1	1378.8	1402.2	1424.8	1442.0	1446.9	1440.4	1410.3	1359.3	1294.9
30°	1231.4	1244.0	1257.8	1281.4	1326.8	1352.8	1381.5	1403.1	1391.0	1350.3	1290.2
32.5°	1101.2	1104.3	1124.9	1151.7	1193.4	1243.4	1288.7	1332.7	1347.3	1326.0	1275.7
35°	895.5	900.7	923.0	949.4	1000.4	1061.7	1129.9	1190.7	1241.0	1261.2	1235.5
37.5°	730.8	745.6	761.3	789.7	834.6	889.8	960.6	1039.3	1114.3	1164.4	1172.9
40°	652.8	661.9	673.4	694.9	733.1	787.4	848.2	938.5	1018.0	1090.0	1113.4
42.5°	591.2	596.5	603.5	623.0	652.1	706.1	761.7	841.0	921.0	1006.9	1046.2
45°	502.4	507.9	519.6	531.0	553.0	590.4	642.2	707.4	787.7	870.6	943.2
47.5°	438.3	441.9	448.8	461.0	479.7	504.4	546.4	600.9	675.3	755.8	833.2
50°	401.9	404.8	410.4	421.4	435.6	457.7	492.1	543.1	601.4	682.5	758.4
52.5°	373.2	374.4	378.4	385.9	397.3	415.8	444.0	486.2	540.5	612.7	688.2
55°	328.6	330.1	333.8	339.2	349.1	360.9	382.5	414.1	461.4	524.1	589.7
57.5°	291.9	292.9	296.1	298.1	306.3	315.8	332.4	355.0	390.9	444.0	502.7
60°	268.4	267.7	271.4	273.2	278.7	286.8	299.6	321.2	352.4	395.3	449.2
62.5°	245.5	244.5	247.6	250.1	253.2	260.0	270.6	287.5	312.8	351.7	398.2
65°	211.2	209.8	211.6	214.5	217.4	221.1	228.8	243.8	264.0	291.9	327.4
67.5°	176.7	178.3	178.6	180.0	181.7	186.7	192.0	202.6	216.9	239.2	269.3
70°	156.2	156.6	158.1	158.1	159.2	163.5	168.0	174.2	188.1	208.7	233.3
72.5°	135.7	137.2	136.7	137.8	138.6	141.6	144.8	150.7	162.6	177.9	198.6
75°	105.7	106.7	106.7	107.1	108.2	109.2	111.9	116.2	124.7	136.0	150.3
77.5°	77.0	77.2	77.7	79.0	79.0	80.8	82.7	86.1	90.4	98.1	106.9
80°	59.4	60.1	59.8	60.5	60.5	62.0	62.7	67.1	68.9	74.1	81.1
82.5°	43.5	44.3	44.2	45.2	45.8	46.1	47.1	48.9	50.7	55.3	58.2
85°	22.0	22.7	22.0	22.7	23.8	24.2	25.3	25.6	27.1	28.3	30.8
87.5°	10.7	11.5	11.4	11.6	12.2	12.3	12.4	12.0	12.9	13.0	13.9
90°	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2	16.3	15.4	14.1
92.5°	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7	15.7	14.8	13.6
95°	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2	16.3	15.4	15.3
97.5°	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6	18.5	35.8
100°	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5	28.2	30.8	52.2
102.5°	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3	119.8	148.4	151.1
105°	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1	219.7	218.3	217.5
107.5°	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5	272.9	272.1	271.1
110°	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2	308.9	308.5	307.6



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7	343.7	343.8	343.4
115°	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2	394.9	394.5	394.7
117.5°	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0	447.1	447.2	446.9
120°	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5	478.7
122.5°	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9	510.7	510.5	510.2
125°	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1	554.6	554.1	554.4
127.5°	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0	599.1	599.2	598.4
130°	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8	625.7	625.5	625.0
132.5°	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1	652.0	651.8	651.2
135°	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3	688.1	687.8	687.1
137.5°	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1	722.7	722.5	721.8
140°	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6	744.1	743.8	743.4
142.5°	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6	764.2	763.8	763.6
145°	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0	792.9	792.7	792.7
147.5°	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9	817.8	817.7	817.8
150°	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0	834.0	834.0	834.2
152.5°	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9	847.6	847.4	847.7
155°	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7	866.1	865.4	865.9
157.5°	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3	881.7
160°	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4	891.5
162.5°	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6	900.7	899.8	899.8
165°	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4	912.2	911.0	911.0
167.5°	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1	920.7	919.4	919.5
170°	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4	926.1	924.9	924.7
172.5°	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8	929.5	928.3	928.1
175°	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7	933.3	931.9	931.8
177.5°	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3	935.3	934.2	934.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	913.7	909.6	906.7	904.4	897.9	894.1	891.2	887.0	882.3	877.3	871.2
5°	965.6	953.1	944.0	930.0	916.8	905.8	894.5	884.2	871.7	858.2	848.2
7.5°	1020.1	1001.5	977.8	957.2	934.0	913.8	895.8	877.3	858.1	839.4	822.4
10°	1054.7	1030.9	1004.5	973.3	944.0	917.9	893.7	870.2	847.5	824.7	805.3
12.5°	1091.9	1062.2	1023.2	986.7	953.9	919.1	889.9	861.1	833.7	809.8	787.1
15°	1142.0	1099.1	1054.0	1005.2	962.0	921.2	881.3	844.9	814.2	782.6	760.6
17.5°	1172.7	1119.6	1068.1	1017.1	964.7	913.3	870.2	828.4	789.8	758.5	730.8
20°	1193.0	1140.2	1076.0	1025.0	962.6	909.8	860.0	813.4	773.1	739.7	711.1
22.5°	1210.6	1149.5	1085.3	1018.2	956.2	900.1	845.6	798.7	757.5	722.4	694.9
25°	1220.1	1150.1	1080.3	1013.6	943.2	876.8	827.4	772.3	728.3	691.3	661.9
27.5°	1221.2	1146.2	1067.4	993.3	920.6	858.8	796.3	747.1	701.4	662.2	634.0
30°	1217.9	1139.8	1055.1	974.8	901.8	834.6	780.4	726.9	680.2	641.4	612.1
32.5°	1207.6	1126.2	1039.2	954.2	878.6	812.9	757.0	706.1	660.6	622.4	591.5
35°	1177.9	1097.6	1004.8	916.4	839.1	772.7	722.1	670.3	624.9	588.6	558.9
37.5°	1131.5	1058.9	964.6	873.1	797.1	730.5	680.2	633.6	592.6	555.6	525.2
40°	1091.0	1027.2	932.6	843.5	761.3	697.9	650.9	608.0	567.3	532.4	503.5
42.5°	1044.3	988.7	901.4	807.1	727.8	664.1	618.4	579.9	541.5	509.3	480.3
45°	961.2	924.5	842.4	755.1	672.6	612.5	568.8	535.1	502.8	471.3	447.0
47.5°	865.5	847.3	778.2	695.3	617.0	557.7	519.9	488.7	460.4	433.7	412.4
50°	801.3	792.5	732.7	652.8	578.0	522.3	484.1	457.3	433.1	409.6	389.5
52.5°	737.9	737.6	683.7	610.5	541.3	487.6	449.8	424.7	403.8	384.7	366.6
55°	641.0	651.3	609.2	543.8	481.9	433.5	399.4	377.0	362.3	346.6	333.0
57.5°	552.0	569.1	534.3	476.8	425.1	380.5	350.8	334.0	318.4	308.9	299.0
60°	494.0	510.1	483.0	434.6	385.8	347.6	319.4	304.3	290.8	284.2	277.2
62.5°	442.3	456.8	436.6	391.7	349.4	312.7	288.9	274.5	265.3	258.1	253.4
65°	368.5	380.7	363.4	330.8	294.5	265.1	245.7	234.3	225.6	222.6	217.4
67.5°	297.9	309.0	299.6	271.9	242.8	220.6	205.4	194.4	189.3	186.6	183.0
70°	256.0	267.0	257.0	232.9	210.5	191.8	177.5	171.3	165.8	164.7	159.6
72.5°	220.5	228.0	218.0	199.2	180.0	164.2	153.2	146.7	143.7	141.8	139.0
75°	165.4	172.0	165.4	150.7	137.1	126.1	116.6	114.0	110.7	109.6	107.8
77.5°	117.1	122.8	117.7	108.6	98.4	89.9	84.8	81.5	80.8	78.9	79.7
80°	89.4	93.1	88.4	82.2	74.1	68.2	64.6	62.7	60.5	59.8	61.3
82.5°	64.3	65.9	63.4	59.3	53.3	49.4	46.9	44.8	44.4	44.5	44.5
85°	33.4	33.0	32.6	28.9	27.1	24.6	23.1	22.7	22.3	23.1	23.8
87.5°	13.8	13.8	13.2	11.8	10.6	9.3	8.7	8.0	8.7	9.3	10.0
90°	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1	3.8	5.6	7.3
92.5°	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9	9.0	9.0	9.0
95°	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5	33.2	27.9	22.6
97.5°	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7	85.0	88.3	91.6
100°	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7	117.5	120.4	123.1
102.5°	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7	153.7	155.8	157.9
105°	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6	211.5	212.4	213.4
107.5°	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3	265.8	266.3	266.7
110°	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3	302.7	303.2	303.7



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1	338.9	339.8	340.5
115°	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2	393.7	394.2	394.5
117.5°	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9	443.5	444.1	444.7
120°	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5	477.1	477.7	478.3
122.5°	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8	508.1	508.5	508.9
125°	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7	553.4	553.9	554.6
127.5°	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2	595.4	595.6	595.7
130°	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6	622.8	623.0	623.1
132.5°	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9	648.2	648.5	648.7
135°	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6	685.5	685.3	685.1
137.5°	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1	719.2	719.3	719.3
140°	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9	741.2	741.5	741.9
142.5°	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5	761.1	761.7	762.1
145°	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6	791.1	791.5	792.0
147.5°	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5	815.4	816.2	817.1
150°	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9	832.5	833.1	833.8
152.5°	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4	846.9	847.4	847.9
155°	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9	867.0	867.1	867.3
157.5°	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1	884.0	883.9	883.8
160°	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1	893.6	893.2	892.8
162.5°	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1	902.5	901.9	901.4
165°	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5	913.6	912.9	912.1
167.5°	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4	922.6	921.8	921.0
170°	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4	927.5	926.5	925.6
172.5°	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8	930.9	929.9	929.0
175°	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4	934.4	933.6	932.6
177.5°	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1	936.2	935.4	934.4
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	868.3	865.6	861.8	856.5	852.2	847.4	846.2	844.5	848.0	845.1	844.2
5°	839.8	832.1	822.2	810.9	804.3	794.7	792.9	789.2	785.5	785.1	781.5
7.5°	809.6	798.3	785.4	773.8	763.1	752.7	745.8	744.4	739.0	735.8	732.2
10°	790.3	776.4	761.3	750.4	737.8	726.9	719.2	714.7	711.1	707.0	703.4
12.5°	767.4	752.6	740.2	728.3	713.5	705.1	692.5	684.9	684.1	684.2	674.7
15°	740.7	726.1	707.0	690.2	682.1	666.0	659.0	650.2	644.7	639.2	634.8
17.5°	710.4	692.1	677.2	657.8	642.4	629.6	620.4	615.1	606.9	599.1	593.4
20°	691.3	671.8	656.1	635.6	618.7	602.9	595.2	587.9	581.6	575.0	568.8
22.5°	671.9	651.6	632.4	612.4	596.6	580.0	572.6	562.6	556.7	553.0	546.8
25°	641.4	619.4	597.4	578.3	562.2	547.5	537.6	529.9	523.3	520.4	516.3
27.5°	608.2	586.4	565.1	543.5	525.2	514.5	506.6	500.8	497.0	493.1	491.3
30°	587.1	564.4	541.7	521.5	504.6	494.0	486.6	482.6	479.7	477.9	476.0
32.5°	565.7	543.3	519.3	501.0	485.9	476.4	470.8	466.7	465.3	464.7	464.0
35°	531.4	508.7	486.6	470.1	455.8	452.1	447.4	445.2	444.5	447.0	448.2
37.5°	498.1	477.0	456.8	440.8	431.4	426.0	424.4	424.5	427.2	429.4	432.1
40°	476.7	456.2	437.2	423.2	414.4	411.1	410.4	412.2	415.1	417.7	420.7
42.5°	455.9	435.6	418.4	405.3	399.2	396.2	396.6	398.4	402.6	405.7	410.1
45°	423.6	406.7	389.8	379.2	374.1	374.8	374.8	378.1	382.1	386.9	391.6
47.5°	393.1	376.1	362.2	353.3	350.6	350.0	352.0	356.4	362.2	368.1	374.8
50°	372.6	356.5	344.3	336.3	333.4	334.4	337.4	341.4	348.4	355.7	362.7
52.5°	351.8	337.1	325.8	318.4	316.3	318.3	321.2	327.6	333.8	341.7	350.1
55°	319.4	307.0	298.1	292.7	291.9	293.0	296.3	303.3	312.1	322.0	330.1
57.5°	287.2	276.8	268.7	264.9	265.3	266.4	271.7	280.0	289.5	300.0	310.4
60°	265.5	256.0	249.4	246.5	246.9	249.0	255.6	263.3	275.0	285.3	296.3
62.5°	245.0	236.6	230.3	227.6	227.2	232.0	238.3	246.3	258.1	269.5	281.3
65°	212.0	205.4	200.2	198.8	199.8	203.5	211.6	222.3	232.1	244.2	256.7
67.5°	179.6	174.3	170.8	171.4	172.8	178.1	184.9	194.1	205.3	217.8	230.2
70°	159.2	154.0	151.1	151.5	153.6	160.2	166.2	175.3	187.4	200.2	210.5
72.5°	138.1	134.7	132.1	133.6	135.7	140.3	147.6	156.8	167.5	179.4	190.3
75°	105.9	105.9	104.5	105.7	109.0	113.3	118.9	128.4	139.0	148.5	157.3
77.5°	78.6	77.9	78.8	80.1	82.0	87.2	93.5	100.4	108.3	117.9	125.2
80°	60.1	60.5	62.3	64.6	65.3	69.3	75.9	82.2	88.4	96.4	103.4
82.5°	45.1	45.5	46.5	49.3	50.0	54.4	58.6	64.8	70.5	75.9	81.7
85°	24.6	24.6	26.4	27.5	29.3	32.2	34.9	38.5	43.6	47.3	52.8
87.5°	11.2	11.5	12.9	13.8	14.9	16.6	17.3	20.7	22.1	23.8	26.6
90°	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2	18.2	19.1	19.7
92.5°	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7	17.6	18.6	19.0
95°	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2	18.2	19.1	19.7
97.5°	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7	18.8	18.9	18.9
100°	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5	22.8	20.2	18.9
102.5°	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3	62.8	34.3	20.0
105°	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1	222.4	223.9	221.8
107.5°	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5	274.2	274.9	275.5
110°	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2	309.4	309.8	310.2



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7	343.7	343.6	343.8
115°	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2	395.5	395.9	396.0
117.5°	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0	447.0	447.0	446.9
120°	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2	479.5	479.8	479.8
122.5°	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9	511.0	511.2	511.1
125°	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1	555.5	556.0	556.3
127.5°	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0	598.9	598.8	598.7
130°	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8	625.9	626.1	626.1
132.5°	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1	652.2	652.4	652.4
135°	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3	688.7	689.0	689.3
137.5°	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1	723.5	723.8	724.0
140°	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6	745.1	745.6	745.9
142.5°	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6	764.9	765.3	765.4
145°	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0	793.1	793.3	793.5
147.5°	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9	818.1	818.2	818.4
150°	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0	834.0	834.0	834.1
152.5°	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9	848.1	848.4	848.5
155°	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7	867.3	867.9	868.0
157.5°	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9	883.7	884.5	884.5
160°	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2	894.1	895.0	895.0
162.5°	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6	902.5	903.4	903.4
165°	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4	914.6	915.9	915.9
167.5°	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1	923.4	924.8	924.7
170°	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4	928.7	929.9	929.7
172.5°	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8	932.0	933.2	933.0
175°	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7	936.1	937.5	937.3
177.5°	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3	937.3	938.3	938.0
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	843.6	843.0	840.9	840.7	840.9	843.0	843.6	844.2	845.1	848.0	844.5
5°	779.3	777.5	776.4	780.4	776.4	777.5	779.3	781.5	785.1	785.5	789.2
7.5°	730.8	729.3	726.1	725.1	726.1	729.3	730.8	732.2	735.8	739.0	744.4
10°	699.7	698.2	695.3	694.6	695.3	698.2	699.7	703.4	707.0	711.1	714.7
12.5°	669.8	666.8	666.3	667.0	666.3	666.8	669.8	674.7	684.2	684.1	684.9
15°	630.0	628.6	624.5	625.7	624.5	628.6	630.0	634.8	639.2	644.7	650.2
17.5°	590.9	589.1	584.2	588.5	584.2	589.1	590.9	593.4	599.1	606.9	615.1
20°	566.2	563.3	560.7	560.3	560.7	563.3	566.2	568.8	575.0	581.6	587.9
22.5°	542.7	540.1	539.9	537.4	539.9	540.1	542.7	546.8	553.0	556.7	562.6
25°	513.4	510.9	510.1	508.3	510.1	510.9	513.4	516.3	520.4	523.3	529.9
27.5°	490.9	489.7	488.3	488.9	488.3	489.7	490.9	491.3	493.1	497.0	500.8
30°	477.1	476.7	476.0	476.0	476.0	476.7	477.1	476.0	477.9	479.7	482.6
32.5°	465.7	465.6	466.0	466.0	466.0	465.6	465.7	464.0	464.7	465.3	466.7
35°	449.6	450.7	451.5	450.3	451.5	450.7	449.6	448.2	447.0	444.5	445.2
37.5°	435.1	436.2	437.2	438.5	437.2	436.2	435.1	432.1	429.4	427.2	424.5
40°	424.0	426.5	427.3	429.0	427.3	426.5	424.0	420.7	417.7	415.1	412.2
42.5°	413.4	416.2	418.1	418.5	418.1	416.2	413.4	410.1	405.7	402.6	398.4
45°	397.2	400.1	402.7	402.7	402.7	400.1	397.2	391.6	386.9	382.1	378.1
47.5°	380.4	384.7	387.2	387.9	387.2	384.7	380.4	374.8	368.1	362.2	356.4
50°	368.9	374.1	376.6	378.4	376.6	374.1	368.9	362.7	355.7	348.4	341.4
52.5°	357.8	362.9	366.4	367.3	366.4	362.9	357.8	350.1	341.7	333.8	327.6
55°	338.5	345.8	349.9	351.3	349.9	345.8	338.5	330.1	322.0	312.1	303.3
57.5°	320.3	327.1	331.8	332.8	331.8	327.1	320.3	310.4	300.0	289.5	280.0
60°	306.2	313.6	319.4	320.6	319.4	313.6	306.2	296.3	285.3	275.0	263.3
62.5°	291.8	299.4	304.7	307.6	304.7	299.4	291.8	281.3	269.5	258.1	246.3
65°	267.0	274.7	279.8	280.9	279.8	274.7	267.0	256.7	244.2	232.1	222.3
67.5°	239.9	247.5	250.9	253.1	250.9	247.5	239.9	230.2	217.8	205.3	194.1
70°	220.7	227.0	230.6	232.5	230.6	227.0	220.7	210.5	200.2	187.4	175.3
72.5°	199.1	205.6	209.8	210.2	209.8	205.6	199.1	190.3	179.4	167.5	156.8
75°	165.8	171.6	173.8	173.8	173.8	171.6	165.8	157.3	148.5	139.0	128.4
77.5°	131.2	134.2	137.0	137.6	137.0	134.2	131.2	125.2	117.9	108.3	100.4
80°	109.0	110.7	112.9	112.9	112.9	110.7	109.0	103.4	96.4	88.4	82.2
82.5°	86.1	87.6	89.7	89.4	89.7	87.6	86.1	81.7	75.9	70.5	64.8
85°	52.0	55.4	55.0	54.3	55.0	55.4	52.0	52.8	47.3	43.6	38.5
87.5°	27.5	27.8	28.7	29.4	28.7	27.8	27.5	26.6	23.8	22.1	20.7
90°	20.1	20.4	20.6	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2
92.5°	19.1	19.2	19.2	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7
95°	19.8	20.0	20.2	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2
97.5°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7
100°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5
102.5°	20.1	20.1	20.1	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3
105°	216.2	210.6	205.0	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1
107.5°	276.2	276.7	277.3	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5
110°	310.7	311.1	311.6	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.4	345.0	345.6	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7
115°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2
117.5°	446.9	446.8	446.7	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0
120°	479.5	479.2	478.9	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2
122.5°	510.9	510.5	510.2	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9
125°	556.5	556.6	556.8	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1
127.5°	598.6	598.4	598.3	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0
130°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8
132.5°	652.3	652.1	652.1	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1
135°	689.6	689.9	690.2	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3
137.5°	723.9	723.8	723.7	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1
140°	746.0	746.2	746.4	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6
142.5°	765.4	765.4	765.5	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6
145°	793.8	794.2	794.5	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0
147.5°	818.5	818.7	818.9	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9
150°	834.2	834.3	834.5	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0
152.5°	848.4	848.3	848.2	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9
155°	867.5	867.0	866.6	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7
157.5°	883.7	882.9	882.0	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9
160°	894.1	893.2	892.3	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2
162.5°	902.4	901.3	900.2	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6
165°	914.5	913.0	911.6	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4
167.5°	923.1	921.6	920.0	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1
170°	928.2	926.6	925.1	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4
172.5°	931.3	929.7	928.0	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8
175°	935.4	933.6	931.7	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7
177.5°	936.5	935.0	933.6	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	846.2	847.4	852.2	856.5	861.8	865.6	868.3	871.2	877.3	882.3	887.0
5°	792.9	794.7	804.3	810.9	822.2	832.1	839.8	848.2	858.2	871.7	884.2
7.5°	745.8	752.7	763.1	773.8	785.4	798.3	809.6	822.4	839.4	858.1	877.3
10°	719.2	726.9	737.8	750.4	761.3	776.4	790.3	805.3	824.7	847.5	870.2
12.5°	692.5	705.1	713.5	728.3	740.2	752.6	767.4	787.1	809.8	833.7	861.1
15°	659.0	666.0	682.1	690.2	707.0	726.1	740.7	760.6	782.6	814.2	844.9
17.5°	620.4	629.6	642.4	657.8	677.2	692.1	710.4	730.8	758.5	789.8	828.4
20°	595.2	602.9	618.7	635.6	656.1	671.8	691.3	711.1	739.7	773.1	813.4
22.5°	572.6	580.0	596.6	612.4	632.4	651.6	671.9	694.9	722.4	757.5	798.7
25°	537.6	547.5	562.2	578.3	597.4	619.4	641.4	661.9	691.3	728.3	772.3
27.5°	506.6	514.5	525.2	543.5	565.1	586.4	608.2	634.0	662.2	701.4	747.1
30°	486.6	494.0	504.6	521.5	541.7	564.4	587.1	612.1	641.4	680.2	726.9
32.5°	470.8	476.4	485.9	501.0	519.3	543.3	565.7	591.5	622.4	660.6	706.1
35°	447.4	452.1	455.8	470.1	486.6	508.7	531.4	558.9	588.6	624.9	670.3
37.5°	424.4	426.0	431.4	440.8	456.8	477.0	498.1	525.2	555.6	592.6	633.6
40°	410.4	411.1	414.4	423.2	437.2	456.2	476.7	503.5	532.4	567.3	608.0
42.5°	396.6	396.2	399.2	405.3	418.4	435.6	455.9	480.3	509.3	541.5	579.9
45°	374.8	374.8	374.1	379.2	389.8	406.7	423.6	447.0	471.3	502.8	535.1
47.5°	352.0	350.0	350.6	353.3	362.2	376.1	393.1	412.4	433.7	460.4	488.7
50°	337.4	334.4	333.4	336.3	344.3	356.5	372.6	389.5	409.6	433.1	457.3
52.5°	321.2	318.3	316.3	318.4	325.8	337.1	351.8	366.6	384.7	403.8	424.7
55°	296.3	293.0	291.9	292.7	298.1	307.0	319.4	333.0	346.6	362.3	377.0
57.5°	271.7	266.4	265.3	264.9	268.7	276.8	287.2	299.0	308.9	318.4	334.0
60°	255.6	249.0	246.9	246.5	249.4	256.0	265.5	277.2	284.2	290.8	304.3
62.5°	238.3	232.0	227.2	227.6	230.3	236.6	245.0	253.4	258.1	265.3	274.5
65°	211.6	203.5	199.8	198.8	200.2	205.4	212.0	217.4	222.6	225.6	234.3
67.5°	184.9	178.1	172.8	171.4	170.8	174.3	179.6	183.0	186.6	189.3	194.4
70°	166.2	160.2	153.6	151.5	151.1	154.0	159.2	159.6	164.7	165.8	171.3
72.5°	147.6	140.3	135.7	133.6	132.1	134.7	138.1	139.0	141.8	143.7	146.7
75°	118.9	113.3	109.0	105.7	104.5	105.9	105.9	107.8	109.6	110.7	114.0
77.5°	93.5	87.2	82.0	80.1	78.8	77.9	78.6	79.7	78.9	80.8	81.5
80°	75.9	69.3	65.3	64.6	62.3	60.5	60.1	61.3	59.8	60.5	62.7
82.5°	58.6	54.4	50.0	49.3	46.5	45.5	45.1	44.5	44.5	44.4	44.8
85°	34.9	32.2	29.3	27.5	26.4	24.6	24.6	23.8	23.1	22.3	22.7
87.5°	17.3	16.6	14.9	13.8	12.9	11.5	11.2	10.0	9.3	8.7	8.0
90°	16.3	15.4	14.1	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1
92.5°	15.7	14.8	13.6	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9
95°	16.3	15.4	15.3	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5
97.5°	18.6	18.5	35.8	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7
100°	28.2	30.8	52.2	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7
102.5°	119.8	148.4	151.1	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7
105°	219.7	218.3	217.5	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6
107.5°	272.9	272.1	271.1	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3
110°	308.9	308.5	307.6	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	343.7	343.8	343.4	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1
115°	394.9	394.5	394.7	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2
117.5°	447.1	447.2	446.9	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9
120°	478.9	478.5	478.7	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5
122.5°	510.7	510.5	510.2	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8
125°	554.6	554.1	554.4	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7
127.5°	599.1	599.2	598.4	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2
130°	625.7	625.5	625.0	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6
132.5°	652.0	651.8	651.2	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9
135°	688.1	687.8	687.1	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6
137.5°	722.7	722.5	721.8	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1
140°	744.1	743.8	743.4	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9
142.5°	764.2	763.8	763.6	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5
145°	792.9	792.7	792.7	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6
147.5°	817.8	817.7	817.8	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5
150°	834.0	834.0	834.2	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9
152.5°	847.6	847.4	847.7	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4
155°	866.1	865.4	865.9	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9
157.5°	882.0	881.3	881.7	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1
160°	892.3	891.4	891.5	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1
162.5°	900.7	899.8	899.8	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1
165°	912.2	911.0	911.0	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5
167.5°	920.7	919.4	919.5	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4
170°	926.1	924.9	924.7	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4
172.5°	929.5	928.3	928.1	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8
175°	933.3	931.9	931.8	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4
177.5°	935.3	934.2	934.1	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	891.2	894.1	897.9	904.4	906.7	909.6	913.7	913.4	914.6	919.0	928.4
5°	894.5	905.8	916.8	930.0	944.0	953.1	965.6	973.3	981.0	990.9	1007.8
7.5°	895.8	913.8	934.0	957.2	977.8	1001.5	1020.1	1037.6	1053.3	1074.2	1094.3
10°	893.7	917.9	944.0	973.3	1004.5	1030.9	1054.7	1081.9	1104.9	1130.2	1153.0
12.5°	889.9	919.1	953.9	986.7	1023.2	1062.2	1091.9	1119.4	1150.1	1179.2	1214.3
15°	881.3	921.2	962.0	1005.2	1054.0	1099.1	1142.0	1177.5	1210.6	1254.2	1300.0
17.5°	870.2	913.3	964.7	1017.1	1068.1	1119.6	1172.7	1226.2	1267.8	1322.0	1357.9
20°	860.0	909.8	962.6	1025.0	1076.0	1140.2	1193.0	1244.6	1301.8	1355.8	1398.7
22.5°	845.6	900.1	956.2	1018.2	1085.3	1149.5	1210.6	1266.7	1323.9	1382.5	1434.5
25°	827.4	876.8	943.2	1013.6	1080.3	1150.1	1220.1	1290.5	1352.1	1414.1	1462.5
27.5°	796.3	858.8	920.6	993.3	1067.4	1146.2	1221.2	1294.9	1359.3	1410.3	1440.4
30°	780.4	834.6	901.8	974.8	1055.1	1139.8	1217.9	1290.2	1350.3	1391.0	1403.1
32.5°	757.0	812.9	878.6	954.2	1039.2	1126.2	1207.6	1275.7	1326.0	1347.3	1332.7
35°	722.1	772.7	839.1	916.4	1004.8	1097.6	1177.9	1235.5	1261.2	1241.0	1190.7
37.5°	680.2	730.5	797.1	873.1	964.6	1058.9	1131.5	1172.9	1164.4	1114.3	1039.3
40°	650.9	697.9	761.3	843.5	932.6	1027.2	1091.0	1113.4	1090.0	1018.0	938.5
42.5°	618.4	664.1	727.8	807.1	901.4	988.7	1044.3	1046.2	1006.9	921.0	841.0
45°	568.8	612.5	672.6	755.1	842.4	924.5	961.2	943.2	870.6	787.7	707.4
47.5°	519.9	557.7	617.0	695.3	778.2	847.3	865.5	833.2	755.8	675.3	600.9
50°	484.1	522.3	578.0	652.8	732.7	792.5	801.3	758.4	682.5	601.4	543.1
52.5°	449.8	487.6	541.3	610.5	683.7	737.6	737.9	688.2	612.7	540.5	486.2
55°	399.4	433.5	481.9	543.8	609.2	651.3	641.0	589.7	524.1	461.4	414.1
57.5°	350.8	380.5	425.1	476.8	534.3	569.1	552.0	502.7	444.0	390.9	355.0
60°	319.4	347.6	385.8	434.6	483.0	510.1	494.0	449.2	395.3	352.4	321.2
62.5°	288.9	312.7	349.4	391.7	436.6	456.8	442.3	398.2	351.7	312.8	287.5
65°	245.7	265.1	294.5	330.8	363.4	380.7	368.5	327.4	291.9	264.0	243.8
67.5°	205.4	220.6	242.8	271.9	299.6	309.0	297.9	269.3	239.2	216.9	202.6
70°	177.5	191.8	210.5	232.9	257.0	267.0	256.0	233.3	208.7	188.1	174.2
72.5°	153.2	164.2	180.0	199.2	218.0	228.0	220.5	198.6	177.9	162.6	150.7
75°	116.6	126.1	137.1	150.7	165.4	172.0	165.4	150.3	136.0	124.7	116.2
77.5°	84.8	89.9	98.4	108.6	117.7	122.8	117.1	106.9	98.1	90.4	86.1
80°	64.6	68.2	74.1	82.2	88.4	93.1	89.4	81.1	74.1	68.9	67.1
82.5°	46.9	49.4	53.3	59.3	63.4	65.9	64.3	58.2	55.3	50.7	48.9
85°	23.1	24.6	27.1	28.9	32.6	33.0	33.4	30.8	28.3	27.1	25.6
87.5°	8.7	9.3	10.6	11.8	13.2	13.8	13.8	13.9	13.0	12.9	12.0
90°	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2
92.5°	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7
95°	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2
97.5°	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7
100°	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5
102.5°	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3
105°	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1
107.5°	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5
110°	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7
115°	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2
117.5°	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0
120°	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2
122.5°	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9
125°	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1
127.5°	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0
130°	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8
132.5°	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1
135°	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3
137.5°	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1
140°	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6
142.5°	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6
145°	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0
147.5°	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9
150°	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0
152.5°	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9
155°	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7
157.5°	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9
160°	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2
162.5°	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6
165°	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4
167.5°	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1
170°	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4
172.5°	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8
175°	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7
177.5°	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	933.1	933.7	936.3	938.4	939.0	941.9	942.2
5°	1015.1	1021.3	1033.4	1034.5	1036.3	1045.9	1038.6
7.5°	1111.2	1127.0	1137.6	1146.9	1150.3	1154.4	1153.6
10°	1172.8	1196.3	1208.0	1226.7	1227.5	1232.2	1229.3
12.5°	1234.7	1262.0	1283.4	1286.9	1302.5	1305.0	1309.1
15°	1322.4	1351.4	1381.1	1391.8	1413.3	1418.5	1426.5
17.5°	1404.9	1434.5	1455.3	1482.8	1491.7	1503.5	1495.5
20°	1450.0	1482.3	1508.7	1530.3	1539.5	1546.1	1545.4
22.5°	1477.3	1509.9	1531.3	1547.7	1556.2	1559.1	1558.9
25°	1494.4	1513.2	1519.8	1526.0	1516.5	1513.2	1514.6
27.5°	1446.9	1442.0	1424.8	1402.2	1378.8	1360.1	1350.0
30°	1381.5	1352.8	1326.8	1281.4	1257.8	1244.0	1231.4
32.5°	1288.7	1243.4	1193.4	1151.7	1124.9	1104.3	1101.2
35°	1129.9	1061.7	1000.4	949.4	923.0	900.7	895.5
37.5°	960.6	889.8	834.6	789.7	761.3	745.6	730.8
40°	848.2	787.4	733.1	694.9	673.4	661.9	652.8
42.5°	761.7	706.1	652.1	623.0	603.5	596.5	591.2
45°	642.2	590.4	553.0	531.0	519.6	507.9	502.4
47.5°	546.4	504.4	479.7	461.0	448.8	441.9	438.3
50°	492.1	457.7	435.6	421.4	410.4	404.8	401.9
52.5°	444.0	415.8	397.3	385.9	378.4	374.4	373.2
55°	382.5	360.9	349.1	339.2	333.8	330.1	328.6
57.5°	332.4	315.8	306.3	298.1	296.1	292.9	291.9
60°	299.6	286.8	278.7	273.2	271.4	267.7	268.4
62.5°	270.6	260.0	253.2	250.1	247.6	244.5	245.5
65°	228.8	221.1	217.4	214.5	211.6	209.8	211.2
67.5°	192.0	186.7	181.7	180.0	178.6	178.3	176.7
70°	168.0	163.5	159.2	158.1	158.1	156.6	156.2
72.5°	144.8	141.6	138.6	137.8	136.7	137.2	135.7
75°	111.9	109.2	108.2	107.1	106.7	106.7	105.7
77.5°	82.7	80.8	79.0	79.0	77.7	77.2	77.0
80°	62.7	62.0	60.5	60.5	59.8	60.1	59.4
82.5°	47.1	46.1	45.8	45.2	44.2	44.3	43.5
85°	25.3	24.2	23.8	22.7	22.0	22.7	22.0
87.5°	12.4	12.3	12.2	11.6	11.4	11.5	10.7
90°	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P332751-830

CATALOG NUMBER: S124DIW-S575D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)