

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333077-830

Luminaire Tested: **S124RDIW-S1020D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333077-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D470U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5700.5 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	54	50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43
4	79	68	60	54	74	64	57	51	58	52	48	52	47	44	47	43	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	33	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.8
10°-20°	445.8	7.8
20°-30°	643.8	11.3
30°-40°	729.7	12.8
40°-50°	704.7	12.4
50°-60°	586.0	10.3
60°-70°	404.6	7.1
70°-80°	205.1	3.6
80°-90°	54.3	1.0
90°-100°	19.5	0.3
100°-110°	124.6	2.2
110°-120°	238.3	4.2
120°-130°	302.4	5.3
130°-140°	323.6	5.7
140°-150°	302.6	5.3
150°-160°	244.0	4.3
160°-170°	157.4	2.8
170°-180°	54.2	1.0
0°-30°	1249.5	21.9
0°-40°	1979.2	34.7
0°-60°	3269.8	57.4
0°-90°	3933.8	69.0
90°-120°	382.4	6.7
90°-150°	1311.0	23.0
90°-180°	1767.0	31.0
0°-180°	5700.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	1	6	9	12	13	4
95°	24	10	9	12	12	30
105°	129	131	133	136	122	135
115°	240	241	241	242	242	236
125°	337	339	338	340	340	301
135°	419	418	420	421	422	322
145°	483	484	484	484	485	301
155°	529	530	528	530	529	244
165°	558	556	556	559	556	158
175°	571	569	569	572	568	54
180°	571	571	571	571	571	



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.2	22.6	20.9	19.3	17.6	16.8	16.7	16.6	16.6	16.5	16.4
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	5.4	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6
95°	23.5	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0
97.5°	49.9	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3
100°	70.0	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2
102.5°	92.7	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1
105°	128.6	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1
107.5°	162.0	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5
110°	184.5	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.4	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9
115°	240.1	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1
117.5°	270.4	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0
120°	290.9	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4
122.5°	310.0	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8
125°	337.4	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6
127.5°	363.4	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8
130°	380.1	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0
132.5°	395.6	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0
135°	418.6	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1
137.5°	439.0	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3
140°	452.3	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4
142.5°	464.3	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6
145°	482.7	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1
147.5°	497.3	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4
150°	507.9	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2
152.5°	516.8	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6
155°	529.2	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8
157.5°	539.8	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6
160°	545.9	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8
162.5°	551.4	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9
165°	558.3	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9
167.5°	563.7	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1
170°	566.8	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4
172.5°	568.9	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5
175°	571.1	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9
177.5°	572.1	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	16.2	16.1	16.0	16.1	16.3	16.6	16.9	17.2
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.2	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	10.6	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	15.6	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	55.7	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.0	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.0	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	188.8	189.0	189.2	189.4	189.6	189.9	190.2	190.5



TEST NUMBER: P333077-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	209.8	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.3	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	311.9	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	338.8	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.7	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.1	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.1	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.3	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.5	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	454.7	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	466.7	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.2	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.6	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.1	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	550.4	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	557.7	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.0	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.2	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	568.3	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	570.7	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	571.7	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)