

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333082-830

Luminaire Tested: **S124RDIW-S1020D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333082-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D770U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6444.4 lumens  
Efficiency: N/A  
Efficacy: 120.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	52	50	48
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	35	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.9	2.5
10°-20°	445.8	6.9
20°-30°	643.8	10.0
30°-40°	729.7	11.3
40°-50°	704.7	10.9
50°-60°	586.0	9.1
60°-70°	404.6	6.3
70°-80°	205.1	3.2
80°-90°	55.3	0.9
90°-100°	59.7	0.9
100°-110°	176.7	2.7
110°-120°	300.0	4.7
120°-130°	395.5	6.1
130°-140°	444.2	6.9
140°-150°	436.5	6.8
150°-160°	367.1	5.7
160°-170°	244.3	3.8
170°-180°	85.5	1.3
0°-30°	1249.5	19.4
0°-40°	1979.2	30.7
0°-60°	3269.8	50.7
0°-90°	3934.9	61.1
90°-120°	536.4	8.3
90°-150°	1812.6	28.1
90°-180°	2510.0	38.9
0°-180°	6444.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	2	10	15	19	21	6
95°	42	48	53	55	55	47
105°	163	164	166	169	171	173
115°	305	305	304	303	302	301
125°	444	444	444	442	441	396
135°	573	577	577	576	574	443
145°	696	699	700	699	697	435
155°	798	797	797	799	797	367
165°	868	866	865	868	866	245
175°	903	900	899	903	899	86
180°	904	904	904	904	904	



TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.4	22.9	21.4	19.9	18.4	17.6	17.6	17.6	17.6	17.7	17.6
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	15.0	17.0	18.9	20.8	22.8	24.2	25.1	25.9	26.9	27.7	28.3
95°	41.9	43.4	44.8	46.2	47.6	48.8	49.9	51.0	52.1	53.2	53.6
97.5°	73.3	74.5	75.6	76.6	77.8	79.0	80.3	81.5	82.8	84.1	84.6
100°	97.9	98.6	99.2	99.8	100.4	101.4	102.8	104.2	105.7	107.1	107.4
102.5°	123.7	123.9	124.1	124.4	124.7	125.5	126.7	128.0	129.2	130.5	131.0
105°	163.0	163.2	163.3	163.4	163.6	164.0	164.7	165.2	165.9	166.5	166.9
107.5°	204.2	204.4	204.6	204.8	205.0	205.2	205.3	205.4	205.5	205.6	205.9
110°	232.2	232.5	232.9	233.2	233.5	233.6	233.4	233.3	233.1	232.9	232.6



TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.4	261.4	261.5	261.6	261.6	261.5	261.2	260.9	260.6	260.3	260.3
115°	305.0	305.0	305.0	305.0	305.0	304.8	304.5	304.3	303.9	303.6	303.4
117.5°	346.1	346.3	346.4	346.5	346.7	346.6	346.4	346.2	345.9	345.7	345.2
120°	373.5	374.2	374.8	375.4	376.1	376.1	375.7	375.2	374.8	374.3	373.4
122.5°	402.1	402.4	402.6	402.8	403.1	403.1	402.9	402.7	402.5	402.3	401.7
125°	444.2	444.2	444.2	444.2	444.2	444.1	443.9	443.8	443.7	443.5	443.2
127.5°	482.4	482.9	483.3	483.8	484.3	484.4	484.1	483.9	483.6	483.4	483.1
130°	509.3	509.7	510.2	510.7	511.1	511.3	511.3	511.3	511.3	511.3	511.0
132.5°	536.7	537.1	537.3	537.7	538.1	538.2	538.0	537.9	537.8	537.6	537.3
135°	573.0	573.8	574.8	575.7	576.6	577.1	577.1	577.1	577.1	577.1	576.8
137.5°	612.4	612.8	613.2	613.7	614.2	614.4	614.7	614.9	615.2	615.5	615.0
140°	638.7	638.9	639.3	639.6	639.9	640.1	640.1	640.1	640.1	640.1	639.9
142.5°	662.7	663.1	663.4	663.6	664.0	664.1	663.9	663.8	663.7	663.5	663.5
145°	696.1	696.6	697.3	698.0	698.5	698.9	699.1	699.3	699.4	699.6	699.4
147.5°	729.1	729.8	730.6	731.3	732.1	732.4	732.3	732.1	732.0	731.9	731.7
150°	749.2	749.8	750.5	751.1	751.7	752.1	752.1	752.1	752.1	752.1	752.1
152.5°	768.3	768.6	769.0	769.4	769.8	770.0	770.1	770.2	770.3	770.4	770.8
155°	797.5	797.5	797.5	797.5	797.5	797.4	797.2	797.1	796.9	796.8	797.4
157.5°	822.1	821.8	821.5	821.2	821.0	820.9	820.8	820.8	820.8	820.7	821.1
160°	836.7	836.5	836.3	836.2	836.0	835.8	835.8	835.6	835.4	835.3	835.8
162.5°	850.1	849.7	849.2	848.9	848.5	848.2	848.0	847.9	847.7	847.5	848.4
165°	868.2	867.7	867.2	866.8	866.3	865.9	865.5	865.3	865.0	864.6	865.5
167.5°	881.9	881.4	880.7	880.1	879.4	879.0	879.1	879.1	879.1	879.2	880.1
170°	889.9	889.0	888.3	887.5	886.7	886.4	886.6	886.7	886.8	887.0	888.0
172.5°	895.4	894.8	894.1	893.4	892.8	892.5	892.5	892.6	892.6	892.6	893.7
175°	903.1	902.3	901.5	900.8	900.0	899.6	899.4	899.2	899.1	898.9	900.0
177.5°	905.6	905.0	904.4	903.8	903.1	902.9	902.9	902.9	902.9	902.9	903.7
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	17.6	17.5	17.5	17.6	17.9	18.2	18.5	18.8
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	28.8	29.4	30.0	30.3	30.5	30.7	30.9	31.1
95°	54.1	54.6	55.0	55.2	55.2	55.2	55.2	55.2
97.5°	85.2	85.8	86.3	86.6	86.6	86.6	86.6	86.6
100°	107.6	107.9	108.3	108.4	108.4	108.4	108.4	108.4
102.5°	131.4	131.9	132.2	132.5	132.7	132.8	132.9	133.1
105°	167.4	167.9	168.3	168.8	169.3	169.8	170.2	170.7
107.5°	206.4	206.8	207.3	207.5	207.5	207.5	207.4	207.4
110°	232.3	232.1	231.7	231.8	232.2	232.7	233.2	233.7





TEST NUMBER: P333082-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.2	260.1	260.1	260.1	260.2	260.3	260.4	260.5
115°	303.3	303.1	302.9	302.8	302.7	302.6	302.4	302.2
117.5°	344.7	344.1	343.6	343.2	342.9	342.5	342.2	342.0
120°	372.7	371.9	371.2	370.9	371.3	371.6	371.8	372.1
122.5°	401.1	400.7	400.1	399.5	399.0	398.4	397.9	397.4
125°	442.9	442.6	442.2	442.0	441.7	441.3	441.0	440.7
127.5°	482.8	482.5	482.1	481.8	481.6	481.4	481.1	480.9
130°	510.8	510.4	510.1	509.6	509.1	508.4	507.7	507.2
132.5°	537.1	536.8	536.4	536.1	535.9	535.6	535.4	535.2
135°	576.5	576.2	575.9	575.5	575.0	574.6	574.1	573.6
137.5°	614.6	614.3	613.9	613.7	613.8	613.9	614.0	614.1
140°	639.8	639.6	639.4	639.3	639.1	638.9	638.9	638.7
142.5°	663.5	663.5	663.5	663.5	663.4	663.4	663.4	663.3
145°	699.3	699.1	698.9	698.6	698.1	697.7	697.2	696.7
147.5°	731.6	731.5	731.3	731.2	731.0	730.9	730.8	730.6
150°	752.1	752.1	752.1	752.0	751.8	751.6	751.5	751.3
152.5°	771.2	771.6	771.9	771.9	771.6	771.2	770.7	770.3
155°	798.1	798.6	799.3	799.3	798.6	798.1	797.4	796.8
157.5°	821.6	822.1	822.6	822.6	822.0	821.5	821.0	820.4
160°	836.2	836.7	837.2	837.0	836.2	835.4	834.6	833.9
162.5°	849.2	850.1	850.9	850.9	850.2	849.4	848.7	847.8
165°	866.5	867.4	868.4	868.6	867.9	867.2	866.7	866.0
167.5°	881.1	881.9	882.9	882.9	881.9	881.0	880.1	879.0
170°	888.9	889.9	890.8	890.7	889.6	888.5	887.4	886.4
172.5°	894.8	895.8	896.8	896.8	895.7	894.7	893.5	892.5
175°	901.1	902.2	903.2	903.2	902.2	901.1	900.0	898.9
177.5°	904.6	905.4	906.3	906.3	905.2	904.3	903.2	902.3
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5

(END OF REPORT)