

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333037-830

Luminaire Tested: **S124RDIW-S575D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333037-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D470U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3981.4 lumens  
Efficiency: N/A  
Efficacy: 131.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73			61	61	61	56
1	99	95	91	88		92	89	85	82		76	74	72		65	63	62			55	53	52	47
2	91	83	77	72		84	78	72	68		67	63	60		57	55	52			48	46	45	40
3	83	74	66	61		77	69	62	57		60	55	51		51	47	44			43	41	38	34
4	76	65	57	51		70	61	54	49		53	48	43		46	42	38			39	36	33	30
5	70	58	50	44		65	55	47	42		48	42	38		41	37	33			35	32	29	26
6	64	52	44	39		60	49	42	37		43	37	33		37	33	29			32	28	26	23
7	60	47	40	34		55	45	37	32		39	33	29		34	29	26			29	26	23	20
8	55	43	35	30		52	41	34	29		36	30	26		31	27	23			27	23	21	18
9	52	40	32	27		48	37	30	26		33	27	23		29	24	21			25	21	19	17
10	48	36	29	24		45	34	28	23		30	25	21		27	22	19			23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	2.3
10°-20°	250.9	6.3
20°-30°	362.3	9.1
30°-40°	410.7	10.3
40°-50°	396.6	10.0
50°-60°	329.8	8.3
60°-70°	227.7	5.7
70°-80°	115.4	2.9
80°-90°	31.3	0.8
90°-100°	19.5	0.5
100°-110°	124.6	3.1
110°-120°	238.3	6.0
120°-130°	302.4	7.6
130°-140°	323.6	8.1
140°-150°	302.6	7.6
150°-160°	244.0	6.1
160°-170°	157.4	4.0
170°-180°	54.2	1.4
0°-30°	703.2	17.7
0°-40°	1113.9	28.0
0°-60°	1840.3	46.2
0°-90°	2214.8	55.6
90°-120°	382.4	9.6
90°-150°	1311.0	32.9
90°-180°	1767.0	44.4
0°-180°	3981.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	1	6	9	12	13	3
95°	24	10	9	12	12	30
105°	129	131	133	136	122	135
115°	240	241	241	242	242	236
125°	337	339	338	340	340	301
135°	419	418	420	421	422	322
145°	483	484	484	484	485	301
155°	529	530	528	530	529	244
165°	558	556	556	559	556	158
175°	571	569	569	572	568	54
180°	571	571	571	571	571	



TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	13.8	12.9	12.1	11.2	10.4	10.0	10.0	10.1	10.1	10.1	10.1
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	5.4	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6
95°	23.5	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0
97.5°	49.9	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3
100°	70.0	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2
102.5°	92.7	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1
105°	128.6	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1
107.5°	162.0	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5
110°	184.5	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6



TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.4	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9
115°	240.1	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1
117.5°	270.4	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0
120°	290.9	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4
122.5°	310.0	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8
125°	337.4	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6
127.5°	363.4	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8
130°	380.1	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0
132.5°	395.6	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0
135°	418.6	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1
137.5°	439.0	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3
140°	452.3	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4
142.5°	464.3	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6
145°	482.7	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1
147.5°	497.3	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4
150°	507.9	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2
152.5°	516.8	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6
155°	529.2	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8
157.5°	539.8	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6
160°	545.9	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8
162.5°	551.4	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9
165°	558.3	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9
167.5°	563.7	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1
170°	566.8	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4
172.5°	568.9	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5
175°	571.1	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9
177.5°	572.1	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	10.1	10.1	10.0	10.1	10.3	10.5	10.7	10.7
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.2	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	10.6	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	15.6	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	55.7	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.0	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.0	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	188.8	189.0	189.2	189.4	189.6	189.9	190.2	190.5





TEST NUMBER: P333037-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	209.8	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.3	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	311.9	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	338.8	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.7	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.1	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.1	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.3	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.5	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	454.7	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	466.7	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.2	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.6	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.1	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	550.4	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	557.7	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.0	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.2	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	568.3	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	570.7	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	571.7	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)