

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332810-930

Luminaire Tested: **S124DIW-S1020D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332810-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D470U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4936.8 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	2.7
10°-20°	373.3	7.6
20°-30°	549.4	11.1
30°-40°	638.7	12.9
40°-50°	638.7	12.9
50°-60°	558.7	11.3
60°-70°	414.9	8.4
70°-80°	235.7	4.8
80°-90°	69.5	1.4
90°-100°	31.5	0.6
100°-110°	93.3	1.9
110°-120°	158.4	3.2
120°-130°	208.9	4.2
130°-140°	234.6	4.8
140°-150°	230.5	4.7
150°-160°	193.9	3.9
160°-170°	129.0	2.6
170°-180°	45.2	0.9
0°-30°	1055.2	21.4
0°-40°	1693.9	34.3
0°-60°	2891.3	58.6
0°-90°	3611.5	73.2
90°-120°	283.3	5.7
90°-150°	957.2	19.4
90°-180°	1325.0	26.8
0°-180°	4936.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	1	5	8	10	11	5
95°	22	25	28	29	29	25
105°	86	86	88	89	90	91
115°	161	161	160	160	160	159
125°	235	235	234	234	233	209
135°	303	305	305	304	303	234
145°	368	369	369	369	368	230
155°	421	421	421	422	421	194
165°	458	457	457	459	457	129
175°	477	475	475	477	475	45
180°	478	478	478	478	478	



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	23.6	23.6	23.6	23.6	23.6	23.6	23.5	23.4	23.3	23.2	23.4
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	7.9	9.0	9.9	11.0	12.1	12.8	13.3	13.7	14.2	14.6	14.9
95°	22.2	22.9	23.6	24.4	25.1	25.8	26.3	26.9	27.5	28.0	28.3
97.5°	38.7	39.3	39.9	40.5	41.1	41.7	42.4	43.0	43.7	44.4	44.7
100°	51.7	52.0	52.3	52.7	53.1	53.6	54.3	55.0	55.8	56.5	56.7
102.5°	65.3	65.5	65.6	65.7	65.9	66.3	66.9	67.6	68.2	69.0	69.1
105°	86.1	86.2	86.3	86.3	86.4	86.6	86.9	87.2	87.6	87.9	88.1
107.5°	107.9	107.9	108.1	108.2	108.3	108.4	108.4	108.4	108.5	108.5	108.8
110°	122.6	122.8	122.9	123.1	123.3	123.4	123.3	123.2	123.1	123.0	122.9



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.0	138.0	138.1	138.1	138.2	138.1	137.9	137.8	137.6	137.5	137.5
115°	161.1	161.1	161.1	161.1	161.1	161.0	160.9	160.7	160.5	160.4	160.3
117.5°	182.8	182.9	183.0	183.0	183.0	183.0	183.0	182.8	182.7	182.5	182.3
120°	197.3	197.6	198.0	198.3	198.6	198.6	198.4	198.1	197.9	197.6	197.2
122.5°	212.4	212.5	212.6	212.7	212.9	212.9	212.8	212.6	212.5	212.5	212.1
125°	234.6	234.6	234.6	234.6	234.6	234.6	234.5	234.4	234.3	234.2	234.1
127.5°	254.8	255.0	255.3	255.5	255.8	255.8	255.7	255.5	255.4	255.3	255.1
130°	269.0	269.2	269.5	269.7	269.9	270.0	270.0	270.0	270.0	270.0	269.9
132.5°	283.4	283.6	283.8	284.0	284.1	284.2	284.1	284.1	284.1	284.0	283.8
135°	302.6	303.0	303.5	304.0	304.5	304.8	304.8	304.8	304.8	304.8	304.6
137.5°	323.4	323.7	323.8	324.1	324.3	324.5	324.7	324.8	324.9	325.1	324.8
140°	337.3	337.5	337.6	337.8	337.9	338.0	338.0	338.0	338.0	338.0	337.9
142.5°	350.0	350.2	350.3	350.5	350.7	350.7	350.7	350.6	350.5	350.4	350.4
145°	367.6	367.9	368.3	368.6	368.9	369.1	369.2	369.2	369.3	369.4	369.3
147.5°	385.1	385.4	385.8	386.2	386.6	386.8	386.7	386.6	386.6	386.5	386.5
150°	395.7	396.0	396.3	396.6	397.0	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	405.7	405.9	406.1	406.3	406.5	406.7	406.7	406.8	406.8	406.9	407.1
155°	421.2	421.2	421.2	421.2	421.2	421.1	421.0	420.9	420.9	420.8	421.1
157.5°	434.1	434.0	433.9	433.7	433.6	433.5	433.5	433.5	433.4	433.4	433.7
160°	441.9	441.8	441.7	441.6	441.6	441.5	441.4	441.3	441.2	441.2	441.4
162.5°	449.0	448.7	448.5	448.3	448.1	447.9	447.8	447.8	447.7	447.6	448.1
165°	458.4	458.2	458.0	457.7	457.5	457.3	457.1	457.0	456.8	456.6	457.1
167.5°	465.8	465.5	465.1	464.8	464.4	464.2	464.2	464.3	464.3	464.3	464.8
170°	469.9	469.5	469.1	468.7	468.3	468.1	468.2	468.3	468.4	468.5	469.0
172.5°	472.9	472.5	472.2	471.9	471.5	471.3	471.3	471.4	471.4	471.4	472.0
175°	477.0	476.5	476.1	475.7	475.3	475.1	475.0	474.9	474.8	474.7	475.3
177.5°	478.3	477.9	477.6	477.3	477.0	476.8	476.8	476.8	476.8	476.8	477.3
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	23.5	23.6	23.6	23.7	23.7	23.8	23.8	23.9
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	15.2	15.5	15.8	16.0	16.1	16.2	16.3	16.4
95°	28.5	28.8	29.0	29.2	29.2	29.2	29.2	29.2
97.5°	45.0	45.3	45.6	45.7	45.7	45.7	45.7	45.7
100°	56.8	57.0	57.2	57.2	57.2	57.2	57.2	57.2
102.5°	69.4	69.6	69.9	70.0	70.0	70.1	70.2	70.3
105°	88.5	88.7	88.9	89.2	89.4	89.7	89.9	90.2
107.5°	109.0	109.3	109.5	109.6	109.6	109.6	109.5	109.5
110°	122.7	122.5	122.4	122.4	122.6	122.9	123.1	123.4



TEST NUMBER: P332810-930

CATALOG NUMBER: S124DIW-S1020D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.4	137.4	137.4	137.5	137.5	137.5	137.5
115°	160.2	160.1	160.0	160.0	159.9	159.8	159.7	159.6
117.5°	182.1	181.7	181.5	181.2	181.1	180.9	180.8	180.6
120°	196.8	196.4	196.0	195.9	196.1	196.2	196.4	196.6
122.5°	211.9	211.6	211.3	211.0	210.8	210.4	210.1	209.9
125°	233.9	233.7	233.6	233.4	233.3	233.1	232.9	232.8
127.5°	254.9	254.8	254.6	254.5	254.4	254.2	254.1	254.0
130°	269.7	269.5	269.4	269.1	268.8	268.5	268.2	267.8
132.5°	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.7
135°	304.4	304.3	304.1	303.9	303.7	303.5	303.2	303.0
137.5°	324.6	324.4	324.2	324.1	324.2	324.2	324.2	324.3
140°	337.9	337.8	337.7	337.6	337.5	337.5	337.4	337.3
142.5°	350.4	350.4	350.4	350.3	350.3	350.3	350.3	350.3
145°	369.2	369.2	369.1	368.9	368.7	368.4	368.2	367.9
147.5°	386.4	386.3	386.3	386.2	386.1	386.0	386.0	385.9
150°	397.1	397.1	397.1	397.1	397.1	397.0	396.9	396.8
152.5°	407.3	407.5	407.7	407.6	407.5	407.2	407.1	406.8
155°	421.4	421.8	422.1	422.1	421.8	421.4	421.1	420.8
157.5°	433.9	434.1	434.4	434.4	434.1	433.8	433.6	433.3
160°	441.6	441.9	442.1	442.1	441.6	441.2	440.8	440.3
162.5°	448.5	449.0	449.4	449.4	449.0	448.6	448.2	447.8
165°	457.6	458.1	458.6	458.7	458.4	458.0	457.7	457.4
167.5°	465.3	465.8	466.3	466.3	465.8	465.3	464.7	464.2
170°	469.4	469.9	470.4	470.3	469.8	469.2	468.6	468.1
172.5°	472.5	473.1	473.6	473.6	473.0	472.5	471.9	471.3
175°	475.9	476.5	477.0	477.0	476.5	475.9	475.3	474.7
177.5°	477.8	478.2	478.7	478.6	478.1	477.6	477.0	476.5
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7

(END OF REPORT)