

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332740-930

Luminaire Tested: **S124DIW-S350D1560U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332740-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U930-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5699.9 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3760	3760	3760	3760
5°	4428	3770	3327	3770
10°	5302	3754	2995	3754
15°	6273	3716	2751	3716
20°	6985	3677	2533	3677
25°	7098	3619	2382	3619
30°	6040	3566	2335	3566
35°	4644	3476	2335	3476
40°	3620	3371	2380	3371
45°	3017	3214	2419	3214
50°	2656	3022	2501	3022
55°	2434	2792	2601	2792
60°	2280	2585	2722	2585
65°	2122	2355	2823	2355
70°	1940	2127	2887	2127
75°	1734	1871	2854	1871
80°	1450	1534	2762	1534
85°	1074	1112	2640	1112



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	0.8
10°-20°	139.9	2.5
20°-30°	221.8	3.9
30°-40°	246.8	4.3
40°-50°	224.7	3.9
50°-60°	183.6	3.2
60°-70°	131.1	2.3
70°-80°	72.2	1.3
80°-90°	24.4	0.4
90°-100°	104.8	1.8
100°-110°	310.6	5.4
110°-120°	527.1	9.2
120°-130°	695.1	12.2
130°-140°	780.6	13.7
140°-150°	767.1	13.5
150°-160°	645.2	11.3
160°-170°	429.2	7.5
170°-180°	150.3	2.6
0°-30°	407.0	7.1
0°-40°	653.9	11.5
0°-60°	1062.2	18.6
0°-90°	1289.9	22.6
90°-120°	942.5	16.5
90°-150°	3185.3	55.9
90°-180°	4410.0	77.4
0°-180°	5699.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	466	466	466	466	466	
5°	546	465	411	465	546	56
15°	751	445	329	445	751	212
25°	797	406	267	406	797	351
35°	471	353	237	353	471	299
45°	264	282	212	282	264	208
55°	173	198	185	198	173	156
65°	111	123	148	123	111	110
75°	56	60	92	60	56	59
85°	12	12	28	12	12	15
90°	37	4	37	4	37	19
95°	97	74	97	74	97	101
105°	300	286	300	286	300	316
115°	531	536	531	536	531	525
125°	774	781	774	781	774	691
135°	1008	1007	1008	1007	1008	778
145°	1224	1223	1224	1223	1224	766
155°	1400	1401	1400	1401	1400	645
165°	1522	1526	1522	1526	1522	429
175°	1580	1587	1580	1587	1580	150
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	495.7	495.6	494.1	493.7	492.7	491.3	491.0	488.4	483.6	481.2	480.6
5°	546.4	550.3	545.3	544.3	543.7	537.4	534.1	530.3	521.4	516.2	512.1
7.5°	607.0	607.4	605.2	603.5	598.5	593.0	584.7	575.8	565.2	554.2	545.9
10°	646.8	648.3	645.8	645.5	635.6	629.4	617.1	606.7	594.7	581.4	569.2
12.5°	688.8	686.6	685.3	677.1	675.2	664.0	649.6	639.0	620.4	605.1	589.0
15°	750.6	746.3	743.6	732.3	726.7	711.0	695.8	684.0	659.9	636.9	619.5
17.5°	786.8	791.1	784.9	780.2	765.7	754.7	739.2	714.4	695.6	667.1	645.1
20°	813.1	813.5	810.0	805.2	793.9	779.9	763.0	736.0	713.4	685.0	654.8
22.5°	820.2	820.3	818.8	814.3	805.7	794.4	777.3	754.7	727.4	696.6	666.4
25°	796.9	796.1	797.9	802.9	799.6	796.1	786.3	769.5	744.0	711.4	679.0
27.5°	710.3	715.7	725.5	737.8	749.7	758.7	761.2	757.8	742.1	715.3	681.3
30°	647.9	654.5	661.9	674.2	698.1	711.8	726.8	738.3	731.9	710.5	678.8
32.5°	579.4	581.1	591.9	605.9	627.9	654.2	678.1	701.2	708.9	697.7	671.2
35°	471.2	473.9	485.7	499.5	526.4	558.6	594.5	626.6	653.0	663.6	650.0
37.5°	384.5	392.2	400.6	415.5	439.1	468.1	505.4	546.9	586.3	612.7	617.2
40°	343.5	348.3	354.2	365.7	385.7	414.3	446.3	493.7	535.7	573.5	585.8
42.5°	311.0	313.9	317.6	327.8	343.1	371.5	400.8	442.5	484.5	529.8	550.5
45°	264.3	267.3	273.5	279.4	291.0	310.6	337.9	372.2	414.5	458.0	496.3
47.5°	230.6	232.4	236.1	242.6	252.4	265.4	287.5	316.2	355.3	397.7	438.4
50°	211.5	213.0	215.9	221.7	229.3	240.8	258.9	285.8	316.4	359.1	399.0
52.5°	196.3	197.0	199.1	203.0	209.0	218.7	233.7	255.8	284.4	322.4	362.2
55°	172.9	173.7	175.6	178.5	183.7	189.9	201.2	217.8	242.7	275.7	310.3
57.5°	153.6	154.2	155.7	156.9	161.2	166.2	175.0	186.8	205.6	233.7	264.5
60°	141.2	140.9	142.8	143.7	146.7	150.9	157.7	169.0	185.4	208.0	236.4
62.5°	129.2	128.7	130.3	131.6	133.2	136.8	142.4	151.2	164.6	185.0	209.5
65°	111.1	110.4	111.4	112.9	114.4	116.3	120.4	128.3	138.9	153.6	172.3
67.5°	93.0	93.8	94.0	94.7	95.6	98.2	101.0	106.6	114.1	125.9	141.7
70°	82.2	82.4	83.2	83.2	83.7	86.1	88.4	91.6	99.0	109.8	122.7
72.5°	71.4	72.2	71.9	72.5	73.0	74.5	76.1	79.3	85.5	93.6	104.5
75°	55.6	56.2	56.2	56.3	56.9	57.5	58.9	61.1	65.6	71.6	79.1
77.5°	40.5	40.6	40.8	41.6	41.6	42.5	43.5	45.3	47.5	51.6	56.3
80°	31.2	31.6	31.5	31.9	31.9	32.6	33.0	35.3	36.3	39.0	42.6
82.5°	22.9	23.3	23.2	23.8	24.1	24.3	24.8	25.8	26.7	29.1	30.6
85°	11.6	12.0	11.6	12.0	12.6	12.7	13.3	13.5	14.3	14.8	16.2
87.5°	10.8	11.1	11.0	11.1	11.3	11.2	11.0	10.5	10.8	10.7	10.8
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	54.5	54.2	53.9	53.6	53.2	52.6	51.6	50.6	49.7	48.7	47.1
95°	97.1	97.1	97.1	97.1	97.1	96.7	95.9	95.1	94.2	93.4	91.6
97.5°	152.2	152.2	152.2	152.2	152.2	151.7	150.7	149.8	148.7	147.7	145.5
100°	190.5	190.5	190.5	190.5	190.5	190.3	189.7	189.1	188.7	188.1	185.6
102.5°	233.8	233.6	233.4	233.2	232.9	232.4	231.7	230.9	230.2	229.4	227.1
105°	299.9	299.1	298.3	297.5	296.7	295.9	295.1	294.2	293.4	292.6	291.5
107.5°	364.4	364.4	364.5	364.5	364.6	364.3	363.5	362.7	361.9	361.2	361.0
110°	410.6	409.8	409.0	408.1	407.3	407.2	407.7	408.3	408.8	409.4	409.6



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.8	457.6	457.5	457.3	457.1	457.1	457.2	457.3	457.5	457.5	458.0
115°	531.1	531.3	531.7	531.9	532.1	532.5	532.7	533.0	533.3	533.5	534.1
117.5°	600.9	601.4	602.0	602.5	603.1	603.8	604.8	605.7	606.6	607.6	607.9
120°	654.0	653.5	652.9	652.4	651.8	652.2	653.6	654.9	656.3	657.7	658.5
122.5°	698.3	699.3	700.3	701.2	702.2	703.2	704.1	705.0	706.0	706.9	707.3
125°	774.5	775.0	775.6	776.1	776.7	777.2	777.8	778.3	778.9	779.4	779.7
127.5°	845.1	845.5	846.0	846.4	846.8	847.3	847.8	848.4	848.9	849.5	849.9
130°	891.3	892.3	893.5	894.5	895.6	896.4	897.0	897.6	898.1	898.6	898.6
132.5°	940.4	940.9	941.3	941.8	942.2	942.6	943.2	943.8	944.4	944.9	945.1
135°	1008.0	1008.9	1009.7	1010.5	1011.3	1012.0	1012.6	1013.1	1013.7	1014.2	1014.2
137.5°	1079.1	1079.0	1078.8	1078.6	1078.5	1078.7	1079.5	1080.2	1080.8	1081.6	1081.2
140°	1122.4	1122.7	1122.9	1123.2	1123.5	1123.7	1124.1	1124.3	1124.5	1124.9	1124.9
142.5°	1165.6	1165.7	1165.8	1165.8	1165.9	1166.0	1166.0	1166.0	1166.1	1166.1	1166.4
145°	1224.4	1225.2	1226.0	1226.9	1227.7	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1283.9	1284.2	1284.5	1284.7	1285.0	1285.2	1285.5	1285.7	1285.9	1286.1	1286.4
150°	1320.3	1320.6	1320.9	1321.1	1321.4	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1353.7	1354.5	1355.2	1355.8	1356.6	1356.6	1355.9	1355.3	1354.6	1354.0	1353.8
155°	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2	1400.5
157.5°	1441.8	1442.7	1443.7	1444.5	1445.4	1445.5	1444.7	1443.9	1443.1	1442.3	1442.3
160°	1465.3	1466.7	1468.1	1469.5	1470.8	1471.1	1470.3	1469.5	1468.7	1467.9	1468.1
162.5°	1490.0	1491.3	1492.7	1494.0	1495.4	1495.3	1493.9	1492.4	1490.9	1489.5	1489.7
165°	1521.9	1523.0	1524.1	1525.2	1526.3	1526.0	1524.4	1522.7	1521.1	1519.5	1520.0
167.5°	1544.7	1546.5	1548.2	1549.9	1551.6	1551.6	1550.0	1548.3	1546.7	1545.1	1545.0
170°	1557.5	1559.5	1561.4	1563.3	1565.2	1565.4	1563.7	1562.1	1560.4	1558.8	1558.5
172.5°	1568.4	1570.3	1572.2	1574.1	1576.1	1576.1	1574.2	1572.4	1570.5	1568.6	1568.6
175°	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7	1580.0
177.5°	1585.6	1587.4	1589.1	1590.8	1592.6	1592.7	1591.1	1589.7	1588.1	1586.6	1586.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	480.8	478.6	477.0	475.8	472.5	470.4	468.9	466.8	464.2	461.6	458.4
5°	508.0	501.5	496.7	489.3	482.4	476.6	470.6	465.2	458.7	451.5	446.3
7.5°	536.7	526.9	514.5	503.6	491.4	480.8	471.3	461.6	451.5	441.6	432.7
10°	555.0	542.4	528.5	512.1	496.7	483.0	470.3	457.9	445.9	434.0	423.7
12.5°	574.5	558.9	538.3	519.2	501.9	483.6	468.2	453.1	438.6	426.1	414.2
15°	600.9	578.3	554.6	528.9	506.1	484.7	463.7	444.6	428.4	411.7	400.1
17.5°	617.0	589.1	562.0	535.2	507.6	480.5	457.9	435.9	415.6	399.1	384.5
20°	627.7	599.9	566.1	539.3	506.5	478.7	452.5	428.0	406.8	389.2	374.1
22.5°	636.9	604.9	571.0	535.7	503.1	473.6	444.9	420.3	398.6	380.1	365.7
25°	642.0	605.1	568.4	533.3	496.3	461.4	435.3	406.3	383.2	363.7	348.3
27.5°	642.5	603.1	561.6	522.6	484.4	451.8	419.0	393.1	369.1	348.5	333.6
30°	640.8	599.7	555.1	512.9	474.5	439.2	410.6	382.5	357.9	337.5	322.0
32.5°	635.4	592.6	546.8	502.1	462.3	427.7	398.3	371.5	347.6	327.4	311.2
35°	619.8	577.5	528.7	482.2	441.5	406.6	379.9	352.7	328.8	309.7	294.1
37.5°	595.3	557.2	507.5	459.4	419.4	384.3	357.9	333.4	311.8	292.4	276.4
40°	574.1	540.5	490.6	443.8	400.6	367.2	342.5	319.9	298.5	280.1	264.9
42.5°	549.5	520.2	474.3	424.7	382.9	349.4	325.4	305.1	284.9	268.0	252.7
45°	505.7	486.4	443.2	397.3	353.8	322.2	299.3	281.5	264.6	247.9	235.2
47.5°	455.4	445.8	409.4	365.8	324.7	293.4	273.5	257.1	242.2	228.2	217.0
50°	421.6	416.9	385.6	343.5	304.1	274.8	254.7	240.6	227.9	215.6	204.9
52.5°	388.2	388.1	359.7	321.2	284.8	256.6	236.6	223.5	212.5	202.4	192.9
55°	337.3	342.7	320.5	286.2	253.6	228.0	210.1	198.4	190.6	182.4	175.2
57.5°	290.5	299.5	281.1	250.9	223.6	200.2	184.6	175.8	167.5	162.5	157.3
60°	259.9	268.4	254.1	228.7	203.0	183.0	168.0	160.1	153.0	149.5	145.9
62.5°	232.8	240.3	229.8	206.1	183.8	164.5	152.0	144.4	139.6	135.8	133.4
65°	194.0	200.3	191.2	174.1	154.9	139.5	129.3	123.3	118.7	117.2	114.4
67.5°	156.8	162.6	157.7	143.1	127.8	116.0	108.0	102.3	99.5	98.2	96.3
70°	134.7	140.5	135.3	122.5	110.7	100.9	93.4	90.1	87.2	86.7	84.0
72.5°	116.0	119.9	114.7	104.8	94.7	86.4	80.6	77.1	75.7	74.6	73.1
75°	87.0	90.5	87.0	79.3	72.2	66.4	61.4	60.0	58.3	57.7	56.7
77.5°	61.6	64.6	62.0	57.2	51.8	47.3	44.6	42.9	42.5	41.5	42.0
80°	47.0	49.0	46.5	43.2	39.0	35.9	34.0	33.0	31.9	31.5	32.2
82.5°	33.8	34.7	33.3	31.1	28.0	26.0	24.7	23.6	23.3	23.4	23.4
85°	17.5	17.4	17.2	15.2	14.3	13.0	12.1	12.0	11.7	12.1	12.6
87.5°	10.4	10.1	9.5	8.4	7.3	6.3	5.5	4.7	5.5	6.3	7.0
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	45.7	44.1	42.6	40.1	36.6	33.2	29.8	26.3	29.8	33.2	36.6
95°	89.6	87.7	85.8	83.6	81.1	78.7	76.2	73.8	76.2	78.7	81.1
97.5°	143.2	141.0	138.8	136.7	134.8	132.7	130.8	128.8	130.8	132.7	134.8
100°	183.2	180.8	178.2	176.5	175.4	174.3	173.2	172.1	173.2	174.3	175.4
102.5°	224.9	222.7	220.5	219.1	218.7	218.3	217.8	217.4	217.8	218.3	218.7
105°	290.4	289.3	288.2	287.6	287.2	287.0	286.7	286.4	286.7	287.0	287.2
107.5°	360.9	360.7	360.5	360.3	360.0	359.6	359.3	359.0	359.3	359.6	360.0
110°	409.9	410.2	410.5	410.3	409.8	409.2	408.7	408.1	408.7	409.2	409.8



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	459.0	459.5	459.7	459.6	459.5	459.4	459.3	459.4	459.5	459.6
115°	534.6	535.2	535.7	536.0	536.0	536.0	536.0	536.0	536.0	536.0	536.0
117.5°	608.3	608.7	609.1	609.2	608.9	608.7	608.5	608.3	608.5	608.7	608.9
120°	659.3	660.1	661.0	660.8	659.7	658.7	657.5	656.5	657.5	658.7	659.7
122.5°	707.6	708.0	708.4	708.3	707.9	707.5	707.0	706.6	707.0	707.5	707.9
125°	779.9	780.2	780.5	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
127.5°	850.4	850.8	851.3	851.0	850.2	849.4	848.6	847.7	848.6	849.4	850.2
130°	898.6	898.6	898.6	898.2	897.4	896.6	895.8	895.0	895.8	896.6	897.4
132.5°	945.3	945.5	945.7	945.6	944.9	944.4	943.8	943.1	943.8	944.4	944.9
135°	1014.2	1014.2	1014.2	1013.4	1011.8	1010.1	1008.4	1006.8	1008.4	1010.1	1011.8
137.5°	1080.7	1080.3	1079.9	1079.2	1078.5	1077.7	1076.9	1076.2	1076.9	1077.7	1078.5
140°	1124.9	1124.9	1124.9	1124.5	1124.1	1123.5	1122.9	1122.4	1122.9	1123.5	1124.1
142.5°	1166.6	1166.8	1167.0	1166.9	1166.3	1165.8	1165.2	1164.7	1165.2	1165.8	1166.3
145°	1228.8	1228.5	1228.2	1227.6	1226.5	1225.4	1224.3	1223.2	1224.3	1225.4	1226.5
147.5°	1286.5	1286.8	1287.0	1286.5	1285.2	1283.9	1282.5	1281.2	1282.5	1283.9	1285.2
150°	1321.5	1321.5	1321.5	1321.0	1319.9	1318.8	1317.7	1316.6	1317.7	1318.8	1319.9
152.5°	1353.6	1353.3	1353.2	1352.7	1352.0	1351.4	1350.7	1350.1	1350.7	1351.4	1352.0
155°	1400.8	1401.0	1401.3	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4	1401.4
157.5°	1442.3	1442.4	1442.5	1442.8	1443.2	1443.7	1444.2	1444.7	1444.2	1443.7	1443.2
160°	1468.4	1468.7	1468.9	1469.2	1469.5	1469.7	1470.0	1470.3	1470.0	1469.7	1469.5
162.5°	1490.0	1490.3	1490.5	1491.0	1491.8	1492.5	1493.2	1493.9	1493.2	1492.5	1491.8
165°	1520.5	1521.1	1521.7	1522.3	1523.1	1524.0	1524.8	1525.6	1524.8	1524.0	1523.1
167.5°	1544.9	1544.9	1544.8	1545.4	1546.5	1547.7	1548.8	1550.0	1548.8	1547.7	1546.5
170°	1558.3	1558.0	1557.7	1558.3	1559.6	1561.0	1562.4	1563.7	1562.4	1561.0	1559.6
172.5°	1568.6	1568.5	1568.4	1569.0	1570.1	1571.2	1572.4	1573.5	1572.4	1571.2	1570.1
175°	1580.2	1580.5	1580.8	1581.6	1583.0	1584.4	1585.7	1587.1	1585.7	1584.4	1583.0
177.5°	1586.6	1586.6	1586.6	1587.1	1588.2	1589.3	1590.4	1591.5	1590.4	1589.3	1588.2
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	456.8	455.4	453.5	450.7	448.3	445.9	445.2	444.3	446.2	444.7	444.2
5°	441.9	437.8	432.6	426.6	423.1	418.2	417.2	415.2	413.3	413.1	411.2
7.5°	426.0	420.0	413.2	407.2	401.5	396.0	392.4	391.7	388.8	387.1	385.2
10°	415.8	408.5	400.6	394.8	388.2	382.5	378.4	376.1	374.1	372.0	370.1
12.5°	403.8	396.0	389.5	383.2	375.4	371.0	364.4	360.4	360.0	360.0	355.0
15°	389.8	382.0	372.0	363.1	358.9	350.4	346.7	342.1	339.2	336.3	334.0
17.5°	373.7	364.1	356.3	346.1	338.0	331.3	326.4	323.7	319.3	315.2	312.3
20°	363.7	353.5	345.2	334.4	325.5	317.2	313.2	309.3	306.1	302.6	299.3
22.5°	353.5	342.8	332.7	322.2	314.0	305.2	301.3	296.0	292.9	291.0	287.7
25°	337.5	325.9	314.3	304.3	295.8	288.0	282.9	278.8	275.3	273.8	271.7
27.5°	320.0	308.5	297.3	285.9	276.3	270.7	266.5	263.5	261.5	259.4	258.4
30°	308.9	296.9	285.0	274.3	265.5	259.9	256.1	254.0	252.4	251.4	250.5
32.5°	297.7	285.8	273.3	263.6	255.6	250.6	247.7	245.6	244.8	244.5	244.1
35°	279.6	267.7	256.1	247.4	239.9	237.9	235.4	234.2	233.8	235.2	235.8
37.5°	262.1	251.0	240.4	232.0	227.0	224.2	223.3	223.4	224.8	225.9	227.3
40°	250.9	240.0	230.0	222.7	218.0	216.3	215.9	216.9	218.4	219.8	221.4
42.5°	239.9	229.3	220.1	213.3	210.0	208.4	208.6	209.6	211.8	213.4	215.7
45°	222.9	214.0	205.1	199.5	196.8	197.2	197.2	198.9	201.1	203.6	206.1
47.5°	206.8	197.9	190.6	185.9	184.5	184.2	185.2	187.5	190.5	193.6	197.1
50°	196.1	187.5	181.2	176.9	175.4	175.9	177.5	179.6	183.3	187.2	190.9
52.5°	185.1	177.3	171.5	167.5	166.4	167.5	169.0	172.4	175.6	179.8	184.2
55°	168.0	161.5	156.9	154.0	153.6	154.2	155.9	159.6	164.2	169.4	173.7
57.5°	151.2	145.6	141.4	139.4	139.6	140.1	143.0	147.3	152.3	157.8	163.3
60°	139.7	134.7	131.2	129.6	129.9	131.0	134.5	138.5	144.7	150.1	155.9
62.5°	128.9	124.5	121.2	119.8	119.5	122.1	125.4	129.6	135.7	141.8	148.1
65°	111.5	108.0	105.3	104.6	105.2	107.1	111.4	116.9	122.1	128.5	135.1
67.5°	94.6	91.7	89.8	90.2	90.9	93.8	97.3	102.1	108.0	114.6	121.1
70°	83.7	81.0	79.5	79.7	80.9	84.3	87.4	92.2	98.6	105.3	110.7
72.5°	72.6	70.8	69.5	70.3	71.4	73.8	77.7	82.5	88.1	94.4	100.1
75°	55.8	55.8	55.0	55.6	57.3	59.6	62.5	67.5	73.1	78.2	82.8
77.5°	41.3	40.9	41.4	42.2	43.1	45.9	49.2	52.8	57.0	62.0	65.9
80°	31.6	31.9	32.8	34.0	34.3	36.4	39.9	43.2	46.5	50.7	54.4
82.5°	23.8	24.0	24.5	25.9	26.3	28.6	30.8	34.1	37.1	39.9	43.0
85°	13.0	13.0	13.9	14.5	15.4	17.0	18.3	20.3	23.0	24.9	27.8
87.5°	8.1	8.6	9.6	10.4	11.3	12.5	13.1	15.2	16.1	17.2	18.8
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	40.1	42.6	44.1	45.7	47.1	48.7	49.7	50.6	51.6	52.6	53.2
95°	83.6	85.8	87.7	89.6	91.6	93.4	94.2	95.1	95.9	96.7	97.1
97.5°	136.7	138.8	141.0	143.2	145.5	147.7	148.7	149.8	150.7	151.7	152.2
100°	176.5	178.2	180.8	183.2	185.6	188.1	188.7	189.1	189.7	190.3	190.5
102.5°	219.1	220.5	222.7	224.9	227.1	229.4	230.2	230.9	231.7	232.4	232.9
105°	287.6	288.2	289.3	290.4	291.5	292.6	293.4	294.2	295.1	295.9	296.7
107.5°	360.3	360.5	360.7	360.9	361.0	361.2	361.9	362.7	363.5	364.3	364.6
110°	410.3	410.5	410.2	409.9	409.6	409.4	408.8	408.3	407.7	407.2	407.3



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	459.7	459.5	459.0	458.5	458.0	457.5	457.5	457.3	457.2	457.1	457.1
115°	536.0	535.7	535.2	534.6	534.1	533.5	533.3	533.0	532.7	532.5	532.1
117.5°	609.2	609.1	608.7	608.3	607.9	607.6	606.6	605.7	604.8	603.8	603.1
120°	660.8	661.0	660.1	659.3	658.5	657.7	656.3	654.9	653.6	652.2	651.8
122.5°	708.3	708.4	708.0	707.6	707.3	706.9	706.0	705.0	704.1	703.2	702.2
125°	780.6	780.5	780.2	779.9	779.7	779.4	778.9	778.3	777.8	777.2	776.7
127.5°	851.0	851.3	850.8	850.4	849.9	849.5	848.9	848.4	847.8	847.3	846.8
130°	898.2	898.6	898.6	898.6	898.6	898.6	898.1	897.6	897.0	896.4	895.6
132.5°	945.6	945.7	945.5	945.3	945.1	944.9	944.4	943.8	943.2	942.6	942.2
135°	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7	1013.1	1012.6	1012.0	1011.3
137.5°	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8	1080.2	1079.5	1078.7	1078.5
140°	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.3	1124.1	1123.7	1123.5
142.5°	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1	1166.0	1166.0	1166.0	1165.9
145°	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1	1228.8	1228.5	1228.2	1227.7
147.5°	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9	1285.7	1285.5	1285.2	1285.0
150°	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.4
152.5°	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6	1355.3	1355.9	1356.6	1356.6
155°	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6
157.5°	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1	1443.9	1444.7	1445.5	1445.4
160°	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7	1469.5	1470.3	1471.1	1470.8
162.5°	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9	1492.4	1493.9	1495.3	1495.4
165°	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1	1522.7	1524.4	1526.0	1526.3
167.5°	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7	1548.3	1550.0	1551.6	1551.6
170°	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4	1562.1	1563.7	1565.4	1565.2
172.5°	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5	1572.4	1574.2	1576.1	1576.1
175°	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4
177.5°	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1	1589.7	1591.1	1592.7	1592.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	443.8	443.6	442.5	442.3	442.5	443.6	443.8	444.2	444.7	446.2	444.3
5°	410.0	409.0	408.5	410.6	408.5	409.0	410.0	411.2	413.1	413.3	415.2
7.5°	384.5	383.8	382.0	381.5	382.0	383.8	384.5	385.2	387.1	388.8	391.7
10°	368.2	367.4	365.8	365.4	365.8	367.4	368.2	370.1	372.0	374.1	376.1
12.5°	352.4	350.9	350.6	351.0	350.6	350.9	352.4	355.0	360.0	360.0	360.4
15°	331.5	330.7	328.6	329.2	328.6	330.7	331.5	334.0	336.3	339.2	342.1
17.5°	310.9	310.0	307.4	309.7	307.4	310.0	310.9	312.3	315.2	319.3	323.7
20°	297.9	296.4	295.1	294.8	295.1	296.4	297.9	299.3	302.6	306.1	309.3
22.5°	285.6	284.2	284.1	282.8	284.1	284.2	285.6	287.7	291.0	292.9	296.0
25°	270.1	268.8	268.4	267.4	268.4	268.8	270.1	271.7	273.8	275.3	278.8
27.5°	258.3	257.6	256.9	257.2	256.9	257.6	258.3	258.4	259.4	261.5	263.5
30°	251.0	250.9	250.5	250.5	250.5	250.9	251.0	250.5	251.4	252.4	254.0
32.5°	245.0	245.0	245.2	245.2	245.2	245.0	245.0	244.1	244.5	244.8	245.6
35°	236.6	237.2	237.5	236.9	237.5	237.2	236.6	235.8	235.2	233.8	234.2
37.5°	228.9	229.5	230.1	230.7	230.1	229.5	228.9	227.3	225.9	224.8	223.4
40°	223.1	224.4	224.8	225.8	224.8	224.4	223.1	221.4	219.8	218.4	216.9
42.5°	217.5	219.0	220.0	220.2	220.0	219.0	217.5	215.7	213.4	211.8	209.6
45°	209.0	210.5	211.9	211.9	211.9	210.5	209.0	206.1	203.6	201.1	198.9
47.5°	200.2	202.4	203.7	204.1	203.7	202.4	200.2	197.1	193.6	190.5	187.5
50°	194.1	196.8	198.2	199.1	198.2	196.8	194.1	190.9	187.2	183.3	179.6
52.5°	188.3	190.9	192.7	193.2	192.7	190.9	188.3	184.2	179.8	175.6	172.4
55°	178.1	182.0	184.1	184.8	184.1	182.0	178.1	173.7	169.4	164.2	159.6
57.5°	168.5	172.1	174.6	175.1	174.6	172.1	168.5	163.3	157.8	152.3	147.3
60°	161.1	165.0	168.0	168.6	168.0	165.0	161.1	155.9	150.1	144.7	138.5
62.5°	153.5	157.6	160.4	161.8	160.4	157.6	153.5	148.1	141.8	135.7	129.6
65°	140.5	144.6	147.2	147.8	147.2	144.6	140.5	135.1	128.5	122.1	116.9
67.5°	126.2	130.3	132.0	133.1	132.0	130.3	126.2	121.1	114.6	108.0	102.1
70°	116.2	119.4	121.4	122.3	121.4	119.4	116.2	110.7	105.3	98.6	92.2
72.5°	104.8	108.2	110.4	110.6	110.4	108.2	104.8	100.1	94.4	88.1	82.5
75°	87.2	90.3	91.5	91.5	91.5	90.3	87.2	82.8	78.2	73.1	67.5
77.5°	69.1	70.6	72.1	72.4	72.1	70.6	69.1	65.9	62.0	57.0	52.8
80°	57.3	58.3	59.4	59.4	59.4	58.3	57.3	54.4	50.7	46.5	43.2
82.5°	45.2	46.1	47.2	47.0	47.2	46.1	45.2	43.0	39.9	37.1	34.1
85°	27.4	29.1	28.9	28.5	28.9	29.1	27.4	27.8	24.9	23.0	20.3
87.5°	19.4	19.6	20.2	20.6	20.2	19.6	19.4	18.8	17.2	16.1	15.2
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	53.6	53.9	54.2	54.5	54.2	53.9	53.6	53.2	52.6	51.6	50.6
95°	97.1	97.1	97.1	97.1	97.1	97.1	97.1	97.1	96.7	95.9	95.1
97.5°	152.2	152.2	152.2	152.2	152.2	152.2	152.2	152.2	151.7	150.7	149.8
100°	190.5	190.5	190.5	190.5	190.5	190.5	190.5	190.5	190.3	189.7	189.1
102.5°	233.2	233.4	233.6	233.8	233.6	233.4	233.2	232.9	232.4	231.7	230.9
105°	297.5	298.3	299.1	299.9	299.1	298.3	297.5	296.7	295.9	295.1	294.2
107.5°	364.5	364.5	364.4	364.4	364.4	364.5	364.5	364.6	364.3	363.5	362.7
110°	408.1	409.0	409.8	410.6	409.8	409.0	408.1	407.3	407.2	407.7	408.3



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	457.3	457.5	457.6	457.8	457.6	457.5	457.3	457.1	457.1	457.2	457.3
115°	531.9	531.7	531.3	531.1	531.3	531.7	531.9	532.1	532.5	532.7	533.0
117.5°	602.5	602.0	601.4	600.9	601.4	602.0	602.5	603.1	603.8	604.8	605.7
120°	652.4	652.9	653.5	654.0	653.5	652.9	652.4	651.8	652.2	653.6	654.9
122.5°	701.2	700.3	699.3	698.3	699.3	700.3	701.2	702.2	703.2	704.1	705.0
125°	776.1	775.6	775.0	774.5	775.0	775.6	776.1	776.7	777.2	777.8	778.3
127.5°	846.4	846.0	845.5	845.1	845.5	846.0	846.4	846.8	847.3	847.8	848.4
130°	894.5	893.5	892.3	891.3	892.3	893.5	894.5	895.6	896.4	897.0	897.6
132.5°	941.8	941.3	940.9	940.4	940.9	941.3	941.8	942.2	942.6	943.2	943.8
135°	1010.5	1009.7	1008.9	1008.0	1008.9	1009.7	1010.5	1011.3	1012.0	1012.6	1013.1
137.5°	1078.6	1078.8	1079.0	1079.1	1079.0	1078.8	1078.6	1078.5	1078.7	1079.5	1080.2
140°	1123.2	1122.9	1122.7	1122.4	1122.7	1122.9	1123.2	1123.5	1123.7	1124.1	1124.3
142.5°	1165.8	1165.8	1165.7	1165.6	1165.7	1165.8	1165.8	1165.9	1166.0	1166.0	1166.0
145°	1226.9	1226.0	1225.2	1224.4	1225.2	1226.0	1226.9	1227.7	1228.2	1228.5	1228.8
147.5°	1284.7	1284.5	1284.2	1283.9	1284.2	1284.5	1284.7	1285.0	1285.2	1285.5	1285.7
150°	1321.1	1320.9	1320.6	1320.3	1320.6	1320.9	1321.1	1321.4	1321.5	1321.5	1321.5
152.5°	1355.8	1355.2	1354.5	1353.7	1354.5	1355.2	1355.8	1356.6	1356.6	1355.9	1355.3
155°	1403.5	1402.4	1401.3	1400.2	1401.3	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4
157.5°	1444.5	1443.7	1442.7	1441.8	1442.7	1443.7	1444.5	1445.4	1445.5	1444.7	1443.9
160°	1469.5	1468.1	1466.7	1465.3	1466.7	1468.1	1469.5	1470.8	1471.1	1470.3	1469.5
162.5°	1494.0	1492.7	1491.3	1490.0	1491.3	1492.7	1494.0	1495.4	1495.3	1493.9	1492.4
165°	1525.2	1524.1	1523.0	1521.9	1523.0	1524.1	1525.2	1526.3	1526.0	1524.4	1522.7
167.5°	1549.9	1548.2	1546.5	1544.7	1546.5	1548.2	1549.9	1551.6	1551.6	1550.0	1548.3
170°	1563.3	1561.4	1559.5	1557.5	1559.5	1561.4	1563.3	1565.2	1565.4	1563.7	1562.1
172.5°	1574.1	1572.2	1570.3	1568.4	1570.3	1572.2	1574.1	1576.1	1576.1	1574.2	1572.4
175°	1585.4	1583.6	1581.6	1579.7	1581.6	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6
177.5°	1590.8	1589.1	1587.4	1585.6	1587.4	1589.1	1590.8	1592.6	1592.7	1591.1	1589.7
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	445.2	445.9	448.3	450.7	453.5	455.4	456.8	458.4	461.6	464.2	466.8
5°	417.2	418.2	423.1	426.6	432.6	437.8	441.9	446.3	451.5	458.7	465.2
7.5°	392.4	396.0	401.5	407.2	413.2	420.0	426.0	432.7	441.6	451.5	461.6
10°	378.4	382.5	388.2	394.8	400.6	408.5	415.8	423.7	434.0	445.9	457.9
12.5°	364.4	371.0	375.4	383.2	389.5	396.0	403.8	414.2	426.1	438.6	453.1
15°	346.7	350.4	358.9	363.1	372.0	382.0	389.8	400.1	411.7	428.4	444.6
17.5°	326.4	331.3	338.0	346.1	356.3	364.1	373.7	384.5	399.1	415.6	435.9
20°	313.2	317.2	325.5	334.4	345.2	353.5	363.7	374.1	389.2	406.8	428.0
22.5°	301.3	305.2	314.0	322.2	332.7	342.8	353.5	365.7	380.1	398.6	420.3
25°	282.9	288.0	295.8	304.3	314.3	325.9	337.5	348.3	363.7	383.2	406.3
27.5°	266.5	270.7	276.3	285.9	297.3	308.5	320.0	333.6	348.5	369.1	393.1
30°	256.1	259.9	265.5	274.3	285.0	296.9	308.9	322.0	337.5	357.9	382.5
32.5°	247.7	250.6	255.6	263.6	273.3	285.8	297.7	311.2	327.4	347.6	371.5
35°	235.4	237.9	239.9	247.4	256.1	267.7	279.6	294.1	309.7	328.8	352.7
37.5°	223.3	224.2	227.0	232.0	240.4	251.0	262.1	276.4	292.4	311.8	333.4
40°	215.9	216.3	218.0	222.7	230.0	240.0	250.9	264.9	280.1	298.5	319.9
42.5°	208.6	208.4	210.0	213.3	220.1	229.3	239.9	252.7	268.0	284.9	305.1
45°	197.2	197.2	196.8	199.5	205.1	214.0	222.9	235.2	247.9	264.6	281.5
47.5°	185.2	184.2	184.5	185.9	190.6	197.9	206.8	217.0	228.2	242.2	257.1
50°	177.5	175.9	175.4	176.9	181.2	187.5	196.1	204.9	215.6	227.9	240.6
52.5°	169.0	167.5	166.4	167.5	171.5	177.3	185.1	192.9	202.4	212.5	223.5
55°	155.9	154.2	153.6	154.0	156.9	161.5	168.0	175.2	182.4	190.6	198.4
57.5°	143.0	140.1	139.6	139.4	141.4	145.6	151.2	157.3	162.5	167.5	175.8
60°	134.5	131.0	129.9	129.6	131.2	134.7	139.7	145.9	149.5	153.0	160.1
62.5°	125.4	122.1	119.5	119.8	121.2	124.5	128.9	133.4	135.8	139.6	144.4
65°	111.4	107.1	105.2	104.6	105.3	108.0	111.5	114.4	117.2	118.7	123.3
67.5°	97.3	93.8	90.9	90.2	89.8	91.7	94.6	96.3	98.2	99.5	102.3
70°	87.4	84.3	80.9	79.7	79.5	81.0	83.7	84.0	86.7	87.2	90.1
72.5°	77.7	73.8	71.4	70.3	69.5	70.8	72.6	73.1	74.6	75.7	77.1
75°	62.5	59.6	57.3	55.6	55.0	55.8	55.8	56.7	57.7	58.3	60.0
77.5°	49.2	45.9	43.1	42.2	41.4	40.9	41.3	42.0	41.5	42.5	42.9
80°	39.9	36.4	34.3	34.0	32.8	31.9	31.6	32.2	31.5	31.9	33.0
82.5°	30.8	28.6	26.3	25.9	24.5	24.0	23.8	23.4	23.4	23.3	23.6
85°	18.3	17.0	15.4	14.5	13.9	13.0	13.0	12.6	12.1	11.7	12.0
87.5°	13.1	12.5	11.3	10.4	9.6	8.6	8.1	7.0	6.3	5.5	4.7
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	49.7	48.7	47.1	45.7	44.1	42.6	40.1	36.6	33.2	29.8	26.3
95°	94.2	93.4	91.6	89.6	87.7	85.8	83.6	81.1	78.7	76.2	73.8
97.5°	148.7	147.7	145.5	143.2	141.0	138.8	136.7	134.8	132.7	130.8	128.8
100°	188.7	188.1	185.6	183.2	180.8	178.2	176.5	175.4	174.3	173.2	172.1
102.5°	230.2	229.4	227.1	224.9	222.7	220.5	219.1	218.7	218.3	217.8	217.4
105°	293.4	292.6	291.5	290.4	289.3	288.2	287.6	287.2	287.0	286.7	286.4
107.5°	361.9	361.2	361.0	360.9	360.7	360.5	360.3	360.0	359.6	359.3	359.0
110°	408.8	409.4	409.6	409.9	410.2	410.5	410.3	409.8	409.2	408.7	408.1



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.5	457.5	458.0	458.5	459.0	459.5	459.7	459.6	459.5	459.4	459.3
115°	533.3	533.5	534.1	534.6	535.2	535.7	536.0	536.0	536.0	536.0	536.0
117.5°	606.6	607.6	607.9	608.3	608.7	609.1	609.2	608.9	608.7	608.5	608.3
120°	656.3	657.7	658.5	659.3	660.1	661.0	660.8	659.7	658.7	657.5	656.5
122.5°	706.0	706.9	707.3	707.6	708.0	708.4	708.3	707.9	707.5	707.0	706.6
125°	778.9	779.4	779.7	779.9	780.2	780.5	780.6	780.6	780.6	780.6	780.6
127.5°	848.9	849.5	849.9	850.4	850.8	851.3	851.0	850.2	849.4	848.6	847.7
130°	898.1	898.6	898.6	898.6	898.6	898.6	898.2	897.4	896.6	895.8	895.0
132.5°	944.4	944.9	945.1	945.3	945.5	945.7	945.6	944.9	944.4	943.8	943.1
135°	1013.7	1014.2	1014.2	1014.2	1014.2	1014.2	1013.4	1011.8	1010.1	1008.4	1006.8
137.5°	1080.8	1081.6	1081.2	1080.7	1080.3	1079.9	1079.2	1078.5	1077.7	1076.9	1076.2
140°	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.1	1123.5	1122.9	1122.4
142.5°	1166.1	1166.1	1166.4	1166.6	1166.8	1167.0	1166.9	1166.3	1165.8	1165.2	1164.7
145°	1229.1	1229.3	1229.1	1228.8	1228.5	1228.2	1227.6	1226.5	1225.4	1224.3	1223.2
147.5°	1285.9	1286.1	1286.4	1286.5	1286.8	1287.0	1286.5	1285.2	1283.9	1282.5	1281.2
150°	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.0	1319.9	1318.8	1317.7	1316.6
152.5°	1354.6	1354.0	1353.8	1353.6	1353.3	1353.2	1352.7	1352.0	1351.4	1350.7	1350.1
155°	1401.3	1400.2	1400.5	1400.8	1401.0	1401.3	1401.4	1401.4	1401.4	1401.4	1401.4
157.5°	1443.1	1442.3	1442.3	1442.3	1442.4	1442.5	1442.8	1443.2	1443.7	1444.2	1444.7
160°	1468.7	1467.9	1468.1	1468.4	1468.7	1468.9	1469.2	1469.5	1469.7	1470.0	1470.3
162.5°	1490.9	1489.5	1489.7	1490.0	1490.3	1490.5	1491.0	1491.8	1492.5	1493.2	1493.9
165°	1521.1	1519.5	1520.0	1520.5	1521.1	1521.7	1522.3	1523.1	1524.0	1524.8	1525.6
167.5°	1546.7	1545.1	1545.0	1544.9	1544.9	1544.8	1545.4	1546.5	1547.7	1548.8	1550.0
170°	1560.4	1558.8	1558.5	1558.3	1558.0	1557.7	1558.3	1559.6	1561.0	1562.4	1563.7
172.5°	1570.5	1568.6	1568.6	1568.6	1568.5	1568.4	1569.0	1570.1	1571.2	1572.4	1573.5
175°	1581.6	1579.7	1580.0	1580.2	1580.5	1580.8	1581.6	1583.0	1584.4	1585.7	1587.1
177.5°	1588.1	1586.6	1586.6	1586.6	1586.6	1586.6	1587.1	1588.2	1589.3	1590.4	1591.5
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	468.9	470.4	472.5	475.8	477.0	478.6	480.8	480.6	481.2	483.6	488.4
5°	470.6	476.6	482.4	489.3	496.7	501.5	508.0	512.1	516.2	521.4	530.3
7.5°	471.3	480.8	491.4	503.6	514.5	526.9	536.7	545.9	554.2	565.2	575.8
10°	470.3	483.0	496.7	512.1	528.5	542.4	555.0	569.2	581.4	594.7	606.7
12.5°	468.2	483.6	501.9	519.2	538.3	558.9	574.5	589.0	605.1	620.4	639.0
15°	463.7	484.7	506.1	528.9	554.6	578.3	600.9	619.5	636.9	659.9	684.0
17.5°	457.9	480.5	507.6	535.2	562.0	589.1	617.0	645.1	667.1	695.6	714.4
20°	452.5	478.7	506.5	539.3	566.1	599.9	627.7	654.8	685.0	713.4	736.0
22.5°	444.9	473.6	503.1	535.7	571.0	604.9	636.9	666.4	696.6	727.4	754.7
25°	435.3	461.4	496.3	533.3	568.4	605.1	642.0	679.0	711.4	744.0	769.5
27.5°	419.0	451.8	484.4	522.6	561.6	603.1	642.5	681.3	715.3	742.1	757.8
30°	410.6	439.2	474.5	512.9	555.1	599.7	640.8	678.8	710.5	731.9	738.3
32.5°	398.3	427.7	462.3	502.1	546.8	592.6	635.4	671.2	697.7	708.9	701.2
35°	379.9	406.6	441.5	482.2	528.7	577.5	619.8	650.0	663.6	653.0	626.6
37.5°	357.9	384.3	419.4	459.4	507.5	557.2	595.3	617.2	612.7	586.3	546.9
40°	342.5	367.2	400.6	443.8	490.6	540.5	574.1	585.8	573.5	535.7	493.7
42.5°	325.4	349.4	382.9	424.7	474.3	520.2	549.5	550.5	529.8	484.5	442.5
45°	299.3	322.2	353.8	397.3	443.2	486.4	505.7	496.3	458.0	414.5	372.2
47.5°	273.5	293.4	324.7	365.8	409.4	445.8	455.4	438.4	397.7	355.3	316.2
50°	254.7	274.8	304.1	343.5	385.6	416.9	421.6	399.0	359.1	316.4	285.8
52.5°	236.6	256.6	284.8	321.2	359.7	388.1	388.2	362.2	322.4	284.4	255.8
55°	210.1	228.0	253.6	286.2	320.5	342.7	337.3	310.3	275.7	242.7	217.8
57.5°	184.6	200.2	223.6	250.9	281.1	299.5	290.5	264.5	233.7	205.6	186.8
60°	168.0	183.0	203.0	228.7	254.1	268.4	259.9	236.4	208.0	185.4	169.0
62.5°	152.0	164.5	183.8	206.1	229.8	240.3	232.8	209.5	185.0	164.6	151.2
65°	129.3	139.5	154.9	174.1	191.2	200.3	194.0	172.3	153.6	138.9	128.3
67.5°	108.0	116.0	127.8	143.1	157.7	162.6	156.8	141.7	125.9	114.1	106.6
70°	93.4	100.9	110.7	122.5	135.3	140.5	134.7	122.7	109.8	99.0	91.6
72.5°	80.6	86.4	94.7	104.8	114.7	119.9	116.0	104.5	93.6	85.5	79.3
75°	61.4	66.4	72.2	79.3	87.0	90.5	87.0	79.1	71.6	65.6	61.1
77.5°	44.6	47.3	51.8	57.2	62.0	64.6	61.6	56.3	51.6	47.5	45.3
80°	34.0	35.9	39.0	43.2	46.5	49.0	47.0	42.6	39.0	36.3	35.3
82.5°	24.7	26.0	28.0	31.1	33.3	34.7	33.8	30.6	29.1	26.7	25.8
85°	12.1	13.0	14.3	15.2	17.2	17.4	17.5	16.2	14.8	14.3	13.5
87.5°	5.5	6.3	7.3	8.4	9.5	10.1	10.4	10.8	10.7	10.8	10.5
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7	50.6
95°	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2	95.1
97.5°	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7	149.8
100°	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7	189.1
102.5°	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2	230.9
105°	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4	294.2
107.5°	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9	362.7
110°	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8	408.3



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5	457.3
115°	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3	533.0
117.5°	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6	605.7
120°	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3	654.9
122.5°	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0	705.0
125°	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9	778.3
127.5°	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9	848.4
130°	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1	897.6
132.5°	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4	943.8
135°	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7	1013.1
137.5°	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8	1080.2
140°	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5	1124.3
142.5°	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1	1166.0
145°	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1	1228.8
147.5°	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9	1285.7
150°	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6	1355.3
155°	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3	1402.4
157.5°	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1	1443.9
160°	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7	1469.5
162.5°	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9	1492.4
165°	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1	1522.7
167.5°	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7	1548.3
170°	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4	1562.1
172.5°	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5	1572.4
175°	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6	1583.6
177.5°	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1	1589.7
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	491.0	491.3	492.7	493.7	494.1	495.6	495.7
5°	534.1	537.4	543.7	544.3	545.3	550.3	546.4
7.5°	584.7	593.0	598.5	603.5	605.2	607.4	607.0
10°	617.1	629.4	635.6	645.5	645.8	648.3	646.8
12.5°	649.6	664.0	675.2	677.1	685.3	686.6	688.8
15°	695.8	711.0	726.7	732.3	743.6	746.3	750.6
17.5°	739.2	754.7	765.7	780.2	784.9	791.1	786.8
20°	763.0	779.9	793.9	805.2	810.0	813.5	813.1
22.5°	777.3	794.4	805.7	814.3	818.8	820.3	820.2
25°	786.3	796.1	799.6	802.9	797.9	796.1	796.9
27.5°	761.2	758.7	749.7	737.8	725.5	715.7	710.3
30°	726.8	711.8	698.1	674.2	661.9	654.5	647.9
32.5°	678.1	654.2	627.9	605.9	591.9	581.1	579.4
35°	594.5	558.6	526.4	499.5	485.7	473.9	471.2
37.5°	505.4	468.1	439.1	415.5	400.6	392.2	384.5
40°	446.3	414.3	385.7	365.7	354.2	348.3	343.5
42.5°	400.8	371.5	343.1	327.8	317.6	313.9	311.0
45°	337.9	310.6	291.0	279.4	273.5	267.3	264.3
47.5°	287.5	265.4	252.4	242.6	236.1	232.4	230.6
50°	258.9	240.8	229.3	221.7	215.9	213.0	211.5
52.5°	233.7	218.7	209.0	203.0	199.1	197.0	196.3
55°	201.2	189.9	183.7	178.5	175.6	173.7	172.9
57.5°	175.0	166.2	161.2	156.9	155.7	154.2	153.6
60°	157.7	150.9	146.7	143.7	142.8	140.9	141.2
62.5°	142.4	136.8	133.2	131.6	130.3	128.7	129.2
65°	120.4	116.3	114.4	112.9	111.4	110.4	111.1
67.5°	101.0	98.2	95.6	94.7	94.0	93.8	93.0
70°	88.4	86.1	83.7	83.2	83.2	82.4	82.2
72.5°	76.1	74.5	73.0	72.5	71.9	72.2	71.4
75°	58.9	57.5	56.9	56.3	56.2	56.2	55.6
77.5°	43.5	42.5	41.6	41.6	40.8	40.6	40.5
80°	33.0	32.6	31.9	31.9	31.5	31.6	31.2
82.5°	24.8	24.3	24.1	23.8	23.2	23.3	22.9
85°	13.3	12.7	12.6	12.0	11.6	12.0	11.6
87.5°	11.0	11.2	11.3	11.1	11.0	11.1	10.8
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P332740-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)