

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332764-930

Luminaire Tested: **S124DIW-S575D1340U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332764-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1340U930-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5909.9 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	63	57	52	51	47	44	40	37	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6181	6181	6181	6181
5°	7280	6198	5471	6198
10°	8716	6171	4925	6171
15°	10313	6108	4523	6108
20°	11485	6045	4164	6045
25°	11670	5951	3917	5951
30°	9930	5862	3838	5862
35°	7634	5714	3840	5714
40°	5951	5542	3911	5542
45°	4962	5284	3976	5284
50°	4366	4968	4111	4968
55°	4000	4590	4277	4590
60°	3749	4251	4477	4251
65°	3490	3872	4642	3872
70°	3189	3496	4747	3496
75°	2851	3079	4688	3079
80°	2390	2520	4542	2520
85°	1760	1815	4353	1815



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.3
10°-20°	230.0	3.9
20°-30°	364.6	6.2
30°-40°	405.8	6.9
40°-50°	369.4	6.3
50°-60°	301.9	5.1
60°-70°	215.5	3.6
70°-80°	118.7	2.0
80°-90°	36.5	0.6
90°-100°	90.2	1.5
100°-110°	267.1	4.5
110°-120°	453.4	7.7
120°-130°	597.8	10.1
130°-140°	671.4	11.4
140°-150°	659.8	11.2
150°-160°	554.9	9.4
160°-170°	369.2	6.2
170°-180°	129.3	2.2
0°-30°	669.2	11.3
0°-40°	1075.0	18.2
0°-60°	1746.2	29.5
0°-90°	2116.8	35.8
90°-120°	810.7	13.7
90°-150°	2739.7	46.4
90°-180°	3793.0	64.2
0°-180°	5909.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	766	766	766	766	766	
5°	898	765	675	765	898	91
15°	1234	731	541	731	1234	349
25°	1310	668	440	668	1310	578
35°	775	580	390	580	775	492
45°	435	463	348	463	435	342
55°	284	326	304	326	284	257
65°	183	203	243	203	183	181
75°	91	99	150	99	91	97
85°	19	20	47	20	19	24
90°	32	3	32	3	32	17
95°	84	63	84	63	84	87
105°	258	246	258	246	258	272
115°	457	461	457	461	457	452
125°	666	671	666	671	666	594
135°	867	866	867	866	867	670
145°	1053	1052	1053	1052	1053	659
155°	1204	1205	1204	1205	1204	554
165°	1309	1312	1309	1312	1309	369
175°	1359	1365	1359	1365	1359	129
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	815.0	814.7	812.2	811.7	809.9	807.6	807.1	803.1	794.9	791.2	790.1
5°	898.4	904.7	896.4	894.9	893.9	883.5	878.1	871.7	857.1	848.6	841.9
7.5°	997.8	998.6	995.0	992.1	984.0	974.9	961.2	946.6	929.2	911.1	897.5
10°	1063.3	1065.8	1061.8	1061.1	1044.9	1034.8	1014.5	997.4	977.6	955.8	935.8
12.5°	1132.4	1128.8	1126.7	1113.1	1110.1	1091.6	1068.0	1050.4	1020.0	994.8	968.2
15°	1234.0	1227.0	1222.5	1203.9	1194.7	1169.0	1143.9	1124.5	1084.9	1047.2	1018.6
17.5°	1293.6	1300.6	1290.3	1282.6	1258.8	1240.8	1215.2	1174.6	1143.5	1096.7	1060.6
20°	1336.8	1337.4	1331.7	1323.7	1305.0	1282.2	1254.3	1209.9	1172.7	1126.1	1076.6
22.5°	1348.4	1348.6	1346.1	1338.7	1324.5	1306.0	1277.9	1240.8	1195.9	1145.2	1095.7
25°	1310.1	1308.9	1311.7	1320.0	1314.6	1308.9	1292.7	1265.1	1223.2	1169.5	1116.3
27.5°	1167.8	1176.5	1192.6	1212.9	1232.5	1247.3	1251.6	1245.9	1219.9	1175.8	1120.1
30°	1065.2	1076.0	1088.0	1108.4	1147.7	1170.2	1195.0	1213.7	1203.2	1168.0	1116.0
32.5°	952.5	955.2	973.1	996.2	1032.3	1075.5	1114.8	1152.8	1165.4	1147.0	1103.5
35°	774.6	779.1	798.4	821.3	865.4	918.4	977.4	1030.0	1073.5	1091.0	1068.7
37.5°	632.2	644.9	658.5	683.1	721.9	769.6	831.0	899.0	963.8	1007.2	1014.6
40°	564.7	572.6	582.4	601.1	634.1	681.1	733.7	811.8	880.6	942.8	963.1
42.5°	511.4	516.0	522.0	538.9	564.1	610.7	658.8	727.5	796.6	871.0	905.0
45°	434.6	439.4	449.5	459.3	478.3	510.7	555.5	611.9	681.3	753.1	815.9
47.5°	379.1	382.2	388.2	398.8	414.9	436.3	472.6	519.8	584.2	653.8	720.7
50°	347.6	350.2	355.0	364.5	376.8	395.9	425.7	469.8	520.2	590.4	656.0
52.5°	322.8	323.8	327.3	333.8	343.6	359.6	384.1	420.5	467.5	529.9	595.3
55°	284.2	285.5	288.7	293.4	302.0	312.2	330.8	358.2	399.1	453.3	510.1
57.5°	252.5	253.4	256.1	257.9	265.0	273.2	287.6	307.0	338.1	384.1	434.8
60°	232.2	231.5	234.7	236.4	241.1	248.1	259.2	277.9	304.8	341.9	388.6
62.5°	212.4	211.5	214.2	216.3	219.0	224.9	234.1	248.7	270.6	304.2	344.5
65°	182.7	181.5	183.0	185.6	188.1	191.3	198.0	210.9	228.4	252.5	283.2
67.5°	152.9	154.3	154.5	155.7	157.2	161.5	166.1	175.3	187.6	206.9	232.9
70°	135.1	135.4	136.7	136.7	137.7	141.5	145.3	150.7	162.7	180.5	201.8
72.5°	117.4	118.7	118.2	119.2	119.9	122.5	125.2	130.4	140.6	153.8	171.8
75°	91.4	92.3	92.3	92.6	93.6	94.5	96.8	100.5	107.9	117.6	130.0
77.5°	66.6	66.8	67.2	68.3	68.3	69.9	71.5	74.5	78.2	84.9	92.5
80°	51.4	52.0	51.7	52.3	52.3	53.6	54.2	58.0	59.6	64.1	70.1
82.5°	37.7	38.3	38.2	39.1	39.6	39.9	40.8	42.3	43.9	47.9	50.3
85°	19.0	19.6	19.0	19.6	20.6	21.0	21.9	22.2	23.5	24.5	26.7
87.5°	11.9	12.6	12.5	12.6	13.0	13.1	13.1	12.6	13.3	13.3	13.9
90°	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1	24.7	23.2	21.4
92.5°	47.0	46.6	46.4	46.1	45.8	45.2	44.4	43.5	42.7	41.9	40.5
95°	83.6	83.6	83.6	83.6	83.6	83.2	82.5	81.8	81.0	80.4	78.7
97.5°	130.9	130.9	130.9	130.9	130.9	130.4	129.6	128.8	127.9	127.1	125.1
100°	163.9	163.9	163.9	163.9	163.9	163.6	163.2	162.7	162.2	161.8	159.6
102.5°	201.1	200.9	200.7	200.6	200.3	199.9	199.3	198.6	198.0	197.3	195.3
105°	258.0	257.3	256.6	255.8	255.2	254.5	253.8	253.1	252.3	251.7	250.7
107.5°	313.4	313.5	313.5	313.6	313.6	313.3	312.6	311.9	311.3	310.6	310.5
110°	353.2	352.5	351.7	351.1	350.3	350.3	350.7	351.1	351.6	352.1	352.4



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.8	393.6	393.5	393.3	393.2	393.1	393.3	393.4	393.5	393.5	394.0
115°	456.8	457.0	457.2	457.5	457.7	458.0	458.2	458.4	458.7	458.9	459.3
117.5°	516.8	517.3	517.8	518.2	518.7	519.3	520.2	521.0	521.7	522.5	522.9
120°	562.5	562.1	561.6	561.1	560.6	561.0	562.1	563.4	564.5	565.7	566.4
122.5°	600.5	601.4	602.3	603.1	604.0	604.8	605.6	606.3	607.2	608.0	608.3
125°	666.1	666.6	667.1	667.6	668.0	668.5	669.0	669.4	669.8	670.3	670.6
127.5°	726.8	727.2	727.6	728.0	728.3	728.7	729.2	729.7	730.2	730.6	731.0
130°	766.5	767.5	768.4	769.4	770.4	771.0	771.5	772.0	772.4	772.9	772.9
132.5°	808.9	809.3	809.6	810.0	810.4	810.8	811.3	811.7	812.2	812.7	812.9
135°	867.0	867.7	868.5	869.1	869.8	870.4	870.9	871.4	871.9	872.3	872.3
137.5°	928.1	928.0	927.9	927.7	927.6	927.8	928.5	929.0	929.6	930.3	929.8
140°	965.4	965.6	965.8	966.0	966.3	966.5	966.8	967.0	967.3	967.4	967.4
142.5°	1002.6	1002.7	1002.7	1002.7	1002.7	1002.8	1002.9	1002.9	1003.0	1003.0	1003.2
145°	1053.1	1053.9	1054.5	1055.2	1056.0	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1104.3	1104.6	1104.7	1105.0	1105.2	1105.5	1105.6	1105.8	1106.0	1106.2	1106.4
150°	1135.6	1135.8	1136.0	1136.3	1136.5	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1164.3	1165.0	1165.6	1166.2	1166.8	1166.9	1166.3	1165.7	1165.1	1164.6	1164.4
155°	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4	1204.5
157.5°	1240.1	1240.9	1241.6	1242.4	1243.2	1243.3	1242.6	1241.9	1241.2	1240.5	1240.6
160°	1260.4	1261.5	1262.7	1263.9	1265.0	1265.3	1264.6	1263.9	1263.1	1262.5	1262.7
162.5°	1281.5	1282.7	1283.9	1285.0	1286.2	1286.1	1284.9	1283.6	1282.4	1281.1	1281.3
165°	1309.0	1309.9	1310.8	1311.8	1312.8	1312.6	1311.1	1309.7	1308.3	1306.8	1307.3
167.5°	1328.7	1330.2	1331.5	1333.0	1334.5	1334.5	1333.1	1331.7	1330.3	1328.9	1328.9
170°	1339.7	1341.3	1343.0	1344.6	1346.2	1346.4	1344.9	1343.5	1342.1	1340.7	1340.5
172.5°	1349.0	1350.6	1352.3	1353.9	1355.5	1355.6	1354.0	1352.3	1350.8	1349.2	1349.2
175°	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7	1358.9
177.5°	1363.8	1365.3	1366.8	1368.3	1369.8	1369.9	1368.6	1367.3	1366.0	1364.6	1364.6
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	790.4	786.8	784.3	782.3	776.7	773.4	770.9	767.3	763.2	758.9	753.6
5°	835.3	824.4	816.5	804.5	793.0	783.5	773.7	764.8	754.0	742.3	733.7
7.5°	882.4	866.3	845.8	827.9	807.9	790.4	774.9	758.9	742.2	726.1	711.3
10°	912.3	891.7	868.9	841.9	816.5	794.0	773.1	752.8	733.1	713.4	696.6
12.5°	944.5	918.8	885.1	853.5	825.2	795.0	769.7	744.9	721.1	700.5	680.9
15°	987.8	950.7	911.7	869.5	832.1	796.9	762.3	730.8	704.3	676.9	657.9
17.5°	1014.4	968.5	923.9	879.8	834.5	790.0	752.8	716.6	683.1	656.1	632.1
20°	1031.9	986.3	930.7	886.6	832.7	787.0	743.9	703.6	668.7	639.8	615.1
22.5°	1047.2	994.3	938.8	880.8	827.1	778.6	731.4	690.9	655.3	624.8	601.1
25°	1055.4	994.8	934.5	876.8	815.9	758.5	715.7	668.1	630.0	597.9	572.6
27.5°	1056.3	991.5	923.3	859.2	796.3	742.8	688.8	646.2	606.7	572.8	548.5
30°	1053.4	985.9	912.6	843.2	780.1	721.9	675.1	628.8	588.4	554.8	529.5
32.5°	1044.6	974.2	898.9	825.4	760.0	703.2	654.8	610.7	571.4	538.3	511.7
35°	1018.9	949.4	869.2	792.7	725.8	668.4	624.6	579.8	540.5	509.2	483.5
37.5°	978.8	915.9	834.4	755.2	689.5	631.9	588.4	548.0	512.6	480.6	454.3
40°	943.7	888.5	806.7	729.6	658.5	603.6	563.0	525.9	490.7	460.6	435.5
42.5°	903.4	855.2	779.8	698.1	629.6	574.5	534.9	501.6	468.4	440.6	415.5
45°	831.4	799.7	728.6	653.1	581.8	529.8	492.0	462.8	434.9	407.6	386.7
47.5°	748.7	733.0	673.1	601.4	533.7	482.4	449.7	422.7	398.3	375.1	356.7
50°	693.1	685.5	633.8	564.7	499.9	451.8	418.7	395.6	374.6	354.3	336.9
52.5°	638.3	638.1	591.4	528.1	468.2	421.8	389.1	367.4	349.3	332.7	317.1
55°	554.5	563.4	526.9	470.4	416.9	375.0	345.4	326.1	313.4	299.8	288.0
57.5°	477.5	492.3	462.2	412.5	367.7	329.1	303.5	288.9	275.4	267.2	258.6
60°	427.3	441.2	417.8	375.9	333.7	300.7	276.3	263.3	251.5	245.8	239.8
62.5°	382.6	395.1	377.6	338.8	302.2	270.5	249.9	237.4	229.5	223.2	219.2
65°	318.8	329.3	314.4	286.2	254.7	229.3	212.5	202.7	195.1	192.6	188.1
67.5°	257.7	267.3	259.2	235.2	210.0	190.8	177.7	168.2	163.7	161.4	158.3
70°	221.4	231.0	222.3	201.5	182.1	165.9	153.5	148.1	143.4	142.4	138.0
72.5°	190.7	197.2	188.6	172.3	155.7	142.0	132.5	126.9	124.3	122.6	120.3
75°	143.1	148.8	143.1	130.4	118.6	109.1	100.9	98.7	95.8	94.8	93.3
77.5°	101.3	106.2	101.8	93.9	85.1	77.8	73.4	70.5	69.9	68.2	69.0
80°	77.4	80.6	76.5	71.1	64.1	59.0	55.8	54.2	52.3	51.7	53.0
82.5°	55.6	57.0	54.9	51.3	46.1	42.7	40.6	38.7	38.4	38.5	38.5
85°	28.9	28.5	28.2	25.0	23.5	21.3	20.0	19.6	19.3	20.0	20.6
87.5°	13.5	13.5	12.8	11.3	10.0	8.8	8.0	7.3	8.0	8.8	9.5
90°	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2	5.8	8.3	10.9
92.5°	39.2	37.9	36.6	34.5	31.5	28.5	25.6	22.7	25.6	28.5	31.5
95°	77.0	75.4	73.8	71.9	69.8	67.7	65.6	63.4	65.6	67.7	69.8
97.5°	123.3	121.3	119.4	117.6	115.9	114.2	112.5	110.8	112.5	114.2	115.9
100°	157.5	155.4	153.3	151.8	150.8	149.9	149.0	148.1	149.0	149.9	150.8
102.5°	193.5	191.5	189.6	188.4	188.1	187.7	187.4	186.9	187.4	187.7	188.1
105°	249.8	248.8	247.9	247.3	247.0	246.9	246.6	246.4	246.6	246.9	247.0
107.5°	310.4	310.2	310.1	309.9	309.6	309.3	309.0	308.8	309.0	309.3	309.6
110°	352.5	352.8	353.0	352.9	352.5	352.0	351.5	351.1	351.5	352.0	352.5



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	394.4	394.8	395.3	395.4	395.3	395.2	395.1	395.0	395.1	395.2	395.3
115°	459.8	460.3	460.8	461.0	461.0	461.0	461.0	461.0	461.0	461.0	461.0
117.5°	523.2	523.5	523.8	523.9	523.7	523.6	523.3	523.2	523.3	523.6	523.7
120°	567.1	567.8	568.5	568.3	567.4	566.5	565.6	564.6	565.6	566.5	567.4
122.5°	608.6	608.9	609.3	609.3	608.9	608.5	608.1	607.7	608.1	608.5	608.9
125°	670.8	671.1	671.3	671.4	671.4	671.4	671.4	671.4	671.4	671.4	671.4
127.5°	731.4	731.7	732.1	732.0	731.2	730.6	729.9	729.1	729.9	730.6	731.2
130°	772.9	772.9	772.9	772.6	771.8	771.2	770.5	769.7	770.5	771.2	771.8
132.5°	813.0	813.3	813.4	813.3	812.8	812.2	811.7	811.2	811.7	812.2	812.8
135°	872.3	872.3	872.3	871.6	870.2	868.8	867.4	865.9	867.4	868.8	870.2
137.5°	929.5	929.1	928.8	928.2	927.6	926.9	926.3	925.6	926.3	926.9	927.6
140°	967.4	967.4	967.4	967.3	966.8	966.3	965.8	965.4	965.8	966.3	966.8
142.5°	1003.4	1003.6	1003.7	1003.6	1003.1	1002.7	1002.2	1001.8	1002.2	1002.7	1003.1
145°	1056.9	1056.6	1056.4	1055.8	1054.9	1053.9	1053.0	1052.1	1053.0	1053.9	1054.9
147.5°	1106.6	1106.8	1106.9	1106.4	1105.4	1104.2	1103.1	1102.0	1103.1	1104.2	1105.4
150°	1136.6	1136.6	1136.6	1136.2	1135.2	1134.3	1133.3	1132.5	1133.3	1134.3	1135.2
152.5°	1164.2	1164.0	1163.8	1163.4	1162.9	1162.3	1161.7	1161.1	1161.7	1162.3	1162.9
155°	1204.8	1205.0	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
157.5°	1240.6	1240.6	1240.6	1240.9	1241.3	1241.8	1242.2	1242.6	1242.2	1241.8	1241.3
160°	1263.0	1263.1	1263.4	1263.6	1263.9	1264.1	1264.4	1264.6	1264.4	1264.1	1263.9
162.5°	1281.6	1281.8	1282.1	1282.5	1283.0	1283.7	1284.3	1284.9	1284.3	1283.7	1283.0
165°	1307.8	1308.3	1308.8	1309.4	1310.0	1310.8	1311.5	1312.1	1311.5	1310.8	1310.0
167.5°	1328.8	1328.8	1328.7	1329.2	1330.2	1331.1	1332.1	1333.1	1332.1	1331.1	1330.2
170°	1340.3	1340.0	1339.8	1340.3	1341.4	1342.6	1343.8	1344.9	1343.8	1342.6	1341.4
172.5°	1349.1	1349.1	1349.0	1349.5	1350.5	1351.4	1352.4	1353.4	1352.4	1351.4	1350.5
175°	1359.2	1359.4	1359.6	1360.3	1361.5	1362.7	1363.8	1365.1	1363.8	1362.7	1361.5
177.5°	1364.6	1364.6	1364.6	1365.1	1366.0	1366.9	1367.9	1368.8	1367.9	1366.9	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	751.1	748.8	745.4	740.9	737.1	733.0	732.0	730.5	733.5	731.0	730.3
5°	726.4	719.7	711.2	701.4	695.7	687.4	685.8	682.7	679.5	679.1	676.0
7.5°	700.3	690.6	679.4	669.4	660.1	651.1	645.1	643.9	639.2	636.5	633.3
10°	683.6	671.6	658.5	649.1	638.2	628.8	622.1	618.2	615.1	611.6	608.5
12.5°	663.8	651.0	640.3	630.0	617.2	609.9	599.0	592.4	591.7	591.8	583.6
15°	640.7	628.1	611.6	597.0	590.0	576.1	570.1	562.4	557.7	552.9	549.1
17.5°	614.5	598.7	585.8	569.0	555.7	544.6	536.6	532.1	525.0	518.2	513.3
20°	597.9	581.1	567.5	549.8	535.2	521.5	514.9	508.5	503.1	497.4	492.0
22.5°	581.2	563.6	547.0	529.7	516.1	501.7	495.3	486.7	481.5	478.3	473.0
25°	554.8	535.8	516.7	500.3	486.3	473.6	465.0	458.4	452.7	450.1	446.6
27.5°	526.1	507.2	488.9	470.1	454.3	445.1	438.2	433.2	429.9	426.6	424.9
30°	507.8	488.2	468.6	451.1	436.5	427.3	420.9	417.4	414.9	413.4	411.7
32.5°	489.3	469.9	449.2	433.3	420.3	412.1	407.2	403.7	402.5	401.9	401.4
35°	459.7	440.0	420.9	406.7	394.3	391.1	387.0	385.1	384.5	386.7	387.7
37.5°	430.9	412.6	395.1	381.3	373.2	368.5	367.1	367.2	369.5	371.5	373.7
40°	412.4	394.6	378.1	366.1	358.5	355.6	355.0	356.5	359.1	361.3	363.9
42.5°	394.4	376.8	361.9	350.6	345.3	342.7	343.1	344.6	348.2	350.9	354.7
45°	366.4	351.8	337.2	328.0	323.6	324.2	324.2	327.0	330.5	334.7	338.8
47.5°	340.1	325.3	313.3	305.6	303.3	302.7	304.5	308.3	313.3	318.4	324.2
50°	322.3	308.3	297.8	290.9	288.4	289.3	291.9	295.3	301.3	307.7	313.7
52.5°	304.3	291.6	281.8	275.4	273.6	275.3	277.9	283.4	288.7	295.5	302.8
55°	276.3	265.5	257.9	253.2	252.5	253.5	256.3	262.4	269.9	278.5	285.5
57.5°	248.4	239.5	232.4	229.2	229.5	230.4	235.1	242.2	250.4	259.5	268.5
60°	229.7	221.4	215.7	213.2	213.5	215.4	221.1	227.8	237.9	246.8	256.3
62.5°	211.9	204.6	199.2	196.9	196.5	200.6	206.1	213.0	223.2	233.1	243.4
65°	183.4	177.7	173.2	171.9	172.8	176.0	183.0	192.2	200.8	211.2	222.1
67.5°	155.4	150.7	147.7	148.3	149.4	154.1	160.0	167.9	177.6	188.4	199.1
70°	137.7	133.2	130.7	131.0	132.9	138.6	143.7	151.6	162.1	173.2	182.1
72.5°	119.4	116.5	114.2	115.5	117.4	121.4	127.7	135.7	144.9	155.2	164.6
75°	91.6	91.6	90.4	91.4	94.2	98.0	102.8	111.0	120.3	128.5	136.1
77.5°	68.0	67.3	68.2	69.3	70.9	75.4	80.9	86.8	93.7	102.0	108.3
80°	52.0	52.3	53.9	55.8	56.5	59.9	65.6	71.1	76.5	83.4	89.4
82.5°	39.1	39.4	40.2	42.6	43.3	47.0	50.7	56.1	61.0	65.6	70.7
85°	21.3	21.3	22.8	23.8	25.4	27.9	30.2	33.3	37.7	40.9	45.7
87.5°	10.8	11.3	12.6	13.5	14.7	16.3	17.1	20.2	21.5	23.1	25.5
90°	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1	27.5	28.9	29.8
92.5°	34.5	36.6	37.9	39.2	40.5	41.9	42.7	43.5	44.4	45.2	45.8
95°	71.9	73.8	75.4	77.0	78.7	80.4	81.0	81.8	82.5	83.2	83.6
97.5°	117.6	119.4	121.3	123.3	125.1	127.1	127.9	128.8	129.6	130.4	130.9
100°	151.8	153.3	155.4	157.5	159.6	161.8	162.2	162.7	163.2	163.6	163.9
102.5°	188.4	189.6	191.5	193.5	195.3	197.3	198.0	198.6	199.3	199.9	200.3
105°	247.3	247.9	248.8	249.8	250.7	251.7	252.3	253.1	253.8	254.5	255.2
107.5°	309.9	310.1	310.2	310.4	310.5	310.6	311.3	311.9	312.6	313.3	313.6
110°	352.9	353.0	352.8	352.5	352.4	352.1	351.6	351.1	350.7	350.3	350.3



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	395.4	395.3	394.8	394.4	394.0	393.5	393.5	393.4	393.3	393.1	393.2
115°	461.0	460.8	460.3	459.8	459.3	458.9	458.7	458.4	458.2	458.0	457.7
117.5°	523.9	523.8	523.5	523.2	522.9	522.5	521.7	521.0	520.2	519.3	518.7
120°	568.3	568.5	567.8	567.1	566.4	565.7	564.5	563.4	562.1	561.0	560.6
122.5°	609.3	609.3	608.9	608.6	608.3	608.0	607.2	606.3	605.6	604.8	604.0
125°	671.4	671.3	671.1	670.8	670.6	670.3	669.8	669.4	669.0	668.5	668.0
127.5°	732.0	732.1	731.7	731.4	731.0	730.6	730.2	729.7	729.2	728.7	728.3
130°	772.6	772.9	772.9	772.9	772.9	772.9	772.4	772.0	771.5	771.0	770.4
132.5°	813.3	813.4	813.3	813.0	812.9	812.7	812.2	811.7	811.3	810.8	810.4
135°	871.6	872.3	872.3	872.3	872.3	872.3	871.9	871.4	870.9	870.4	869.8
137.5°	928.2	928.8	929.1	929.5	929.8	930.3	929.6	929.0	928.5	927.8	927.6
140°	967.3	967.4	967.4	967.4	967.4	967.4	967.3	967.0	966.8	966.5	966.3
142.5°	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0	1002.9	1002.9	1002.8	1002.7
145°	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1	1056.9	1056.6	1056.4	1056.0
147.5°	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0	1105.8	1105.6	1105.5	1105.2
150°	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.5
152.5°	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1	1165.7	1166.3	1166.9	1166.8
155°	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1
157.5°	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2	1241.9	1242.6	1243.3	1243.2
160°	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1	1263.9	1264.6	1265.3	1265.0
162.5°	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4	1283.6	1284.9	1286.1	1286.2
165°	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3	1309.7	1311.1	1312.6	1312.8
167.5°	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3	1331.7	1333.1	1334.5	1334.5
170°	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1	1343.5	1344.9	1346.4	1346.2
172.5°	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8	1352.3	1354.0	1355.6	1355.5
175°	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3
177.5°	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0	1367.3	1368.6	1369.9	1369.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	729.7	729.2	727.4	727.2	727.4	729.2	729.7	730.3	731.0	733.5	730.5
5°	674.1	672.5	671.6	675.1	671.6	672.5	674.1	676.0	679.1	679.5	682.7
7.5°	632.2	630.9	628.1	627.2	628.1	630.9	632.2	633.3	636.5	639.2	643.9
10°	605.3	604.0	601.4	600.8	601.4	604.0	605.3	608.5	611.6	615.1	618.2
12.5°	579.4	576.8	576.3	577.0	576.3	576.8	579.4	583.6	591.8	591.7	592.4
15°	544.9	543.7	540.2	541.2	540.2	543.7	544.9	549.1	552.9	557.7	562.4
17.5°	511.1	509.6	505.3	509.1	505.3	509.6	511.1	513.3	518.2	525.0	532.1
20°	489.8	487.2	485.0	484.7	485.0	487.2	489.8	492.0	497.4	503.1	508.5
22.5°	469.4	467.2	467.0	464.9	467.0	467.2	469.4	473.0	478.3	481.5	486.7
25°	444.1	441.9	441.2	439.7	441.2	441.9	444.1	446.6	450.1	452.7	458.4
27.5°	424.6	423.5	422.4	422.9	422.4	423.5	424.6	424.9	426.6	429.9	433.2
30°	412.7	412.4	411.7	411.7	411.7	412.4	412.7	411.7	413.4	414.9	417.4
32.5°	402.8	402.8	403.1	403.1	403.1	402.8	402.8	401.4	401.9	402.5	403.7
35°	388.9	389.9	390.5	389.6	390.5	389.9	388.9	387.7	386.7	384.5	385.1
37.5°	376.3	377.3	378.2	379.3	378.2	377.3	376.3	373.7	371.5	369.5	367.2
40°	366.7	368.9	369.6	371.1	369.6	368.9	366.7	363.9	361.3	359.1	356.5
42.5°	357.6	360.0	361.7	362.0	361.7	360.0	357.6	354.7	350.9	348.2	344.6
45°	343.6	346.1	348.3	348.3	348.3	346.1	343.6	338.8	334.7	330.5	327.0
47.5°	329.1	332.7	334.9	335.5	334.9	332.7	329.1	324.2	318.4	313.3	308.3
50°	319.1	323.6	325.8	327.3	325.8	323.6	319.1	313.7	307.7	301.3	295.3
52.5°	309.5	313.9	316.9	317.7	316.9	313.9	309.5	302.8	295.5	288.7	283.4
55°	292.8	299.1	302.6	303.9	302.6	299.1	292.8	285.5	278.5	269.9	262.4
57.5°	277.0	282.9	287.0	287.9	287.0	282.9	277.0	268.5	259.5	250.4	242.2
60°	264.9	271.3	276.3	277.3	276.3	271.3	264.9	256.3	246.8	237.9	227.8
62.5°	252.4	259.0	263.6	266.1	263.6	259.0	252.4	243.4	233.1	223.2	213.0
65°	231.0	237.6	242.1	243.0	242.1	237.6	231.0	222.1	211.2	200.8	192.2
67.5°	207.5	214.1	217.0	218.9	217.0	214.1	207.5	199.1	188.4	177.6	167.9
70°	190.9	196.3	199.5	201.1	199.5	196.3	190.9	182.1	173.2	162.1	151.6
72.5°	172.2	177.8	181.5	181.8	181.5	177.8	172.2	164.6	155.2	144.9	135.7
75°	143.4	148.5	150.3	150.3	150.3	148.5	143.4	136.1	128.5	120.3	111.0
77.5°	113.5	116.1	118.5	119.0	118.5	116.1	113.5	108.3	102.0	93.7	86.8
80°	94.2	95.8	97.7	97.7	97.7	95.8	94.2	89.4	83.4	76.5	71.1
82.5°	74.4	75.7	77.6	77.4	77.6	75.7	74.4	70.7	65.6	61.0	56.1
85°	45.0	47.9	47.6	47.0	47.6	47.9	45.0	45.7	40.9	37.7	33.3
87.5°	26.3	26.7	27.6	28.2	27.6	26.7	26.3	25.5	23.1	21.5	20.2
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1
92.5°	46.1	46.4	46.6	47.0	46.6	46.4	46.1	45.8	45.2	44.4	43.5
95°	83.6	83.6	83.6	83.6	83.6	83.6	83.6	83.6	83.2	82.5	81.8
97.5°	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.4	129.6	128.8
100°	163.9	163.9	163.9	163.9	163.9	163.9	163.9	163.9	163.6	163.2	162.7
102.5°	200.6	200.7	200.9	201.1	200.9	200.7	200.6	200.3	199.9	199.3	198.6
105°	255.8	256.6	257.3	258.0	257.3	256.6	255.8	255.2	254.5	253.8	253.1
107.5°	313.6	313.5	313.5	313.4	313.5	313.5	313.6	313.6	313.3	312.6	311.9
110°	351.1	351.7	352.5	353.2	352.5	351.7	351.1	350.3	350.3	350.7	351.1



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	393.3	393.5	393.6	393.8	393.6	393.5	393.3	393.2	393.1	393.3	393.4
115°	457.5	457.2	457.0	456.8	457.0	457.2	457.5	457.7	458.0	458.2	458.4
117.5°	518.2	517.8	517.3	516.8	517.3	517.8	518.2	518.7	519.3	520.2	521.0
120°	561.1	561.6	562.1	562.5	562.1	561.6	561.1	560.6	561.0	562.1	563.4
122.5°	603.1	602.3	601.4	600.5	601.4	602.3	603.1	604.0	604.8	605.6	606.3
125°	667.6	667.1	666.6	666.1	666.6	667.1	667.6	668.0	668.5	669.0	669.4
127.5°	728.0	727.6	727.2	726.8	727.2	727.6	728.0	728.3	728.7	729.2	729.7
130°	769.4	768.4	767.5	766.5	767.5	768.4	769.4	770.4	771.0	771.5	772.0
132.5°	810.0	809.6	809.3	808.9	809.3	809.6	810.0	810.4	810.8	811.3	811.7
135°	869.1	868.5	867.7	867.0	867.7	868.5	869.1	869.8	870.4	870.9	871.4
137.5°	927.7	927.9	928.0	928.1	928.0	927.9	927.7	927.6	927.8	928.5	929.0
140°	966.0	965.8	965.6	965.4	965.6	965.8	966.0	966.3	966.5	966.8	967.0
142.5°	1002.7	1002.7	1002.7	1002.6	1002.7	1002.7	1002.7	1002.7	1002.8	1002.9	1002.9
145°	1055.2	1054.5	1053.9	1053.1	1053.9	1054.5	1055.2	1056.0	1056.4	1056.6	1056.9
147.5°	1105.0	1104.7	1104.6	1104.3	1104.6	1104.7	1105.0	1105.2	1105.5	1105.6	1105.8
150°	1136.3	1136.0	1135.8	1135.6	1135.8	1136.0	1136.3	1136.5	1136.6	1136.6	1136.6
152.5°	1166.2	1165.6	1165.0	1164.3	1165.0	1165.6	1166.2	1166.8	1166.9	1166.3	1165.7
155°	1207.1	1206.2	1205.3	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2
157.5°	1242.4	1241.6	1240.9	1240.1	1240.9	1241.6	1242.4	1243.2	1243.3	1242.6	1241.9
160°	1263.9	1262.7	1261.5	1260.4	1261.5	1262.7	1263.9	1265.0	1265.3	1264.6	1263.9
162.5°	1285.0	1283.9	1282.7	1281.5	1282.7	1283.9	1285.0	1286.2	1286.1	1284.9	1283.6
165°	1311.8	1310.8	1309.9	1309.0	1309.9	1310.8	1311.8	1312.8	1312.6	1311.1	1309.7
167.5°	1333.0	1331.5	1330.2	1328.7	1330.2	1331.5	1333.0	1334.5	1334.5	1333.1	1331.7
170°	1344.6	1343.0	1341.3	1339.7	1341.3	1343.0	1344.6	1346.2	1346.4	1344.9	1343.5
172.5°	1353.9	1352.3	1350.6	1349.0	1350.6	1352.3	1353.9	1355.5	1355.6	1354.0	1352.3
175°	1363.6	1362.0	1360.3	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0
177.5°	1368.3	1366.8	1365.3	1363.8	1365.3	1366.8	1368.3	1369.8	1369.9	1368.6	1367.3
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	732.0	733.0	737.1	740.9	745.4	748.8	751.1	753.6	758.9	763.2	767.3
5°	685.8	687.4	695.7	701.4	711.2	719.7	726.4	733.7	742.3	754.0	764.8
7.5°	645.1	651.1	660.1	669.4	679.4	690.6	700.3	711.3	726.1	742.2	758.9
10°	622.1	628.8	638.2	649.1	658.5	671.6	683.6	696.6	713.4	733.1	752.8
12.5°	599.0	609.9	617.2	630.0	640.3	651.0	663.8	680.9	700.5	721.1	744.9
15°	570.1	576.1	590.0	597.0	611.6	628.1	640.7	657.9	676.9	704.3	730.8
17.5°	536.6	544.6	555.7	569.0	585.8	598.7	614.5	632.1	656.1	683.1	716.6
20°	514.9	521.5	535.2	549.8	567.5	581.1	597.9	615.1	639.8	668.7	703.6
22.5°	495.3	501.7	516.1	529.7	547.0	563.6	581.2	601.1	624.8	655.3	690.9
25°	465.0	473.6	486.3	500.3	516.7	535.8	554.8	572.6	597.9	630.0	668.1
27.5°	438.2	445.1	454.3	470.1	488.9	507.2	526.1	548.5	572.8	606.7	646.2
30°	420.9	427.3	436.5	451.1	468.6	488.2	507.8	529.5	554.8	588.4	628.8
32.5°	407.2	412.1	420.3	433.3	449.2	469.9	489.3	511.7	538.3	571.4	610.7
35°	387.0	391.1	394.3	406.7	420.9	440.0	459.7	483.5	509.2	540.5	579.8
37.5°	367.1	368.5	373.2	381.3	395.1	412.6	430.9	454.3	480.6	512.6	548.0
40°	355.0	355.6	358.5	366.1	378.1	394.6	412.4	435.5	460.6	490.7	525.9
42.5°	343.1	342.7	345.3	350.6	361.9	376.8	394.4	415.5	440.6	468.4	501.6
45°	324.2	324.2	323.6	328.0	337.2	351.8	366.4	386.7	407.6	434.9	462.8
47.5°	304.5	302.7	303.3	305.6	313.3	325.3	340.1	356.7	375.1	398.3	422.7
50°	291.9	289.3	288.4	290.9	297.8	308.3	322.3	336.9	354.3	374.6	395.6
52.5°	277.9	275.3	273.6	275.4	281.8	291.6	304.3	317.1	332.7	349.3	367.4
55°	256.3	253.5	252.5	253.2	257.9	265.5	276.3	288.0	299.8	313.4	326.1
57.5°	235.1	230.4	229.5	229.2	232.4	239.5	248.4	258.6	267.2	275.4	288.9
60°	221.1	215.4	213.5	213.2	215.7	221.4	229.7	239.8	245.8	251.5	263.3
62.5°	206.1	200.6	196.5	196.9	199.2	204.6	211.9	219.2	223.2	229.5	237.4
65°	183.0	176.0	172.8	171.9	173.2	177.7	183.4	188.1	192.6	195.1	202.7
67.5°	160.0	154.1	149.4	148.3	147.7	150.7	155.4	158.3	161.4	163.7	168.2
70°	143.7	138.6	132.9	131.0	130.7	133.2	137.7	138.0	142.4	143.4	148.1
72.5°	127.7	121.4	117.4	115.5	114.2	116.5	119.4	120.3	122.6	124.3	126.9
75°	102.8	98.0	94.2	91.4	90.4	91.6	91.6	93.3	94.8	95.8	98.7
77.5°	80.9	75.4	70.9	69.3	68.2	67.3	68.0	69.0	68.2	69.9	70.5
80°	65.6	59.9	56.5	55.8	53.9	52.3	52.0	53.0	51.7	52.3	54.2
82.5°	50.7	47.0	43.3	42.6	40.2	39.4	39.1	38.5	38.5	38.4	38.7
85°	30.2	27.9	25.4	23.8	22.8	21.3	21.3	20.6	20.0	19.3	19.6
87.5°	17.1	16.3	14.7	13.5	12.6	11.3	10.8	9.5	8.8	8.0	7.3
90°	24.7	23.2	21.4	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2
92.5°	42.7	41.9	40.5	39.2	37.9	36.6	34.5	31.5	28.5	25.6	22.7
95°	81.0	80.4	78.7	77.0	75.4	73.8	71.9	69.8	67.7	65.6	63.4
97.5°	127.9	127.1	125.1	123.3	121.3	119.4	117.6	115.9	114.2	112.5	110.8
100°	162.2	161.8	159.6	157.5	155.4	153.3	151.8	150.8	149.9	149.0	148.1
102.5°	198.0	197.3	195.3	193.5	191.5	189.6	188.4	188.1	187.7	187.4	186.9
105°	252.3	251.7	250.7	249.8	248.8	247.9	247.3	247.0	246.9	246.6	246.4
107.5°	311.3	310.6	310.5	310.4	310.2	310.1	309.9	309.6	309.3	309.0	308.8
110°	351.6	352.1	352.4	352.5	352.8	353.0	352.9	352.5	352.0	351.5	351.1



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.5	393.5	394.0	394.4	394.8	395.3	395.4	395.3	395.2	395.1	395.0
115°	458.7	458.9	459.3	459.8	460.3	460.8	461.0	461.0	461.0	461.0	461.0
117.5°	521.7	522.5	522.9	523.2	523.5	523.8	523.9	523.7	523.6	523.3	523.2
120°	564.5	565.7	566.4	567.1	567.8	568.5	568.3	567.4	566.5	565.6	564.6
122.5°	607.2	608.0	608.3	608.6	608.9	609.3	609.3	608.9	608.5	608.1	607.7
125°	669.8	670.3	670.6	670.8	671.1	671.3	671.4	671.4	671.4	671.4	671.4
127.5°	730.2	730.6	731.0	731.4	731.7	732.1	732.0	731.2	730.6	729.9	729.1
130°	772.4	772.9	772.9	772.9	772.9	772.9	772.6	771.8	771.2	770.5	769.7
132.5°	812.2	812.7	812.9	813.0	813.3	813.4	813.3	812.8	812.2	811.7	811.2
135°	871.9	872.3	872.3	872.3	872.3	872.3	871.6	870.2	868.8	867.4	865.9
137.5°	929.6	930.3	929.8	929.5	929.1	928.8	928.2	927.6	926.9	926.3	925.6
140°	967.3	967.4	967.4	967.4	967.4	967.4	967.3	966.8	966.3	965.8	965.4
142.5°	1003.0	1003.0	1003.2	1003.4	1003.6	1003.7	1003.6	1003.1	1002.7	1002.2	1001.8
145°	1057.1	1057.4	1057.1	1056.9	1056.6	1056.4	1055.8	1054.9	1053.9	1053.0	1052.1
147.5°	1106.0	1106.2	1106.4	1106.6	1106.8	1106.9	1106.4	1105.4	1104.2	1103.1	1102.0
150°	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.2	1135.2	1134.3	1133.3	1132.5
152.5°	1165.1	1164.6	1164.4	1164.2	1164.0	1163.8	1163.4	1162.9	1162.3	1161.7	1161.1
155°	1205.3	1204.4	1204.5	1204.8	1205.0	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
157.5°	1241.2	1240.5	1240.6	1240.6	1240.6	1240.6	1240.9	1241.3	1241.8	1242.2	1242.6
160°	1263.1	1262.5	1262.7	1263.0	1263.1	1263.4	1263.6	1263.9	1264.1	1264.4	1264.6
162.5°	1282.4	1281.1	1281.3	1281.6	1281.8	1282.1	1282.5	1283.0	1283.7	1284.3	1284.9
165°	1308.3	1306.8	1307.3	1307.8	1308.3	1308.8	1309.4	1310.0	1310.8	1311.5	1312.1
167.5°	1330.3	1328.9	1328.9	1328.8	1328.8	1328.7	1329.2	1330.2	1331.1	1332.1	1333.1
170°	1342.1	1340.7	1340.5	1340.3	1340.0	1339.8	1340.3	1341.4	1342.6	1343.8	1344.9
172.5°	1350.8	1349.2	1349.2	1349.1	1349.1	1349.0	1349.5	1350.5	1351.4	1352.4	1353.4
175°	1360.3	1358.7	1358.9	1359.2	1359.4	1359.6	1360.3	1361.5	1362.7	1363.8	1365.1
177.5°	1366.0	1364.6	1364.6	1364.6	1364.6	1364.6	1365.1	1366.0	1366.9	1367.9	1368.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	770.9	773.4	776.7	782.3	784.3	786.8	790.4	790.1	791.2	794.9	803.1
5°	773.7	783.5	793.0	804.5	816.5	824.4	835.3	841.9	848.6	857.1	871.7
7.5°	774.9	790.4	807.9	827.9	845.8	866.3	882.4	897.5	911.1	929.2	946.6
10°	773.1	794.0	816.5	841.9	868.9	891.7	912.3	935.8	955.8	977.6	997.4
12.5°	769.7	795.0	825.2	853.5	885.1	918.8	944.5	968.2	994.8	1020.0	1050.4
15°	762.3	796.9	832.1	869.5	911.7	950.7	987.8	1018.6	1047.2	1084.9	1124.5
17.5°	752.8	790.0	834.5	879.8	923.9	968.5	1014.4	1060.6	1096.7	1143.5	1174.6
20°	743.9	787.0	832.7	886.6	930.7	986.3	1031.9	1076.6	1126.1	1172.7	1209.9
22.5°	731.4	778.6	827.1	880.8	938.8	994.3	1047.2	1095.7	1145.2	1195.9	1240.8
25°	715.7	758.5	815.9	876.8	934.5	994.8	1055.4	1116.3	1169.5	1223.2	1265.1
27.5°	688.8	742.8	796.3	859.2	923.3	991.5	1056.3	1120.1	1175.8	1219.9	1245.9
30°	675.1	721.9	780.1	843.2	912.6	985.9	1053.4	1116.0	1168.0	1203.2	1213.7
32.5°	654.8	703.2	760.0	825.4	898.9	974.2	1044.6	1103.5	1147.0	1165.4	1152.8
35°	624.6	668.4	725.8	792.7	869.2	949.4	1018.9	1068.7	1091.0	1073.5	1030.0
37.5°	588.4	631.9	689.5	755.2	834.4	915.9	978.8	1014.6	1007.2	963.8	899.0
40°	563.0	603.6	658.5	729.6	806.7	888.5	943.7	963.1	942.8	880.6	811.8
42.5°	534.9	574.5	629.6	698.1	779.8	855.2	903.4	905.0	871.0	796.6	727.5
45°	492.0	529.8	581.8	653.1	728.6	799.7	831.4	815.9	753.1	681.3	611.9
47.5°	449.7	482.4	533.7	601.4	673.1	733.0	748.7	720.7	653.8	584.2	519.8
50°	418.7	451.8	499.9	564.7	633.8	685.5	693.1	656.0	590.4	520.2	469.8
52.5°	389.1	421.8	468.2	528.1	591.4	638.1	638.3	595.3	529.9	467.5	420.5
55°	345.4	375.0	416.9	470.4	526.9	563.4	554.5	510.1	453.3	399.1	358.2
57.5°	303.5	329.1	367.7	412.5	462.2	492.3	477.5	434.8	384.1	338.1	307.0
60°	276.3	300.7	333.7	375.9	417.8	441.2	427.3	388.6	341.9	304.8	277.9
62.5°	249.9	270.5	302.2	338.8	377.6	395.1	382.6	344.5	304.2	270.6	248.7
65°	212.5	229.3	254.7	286.2	314.4	329.3	318.8	283.2	252.5	228.4	210.9
67.5°	177.7	190.8	210.0	235.2	259.2	267.3	257.7	232.9	206.9	187.6	175.3
70°	153.5	165.9	182.1	201.5	222.3	231.0	221.4	201.8	180.5	162.7	150.7
72.5°	132.5	142.0	155.7	172.3	188.6	197.2	190.7	171.8	153.8	140.6	130.4
75°	100.9	109.1	118.6	130.4	143.1	148.8	143.1	130.0	117.6	107.9	100.5
77.5°	73.4	77.8	85.1	93.9	101.8	106.2	101.3	92.5	84.9	78.2	74.5
80°	55.8	59.0	64.1	71.1	76.5	80.6	77.4	70.1	64.1	59.6	58.0
82.5°	40.6	42.7	46.1	51.3	54.9	57.0	55.6	50.3	47.9	43.9	42.3
85°	20.0	21.3	23.5	25.0	28.2	28.5	28.9	26.7	24.5	23.5	22.2
87.5°	8.0	8.8	10.0	11.3	12.8	13.5	13.5	13.9	13.3	13.3	12.6
90°	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1
92.5°	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7	43.5
95°	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0	81.8
97.5°	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9	128.8
100°	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2	162.7
102.5°	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0	198.6
105°	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3	253.1
107.5°	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3	311.9
110°	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6	351.1



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5	393.4
115°	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7	458.4
117.5°	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7	521.0
120°	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5	563.4
122.5°	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2	606.3
125°	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8	669.4
127.5°	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2	729.7
130°	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4	772.0
132.5°	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2	811.7
135°	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9	871.4
137.5°	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6	929.0
140°	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3	967.0
142.5°	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0	1002.9
145°	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1	1056.9
147.5°	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0	1105.8
150°	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1	1165.7
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3	1206.2
157.5°	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2	1241.9
160°	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1	1263.9
162.5°	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4	1283.6
165°	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3	1309.7
167.5°	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3	1331.7
170°	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1	1343.5
172.5°	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8	1352.3
175°	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3	1362.0
177.5°	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0	1367.3
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	807.1	807.6	809.9	811.7	812.2	814.7	815.0
5°	878.1	883.5	893.9	894.9	896.4	904.7	898.4
7.5°	961.2	974.9	984.0	992.1	995.0	998.6	997.8
10°	1014.5	1034.8	1044.9	1061.1	1061.8	1065.8	1063.3
12.5°	1068.0	1091.6	1110.1	1113.1	1126.7	1128.8	1132.4
15°	1143.9	1169.0	1194.7	1203.9	1222.5	1227.0	1234.0
17.5°	1215.2	1240.8	1258.8	1282.6	1290.3	1300.6	1293.6
20°	1254.3	1282.2	1305.0	1323.7	1331.7	1337.4	1336.8
22.5°	1277.9	1306.0	1324.5	1338.7	1346.1	1348.6	1348.4
25°	1292.7	1308.9	1314.6	1320.0	1311.7	1308.9	1310.1
27.5°	1251.6	1247.3	1232.5	1212.9	1192.6	1176.5	1167.8
30°	1195.0	1170.2	1147.7	1108.4	1088.0	1076.0	1065.2
32.5°	1114.8	1075.5	1032.3	996.2	973.1	955.2	952.5
35°	977.4	918.4	865.4	821.3	798.4	779.1	774.6
37.5°	831.0	769.6	721.9	683.1	658.5	644.9	632.2
40°	733.7	681.1	634.1	601.1	582.4	572.6	564.7
42.5°	658.8	610.7	564.1	538.9	522.0	516.0	511.4
45°	555.5	510.7	478.3	459.3	449.5	439.4	434.6
47.5°	472.6	436.3	414.9	398.8	388.2	382.2	379.1
50°	425.7	395.9	376.8	364.5	355.0	350.2	347.6
52.5°	384.1	359.6	343.6	333.8	327.3	323.8	322.8
55°	330.8	312.2	302.0	293.4	288.7	285.5	284.2
57.5°	287.6	273.2	265.0	257.9	256.1	253.4	252.5
60°	259.2	248.1	241.1	236.4	234.7	231.5	232.2
62.5°	234.1	224.9	219.0	216.3	214.2	211.5	212.4
65°	198.0	191.3	188.1	185.6	183.0	181.5	182.7
67.5°	166.1	161.5	157.2	155.7	154.5	154.3	152.9
70°	145.3	141.5	137.7	136.7	136.7	135.4	135.1
72.5°	125.2	122.5	119.9	119.2	118.2	118.7	117.4
75°	96.8	94.5	93.6	92.6	92.3	92.3	91.4
77.5°	71.5	69.9	68.3	68.3	67.2	66.8	66.6
80°	54.2	53.6	52.3	52.3	51.7	52.0	51.4
82.5°	40.8	39.9	39.6	39.1	38.2	38.3	37.7
85°	21.9	21.0	20.6	19.6	19.0	19.6	19.0
87.5°	13.1	13.1	13.0	12.6	12.5	12.6	11.9
90°	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	350.7	350.3	350.3	351.1	351.7	352.5	353.2



TEST NUMBER: P332764-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)