

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332768-930

Luminaire Tested: **S124DIW-S575D1340U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332768-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1340U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5828.9 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21				
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	42	37	40	35	31	31	28	25	23	21	19	15				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	1.3
10°-20°	210.1	3.6
20°-30°	309.2	5.3
30°-40°	359.5	6.2
40°-50°	359.5	6.2
50°-60°	314.5	5.4
60°-70°	233.5	4.0
70°-80°	132.7	2.3
80°-90°	42.4	0.7
90°-100°	90.2	1.5
100°-110°	267.1	4.6
110°-120°	453.4	7.8
120°-130°	597.8	10.3
130°-140°	671.4	11.5
140°-150°	659.8	11.3
150°-160°	554.9	9.5
160°-170°	369.2	6.3
170°-180°	129.3	2.2
0°-30°	593.9	10.2
0°-40°	953.4	16.4
0°-60°	1627.3	27.9
0°-90°	2035.9	34.9
90°-120°	810.7	13.9
90°-150°	2739.7	47.0
90°-180°	3793.0	65.1
0°-180°	5828.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	3	15	23	29	32	6
95°	63	73	80	83	84	71
105°	246	248	252	255	258	261
115°	461	461	459	458	457	454
125°	671	671	670	668	666	598
135°	866	872	872	870	867	670
145°	1052	1056	1057	1056	1053	658
155°	1205	1205	1204	1208	1204	554
165°	1312	1309	1307	1313	1309	370
175°	1365	1360	1359	1365	1359	130
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.9	14.3	14.7	15.1	15.4	15.8	16.1	16.3	16.6	16.8	17.1
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	22.7	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7
95°	63.4	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0
97.5°	110.8	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9
100°	148.1	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2
102.5°	186.9	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0
105°	246.4	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3
107.5°	308.8	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3
110°	351.1	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6



TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.0	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5
115°	461.0	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7
117.5°	523.2	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7
120°	564.6	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5
122.5°	607.7	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2
125°	671.4	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8
127.5°	729.1	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2
130°	769.7	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4
132.5°	811.2	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2
135°	865.9	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9
137.5°	925.6	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6
140°	965.4	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3
142.5°	1001.8	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0
145°	1052.1	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1102.0	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0
150°	1132.5	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.1	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3
157.5°	1242.6	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2
160°	1264.6	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1
162.5°	1284.9	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4
165°	1312.1	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3
167.5°	1333.1	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3
170°	1344.9	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1
172.5°	1353.4	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8
175°	1365.1	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3
177.5°	1368.8	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	17.4	17.7	17.9	18.2	18.3	18.3	18.4	18.5
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	43.5	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	81.8	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	128.8	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	162.7	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	198.6	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.1	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	311.9	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	351.1	350.7	350.3	350.3	351.1	351.7	352.5	353.2





TEST NUMBER: P332768-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	393.4	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.4	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	521.0	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	563.4	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	606.3	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.4	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.7	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	772.0	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.7	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	871.4	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	929.0	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	967.0	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.9	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.8	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1165.7	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1241.9	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1263.9	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1283.6	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1309.7	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1331.7	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1343.5	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1352.3	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1367.3	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)