

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769-930

Luminaire Tested: **S124DIW-S575D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332769-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1560U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7202.4 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6181	6181	6181	6181
5°	7280	6198	5471	6198
10°	8716	6171	4925	6171
15°	10313	6108	4523	6108
20°	11485	6045	4164	6045
25°	11670	5951	3917	5951
30°	9930	5862	3838	5862
35°	7634	5714	3840	5714
40°	5951	5542	3911	5542
45°	4962	5284	3976	5284
50°	4366	4968	4111	4968
55°	4000	4590	4277	4590
60°	3749	4251	4477	4251
65°	3490	3872	4642	3872
70°	3189	3496	4747	3496
75°	2851	3079	4688	3079
80°	2390	2520	4542	2520
85°	1760	1815	4353	1815



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	1.0
10°-20°	230.0	3.2
20°-30°	364.6	5.1
30°-40°	405.8	5.6
40°-50°	369.4	5.1
50°-60°	301.9	4.2
60°-70°	215.5	3.0
70°-80°	118.7	1.6
80°-90°	37.1	0.5
90°-100°	56.2	0.8
100°-110°	358.5	5.0
110°-120°	685.8	9.5
120°-130°	870.5	12.1
130°-140°	931.4	12.9
140°-150°	871.0	12.1
150°-160°	702.4	9.8
160°-170°	453.0	6.3
170°-180°	156.1	2.2
0°-30°	669.2	9.3
0°-40°	1075.0	14.9
0°-60°	1746.2	24.2
0°-90°	2117.5	29.4
90°-120°	1100.5	15.3
90°-150°	3773.4	52.4
90°-180°	5085.0	70.6
0°-180°	7202.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	766	766	766	766	766	
5°	898	765	675	765	898	91
15°	1234	731	541	731	1234	349
25°	1310	668	440	668	1310	578
35°	775	580	390	580	775	492
45°	435	463	348	463	435	342
55°	284	326	304	326	284	257
65°	183	203	243	203	183	181
75°	91	99	150	99	91	97
85°	19	20	47	20	19	24
90°	37	4	37	4	37	17
95°	36	68	36	68	36	28
105°	350	370	350	370	350	306
115°	696	691	696	691	696	689
125°	979	971	979	971	979	872
135°	1214	1205	1214	1205	1214	934
145°	1397	1389	1397	1389	1397	873
155°	1522	1523	1522	1523	1522	702
165°	1600	1607	1600	1607	1600	452
175°	1634	1644	1634	1644	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	815.0	814.7	812.2	811.7	809.9	807.6	807.1	803.1	794.9	791.2	790.1
5°	898.4	904.7	896.4	894.9	893.9	883.5	878.1	871.7	857.1	848.6	841.9
7.5°	997.8	998.6	995.0	992.1	984.0	974.9	961.2	946.6	929.2	911.1	897.5
10°	1063.3	1065.8	1061.8	1061.1	1044.9	1034.8	1014.5	997.4	977.6	955.8	935.8
12.5°	1132.4	1128.8	1126.7	1113.1	1110.1	1091.6	1068.0	1050.4	1020.0	994.8	968.2
15°	1234.0	1227.0	1222.5	1203.9	1194.7	1169.0	1143.9	1124.5	1084.9	1047.2	1018.6
17.5°	1293.6	1300.6	1290.3	1282.6	1258.8	1240.8	1215.2	1174.6	1143.5	1096.7	1060.6
20°	1336.8	1337.4	1331.7	1323.7	1305.0	1282.2	1254.3	1209.9	1172.7	1126.1	1076.6
22.5°	1348.4	1348.6	1346.1	1338.7	1324.5	1306.0	1277.9	1240.8	1195.9	1145.2	1095.7
25°	1310.1	1308.9	1311.7	1320.0	1314.6	1308.9	1292.7	1265.1	1223.2	1169.5	1116.3
27.5°	1167.8	1176.5	1192.6	1212.9	1232.5	1247.3	1251.6	1245.9	1219.9	1175.8	1120.1
30°	1065.2	1076.0	1088.0	1108.4	1147.7	1170.2	1195.0	1213.7	1203.2	1168.0	1116.0
32.5°	952.5	955.2	973.1	996.2	1032.3	1075.5	1114.8	1152.8	1165.4	1147.0	1103.5
35°	774.6	779.1	798.4	821.3	865.4	918.4	977.4	1030.0	1073.5	1091.0	1068.7
37.5°	632.2	644.9	658.5	683.1	721.9	769.6	831.0	899.0	963.8	1007.2	1014.6
40°	564.7	572.6	582.4	601.1	634.1	681.1	733.7	811.8	880.6	942.8	963.1
42.5°	511.4	516.0	522.0	538.9	564.1	610.7	658.8	727.5	796.6	871.0	905.0
45°	434.6	439.4	449.5	459.3	478.3	510.7	555.5	611.9	681.3	753.1	815.9
47.5°	379.1	382.2	388.2	398.8	414.9	436.3	472.6	519.8	584.2	653.8	720.7
50°	347.6	350.2	355.0	364.5	376.8	395.9	425.7	469.8	520.2	590.4	656.0
52.5°	322.8	323.8	327.3	333.8	343.6	359.6	384.1	420.5	467.5	529.9	595.3
55°	284.2	285.5	288.7	293.4	302.0	312.2	330.8	358.2	399.1	453.3	510.1
57.5°	252.5	253.4	256.1	257.9	265.0	273.2	287.6	307.0	338.1	384.1	434.8
60°	232.2	231.5	234.7	236.4	241.1	248.1	259.2	277.9	304.8	341.9	388.6
62.5°	212.4	211.5	214.2	216.3	219.0	224.9	234.1	248.7	270.6	304.2	344.5
65°	182.7	181.5	183.0	185.6	188.1	191.3	198.0	210.9	228.4	252.5	283.2
67.5°	152.9	154.3	154.5	155.7	157.2	161.5	166.1	175.3	187.6	206.9	232.9
70°	135.1	135.4	136.7	136.7	137.7	141.5	145.3	150.7	162.7	180.5	201.8
72.5°	117.4	118.7	118.2	119.2	119.9	122.5	125.2	130.4	140.6	153.8	171.8
75°	91.4	92.3	92.3	92.6	93.6	94.5	96.8	100.5	107.9	117.6	130.0
77.5°	66.6	66.8	67.2	68.3	68.3	69.9	71.5	74.5	78.2	84.9	92.5
80°	51.4	52.0	51.7	52.3	52.3	53.6	54.2	58.0	59.6	64.1	70.1
82.5°	37.7	38.3	38.2	39.1	39.6	39.9	40.8	42.3	43.9	47.9	50.3
85°	19.0	19.6	19.0	19.6	20.6	21.0	21.9	22.2	23.5	24.5	26.7
87.5°	13.0	13.6	13.5	13.6	14.0	14.1	14.0	13.5	14.1	14.0	14.6
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4	27.7	26.1	23.9
95°	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3	28.7	27.1	26.7
97.5°	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8	32.6	32.4	62.9
100°	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8	49.5	54.1	91.8
102.5°	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5	210.5	260.7	265.5
105°	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5	386.0	383.6	382.2
107.5°	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7	479.5	478.3	476.4
110°	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3	542.7	542.2	540.5



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0	604.1	604.2	603.4
115°	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6	694.0	693.4	693.7
117.5°	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7	785.8	785.9	785.3
120°	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0	841.2
122.5°	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7	897.4	897.1	896.7
125°	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4	974.6	973.8	974.3
127.5°	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6	1052.8	1053.0	1051.7
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8	1099.4	1099.2	1098.4
132.5°	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0	1145.7	1145.4	1144.4
135°	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7	1209.2	1208.6	1207.5
137.5°	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8	1270.2	1269.6	1268.4
140°	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6	1307.8	1306.9	1306.4
142.5°	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6	1343.0	1342.4	1342.1
145°	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6	1393.3	1393.0	1393.0
147.5°	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5	1437.3	1437.0	1437.3
150°	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6	1465.6	1465.6	1465.8
152.5°	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0	1489.6	1489.1	1489.6
155°	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1	1522.0	1520.9	1521.8
157.5°	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7	1549.6
160°	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4	1566.7
162.5°	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5	1582.7	1581.1	1581.4
165°	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2	1603.0	1600.8	1600.8
167.5°	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4	1618.0	1615.6	1615.8
170°	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8	1627.6	1625.4	1625.1
172.5°	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7	1633.5	1631.3	1631.0
175°	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6	1640.1	1637.7	1637.4
177.5°	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4	1643.6	1641.8	1641.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	790.4	786.8	784.3	782.3	776.7	773.4	770.9	767.3	763.2	758.9	753.6
5°	835.3	824.4	816.5	804.5	793.0	783.5	773.7	764.8	754.0	742.3	733.7
7.5°	882.4	866.3	845.8	827.9	807.9	790.4	774.9	758.9	742.2	726.1	711.3
10°	912.3	891.7	868.9	841.9	816.5	794.0	773.1	752.8	733.1	713.4	696.6
12.5°	944.5	918.8	885.1	853.5	825.2	795.0	769.7	744.9	721.1	700.5	680.9
15°	987.8	950.7	911.7	869.5	832.1	796.9	762.3	730.8	704.3	676.9	657.9
17.5°	1014.4	968.5	923.9	879.8	834.5	790.0	752.8	716.6	683.1	656.1	632.1
20°	1031.9	986.3	930.7	886.6	832.7	787.0	743.9	703.6	668.7	639.8	615.1
22.5°	1047.2	994.3	938.8	880.8	827.1	778.6	731.4	690.9	655.3	624.8	601.1
25°	1055.4	994.8	934.5	876.8	815.9	758.5	715.7	668.1	630.0	597.9	572.6
27.5°	1056.3	991.5	923.3	859.2	796.3	742.8	688.8	646.2	606.7	572.8	548.5
30°	1053.4	985.9	912.6	843.2	780.1	721.9	675.1	628.8	588.4	554.8	529.5
32.5°	1044.6	974.2	898.9	825.4	760.0	703.2	654.8	610.7	571.4	538.3	511.7
35°	1018.9	949.4	869.2	792.7	725.8	668.4	624.6	579.8	540.5	509.2	483.5
37.5°	978.8	915.9	834.4	755.2	689.5	631.9	588.4	548.0	512.6	480.6	454.3
40°	943.7	888.5	806.7	729.6	658.5	603.6	563.0	525.9	490.7	460.6	435.5
42.5°	903.4	855.2	779.8	698.1	629.6	574.5	534.9	501.6	468.4	440.6	415.5
45°	831.4	799.7	728.6	653.1	581.8	529.8	492.0	462.8	434.9	407.6	386.7
47.5°	748.7	733.0	673.1	601.4	533.7	482.4	449.7	422.7	398.3	375.1	356.7
50°	693.1	685.5	633.8	564.7	499.9	451.8	418.7	395.6	374.6	354.3	336.9
52.5°	638.3	638.1	591.4	528.1	468.2	421.8	389.1	367.4	349.3	332.7	317.1
55°	554.5	563.4	526.9	470.4	416.9	375.0	345.4	326.1	313.4	299.8	288.0
57.5°	477.5	492.3	462.2	412.5	367.7	329.1	303.5	288.9	275.4	267.2	258.6
60°	427.3	441.2	417.8	375.9	333.7	300.7	276.3	263.3	251.5	245.8	239.8
62.5°	382.6	395.1	377.6	338.8	302.2	270.5	249.9	237.4	229.5	223.2	219.2
65°	318.8	329.3	314.4	286.2	254.7	229.3	212.5	202.7	195.1	192.6	188.1
67.5°	257.7	267.3	259.2	235.2	210.0	190.8	177.7	168.2	163.7	161.4	158.3
70°	221.4	231.0	222.3	201.5	182.1	165.9	153.5	148.1	143.4	142.4	138.0
72.5°	190.7	197.2	188.6	172.3	155.7	142.0	132.5	126.9	124.3	122.6	120.3
75°	143.1	148.8	143.1	130.4	118.6	109.1	100.9	98.7	95.8	94.8	93.3
77.5°	101.3	106.2	101.8	93.9	85.1	77.8	73.4	70.5	69.9	68.2	69.0
80°	77.4	80.6	76.5	71.1	64.1	59.0	55.8	54.2	52.3	51.7	53.0
82.5°	55.6	57.0	54.9	51.3	46.1	42.7	40.6	38.7	38.4	38.5	38.5
85°	28.9	28.5	28.2	25.0	23.5	21.3	20.0	19.6	19.3	20.0	20.6
87.5°	14.2	14.0	13.3	11.7	10.4	9.0	8.2	7.3	8.2	9.0	9.9
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5	15.7	15.8	16.0
95°	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6	58.3	49.1	39.8
97.5°	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6	149.4	155.2	161.0
100°	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6	206.6	211.5	216.4
102.5°	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5	270.2	273.8	277.4
105°	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1	371.7	373.3	375.0
107.5°	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2	467.1	467.9	468.7
110°	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2	532.0	532.8	533.6





TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1	595.6	597.0	598.5
115°	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0	691.8	692.6	693.4
117.5°	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3	779.3	780.5	781.5
120°	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3	838.4	839.5	840.6
122.5°	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3	893.0	893.6	894.3
125°	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3	972.4	973.5	974.6
127.5°	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0	1046.4	1046.6	1046.8
130°	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3	1094.5	1094.8	1095.1
132.5°	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5	1139.0	1139.5	1140.0
135°	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9	1204.6	1204.4	1204.1
137.5°	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7	1263.8	1263.9	1264.0
140°	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0	1302.6	1303.2	1303.7
142.5°	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5
145°	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4	1390.2	1391.0	1391.8
147.5°	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4	1432.9	1434.4	1436.0
150°	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9	1463.0	1464.0	1465.2
152.5°	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4	1488.3	1489.2	1490.0
155°	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4	1523.6	1523.9	1524.2
157.5°	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6	1553.5	1553.3	1553.1
160°	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3	1570.5	1569.7	1568.9
162.5°	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1	1586.0	1584.9	1584.0
165°	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0	1605.6	1604.3	1602.9
167.5°	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7	1621.3	1619.8	1618.5
170°	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6	1629.9	1628.2	1626.6
172.5°	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4	1635.8	1634.2	1632.6
175°	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8	1642.2	1640.5	1638.9
177.5°	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8	1645.3	1643.7	1642.2
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	751.1	748.8	745.4	740.9	737.1	733.0	732.0	730.5	733.5	731.0	730.3
5°	726.4	719.7	711.2	701.4	695.7	687.4	685.8	682.7	679.5	679.1	676.0
7.5°	700.3	690.6	679.4	669.4	660.1	651.1	645.1	643.9	639.2	636.5	633.3
10°	683.6	671.6	658.5	649.1	638.2	628.8	622.1	618.2	615.1	611.6	608.5
12.5°	663.8	651.0	640.3	630.0	617.2	609.9	599.0	592.4	591.7	591.8	583.6
15°	640.7	628.1	611.6	597.0	590.0	576.1	570.1	562.4	557.7	552.9	549.1
17.5°	614.5	598.7	585.8	569.0	555.7	544.6	536.6	532.1	525.0	518.2	513.3
20°	597.9	581.1	567.5	549.8	535.2	521.5	514.9	508.5	503.1	497.4	492.0
22.5°	581.2	563.6	547.0	529.7	516.1	501.7	495.3	486.7	481.5	478.3	473.0
25°	554.8	535.8	516.7	500.3	486.3	473.6	465.0	458.4	452.7	450.1	446.6
27.5°	526.1	507.2	488.9	470.1	454.3	445.1	438.2	433.2	429.9	426.6	424.9
30°	507.8	488.2	468.6	451.1	436.5	427.3	420.9	417.4	414.9	413.4	411.7
32.5°	489.3	469.9	449.2	433.3	420.3	412.1	407.2	403.7	402.5	401.9	401.4
35°	459.7	440.0	420.9	406.7	394.3	391.1	387.0	385.1	384.5	386.7	387.7
37.5°	430.9	412.6	395.1	381.3	373.2	368.5	367.1	367.2	369.5	371.5	373.7
40°	412.4	394.6	378.1	366.1	358.5	355.6	355.0	356.5	359.1	361.3	363.9
42.5°	394.4	376.8	361.9	350.6	345.3	342.7	343.1	344.6	348.2	350.9	354.7
45°	366.4	351.8	337.2	328.0	323.6	324.2	324.2	327.0	330.5	334.7	338.8
47.5°	340.1	325.3	313.3	305.6	303.3	302.7	304.5	308.3	313.3	318.4	324.2
50°	322.3	308.3	297.8	290.9	288.4	289.3	291.9	295.3	301.3	307.7	313.7
52.5°	304.3	291.6	281.8	275.4	273.6	275.3	277.9	283.4	288.7	295.5	302.8
55°	276.3	265.5	257.9	253.2	252.5	253.5	256.3	262.4	269.9	278.5	285.5
57.5°	248.4	239.5	232.4	229.2	229.5	230.4	235.1	242.2	250.4	259.5	268.5
60°	229.7	221.4	215.7	213.2	213.5	215.4	221.1	227.8	237.9	246.8	256.3
62.5°	211.9	204.6	199.2	196.9	196.5	200.6	206.1	213.0	223.2	233.1	243.4
65°	183.4	177.7	173.2	171.9	172.8	176.0	183.0	192.2	200.8	211.2	222.1
67.5°	155.4	150.7	147.7	148.3	149.4	154.1	160.0	167.9	177.6	188.4	199.1
70°	137.7	133.2	130.7	131.0	132.9	138.6	143.7	151.6	162.1	173.2	182.1
72.5°	119.4	116.5	114.2	115.5	117.4	121.4	127.7	135.7	144.9	155.2	164.6
75°	91.6	91.6	90.4	91.4	94.2	98.0	102.8	111.0	120.3	128.5	136.1
77.5°	68.0	67.3	68.2	69.3	70.9	75.4	80.9	86.8	93.7	102.0	108.3
80°	52.0	52.3	53.9	55.8	56.5	59.9	65.6	71.1	76.5	83.4	89.4
82.5°	39.1	39.4	40.2	42.6	43.3	47.0	50.7	56.1	61.0	65.6	70.7
85°	21.3	21.3	22.8	23.8	25.4	27.9	30.2	33.3	37.7	40.9	45.7
87.5°	11.3	11.8	13.2	14.2	15.4	17.1	17.9	21.0	22.4	24.0	26.5
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4	31.0	32.6	33.5
95°	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3	32.0	33.6	34.6
97.5°	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8	32.9	33.1	33.3
100°	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8	40.2	35.5	33.3
102.5°	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5	110.3	60.3	35.2
105°	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5	391.0	393.5	389.7
107.5°	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7	481.9	483.1	484.2
110°	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3	543.9	544.4	545.1



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0	603.8	603.7	604.2
115°	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6	695.0	695.6	695.9
117.5°	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7	785.5	785.5	785.4
120°	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0	842.6	843.2	843.2
122.5°	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7	898.1	898.4	898.2
125°	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4	976.2	977.1	977.6
127.5°	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6	1052.5	1052.3	1052.1
130°	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8	1100.0	1100.2	1100.4
132.5°	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0	1146.2	1146.5	1146.6
135°	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7	1210.2	1210.8	1211.4
137.5°	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8	1271.4	1272.0	1272.2
140°	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6	1309.5	1310.3	1310.8
142.5°	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6	1344.2	1344.8	1345.1
145°	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6	1393.8	1394.1	1394.6
147.5°	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5	1437.7	1437.9	1438.2
150°	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6	1465.6	1465.6	1465.7
152.5°	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0	1490.4	1490.9	1491.0
155°	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1	1524.2	1525.3	1525.4
157.5°	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4
160°	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0
162.5°	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5	1586.1	1587.7	1587.6
165°	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2	1607.4	1609.6	1609.4
167.5°	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4	1622.8	1625.2	1625.1
170°	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8	1632.0	1634.2	1633.9
172.5°	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7	1637.9	1640.1	1639.6
175°	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6	1645.1	1647.6	1647.1
177.5°	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4	1647.1	1648.9	1648.5
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	729.7	729.2	727.4	727.2	727.4	729.2	729.7	730.3	731.0	733.5	730.5
5°	674.1	672.5	671.6	675.1	671.6	672.5	674.1	676.0	679.1	679.5	682.7
7.5°	632.2	630.9	628.1	627.2	628.1	630.9	632.2	633.3	636.5	639.2	643.9
10°	605.3	604.0	601.4	600.8	601.4	604.0	605.3	608.5	611.6	615.1	618.2
12.5°	579.4	576.8	576.3	577.0	576.3	576.8	579.4	583.6	591.8	591.7	592.4
15°	544.9	543.7	540.2	541.2	540.2	543.7	544.9	549.1	552.9	557.7	562.4
17.5°	511.1	509.6	505.3	509.1	505.3	509.6	511.1	513.3	518.2	525.0	532.1
20°	489.8	487.2	485.0	484.7	485.0	487.2	489.8	492.0	497.4	503.1	508.5
22.5°	469.4	467.2	467.0	464.9	467.0	467.2	469.4	473.0	478.3	481.5	486.7
25°	444.1	441.9	441.2	439.7	441.2	441.9	444.1	446.6	450.1	452.7	458.4
27.5°	424.6	423.5	422.4	422.9	422.4	423.5	424.6	424.9	426.6	429.9	433.2
30°	412.7	412.4	411.7	411.7	411.7	412.4	412.7	411.7	413.4	414.9	417.4
32.5°	402.8	402.8	403.1	403.1	403.1	402.8	402.8	401.4	401.9	402.5	403.7
35°	388.9	389.9	390.5	389.6	390.5	389.9	388.9	387.7	386.7	384.5	385.1
37.5°	376.3	377.3	378.2	379.3	378.2	377.3	376.3	373.7	371.5	369.5	367.2
40°	366.7	368.9	369.6	371.1	369.6	368.9	366.7	363.9	361.3	359.1	356.5
42.5°	357.6	360.0	361.7	362.0	361.7	360.0	357.6	354.7	350.9	348.2	344.6
45°	343.6	346.1	348.3	348.3	348.3	346.1	343.6	338.8	334.7	330.5	327.0
47.5°	329.1	332.7	334.9	335.5	334.9	332.7	329.1	324.2	318.4	313.3	308.3
50°	319.1	323.6	325.8	327.3	325.8	323.6	319.1	313.7	307.7	301.3	295.3
52.5°	309.5	313.9	316.9	317.7	316.9	313.9	309.5	302.8	295.5	288.7	283.4
55°	292.8	299.1	302.6	303.9	302.6	299.1	292.8	285.5	278.5	269.9	262.4
57.5°	277.0	282.9	287.0	287.9	287.0	282.9	277.0	268.5	259.5	250.4	242.2
60°	264.9	271.3	276.3	277.3	276.3	271.3	264.9	256.3	246.8	237.9	227.8
62.5°	252.4	259.0	263.6	266.1	263.6	259.0	252.4	243.4	233.1	223.2	213.0
65°	231.0	237.6	242.1	243.0	242.1	237.6	231.0	222.1	211.2	200.8	192.2
67.5°	207.5	214.1	217.0	218.9	217.0	214.1	207.5	199.1	188.4	177.6	167.9
70°	190.9	196.3	199.5	201.1	199.5	196.3	190.9	182.1	173.2	162.1	151.6
72.5°	172.2	177.8	181.5	181.8	181.5	177.8	172.2	164.6	155.2	144.9	135.7
75°	143.4	148.5	150.3	150.3	150.3	148.5	143.4	136.1	128.5	120.3	111.0
77.5°	113.5	116.1	118.5	119.0	118.5	116.1	113.5	108.3	102.0	93.7	86.8
80°	94.2	95.8	97.7	97.7	97.7	95.8	94.2	89.4	83.4	76.5	71.1
82.5°	74.4	75.7	77.6	77.4	77.6	75.7	74.4	70.7	65.6	61.0	56.1
85°	45.0	47.9	47.6	47.0	47.6	47.9	45.0	45.7	40.9	37.7	33.3
87.5°	27.3	27.7	28.6	29.2	28.6	27.7	27.3	26.5	24.0	22.4	21.0
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	33.6	33.8	33.8	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4
95°	34.8	35.1	35.4	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3
97.5°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8
100°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8
102.5°	35.2	35.3	35.4	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5
105°	379.9	370.1	360.3	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5
107.5°	485.3	486.2	487.3	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7
110°	545.9	546.7	547.6	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	605.3	606.3	607.3	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0
115°	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6
117.5°	785.2	785.1	785.1	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7
120°	842.6	842.0	841.6	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0
122.5°	897.7	897.2	896.6	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7
125°	977.9	978.1	978.4	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4
127.5°	1051.9	1051.7	1051.4	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8
132.5°	1146.3	1146.1	1145.9	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0
135°	1211.9	1212.4	1213.0	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7
137.5°	1272.0	1271.9	1271.7	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8
140°	1311.1	1311.3	1311.6	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6
142.5°	1345.2	1345.2	1345.2	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6
145°	1395.1	1395.6	1396.2	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6
147.5°	1438.4	1438.7	1439.0	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5
150°	1466.0	1466.2	1466.6	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6
152.5°	1490.9	1490.7	1490.5	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0
155°	1524.6	1523.8	1523.0	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1
157.5°	1553.0	1551.5	1550.1	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5
160°	1571.3	1569.7	1568.1	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7
162.5°	1585.8	1583.9	1582.0	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5
165°	1607.0	1604.5	1602.1	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2
167.5°	1622.3	1619.6	1616.8	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4
170°	1631.2	1628.4	1625.7	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8
172.5°	1636.7	1633.8	1630.8	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7
175°	1643.8	1640.5	1637.3	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6
177.5°	1645.8	1643.2	1640.5	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	732.0	733.0	737.1	740.9	745.4	748.8	751.1	753.6	758.9	763.2	767.3
5°	685.8	687.4	695.7	701.4	711.2	719.7	726.4	733.7	742.3	754.0	764.8
7.5°	645.1	651.1	660.1	669.4	679.4	690.6	700.3	711.3	726.1	742.2	758.9
10°	622.1	628.8	638.2	649.1	658.5	671.6	683.6	696.6	713.4	733.1	752.8
12.5°	599.0	609.9	617.2	630.0	640.3	651.0	663.8	680.9	700.5	721.1	744.9
15°	570.1	576.1	590.0	597.0	611.6	628.1	640.7	657.9	676.9	704.3	730.8
17.5°	536.6	544.6	555.7	569.0	585.8	598.7	614.5	632.1	656.1	683.1	716.6
20°	514.9	521.5	535.2	549.8	567.5	581.1	597.9	615.1	639.8	668.7	703.6
22.5°	495.3	501.7	516.1	529.7	547.0	563.6	581.2	601.1	624.8	655.3	690.9
25°	465.0	473.6	486.3	500.3	516.7	535.8	554.8	572.6	597.9	630.0	668.1
27.5°	438.2	445.1	454.3	470.1	488.9	507.2	526.1	548.5	572.8	606.7	646.2
30°	420.9	427.3	436.5	451.1	468.6	488.2	507.8	529.5	554.8	588.4	628.8
32.5°	407.2	412.1	420.3	433.3	449.2	469.9	489.3	511.7	538.3	571.4	610.7
35°	387.0	391.1	394.3	406.7	420.9	440.0	459.7	483.5	509.2	540.5	579.8
37.5°	367.1	368.5	373.2	381.3	395.1	412.6	430.9	454.3	480.6	512.6	548.0
40°	355.0	355.6	358.5	366.1	378.1	394.6	412.4	435.5	460.6	490.7	525.9
42.5°	343.1	342.7	345.3	350.6	361.9	376.8	394.4	415.5	440.6	468.4	501.6
45°	324.2	324.2	323.6	328.0	337.2	351.8	366.4	386.7	407.6	434.9	462.8
47.5°	304.5	302.7	303.3	305.6	313.3	325.3	340.1	356.7	375.1	398.3	422.7
50°	291.9	289.3	288.4	290.9	297.8	308.3	322.3	336.9	354.3	374.6	395.6
52.5°	277.9	275.3	273.6	275.4	281.8	291.6	304.3	317.1	332.7	349.3	367.4
55°	256.3	253.5	252.5	253.2	257.9	265.5	276.3	288.0	299.8	313.4	326.1
57.5°	235.1	230.4	229.5	229.2	232.4	239.5	248.4	258.6	267.2	275.4	288.9
60°	221.1	215.4	213.5	213.2	215.7	221.4	229.7	239.8	245.8	251.5	263.3
62.5°	206.1	200.6	196.5	196.9	199.2	204.6	211.9	219.2	223.2	229.5	237.4
65°	183.0	176.0	172.8	171.9	173.2	177.7	183.4	188.1	192.6	195.1	202.7
67.5°	160.0	154.1	149.4	148.3	147.7	150.7	155.4	158.3	161.4	163.7	168.2
70°	143.7	138.6	132.9	131.0	130.7	133.2	137.7	138.0	142.4	143.4	148.1
72.5°	127.7	121.4	117.4	115.5	114.2	116.5	119.4	120.3	122.6	124.3	126.9
75°	102.8	98.0	94.2	91.4	90.4	91.6	91.6	93.3	94.8	95.8	98.7
77.5°	80.9	75.4	70.9	69.3	68.2	67.3	68.0	69.0	68.2	69.9	70.5
80°	65.6	59.9	56.5	55.8	53.9	52.3	52.0	53.0	51.7	52.3	54.2
82.5°	50.7	47.0	43.3	42.6	40.2	39.4	39.1	38.5	38.5	38.4	38.7
85°	30.2	27.9	25.4	23.8	22.8	21.3	21.3	20.6	20.0	19.3	19.6
87.5°	17.9	17.1	15.4	14.2	13.2	11.8	11.3	9.9	9.0	8.2	7.3
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	27.7	26.1	23.9	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5
95°	28.7	27.1	26.7	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6
97.5°	32.6	32.4	62.9	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6
100°	49.5	54.1	91.8	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6
102.5°	210.5	260.7	265.5	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5
105°	386.0	383.6	382.2	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1
107.5°	479.5	478.3	476.4	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2
110°	542.7	542.2	540.5	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	604.1	604.2	603.4	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1
115°	694.0	693.4	693.7	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0
117.5°	785.8	785.9	785.3	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3
120°	841.6	841.0	841.2	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3
122.5°	897.4	897.1	896.7	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3
125°	974.6	973.8	974.3	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3
127.5°	1052.8	1053.0	1051.7	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0
130°	1099.4	1099.2	1098.4	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3
132.5°	1145.7	1145.4	1144.4	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5
135°	1209.2	1208.6	1207.5	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9
137.5°	1270.2	1269.6	1268.4	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7
140°	1307.8	1306.9	1306.4	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0
142.5°	1343.0	1342.4	1342.1	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4
145°	1393.3	1393.0	1393.0	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4
147.5°	1437.3	1437.0	1437.3	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4
150°	1465.6	1465.6	1465.8	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9
152.5°	1489.6	1489.1	1489.6	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4
155°	1522.0	1520.9	1521.8	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4
157.5°	1550.1	1548.7	1549.6	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6
160°	1568.1	1566.4	1566.7	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3
162.5°	1582.7	1581.1	1581.4	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1
165°	1603.0	1600.8	1600.8	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0
167.5°	1618.0	1615.6	1615.8	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7
170°	1627.6	1625.4	1625.1	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6
172.5°	1633.5	1631.3	1631.0	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4
175°	1640.1	1637.7	1637.4	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8
177.5°	1643.6	1641.8	1641.4	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	770.9	773.4	776.7	782.3	784.3	786.8	790.4	790.1	791.2	794.9	803.1
5°	773.7	783.5	793.0	804.5	816.5	824.4	835.3	841.9	848.6	857.1	871.7
7.5°	774.9	790.4	807.9	827.9	845.8	866.3	882.4	897.5	911.1	929.2	946.6
10°	773.1	794.0	816.5	841.9	868.9	891.7	912.3	935.8	955.8	977.6	997.4
12.5°	769.7	795.0	825.2	853.5	885.1	918.8	944.5	968.2	994.8	1020.0	1050.4
15°	762.3	796.9	832.1	869.5	911.7	950.7	987.8	1018.6	1047.2	1084.9	1124.5
17.5°	752.8	790.0	834.5	879.8	923.9	968.5	1014.4	1060.6	1096.7	1143.5	1174.6
20°	743.9	787.0	832.7	886.6	930.7	986.3	1031.9	1076.6	1126.1	1172.7	1209.9
22.5°	731.4	778.6	827.1	880.8	938.8	994.3	1047.2	1095.7	1145.2	1195.9	1240.8
25°	715.7	758.5	815.9	876.8	934.5	994.8	1055.4	1116.3	1169.5	1223.2	1265.1
27.5°	688.8	742.8	796.3	859.2	923.3	991.5	1056.3	1120.1	1175.8	1219.9	1245.9
30°	675.1	721.9	780.1	843.2	912.6	985.9	1053.4	1116.0	1168.0	1203.2	1213.7
32.5°	654.8	703.2	760.0	825.4	898.9	974.2	1044.6	1103.5	1147.0	1165.4	1152.8
35°	624.6	668.4	725.8	792.7	869.2	949.4	1018.9	1068.7	1091.0	1073.5	1030.0
37.5°	588.4	631.9	689.5	755.2	834.4	915.9	978.8	1014.6	1007.2	963.8	899.0
40°	563.0	603.6	658.5	729.6	806.7	888.5	943.7	963.1	942.8	880.6	811.8
42.5°	534.9	574.5	629.6	698.1	779.8	855.2	903.4	905.0	871.0	796.6	727.5
45°	492.0	529.8	581.8	653.1	728.6	799.7	831.4	815.9	753.1	681.3	611.9
47.5°	449.7	482.4	533.7	601.4	673.1	733.0	748.7	720.7	653.8	584.2	519.8
50°	418.7	451.8	499.9	564.7	633.8	685.5	693.1	656.0	590.4	520.2	469.8
52.5°	389.1	421.8	468.2	528.1	591.4	638.1	638.3	595.3	529.9	467.5	420.5
55°	345.4	375.0	416.9	470.4	526.9	563.4	554.5	510.1	453.3	399.1	358.2
57.5°	303.5	329.1	367.7	412.5	462.2	492.3	477.5	434.8	384.1	338.1	307.0
60°	276.3	300.7	333.7	375.9	417.8	441.2	427.3	388.6	341.9	304.8	277.9
62.5°	249.9	270.5	302.2	338.8	377.6	395.1	382.6	344.5	304.2	270.6	248.7
65°	212.5	229.3	254.7	286.2	314.4	329.3	318.8	283.2	252.5	228.4	210.9
67.5°	177.7	190.8	210.0	235.2	259.2	267.3	257.7	232.9	206.9	187.6	175.3
70°	153.5	165.9	182.1	201.5	222.3	231.0	221.4	201.8	180.5	162.7	150.7
72.5°	132.5	142.0	155.7	172.3	188.6	197.2	190.7	171.8	153.8	140.6	130.4
75°	100.9	109.1	118.6	130.4	143.1	148.8	143.1	130.0	117.6	107.9	100.5
77.5°	73.4	77.8	85.1	93.9	101.8	106.2	101.3	92.5	84.9	78.2	74.5
80°	55.8	59.0	64.1	71.1	76.5	80.6	77.4	70.1	64.1	59.6	58.0
82.5°	40.6	42.7	46.1	51.3	54.9	57.0	55.6	50.3	47.9	43.9	42.3
85°	20.0	21.3	23.5	25.0	28.2	28.5	28.9	26.7	24.5	23.5	22.2
87.5°	8.2	9.0	10.4	11.7	13.3	14.0	14.2	14.6	14.0	14.1	13.5
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4
95°	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3
97.5°	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8
100°	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8
102.5°	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5
105°	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5
107.5°	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7
110°	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3





TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0
115°	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6
117.5°	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7
120°	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0
122.5°	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7
125°	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4
127.5°	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6
130°	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8
132.5°	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0
135°	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7
137.5°	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8
140°	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6
142.5°	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6
145°	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6
147.5°	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5
150°	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6
152.5°	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0
155°	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1
157.5°	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5
160°	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7
162.5°	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5
165°	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2
167.5°	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4
170°	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8
172.5°	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7
175°	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6
177.5°	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	765.7	765.7	765.7	765.7	765.7	765.7	765.7
2.5°	807.1	807.6	809.9	811.7	812.2	814.7	815.0
5°	878.1	883.5	893.9	894.9	896.4	904.7	898.4
7.5°	961.2	974.9	984.0	992.1	995.0	998.6	997.8
10°	1014.5	1034.8	1044.9	1061.1	1061.8	1065.8	1063.3
12.5°	1068.0	1091.6	1110.1	1113.1	1126.7	1128.8	1132.4
15°	1143.9	1169.0	1194.7	1203.9	1222.5	1227.0	1234.0
17.5°	1215.2	1240.8	1258.8	1282.6	1290.3	1300.6	1293.6
20°	1254.3	1282.2	1305.0	1323.7	1331.7	1337.4	1336.8
22.5°	1277.9	1306.0	1324.5	1338.7	1346.1	1348.6	1348.4
25°	1292.7	1308.9	1314.6	1320.0	1311.7	1308.9	1310.1
27.5°	1251.6	1247.3	1232.5	1212.9	1192.6	1176.5	1167.8
30°	1195.0	1170.2	1147.7	1108.4	1088.0	1076.0	1065.2
32.5°	1114.8	1075.5	1032.3	996.2	973.1	955.2	952.5
35°	977.4	918.4	865.4	821.3	798.4	779.1	774.6
37.5°	831.0	769.6	721.9	683.1	658.5	644.9	632.2
40°	733.7	681.1	634.1	601.1	582.4	572.6	564.7
42.5°	658.8	610.7	564.1	538.9	522.0	516.0	511.4
45°	555.5	510.7	478.3	459.3	449.5	439.4	434.6
47.5°	472.6	436.3	414.9	398.8	388.2	382.2	379.1
50°	425.7	395.9	376.8	364.5	355.0	350.2	347.6
52.5°	384.1	359.6	343.6	333.8	327.3	323.8	322.8
55°	330.8	312.2	302.0	293.4	288.7	285.5	284.2
57.5°	287.6	273.2	265.0	257.9	256.1	253.4	252.5
60°	259.2	248.1	241.1	236.4	234.7	231.5	232.2
62.5°	234.1	224.9	219.0	216.3	214.2	211.5	212.4
65°	198.0	191.3	188.1	185.6	183.0	181.5	182.7
67.5°	166.1	161.5	157.2	155.7	154.5	154.3	152.9
70°	145.3	141.5	137.7	136.7	136.7	135.4	135.1
72.5°	125.2	122.5	119.9	119.2	118.2	118.7	117.4
75°	96.8	94.5	93.6	92.6	92.3	92.3	91.4
77.5°	71.5	69.9	68.3	68.3	67.2	66.8	66.6
80°	54.2	53.6	52.3	52.3	51.7	52.0	51.4
82.5°	40.8	39.9	39.6	39.1	38.2	38.3	37.7
85°	21.9	21.0	20.6	19.6	19.0	19.6	19.0
87.5°	14.0	14.1	14.0	13.6	13.5	13.6	13.0
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332769-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)