

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332773-930

Luminaire Tested: **S124DIW-S575D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332773-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7121.5 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29				
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24				
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20				
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17				
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	20	19	15				
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13				
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11				
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	10				
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.0
10°-20°	210.1	3.0
20°-30°	309.2	4.3
30°-40°	359.5	5.0
40°-50°	359.5	5.0
50°-60°	314.5	4.4
60°-70°	233.5	3.3
70°-80°	132.7	1.9
80°-90°	43.0	0.6
90°-100°	56.2	0.8
100°-110°	358.5	5.0
110°-120°	685.8	9.6
120°-130°	870.5	12.2
130°-140°	931.4	13.1
140°-150°	871.0	12.2
150°-160°	702.4	9.9
160°-170°	453.0	6.4
170°-180°	156.1	2.2
0°-30°	593.9	8.3
0°-40°	953.4	13.4
0°-60°	1627.3	22.9
0°-90°	2036.5	28.6
90°-120°	1100.5	15.5
90°-150°	3773.4	53.0
90°-180°	5085.0	71.4
0°-180°	7121.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	4	17	27	34	37	5
95°	68	28	27	34	36	87
105°	370	377	384	392	350	387
115°	691	694	693	696	696	680
125°	971	976	974	977	979	867
135°	1205	1204	1209	1211	1214	928
145°	1389	1393	1393	1394	1397	868
155°	1523	1524	1521	1525	1522	702
165°	1607	1601	1601	1610	1600	454
175°	1644	1637	1638	1647	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.9	14.4	14.9	15.4	15.9	16.3	16.6	17.0	17.3	17.6	17.9
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	15.5	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7
95°	67.6	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7
97.5°	143.6	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6
100°	201.6	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5
102.5°	266.5	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5
105°	370.1	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0
107.5°	466.2	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5
110°	531.2	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	594.1	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1
115°	691.0	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0
117.5°	778.3	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8
120°	837.3	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6
122.5°	892.3	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4
125°	971.3	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6
127.5°	1046.0	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8
130°	1094.3	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4
132.5°	1138.5	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7
135°	1204.9	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2
137.5°	1263.7	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2
140°	1302.0	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8
142.5°	1336.4	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0
145°	1389.4	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3
147.5°	1431.4	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3
150°	1461.9	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6
152.5°	1487.4	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6
155°	1523.4	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0
157.5°	1553.6	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1
160°	1571.3	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1
162.5°	1587.1	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7
165°	1607.0	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0
167.5°	1622.7	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0
170°	1631.6	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6
172.5°	1637.4	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5
175°	1643.8	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1
177.5°	1646.8	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	18.3	18.6	18.9	19.2	19.2	19.3	19.5	19.6
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	29.4	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	30.3	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.8	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	44.8	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	160.5	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	388.5	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	480.7	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.3	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332773-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	604.0	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	694.6	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.7	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	897.7	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	975.4	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.6	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1099.8	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.0	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1209.7	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1270.8	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1308.6	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1343.6	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.6	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.5	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.0	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1523.1	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1584.5	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1605.2	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1620.4	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1629.8	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1635.7	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1642.6	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1645.4	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)