

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332774-930

Luminaire Tested: **S124DIW-S575D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332774-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6446.6 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	32	
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	35	34	33	27	
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	30	29	28	22	
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	27	25	24	19	
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	24	22	20	16	
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	22	19	18	14	
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	20	17	16	12	
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	18	16	14	11	
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	16	14	12	10	
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	15	13	11	9	
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	14	12	10	8	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.2
10°-20°	210.1	3.3
20°-30°	309.2	4.8
30°-40°	359.5	5.6
40°-50°	359.5	5.6
50°-60°	314.5	4.9
60°-70°	233.5	3.6
70°-80°	132.7	2.1
80°-90°	43.0	0.7
90°-100°	104.8	1.6
100°-110°	310.6	4.8
110°-120°	527.1	8.2
120°-130°	695.1	10.8
130°-140°	780.6	12.1
140°-150°	767.1	11.9
150°-160°	645.2	10.0
160°-170°	429.2	6.7
170°-180°	150.3	2.3
0°-30°	593.9	9.2
0°-40°	953.4	14.8
0°-60°	1627.3	25.2
0°-90°	2036.5	31.6
90°-120°	942.5	14.6
90°-150°	3185.3	49.4
90°-180°	4410.0	68.4
0°-180°	6446.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	4	17	27	34	37	7
95°	74	85	93	97	97	82
105°	286	288	293	296	300	304
115°	536	536	534	532	531	528
125°	781	781	779	777	774	695
135°	1007	1014	1014	1012	1008	779
145°	1223	1228	1229	1228	1224	765
155°	1401	1401	1400	1405	1400	645
165°	1526	1522	1520	1526	1522	430
175°	1587	1581	1580	1587	1580	151
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.9	14.4	14.9	15.4	15.9	16.3	16.6	17.0	17.3	17.6	17.9
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	26.3	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7
95°	73.8	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2
97.5°	128.8	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7
100°	172.1	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7
102.5°	217.4	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2
105°	286.4	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4
107.5°	359.0	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9
110°	408.1	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.3	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5
115°	536.0	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3
117.5°	608.3	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6
120°	656.5	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3
122.5°	706.6	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0
125°	780.6	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9
127.5°	847.7	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9
130°	895.0	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1
132.5°	943.1	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4
135°	1006.8	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7
137.5°	1076.2	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8
140°	1122.4	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5
142.5°	1164.7	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1
145°	1223.2	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1281.2	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9
150°	1316.6	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.1	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6
155°	1401.4	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3
157.5°	1444.7	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1
160°	1470.3	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7
162.5°	1493.9	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9
165°	1525.6	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1
167.5°	1550.0	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7
170°	1563.7	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4
172.5°	1573.5	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5
175°	1587.1	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6
177.5°	1591.5	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	18.3	18.6	18.9	19.2	19.2	19.3	19.5	19.6
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	50.6	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.1	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	149.8	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.1	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	230.9	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	294.2	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	362.7	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	408.3	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P332774-930

CATALOG NUMBER: S124DIW-S575D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.3	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	533.0	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	605.7	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	654.9	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	705.0	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	778.3	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	848.4	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.6	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.8	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1013.1	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1080.2	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.3	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.8	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.7	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.3	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1443.9	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1469.5	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1492.4	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1522.7	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1548.3	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1562.1	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1572.4	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1589.7	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)