

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333077-930

Luminaire Tested: **S124RDIW-S1020D470U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333077-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D470U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4930.9 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69				
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	54	50				
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43				
4	79	68	60	54	74	64	57	51	58	52	48	52	47	44	47	43	40	37				
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32				
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	38	34	31	28				
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25				
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23				
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21				
10	50	38	31	26	48	36	30	25	33	28	24	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.8
10°-20°	385.6	7.8
20°-30°	556.9	11.3
30°-40°	631.2	12.8
40°-50°	609.5	12.4
50°-60°	506.9	10.3
60°-70°	350.0	7.1
70°-80°	177.4	3.6
80°-90°	46.9	1.0
90°-100°	16.9	0.3
100°-110°	107.7	2.2
110°-120°	206.1	4.2
120°-130°	261.6	5.3
130°-140°	279.9	5.7
140°-150°	261.7	5.3
150°-160°	211.1	4.3
160°-170°	136.1	2.8
170°-180°	46.9	1.0
0°-30°	1080.8	21.9
0°-40°	1712.0	34.7
0°-60°	2828.4	57.4
0°-90°	3402.7	69.0
90°-120°	330.7	6.7
90°-150°	1134.0	23.0
90°-180°	1528.0	31.0
0°-180°	4930.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	68
90°	1	5	8	10	11	4
95°	20	8	8	10	11	26
105°	111	113	115	118	105	116
115°	208	209	208	209	209	204
125°	292	293	293	294	294	261
135°	362	362	363	364	365	279
145°	418	419	419	419	420	261
155°	458	458	457	458	458	211
165°	483	481	481	484	481	136
175°	494	492	492	495	491	47
180°	494	494	494	494	494	



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.0	19.6	18.1	16.7	15.2	14.5	14.4	14.3	14.3	14.3	14.2
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	4.6	4.7	4.7	4.8	4.9	5.2	5.9	6.5	7.2	7.8	8.3
95°	20.3	17.5	14.8	12.0	9.1	7.8	7.9	8.0	8.1	8.2	8.6
97.5°	43.1	44.9	46.6	48.3	50.1	46.4	37.3	28.0	18.9	9.8	9.8
100°	60.6	62.0	63.6	65.1	66.5	61.6	50.2	38.9	27.6	16.2	14.8
102.5°	80.1	81.2	82.3	83.3	84.5	84.2	82.8	81.3	79.8	78.4	63.3
105°	111.2	111.7	112.2	112.7	113.2	113.7	114.1	114.5	114.9	115.3	116.0
107.5°	140.1	140.4	140.6	140.9	141.1	141.5	142.0	142.6	143.2	143.7	144.1
110°	159.6	159.9	160.1	160.4	160.6	160.9	161.4	162.0	162.5	163.0	163.1



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	178.6	179.0	179.4	179.9	180.3	180.7	180.9	181.1	181.3	181.6	181.6
115°	207.7	207.9	208.1	208.4	208.6	208.7	208.6	208.6	208.5	208.4	208.6
117.5°	233.9	234.2	234.6	234.9	235.2	235.5	235.6	235.8	236.0	236.2	236.1
120°	251.6	251.9	252.3	252.6	252.9	253.1	253.0	252.9	252.8	252.7	252.9
122.5°	268.2	268.4	268.6	268.8	269.0	269.1	269.2	269.4	269.5	269.6	269.7
125°	291.9	292.2	292.5	292.9	293.2	293.3	293.1	292.9	292.8	292.6	292.9
127.5°	314.4	314.5	314.5	314.6	314.7	315.0	315.3	315.7	316.1	316.4	316.4
130°	328.8	328.9	329.1	329.1	329.2	329.4	329.6	329.9	330.1	330.4	330.4
132.5°	342.2	342.3	342.4	342.6	342.8	343.0	343.3	343.6	343.9	344.2	344.3
135°	362.1	362.0	361.9	361.8	361.7	361.9	362.2	362.6	362.9	363.2	363.4
137.5°	379.8	379.8	379.8	379.8	379.9	380.1	380.4	380.8	381.2	381.6	381.7
140°	391.3	391.4	391.6	391.8	391.9	392.1	392.2	392.5	392.6	392.8	393.1
142.5°	401.6	401.9	402.3	402.5	402.8	403.0	403.1	403.2	403.3	403.4	403.6
145°	417.5	417.8	418.0	418.2	418.5	418.7	418.7	418.7	418.7	418.7	418.7
147.5°	430.2	430.6	431.0	431.5	432.0	432.2	432.1	432.0	431.9	431.9	431.9
150°	439.4	439.7	440.0	440.3	440.7	440.8	440.7	440.6	440.5	440.4	440.4
152.5°	447.0	447.3	447.5	447.8	448.1	448.1	448.0	447.8	447.7	447.5	447.7
155°	457.8	457.9	458.0	458.0	458.1	458.0	457.8	457.5	457.3	457.1	457.4
157.5°	466.9	466.8	466.8	466.8	466.7	466.5	466.3	465.9	465.7	465.5	465.9
160°	472.2	472.0	471.7	471.5	471.2	471.1	471.0	470.9	470.8	470.8	471.2
162.5°	477.0	476.6	476.3	476.0	475.7	475.5	475.4	475.3	475.2	475.2	475.6
165°	482.9	482.5	482.1	481.7	481.3	481.1	481.1	481.1	481.1	481.1	481.8
167.5°	487.6	487.2	486.8	486.4	485.9	485.7	485.7	485.6	485.6	485.5	486.2
170°	490.3	489.8	489.3	488.9	488.4	488.1	488.2	488.3	488.4	488.4	489.1
172.5°	492.1	491.6	491.1	490.6	490.2	489.9	490.0	490.1	490.2	490.2	490.9
175°	494.0	493.5	493.0	492.5	492.0	491.9	492.0	492.0	492.1	492.2	492.9
177.5°	494.9	494.5	494.0	493.5	493.1	492.9	493.0	493.2	493.3	493.4	493.9
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	14.0	13.9	13.9	13.9	14.1	14.3	14.6	14.8
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	8.8	9.3	9.8	10.0	10.1	10.1	10.2	10.2
95°	9.1	9.6	10.1	10.4	10.4	10.5	10.6	10.7
97.5°	9.9	9.9	9.9	10.0	10.1	10.2	10.3	10.4
100°	13.5	12.1	10.7	10.0	10.1	10.2	10.3	10.4
102.5°	48.2	33.2	18.1	10.6	10.6	10.6	10.6	10.7
105°	116.8	117.5	118.2	117.2	114.1	111.2	108.3	105.3
107.5°	144.5	144.8	145.2	145.5	145.9	146.1	146.4	146.8
110°	163.3	163.5	163.6	163.8	164.0	164.3	164.5	164.8



TEST NUMBER: P333077-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.5	181.5	181.4	181.6	181.9	182.2	182.5	182.8
115°	208.7	208.9	209.0	209.1	209.1	209.1	209.1	209.1
117.5°	236.1	236.1	236.0	236.0	235.9	235.9	235.9	235.9
120°	253.1	253.2	253.4	253.4	253.2	253.1	252.9	252.7
122.5°	269.8	269.9	269.9	269.9	269.8	269.6	269.5	269.3
125°	293.1	293.3	293.6	293.8	293.8	293.9	294.0	294.1
127.5°	316.3	316.3	316.3	316.2	316.1	316.0	316.0	315.9
130°	330.5	330.6	330.7	330.7	330.7	330.7	330.7	330.7
132.5°	344.4	344.5	344.5	344.5	344.5	344.5	344.4	344.3
135°	363.5	363.7	363.9	364.0	364.2	364.4	364.5	364.7
137.5°	381.9	382.0	382.3	382.3	382.3	382.2	382.2	382.1
140°	393.3	393.5	393.8	394.0	394.0	394.1	394.2	394.3
142.5°	403.7	404.0	404.1	404.2	404.2	404.3	404.3	404.3
145°	418.8	418.9	419.0	419.1	419.2	419.4	419.6	419.7
147.5°	432.0	432.0	432.1	432.2	432.3	432.4	432.4	432.5
150°	440.4	440.4	440.4	440.5	440.6	440.7	440.8	440.8
152.5°	447.8	447.9	448.1	448.1	448.1	448.0	447.9	447.9
155°	457.7	458.0	458.4	458.4	458.2	458.0	457.7	457.5
157.5°	466.3	466.7	467.1	467.1	466.7	466.3	465.9	465.5
160°	471.7	472.2	472.7	472.7	472.2	471.7	471.2	470.8
162.5°	476.1	476.6	477.1	477.1	476.5	476.0	475.4	474.9
165°	482.4	483.1	483.7	483.6	482.9	482.2	481.4	480.7
167.5°	487.0	487.7	488.4	488.4	487.5	486.7	485.9	485.1
170°	489.8	490.4	491.1	491.1	490.2	489.3	488.5	487.7
172.5°	491.5	492.2	492.8	492.8	491.9	491.0	490.1	489.2
175°	493.7	494.4	495.1	495.0	494.0	493.0	492.0	491.1
177.5°	494.5	495.0	495.5	495.4	494.6	493.8	493.0	492.3
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0

(END OF REPORT)