

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333078-930

Luminaire Tested: **S124RDIW-S1020D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333078-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1020D470U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4728.0 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333078-930  
CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72	72	72	72	
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61	61	61	61	
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	52	52	52	52	
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45	45	45	45	
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	38	38	38	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34	34	34	34	
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30	30	30	30	
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26	26	26	26	
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24	24	24	24	
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	21	21	21	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	20	20	20	20	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.3	2.9
10°-20°	385.6	8.2
20°-30°	556.9	11.8
30°-40°	631.2	13.4
40°-50°	609.5	12.9
50°-60°	506.9	10.7
60°-70°	350.0	7.4
70°-80°	177.4	3.8
80°-90°	46.9	1.0
90°-100°	31.5	0.7
100°-110°	93.3	2.0
110°-120°	158.4	3.4
120°-130°	208.9	4.4
130°-140°	234.6	5.0
140°-150°	230.5	4.9
150°-160°	193.9	4.1
160°-170°	129.0	2.7
170°-180°	45.2	1.0
0°-30°	1080.8	22.9
0°-40°	1712.0	36.2
0°-60°	2828.4	59.8
0°-90°	3402.7	72.0
90°-120°	283.3	6.0
90°-150°	957.2	20.2
90°-180°	1325.0	28.0
0°-180°	4728.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	68
90°	1	5	8	10	11	4
95°	22	25	28	29	29	25
105°	86	86	88	89	90	91
115°	161	161	160	160	160	159
125°	235	235	234	234	233	209
135°	303	305	305	304	303	234
145°	368	369	369	369	368	230
155°	421	421	421	422	421	194
165°	458	457	457	459	457	129
175°	477	475	475	477	475	45
180°	478	478	478	478	478	



TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.0	19.6	18.1	16.7	15.2	14.5	14.4	14.3	14.3	14.3	14.2
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	7.9	9.0	9.9	11.0	12.1	12.8	13.3	13.7	14.2	14.6	14.9
95°	22.2	22.9	23.6	24.4	25.1	25.8	26.3	26.9	27.5	28.0	28.3
97.5°	38.7	39.3	39.9	40.5	41.1	41.7	42.4	43.0	43.7	44.4	44.7
100°	51.7	52.0	52.3	52.7	53.1	53.6	54.3	55.0	55.8	56.5	56.7
102.5°	65.3	65.5	65.6	65.7	65.9	66.3	66.9	67.6	68.2	69.0	69.1
105°	86.1	86.2	86.3	86.3	86.4	86.6	86.9	87.2	87.6	87.9	88.1
107.5°	107.9	107.9	108.1	108.2	108.3	108.4	108.4	108.4	108.5	108.5	108.8
110°	122.6	122.8	122.9	123.1	123.3	123.4	123.3	123.2	123.1	123.0	122.9



TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.0	138.0	138.1	138.1	138.2	138.1	137.9	137.8	137.6	137.5	137.5
115°	161.1	161.1	161.1	161.1	161.1	161.0	160.9	160.7	160.5	160.4	160.3
117.5°	182.8	182.9	183.0	183.0	183.0	183.0	183.0	182.8	182.7	182.5	182.3
120°	197.3	197.6	198.0	198.3	198.6	198.6	198.4	198.1	197.9	197.6	197.2
122.5°	212.4	212.5	212.6	212.7	212.9	212.9	212.8	212.6	212.5	212.5	212.1
125°	234.6	234.6	234.6	234.6	234.6	234.6	234.5	234.4	234.3	234.2	234.1
127.5°	254.8	255.0	255.3	255.5	255.8	255.8	255.7	255.5	255.4	255.3	255.1
130°	269.0	269.2	269.5	269.7	269.9	270.0	270.0	270.0	270.0	270.0	269.9
132.5°	283.4	283.6	283.8	284.0	284.1	284.2	284.1	284.1	284.1	284.0	283.8
135°	302.6	303.0	303.5	304.0	304.5	304.8	304.8	304.8	304.8	304.8	304.6
137.5°	323.4	323.7	323.8	324.1	324.3	324.5	324.7	324.8	324.9	325.1	324.8
140°	337.3	337.5	337.6	337.8	337.9	338.0	338.0	338.0	338.0	338.0	337.9
142.5°	350.0	350.2	350.3	350.5	350.7	350.7	350.7	350.6	350.5	350.4	350.4
145°	367.6	367.9	368.3	368.6	368.9	369.1	369.2	369.2	369.3	369.4	369.3
147.5°	385.1	385.4	385.8	386.2	386.6	386.8	386.7	386.6	386.6	386.5	386.5
150°	395.7	396.0	396.3	396.6	397.0	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	405.7	405.9	406.1	406.3	406.5	406.7	406.7	406.8	406.8	406.9	407.1
155°	421.2	421.2	421.2	421.2	421.2	421.1	421.0	420.9	420.9	420.8	421.1
157.5°	434.1	434.0	433.9	433.7	433.6	433.5	433.5	433.5	433.4	433.4	433.7
160°	441.9	441.8	441.7	441.6	441.6	441.5	441.4	441.3	441.2	441.2	441.4
162.5°	449.0	448.7	448.5	448.3	448.1	447.9	447.8	447.8	447.7	447.6	448.1
165°	458.4	458.2	458.0	457.7	457.5	457.3	457.1	457.0	456.8	456.6	457.1
167.5°	465.8	465.5	465.1	464.8	464.4	464.2	464.2	464.3	464.3	464.3	464.8
170°	469.9	469.5	469.1	468.7	468.3	468.1	468.2	468.3	468.4	468.5	469.0
172.5°	472.9	472.5	472.2	471.9	471.5	471.3	471.3	471.4	471.4	471.4	472.0
175°	477.0	476.5	476.1	475.7	475.3	475.1	475.0	474.9	474.8	474.7	475.3
177.5°	478.3	477.9	477.6	477.3	477.0	476.8	476.8	476.8	476.8	476.8	477.3
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7



TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	14.0	13.9	13.9	13.9	14.1	14.3	14.6	14.8
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	15.2	15.5	15.8	16.0	16.1	16.2	16.3	16.4
95°	28.5	28.8	29.0	29.2	29.2	29.2	29.2	29.2
97.5°	45.0	45.3	45.6	45.7	45.7	45.7	45.7	45.7
100°	56.8	57.0	57.2	57.2	57.2	57.2	57.2	57.2
102.5°	69.4	69.6	69.9	70.0	70.0	70.1	70.2	70.3
105°	88.5	88.7	88.9	89.2	89.4	89.7	89.9	90.2
107.5°	109.0	109.3	109.5	109.6	109.6	109.6	109.5	109.5
110°	122.7	122.5	122.4	122.4	122.6	122.9	123.1	123.4





TEST NUMBER: P333078-930

CATALOG NUMBER: S124RDIW-S1020D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.4	137.4	137.4	137.5	137.5	137.5	137.5
115°	160.2	160.1	160.0	160.0	159.9	159.8	159.7	159.6
117.5°	182.1	181.7	181.5	181.2	181.1	180.9	180.8	180.6
120°	196.8	196.4	196.0	195.9	196.1	196.2	196.4	196.6
122.5°	211.9	211.6	211.3	211.0	210.8	210.4	210.1	209.9
125°	233.9	233.7	233.6	233.4	233.3	233.1	232.9	232.8
127.5°	254.9	254.8	254.6	254.5	254.4	254.2	254.1	254.0
130°	269.7	269.5	269.4	269.1	268.8	268.5	268.2	267.8
132.5°	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.7
135°	304.4	304.3	304.1	303.9	303.7	303.5	303.2	303.0
137.5°	324.6	324.4	324.2	324.1	324.2	324.2	324.2	324.3
140°	337.9	337.8	337.7	337.6	337.5	337.5	337.4	337.3
142.5°	350.4	350.4	350.4	350.3	350.3	350.3	350.3	350.3
145°	369.2	369.2	369.1	368.9	368.7	368.4	368.2	367.9
147.5°	386.4	386.3	386.3	386.2	386.1	386.0	386.0	385.9
150°	397.1	397.1	397.1	397.1	397.1	397.0	396.9	396.8
152.5°	407.3	407.5	407.7	407.6	407.5	407.2	407.1	406.8
155°	421.4	421.8	422.1	422.1	421.8	421.4	421.1	420.8
157.5°	433.9	434.1	434.4	434.4	434.1	433.8	433.6	433.3
160°	441.6	441.9	442.1	442.1	441.6	441.2	440.8	440.3
162.5°	448.5	449.0	449.4	449.4	449.0	448.6	448.2	447.8
165°	457.6	458.1	458.6	458.7	458.4	458.0	457.7	457.4
167.5°	465.3	465.8	466.3	466.3	465.8	465.3	464.7	464.2
170°	469.4	469.9	470.4	470.3	469.8	469.2	468.6	468.1
172.5°	472.5	473.1	473.6	473.6	473.0	472.5	471.9	471.3
175°	475.9	476.5	477.0	477.0	476.5	475.9	475.3	474.7
177.5°	477.8	478.2	478.7	478.6	478.1	477.6	477.0	476.5
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7

(END OF REPORT)