

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333047-930

Luminaire Tested: **S124RDIW-S575D1340U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333047-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6367.8 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	43	38	36	33	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	22	20	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	20	18	17	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	16	15	12
8	52	40	33	28	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6356	6356	6356	6356
5°	7373	6375	5635	6375
10°	8722	6347	5029	6347
15°	10074	6288	4322	6288
20°	11217	6208	3908	6208
25°	11580	6128	3628	6128
30°	10137	6032	3459	6032
35°	7890	5889	3358	5889
40°	5917	5727	3303	5727
45°	4672	5465	3273	5465
50°	3945	5163	3180	5163
55°	3438	4830	3009	4830
60°	3094	4487	2662	4487
65°	2728	4115	2290	4115
70°	2455	3729	2068	3729
75°	2059	3306	1762	3306
80°	1739	2817	1650	2817
85°	1473	2205	1473	2205



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	1.2
10°-20°	230.1	3.6
20°-30°	359.9	5.7
30°-40°	400.1	6.3
40°-50°	355.0	5.6
50°-60°	276.6	4.3
60°-70°	181.1	2.8
70°-80°	89.1	1.4
80°-90°	26.1	0.4
90°-100°	48.4	0.8
100°-110°	308.3	4.8
110°-120°	589.8	9.3
120°-130°	748.7	11.8
130°-140°	801.1	12.6
140°-150°	749.1	11.8
150°-160°	604.1	9.5
160°-170°	389.6	6.1
170°-180°	134.3	2.1
0°-30°	666.3	10.5
0°-40°	1066.4	16.7
0°-60°	1698.1	26.7
0°-90°	1994.3	31.3
90°-120°	946.5	14.9
90°-150°	3245.5	51.0
90°-180°	4374.0	68.7
0°-180°	6367.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	910	787	695	787	910	92
15°	1205	752	517	752	1205	343
25°	1300	688	407	688	1300	577
35°	801	598	341	598	801	502
45°	409	479	287	479	409	324
55°	244	343	214	343	244	222
65°	143	215	120	215	143	144
75°	66	106	56	106	66	73
85°	16	24	16	24	16	19
90°	32	3	32	3	32	14
95°	31	58	31	58	31	24
105°	301	318	301	318	301	263
115°	598	594	598	594	598	592
125°	842	835	842	835	842	750
135°	1044	1036	1044	1036	1044	803
145°	1201	1195	1201	1195	1201	751
155°	1309	1310	1309	1310	1309	604
165°	1376	1382	1376	1382	1376	389
175°	1405	1414	1405	1414	1405	134
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	830.5	832.7	830.5	830.2	827.7	827.0	825.9	822.6	816.5	812.9	813.8
5°	909.8	917.7	913.3	912.6	905.6	898.7	894.2	884.1	873.3	866.0	860.0
7.5°	1001.5	1006.1	1003.3	998.8	987.6	981.1	970.9	957.5	938.2	923.3	909.9
10°	1064.0	1067.7	1066.5	1058.3	1050.0	1033.1	1023.7	1004.9	980.5	961.2	943.1
12.5°	1125.4	1129.4	1118.3	1118.7	1103.0	1089.7	1074.6	1051.2	1022.9	997.9	975.3
15°	1205.4	1200.4	1200.4	1194.0	1176.6	1158.1	1142.6	1117.9	1082.3	1052.6	1021.2
17.5°	1268.1	1269.9	1267.3	1252.3	1238.6	1219.6	1191.1	1162.2	1129.2	1089.2	1057.1
20°	1305.7	1305.7	1302.8	1292.7	1274.9	1254.6	1223.8	1192.5	1150.6	1110.3	1074.1
22.5°	1320.9	1321.9	1318.6	1310.2	1294.2	1274.4	1248.2	1216.3	1173.1	1127.8	1083.0
25°	1300.0	1305.9	1306.6	1304.4	1299.7	1287.6	1265.1	1232.4	1193.7	1144.5	1096.3
27.5°	1193.5	1201.1	1207.8	1218.7	1233.3	1241.0	1241.9	1225.3	1191.6	1144.3	1095.8
30°	1087.4	1093.7	1114.4	1141.3	1162.3	1181.3	1197.8	1202.2	1183.2	1140.7	1089.6
32.5°	969.6	978.3	998.9	1027.9	1062.8	1095.0	1132.1	1151.0	1150.5	1124.9	1077.7
35°	800.6	807.0	826.1	856.5	898.4	946.2	1004.9	1050.6	1081.7	1079.5	1050.6
37.5°	645.7	652.9	672.1	697.4	738.0	797.3	854.1	917.0	974.5	1006.8	997.1
40°	561.5	561.8	580.5	606.5	644.6	696.3	758.1	827.9	892.0	944.4	954.5
42.5°	495.0	495.0	507.4	535.5	562.9	611.6	670.6	739.9	814.9	875.3	902.2
45°	409.2	412.1	422.2	439.0	460.6	501.8	549.1	613.5	697.6	769.2	814.0
47.5°	346.5	350.7	357.2	370.9	388.1	415.6	454.6	512.5	580.9	659.7	723.4
50°	314.1	314.7	322.9	330.5	345.4	367.4	401.6	449.8	512.7	588.4	659.2
52.5°	286.2	286.0	291.0	300.6	312.7	329.8	357.4	401.4	457.1	525.0	598.0
55°	244.3	245.8	249.6	257.2	266.4	278.5	300.4	333.4	377.2	435.2	501.5
57.5°	212.4	213.2	216.2	219.5	227.9	236.7	253.1	276.0	312.9	360.4	422.2
60°	191.6	191.9	192.9	197.6	204.3	212.5	223.6	243.0	274.1	317.6	366.4
62.5°	171.3	171.9	173.3	176.8	182.0	187.7	199.3	214.8	240.6	277.7	321.7
65°	142.8	143.1	145.3	146.6	150.7	155.7	164.3	174.8	192.6	223.6	257.0
67.5°	119.3	119.3	119.4	121.2	124.0	127.3	132.5	140.9	154.3	173.3	202.7
70°	104.0	104.0	104.7	105.7	107.2	110.1	112.9	119.3	129.1	144.6	167.1
72.5°	89.8	90.1	90.7	90.9	91.7	94.1	96.2	100.2	107.5	119.3	137.5
75°	66.0	66.9	68.5	69.8	71.3	71.1	73.3	75.8	78.0	85.0	95.5
77.5°	49.1	48.6	48.8	49.9	50.1	50.4	51.9	53.9	55.6	58.9	62.6
80°	37.4	37.4	38.4	38.7	38.4	38.7	40.3	41.3	41.9	43.1	46.6
82.5°	28.3	28.8	28.5	28.8	29.0	29.4	30.7	30.8	31.5	32.0	33.4
85°	15.9	16.1	16.5	15.9	15.9	15.9	16.5	16.8	17.4	17.1	17.8
87.5°	11.9	11.6	11.7	11.7	11.8	11.3	11.3	11.6	10.8	10.8	10.4
90°	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1	24.7	23.2	21.4
92.5°	29.2	29.1	29.0	28.9	28.8	28.0	26.7	25.3	23.8	22.4	20.5
95°	30.7	30.4	30.2	29.9	29.8	28.9	27.5	26.1	24.7	23.2	23.0
97.5°	29.6	29.4	29.1	28.9	28.7	28.5	28.4	28.2	28.0	27.9	54.1
100°	29.6	29.4	29.1	28.9	28.7	30.6	34.6	38.6	42.6	46.6	78.9
102.5°	30.5	30.4	30.3	30.3	30.2	51.8	94.9	138.0	181.1	224.2	228.4
105°	301.4	309.8	318.3	326.8	335.3	338.4	336.3	334.2	332.1	330.0	328.7
107.5°	420.0	419.1	418.2	417.4	416.5	415.5	414.5	413.4	412.4	411.4	409.8
110°	471.7	470.9	470.3	469.5	468.8	468.2	467.7	467.3	466.8	466.4	465.0



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.3	522.4	521.5	520.6	519.7	519.3	519.3	519.4	519.6	519.7	519.0
115°	598.5	598.5	598.5	598.5	598.5	598.3	597.9	597.4	596.9	596.4	596.6
117.5°	675.1	675.2	675.3	675.4	675.5	675.6	675.6	675.7	675.9	676.0	675.4
120°	723.3	723.8	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3	723.6
122.5°	770.7	771.2	771.6	772.1	772.6	772.7	772.4	772.1	771.8	771.5	771.2
125°	841.8	841.6	841.3	841.1	840.8	840.3	839.7	838.9	838.2	837.6	838.0
127.5°	904.2	904.3	904.5	904.7	904.9	905.1	905.2	905.4	905.5	905.6	904.6
130°	946.5	946.5	946.5	946.5	946.5	946.3	946.1	945.8	945.7	945.4	944.7
132.5°	985.4	985.5	985.8	985.9	986.1	986.1	985.9	985.6	985.4	985.1	984.2
135°	1043.7	1043.3	1042.8	1042.4	1041.9	1041.4	1040.9	1040.5	1040.0	1039.5	1038.6
137.5°	1093.6	1093.8	1094.0	1094.1	1094.2	1094.1	1093.5	1093.0	1092.5	1091.9	1091.0
140°	1128.4	1128.1	1127.9	1127.6	1127.4	1126.9	1126.3	1125.5	1124.8	1124.1	1123.6
142.5°	1157.1	1157.1	1157.0	1157.0	1156.9	1156.7	1156.1	1155.6	1155.1	1154.5	1154.3
145°	1201.3	1200.9	1200.4	1199.9	1199.5	1199.1	1198.8	1198.6	1198.4	1198.2	1198.2
147.5°	1237.9	1237.6	1237.5	1237.2	1237.0	1236.7	1236.6	1236.4	1236.2	1236.0	1236.2
150°	1261.6	1261.3	1261.1	1260.9	1260.6	1260.5	1260.5	1260.5	1260.5	1260.5	1260.8
152.5°	1281.9	1282.1	1282.1	1282.3	1282.5	1282.3	1282.0	1281.6	1281.2	1280.8	1281.2
155°	1309.2	1309.9	1310.6	1311.3	1312.0	1311.9	1310.9	1310.0	1309.0	1308.1	1308.8
157.5°	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0	1332.9
160°	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3	1347.4
162.5°	1359.1	1360.7	1362.3	1363.9	1365.5	1365.5	1364.2	1362.8	1361.3	1359.9	1360.2
165°	1375.8	1377.9	1380.1	1382.2	1384.2	1384.4	1382.5	1380.6	1378.8	1376.9	1376.9
167.5°	1388.3	1390.7	1392.9	1395.3	1397.7	1397.8	1395.7	1393.7	1391.6	1389.5	1389.7
170°	1395.9	1398.2	1400.6	1403.0	1405.2	1405.5	1403.6	1401.7	1399.9	1398.0	1397.7
172.5°	1400.1	1402.6	1405.2	1407.7	1410.3	1410.6	1408.8	1406.8	1404.9	1403.0	1402.8
175°	1405.4	1408.2	1411.0	1413.9	1416.7	1417.1	1415.0	1412.8	1410.7	1408.6	1408.3
177.5°	1408.8	1411.0	1413.3	1415.5	1417.8	1418.2	1416.7	1415.2	1413.6	1412.2	1411.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	811.2	807.6	805.8	801.8	797.0	794.4	792.1	788.9	784.6	780.0	776.7
5°	852.4	844.7	835.2	823.8	813.7	803.8	795.2	786.7	776.9	766.7	756.6
7.5°	894.6	879.6	863.5	844.7	826.6	810.0	794.8	780.2	763.7	748.9	735.4
10°	924.1	903.8	881.3	857.5	833.6	813.0	792.7	774.3	754.0	736.0	720.7
12.5°	947.9	924.1	897.0	867.3	838.7	813.8	790.4	766.5	743.4	723.7	703.4
15°	987.5	954.8	918.4	882.8	845.7	811.8	780.3	752.4	726.1	698.5	679.1
17.5°	1014.7	975.9	931.6	888.9	845.1	805.0	768.8	735.6	705.2	677.0	654.0
20°	1030.9	988.1	939.0	890.4	841.2	798.4	759.5	722.6	691.2	660.8	637.0
22.5°	1040.1	992.7	939.0	888.1	837.2	790.8	748.0	709.7	675.5	645.1	618.7
25°	1043.0	992.2	937.3	879.0	823.2	774.0	729.6	688.0	650.0	619.5	591.6
27.5°	1038.9	979.2	923.0	863.1	805.5	753.7	707.0	663.3	625.3	592.6	563.9
30°	1032.8	968.8	908.5	846.4	788.0	738.2	689.0	647.1	607.5	573.6	544.7
32.5°	1019.7	956.1	891.3	827.5	768.4	717.1	670.5	628.4	589.5	554.7	524.1
35°	993.5	929.1	858.7	793.4	735.3	682.0	638.2	597.6	560.5	523.4	491.1
37.5°	959.0	893.3	823.2	751.7	693.6	643.3	603.1	565.0	528.7	494.9	459.0
40°	926.6	866.7	794.3	723.3	663.7	615.1	578.0	543.4	507.0	473.3	437.4
42.5°	887.3	836.2	763.1	691.8	632.9	586.1	551.5	517.8	484.6	452.0	414.6
45°	821.6	782.9	714.4	645.9	586.5	540.2	508.5	478.7	449.5	418.4	383.2
47.5°	746.3	720.2	661.0	590.8	536.0	494.3	463.7	439.3	414.6	383.5	352.6
50°	694.1	677.3	620.2	556.1	503.8	465.4	434.0	411.1	390.5	360.7	333.0
52.5°	638.2	629.3	581.1	519.8	469.2	431.6	404.8	384.3	363.4	338.6	312.7
55°	553.3	558.0	517.1	464.1	416.5	384.8	360.4	343.2	325.5	304.5	284.5
57.5°	466.3	483.7	456.2	409.7	365.1	335.8	317.4	303.0	288.1	270.7	253.6
60°	414.3	428.8	413.4	372.4	333.4	306.1	289.0	277.9	262.9	247.1	234.1
62.5°	363.5	379.1	369.9	336.9	300.7	277.2	262.1	251.8	240.7	226.8	213.3
65°	299.8	309.9	305.5	282.7	257.0	236.9	223.0	215.4	205.2	195.1	183.0
67.5°	229.6	249.2	246.6	234.5	212.3	196.7	187.5	180.8	171.5	164.0	155.8
70°	188.7	206.8	206.5	196.7	184.6	170.0	163.7	158.0	149.7	142.4	135.7
72.5°	154.5	171.0	173.5	166.0	157.8	146.7	140.6	136.6	128.7	123.7	118.2
75°	108.2	120.3	123.4	123.4	119.6	113.9	108.5	106.0	100.2	95.8	92.6
77.5°	70.9	78.5	83.5	84.6	85.2	83.3	78.8	77.0	72.7	71.1	68.1
80°	50.1	55.2	60.9	62.8	64.4	63.8	61.9	60.6	56.5	54.9	53.6
82.5°	34.7	37.4	42.2	46.3	45.9	47.5	45.9	44.8	41.7	41.2	39.9
85°	18.1	18.4	19.0	21.9	23.5	24.1	24.5	23.8	22.8	22.8	20.6
87.5°	10.0	9.4	9.5	9.0	8.8	9.3	9.5	9.3	9.0	8.8	8.6
90°	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2	5.8	8.3	10.9
92.5°	18.7	16.8	14.9	13.9	13.8	13.6	13.5	13.3	13.5	13.6	13.8
95°	22.8	22.6	22.3	26.2	34.2	42.2	50.1	58.1	50.1	42.2	34.2
97.5°	80.4	106.6	132.8	143.4	138.4	133.5	128.5	123.5	128.5	133.5	138.4
100°	111.4	143.8	176.3	190.4	186.1	181.9	177.7	173.4	177.7	181.9	186.1
102.5°	232.7	236.8	241.1	241.7	238.6	235.5	232.4	229.3	232.4	235.5	238.6
105°	327.6	326.4	325.2	323.9	322.5	321.1	319.7	318.3	319.7	321.1	322.5
107.5°	408.1	406.6	405.0	403.8	403.1	402.4	401.7	401.0	401.7	402.4	403.1
110°	463.5	462.1	460.7	459.7	458.9	458.3	457.5	456.8	457.5	458.3	458.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	518.4	517.7	517.0	516.1	514.8	513.6	512.3	510.9	512.3	513.6	514.8
115°	596.9	597.1	597.4	597.1	596.4	595.7	595.0	594.3	595.0	595.7	596.4
117.5°	674.9	674.4	673.8	673.1	672.2	671.2	670.3	669.4	670.3	671.2	672.2
120°	723.8	724.1	724.2	723.9	723.0	722.0	721.1	720.2	721.1	722.0	723.0
122.5°	770.9	770.5	770.2	769.8	769.2	768.7	768.1	767.5	768.1	768.7	769.2
125°	838.5	838.9	839.4	839.2	838.2	837.3	836.3	835.4	836.3	837.3	838.2
127.5°	903.4	902.4	901.3	900.7	900.4	900.2	899.9	899.7	899.9	900.2	900.4
130°	944.0	943.3	942.6	942.1	941.8	941.7	941.4	941.2	941.4	941.7	941.8
132.5°	983.3	982.5	981.6	980.9	980.5	980.1	979.7	979.3	979.7	980.1	980.5
135°	1037.6	1036.7	1035.8	1035.4	1035.7	1035.8	1036.1	1036.3	1036.1	1035.8	1035.7
137.5°	1089.9	1088.8	1087.9	1087.3	1087.2	1087.0	1087.0	1086.9	1087.0	1087.0	1087.2
140°	1123.2	1122.7	1122.3	1121.8	1121.3	1120.8	1120.4	1119.9	1120.4	1120.8	1121.3
142.5°	1154.0	1153.7	1153.4	1152.9	1152.0	1151.2	1150.3	1149.5	1150.3	1151.2	1152.0
145°	1198.2	1198.2	1198.2	1197.8	1197.1	1196.4	1195.6	1195.0	1195.6	1196.4	1197.1
147.5°	1236.5	1236.7	1237.0	1236.4	1235.1	1233.8	1232.4	1231.1	1232.4	1233.8	1235.1
150°	1261.0	1261.3	1261.4	1261.1	1260.2	1259.2	1258.3	1257.4	1258.3	1259.2	1260.2
152.5°	1281.7	1282.1	1282.5	1282.4	1281.6	1280.8	1280.1	1279.4	1280.1	1280.8	1281.6
155°	1309.5	1310.3	1310.9	1311.2	1310.9	1310.7	1310.4	1310.3	1310.4	1310.7	1310.9
157.5°	1333.6	1334.4	1335.2	1335.7	1335.8	1335.9	1336.1	1336.3	1336.1	1335.9	1335.8
160°	1347.7	1347.9	1348.2	1348.7	1349.3	1350.1	1350.8	1351.4	1350.8	1350.1	1349.3
162.5°	1360.4	1360.7	1360.9	1361.5	1362.4	1363.3	1364.1	1365.0	1364.1	1363.3	1362.4
165°	1376.9	1376.9	1376.9	1377.4	1378.6	1379.8	1381.0	1382.2	1381.0	1379.8	1378.6
167.5°	1389.8	1390.0	1390.1	1390.8	1392.0	1393.3	1394.5	1395.7	1394.5	1393.3	1392.0
170°	1397.5	1397.3	1397.1	1397.7	1399.1	1400.4	1401.9	1403.3	1401.9	1400.4	1399.1
172.5°	1402.6	1402.4	1402.2	1402.7	1404.1	1405.6	1407.0	1408.3	1407.0	1405.6	1404.1
175°	1408.1	1407.9	1407.6	1408.2	1409.7	1411.0	1412.4	1413.9	1412.4	1411.0	1409.7
177.5°	1411.4	1411.0	1410.6	1411.1	1412.4	1413.7	1415.1	1416.4	1415.1	1413.7	1412.4
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	773.1	770.6	767.3	763.4	758.9	754.9	753.1	754.6	755.4	753.3	753.1
5°	749.6	741.7	735.3	725.8	718.2	711.8	707.4	705.5	706.1	701.1	699.8
7.5°	723.1	713.7	703.4	692.0	681.5	672.2	667.3	664.6	659.3	657.0	653.1
10°	706.1	693.4	683.3	669.9	657.9	646.8	641.4	637.0	631.6	629.0	623.6
12.5°	688.6	673.9	662.8	648.9	636.6	623.2	618.1	609.8	601.4	596.1	589.1
15°	663.9	646.2	632.5	616.0	601.4	586.2	572.6	557.3	551.6	539.6	532.6
17.5°	635.0	617.0	600.1	578.0	555.5	536.6	522.0	507.5	498.7	491.1	487.5
20°	616.0	599.6	576.1	550.4	525.3	504.3	492.6	483.1	473.6	468.2	464.4
22.5°	598.0	577.0	549.7	522.0	496.9	480.5	470.6	460.8	453.1	447.9	442.9
25°	567.9	540.2	511.4	479.6	462.5	448.3	437.4	429.5	424.8	418.1	415.6
27.5°	536.8	503.4	471.5	450.2	432.4	419.3	409.9	404.0	397.9	393.6	390.4
30°	512.9	479.0	450.5	430.2	412.1	401.3	393.6	386.7	382.0	378.5	375.9
32.5°	489.3	455.4	431.4	409.6	395.3	384.8	376.7	371.5	367.7	363.2	361.7
35°	455.2	425.1	404.1	384.5	369.9	360.4	354.0	348.6	345.4	344.2	343.2
37.5°	422.4	397.7	375.2	359.1	346.1	338.6	331.1	328.5	326.3	324.0	325.1
40°	401.6	378.5	358.5	341.4	330.8	322.6	318.1	315.0	313.1	313.1	313.1
42.5°	383.6	360.9	341.4	326.1	315.6	308.7	303.7	301.0	300.4	300.1	301.7
45°	355.6	334.7	315.0	302.3	293.4	286.4	283.6	281.4	281.4	282.7	283.0
47.5°	327.9	308.3	292.4	278.3	270.1	265.8	263.3	262.1	262.3	263.5	265.0
50°	310.9	291.6	276.0	263.3	255.7	251.5	249.3	248.7	249.3	249.3	251.5
52.5°	292.4	275.0	259.8	249.1	240.4	236.6	235.4	234.5	234.9	235.9	236.8
55°	265.2	249.6	235.1	224.9	218.6	216.1	213.2	213.5	212.9	213.5	213.5
57.5°	238.0	224.0	210.4	202.4	196.8	193.1	190.0	190.9	190.0	189.8	189.3
60°	220.5	205.2	194.4	187.2	180.8	177.7	174.8	175.5	174.5	173.8	172.6
62.5°	201.5	188.7	178.5	171.5	166.3	162.7	159.8	159.1	156.9	154.8	152.0
65°	173.8	163.4	154.2	147.5	142.8	139.9	137.7	135.7	131.0	126.0	123.4
67.5°	147.0	139.4	130.9	125.2	121.4	117.6	113.4	110.1	105.7	102.9	101.3
70°	129.7	122.5	115.1	109.7	105.7	102.2	97.3	95.1	92.0	90.7	89.1
72.5°	113.2	106.5	99.6	94.8	90.4	87.6	84.0	81.7	80.3	79.8	78.2
75°	88.2	82.8	77.7	73.3	69.8	67.9	66.3	64.7	64.1	61.2	59.6
77.5°	64.3	60.7	57.6	54.5	51.9	50.7	47.6	45.8	44.8	43.4	43.0
80°	50.1	47.6	44.4	42.5	39.1	37.7	36.4	36.2	35.9	35.5	35.2
82.5°	37.7	35.1	32.0	30.8	29.9	29.1	28.4	28.0	27.7	27.9	27.9
85°	19.0	17.8	17.8	17.4	17.1	16.8	16.5	16.5	16.1	16.5	16.1
87.5°	9.0	9.2	9.6	9.5	10.1	10.5	10.5	10.8	11.3	11.1	11.3
90°	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1	27.5	28.9	29.8
92.5°	13.9	14.9	16.8	18.7	20.5	22.4	23.8	25.3	26.7	28.0	28.8
95°	26.2	22.3	22.6	22.8	23.0	23.2	24.7	26.1	27.5	28.9	29.8
97.5°	143.4	132.8	106.6	80.4	54.1	27.9	28.0	28.2	28.4	28.5	28.7
100°	190.4	176.3	143.8	111.4	78.9	46.6	42.6	38.6	34.6	30.6	28.7
102.5°	241.7	241.1	236.8	232.7	228.4	224.2	181.1	138.0	94.9	51.8	30.2
105°	323.9	325.2	326.4	327.6	328.7	330.0	332.1	334.2	336.3	338.4	335.3
107.5°	403.8	405.0	406.6	408.1	409.8	411.4	412.4	413.4	414.5	415.5	416.5
110°	459.7	460.7	462.1	463.5	465.0	466.4	466.8	467.3	467.7	468.2	468.8



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	516.1	517.0	517.7	518.4	519.0	519.7	519.6	519.4	519.3	519.3	519.7
115°	597.1	597.4	597.1	596.9	596.6	596.4	596.9	597.4	597.9	598.3	598.5
117.5°	673.1	673.8	674.4	674.9	675.4	676.0	675.9	675.7	675.6	675.6	675.5
120°	723.9	724.2	724.1	723.8	723.6	723.3	723.8	724.2	724.7	725.2	725.2
122.5°	769.8	770.2	770.5	770.9	771.2	771.5	771.8	772.1	772.4	772.7	772.6
125°	839.2	839.4	838.9	838.5	838.0	837.6	838.2	838.9	839.7	840.3	840.8
127.5°	900.7	901.3	902.4	903.4	904.6	905.6	905.5	905.4	905.2	905.1	904.9
130°	942.1	942.6	943.3	944.0	944.7	945.4	945.7	945.8	946.1	946.3	946.5
132.5°	980.9	981.6	982.5	983.3	984.2	985.1	985.4	985.6	985.9	986.1	986.1
135°	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0	1040.5	1040.9	1041.4	1041.9
137.5°	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5	1093.0	1093.5	1094.1	1094.2
140°	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8	1125.5	1126.3	1126.9	1127.4
142.5°	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1	1155.6	1156.1	1156.7	1156.9
145°	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4	1198.6	1198.8	1199.1	1199.5
147.5°	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2	1236.4	1236.6	1236.7	1237.0
150°	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5	1260.5	1260.5	1260.5	1260.6
152.5°	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2	1281.6	1282.0	1282.3	1282.5
155°	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0	1310.0	1310.9	1311.9	1312.0
157.5°	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9
160°	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9
162.5°	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3	1362.8	1364.2	1365.5	1365.5
165°	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8	1380.6	1382.5	1384.4	1384.2
167.5°	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6	1393.7	1395.7	1397.8	1397.7
170°	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9	1401.7	1403.6	1405.5	1405.2
172.5°	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9	1406.8	1408.8	1410.6	1410.3
175°	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7	1412.8	1415.0	1417.1	1416.7
177.5°	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6	1415.2	1416.7	1418.2	1417.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	751.5	752.0	750.3	749.7	750.3	752.0	751.5	753.1	753.3	755.4	754.6
5°	697.2	696.6	695.0	695.4	695.0	696.6	697.2	699.8	701.1	706.1	705.5
7.5°	650.8	648.3	649.1	646.5	649.1	648.3	650.8	653.1	657.0	659.3	664.6
10°	622.4	618.9	616.0	613.5	616.0	618.9	622.4	623.6	629.0	631.6	637.0
12.5°	583.6	580.6	576.7	577.5	576.7	580.6	583.6	589.1	596.1	601.4	609.8
15°	528.5	523.7	516.1	517.1	516.1	523.7	528.5	532.6	539.6	551.6	557.3
17.5°	481.8	481.9	478.4	479.2	478.4	481.9	481.8	487.5	491.1	498.7	507.5
20°	457.7	455.5	455.8	454.9	455.8	455.5	457.7	464.4	468.2	473.6	483.1
22.5°	441.0	438.3	436.0	434.1	436.0	438.3	441.0	442.9	447.9	453.1	460.8
25°	412.7	410.8	408.0	407.3	408.0	410.8	412.7	415.6	418.1	424.8	429.5
27.5°	387.8	387.4	386.3	384.8	386.3	387.4	387.8	390.4	393.6	397.9	404.0
30°	373.3	372.8	372.1	371.1	372.1	372.8	373.3	375.9	378.5	382.0	386.7
32.5°	360.4	360.0	359.4	359.5	359.4	360.0	360.4	361.7	363.2	367.7	371.5
35°	341.9	341.6	341.0	340.7	341.0	341.6	341.9	343.2	344.2	345.4	348.6
37.5°	324.7	325.5	325.1	325.1	325.1	325.5	324.7	325.1	324.0	326.3	328.5
40°	312.7	313.1	313.7	313.4	313.7	313.1	312.7	313.1	313.1	313.1	315.0
42.5°	302.9	303.0	303.9	302.7	303.9	303.0	302.9	301.7	300.1	300.4	301.0
45°	285.2	287.1	286.7	286.7	286.7	287.1	285.2	283.0	282.7	281.4	281.4
47.5°	265.8	267.5	267.9	267.8	267.9	267.5	265.8	265.0	263.5	262.3	262.1
50°	253.2	252.5	253.5	253.2	253.5	252.5	253.2	251.5	249.3	249.3	248.7
52.5°	237.7	237.8	237.7	237.4	237.7	237.8	237.7	236.8	235.9	234.9	234.5
55°	213.8	214.1	213.5	213.8	213.5	214.1	213.8	213.5	213.5	212.9	213.5
57.5°	187.9	186.4	187.0	186.3	187.0	186.4	187.9	189.3	189.8	190.0	190.9
60°	169.4	166.9	166.2	164.9	166.2	166.9	169.4	172.6	173.8	174.5	175.5
62.5°	148.5	146.8	144.6	145.7	144.6	146.8	148.5	152.0	154.8	156.9	159.1
65°	120.8	119.6	118.6	119.9	118.6	119.6	120.8	123.4	126.0	131.0	135.7
67.5°	100.0	99.4	99.4	98.7	99.4	99.4	100.0	101.3	102.9	105.7	110.1
70°	89.1	88.2	88.2	87.6	88.2	88.2	89.1	89.1	90.7	92.0	95.1
72.5°	77.9	77.0	77.3	76.9	77.3	77.0	77.9	78.2	79.8	80.3	81.7
75°	57.7	56.2	56.2	56.5	56.2	56.2	57.7	59.6	61.2	64.1	64.7
77.5°	43.0	42.7	43.2	42.6	43.2	42.7	43.0	43.0	43.4	44.8	45.8
80°	35.2	34.9	34.6	35.5	34.6	34.9	35.2	35.2	35.5	35.9	36.2
82.5°	27.3	27.3	27.2	28.5	27.2	27.3	27.3	27.9	27.9	27.7	28.0
85°	16.5	15.9	16.5	15.9	16.5	15.9	16.5	16.1	16.5	16.1	16.5
87.5°	11.9	11.7	11.6	11.9	11.6	11.7	11.9	11.3	11.1	11.3	10.8
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1
92.5°	28.9	29.0	29.1	29.2	29.1	29.0	28.9	28.8	28.0	26.7	25.3
95°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.8	28.9	27.5	26.1
97.5°	28.9	29.1	29.4	29.6	29.4	29.1	28.9	28.7	28.5	28.4	28.2
100°	28.9	29.1	29.4	29.6	29.4	29.1	28.9	28.7	30.6	34.6	38.6
102.5°	30.3	30.3	30.4	30.5	30.4	30.3	30.3	30.2	51.8	94.9	138.0
105°	326.8	318.3	309.8	301.4	309.8	318.3	326.8	335.3	338.4	336.3	334.2
107.5°	417.4	418.2	419.1	420.0	419.1	418.2	417.4	416.5	415.5	414.5	413.4
110°	469.5	470.3	470.9	471.7	470.9	470.3	469.5	468.8	468.2	467.7	467.3



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.6	521.5	522.4	523.3	522.4	521.5	520.6	519.7	519.3	519.3	519.4
115°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.3	597.9	597.4
117.5°	675.4	675.3	675.2	675.1	675.2	675.3	675.4	675.5	675.6	675.6	675.7
120°	724.7	724.2	723.8	723.3	723.8	724.2	724.7	725.2	725.2	724.7	724.2
122.5°	772.1	771.6	771.2	770.7	771.2	771.6	772.1	772.6	772.7	772.4	772.1
125°	841.1	841.3	841.6	841.8	841.6	841.3	841.1	840.8	840.3	839.7	838.9
127.5°	904.7	904.5	904.3	904.2	904.3	904.5	904.7	904.9	905.1	905.2	905.4
130°	946.5	946.5	946.5	946.5	946.5	946.5	946.5	946.5	946.3	946.1	945.8
132.5°	985.9	985.8	985.5	985.4	985.5	985.8	985.9	986.1	986.1	985.9	985.6
135°	1042.4	1042.8	1043.3	1043.7	1043.3	1042.8	1042.4	1041.9	1041.4	1040.9	1040.5
137.5°	1094.1	1094.0	1093.8	1093.6	1093.8	1094.0	1094.1	1094.2	1094.1	1093.5	1093.0
140°	1127.6	1127.9	1128.1	1128.4	1128.1	1127.9	1127.6	1127.4	1126.9	1126.3	1125.5
142.5°	1157.0	1157.0	1157.1	1157.1	1157.1	1157.0	1157.0	1156.9	1156.7	1156.1	1155.6
145°	1199.9	1200.4	1200.9	1201.3	1200.9	1200.4	1199.9	1199.5	1199.1	1198.8	1198.6
147.5°	1237.2	1237.5	1237.6	1237.9	1237.6	1237.5	1237.2	1237.0	1236.7	1236.6	1236.4
150°	1260.9	1261.1	1261.3	1261.6	1261.3	1261.1	1260.9	1260.6	1260.5	1260.5	1260.5
152.5°	1282.3	1282.1	1282.1	1281.9	1282.1	1282.1	1282.3	1282.5	1282.3	1282.0	1281.6
155°	1311.3	1310.6	1309.9	1309.2	1309.9	1310.6	1311.3	1312.0	1311.9	1310.9	1310.0
157.5°	1335.7	1334.5	1333.3	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5
160°	1351.4	1350.1	1348.7	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1
162.5°	1363.9	1362.3	1360.7	1359.1	1360.7	1362.3	1363.9	1365.5	1365.5	1364.2	1362.8
165°	1382.2	1380.1	1377.9	1375.8	1377.9	1380.1	1382.2	1384.2	1384.4	1382.5	1380.6
167.5°	1395.3	1392.9	1390.7	1388.3	1390.7	1392.9	1395.3	1397.7	1397.8	1395.7	1393.7
170°	1403.0	1400.6	1398.2	1395.9	1398.2	1400.6	1403.0	1405.2	1405.5	1403.6	1401.7
172.5°	1407.7	1405.2	1402.6	1400.1	1402.6	1405.2	1407.7	1410.3	1410.6	1408.8	1406.8
175°	1413.9	1411.0	1408.2	1405.4	1408.2	1411.0	1413.9	1416.7	1417.1	1415.0	1412.8
177.5°	1415.5	1413.3	1411.0	1408.8	1411.0	1413.3	1415.5	1417.8	1418.2	1416.7	1415.2
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	753.1	754.9	758.9	763.4	767.3	770.6	773.1	776.7	780.0	784.6	788.9
5°	707.4	711.8	718.2	725.8	735.3	741.7	749.6	756.6	766.7	776.9	786.7
7.5°	667.3	672.2	681.5	692.0	703.4	713.7	723.1	735.4	748.9	763.7	780.2
10°	641.4	646.8	657.9	669.9	683.3	693.4	706.1	720.7	736.0	754.0	774.3
12.5°	618.1	623.2	636.6	648.9	662.8	673.9	688.6	703.4	723.7	743.4	766.5
15°	572.6	586.2	601.4	616.0	632.5	646.2	663.9	679.1	698.5	726.1	752.4
17.5°	522.0	536.6	555.5	578.0	600.1	617.0	635.0	654.0	677.0	705.2	735.6
20°	492.6	504.3	525.3	550.4	576.1	599.6	616.0	637.0	660.8	691.2	722.6
22.5°	470.6	480.5	496.9	522.0	549.7	577.0	598.0	618.7	645.1	675.5	709.7
25°	437.4	448.3	462.5	479.6	511.4	540.2	567.9	591.6	619.5	650.0	688.0
27.5°	409.9	419.3	432.4	450.2	471.5	503.4	536.8	563.9	592.6	625.3	663.3
30°	393.6	401.3	412.1	430.2	450.5	479.0	512.9	544.7	573.6	607.5	647.1
32.5°	376.7	384.8	395.3	409.6	431.4	455.4	489.3	524.1	554.7	589.5	628.4
35°	354.0	360.4	369.9	384.5	404.1	425.1	455.2	491.1	523.4	560.5	597.6
37.5°	331.1	338.6	346.1	359.1	375.2	397.7	422.4	459.0	494.9	528.7	565.0
40°	318.1	322.6	330.8	341.4	358.5	378.5	401.6	437.4	473.3	507.0	543.4
42.5°	303.7	308.7	315.6	326.1	341.4	360.9	383.6	414.6	452.0	484.6	517.8
45°	283.6	286.4	293.4	302.3	315.0	334.7	355.6	383.2	418.4	449.5	478.7
47.5°	263.3	265.8	270.1	278.3	292.4	308.3	327.9	352.6	383.5	414.6	439.3
50°	249.3	251.5	255.7	263.3	276.0	291.6	310.9	333.0	360.7	390.5	411.1
52.5°	235.4	236.6	240.4	249.1	259.8	275.0	292.4	312.7	338.6	363.4	384.3
55°	213.2	216.1	218.6	224.9	235.1	249.6	265.2	284.5	304.5	325.5	343.2
57.5°	190.0	193.1	196.8	202.4	210.4	224.0	238.0	253.6	270.7	288.1	303.0
60°	174.8	177.7	180.8	187.2	194.4	205.2	220.5	234.1	247.1	262.9	277.9
62.5°	159.8	162.7	166.3	171.5	178.5	188.7	201.5	213.3	226.8	240.7	251.8
65°	137.7	139.9	142.8	147.5	154.2	163.4	173.8	183.0	195.1	205.2	215.4
67.5°	113.4	117.6	121.4	125.2	130.9	139.4	147.0	155.8	164.0	171.5	180.8
70°	97.3	102.2	105.7	109.7	115.1	122.5	129.7	135.7	142.4	149.7	158.0
72.5°	84.0	87.6	90.4	94.8	99.6	106.5	113.2	118.2	123.7	128.7	136.6
75°	66.3	67.9	69.8	73.3	77.7	82.8	88.2	92.6	95.8	100.2	106.0
77.5°	47.6	50.7	51.9	54.5	57.6	60.7	64.3	68.1	71.1	72.7	77.0
80°	36.4	37.7	39.1	42.5	44.4	47.6	50.1	53.6	54.9	56.5	60.6
82.5°	28.4	29.1	29.9	30.8	32.0	35.1	37.7	39.9	41.2	41.7	44.8
85°	16.5	16.8	17.1	17.4	17.8	17.8	19.0	20.6	22.8	22.8	23.8
87.5°	10.5	10.5	10.1	9.5	9.6	9.2	9.0	8.6	8.8	9.0	9.3
90°	24.7	23.2	21.4	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2
92.5°	23.8	22.4	20.5	18.7	16.8	14.9	13.9	13.8	13.6	13.5	13.3
95°	24.7	23.2	23.0	22.8	22.6	22.3	26.2	34.2	42.2	50.1	58.1
97.5°	28.0	27.9	54.1	80.4	106.6	132.8	143.4	138.4	133.5	128.5	123.5
100°	42.6	46.6	78.9	111.4	143.8	176.3	190.4	186.1	181.9	177.7	173.4
102.5°	181.1	224.2	228.4	232.7	236.8	241.1	241.7	238.6	235.5	232.4	229.3
105°	332.1	330.0	328.7	327.6	326.4	325.2	323.9	322.5	321.1	319.7	318.3
107.5°	412.4	411.4	409.8	408.1	406.6	405.0	403.8	403.1	402.4	401.7	401.0
110°	466.8	466.4	465.0	463.5	462.1	460.7	459.7	458.9	458.3	457.5	456.8



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	519.6	519.7	519.0	518.4	517.7	517.0	516.1	514.8	513.6	512.3	510.9
115°	596.9	596.4	596.6	596.9	597.1	597.4	597.1	596.4	595.7	595.0	594.3
117.5°	675.9	676.0	675.4	674.9	674.4	673.8	673.1	672.2	671.2	670.3	669.4
120°	723.8	723.3	723.6	723.8	724.1	724.2	723.9	723.0	722.0	721.1	720.2
122.5°	771.8	771.5	771.2	770.9	770.5	770.2	769.8	769.2	768.7	768.1	767.5
125°	838.2	837.6	838.0	838.5	838.9	839.4	839.2	838.2	837.3	836.3	835.4
127.5°	905.5	905.6	904.6	903.4	902.4	901.3	900.7	900.4	900.2	899.9	899.7
130°	945.7	945.4	944.7	944.0	943.3	942.6	942.1	941.8	941.7	941.4	941.2
132.5°	985.4	985.1	984.2	983.3	982.5	981.6	980.9	980.5	980.1	979.7	979.3
135°	1040.0	1039.5	1038.6	1037.6	1036.7	1035.8	1035.4	1035.7	1035.8	1036.1	1036.3
137.5°	1092.5	1091.9	1091.0	1089.9	1088.8	1087.9	1087.3	1087.2	1087.0	1087.0	1086.9
140°	1124.8	1124.1	1123.6	1123.2	1122.7	1122.3	1121.8	1121.3	1120.8	1120.4	1119.9
142.5°	1155.1	1154.5	1154.3	1154.0	1153.7	1153.4	1152.9	1152.0	1151.2	1150.3	1149.5
145°	1198.4	1198.2	1198.2	1198.2	1198.2	1198.2	1197.8	1197.1	1196.4	1195.6	1195.0
147.5°	1236.2	1236.0	1236.2	1236.5	1236.7	1237.0	1236.4	1235.1	1233.8	1232.4	1231.1
150°	1260.5	1260.5	1260.8	1261.0	1261.3	1261.4	1261.1	1260.2	1259.2	1258.3	1257.4
152.5°	1281.2	1280.8	1281.2	1281.7	1282.1	1282.5	1282.4	1281.6	1280.8	1280.1	1279.4
155°	1309.0	1308.1	1308.8	1309.5	1310.3	1310.9	1311.2	1310.9	1310.7	1310.4	1310.3
157.5°	1333.3	1332.0	1332.9	1333.6	1334.4	1335.2	1335.7	1335.8	1335.9	1336.1	1336.3
160°	1348.7	1347.3	1347.4	1347.7	1347.9	1348.2	1348.7	1349.3	1350.1	1350.8	1351.4
162.5°	1361.3	1359.9	1360.2	1360.4	1360.7	1360.9	1361.5	1362.4	1363.3	1364.1	1365.0
165°	1378.8	1376.9	1376.9	1376.9	1376.9	1376.9	1377.4	1378.6	1379.8	1381.0	1382.2
167.5°	1391.6	1389.5	1389.7	1389.8	1390.0	1390.1	1390.8	1392.0	1393.3	1394.5	1395.7
170°	1399.9	1398.0	1397.7	1397.5	1397.3	1397.1	1397.7	1399.1	1400.4	1401.9	1403.3
172.5°	1404.9	1403.0	1402.8	1402.6	1402.4	1402.2	1402.7	1404.1	1405.6	1407.0	1408.3
175°	1410.7	1408.6	1408.3	1408.1	1407.9	1407.6	1408.2	1409.7	1411.0	1412.4	1413.9
177.5°	1413.6	1412.2	1411.8	1411.4	1411.0	1410.6	1411.1	1412.4	1413.7	1415.1	1416.4
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	792.1	794.4	797.0	801.8	805.8	807.6	811.2	813.8	812.9	816.5	822.6
5°	795.2	803.8	813.7	823.8	835.2	844.7	852.4	860.0	866.0	873.3	884.1
7.5°	794.8	810.0	826.6	844.7	863.5	879.6	894.6	909.9	923.3	938.2	957.5
10°	792.7	813.0	833.6	857.5	881.3	903.8	924.1	943.1	961.2	980.5	1004.9
12.5°	790.4	813.8	838.7	867.3	897.0	924.1	947.9	975.3	997.9	1022.9	1051.2
15°	780.3	811.8	845.7	882.8	918.4	954.8	987.5	1021.2	1052.6	1082.3	1117.9
17.5°	768.8	805.0	845.1	888.9	931.6	975.9	1014.7	1057.1	1089.2	1129.2	1162.2
20°	759.5	798.4	841.2	890.4	939.0	988.1	1030.9	1074.1	1110.3	1150.6	1192.5
22.5°	748.0	790.8	837.2	888.1	939.0	992.7	1040.1	1083.0	1127.8	1173.1	1216.3
25°	729.6	774.0	823.2	879.0	937.3	992.2	1043.0	1096.3	1144.5	1193.7	1232.4
27.5°	707.0	753.7	805.5	863.1	923.0	979.2	1038.9	1095.8	1144.3	1191.6	1225.3
30°	689.0	738.2	788.0	846.4	908.5	968.8	1032.8	1089.6	1140.7	1183.2	1202.2
32.5°	670.5	717.1	768.4	827.5	891.3	956.1	1019.7	1077.7	1124.9	1150.5	1151.0
35°	638.2	682.0	735.3	793.4	858.7	929.1	993.5	1050.6	1079.5	1081.7	1050.6
37.5°	603.1	643.3	693.6	751.7	823.2	893.3	959.0	997.1	1006.8	974.5	917.0
40°	578.0	615.1	663.7	723.3	794.3	866.7	926.6	954.5	944.4	892.0	827.9
42.5°	551.5	586.1	632.9	691.8	763.1	836.2	887.3	902.2	875.3	814.9	739.9
45°	508.5	540.2	586.5	645.9	714.4	782.9	821.6	814.0	769.2	697.6	613.5
47.5°	463.7	494.3	536.0	590.8	661.0	720.2	746.3	723.4	659.7	580.9	512.5
50°	434.0	465.4	503.8	556.1	620.2	677.3	694.1	659.2	588.4	512.7	449.8
52.5°	404.8	431.6	469.2	519.8	581.1	629.3	638.2	598.0	525.0	457.1	401.4
55°	360.4	384.8	416.5	464.1	517.1	558.0	553.3	501.5	435.2	377.2	333.4
57.5°	317.4	335.8	365.1	409.7	456.2	483.7	466.3	422.2	360.4	312.9	276.0
60°	289.0	306.1	333.4	372.4	413.4	428.8	414.3	366.4	317.6	274.1	243.0
62.5°	262.1	277.2	300.7	336.9	369.9	379.1	363.5	321.7	277.7	240.6	214.8
65°	223.0	236.9	257.0	282.7	305.5	309.9	299.8	257.0	223.6	192.6	174.8
67.5°	187.5	196.7	212.3	234.5	246.6	249.2	229.6	202.7	173.3	154.3	140.9
70°	163.7	170.0	184.6	196.7	206.5	206.8	188.7	167.1	144.6	129.1	119.3
72.5°	140.6	146.7	157.8	166.0	173.5	171.0	154.5	137.5	119.3	107.5	100.2
75°	108.5	113.9	119.6	123.4	123.4	120.3	108.2	95.5	85.0	78.0	75.8
77.5°	78.8	83.3	85.2	84.6	83.5	78.5	70.9	62.6	58.9	55.6	53.9
80°	61.9	63.8	64.4	62.8	60.9	55.2	50.1	46.6	43.1	41.9	41.3
82.5°	45.9	47.5	45.9	46.3	42.2	37.4	34.7	33.4	32.0	31.5	30.8
85°	24.5	24.1	23.5	21.9	19.0	18.4	18.1	17.8	17.1	17.4	16.8
87.5°	9.5	9.3	8.8	9.0	9.5	9.4	10.0	10.4	10.8	10.8	11.6
90°	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1
92.5°	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8	25.3
95°	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7	26.1
97.5°	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0	28.2
100°	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6	38.6
102.5°	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1	138.0
105°	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1	334.2
107.5°	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4	413.4
110°	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8	467.3



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6	519.4
115°	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9	597.4
117.5°	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9	675.7
120°	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8	724.2
122.5°	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8	772.1
125°	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2	838.9
127.5°	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5	905.4
130°	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7	945.8
132.5°	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4	985.6
135°	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0	1040.5
137.5°	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5	1093.0
140°	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8	1125.5
142.5°	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1	1155.6
145°	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4	1198.6
147.5°	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2	1236.4
150°	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5	1260.5
152.5°	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2	1281.6
155°	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0	1310.0
157.5°	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3	1334.5
160°	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7	1350.1
162.5°	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3	1362.8
165°	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8	1380.6
167.5°	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6	1393.7
170°	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9	1401.7
172.5°	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9	1406.8
175°	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7	1412.8
177.5°	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6	1415.2
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	825.9	827.0	827.7	830.2	830.5	832.7	830.5
5°	894.2	898.7	905.6	912.6	913.3	917.7	909.8
7.5°	970.9	981.1	987.6	998.8	1003.3	1006.1	1001.5
10°	1023.7	1033.1	1050.0	1058.3	1066.5	1067.7	1064.0
12.5°	1074.6	1089.7	1103.0	1118.7	1118.3	1129.4	1125.4
15°	1142.6	1158.1	1176.6	1194.0	1200.4	1200.4	1205.4
17.5°	1191.1	1219.6	1238.6	1252.3	1267.3	1269.9	1268.1
20°	1223.8	1254.6	1274.9	1292.7	1302.8	1305.7	1305.7
22.5°	1248.2	1274.4	1294.2	1310.2	1318.6	1321.9	1320.9
25°	1265.1	1287.6	1299.7	1304.4	1306.6	1305.9	1300.0
27.5°	1241.9	1241.0	1233.3	1218.7	1207.8	1201.1	1193.5
30°	1197.8	1181.3	1162.3	1141.3	1114.4	1093.7	1087.4
32.5°	1132.1	1095.0	1062.8	1027.9	998.9	978.3	969.6
35°	1004.9	946.2	898.4	856.5	826.1	807.0	800.6
37.5°	854.1	797.3	738.0	697.4	672.1	652.9	645.7
40°	758.1	696.3	644.6	606.5	580.5	561.8	561.5
42.5°	670.6	611.6	562.9	535.5	507.4	495.0	495.0
45°	549.1	501.8	460.6	439.0	422.2	412.1	409.2
47.5°	454.6	415.6	388.1	370.9	357.2	350.7	346.5
50°	401.6	367.4	345.4	330.5	322.9	314.7	314.1
52.5°	357.4	329.8	312.7	300.6	291.0	286.0	286.2
55°	300.4	278.5	266.4	257.2	249.6	245.8	244.3
57.5°	253.1	236.7	227.9	219.5	216.2	213.2	212.4
60°	223.6	212.5	204.3	197.6	192.9	191.9	191.6
62.5°	199.3	187.7	182.0	176.8	173.3	171.9	171.3
65°	164.3	155.7	150.7	146.6	145.3	143.1	142.8
67.5°	132.5	127.3	124.0	121.2	119.4	119.3	119.3
70°	112.9	110.1	107.2	105.7	104.7	104.0	104.0
72.5°	96.2	94.1	91.7	90.9	90.7	90.1	89.8
75°	73.3	71.1	71.3	69.8	68.5	66.9	66.0
77.5°	51.9	50.4	50.1	49.9	48.8	48.6	49.1
80°	40.3	38.7	38.4	38.7	38.4	37.4	37.4
82.5°	30.7	29.4	29.0	28.8	28.5	28.8	28.3
85°	16.5	15.9	15.9	15.9	16.5	16.1	15.9
87.5°	11.3	11.3	11.8	11.7	11.7	11.6	11.9
90°	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P333047-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)