

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333051-930

Luminaire Tested: **S124RDIW-S575D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333051-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1560U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7079.9 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - · 135°-315°



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	14	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6356	6356	6356	6356
5°	7373	6375	5635	6375
10°	8722	6347	5029	6347
15°	10074	6288	4322	6288
20°	11217	6208	3908	6208
25°	11580	6128	3628	6128
30°	10137	6032	3459	6032
35°	7890	5889	3358	5889
40°	5917	5727	3303	5727
45°	4672	5465	3273	5465
50°	3945	5163	3180	5163
55°	3438	4830	3009	4830
60°	3094	4487	2662	4487
65°	2728	4115	2290	4115
70°	2455	3729	2068	3729
75°	2059	3306	1762	3306
80°	1739	2817	1650	2817
85°	1473	2205	1473	2205



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	1.1
10°-20°	230.1	3.3
20°-30°	359.9	5.1
30°-40°	400.1	5.7
40°-50°	355.0	5.0
50°-60°	276.6	3.9
60°-70°	181.1	2.6
70°-80°	89.1	1.3
80°-90°	26.7	0.4
90°-100°	56.2	0.8
100°-110°	358.5	5.1
110°-120°	685.8	9.7
120°-130°	870.5	12.3
130°-140°	931.4	13.2
140°-150°	871.0	12.3
150°-160°	702.4	9.9
160°-170°	453.0	6.4
170°-180°	156.1	2.2
0°-30°	666.3	9.4
0°-40°	1066.4	15.1
0°-60°	1698.1	24.0
0°-90°	1994.9	28.2
90°-120°	1100.5	15.5
90°-150°	3773.4	53.3
90°-180°	5085.0	71.8
0°-180°	7079.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	910	787	695	787	910	92
15°	1205	752	517	752	1205	343
25°	1300	688	407	688	1300	577
35°	801	598	341	598	801	502
45°	409	479	287	479	409	324
55°	244	343	214	343	244	222
65°	143	215	120	215	143	144
75°	66	106	56	106	66	73
85°	16	24	16	24	16	19
90°	37	4	37	4	37	17
95°	36	68	36	68	36	28
105°	350	370	350	370	350	306
115°	696	691	696	691	696	689
125°	979	971	979	971	979	872
135°	1214	1205	1214	1205	1214	934
145°	1397	1389	1397	1389	1397	873
155°	1522	1523	1522	1523	1522	702
165°	1600	1607	1600	1607	1600	452
175°	1634	1644	1634	1644	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	830.5	832.7	830.5	830.2	827.7	827.0	825.9	822.6	816.5	812.9	813.8
5°	909.8	917.7	913.3	912.6	905.6	898.7	894.2	884.1	873.3	866.0	860.0
7.5°	1001.5	1006.1	1003.3	998.8	987.6	981.1	970.9	957.5	938.2	923.3	909.9
10°	1064.0	1067.7	1066.5	1058.3	1050.0	1033.1	1023.7	1004.9	980.5	961.2	943.1
12.5°	1125.4	1129.4	1118.3	1118.7	1103.0	1089.7	1074.6	1051.2	1022.9	997.9	975.3
15°	1205.4	1200.4	1200.4	1194.0	1176.6	1158.1	1142.6	1117.9	1082.3	1052.6	1021.2
17.5°	1268.1	1269.9	1267.3	1252.3	1238.6	1219.6	1191.1	1162.2	1129.2	1089.2	1057.1
20°	1305.7	1305.7	1302.8	1292.7	1274.9	1254.6	1223.8	1192.5	1150.6	1110.3	1074.1
22.5°	1320.9	1321.9	1318.6	1310.2	1294.2	1274.4	1248.2	1216.3	1173.1	1127.8	1083.0
25°	1300.0	1305.9	1306.6	1304.4	1299.7	1287.6	1265.1	1232.4	1193.7	1144.5	1096.3
27.5°	1193.5	1201.1	1207.8	1218.7	1233.3	1241.0	1241.9	1225.3	1191.6	1144.3	1095.8
30°	1087.4	1093.7	1114.4	1141.3	1162.3	1181.3	1197.8	1202.2	1183.2	1140.7	1089.6
32.5°	969.6	978.3	998.9	1027.9	1062.8	1095.0	1132.1	1151.0	1150.5	1124.9	1077.7
35°	800.6	807.0	826.1	856.5	898.4	946.2	1004.9	1050.6	1081.7	1079.5	1050.6
37.5°	645.7	652.9	672.1	697.4	738.0	797.3	854.1	917.0	974.5	1006.8	997.1
40°	561.5	561.8	580.5	606.5	644.6	696.3	758.1	827.9	892.0	944.4	954.5
42.5°	495.0	495.0	507.4	535.5	562.9	611.6	670.6	739.9	814.9	875.3	902.2
45°	409.2	412.1	422.2	439.0	460.6	501.8	549.1	613.5	697.6	769.2	814.0
47.5°	346.5	350.7	357.2	370.9	388.1	415.6	454.6	512.5	580.9	659.7	723.4
50°	314.1	314.7	322.9	330.5	345.4	367.4	401.6	449.8	512.7	588.4	659.2
52.5°	286.2	286.0	291.0	300.6	312.7	329.8	357.4	401.4	457.1	525.0	598.0
55°	244.3	245.8	249.6	257.2	266.4	278.5	300.4	333.4	377.2	435.2	501.5
57.5°	212.4	213.2	216.2	219.5	227.9	236.7	253.1	276.0	312.9	360.4	422.2
60°	191.6	191.9	192.9	197.6	204.3	212.5	223.6	243.0	274.1	317.6	366.4
62.5°	171.3	171.9	173.3	176.8	182.0	187.7	199.3	214.8	240.6	277.7	321.7
65°	142.8	143.1	145.3	146.6	150.7	155.7	164.3	174.8	192.6	223.6	257.0
67.5°	119.3	119.3	119.4	121.2	124.0	127.3	132.5	140.9	154.3	173.3	202.7
70°	104.0	104.0	104.7	105.7	107.2	110.1	112.9	119.3	129.1	144.6	167.1
72.5°	89.8	90.1	90.7	90.9	91.7	94.1	96.2	100.2	107.5	119.3	137.5
75°	66.0	66.9	68.5	69.8	71.3	71.1	73.3	75.8	78.0	85.0	95.5
77.5°	49.1	48.6	48.8	49.9	50.1	50.4	51.9	53.9	55.6	58.9	62.6
80°	37.4	37.4	38.4	38.7	38.4	38.7	40.3	41.3	41.9	43.1	46.6
82.5°	28.3	28.8	28.5	28.8	29.0	29.4	30.7	30.8	31.5	32.0	33.4
85°	15.9	16.1	16.5	15.9	15.9	15.9	16.5	16.8	17.4	17.1	17.8
87.5°	13.0	12.6	12.7	12.6	12.8	12.3	12.2	12.4	11.6	11.5	11.1
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4	27.7	26.1	23.9
95°	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3	28.7	27.1	26.7
97.5°	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8	32.6	32.4	62.9
100°	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8	49.5	54.1	91.8
102.5°	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5	210.5	260.7	265.5
105°	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5	386.0	383.6	382.2
107.5°	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7	479.5	478.3	476.4
110°	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3	542.7	542.2	540.5



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0	604.1	604.2	603.4
115°	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6	694.0	693.4	693.7
117.5°	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7	785.8	785.9	785.3
120°	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0	841.2
122.5°	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7	897.4	897.1	896.7
125°	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4	974.6	973.8	974.3
127.5°	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6	1052.8	1053.0	1051.7
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8	1099.4	1099.2	1098.4
132.5°	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0	1145.7	1145.4	1144.4
135°	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7	1209.2	1208.6	1207.5
137.5°	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8	1270.2	1269.6	1268.4
140°	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6	1307.8	1306.9	1306.4
142.5°	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6	1343.0	1342.4	1342.1
145°	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6	1393.3	1393.0	1393.0
147.5°	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5	1437.3	1437.0	1437.3
150°	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6	1465.6	1465.6	1465.8
152.5°	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0	1489.6	1489.1	1489.6
155°	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1	1522.0	1520.9	1521.8
157.5°	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7	1549.6
160°	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4	1566.7
162.5°	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5	1582.7	1581.1	1581.4
165°	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2	1603.0	1600.8	1600.8
167.5°	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4	1618.0	1615.6	1615.8
170°	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8	1627.6	1625.4	1625.1
172.5°	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7	1633.5	1631.3	1631.0
175°	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6	1640.1	1637.7	1637.4
177.5°	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4	1643.6	1641.8	1641.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	811.2	807.6	805.8	801.8	797.0	794.4	792.1	788.9	784.6	780.0	776.7
5°	852.4	844.7	835.2	823.8	813.7	803.8	795.2	786.7	776.9	766.7	756.6
7.5°	894.6	879.6	863.5	844.7	826.6	810.0	794.8	780.2	763.7	748.9	735.4
10°	924.1	903.8	881.3	857.5	833.6	813.0	792.7	774.3	754.0	736.0	720.7
12.5°	947.9	924.1	897.0	867.3	838.7	813.8	790.4	766.5	743.4	723.7	703.4
15°	987.5	954.8	918.4	882.8	845.7	811.8	780.3	752.4	726.1	698.5	679.1
17.5°	1014.7	975.9	931.6	888.9	845.1	805.0	768.8	735.6	705.2	677.0	654.0
20°	1030.9	988.1	939.0	890.4	841.2	798.4	759.5	722.6	691.2	660.8	637.0
22.5°	1040.1	992.7	939.0	888.1	837.2	790.8	748.0	709.7	675.5	645.1	618.7
25°	1043.0	992.2	937.3	879.0	823.2	774.0	729.6	688.0	650.0	619.5	591.6
27.5°	1038.9	979.2	923.0	863.1	805.5	753.7	707.0	663.3	625.3	592.6	563.9
30°	1032.8	968.8	908.5	846.4	788.0	738.2	689.0	647.1	607.5	573.6	544.7
32.5°	1019.7	956.1	891.3	827.5	768.4	717.1	670.5	628.4	589.5	554.7	524.1
35°	993.5	929.1	858.7	793.4	735.3	682.0	638.2	597.6	560.5	523.4	491.1
37.5°	959.0	893.3	823.2	751.7	693.6	643.3	603.1	565.0	528.7	494.9	459.0
40°	926.6	866.7	794.3	723.3	663.7	615.1	578.0	543.4	507.0	473.3	437.4
42.5°	887.3	836.2	763.1	691.8	632.9	586.1	551.5	517.8	484.6	452.0	414.6
45°	821.6	782.9	714.4	645.9	586.5	540.2	508.5	478.7	449.5	418.4	383.2
47.5°	746.3	720.2	661.0	590.8	536.0	494.3	463.7	439.3	414.6	383.5	352.6
50°	694.1	677.3	620.2	556.1	503.8	465.4	434.0	411.1	390.5	360.7	333.0
52.5°	638.2	629.3	581.1	519.8	469.2	431.6	404.8	384.3	363.4	338.6	312.7
55°	553.3	558.0	517.1	464.1	416.5	384.8	360.4	343.2	325.5	304.5	284.5
57.5°	466.3	483.7	456.2	409.7	365.1	335.8	317.4	303.0	288.1	270.7	253.6
60°	414.3	428.8	413.4	372.4	333.4	306.1	289.0	277.9	262.9	247.1	234.1
62.5°	363.5	379.1	369.9	336.9	300.7	277.2	262.1	251.8	240.7	226.8	213.3
65°	299.8	309.9	305.5	282.7	257.0	236.9	223.0	215.4	205.2	195.1	183.0
67.5°	229.6	249.2	246.6	234.5	212.3	196.7	187.5	180.8	171.5	164.0	155.8
70°	188.7	206.8	206.5	196.7	184.6	170.0	163.7	158.0	149.7	142.4	135.7
72.5°	154.5	171.0	173.5	166.0	157.8	146.7	140.6	136.6	128.7	123.7	118.2
75°	108.2	120.3	123.4	123.4	119.6	113.9	108.5	106.0	100.2	95.8	92.6
77.5°	70.9	78.5	83.5	84.6	85.2	83.3	78.8	77.0	72.7	71.1	68.1
80°	50.1	55.2	60.9	62.8	64.4	63.8	61.9	60.6	56.5	54.9	53.6
82.5°	34.7	37.4	42.2	46.3	45.9	47.5	45.9	44.8	41.7	41.2	39.9
85°	18.1	18.4	19.0	21.9	23.5	24.1	24.5	23.8	22.8	22.8	20.6
87.5°	10.6	9.9	10.0	9.5	9.1	9.5	9.7	9.4	9.2	9.0	8.9
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5	15.7	15.8	16.0
95°	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6	58.3	49.1	39.8
97.5°	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6	149.4	155.2	161.0
100°	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6	206.6	211.5	216.4
102.5°	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5	270.2	273.8	277.4
105°	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1	371.7	373.3	375.0
107.5°	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2	467.1	467.9	468.7
110°	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2	532.0	532.8	533.6



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1	595.6	597.0	598.5
115°	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0	691.8	692.6	693.4
117.5°	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3	779.3	780.5	781.5
120°	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3	838.4	839.5	840.6
122.5°	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3	893.0	893.6	894.3
125°	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3	972.4	973.5	974.6
127.5°	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0	1046.4	1046.6	1046.8
130°	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3	1094.5	1094.8	1095.1
132.5°	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5	1139.0	1139.5	1140.0
135°	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9	1204.6	1204.4	1204.1
137.5°	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7	1263.8	1263.9	1264.0
140°	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0	1302.6	1303.2	1303.7
142.5°	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5
145°	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4	1390.2	1391.0	1391.8
147.5°	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4	1432.9	1434.4	1436.0
150°	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9	1463.0	1464.0	1465.2
152.5°	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4	1488.3	1489.2	1490.0
155°	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4	1523.6	1523.9	1524.2
157.5°	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6	1553.5	1553.3	1553.1
160°	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3	1570.5	1569.7	1568.9
162.5°	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1	1586.0	1584.9	1584.0
165°	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0	1605.6	1604.3	1602.9
167.5°	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7	1621.3	1619.8	1618.5
170°	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6	1629.9	1628.2	1626.6
172.5°	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4	1635.8	1634.2	1632.6
175°	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8	1642.2	1640.5	1638.9
177.5°	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8	1645.3	1643.7	1642.2
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	773.1	770.6	767.3	763.4	758.9	754.9	753.1	754.6	755.4	753.3	753.1
5°	749.6	741.7	735.3	725.8	718.2	711.8	707.4	705.5	706.1	701.1	699.8
7.5°	723.1	713.7	703.4	692.0	681.5	672.2	667.3	664.6	659.3	657.0	653.1
10°	706.1	693.4	683.3	669.9	657.9	646.8	641.4	637.0	631.6	629.0	623.6
12.5°	688.6	673.9	662.8	648.9	636.6	623.2	618.1	609.8	601.4	596.1	589.1
15°	663.9	646.2	632.5	616.0	601.4	586.2	572.6	557.3	551.6	539.6	532.6
17.5°	635.0	617.0	600.1	578.0	555.5	536.6	522.0	507.5	498.7	491.1	487.5
20°	616.0	599.6	576.1	550.4	525.3	504.3	492.6	483.1	473.6	468.2	464.4
22.5°	598.0	577.0	549.7	522.0	496.9	480.5	470.6	460.8	453.1	447.9	442.9
25°	567.9	540.2	511.4	479.6	462.5	448.3	437.4	429.5	424.8	418.1	415.6
27.5°	536.8	503.4	471.5	450.2	432.4	419.3	409.9	404.0	397.9	393.6	390.4
30°	512.9	479.0	450.5	430.2	412.1	401.3	393.6	386.7	382.0	378.5	375.9
32.5°	489.3	455.4	431.4	409.6	395.3	384.8	376.7	371.5	367.7	363.2	361.7
35°	455.2	425.1	404.1	384.5	369.9	360.4	354.0	348.6	345.4	344.2	343.2
37.5°	422.4	397.7	375.2	359.1	346.1	338.6	331.1	328.5	326.3	324.0	325.1
40°	401.6	378.5	358.5	341.4	330.8	322.6	318.1	315.0	313.1	313.1	313.1
42.5°	383.6	360.9	341.4	326.1	315.6	308.7	303.7	301.0	300.4	300.1	301.7
45°	355.6	334.7	315.0	302.3	293.4	286.4	283.6	281.4	281.4	282.7	283.0
47.5°	327.9	308.3	292.4	278.3	270.1	265.8	263.3	262.1	262.3	263.5	265.0
50°	310.9	291.6	276.0	263.3	255.7	251.5	249.3	248.7	249.3	249.3	251.5
52.5°	292.4	275.0	259.8	249.1	240.4	236.6	235.4	234.5	234.9	235.9	236.8
55°	265.2	249.6	235.1	224.9	218.6	216.1	213.2	213.5	212.9	213.5	213.5
57.5°	238.0	224.0	210.4	202.4	196.8	193.1	190.0	190.9	190.0	189.8	189.3
60°	220.5	205.2	194.4	187.2	180.8	177.7	174.8	175.5	174.5	173.8	172.6
62.5°	201.5	188.7	178.5	171.5	166.3	162.7	159.8	159.1	156.9	154.8	152.0
65°	173.8	163.4	154.2	147.5	142.8	139.9	137.7	135.7	131.0	126.0	123.4
67.5°	147.0	139.4	130.9	125.2	121.4	117.6	113.4	110.1	105.7	102.9	101.3
70°	129.7	122.5	115.1	109.7	105.7	102.2	97.3	95.1	92.0	90.7	89.1
72.5°	113.2	106.5	99.6	94.8	90.4	87.6	84.0	81.7	80.3	79.8	78.2
75°	88.2	82.8	77.7	73.3	69.8	67.9	66.3	64.7	64.1	61.2	59.6
77.5°	64.3	60.7	57.6	54.5	51.9	50.7	47.6	45.8	44.8	43.4	43.0
80°	50.1	47.6	44.4	42.5	39.1	37.7	36.4	36.2	35.9	35.5	35.2
82.5°	37.7	35.1	32.0	30.8	29.9	29.1	28.4	28.0	27.7	27.9	27.9
85°	19.0	17.8	17.8	17.4	17.1	16.8	16.5	16.5	16.1	16.5	16.1
87.5°	9.5	9.8	10.2	10.1	10.8	11.3	11.3	11.7	12.2	12.1	12.2
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4	31.0	32.6	33.5
95°	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3	32.0	33.6	34.6
97.5°	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8	32.9	33.1	33.3
100°	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8	40.2	35.5	33.3
102.5°	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5	110.3	60.3	35.2
105°	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5	391.0	393.5	389.7
107.5°	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7	481.9	483.1	484.2
110°	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3	543.9	544.4	545.1



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0	603.8	603.7	604.2
115°	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6	695.0	695.6	695.9
117.5°	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7	785.5	785.5	785.4
120°	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0	842.6	843.2	843.2
122.5°	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7	898.1	898.4	898.2
125°	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4	976.2	977.1	977.6
127.5°	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6	1052.5	1052.3	1052.1
130°	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8	1100.0	1100.2	1100.4
132.5°	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0	1146.2	1146.5	1146.6
135°	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7	1210.2	1210.8	1211.4
137.5°	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8	1271.4	1272.0	1272.2
140°	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6	1309.5	1310.3	1310.8
142.5°	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6	1344.2	1344.8	1345.1
145°	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6	1393.8	1394.1	1394.6
147.5°	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5	1437.7	1437.9	1438.2
150°	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6	1465.6	1465.6	1465.7
152.5°	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0	1490.4	1490.9	1491.0
155°	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1	1524.2	1525.3	1525.4
157.5°	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4
160°	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0
162.5°	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5	1586.1	1587.7	1587.6
165°	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2	1607.4	1609.6	1609.4
167.5°	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4	1622.8	1625.2	1625.1
170°	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8	1632.0	1634.2	1633.9
172.5°	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7	1637.9	1640.1	1639.6
175°	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6	1645.1	1647.6	1647.1
177.5°	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4	1647.1	1648.9	1648.5
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	751.5	752.0	750.3	749.7	750.3	752.0	751.5	753.1	753.3	755.4	754.6
5°	697.2	696.6	695.0	695.4	695.0	696.6	697.2	699.8	701.1	706.1	705.5
7.5°	650.8	648.3	649.1	646.5	649.1	648.3	650.8	653.1	657.0	659.3	664.6
10°	622.4	618.9	616.0	613.5	616.0	618.9	622.4	623.6	629.0	631.6	637.0
12.5°	583.6	580.6	576.7	577.5	576.7	580.6	583.6	589.1	596.1	601.4	609.8
15°	528.5	523.7	516.1	517.1	516.1	523.7	528.5	532.6	539.6	551.6	557.3
17.5°	481.8	481.9	478.4	479.2	478.4	481.9	481.8	487.5	491.1	498.7	507.5
20°	457.7	455.5	455.8	454.9	455.8	455.5	457.7	464.4	468.2	473.6	483.1
22.5°	441.0	438.3	436.0	434.1	436.0	438.3	441.0	442.9	447.9	453.1	460.8
25°	412.7	410.8	408.0	407.3	408.0	410.8	412.7	415.6	418.1	424.8	429.5
27.5°	387.8	387.4	386.3	384.8	386.3	387.4	387.8	390.4	393.6	397.9	404.0
30°	373.3	372.8	372.1	371.1	372.1	372.8	373.3	375.9	378.5	382.0	386.7
32.5°	360.4	360.0	359.4	359.5	359.4	360.0	360.4	361.7	363.2	367.7	371.5
35°	341.9	341.6	341.0	340.7	341.0	341.6	341.9	343.2	344.2	345.4	348.6
37.5°	324.7	325.5	325.1	325.1	325.1	325.5	324.7	325.1	324.0	326.3	328.5
40°	312.7	313.1	313.7	313.4	313.7	313.1	312.7	313.1	313.1	313.1	315.0
42.5°	302.9	303.0	303.9	302.7	303.9	303.0	302.9	301.7	300.1	300.4	301.0
45°	285.2	287.1	286.7	286.7	286.7	287.1	285.2	283.0	282.7	281.4	281.4
47.5°	265.8	267.5	267.9	267.8	267.9	267.5	265.8	265.0	263.5	262.3	262.1
50°	253.2	252.5	253.5	253.2	253.5	252.5	253.2	251.5	249.3	249.3	248.7
52.5°	237.7	237.8	237.7	237.4	237.7	237.8	237.7	236.8	235.9	234.9	234.5
55°	213.8	214.1	213.5	213.8	213.5	214.1	213.8	213.5	213.5	212.9	213.5
57.5°	187.9	186.4	187.0	186.3	187.0	186.4	187.9	189.3	189.8	190.0	190.9
60°	169.4	166.9	166.2	164.9	166.2	166.9	169.4	172.6	173.8	174.5	175.5
62.5°	148.5	146.8	144.6	145.7	144.6	146.8	148.5	152.0	154.8	156.9	159.1
65°	120.8	119.6	118.6	119.9	118.6	119.6	120.8	123.4	126.0	131.0	135.7
67.5°	100.0	99.4	99.4	98.7	99.4	99.4	100.0	101.3	102.9	105.7	110.1
70°	89.1	88.2	88.2	87.6	88.2	88.2	89.1	89.1	90.7	92.0	95.1
72.5°	77.9	77.0	77.3	76.9	77.3	77.0	77.9	78.2	79.8	80.3	81.7
75°	57.7	56.2	56.2	56.5	56.2	56.2	57.7	59.6	61.2	64.1	64.7
77.5°	43.0	42.7	43.2	42.6	43.2	42.7	43.0	43.0	43.4	44.8	45.8
80°	35.2	34.9	34.6	35.5	34.6	34.9	35.2	35.2	35.5	35.9	36.2
82.5°	27.3	27.3	27.2	28.5	27.2	27.3	27.3	27.9	27.9	27.7	28.0
85°	16.5	15.9	16.5	15.9	16.5	15.9	16.5	16.1	16.5	16.1	16.5
87.5°	12.9	12.7	12.6	13.0	12.6	12.7	12.9	12.2	12.1	12.2	11.7
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	33.6	33.8	33.8	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4
95°	34.8	35.1	35.4	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3
97.5°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8
100°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8
102.5°	35.2	35.3	35.4	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5
105°	379.9	370.1	360.3	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5
107.5°	485.3	486.2	487.3	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7
110°	545.9	546.7	547.6	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	605.3	606.3	607.3	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0
115°	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6
117.5°	785.2	785.1	785.1	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7
120°	842.6	842.0	841.6	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0
122.5°	897.7	897.2	896.6	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7
125°	977.9	978.1	978.4	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4
127.5°	1051.9	1051.7	1051.4	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8
132.5°	1146.3	1146.1	1145.9	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0
135°	1211.9	1212.4	1213.0	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7
137.5°	1272.0	1271.9	1271.7	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8
140°	1311.1	1311.3	1311.6	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6
142.5°	1345.2	1345.2	1345.2	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6
145°	1395.1	1395.6	1396.2	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6
147.5°	1438.4	1438.7	1439.0	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5
150°	1466.0	1466.2	1466.6	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6
152.5°	1490.9	1490.7	1490.5	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0
155°	1524.6	1523.8	1523.0	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1
157.5°	1553.0	1551.5	1550.1	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5
160°	1571.3	1569.7	1568.1	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7
162.5°	1585.8	1583.9	1582.0	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5
165°	1607.0	1604.5	1602.1	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2
167.5°	1622.3	1619.6	1616.8	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4
170°	1631.2	1628.4	1625.7	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8
172.5°	1636.7	1633.8	1630.8	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7
175°	1643.8	1640.5	1637.3	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6
177.5°	1645.8	1643.2	1640.5	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	753.1	754.9	758.9	763.4	767.3	770.6	773.1	776.7	780.0	784.6	788.9
5°	707.4	711.8	718.2	725.8	735.3	741.7	749.6	756.6	766.7	776.9	786.7
7.5°	667.3	672.2	681.5	692.0	703.4	713.7	723.1	735.4	748.9	763.7	780.2
10°	641.4	646.8	657.9	669.9	683.3	693.4	706.1	720.7	736.0	754.0	774.3
12.5°	618.1	623.2	636.6	648.9	662.8	673.9	688.6	703.4	723.7	743.4	766.5
15°	572.6	586.2	601.4	616.0	632.5	646.2	663.9	679.1	698.5	726.1	752.4
17.5°	522.0	536.6	555.5	578.0	600.1	617.0	635.0	654.0	677.0	705.2	735.6
20°	492.6	504.3	525.3	550.4	576.1	599.6	616.0	637.0	660.8	691.2	722.6
22.5°	470.6	480.5	496.9	522.0	549.7	577.0	598.0	618.7	645.1	675.5	709.7
25°	437.4	448.3	462.5	479.6	511.4	540.2	567.9	591.6	619.5	650.0	688.0
27.5°	409.9	419.3	432.4	450.2	471.5	503.4	536.8	563.9	592.6	625.3	663.3
30°	393.6	401.3	412.1	430.2	450.5	479.0	512.9	544.7	573.6	607.5	647.1
32.5°	376.7	384.8	395.3	409.6	431.4	455.4	489.3	524.1	554.7	589.5	628.4
35°	354.0	360.4	369.9	384.5	404.1	425.1	455.2	491.1	523.4	560.5	597.6
37.5°	331.1	338.6	346.1	359.1	375.2	397.7	422.4	459.0	494.9	528.7	565.0
40°	318.1	322.6	330.8	341.4	358.5	378.5	401.6	437.4	473.3	507.0	543.4
42.5°	303.7	308.7	315.6	326.1	341.4	360.9	383.6	414.6	452.0	484.6	517.8
45°	283.6	286.4	293.4	302.3	315.0	334.7	355.6	383.2	418.4	449.5	478.7
47.5°	263.3	265.8	270.1	278.3	292.4	308.3	327.9	352.6	383.5	414.6	439.3
50°	249.3	251.5	255.7	263.3	276.0	291.6	310.9	333.0	360.7	390.5	411.1
52.5°	235.4	236.6	240.4	249.1	259.8	275.0	292.4	312.7	338.6	363.4	384.3
55°	213.2	216.1	218.6	224.9	235.1	249.6	265.2	284.5	304.5	325.5	343.2
57.5°	190.0	193.1	196.8	202.4	210.4	224.0	238.0	253.6	270.7	288.1	303.0
60°	174.8	177.7	180.8	187.2	194.4	205.2	220.5	234.1	247.1	262.9	277.9
62.5°	159.8	162.7	166.3	171.5	178.5	188.7	201.5	213.3	226.8	240.7	251.8
65°	137.7	139.9	142.8	147.5	154.2	163.4	173.8	183.0	195.1	205.2	215.4
67.5°	113.4	117.6	121.4	125.2	130.9	139.4	147.0	155.8	164.0	171.5	180.8
70°	97.3	102.2	105.7	109.7	115.1	122.5	129.7	135.7	142.4	149.7	158.0
72.5°	84.0	87.6	90.4	94.8	99.6	106.5	113.2	118.2	123.7	128.7	136.6
75°	66.3	67.9	69.8	73.3	77.7	82.8	88.2	92.6	95.8	100.2	106.0
77.5°	47.6	50.7	51.9	54.5	57.6	60.7	64.3	68.1	71.1	72.7	77.0
80°	36.4	37.7	39.1	42.5	44.4	47.6	50.1	53.6	54.9	56.5	60.6
82.5°	28.4	29.1	29.9	30.8	32.0	35.1	37.7	39.9	41.2	41.7	44.8
85°	16.5	16.8	17.1	17.4	17.8	17.8	19.0	20.6	22.8	22.8	23.8
87.5°	11.3	11.3	10.8	10.1	10.2	9.8	9.5	8.9	9.0	9.2	9.4
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	27.7	26.1	23.9	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5
95°	28.7	27.1	26.7	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6
97.5°	32.6	32.4	62.9	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6
100°	49.5	54.1	91.8	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6
102.5°	210.5	260.7	265.5	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5
105°	386.0	383.6	382.2	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1
107.5°	479.5	478.3	476.4	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2
110°	542.7	542.2	540.5	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	604.1	604.2	603.4	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1
115°	694.0	693.4	693.7	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0
117.5°	785.8	785.9	785.3	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3
120°	841.6	841.0	841.2	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3
122.5°	897.4	897.1	896.7	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3
125°	974.6	973.8	974.3	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3
127.5°	1052.8	1053.0	1051.7	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0
130°	1099.4	1099.2	1098.4	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3
132.5°	1145.7	1145.4	1144.4	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5
135°	1209.2	1208.6	1207.5	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9
137.5°	1270.2	1269.6	1268.4	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7
140°	1307.8	1306.9	1306.4	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0
142.5°	1343.0	1342.4	1342.1	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4
145°	1393.3	1393.0	1393.0	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4
147.5°	1437.3	1437.0	1437.3	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4
150°	1465.6	1465.6	1465.8	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9
152.5°	1489.6	1489.1	1489.6	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4
155°	1522.0	1520.9	1521.8	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4
157.5°	1550.1	1548.7	1549.6	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6
160°	1568.1	1566.4	1566.7	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3
162.5°	1582.7	1581.1	1581.4	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1
165°	1603.0	1600.8	1600.8	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0
167.5°	1618.0	1615.6	1615.8	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7
170°	1627.6	1625.4	1625.1	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6
172.5°	1633.5	1631.3	1631.0	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4
175°	1640.1	1637.7	1637.4	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8
177.5°	1643.6	1641.8	1641.4	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	792.1	794.4	797.0	801.8	805.8	807.6	811.2	813.8	812.9	816.5	822.6
5°	795.2	803.8	813.7	823.8	835.2	844.7	852.4	860.0	866.0	873.3	884.1
7.5°	794.8	810.0	826.6	844.7	863.5	879.6	894.6	909.9	923.3	938.2	957.5
10°	792.7	813.0	833.6	857.5	881.3	903.8	924.1	943.1	961.2	980.5	1004.9
12.5°	790.4	813.8	838.7	867.3	897.0	924.1	947.9	975.3	997.9	1022.9	1051.2
15°	780.3	811.8	845.7	882.8	918.4	954.8	987.5	1021.2	1052.6	1082.3	1117.9
17.5°	768.8	805.0	845.1	888.9	931.6	975.9	1014.7	1057.1	1089.2	1129.2	1162.2
20°	759.5	798.4	841.2	890.4	939.0	988.1	1030.9	1074.1	1110.3	1150.6	1192.5
22.5°	748.0	790.8	837.2	888.1	939.0	992.7	1040.1	1083.0	1127.8	1173.1	1216.3
25°	729.6	774.0	823.2	879.0	937.3	992.2	1043.0	1096.3	1144.5	1193.7	1232.4
27.5°	707.0	753.7	805.5	863.1	923.0	979.2	1038.9	1095.8	1144.3	1191.6	1225.3
30°	689.0	738.2	788.0	846.4	908.5	968.8	1032.8	1089.6	1140.7	1183.2	1202.2
32.5°	670.5	717.1	768.4	827.5	891.3	956.1	1019.7	1077.7	1124.9	1150.5	1151.0
35°	638.2	682.0	735.3	793.4	858.7	929.1	993.5	1050.6	1079.5	1081.7	1050.6
37.5°	603.1	643.3	693.6	751.7	823.2	893.3	959.0	997.1	1006.8	974.5	917.0
40°	578.0	615.1	663.7	723.3	794.3	866.7	926.6	954.5	944.4	892.0	827.9
42.5°	551.5	586.1	632.9	691.8	763.1	836.2	887.3	902.2	875.3	814.9	739.9
45°	508.5	540.2	586.5	645.9	714.4	782.9	821.6	814.0	769.2	697.6	613.5
47.5°	463.7	494.3	536.0	590.8	661.0	720.2	746.3	723.4	659.7	580.9	512.5
50°	434.0	465.4	503.8	556.1	620.2	677.3	694.1	659.2	588.4	512.7	449.8
52.5°	404.8	431.6	469.2	519.8	581.1	629.3	638.2	598.0	525.0	457.1	401.4
55°	360.4	384.8	416.5	464.1	517.1	558.0	553.3	501.5	435.2	377.2	333.4
57.5°	317.4	335.8	365.1	409.7	456.2	483.7	466.3	422.2	360.4	312.9	276.0
60°	289.0	306.1	333.4	372.4	413.4	428.8	414.3	366.4	317.6	274.1	243.0
62.5°	262.1	277.2	300.7	336.9	369.9	379.1	363.5	321.7	277.7	240.6	214.8
65°	223.0	236.9	257.0	282.7	305.5	309.9	299.8	257.0	223.6	192.6	174.8
67.5°	187.5	196.7	212.3	234.5	246.6	249.2	229.6	202.7	173.3	154.3	140.9
70°	163.7	170.0	184.6	196.7	206.5	206.8	188.7	167.1	144.6	129.1	119.3
72.5°	140.6	146.7	157.8	166.0	173.5	171.0	154.5	137.5	119.3	107.5	100.2
75°	108.5	113.9	119.6	123.4	123.4	120.3	108.2	95.5	85.0	78.0	75.8
77.5°	78.8	83.3	85.2	84.6	83.5	78.5	70.9	62.6	58.9	55.6	53.9
80°	61.9	63.8	64.4	62.8	60.9	55.2	50.1	46.6	43.1	41.9	41.3
82.5°	45.9	47.5	45.9	46.3	42.2	37.4	34.7	33.4	32.0	31.5	30.8
85°	24.5	24.1	23.5	21.9	19.0	18.4	18.1	17.8	17.1	17.4	16.8
87.5°	9.7	9.5	9.1	9.5	10.0	9.9	10.6	11.1	11.5	11.6	12.4
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4
95°	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3
97.5°	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8
100°	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8
102.5°	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5
105°	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5
107.5°	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7
110°	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0
115°	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6
117.5°	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7
120°	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0
122.5°	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7
125°	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4
127.5°	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6
130°	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8
132.5°	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0
135°	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7
137.5°	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8
140°	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6
142.5°	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6
145°	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6
147.5°	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5
150°	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6
152.5°	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0
155°	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1
157.5°	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5
160°	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7
162.5°	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5
165°	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2
167.5°	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4
170°	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8
172.5°	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7
175°	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6
177.5°	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	787.3	787.3	787.3	787.3	787.3	787.3	787.3
2.5°	825.9	827.0	827.7	830.2	830.5	832.7	830.5
5°	894.2	898.7	905.6	912.6	913.3	917.7	909.8
7.5°	970.9	981.1	987.6	998.8	1003.3	1006.1	1001.5
10°	1023.7	1033.1	1050.0	1058.3	1066.5	1067.7	1064.0
12.5°	1074.6	1089.7	1103.0	1118.7	1118.3	1129.4	1125.4
15°	1142.6	1158.1	1176.6	1194.0	1200.4	1200.4	1205.4
17.5°	1191.1	1219.6	1238.6	1252.3	1267.3	1269.9	1268.1
20°	1223.8	1254.6	1274.9	1292.7	1302.8	1305.7	1305.7
22.5°	1248.2	1274.4	1294.2	1310.2	1318.6	1321.9	1320.9
25°	1265.1	1287.6	1299.7	1304.4	1306.6	1305.9	1300.0
27.5°	1241.9	1241.0	1233.3	1218.7	1207.8	1201.1	1193.5
30°	1197.8	1181.3	1162.3	1141.3	1114.4	1093.7	1087.4
32.5°	1132.1	1095.0	1062.8	1027.9	998.9	978.3	969.6
35°	1004.9	946.2	898.4	856.5	826.1	807.0	800.6
37.5°	854.1	797.3	738.0	697.4	672.1	652.9	645.7
40°	758.1	696.3	644.6	606.5	580.5	561.8	561.5
42.5°	670.6	611.6	562.9	535.5	507.4	495.0	495.0
45°	549.1	501.8	460.6	439.0	422.2	412.1	409.2
47.5°	454.6	415.6	388.1	370.9	357.2	350.7	346.5
50°	401.6	367.4	345.4	330.5	322.9	314.7	314.1
52.5°	357.4	329.8	312.7	300.6	291.0	286.0	286.2
55°	300.4	278.5	266.4	257.2	249.6	245.8	244.3
57.5°	253.1	236.7	227.9	219.5	216.2	213.2	212.4
60°	223.6	212.5	204.3	197.6	192.9	191.9	191.6
62.5°	199.3	187.7	182.0	176.8	173.3	171.9	171.3
65°	164.3	155.7	150.7	146.6	145.3	143.1	142.8
67.5°	132.5	127.3	124.0	121.2	119.4	119.3	119.3
70°	112.9	110.1	107.2	105.7	104.7	104.0	104.0
72.5°	96.2	94.1	91.7	90.9	90.7	90.1	89.8
75°	73.3	71.1	71.3	69.8	68.5	66.9	66.0
77.5°	51.9	50.4	50.1	49.9	48.8	48.6	49.1
80°	40.3	38.7	38.4	38.7	38.4	37.4	37.4
82.5°	30.7	29.4	29.0	28.8	28.5	28.8	28.3
85°	16.5	15.9	15.9	15.9	16.5	16.1	15.9
87.5°	12.2	12.3	12.8	12.6	12.7	12.6	13.0
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P333051-930

CATALOG NUMBER: S124RDIW-S575D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)