

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332716

Luminaire Tested: **S124DIW-S350D470U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332716
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D470U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3203.6 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49									49																			
1	98	94	90	86	90	86	83	80	73	71	68	61	59	58	49	48	47	42									42																			
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35									35																			
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	36	34	30									30																			
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30	26									26																			
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26	23									23																			
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23	20									20																			
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18									18																			
8	54	42	34	29	50	39	32	28	34	28	25	29	25	21	24	21	18	16									16																			
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15									15																			
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15	13									13																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4612	4612	4612	4612
5°	5431	4624	4081	4624
10°	6503	4604	3674	4604
15°	7694	4557	3375	4557
20°	8568	4509	3107	4509
25°	8706	4440	2922	4440
30°	7408	4373	2864	4373
35°	5695	4263	2864	4263
40°	4440	4135	2918	4135
45°	3701	3942	2967	3942
50°	3258	3706	3067	3706
55°	2985	3424	3191	3424
60°	2796	3171	3339	3171
65°	2604	2888	3463	2888
70°	2379	2608	3541	2608
75°	2127	2296	3500	2296
80°	1781	1883	3389	1883
85°	1315	1362	3242	1362



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	1.7
10°-20°	171.6	5.4
20°-30°	272.0	8.5
30°-40°	302.8	9.5
40°-50°	275.6	8.6
50°-60°	225.2	7.0
60°-70°	160.8	5.0
70°-80°	88.5	2.8
80°-90°	25.9	0.8
90°-100°	38.6	1.2
100°-110°	114.5	3.6
110°-120°	194.3	6.1
120°-130°	256.2	8.0
130°-140°	287.7	9.0
140°-150°	282.7	8.8
150°-160°	237.8	7.4
160°-170°	158.2	4.9
170°-180°	55.4	1.7
0°-30°	499.3	15.6
0°-40°	802.0	25.0
0°-60°	1302.8	40.7
0°-90°	1578.0	49.3
90°-120°	347.4	10.8
90°-150°	1174.1	36.6
90°-180°	1626.0	50.8
0°-180°	3203.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	571	571	571	571	571	
5°	670	571	504	571	670	68
15°	921	545	404	545	921	260
25°	977	498	328	498	977	431
35°	578	433	291	433	578	367
45°	324	345	260	345	324	255
55°	212	243	227	243	212	192
65°	136	151	181	151	136	135
75°	68	74	112	74	68	72
85°	14	15	35	15	14	18
90°	14	1	14	1	14	7
95°	36	27	36	27	36	37
105°	111	106	111	106	111	117
115°	196	198	196	198	196	193
125°	286	288	286	288	286	255
135°	372	371	372	371	372	287
145°	451	451	451	451	451	282
155°	516	517	516	517	516	238
165°	561	562	561	562	561	158
175°	582	585	582	585	582	55
180°	586	586	586	586	586	



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	608.0	607.9	606.0	605.6	604.3	602.6	602.2	599.1	593.1	590.2	589.5
5°	670.2	675.0	668.8	667.6	666.9	659.1	655.1	650.4	639.5	633.1	628.1
7.5°	744.5	745.0	742.3	740.2	734.1	727.3	717.1	706.2	693.2	679.8	669.6
10°	793.3	795.2	792.1	791.7	779.6	772.0	756.9	744.1	729.4	713.1	698.2
12.5°	844.8	842.2	840.6	830.5	828.2	814.4	796.8	783.7	761.0	742.2	722.4
15°	920.6	915.4	912.1	898.2	891.3	872.1	853.4	839.0	809.4	781.2	759.9
17.5°	965.1	970.3	962.7	956.9	939.2	925.7	906.6	876.3	853.2	818.2	791.3
20°	997.3	997.8	993.5	987.6	973.7	956.6	935.8	902.7	875.0	840.2	803.2
22.5°	1006.0	1006.1	1004.3	998.8	988.2	974.4	953.4	925.7	892.2	854.4	817.4
25°	977.4	976.5	978.6	984.8	980.8	976.5	964.4	943.8	912.6	872.6	832.8
27.5°	871.2	877.8	889.8	904.9	919.5	930.6	933.7	929.5	910.2	877.3	835.6
30°	794.7	802.8	811.8	826.9	856.3	873.1	891.5	905.5	897.7	871.4	832.6
32.5°	710.7	712.7	726.0	743.2	770.1	802.4	831.7	860.1	869.5	855.7	823.3
35°	577.9	581.3	595.7	612.7	645.6	685.2	729.2	768.5	800.9	813.9	797.3
37.5°	471.6	481.1	491.3	509.6	538.6	574.2	619.9	670.8	719.1	751.5	757.0
40°	421.3	427.2	434.5	448.5	473.1	508.1	547.4	605.6	657.0	703.4	718.5
42.5°	381.5	385.0	389.5	402.1	420.8	455.7	491.6	542.8	594.3	649.8	675.2
45°	324.2	327.8	335.4	342.7	356.9	381.0	414.4	456.5	508.4	561.8	608.7
47.5°	282.9	285.1	289.6	297.5	309.6	325.5	352.6	387.8	435.8	487.8	537.7
50°	259.4	261.3	264.8	271.9	281.2	295.4	317.6	350.5	388.1	440.4	489.4
52.5°	240.8	241.6	244.2	249.0	256.4	268.3	286.6	313.8	348.8	395.4	444.2
55°	212.1	213.0	215.4	218.9	225.3	232.9	246.8	267.2	297.7	338.2	380.6
57.5°	188.4	189.1	191.0	192.4	197.7	203.8	214.6	229.1	252.2	286.6	324.4
60°	173.2	172.8	175.1	176.3	179.9	185.1	193.4	207.3	227.4	255.1	289.9
62.5°	158.5	157.8	159.8	161.4	163.4	167.8	174.6	185.5	201.9	226.9	257.0
65°	136.3	135.4	136.6	138.5	140.3	142.7	147.7	157.4	170.4	188.4	211.3
67.5°	114.1	115.1	115.3	116.2	117.3	120.5	123.9	130.8	140.0	154.4	173.8
70°	100.8	101.1	102.0	102.0	102.7	105.6	108.4	112.4	121.4	134.7	150.5
72.5°	87.6	88.6	88.2	88.9	89.5	91.4	93.4	97.3	104.9	114.8	128.2
75°	68.2	68.9	68.9	69.1	69.8	70.5	72.2	75.0	80.5	87.8	97.0
77.5°	49.7	49.8	50.1	51.0	51.0	52.1	53.3	55.6	58.3	63.3	69.0
80°	38.3	38.8	38.6	39.1	39.1	40.0	40.5	43.3	44.5	47.8	52.3
82.5°	28.1	28.6	28.5	29.2	29.6	29.8	30.4	31.6	32.8	35.7	37.5
85°	14.2	14.7	14.2	14.7	15.4	15.6	16.3	16.6	17.5	18.2	19.9
87.5°	6.9	7.4	7.4	7.5	7.9	8.0	8.0	7.7	8.4	8.4	9.0
90°	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2	10.6	10.0	9.2
92.5°	20.1	20.0	19.9	19.8	19.6	19.4	19.0	18.7	18.3	17.9	17.4
95°	35.8	35.8	35.8	35.8	35.8	35.6	35.3	35.0	34.7	34.4	33.7
97.5°	56.1	56.1	56.1	56.1	56.1	55.9	55.6	55.2	54.8	54.5	53.6
100°	70.2	70.2	70.2	70.2	70.2	70.1	69.9	69.7	69.5	69.3	68.4
102.5°	86.2	86.1	86.0	85.9	85.9	85.7	85.4	85.1	84.8	84.6	83.7
105°	110.6	110.3	110.0	109.7	109.4	109.1	108.8	108.5	108.1	107.8	107.4
107.5°	134.3	134.3	134.4	134.4	134.4	134.3	134.0	133.7	133.4	133.1	133.1
110°	151.3	151.0	150.7	150.4	150.1	150.1	150.3	150.5	150.7	150.9	151.0



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.7	168.7	168.6	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.8
115°	195.8	195.9	196.0	196.1	196.2	196.3	196.4	196.5	196.6	196.7	196.9
117.5°	221.5	221.7	221.9	222.1	222.3	222.6	222.9	223.3	223.6	223.9	224.1
120°	241.1	240.9	240.7	240.5	240.3	240.4	240.9	241.4	241.9	242.4	242.7
122.5°	257.4	257.7	258.1	258.5	258.8	259.2	259.5	259.9	260.2	260.6	260.7
125°	285.5	285.7	285.9	286.1	286.3	286.5	286.7	286.9	287.1	287.3	287.4
127.5°	311.5	311.7	311.8	312.0	312.1	312.3	312.5	312.7	312.9	313.1	313.3
130°	328.5	328.9	329.3	329.7	330.1	330.4	330.6	330.8	331.0	331.2	331.2
132.5°	346.7	346.8	347.0	347.1	347.3	347.5	347.7	347.9	348.1	348.3	348.4
135°	371.6	371.9	372.2	372.5	372.8	373.0	373.2	373.4	373.6	373.8	373.8
137.5°	397.8	397.7	397.6	397.6	397.5	397.6	397.9	398.1	398.4	398.7	398.5
140°	413.7	413.8	413.9	414.0	414.1	414.2	414.3	414.4	414.5	414.6	414.6
142.5°	429.7	429.7	429.7	429.7	429.7	429.8	429.8	429.8	429.8	429.8	429.9
145°	451.3	451.6	451.9	452.2	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	473.3	473.4	473.5	473.6	473.7	473.8	473.8	473.9	474.0	474.1	474.2
150°	486.7	486.8	486.9	487.0	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	499.0	499.3	499.5	499.8	500.0	500.1	499.8	499.6	499.3	499.1	499.0
155°	516.1	516.5	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1	516.2
157.5°	531.4	531.8	532.1	532.5	532.8	532.8	532.5	532.2	531.9	531.6	531.6
160°	540.1	540.6	541.2	541.7	542.2	542.3	542.0	541.7	541.4	541.1	541.2
162.5°	549.2	549.7	550.2	550.7	551.2	551.2	550.7	550.1	549.6	549.0	549.1
165°	561.0	561.4	561.8	562.2	562.6	562.5	561.9	561.3	560.7	560.1	560.3
167.5°	569.4	570.0	570.7	571.3	571.9	571.9	571.3	570.7	570.1	569.5	569.5
170°	574.1	574.8	575.5	576.2	576.9	577.0	576.4	575.8	575.2	574.6	574.5
172.5°	578.1	578.8	579.5	580.2	580.9	580.9	580.3	579.6	578.9	578.2	578.2
175°	582.3	583.0	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3	582.4
177.5°	584.5	585.1	585.8	586.4	587.0	587.1	586.5	586.0	585.4	584.8	584.8
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	589.7	587.0	585.1	583.6	579.5	577.0	575.1	572.5	569.4	566.2	562.2
5°	623.1	615.1	609.2	600.2	591.7	584.6	577.2	570.6	562.6	553.8	547.4
7.5°	658.3	646.3	631.0	617.7	602.7	589.7	578.1	566.2	553.8	541.7	530.7
10°	680.7	665.3	648.2	628.1	609.2	592.4	576.8	561.6	546.9	532.3	519.7
12.5°	704.7	685.5	660.3	636.8	615.6	593.1	574.3	555.7	538.0	522.6	508.0
15°	737.0	709.3	680.2	648.7	620.8	594.5	568.7	545.3	525.4	505.0	490.8
17.5°	756.8	722.5	689.3	656.4	622.6	589.4	561.6	534.6	509.7	489.5	471.6
20°	769.9	735.8	694.4	661.5	621.3	587.2	555.0	524.9	498.9	477.4	458.9
22.5°	781.2	741.9	700.4	657.1	617.1	580.9	545.7	515.5	488.9	466.2	448.5
25°	787.4	742.2	697.2	654.1	608.7	565.9	533.9	498.4	470.0	446.1	427.2
27.5°	788.1	739.7	688.8	641.0	594.1	554.2	513.9	482.1	452.7	427.4	409.2
30°	786.0	735.6	680.9	629.1	582.0	538.7	503.6	469.1	439.0	413.9	395.0
32.5°	779.3	726.9	670.7	615.8	567.0	524.6	488.5	455.6	426.3	401.6	381.7
35°	760.2	708.3	648.5	591.4	541.5	498.7	466.0	432.6	403.3	379.9	360.7
37.5°	730.2	683.4	622.5	563.5	514.4	471.4	439.0	408.9	382.4	358.6	339.0
40°	704.1	662.9	601.8	544.3	491.3	450.4	420.1	392.4	366.1	343.6	324.9
42.5°	674.0	638.1	581.8	520.9	469.7	428.6	399.1	374.2	349.5	328.7	310.0
45°	620.3	596.6	543.6	487.3	434.0	395.2	367.1	345.3	324.5	304.1	288.5
47.5°	558.6	546.8	502.2	448.7	398.2	359.9	335.5	315.4	297.1	279.9	266.1
50°	517.1	511.4	472.9	421.3	373.0	337.0	312.4	295.1	279.5	264.4	251.3
52.5°	476.2	476.0	441.2	394.0	349.3	314.7	290.2	274.1	260.6	248.3	236.6
55°	413.7	420.3	393.1	351.0	311.0	279.7	257.7	243.3	233.8	223.7	214.9
57.5°	356.3	367.3	344.8	307.7	274.3	245.6	226.4	215.6	205.5	199.3	192.9
60°	318.8	329.2	311.7	280.5	249.0	224.4	206.1	196.4	187.7	183.4	178.9
62.5°	285.5	294.7	281.8	252.8	225.5	201.8	186.4	177.1	171.2	166.6	163.6
65°	237.9	245.7	234.5	213.5	190.0	171.1	158.6	151.2	145.6	143.7	140.3
67.5°	192.3	199.4	193.4	175.5	156.7	142.3	132.5	125.5	122.1	120.5	118.1
70°	165.2	172.3	165.9	150.3	135.8	123.8	114.5	110.5	107.0	106.3	103.0
72.5°	142.3	147.1	140.7	128.5	116.2	106.0	98.8	94.6	92.8	91.5	89.7
75°	106.7	111.0	106.7	97.3	88.5	81.4	75.3	73.6	71.5	70.8	69.6
77.5°	75.5	79.2	76.0	70.1	63.5	58.0	54.7	52.6	52.1	50.9	51.5
80°	57.7	60.1	57.0	53.0	47.8	44.0	41.7	40.5	39.1	38.6	39.5
82.5°	41.5	42.5	40.9	38.2	34.4	31.9	30.3	28.9	28.6	28.7	28.7
85°	21.5	21.3	21.1	18.7	17.5	15.9	14.9	14.7	14.4	14.9	15.4
87.5°	8.9	8.9	8.5	7.6	6.8	6.0	5.6	5.2	5.6	6.0	6.4
90°	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	16.8	16.3	15.7	14.8	13.5	12.2	11.0	9.7	11.0	12.2	13.5
95°	33.0	32.3	31.6	30.8	29.9	29.0	28.1	27.2	28.1	29.0	29.9
97.5°	52.8	52.0	51.2	50.4	49.7	48.9	48.2	47.5	48.2	48.9	49.7
100°	67.5	66.6	65.7	65.1	64.6	64.2	63.8	63.4	63.8	64.2	64.6
102.5°	82.9	82.1	81.3	80.8	80.6	80.4	80.3	80.1	80.3	80.4	80.6
105°	107.0	106.6	106.2	106.0	105.9	105.8	105.7	105.6	105.7	105.8	105.9
107.5°	133.0	133.0	132.9	132.8	132.7	132.6	132.4	132.3	132.4	132.6	132.7
110°	151.1	151.2	151.3	151.2	151.0	150.8	150.6	150.4	150.6	150.8	151.0



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.0	169.2	169.4	169.5	169.4	169.4	169.3	169.3	169.3	169.4	169.4
115°	197.1	197.3	197.5	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6
117.5°	224.2	224.4	224.5	224.5	224.5	224.4	224.3	224.2	224.3	224.4	224.5
120°	243.0	243.3	243.6	243.6	243.2	242.8	242.4	242.0	242.4	242.8	243.2
122.5°	260.8	261.0	261.1	261.1	260.9	260.8	260.6	260.5	260.6	260.8	260.9
125°	287.5	287.6	287.7	287.7	287.7	287.7	287.7	287.7	287.7	287.7	287.7
127.5°	313.4	313.6	313.8	313.7	313.4	313.1	312.8	312.5	312.8	313.1	313.4
130°	331.2	331.2	331.2	331.1	330.8	330.5	330.2	329.9	330.2	330.5	330.8
132.5°	348.4	348.5	348.6	348.5	348.3	348.1	347.9	347.6	347.9	348.1	348.3
135°	373.8	373.8	373.8	373.5	372.9	372.3	371.7	371.1	371.7	372.3	372.9
137.5°	398.4	398.2	398.0	397.8	397.5	397.2	397.0	396.7	397.0	397.2	397.5
140°	414.6	414.6	414.6	414.5	414.3	414.1	413.9	413.7	413.9	414.1	414.3
142.5°	430.0	430.1	430.2	430.1	429.9	429.7	429.5	429.3	429.5	429.7	429.9
145°	452.9	452.8	452.7	452.5	452.1	451.7	451.3	450.9	451.3	451.7	452.1
147.5°	474.2	474.3	474.4	474.2	473.7	473.2	472.7	472.3	472.7	473.2	473.7
150°	487.1	487.1	487.1	486.9	486.5	486.1	485.7	485.3	485.7	486.1	486.5
152.5°	498.9	498.8	498.8	498.6	498.4	498.1	497.9	497.6	497.9	498.1	498.4
155°	516.3	516.4	516.5	516.6	516.6	516.6	516.6	516.6	516.6	516.6	516.6
157.5°	531.7	531.7	531.7	531.8	532.0	532.2	532.3	532.5	532.3	532.2	532.0
160°	541.3	541.4	541.5	541.6	541.7	541.8	541.9	542.0	541.9	541.8	541.7
162.5°	549.2	549.3	549.4	549.6	549.9	550.1	550.4	550.7	550.4	550.1	549.9
165°	560.5	560.7	560.9	561.1	561.4	561.7	562.0	562.3	562.0	561.7	561.4
167.5°	569.5	569.4	569.4	569.6	570.1	570.5	570.9	571.3	570.9	570.5	570.1
170°	574.4	574.3	574.2	574.4	574.9	575.4	575.9	576.4	575.9	575.4	574.9
172.5°	578.2	578.1	578.1	578.3	578.8	579.2	579.6	580.0	579.6	579.2	578.8
175°	582.5	582.6	582.7	583.0	583.5	584.0	584.5	585.0	584.5	584.0	583.5
177.5°	584.8	584.8	584.8	585.0	585.4	585.8	586.2	586.6	586.2	585.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	560.3	558.6	556.2	552.8	549.9	546.9	546.1	545.0	547.3	545.4	544.8
5°	542.0	537.0	530.6	523.3	519.0	512.9	511.7	509.3	506.9	506.7	504.3
7.5°	522.5	515.2	506.8	499.4	492.5	485.7	481.3	480.4	476.9	474.8	472.5
10°	510.0	501.0	491.3	484.2	476.2	469.1	464.1	461.3	458.9	456.3	453.9
12.5°	495.3	485.7	477.7	470.0	460.5	455.1	446.9	442.0	441.5	441.5	435.4
15°	478.1	468.6	456.3	445.4	440.2	429.8	425.3	419.6	416.1	412.5	409.7
17.5°	458.4	446.6	437.0	424.5	414.6	406.3	400.4	397.0	391.6	386.6	383.0
20°	446.1	433.6	423.4	410.1	399.3	389.1	384.1	379.4	375.4	371.1	367.1
22.5°	433.6	420.5	408.1	395.2	385.1	374.3	369.5	363.1	359.3	356.9	352.9
25°	413.9	399.7	385.5	373.2	362.8	353.3	347.0	342.0	337.7	335.8	333.2
27.5°	392.5	378.4	364.7	350.7	338.9	332.0	326.9	323.2	320.7	318.2	317.0
30°	378.9	364.2	349.6	336.5	325.7	318.8	314.1	311.5	309.6	308.4	307.2
32.5°	365.1	350.6	335.2	323.3	313.5	307.4	303.8	301.2	300.3	299.9	299.4
35°	342.9	328.3	314.1	303.4	294.2	291.8	288.7	287.3	286.8	288.5	289.2
37.5°	321.5	307.9	294.8	284.5	278.4	275.0	273.9	274.0	275.7	277.1	278.8
40°	307.7	294.4	282.1	273.1	267.4	265.3	264.8	266.0	267.9	269.6	271.5
42.5°	294.2	281.2	270.0	261.6	257.6	255.6	255.9	257.1	259.8	261.8	264.6
45°	273.4	262.5	251.6	244.7	241.4	241.9	241.9	244.0	246.6	249.7	252.8
47.5°	253.7	242.7	233.8	228.0	226.3	225.9	227.2	230.0	233.7	237.5	241.8
50°	240.5	230.0	222.2	217.0	215.1	215.8	217.7	220.3	224.8	229.6	234.1
52.5°	227.0	217.5	210.3	205.5	204.1	205.4	207.3	211.4	215.4	220.5	225.9
55°	206.1	198.1	192.4	188.9	188.4	189.1	191.2	195.7	201.4	207.8	213.0
57.5°	185.4	178.6	173.4	171.0	171.2	171.9	175.4	180.7	186.8	193.6	200.3
60°	171.3	165.2	160.9	159.0	159.3	160.7	165.0	169.9	177.5	184.1	191.2
62.5°	158.1	152.7	148.6	146.9	146.6	149.7	153.8	158.9	166.5	173.9	181.6
65°	136.8	132.5	129.2	128.3	129.0	131.4	136.6	143.4	149.8	157.6	165.7
67.5°	116.0	112.5	110.2	110.6	111.5	115.0	119.3	125.2	132.5	140.6	148.5
70°	102.7	99.4	97.5	97.7	99.2	103.4	107.2	113.1	120.9	129.2	135.8
72.5°	89.1	86.9	85.2	86.2	87.6	90.5	95.3	101.2	108.1	115.8	122.8
75°	68.4	68.4	67.5	68.2	70.3	73.1	76.7	82.8	89.7	95.9	101.5
77.5°	50.7	50.2	50.8	51.7	52.9	56.3	60.4	64.8	69.9	76.1	80.8
80°	38.8	39.1	40.2	41.7	42.1	44.7	49.0	53.0	57.0	62.2	66.7
82.5°	29.2	29.4	30.0	31.8	32.3	35.1	37.8	41.8	45.5	49.0	52.7
85°	15.9	15.9	17.0	17.8	18.9	20.8	22.5	24.9	28.2	30.5	34.1
87.5°	7.2	7.4	8.3	8.9	9.6	10.7	11.2	13.4	14.3	15.4	17.1
90°	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2	11.8	12.4	12.8
92.5°	14.8	15.7	16.3	16.8	17.4	17.9	18.3	18.7	19.0	19.4	19.6
95°	30.8	31.6	32.3	33.0	33.7	34.4	34.7	35.0	35.3	35.6	35.8
97.5°	50.4	51.2	52.0	52.8	53.6	54.5	54.8	55.2	55.6	55.9	56.1
100°	65.1	65.7	66.6	67.5	68.4	69.3	69.5	69.7	69.9	70.1	70.2
102.5°	80.8	81.3	82.1	82.9	83.7	84.6	84.8	85.1	85.4	85.7	85.9
105°	106.0	106.2	106.6	107.0	107.4	107.8	108.1	108.5	108.8	109.1	109.4
107.5°	132.8	132.9	133.0	133.0	133.1	133.1	133.4	133.7	134.0	134.3	134.4
110°	151.2	151.3	151.2	151.1	151.0	150.9	150.7	150.5	150.3	150.1	150.1



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	169.5	169.4	169.2	169.0	168.8	168.7	168.6	168.6	168.5	168.5	168.5
115°	197.6	197.5	197.3	197.1	196.9	196.7	196.6	196.5	196.4	196.3	196.2
117.5°	224.5	224.5	224.4	224.2	224.1	223.9	223.6	223.3	222.9	222.6	222.3
120°	243.6	243.6	243.3	243.0	242.7	242.4	241.9	241.4	240.9	240.4	240.3
122.5°	261.1	261.1	261.0	260.8	260.7	260.6	260.2	259.9	259.5	259.2	258.8
125°	287.7	287.7	287.6	287.5	287.4	287.3	287.1	286.9	286.7	286.5	286.3
127.5°	313.7	313.8	313.6	313.4	313.3	313.1	312.9	312.7	312.5	312.3	312.1
130°	331.1	331.2	331.2	331.2	331.2	331.2	331.0	330.8	330.6	330.4	330.1
132.5°	348.5	348.6	348.5	348.4	348.4	348.3	348.1	347.9	347.7	347.5	347.3
135°	373.5	373.8	373.8	373.8	373.8	373.8	373.6	373.4	373.2	373.0	372.8
137.5°	397.8	398.0	398.2	398.4	398.5	398.7	398.4	398.1	397.9	397.6	397.5
140°	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.4	414.3	414.2	414.1
142.5°	430.1	430.2	430.1	430.0	429.9	429.8	429.8	429.8	429.8	429.8	429.7
145°	452.5	452.7	452.8	452.9	453.0	453.1	453.0	452.9	452.8	452.7	452.5
147.5°	474.2	474.4	474.3	474.2	474.2	474.1	474.0	473.9	473.8	473.8	473.7
150°	486.9	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	498.6	498.8	498.8	498.9	499.0	499.1	499.3	499.6	499.8	500.1	500.0
155°	516.6	516.5	516.4	516.3	516.2	516.1	516.5	516.9	517.3	517.7	517.7
157.5°	531.8	531.7	531.7	531.7	531.6	531.6	531.9	532.2	532.5	532.8	532.8
160°	541.6	541.5	541.4	541.3	541.2	541.1	541.4	541.7	542.0	542.3	542.2
162.5°	549.6	549.4	549.3	549.2	549.1	549.0	549.6	550.1	550.7	551.2	551.2
165°	561.1	560.9	560.7	560.5	560.3	560.1	560.7	561.3	561.9	562.5	562.6
167.5°	569.6	569.4	569.4	569.5	569.5	569.5	570.1	570.7	571.3	571.9	571.9
170°	574.4	574.2	574.3	574.4	574.5	574.6	575.2	575.8	576.4	577.0	576.9
172.5°	578.3	578.1	578.1	578.2	578.2	578.2	578.9	579.6	580.3	580.9	580.9
175°	583.0	582.7	582.6	582.5	582.4	582.3	583.0	583.7	584.4	585.1	585.1
177.5°	585.0	584.8	584.8	584.8	584.8	584.8	585.4	586.0	586.5	587.1	587.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	544.4	544.1	542.7	542.5	542.7	544.1	544.4	544.8	545.4	547.3	545.0
5°	502.9	501.7	501.0	503.6	501.0	501.7	502.9	504.3	506.7	506.9	509.3
7.5°	471.6	470.7	468.6	467.9	468.6	470.7	471.6	472.5	474.8	476.9	480.4
10°	451.6	450.6	448.7	448.2	448.7	450.6	451.6	453.9	456.3	458.9	461.3
12.5°	432.2	430.4	430.0	430.5	430.0	430.4	432.2	435.4	441.5	441.5	442.0
15°	406.6	405.6	403.0	403.8	403.0	405.6	406.6	409.7	412.5	416.1	419.6
17.5°	381.3	380.2	377.0	379.8	377.0	380.2	381.3	383.0	386.6	391.6	397.0
20°	365.4	363.5	361.9	361.6	361.9	363.5	365.4	367.1	371.1	375.4	379.4
22.5°	350.3	348.6	348.4	346.9	348.4	348.6	350.3	352.9	356.9	359.3	363.1
25°	331.3	329.7	329.2	328.0	329.2	329.7	331.3	333.2	335.8	337.7	342.0
27.5°	316.8	316.0	315.1	315.5	315.1	316.0	316.8	317.0	318.2	320.7	323.2
30°	307.9	307.7	307.2	307.2	307.2	307.7	307.9	307.2	308.4	309.6	311.5
32.5°	300.5	300.5	300.8	300.8	300.8	300.5	300.5	299.4	299.9	300.3	301.2
35°	290.2	290.9	291.3	290.6	291.3	290.9	290.2	289.2	288.5	286.8	287.3
37.5°	280.8	281.5	282.2	283.0	282.2	281.5	280.8	278.8	277.1	275.7	274.0
40°	273.6	275.2	275.7	276.9	275.7	275.2	273.6	271.5	269.6	267.9	266.0
42.5°	266.8	268.6	269.8	270.1	269.8	268.6	266.8	264.6	261.8	259.8	257.1
45°	256.3	258.2	259.9	259.9	259.9	258.2	256.3	252.8	249.7	246.6	244.0
47.5°	245.5	248.2	249.9	250.3	249.9	248.2	245.5	241.8	237.5	233.7	230.0
50°	238.1	241.4	243.1	244.2	243.1	241.4	238.1	234.1	229.6	224.8	220.3
52.5°	230.9	234.2	236.4	237.0	236.4	234.2	230.9	225.9	220.5	215.4	211.4
55°	218.4	223.2	225.8	226.7	225.8	223.2	218.4	213.0	207.8	201.4	195.7
57.5°	206.7	211.1	214.1	214.8	214.1	211.1	206.7	200.3	193.6	186.8	180.7
60°	197.6	202.4	206.1	206.8	206.1	202.4	197.6	191.2	184.1	177.5	169.9
62.5°	188.3	193.3	196.7	198.5	196.7	193.3	188.3	181.6	173.9	166.5	158.9
65°	172.3	177.3	180.6	181.3	180.6	177.3	172.3	165.7	157.6	149.8	143.4
67.5°	154.8	159.8	161.9	163.3	161.9	159.8	154.8	148.5	140.6	132.5	125.2
70°	142.5	146.5	148.9	150.0	148.9	146.5	142.5	135.8	129.2	120.9	113.1
72.5°	128.5	132.7	135.4	135.7	135.4	132.7	128.5	122.8	115.8	108.1	101.2
75°	107.0	110.8	112.2	112.2	112.2	110.8	107.0	101.5	95.9	89.7	82.8
77.5°	84.7	86.6	88.4	88.8	88.4	86.6	84.7	80.8	76.1	69.9	64.8
80°	70.3	71.5	72.9	72.9	72.9	71.5	70.3	66.7	62.2	57.0	53.0
82.5°	55.5	56.5	57.9	57.7	57.9	56.5	55.5	52.7	49.0	45.5	41.8
85°	33.6	35.7	35.5	35.0	35.5	35.7	33.6	34.1	30.5	28.2	24.9
87.5°	17.7	18.0	18.6	19.0	18.6	18.0	17.7	17.1	15.4	14.3	13.4
90°	13.0	13.2	13.4	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2
92.5°	19.8	19.9	20.0	20.1	20.0	19.9	19.8	19.6	19.4	19.0	18.7
95°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.6	35.3	35.0
97.5°	56.1	56.1	56.1	56.1	56.1	56.1	56.1	56.1	55.9	55.6	55.2
100°	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.1	69.9	69.7
102.5°	85.9	86.0	86.1	86.2	86.1	86.0	85.9	85.9	85.7	85.4	85.1
105°	109.7	110.0	110.3	110.6	110.3	110.0	109.7	109.4	109.1	108.8	108.5
107.5°	134.4	134.4	134.3	134.3	134.3	134.4	134.4	134.4	134.3	134.0	133.7
110°	150.4	150.7	151.0	151.3	151.0	150.7	150.4	150.1	150.1	150.3	150.5



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	168.6	168.6	168.7	168.7	168.7	168.6	168.6	168.5	168.5	168.5	168.6
115°	196.1	196.0	195.9	195.8	195.9	196.0	196.1	196.2	196.3	196.4	196.5
117.5°	222.1	221.9	221.7	221.5	221.7	221.9	222.1	222.3	222.6	222.9	223.3
120°	240.5	240.7	240.9	241.1	240.9	240.7	240.5	240.3	240.4	240.9	241.4
122.5°	258.5	258.1	257.7	257.4	257.7	258.1	258.5	258.8	259.2	259.5	259.9
125°	286.1	285.9	285.7	285.5	285.7	285.9	286.1	286.3	286.5	286.7	286.9
127.5°	312.0	311.8	311.7	311.5	311.7	311.8	312.0	312.1	312.3	312.5	312.7
130°	329.7	329.3	328.9	328.5	328.9	329.3	329.7	330.1	330.4	330.6	330.8
132.5°	347.1	347.0	346.8	346.7	346.8	347.0	347.1	347.3	347.5	347.7	347.9
135°	372.5	372.2	371.9	371.6	371.9	372.2	372.5	372.8	373.0	373.2	373.4
137.5°	397.6	397.6	397.7	397.8	397.7	397.6	397.6	397.5	397.6	397.9	398.1
140°	414.0	413.9	413.8	413.7	413.8	413.9	414.0	414.1	414.2	414.3	414.4
142.5°	429.7	429.7	429.7	429.7	429.7	429.7	429.7	429.7	429.8	429.8	429.8
145°	452.2	451.9	451.6	451.3	451.6	451.9	452.2	452.5	452.7	452.8	452.9
147.5°	473.6	473.5	473.4	473.3	473.4	473.5	473.6	473.7	473.8	473.8	473.9
150°	487.0	486.9	486.8	486.7	486.8	486.9	487.0	487.1	487.1	487.1	487.1
152.5°	499.8	499.5	499.3	499.0	499.3	499.5	499.8	500.0	500.1	499.8	499.6
155°	517.3	516.9	516.5	516.1	516.5	516.9	517.3	517.7	517.7	517.3	516.9
157.5°	532.5	532.1	531.8	531.4	531.8	532.1	532.5	532.8	532.8	532.5	532.2
160°	541.7	541.2	540.6	540.1	540.6	541.2	541.7	542.2	542.3	542.0	541.7
162.5°	550.7	550.2	549.7	549.2	549.7	550.2	550.7	551.2	551.2	550.7	550.1
165°	562.2	561.8	561.4	561.0	561.4	561.8	562.2	562.6	562.5	561.9	561.3
167.5°	571.3	570.7	570.0	569.4	570.0	570.7	571.3	571.9	571.9	571.3	570.7
170°	576.2	575.5	574.8	574.1	574.8	575.5	576.2	576.9	577.0	576.4	575.8
172.5°	580.2	579.5	578.8	578.1	578.8	579.5	580.2	580.9	580.9	580.3	579.6
175°	584.4	583.7	583.0	582.3	583.0	583.7	584.4	585.1	585.1	584.4	583.7
177.5°	586.4	585.8	585.1	584.5	585.1	585.8	586.4	587.0	587.1	586.5	586.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	546.1	546.9	549.9	552.8	556.2	558.6	560.3	562.2	566.2	569.4	572.5
5°	511.7	512.9	519.0	523.3	530.6	537.0	542.0	547.4	553.8	562.6	570.6
7.5°	481.3	485.7	492.5	499.4	506.8	515.2	522.5	530.7	541.7	553.8	566.2
10°	464.1	469.1	476.2	484.2	491.3	501.0	510.0	519.7	532.3	546.9	561.6
12.5°	446.9	455.1	460.5	470.0	477.7	485.7	495.3	508.0	522.6	538.0	555.7
15°	425.3	429.8	440.2	445.4	456.3	468.6	478.1	490.8	505.0	525.4	545.3
17.5°	400.4	406.3	414.6	424.5	437.0	446.6	458.4	471.6	489.5	509.7	534.6
20°	384.1	389.1	399.3	410.1	423.4	433.6	446.1	458.9	477.4	498.9	524.9
22.5°	369.5	374.3	385.1	395.2	408.1	420.5	433.6	448.5	466.2	488.9	515.5
25°	347.0	353.3	362.8	373.2	385.5	399.7	413.9	427.2	446.1	470.0	498.4
27.5°	326.9	332.0	338.9	350.7	364.7	378.4	392.5	409.2	427.4	452.7	482.1
30°	314.1	318.8	325.7	336.5	349.6	364.2	378.9	395.0	413.9	439.0	469.1
32.5°	303.8	307.4	313.5	323.3	335.2	350.6	365.1	381.7	401.6	426.3	455.6
35°	288.7	291.8	294.2	303.4	314.1	328.3	342.9	360.7	379.9	403.3	432.6
37.5°	273.9	275.0	278.4	284.5	294.8	307.9	321.5	339.0	358.6	382.4	408.9
40°	264.8	265.3	267.4	273.1	282.1	294.4	307.7	324.9	343.6	366.1	392.4
42.5°	255.9	255.6	257.6	261.6	270.0	281.2	294.2	310.0	328.7	349.5	374.2
45°	241.9	241.9	241.4	244.7	251.6	262.5	273.4	288.5	304.1	324.5	345.3
47.5°	227.2	225.9	226.3	228.0	233.8	242.7	253.7	266.1	279.9	297.1	315.4
50°	217.7	215.8	215.1	217.0	222.2	230.0	240.5	251.3	264.4	279.5	295.1
52.5°	207.3	205.4	204.1	205.5	210.3	217.5	227.0	236.6	248.3	260.6	274.1
55°	191.2	189.1	188.4	188.9	192.4	198.1	206.1	214.9	223.7	233.8	243.3
57.5°	175.4	171.9	171.2	171.0	173.4	178.6	185.4	192.9	199.3	205.5	215.6
60°	165.0	160.7	159.3	159.0	160.9	165.2	171.3	178.9	183.4	187.7	196.4
62.5°	153.8	149.7	146.6	146.9	148.6	152.7	158.1	163.6	166.6	171.2	177.1
65°	136.6	131.4	129.0	128.3	129.2	132.5	136.8	140.3	143.7	145.6	151.2
67.5°	119.3	115.0	111.5	110.6	110.2	112.5	116.0	118.1	120.5	122.1	125.5
70°	107.2	103.4	99.2	97.7	97.5	99.4	102.7	103.0	106.3	107.0	110.5
72.5°	95.3	90.5	87.6	86.2	85.2	86.9	89.1	89.7	91.5	92.8	94.6
75°	76.7	73.1	70.3	68.2	67.5	68.4	68.4	69.6	70.8	71.5	73.6
77.5°	60.4	56.3	52.9	51.7	50.8	50.2	50.7	51.5	50.9	52.1	52.6
80°	49.0	44.7	42.1	41.7	40.2	39.1	38.8	39.5	38.6	39.1	40.5
82.5°	37.8	35.1	32.3	31.8	30.0	29.4	29.2	28.7	28.7	28.6	28.9
85°	22.5	20.8	18.9	17.8	17.0	15.9	15.9	15.4	14.9	14.4	14.7
87.5°	11.2	10.7	9.6	8.9	8.3	7.4	7.2	6.4	6.0	5.6	5.2
90°	10.6	10.0	9.2	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4
92.5°	18.3	17.9	17.4	16.8	16.3	15.7	14.8	13.5	12.2	11.0	9.7
95°	34.7	34.4	33.7	33.0	32.3	31.6	30.8	29.9	29.0	28.1	27.2
97.5°	54.8	54.5	53.6	52.8	52.0	51.2	50.4	49.7	48.9	48.2	47.5
100°	69.5	69.3	68.4	67.5	66.6	65.7	65.1	64.6	64.2	63.8	63.4
102.5°	84.8	84.6	83.7	82.9	82.1	81.3	80.8	80.6	80.4	80.3	80.1
105°	108.1	107.8	107.4	107.0	106.6	106.2	106.0	105.9	105.8	105.7	105.6
107.5°	133.4	133.1	133.1	133.0	133.0	132.9	132.8	132.7	132.6	132.4	132.3
110°	150.7	150.9	151.0	151.1	151.2	151.3	151.2	151.0	150.8	150.6	150.4



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	168.6	168.7	168.8	169.0	169.2	169.4	169.5	169.4	169.4	169.3	169.3
115°	196.6	196.7	196.9	197.1	197.3	197.5	197.6	197.6	197.6	197.6	197.6
117.5°	223.6	223.9	224.1	224.2	224.4	224.5	224.5	224.5	224.4	224.3	224.2
120°	241.9	242.4	242.7	243.0	243.3	243.6	243.6	243.2	242.8	242.4	242.0
122.5°	260.2	260.6	260.7	260.8	261.0	261.1	261.1	260.9	260.8	260.6	260.5
125°	287.1	287.3	287.4	287.5	287.6	287.7	287.7	287.7	287.7	287.7	287.7
127.5°	312.9	313.1	313.3	313.4	313.6	313.8	313.7	313.4	313.1	312.8	312.5
130°	331.0	331.2	331.2	331.2	331.2	331.2	331.1	330.8	330.5	330.2	329.9
132.5°	348.1	348.3	348.4	348.4	348.5	348.6	348.5	348.3	348.1	347.9	347.6
135°	373.6	373.8	373.8	373.8	373.8	373.8	373.5	372.9	372.3	371.7	371.1
137.5°	398.4	398.7	398.5	398.4	398.2	398.0	397.8	397.5	397.2	397.0	396.7
140°	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.3	414.1	413.9	413.7
142.5°	429.8	429.8	429.9	430.0	430.1	430.2	430.1	429.9	429.7	429.5	429.3
145°	453.0	453.1	453.0	452.9	452.8	452.7	452.5	452.1	451.7	451.3	450.9
147.5°	474.0	474.1	474.2	474.2	474.3	474.4	474.2	473.7	473.2	472.7	472.3
150°	487.1	487.1	487.1	487.1	487.1	487.1	486.9	486.5	486.1	485.7	485.3
152.5°	499.3	499.1	499.0	498.9	498.8	498.8	498.6	498.4	498.1	497.9	497.6
155°	516.5	516.1	516.2	516.3	516.4	516.5	516.6	516.6	516.6	516.6	516.6
157.5°	531.9	531.6	531.6	531.7	531.7	531.7	531.8	532.0	532.2	532.3	532.5
160°	541.4	541.1	541.2	541.3	541.4	541.5	541.6	541.7	541.8	541.9	542.0
162.5°	549.6	549.0	549.1	549.2	549.3	549.4	549.6	549.9	550.1	550.4	550.7
165°	560.7	560.1	560.3	560.5	560.7	560.9	561.1	561.4	561.7	562.0	562.3
167.5°	570.1	569.5	569.5	569.5	569.4	569.4	569.6	570.1	570.5	570.9	571.3
170°	575.2	574.6	574.5	574.4	574.3	574.2	574.4	574.9	575.4	575.9	576.4
172.5°	578.9	578.2	578.2	578.2	578.1	578.1	578.3	578.8	579.2	579.6	580.0
175°	583.0	582.3	582.4	582.5	582.6	582.7	583.0	583.5	584.0	584.5	585.0
177.5°	585.4	584.8	584.8	584.8	584.8	584.8	585.0	585.4	585.8	586.2	586.6
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	575.1	577.0	579.5	583.6	585.1	587.0	589.7	589.5	590.2	593.1	599.1
5°	577.2	584.6	591.7	600.2	609.2	615.1	623.1	628.1	633.1	639.5	650.4
7.5°	578.1	589.7	602.7	617.7	631.0	646.3	658.3	669.6	679.8	693.2	706.2
10°	576.8	592.4	609.2	628.1	648.2	665.3	680.7	698.2	713.1	729.4	744.1
12.5°	574.3	593.1	615.6	636.8	660.3	685.5	704.7	722.4	742.2	761.0	783.7
15°	568.7	594.5	620.8	648.7	680.2	709.3	737.0	759.9	781.2	809.4	839.0
17.5°	561.6	589.4	622.6	656.4	689.3	722.5	756.8	791.3	818.2	853.2	876.3
20°	555.0	587.2	621.3	661.5	694.4	735.8	769.9	803.2	840.2	875.0	902.7
22.5°	545.7	580.9	617.1	657.1	700.4	741.9	781.2	817.4	854.4	892.2	925.7
25°	533.9	565.9	608.7	654.1	697.2	742.2	787.4	832.8	872.6	912.6	943.8
27.5°	513.9	554.2	594.1	641.0	688.8	739.7	788.1	835.6	877.3	910.2	929.5
30°	503.6	538.7	582.0	629.1	680.9	735.6	786.0	832.6	871.4	897.7	905.5
32.5°	488.5	524.6	567.0	615.8	670.7	726.9	779.3	823.3	855.7	869.5	860.1
35°	466.0	498.7	541.5	591.4	648.5	708.3	760.2	797.3	813.9	800.9	768.5
37.5°	439.0	471.4	514.4	563.5	622.5	683.4	730.2	757.0	751.5	719.1	670.8
40°	420.1	450.4	491.3	544.3	601.8	662.9	704.1	718.5	703.4	657.0	605.6
42.5°	399.1	428.6	469.7	520.9	581.8	638.1	674.0	675.2	649.8	594.3	542.8
45°	367.1	395.2	434.0	487.3	543.6	596.6	620.3	608.7	561.8	508.4	456.5
47.5°	335.5	359.9	398.2	448.7	502.2	546.8	558.6	537.7	487.8	435.8	387.8
50°	312.4	337.0	373.0	421.3	472.9	511.4	517.1	489.4	440.4	388.1	350.5
52.5°	290.2	314.7	349.3	394.0	441.2	476.0	476.2	444.2	395.4	348.8	313.8
55°	257.7	279.7	311.0	351.0	393.1	420.3	413.7	380.6	338.2	297.7	267.2
57.5°	226.4	245.6	274.3	307.7	344.8	367.3	356.3	324.4	286.6	252.2	229.1
60°	206.1	224.4	249.0	280.5	311.7	329.2	318.8	289.9	255.1	227.4	207.3
62.5°	186.4	201.8	225.5	252.8	281.8	294.7	285.5	257.0	226.9	201.9	185.5
65°	158.6	171.1	190.0	213.5	234.5	245.7	237.9	211.3	188.4	170.4	157.4
67.5°	132.5	142.3	156.7	175.5	193.4	199.4	192.3	173.8	154.4	140.0	130.8
70°	114.5	123.8	135.8	150.3	165.9	172.3	165.2	150.5	134.7	121.4	112.4
72.5°	98.8	106.0	116.2	128.5	140.7	147.1	142.3	128.2	114.8	104.9	97.3
75°	75.3	81.4	88.5	97.3	106.7	111.0	106.7	97.0	87.8	80.5	75.0
77.5°	54.7	58.0	63.5	70.1	76.0	79.2	75.5	69.0	63.3	58.3	55.6
80°	41.7	44.0	47.8	53.0	57.0	60.1	57.7	52.3	47.8	44.5	43.3
82.5°	30.3	31.9	34.4	38.2	40.9	42.5	41.5	37.5	35.7	32.8	31.6
85°	14.9	15.9	17.5	18.7	21.1	21.3	21.5	19.9	18.2	17.5	16.6
87.5°	5.6	6.0	6.8	7.6	8.5	8.9	8.9	9.0	8.4	8.4	7.7
90°	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2
92.5°	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3	18.7
95°	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7	35.0
97.5°	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8	55.2
100°	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5	69.7
102.5°	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8	85.1
105°	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1	108.5
107.5°	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4	133.7
110°	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7	150.5



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6	168.6
115°	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6	196.5
117.5°	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6	223.3
120°	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9	241.4
122.5°	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2	259.9
125°	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1	286.9
127.5°	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9	312.7
130°	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0	330.8
132.5°	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1	347.9
135°	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6	373.4
137.5°	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4	398.1
140°	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.4
142.5°	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8	429.8
145°	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0	452.9
147.5°	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0	473.9
150°	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3	499.6
155°	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5	516.9
157.5°	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9	532.2
160°	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4	541.7
162.5°	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6	550.1
165°	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7	561.3
167.5°	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1	570.7
170°	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2	575.8
172.5°	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9	579.6
175°	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0	583.7
177.5°	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4	586.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	602.2	602.6	604.3	605.6	606.0	607.9	608.0
5°	655.1	659.1	666.9	667.6	668.8	675.0	670.2
7.5°	717.1	727.3	734.1	740.2	742.3	745.0	744.5
10°	756.9	772.0	779.6	791.7	792.1	795.2	793.3
12.5°	796.8	814.4	828.2	830.5	840.6	842.2	844.8
15°	853.4	872.1	891.3	898.2	912.1	915.4	920.6
17.5°	906.6	925.7	939.2	956.9	962.7	970.3	965.1
20°	935.8	956.6	973.7	987.6	993.5	997.8	997.3
22.5°	953.4	974.4	988.2	998.8	1004.3	1006.1	1006.0
25°	964.4	976.5	980.8	984.8	978.6	976.5	977.4
27.5°	933.7	930.6	919.5	904.9	889.8	877.8	871.2
30°	891.5	873.1	856.3	826.9	811.8	802.8	794.7
32.5°	831.7	802.4	770.1	743.2	726.0	712.7	710.7
35°	729.2	685.2	645.6	612.7	595.7	581.3	577.9
37.5°	619.9	574.2	538.6	509.6	491.3	481.1	471.6
40°	547.4	508.1	473.1	448.5	434.5	427.2	421.3
42.5°	491.6	455.7	420.8	402.1	389.5	385.0	381.5
45°	414.4	381.0	356.9	342.7	335.4	327.8	324.2
47.5°	352.6	325.5	309.6	297.5	289.6	285.1	282.9
50°	317.6	295.4	281.2	271.9	264.8	261.3	259.4
52.5°	286.6	268.3	256.4	249.0	244.2	241.6	240.8
55°	246.8	232.9	225.3	218.9	215.4	213.0	212.1
57.5°	214.6	203.8	197.7	192.4	191.0	189.1	188.4
60°	193.4	185.1	179.9	176.3	175.1	172.8	173.2
62.5°	174.6	167.8	163.4	161.4	159.8	157.8	158.5
65°	147.7	142.7	140.3	138.5	136.6	135.4	136.3
67.5°	123.9	120.5	117.3	116.2	115.3	115.1	114.1
70°	108.4	105.6	102.7	102.0	102.0	101.1	100.8
72.5°	93.4	91.4	89.5	88.9	88.2	88.6	87.6
75°	72.2	70.5	69.8	69.1	68.9	68.9	68.2
77.5°	53.3	52.1	51.0	51.0	50.1	49.8	49.7
80°	40.5	40.0	39.1	39.1	38.6	38.8	38.3
82.5°	30.4	29.8	29.6	29.2	28.5	28.6	28.1
85°	16.3	15.6	15.4	14.7	14.2	14.7	14.2
87.5°	8.0	8.0	7.9	7.5	7.4	7.4	6.9
90°	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P332716

CATALOG NUMBER: S124DIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)