

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333078

Luminaire Tested: **S124RDIW-S1020D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333078
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D470U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5799.2 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	76	76	76	76	76	76	72		
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	65	65	65	65	65	65	61		
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	56	56	56	56	56	56	52		
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	48	48	48	48	48	48	45		
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	41	41	41	41	41	41	38		
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	36	36	36	36	36	36	34		
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	32	32	32	32	32	32	30		
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	29	29	29	29	29	29	26		
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	26	26	26	26	26	26	24		
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	23	23	23	23	23	23	21		
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	21	21	21	21	21	21	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.9
10°-20°	473.0	8.2
20°-30°	683.0	11.8
30°-40°	774.2	13.4
40°-50°	747.6	12.9
50°-60°	621.7	10.7
60°-70°	429.3	7.4
70°-80°	217.6	3.8
80°-90°	57.6	1.0
90°-100°	38.6	0.7
100°-110°	114.5	2.0
110°-120°	194.3	3.4
120°-130°	256.2	4.4
130°-140°	287.7	5.0
140°-150°	282.7	4.9
150°-160°	237.8	4.1
160°-170°	158.2	2.7
170°-180°	55.4	1.0
0°-30°	1325.6	22.9
0°-40°	2099.9	36.2
0°-60°	3469.2	59.8
0°-90°	4173.6	72.0
90°-120°	347.4	6.0
90°-150°	1174.1	20.2
90°-180°	1626.0	28.0
0°-180°	5799.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	1	6	10	13	14	5
95°	27	31	34	36	36	30
105°	106	106	108	109	111	112
115°	198	198	197	196	196	195
125°	288	288	287	286	286	256
135°	371	374	374	373	372	287
145°	451	453	453	453	451	282
155°	517	517	516	518	516	238
165°	562	561	560	563	561	158
175°	585	583	582	585	582	56
180°	586	586	586	586	586	



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.7	24.0	22.2	20.5	18.7	17.8	17.7	17.6	17.6	17.5	17.4
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	9.7	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3
95°	27.2	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7
97.5°	47.5	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8
100°	63.4	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5
102.5°	80.1	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8
105°	105.6	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1
107.5°	132.3	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4
110°	150.4	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.3	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6
115°	197.6	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6
117.5°	224.2	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6
120°	242.0	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9
122.5°	260.5	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2
125°	287.7	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1
127.5°	312.5	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9
130°	329.9	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0
132.5°	347.6	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1
135°	371.1	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6
137.5°	396.7	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4
140°	413.7	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5
142.5°	429.3	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8
145°	450.9	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	472.3	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0
150°	485.3	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.6	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3
155°	516.6	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5
157.5°	532.5	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9
160°	542.0	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4
162.5°	550.7	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6
165°	562.3	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7
167.5°	571.3	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1
170°	576.4	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2
172.5°	580.0	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9
175°	585.0	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0
177.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	17.2	17.1	17.0	17.1	17.3	17.6	17.9	18.2
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	18.7	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.0	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.2	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.7	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.1	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.5	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	133.7	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.5	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P333078

CATALOG NUMBER: S124RDIW-S1020D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.5	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	223.3	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	241.4	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.9	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.9	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.7	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.8	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.9	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.4	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	398.1	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.4	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.9	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.9	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.6	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.2	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	541.7	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.1	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.3	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	570.7	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	575.8	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	579.6	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.0	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)