

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333016

Luminaire Tested: **S124RDIW-S350D470U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333016
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3112.1 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48						48														
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	48	47	47	41						41														
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35						35														
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30						30														
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26						26														
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	29	26	23						23														
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20						20														
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18						18														
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16						16														
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15						15														
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13						13														

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	1.8
10°-20°	171.7	5.5
20°-30°	268.5	8.6
30°-40°	298.5	9.6
40°-50°	264.9	8.5
50°-60°	206.4	6.6
60°-70°	135.1	4.3
70°-80°	66.4	2.1
80°-90°	18.2	0.6
90°-100°	38.6	1.2
100°-110°	114.5	3.7
110°-120°	194.3	6.2
120°-130°	256.2	8.2
130°-140°	287.7	9.2
140°-150°	282.7	9.1
150°-160°	237.8	7.6
160°-170°	158.2	5.1
170°-180°	55.4	1.8
0°-30°	497.1	16.0
0°-40°	795.6	25.6
0°-60°	1266.9	40.7
0°-90°	1486.6	47.8
90°-120°	347.4	11.2
90°-150°	1174.1	37.7
90°-180°	1626.0	52.2
0°-180°	3112.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	14	1	14	1	14	7
95°	36	27	36	27	36	37
105°	111	106	111	106	111	117
115°	196	198	196	198	196	193
125°	286	288	286	288	286	255
135°	372	371	372	371	372	287
145°	451	451	451	451	451	282
155°	516	517	516	517	516	238
165°	561	562	561	562	561	158
175°	582	585	582	585	582	55
180°	586	586	586	586	586	



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	6.9	6.7	6.8	6.8	6.9	6.6	6.7	7.0	6.5	6.5	6.4
90°	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2	10.6	10.0	9.2
92.5°	20.1	20.0	19.9	19.8	19.6	19.4	19.0	18.7	18.3	17.9	17.4
95°	35.8	35.8	35.8	35.8	35.8	35.6	35.3	35.0	34.7	34.4	33.7
97.5°	56.1	56.1	56.1	56.1	56.1	55.9	55.6	55.2	54.8	54.5	53.6
100°	70.2	70.2	70.2	70.2	70.2	70.1	69.9	69.7	69.5	69.3	68.4
102.5°	86.2	86.1	86.0	85.9	85.9	85.7	85.4	85.1	84.8	84.6	83.7
105°	110.6	110.3	110.0	109.7	109.4	109.1	108.8	108.5	108.1	107.8	107.4
107.5°	134.3	134.3	134.4	134.4	134.4	134.3	134.0	133.7	133.4	133.1	133.1
110°	151.3	151.0	150.7	150.4	150.1	150.1	150.3	150.5	150.7	150.9	151.0



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.7	168.7	168.6	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.8
115°	195.8	195.9	196.0	196.1	196.2	196.3	196.4	196.5	196.6	196.7	196.9
117.5°	221.5	221.7	221.9	222.1	222.3	222.6	222.9	223.3	223.6	223.9	224.1
120°	241.1	240.9	240.7	240.5	240.3	240.4	240.9	241.4	241.9	242.4	242.7
122.5°	257.4	257.7	258.1	258.5	258.8	259.2	259.5	259.9	260.2	260.6	260.7
125°	285.5	285.7	285.9	286.1	286.3	286.5	286.7	286.9	287.1	287.3	287.4
127.5°	311.5	311.7	311.8	312.0	312.1	312.3	312.5	312.7	312.9	313.1	313.3
130°	328.5	328.9	329.3	329.7	330.1	330.4	330.6	330.8	331.0	331.2	331.2
132.5°	346.7	346.8	347.0	347.1	347.3	347.5	347.7	347.9	348.1	348.3	348.4
135°	371.6	371.9	372.2	372.5	372.8	373.0	373.2	373.4	373.6	373.8	373.8
137.5°	397.8	397.7	397.6	397.6	397.5	397.6	397.9	398.1	398.4	398.7	398.5
140°	413.7	413.8	413.9	414.0	414.1	414.2	414.3	414.4	414.5	414.6	414.6
142.5°	429.7	429.7	429.7	429.7	429.7	429.8	429.8	429.8	429.8	429.8	429.9
145°	451.3	451.6	451.9	452.2	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	473.3	473.4	473.5	473.6	473.7	473.8	473.8	473.9	474.0	474.1	474.2
150°	486.7	486.8	486.9	487.0	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	499.0	499.3	499.5	499.8	500.0	500.1	499.8	499.6	499.3	499.1	499.0
155°	516.1	516.5	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1	516.2
157.5°	531.4	531.8	532.1	532.5	532.8	532.8	532.5	532.2	531.9	531.6	531.6
160°	540.1	540.6	541.2	541.7	542.2	542.3	542.0	541.7	541.4	541.1	541.2
162.5°	549.2	549.7	550.2	550.7	551.2	551.2	550.7	550.1	549.6	549.0	549.1
165°	561.0	561.4	561.8	562.2	562.6	562.5	561.9	561.3	560.7	560.1	560.3
167.5°	569.4	570.0	570.7	571.3	571.9	571.9	571.3	570.7	570.1	569.5	569.5
170°	574.1	574.8	575.5	576.2	576.9	577.0	576.4	575.8	575.2	574.6	574.5
172.5°	578.1	578.8	579.5	580.2	580.9	580.9	580.3	579.6	578.9	578.2	578.2
175°	582.3	583.0	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3	582.4
177.5°	584.5	585.1	585.8	586.4	587.0	587.1	586.5	586.0	585.4	584.8	584.8
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	6.2	5.9	6.1	5.9	5.9	6.4	6.7	6.7	6.4	6.0	5.7
90°	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4	2.5	3.6	4.7
92.5°	16.8	16.3	15.7	14.8	13.5	12.2	11.0	9.7	11.0	12.2	13.5
95°	33.0	32.3	31.6	30.8	29.9	29.0	28.1	27.2	28.1	29.0	29.9
97.5°	52.8	52.0	51.2	50.4	49.7	48.9	48.2	47.5	48.2	48.9	49.7
100°	67.5	66.6	65.7	65.1	64.6	64.2	63.8	63.4	63.8	64.2	64.6
102.5°	82.9	82.1	81.3	80.8	80.6	80.4	80.3	80.1	80.3	80.4	80.6
105°	107.0	106.6	106.2	106.0	105.9	105.8	105.7	105.6	105.7	105.8	105.9
107.5°	133.0	133.0	132.9	132.8	132.7	132.6	132.4	132.3	132.4	132.6	132.7
110°	151.1	151.2	151.3	151.2	151.0	150.8	150.6	150.4	150.6	150.8	151.0



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.0	169.2	169.4	169.5	169.4	169.4	169.3	169.3	169.3	169.4	169.4
115°	197.1	197.3	197.5	197.6	197.6	197.6	197.6	197.6	197.6	197.6	197.6
117.5°	224.2	224.4	224.5	224.5	224.5	224.4	224.3	224.2	224.3	224.4	224.5
120°	243.0	243.3	243.6	243.6	243.2	242.8	242.4	242.0	242.4	242.8	243.2
122.5°	260.8	261.0	261.1	261.1	260.9	260.8	260.6	260.5	260.6	260.8	260.9
125°	287.5	287.6	287.7	287.7	287.7	287.7	287.7	287.7	287.7	287.7	287.7
127.5°	313.4	313.6	313.8	313.7	313.4	313.1	312.8	312.5	312.8	313.1	313.4
130°	331.2	331.2	331.2	331.1	330.8	330.5	330.2	329.9	330.2	330.5	330.8
132.5°	348.4	348.5	348.6	348.5	348.3	348.1	347.9	347.6	347.9	348.1	348.3
135°	373.8	373.8	373.8	373.5	372.9	372.3	371.7	371.1	371.7	372.3	372.9
137.5°	398.4	398.2	398.0	397.8	397.5	397.2	397.0	396.7	397.0	397.2	397.5
140°	414.6	414.6	414.6	414.5	414.3	414.1	413.9	413.7	413.9	414.1	414.3
142.5°	430.0	430.1	430.2	430.1	429.9	429.7	429.5	429.3	429.5	429.7	429.9
145°	452.9	452.8	452.7	452.5	452.1	451.7	451.3	450.9	451.3	451.7	452.1
147.5°	474.2	474.3	474.4	474.2	473.7	473.2	472.7	472.3	472.7	473.2	473.7
150°	487.1	487.1	487.1	486.9	486.5	486.1	485.7	485.3	485.7	486.1	486.5
152.5°	498.9	498.8	498.8	498.6	498.4	498.1	497.9	497.6	497.9	498.1	498.4
155°	516.3	516.4	516.5	516.6	516.6	516.6	516.6	516.6	516.6	516.6	516.6
157.5°	531.7	531.7	531.7	531.8	532.0	532.2	532.3	532.5	532.3	532.2	532.0
160°	541.3	541.4	541.5	541.6	541.7	541.8	541.9	542.0	541.9	541.8	541.7
162.5°	549.2	549.3	549.4	549.6	549.9	550.1	550.4	550.7	550.4	550.1	549.9
165°	560.5	560.7	560.9	561.1	561.4	561.7	562.0	562.3	562.0	561.7	561.4
167.5°	569.5	569.4	569.4	569.6	570.1	570.5	570.9	571.3	570.9	570.5	570.1
170°	574.4	574.3	574.2	574.4	574.9	575.4	575.9	576.4	575.9	575.4	574.9
172.5°	578.2	578.1	578.1	578.3	578.8	579.2	579.6	580.0	579.6	579.2	578.8
175°	582.5	582.6	582.7	583.0	583.5	584.0	584.5	585.0	584.5	584.0	583.5
177.5°	584.8	584.8	584.8	585.0	585.4	585.8	586.2	586.6	586.2	585.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	5.9	5.9	6.1	5.8	6.2	6.3	6.3	6.4	6.7	6.5	6.5
90°	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2	11.8	12.4	12.8
92.5°	14.8	15.7	16.3	16.8	17.4	17.9	18.3	18.7	19.0	19.4	19.6
95°	30.8	31.6	32.3	33.0	33.7	34.4	34.7	35.0	35.3	35.6	35.8
97.5°	50.4	51.2	52.0	52.8	53.6	54.5	54.8	55.2	55.6	55.9	56.1
100°	65.1	65.7	66.6	67.5	68.4	69.3	69.5	69.7	69.9	70.1	70.2
102.5°	80.8	81.3	82.1	82.9	83.7	84.6	84.8	85.1	85.4	85.7	85.9
105°	106.0	106.2	106.6	107.0	107.4	107.8	108.1	108.5	108.8	109.1	109.4
107.5°	132.8	132.9	133.0	133.0	133.1	133.1	133.4	133.7	134.0	134.3	134.4
110°	151.2	151.3	151.2	151.1	151.0	150.9	150.7	150.5	150.3	150.1	150.1



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	169.5	169.4	169.2	169.0	168.8	168.7	168.6	168.6	168.5	168.5	168.5
115°	197.6	197.5	197.3	197.1	196.9	196.7	196.6	196.5	196.4	196.3	196.2
117.5°	224.5	224.5	224.4	224.2	224.1	223.9	223.6	223.3	222.9	222.6	222.3
120°	243.6	243.6	243.3	243.0	242.7	242.4	241.9	241.4	240.9	240.4	240.3
122.5°	261.1	261.1	261.0	260.8	260.7	260.6	260.2	259.9	259.5	259.2	258.8
125°	287.7	287.7	287.6	287.5	287.4	287.3	287.1	286.9	286.7	286.5	286.3
127.5°	313.7	313.8	313.6	313.4	313.3	313.1	312.9	312.7	312.5	312.3	312.1
130°	331.1	331.2	331.2	331.2	331.2	331.2	331.0	330.8	330.6	330.4	330.1
132.5°	348.5	348.6	348.5	348.4	348.4	348.3	348.1	347.9	347.7	347.5	347.3
135°	373.5	373.8	373.8	373.8	373.8	373.8	373.6	373.4	373.2	373.0	372.8
137.5°	397.8	398.0	398.2	398.4	398.5	398.7	398.4	398.1	397.9	397.6	397.5
140°	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.4	414.3	414.2	414.1
142.5°	430.1	430.2	430.1	430.0	429.9	429.8	429.8	429.8	429.8	429.8	429.7
145°	452.5	452.7	452.8	452.9	453.0	453.1	453.0	452.9	452.8	452.7	452.5
147.5°	474.2	474.4	474.3	474.2	474.2	474.1	474.0	473.9	473.8	473.8	473.7
150°	486.9	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	498.6	498.8	498.8	498.9	499.0	499.1	499.3	499.6	499.8	500.1	500.0
155°	516.6	516.5	516.4	516.3	516.2	516.1	516.5	516.9	517.3	517.7	517.7
157.5°	531.8	531.7	531.7	531.7	531.6	531.6	531.9	532.2	532.5	532.8	532.8
160°	541.6	541.5	541.4	541.3	541.2	541.1	541.4	541.7	542.0	542.3	542.2
162.5°	549.6	549.4	549.3	549.2	549.1	549.0	549.6	550.1	550.7	551.2	551.2
165°	561.1	560.9	560.7	560.5	560.3	560.1	560.7	561.3	561.9	562.5	562.6
167.5°	569.6	569.4	569.4	569.5	569.5	569.5	570.1	570.7	571.3	571.9	571.9
170°	574.4	574.2	574.3	574.4	574.5	574.6	575.2	575.8	576.4	577.0	576.9
172.5°	578.3	578.1	578.1	578.2	578.2	578.2	578.9	579.6	580.3	580.9	580.9
175°	583.0	582.7	582.6	582.5	582.4	582.3	583.0	583.7	584.4	585.1	585.1
177.5°	585.0	584.8	584.8	584.8	584.8	584.8	585.4	586.0	586.5	587.1	587.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	7.0	6.8	6.7	6.9	6.7	6.8	7.0	6.5	6.5	6.7	6.4
90°	13.0	13.2	13.4	13.6	13.4	13.2	13.0	12.8	12.4	11.8	11.2
92.5°	19.8	19.9	20.0	20.1	20.0	19.9	19.8	19.6	19.4	19.0	18.7
95°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.6	35.3	35.0
97.5°	56.1	56.1	56.1	56.1	56.1	56.1	56.1	56.1	55.9	55.6	55.2
100°	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.2	70.1	69.9	69.7
102.5°	85.9	86.0	86.1	86.2	86.1	86.0	85.9	85.9	85.7	85.4	85.1
105°	109.7	110.0	110.3	110.6	110.3	110.0	109.7	109.4	109.1	108.8	108.5
107.5°	134.4	134.4	134.3	134.3	134.3	134.4	134.4	134.4	134.3	134.0	133.7
110°	150.4	150.7	151.0	151.3	151.0	150.7	150.4	150.1	150.1	150.3	150.5



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	168.6	168.6	168.7	168.7	168.7	168.6	168.6	168.5	168.5	168.5	168.6
115°	196.1	196.0	195.9	195.8	195.9	196.0	196.1	196.2	196.3	196.4	196.5
117.5°	222.1	221.9	221.7	221.5	221.7	221.9	222.1	222.3	222.6	222.9	223.3
120°	240.5	240.7	240.9	241.1	240.9	240.7	240.5	240.3	240.4	240.9	241.4
122.5°	258.5	258.1	257.7	257.4	257.7	258.1	258.5	258.8	259.2	259.5	259.9
125°	286.1	285.9	285.7	285.5	285.7	285.9	286.1	286.3	286.5	286.7	286.9
127.5°	312.0	311.8	311.7	311.5	311.7	311.8	312.0	312.1	312.3	312.5	312.7
130°	329.7	329.3	328.9	328.5	328.9	329.3	329.7	330.1	330.4	330.6	330.8
132.5°	347.1	347.0	346.8	346.7	346.8	347.0	347.1	347.3	347.5	347.7	347.9
135°	372.5	372.2	371.9	371.6	371.9	372.2	372.5	372.8	373.0	373.2	373.4
137.5°	397.6	397.6	397.7	397.8	397.7	397.6	397.6	397.5	397.6	397.9	398.1
140°	414.0	413.9	413.8	413.7	413.8	413.9	414.0	414.1	414.2	414.3	414.4
142.5°	429.7	429.7	429.7	429.7	429.7	429.7	429.7	429.7	429.8	429.8	429.8
145°	452.2	451.9	451.6	451.3	451.6	451.9	452.2	452.5	452.7	452.8	452.9
147.5°	473.6	473.5	473.4	473.3	473.4	473.5	473.6	473.7	473.8	473.8	473.9
150°	487.0	486.9	486.8	486.7	486.8	486.9	487.0	487.1	487.1	487.1	487.1
152.5°	499.8	499.5	499.3	499.0	499.3	499.5	499.8	500.0	500.1	499.8	499.6
155°	517.3	516.9	516.5	516.1	516.5	516.9	517.3	517.7	517.7	517.3	516.9
157.5°	532.5	532.1	531.8	531.4	531.8	532.1	532.5	532.8	532.8	532.5	532.2
160°	541.7	541.2	540.6	540.1	540.6	541.2	541.7	542.2	542.3	542.0	541.7
162.5°	550.7	550.2	549.7	549.2	549.7	550.2	550.7	551.2	551.2	550.7	550.1
165°	562.2	561.8	561.4	561.0	561.4	561.8	562.2	562.6	562.5	561.9	561.3
167.5°	571.3	570.7	570.0	569.4	570.0	570.7	571.3	571.9	571.9	571.3	570.7
170°	576.2	575.5	574.8	574.1	574.8	575.5	576.2	576.9	577.0	576.4	575.8
172.5°	580.2	579.5	578.8	578.1	578.8	579.5	580.2	580.9	580.9	580.3	579.6
175°	584.4	583.7	583.0	582.3	583.0	583.7	584.4	585.1	585.1	584.4	583.7
177.5°	586.4	585.8	585.1	584.5	585.1	585.8	586.4	587.0	587.1	586.5	586.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	6.3	6.3	6.2	5.8	6.1	5.9	5.9	5.7	6.0	6.4	6.7
90°	10.6	10.0	9.2	8.4	7.6	6.7	5.8	4.7	3.6	2.5	1.4
92.5°	18.3	17.9	17.4	16.8	16.3	15.7	14.8	13.5	12.2	11.0	9.7
95°	34.7	34.4	33.7	33.0	32.3	31.6	30.8	29.9	29.0	28.1	27.2
97.5°	54.8	54.5	53.6	52.8	52.0	51.2	50.4	49.7	48.9	48.2	47.5
100°	69.5	69.3	68.4	67.5	66.6	65.7	65.1	64.6	64.2	63.8	63.4
102.5°	84.8	84.6	83.7	82.9	82.1	81.3	80.8	80.6	80.4	80.3	80.1
105°	108.1	107.8	107.4	107.0	106.6	106.2	106.0	105.9	105.8	105.7	105.6
107.5°	133.4	133.1	133.1	133.0	133.0	132.9	132.8	132.7	132.6	132.4	132.3
110°	150.7	150.9	151.0	151.1	151.2	151.3	151.2	151.0	150.8	150.6	150.4



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	168.6	168.7	168.8	169.0	169.2	169.4	169.5	169.4	169.4	169.3	169.3
115°	196.6	196.7	196.9	197.1	197.3	197.5	197.6	197.6	197.6	197.6	197.6
117.5°	223.6	223.9	224.1	224.2	224.4	224.5	224.5	224.5	224.4	224.3	224.2
120°	241.9	242.4	242.7	243.0	243.3	243.6	243.6	243.2	242.8	242.4	242.0
122.5°	260.2	260.6	260.7	260.8	261.0	261.1	261.1	260.9	260.8	260.6	260.5
125°	287.1	287.3	287.4	287.5	287.6	287.7	287.7	287.7	287.7	287.7	287.7
127.5°	312.9	313.1	313.3	313.4	313.6	313.8	313.7	313.4	313.1	312.8	312.5
130°	331.0	331.2	331.2	331.2	331.2	331.2	331.1	330.8	330.5	330.2	329.9
132.5°	348.1	348.3	348.4	348.4	348.5	348.6	348.5	348.3	348.1	347.9	347.6
135°	373.6	373.8	373.8	373.8	373.8	373.8	373.5	372.9	372.3	371.7	371.1
137.5°	398.4	398.7	398.5	398.4	398.2	398.0	397.8	397.5	397.2	397.0	396.7
140°	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.3	414.1	413.9	413.7
142.5°	429.8	429.8	429.9	430.0	430.1	430.2	430.1	429.9	429.7	429.5	429.3
145°	453.0	453.1	453.0	452.9	452.8	452.7	452.5	452.1	451.7	451.3	450.9
147.5°	474.0	474.1	474.2	474.2	474.3	474.4	474.2	473.7	473.2	472.7	472.3
150°	487.1	487.1	487.1	487.1	487.1	487.1	486.9	486.5	486.1	485.7	485.3
152.5°	499.3	499.1	499.0	498.9	498.8	498.8	498.6	498.4	498.1	497.9	497.6
155°	516.5	516.1	516.2	516.3	516.4	516.5	516.6	516.6	516.6	516.6	516.6
157.5°	531.9	531.6	531.6	531.7	531.7	531.7	531.8	532.0	532.2	532.3	532.5
160°	541.4	541.1	541.2	541.3	541.4	541.5	541.6	541.7	541.8	541.9	542.0
162.5°	549.6	549.0	549.1	549.2	549.3	549.4	549.6	549.9	550.1	550.4	550.7
165°	560.7	560.1	560.3	560.5	560.7	560.9	561.1	561.4	561.7	562.0	562.3
167.5°	570.1	569.5	569.5	569.5	569.4	569.4	569.6	570.1	570.5	570.9	571.3
170°	575.2	574.6	574.5	574.4	574.3	574.2	574.4	574.9	575.4	575.9	576.4
172.5°	578.9	578.2	578.2	578.2	578.1	578.1	578.3	578.8	579.2	579.6	580.0
175°	583.0	582.3	582.4	582.5	582.6	582.7	583.0	583.5	584.0	584.5	585.0
177.5°	585.4	584.8	584.8	584.8	584.8	584.8	585.0	585.4	585.8	586.2	586.6
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.7	6.4	5.9	5.9	6.1	5.9	6.2	6.4	6.5	6.5	7.0
90°	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6	11.2
92.5°	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3	18.7
95°	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7	35.0
97.5°	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8	55.2
100°	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5	69.7
102.5°	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8	85.1
105°	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1	108.5
107.5°	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4	133.7
110°	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7	150.5



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6	168.6
115°	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6	196.5
117.5°	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6	223.3
120°	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9	241.4
122.5°	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2	259.9
125°	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1	286.9
127.5°	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9	312.7
130°	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0	330.8
132.5°	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1	347.9
135°	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6	373.4
137.5°	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4	398.1
140°	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5	414.4
142.5°	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8	429.8
145°	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0	452.9
147.5°	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0	473.9
150°	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3	499.6
155°	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5	516.9
157.5°	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9	532.2
160°	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4	541.7
162.5°	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6	550.1
165°	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7	561.3
167.5°	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1	570.7
170°	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2	575.8
172.5°	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9	579.6
175°	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0	583.7
177.5°	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4	586.0
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	6.7	6.6	6.9	6.8	6.8	6.7	6.9
90°	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P333016

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)