

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333040

Luminaire Tested: **S124RDIW-S575D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333040  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U835-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5106.4 lumens  
Efficiency: N/A  
Efficacy: 135.8 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48														
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47	41	41	41	41	41	41	41														
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35	35	35	35	35	35	35														
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30	30	30	30	30	30	30														
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26	26	26	26	26	26	26														
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	32	29	26	23	23	23	23	23	23	23														
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	20	20	20	20	20	20	20														
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18	18	18	18	18	18	18														
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16	16	16	16														
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15	15	15	15	15	15	15														
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	14	14	14	14	14	14	14														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7796	7796	7796	7796
5°	9043	7819	6912	7819
10°	10698	7785	6169	7785
15°	12357	7713	5300	7713
20°	13759	7614	4793	7614
25°	14203	7517	4450	7517
30°	12433	7399	4243	7399
35°	9678	7224	4119	7224
40°	7258	7024	4051	7024
45°	5730	6703	4015	6703
50°	4838	6332	3900	6332
55°	4217	5925	3690	5925
60°	3794	5503	3266	5503
65°	3345	5047	2810	5047
70°	3012	4574	2535	4574
75°	2523	4055	2162	4055
80°	2134	3454	2027	3454
85°	1806	2705	1806	2705



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.6	1.8
10°-20°	282.2	5.5
20°-30°	441.5	8.6
30°-40°	490.8	9.6
40°-50°	435.4	8.5
50°-60°	339.3	6.6
60°-70°	222.1	4.4
70°-80°	109.2	2.1
80°-90°	29.8	0.6
90°-100°	63.3	1.2
100°-110°	187.5	3.7
110°-120°	318.2	6.2
120°-130°	419.6	8.2
130°-140°	471.3	9.2
140°-150°	463.1	9.1
150°-160°	389.5	7.6
160°-170°	259.1	5.1
170°-180°	90.7	1.8
0°-30°	817.3	16.0
0°-40°	1308.0	25.6
0°-60°	2082.7	40.8
0°-90°	2443.9	47.9
90°-120°	569.0	11.1
90°-150°	1923.1	37.7
90°-180°	2662.0	52.1
0°-180°	5106.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	966	966	966	966	966	
5°	1116	965	853	965	1116	113
15°	1478	923	634	923	1478	420
25°	1594	844	500	844	1594	707
35°	982	733	418	733	982	616
45°	502	587	352	587	502	397
55°	300	421	262	421	300	273
65°	175	264	147	264	175	176
75°	81	130	69	130	81	89
85°	20	29	20	29	20	23
90°	22	2	22	2	22	12
95°	59	44	59	44	59	61
105°	181	173	181	173	181	191
115°	321	324	321	324	321	317
125°	468	471	468	471	468	417
135°	609	608	609	608	609	470
145°	739	738	739	738	739	463
155°	845	846	845	846	845	389
165°	919	921	919	921	919	259
175°	954	958	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1018.6	1021.4	1018.6	1018.3	1015.2	1014.3	1013.0	1009.0	1001.5	997.1	998.1
5°	1115.9	1125.6	1120.2	1119.4	1110.8	1102.3	1096.8	1084.4	1071.1	1062.2	1054.8
7.5°	1228.4	1234.0	1230.6	1225.1	1211.3	1203.4	1190.8	1174.4	1150.7	1132.5	1116.0
10°	1305.0	1309.6	1308.1	1298.0	1287.9	1267.2	1255.6	1232.6	1202.6	1178.9	1156.7
12.5°	1380.3	1385.3	1371.6	1372.1	1352.9	1336.6	1318.1	1289.3	1254.6	1224.0	1196.3
15°	1478.5	1472.3	1472.3	1464.5	1443.1	1420.5	1401.5	1371.1	1327.5	1291.0	1252.5
17.5°	1555.4	1557.6	1554.4	1536.0	1519.2	1495.9	1460.9	1425.5	1385.0	1335.9	1296.6
20°	1601.5	1601.5	1598.0	1585.5	1563.7	1538.8	1501.1	1462.6	1411.2	1361.8	1317.4
22.5°	1620.1	1621.4	1617.3	1607.0	1587.4	1563.1	1531.0	1491.8	1438.9	1383.3	1328.3
25°	1594.5	1601.8	1602.6	1599.9	1594.1	1579.3	1551.7	1511.6	1464.1	1403.8	1344.7
27.5°	1463.9	1473.2	1481.4	1494.8	1512.7	1522.1	1523.3	1502.9	1461.5	1403.5	1344.0
30°	1333.8	1341.5	1366.8	1399.9	1425.6	1448.9	1469.2	1474.6	1451.3	1399.1	1336.5
32.5°	1189.3	1199.9	1225.2	1260.8	1303.6	1343.1	1388.6	1411.7	1411.1	1379.8	1321.9
35°	982.0	989.8	1013.2	1050.5	1101.9	1160.6	1232.6	1288.6	1326.8	1324.0	1288.6
37.5°	792.0	800.8	824.4	855.4	905.2	977.9	1047.6	1124.8	1195.3	1234.9	1223.0
40°	688.7	689.1	712.0	743.9	790.6	854.0	929.9	1015.5	1094.1	1158.3	1170.7
42.5°	607.1	607.2	622.4	656.8	690.4	750.1	822.5	907.5	999.5	1073.6	1106.6
45°	501.9	505.4	517.9	538.5	564.9	615.5	673.5	752.5	855.6	943.5	998.4
47.5°	425.0	430.2	438.1	454.9	476.0	509.7	557.6	628.6	712.5	809.2	887.3
50°	385.2	386.0	396.1	405.4	423.7	450.6	492.6	551.7	628.8	721.7	808.5
52.5°	351.0	350.8	356.9	368.7	383.6	404.5	438.4	492.3	560.6	643.9	733.5
55°	299.6	301.5	306.2	315.5	326.8	341.6	368.5	408.9	462.6	533.8	615.1
57.5°	260.5	261.5	265.2	269.2	279.5	290.3	310.4	338.5	383.8	442.1	517.9
60°	235.0	235.4	236.6	242.4	250.6	260.7	274.3	298.0	336.2	389.5	449.4
62.5°	210.1	210.8	212.6	216.9	223.2	230.2	244.4	263.5	295.1	340.6	394.6
65°	175.1	175.5	178.2	179.8	184.8	191.0	201.5	214.4	236.2	274.3	315.2
67.5°	146.3	146.3	146.4	148.6	152.1	156.2	162.5	172.8	189.2	212.6	248.6
70°	127.6	127.6	128.4	129.6	131.5	135.0	138.5	146.3	158.4	177.4	205.0
72.5°	110.2	110.5	111.3	111.5	112.5	115.4	118.0	122.9	131.9	146.3	168.6
75°	80.9	82.1	84.0	85.6	87.5	87.2	89.9	93.0	95.7	104.3	117.1
77.5°	60.2	59.6	59.8	61.2	61.4	61.8	63.7	66.1	68.2	72.2	76.8
80°	45.9	45.9	47.1	47.5	47.1	47.5	49.4	50.6	51.4	52.9	57.2
82.5°	34.7	35.3	34.9	35.3	35.6	36.0	37.6	37.8	38.6	39.2	41.0
85°	19.5	19.8	20.2	19.5	19.5	19.5	20.2	20.6	21.4	21.0	21.8
87.5°	11.3	10.9	11.2	11.1	11.3	10.9	11.0	11.4	10.6	10.7	10.5
90°	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3	17.3	16.3	15.0
92.5°	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6	30.0	29.4	28.5
95°	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4	56.9	56.4	55.3
97.5°	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4	89.8	89.2	87.9
100°	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2	113.9	113.6	112.1
102.5°	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4	139.0	138.5	137.1
105°	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6	177.1	176.6	176.0
107.5°	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0	218.5	218.1	218.0
110°	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5	246.8	247.1	247.3



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1	276.2	276.2	276.5
115°	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8	321.9	322.1	322.4
117.5°	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7	366.2	366.8	367.0
120°	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4	396.2	397.1	397.6
122.5°	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6	426.2	426.8	427.0
125°	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9	470.2	470.5	470.7
127.5°	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2	512.5	512.9	513.1
130°	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9	542.2	542.5	542.5
132.5°	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8	570.1	570.4	570.6
135°	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6	612.0	612.3	612.3
137.5°	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1	652.5	653.0	652.7
140°	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8	678.9	679.1	679.1
142.5°	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0	704.0	704.0	704.2
145°	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2	776.3	776.5	776.6
150°	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2	817.8	817.4	817.3
155°	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4	845.5
157.5°	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7	871.2	870.7	870.8
160°	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2	886.7	886.2	886.3
162.5°	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0	900.1	899.2	899.4
165°	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3	918.3	917.3	917.7
167.5°	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8	933.8	932.8	932.7
170°	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1	942.1	941.1	940.9
172.5°	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3	948.2	947.0	947.0
175°	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7	953.9
177.5°	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7	958.8	957.9	957.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	995.0	990.6	988.4	983.4	977.5	974.4	971.6	967.6	962.3	956.7	952.6
5°	1045.5	1036.1	1024.4	1010.4	998.0	985.9	975.4	964.9	952.9	940.4	928.0
7.5°	1097.3	1078.9	1059.1	1036.1	1013.8	993.5	974.8	956.9	936.7	918.5	902.0
10°	1133.4	1108.5	1080.9	1051.7	1022.5	997.2	972.3	949.7	924.8	902.7	884.0
12.5°	1162.7	1133.4	1100.2	1063.8	1028.7	998.1	969.5	940.1	911.8	887.7	862.8
15°	1211.2	1171.1	1126.4	1082.8	1037.3	995.7	957.1	922.9	890.6	856.8	833.0
17.5°	1244.6	1197.0	1142.7	1090.3	1036.5	987.4	943.0	902.2	864.9	830.4	802.1
20°	1264.5	1212.0	1151.7	1092.1	1031.8	979.3	931.5	886.3	847.8	810.5	781.3
22.5°	1275.7	1217.6	1151.7	1089.3	1026.9	970.0	917.5	870.5	828.5	791.2	758.9
25°	1279.3	1217.0	1149.7	1078.1	1009.7	949.4	894.9	843.9	797.2	759.9	725.6
27.5°	1274.3	1201.0	1132.1	1058.6	988.0	924.4	867.2	813.6	766.9	726.8	691.7
30°	1266.8	1188.3	1114.3	1038.1	966.5	905.4	845.1	793.7	745.1	703.5	668.1
32.5°	1250.7	1172.7	1093.2	1015.0	942.5	879.6	822.4	770.7	723.0	680.4	642.8
35°	1218.6	1139.6	1053.2	973.1	901.9	836.5	782.8	733.0	687.5	642.0	602.3
37.5°	1176.3	1095.7	1009.7	922.0	850.7	789.0	739.7	693.0	648.5	607.0	563.0
40°	1136.5	1063.0	974.3	887.1	814.0	754.4	708.9	666.5	621.8	580.5	536.5
42.5°	1088.3	1025.6	936.0	848.5	776.3	718.9	676.5	635.1	594.4	554.4	508.5
45°	1007.7	960.3	876.2	792.2	719.4	662.6	623.7	587.1	551.3	513.2	470.0
47.5°	915.4	883.3	810.8	724.7	657.4	606.3	568.7	538.8	508.5	470.4	432.5
50°	851.3	830.7	760.7	682.1	617.9	570.8	532.3	504.2	479.0	442.4	408.5
52.5°	782.8	771.9	712.7	637.5	575.5	529.4	496.5	471.3	445.7	415.3	383.6
55°	678.6	684.4	634.2	569.2	510.9	472.0	442.0	421.0	399.2	373.5	349.0
57.5°	571.9	593.3	559.6	502.5	447.8	411.9	389.3	371.6	353.4	332.0	311.1
60°	508.1	526.0	507.0	456.8	408.9	375.5	354.5	340.8	322.5	303.1	287.1
62.5°	445.9	465.0	453.7	413.2	368.8	340.0	321.5	308.8	295.2	278.2	261.6
65°	367.7	380.1	374.7	346.7	315.2	290.6	273.5	264.2	251.7	239.3	224.5
67.5°	281.6	305.7	302.5	287.6	260.4	241.2	230.0	221.8	210.4	201.2	191.1
70°	231.5	253.7	253.3	241.2	226.4	208.5	200.8	193.8	183.6	174.7	166.5
72.5°	189.5	209.8	212.8	203.6	193.5	179.9	172.4	167.6	157.8	151.7	145.0
75°	132.7	147.5	151.4	151.4	146.7	139.7	133.1	130.0	122.9	117.5	113.6
77.5°	87.0	96.3	102.4	103.8	104.5	102.2	96.7	94.5	89.2	87.2	83.5
80°	61.5	67.7	74.7	77.0	79.0	78.2	75.9	74.3	69.3	67.3	65.8
82.5°	42.5	45.9	51.7	56.8	56.3	58.3	56.3	55.0	51.2	50.5	48.9
85°	22.2	22.6	23.3	26.8	28.8	29.6	30.0	29.2	28.0	28.0	25.3
87.5°	10.2	9.6	10.0	9.7	9.6	10.5	11.1	11.0	10.5	9.9	9.3
90°	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2	4.0	5.9	7.7
92.5°	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9	18.0	20.0	22.1
95°	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5	46.0	47.5	49.0
97.5°	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8	79.0	80.2	81.3
100°	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9	104.6	105.2	105.9
102.5°	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2	131.5	131.7	132.0
105°	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9	173.1	173.3	173.4
107.5°	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7	216.9	217.1	217.3
110°	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4	246.7	247.1	247.4





TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3	277.3	277.4	277.5
115°	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6	323.6	323.6	323.6
117.5°	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2	367.4	367.5	367.6
120°	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3	397.0	397.6	398.3
122.5°	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6	426.9	427.1	427.4
125°	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3
127.5°	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8	512.3	512.8	513.3
130°	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3	540.8	541.3	541.8
132.5°	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4	569.8	570.1	570.5
135°	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9	608.8	609.8	610.8
137.5°	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7	650.2	650.6	651.1
140°	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6	677.9	678.3	678.6
142.5°	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1	703.5	703.8	704.1
145°	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5	739.1	739.8	740.5
147.5°	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5	774.3	775.1	775.9
150°	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9	795.5	796.2	796.9
152.5°	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1	815.5	815.9	816.3
155°	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1	846.1	846.1	846.1
157.5°	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2	871.9	871.6	871.3
160°	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7	887.5	887.3	887.2
162.5°	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9	901.5	901.0	900.6
165°	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1	920.6	920.1	919.6
167.5°	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7	935.1	934.4	933.7
170°	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1	943.2	942.4	941.6
172.5°	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0	949.3	948.6	947.9
175°	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2	957.3	956.5	955.7
177.5°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	948.3	945.2	941.1	936.4	930.8	925.9	923.7	925.5	926.5	924.0	923.7
5°	919.4	909.7	901.9	890.2	880.9	873.1	867.6	865.3	866.1	859.9	858.3
7.5°	886.9	875.4	862.7	848.8	835.9	824.5	818.5	815.2	808.6	805.8	801.0
10°	866.1	850.5	838.1	821.7	807.0	793.3	786.7	781.3	774.7	771.5	764.9
12.5°	844.6	826.6	812.9	795.9	780.8	764.4	758.1	748.0	737.6	731.1	722.6
15°	814.3	792.6	775.8	755.6	737.7	719.0	702.3	683.6	676.6	661.8	653.3
17.5°	778.9	756.8	736.1	709.0	681.4	658.2	640.3	622.5	611.7	602.3	597.9
20°	755.6	735.4	706.6	675.1	644.3	618.6	604.2	592.6	580.9	574.3	569.6
22.5°	733.5	707.7	674.2	640.2	609.5	589.4	577.2	565.2	555.7	549.4	543.2
25°	696.5	662.6	627.2	588.3	567.3	549.8	536.5	526.8	521.0	512.8	509.7
27.5°	658.4	617.4	578.3	552.2	530.3	514.3	502.8	495.5	488.1	482.8	478.8
30°	629.1	587.5	552.5	527.6	505.4	492.2	482.8	474.3	468.5	464.2	461.1
32.5°	600.2	558.6	529.1	502.4	484.9	472.0	462.0	455.6	451.0	445.5	443.6
35°	558.3	521.4	495.7	471.6	453.7	442.0	434.2	427.6	423.7	422.2	421.0
37.5°	518.1	487.8	460.2	440.4	424.5	415.3	406.1	402.9	400.2	397.4	398.7
40°	492.6	464.2	439.7	418.7	405.8	395.7	390.2	386.4	384.0	384.0	384.0
42.5°	470.5	442.7	418.8	400.0	387.1	378.6	372.5	369.2	368.5	368.1	370.0
45°	436.2	410.5	386.4	370.8	359.9	351.3	347.8	345.1	345.1	346.7	347.1
47.5°	402.2	378.1	358.7	341.3	331.3	326.0	322.9	321.5	321.7	323.2	325.0
50°	381.3	357.6	338.5	322.9	313.6	308.5	305.8	305.0	305.8	305.8	308.5
52.5°	358.6	337.3	318.6	305.5	294.9	290.2	288.7	287.6	288.1	289.3	290.5
55°	325.3	306.2	288.3	275.9	268.1	265.0	261.5	261.9	261.1	261.9	261.9
57.5°	291.9	274.8	258.1	248.2	241.4	236.9	233.1	234.1	233.0	232.8	232.2
60°	270.4	251.7	238.5	229.6	221.8	217.9	214.4	215.2	214.0	213.2	211.7
62.5°	247.1	231.5	218.9	210.3	204.0	199.5	196.0	195.2	192.5	189.9	186.4
65°	213.2	200.4	189.1	180.9	175.1	171.6	168.9	166.5	160.7	154.5	151.4
67.5°	180.3	171.0	160.5	153.6	148.9	144.3	139.1	135.1	129.6	126.2	124.3
70°	159.1	150.2	141.2	134.6	129.6	125.3	119.4	116.7	112.8	111.3	109.3
72.5°	138.9	130.6	122.2	116.3	110.9	107.5	103.0	100.2	98.5	97.9	95.9
75°	108.2	101.6	95.3	89.9	85.6	83.3	81.3	79.4	78.6	75.1	73.1
77.5°	78.9	74.5	70.7	66.8	63.7	62.2	58.4	56.2	54.9	53.2	52.8
80°	61.5	58.4	54.5	52.1	47.9	46.3	44.7	44.4	44.0	43.6	43.2
82.5°	46.2	43.1	39.2	37.8	36.7	35.7	34.8	34.4	34.0	34.2	34.2
85°	23.3	21.8	21.8	21.4	21.0	20.6	20.2	20.2	19.8	20.2	19.8
87.5°	9.7	9.7	9.9	9.6	10.2	10.4	10.3	10.5	11.0	10.6	10.7
90°	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3	19.3	20.3	20.9
92.5°	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6	31.2	31.8	32.2
95°	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4	57.9	58.4	58.6
97.5°	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4	91.0	91.6	91.9
100°	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2	114.5	114.9	115.0
102.5°	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4	139.9	140.3	140.6
105°	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6	178.1	178.6	179.1
107.5°	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0	219.4	219.9	220.1
110°	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5	246.2	245.8	245.9



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1	276.0	276.0	276.0
115°	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8	321.6	321.4	321.3
117.5°	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7	365.1	364.5	364.1
120°	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4	394.6	393.8	393.5
122.5°	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6	425.1	424.5	423.9
125°	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9	469.6	469.2	468.9
127.5°	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2	511.9	511.5	511.2
130°	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9	541.5	541.2	540.7
132.5°	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8	569.5	569.1	568.8
135°	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6	611.3	611.0	610.6
137.5°	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1	651.7	651.3	651.1
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8	678.6	678.4	678.3
142.5°	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0	703.9	703.9	703.9
145°	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9	741.7	741.5	741.2
147.5°	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2	776.1	775.9	775.8
150°	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.8
152.5°	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2	818.6	819.0	819.0
155°	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7	847.3	848.0	848.0
157.5°	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7	872.2	872.7	872.7
160°	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2	887.7	888.2	888.0
162.5°	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0	901.9	902.8	902.8
165°	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3	920.3	921.3	921.5
167.5°	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8	935.7	936.7	936.7
170°	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1	944.1	945.1	945.0
172.5°	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3	950.4	951.5	951.5
175°	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0	957.2	958.3	958.3
177.5°	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7	960.6	961.6	961.5
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	921.8	922.4	920.3	919.6	920.3	922.4	921.8	923.7	924.0	926.5	925.5
5°	855.2	854.4	852.5	852.9	852.5	854.4	855.2	858.3	859.9	866.1	865.3
7.5°	798.2	795.2	796.1	792.9	796.1	795.2	798.2	801.0	805.8	808.6	815.2
10°	763.4	759.1	755.6	752.5	755.6	759.1	763.4	764.9	771.5	774.7	781.3
12.5°	715.8	712.1	707.3	708.3	707.3	712.1	715.8	722.6	731.1	737.6	748.0
15°	648.2	642.4	633.0	634.2	633.0	642.4	648.2	653.3	661.8	676.6	683.6
17.5°	591.0	591.1	586.8	587.8	586.8	591.1	591.0	597.9	602.3	611.7	622.5
20°	561.4	558.7	559.1	557.9	559.1	558.7	561.4	569.6	574.3	580.9	592.6
22.5°	540.9	537.6	534.8	532.4	534.8	537.6	540.9	543.2	549.4	555.7	565.2
25°	506.2	503.9	500.4	499.6	500.4	503.9	506.2	509.7	512.8	521.0	526.8
27.5°	475.7	475.2	473.8	472.0	473.8	475.2	475.7	478.8	482.8	488.1	495.5
30°	457.9	457.2	456.4	455.2	456.4	457.2	457.9	461.1	464.2	468.5	474.3
32.5°	442.1	441.6	440.8	440.9	440.8	441.6	442.1	443.6	445.5	451.0	455.6
35°	419.4	419.0	418.3	417.9	418.3	419.0	419.4	421.0	422.2	423.7	427.6
37.5°	398.3	399.3	398.8	398.7	398.8	399.3	398.3	398.7	397.4	400.2	402.9
40°	383.6	384.0	384.8	384.4	384.8	384.0	383.6	384.0	384.0	384.0	386.4
42.5°	371.5	371.6	372.7	371.3	372.7	371.6	371.5	370.0	368.1	368.5	369.2
45°	349.8	352.1	351.7	351.7	351.7	352.1	349.8	347.1	346.7	345.1	345.1
47.5°	326.0	328.1	328.6	328.5	328.6	328.1	326.0	325.0	323.2	321.7	321.5
50°	310.5	309.7	310.9	310.5	310.9	309.7	310.5	308.5	305.8	305.8	305.0
52.5°	291.5	291.7	291.6	291.2	291.6	291.7	291.5	290.5	289.3	288.1	287.6
55°	262.2	262.6	261.9	262.2	261.9	262.6	262.2	261.9	261.9	261.1	261.9
57.5°	230.5	228.6	229.4	228.5	229.4	228.6	230.5	232.2	232.8	233.0	234.1
60°	207.8	204.7	203.9	202.3	203.9	204.7	207.8	211.7	213.2	214.0	215.2
62.5°	182.2	180.1	177.4	178.7	177.4	180.1	182.2	186.4	189.9	192.5	195.2
65°	148.2	146.7	145.5	147.1	145.5	146.7	148.2	151.4	154.5	160.7	166.5
67.5°	122.7	121.9	121.9	121.1	121.9	121.9	122.7	124.3	126.2	129.6	135.1
70°	109.3	108.2	108.2	107.4	108.2	108.2	109.3	109.3	111.3	112.8	116.7
72.5°	95.6	94.5	94.8	94.3	94.8	94.5	95.6	95.9	97.9	98.5	100.2
75°	70.8	68.9	68.9	69.3	68.9	68.9	70.8	73.1	75.1	78.6	79.4
77.5°	52.8	52.4	53.0	52.3	53.0	52.4	52.8	52.8	53.2	54.9	56.2
80°	43.2	42.8	42.4	43.6	42.4	42.8	43.2	43.2	43.6	44.0	44.4
82.5°	33.5	33.5	33.4	34.9	33.4	33.5	33.5	34.2	34.2	34.0	34.4
85°	20.2	19.5	20.2	19.5	20.2	19.5	20.2	19.8	20.2	19.8	20.2
87.5°	11.4	11.2	10.9	11.3	10.9	11.2	11.4	10.7	10.6	11.0	10.5
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3
92.5°	32.4	32.6	32.8	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6
95°	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4
97.5°	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4
100°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2
102.5°	140.8	140.9	141.0	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4
105°	179.6	180.1	180.6	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6
107.5°	220.1	220.1	220.0	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0
110°	246.4	246.9	247.4	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	276.1	276.2	276.3	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1
115°	321.1	321.0	320.8	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8
117.5°	363.8	363.4	363.1	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7
120°	393.9	394.2	394.5	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4
122.5°	423.3	422.7	422.2	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6
125°	468.6	468.2	467.9	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9
127.5°	511.0	510.7	510.4	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2
130°	540.1	539.4	538.7	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9
132.5°	568.6	568.3	568.0	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8
135°	610.1	609.6	609.1	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6
137.5°	651.2	651.3	651.4	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1
140°	678.1	677.9	677.8	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8
142.5°	703.8	703.8	703.8	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0
145°	740.7	740.2	739.7	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9
147.5°	775.6	775.5	775.3	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2
150°	797.6	797.4	797.3	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9
152.5°	818.6	818.2	817.7	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2
155°	847.3	846.7	846.0	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7
157.5°	872.1	871.6	871.0	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7
160°	887.2	886.3	885.5	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2
162.5°	902.0	901.2	900.4	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0
165°	920.8	920.1	919.5	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3
167.5°	935.7	934.7	933.7	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8
170°	943.8	942.7	941.5	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1
172.5°	950.3	949.2	948.0	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3
175°	957.2	956.0	954.9	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0
177.5°	960.4	959.4	958.3	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	923.7	925.9	930.8	936.4	941.1	945.2	948.3	952.6	956.7	962.3	967.6
5°	867.6	873.1	880.9	890.2	901.9	909.7	919.4	928.0	940.4	952.9	964.9
7.5°	818.5	824.5	835.9	848.8	862.7	875.4	886.9	902.0	918.5	936.7	956.9
10°	786.7	793.3	807.0	821.7	838.1	850.5	866.1	884.0	902.7	924.8	949.7
12.5°	758.1	764.4	780.8	795.9	812.9	826.6	844.6	862.8	887.7	911.8	940.1
15°	702.3	719.0	737.7	755.6	775.8	792.6	814.3	833.0	856.8	890.6	922.9
17.5°	640.3	658.2	681.4	709.0	736.1	756.8	778.9	802.1	830.4	864.9	902.2
20°	604.2	618.6	644.3	675.1	706.6	735.4	755.6	781.3	810.5	847.8	886.3
22.5°	577.2	589.4	609.5	640.2	674.2	707.7	733.5	758.9	791.2	828.5	870.5
25°	536.5	549.8	567.3	588.3	627.2	662.6	696.5	725.6	759.9	797.2	843.9
27.5°	502.8	514.3	530.3	552.2	578.3	617.4	658.4	691.7	726.8	766.9	813.6
30°	482.8	492.2	505.4	527.6	552.5	587.5	629.1	668.1	703.5	745.1	793.7
32.5°	462.0	472.0	484.9	502.4	529.1	558.6	600.2	642.8	680.4	723.0	770.7
35°	434.2	442.0	453.7	471.6	495.7	521.4	558.3	602.3	642.0	687.5	733.0
37.5°	406.1	415.3	424.5	440.4	460.2	487.8	518.1	563.0	607.0	648.5	693.0
40°	390.2	395.7	405.8	418.7	439.7	464.2	492.6	536.5	580.5	621.8	666.5
42.5°	372.5	378.6	387.1	400.0	418.8	442.7	470.5	508.5	554.4	594.4	635.1
45°	347.8	351.3	359.9	370.8	386.4	410.5	436.2	470.0	513.2	551.3	587.1
47.5°	322.9	326.0	331.3	341.3	358.7	378.1	402.2	432.5	470.4	508.5	538.8
50°	305.8	308.5	313.6	322.9	338.5	357.6	381.3	408.5	442.4	479.0	504.2
52.5°	288.7	290.2	294.9	305.5	318.6	337.3	358.6	383.6	415.3	445.7	471.3
55°	261.5	265.0	268.1	275.9	288.3	306.2	325.3	349.0	373.5	399.2	421.0
57.5°	233.1	236.9	241.4	248.2	258.1	274.8	291.9	311.1	332.0	353.4	371.6
60°	214.4	217.9	221.8	229.6	238.5	251.7	270.4	287.1	303.1	322.5	340.8
62.5°	196.0	199.5	204.0	210.3	218.9	231.5	247.1	261.6	278.2	295.2	308.8
65°	168.9	171.6	175.1	180.9	189.1	200.4	213.2	224.5	239.3	251.7	264.2
67.5°	139.1	144.3	148.9	153.6	160.5	171.0	180.3	191.1	201.2	210.4	221.8
70°	119.4	125.3	129.6	134.6	141.2	150.2	159.1	166.5	174.7	183.6	193.8
72.5°	103.0	107.5	110.9	116.3	122.2	130.6	138.9	145.0	151.7	157.8	167.6
75°	81.3	83.3	85.6	89.9	95.3	101.6	108.2	113.6	117.5	122.9	130.0
77.5°	58.4	62.2	63.7	66.8	70.7	74.5	78.9	83.5	87.2	89.2	94.5
80°	44.7	46.3	47.9	52.1	54.5	58.4	61.5	65.8	67.3	69.3	74.3
82.5°	34.8	35.7	36.7	37.8	39.2	43.1	46.2	48.9	50.5	51.2	55.0
85°	20.2	20.6	21.0	21.4	21.8	21.8	23.3	25.3	28.0	28.0	29.2
87.5°	10.3	10.4	10.2	9.6	9.9	9.7	9.7	9.3	9.9	10.5	11.0
90°	17.3	16.3	15.0	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2
92.5°	30.0	29.4	28.5	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9
95°	56.9	56.4	55.3	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5
97.5°	89.8	89.2	87.9	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8
100°	113.9	113.6	112.1	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9
102.5°	139.0	138.5	137.1	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2
105°	177.1	176.6	176.0	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9
107.5°	218.5	218.1	218.0	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7
110°	246.8	247.1	247.3	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	276.2	276.2	276.5	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3
115°	321.9	322.1	322.4	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6
117.5°	366.2	366.8	367.0	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2
120°	396.2	397.1	397.6	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3
122.5°	426.2	426.8	427.0	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6
125°	470.2	470.5	470.7	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3
127.5°	512.5	512.9	513.1	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8
130°	542.2	542.5	542.5	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3
132.5°	570.1	570.4	570.6	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4
135°	612.0	612.3	612.3	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9
137.5°	652.5	653.0	652.7	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6
142.5°	704.0	704.0	704.2	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1
145°	742.0	742.2	742.0	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5
147.5°	776.3	776.5	776.6	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5
150°	797.9	797.9	797.9	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9
152.5°	817.8	817.4	817.3	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1
155°	846.0	845.4	845.5	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1
157.5°	871.2	870.7	870.8	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2
160°	886.7	886.2	886.3	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7
162.5°	900.1	899.2	899.4	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9
165°	918.3	917.3	917.7	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1
167.5°	933.8	932.8	932.7	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7
170°	942.1	941.1	940.9	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1
172.5°	948.2	947.0	947.0	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0
175°	954.9	953.7	953.9	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2
177.5°	958.8	957.9	957.9	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	971.6	974.4	977.5	983.4	988.4	990.6	995.0	998.1	997.1	1001.5	1009.0
5°	975.4	985.9	998.0	1010.4	1024.4	1036.1	1045.5	1054.8	1062.2	1071.1	1084.4
7.5°	974.8	993.5	1013.8	1036.1	1059.1	1078.9	1097.3	1116.0	1132.5	1150.7	1174.4
10°	972.3	997.2	1022.5	1051.7	1080.9	1108.5	1133.4	1156.7	1178.9	1202.6	1232.6
12.5°	969.5	998.1	1028.7	1063.8	1100.2	1133.4	1162.7	1196.3	1224.0	1254.6	1289.3
15°	957.1	995.7	1037.3	1082.8	1126.4	1171.1	1211.2	1252.5	1291.0	1327.5	1371.1
17.5°	943.0	987.4	1036.5	1090.3	1142.7	1197.0	1244.6	1296.6	1335.9	1385.0	1425.5
20°	931.5	979.3	1031.8	1092.1	1151.7	1212.0	1264.5	1317.4	1361.8	1411.2	1462.6
22.5°	917.5	970.0	1026.9	1089.3	1151.7	1217.6	1275.7	1328.3	1383.3	1438.9	1491.8
25°	894.9	949.4	1009.7	1078.1	1149.7	1217.0	1279.3	1344.7	1403.8	1464.1	1511.6
27.5°	867.2	924.4	988.0	1058.6	1132.1	1201.0	1274.3	1344.0	1403.5	1461.5	1502.9
30°	845.1	905.4	966.5	1038.1	1114.3	1188.3	1266.8	1336.5	1399.1	1451.3	1474.6
32.5°	822.4	879.6	942.5	1015.0	1093.2	1172.7	1250.7	1321.9	1379.8	1411.1	1411.7
35°	782.8	836.5	901.9	973.1	1053.2	1139.6	1218.6	1288.6	1324.0	1326.8	1288.6
37.5°	739.7	789.0	850.7	922.0	1009.7	1095.7	1176.3	1223.0	1234.9	1195.3	1124.8
40°	708.9	754.4	814.0	887.1	974.3	1063.0	1136.5	1170.7	1158.3	1094.1	1015.5
42.5°	676.5	718.9	776.3	848.5	936.0	1025.6	1088.3	1106.6	1073.6	999.5	907.5
45°	623.7	662.6	719.4	792.2	876.2	960.3	1007.7	998.4	943.5	855.6	752.5
47.5°	568.7	606.3	657.4	724.7	810.8	883.3	915.4	887.3	809.2	712.5	628.6
50°	532.3	570.8	617.9	682.1	760.7	830.7	851.3	808.5	721.7	628.8	551.7
52.5°	496.5	529.4	575.5	637.5	712.7	771.9	782.8	733.5	643.9	560.6	492.3
55°	442.0	472.0	510.9	569.2	634.2	684.4	678.6	615.1	533.8	462.6	408.9
57.5°	389.3	411.9	447.8	502.5	559.6	593.3	571.9	517.9	442.1	383.8	338.5
60°	354.5	375.5	408.9	456.8	507.0	526.0	508.1	449.4	389.5	336.2	298.0
62.5°	321.5	340.0	368.8	413.2	453.7	465.0	445.9	394.6	340.6	295.1	263.5
65°	273.5	290.6	315.2	346.7	374.7	380.1	367.7	315.2	274.3	236.2	214.4
67.5°	230.0	241.2	260.4	287.6	302.5	305.7	281.6	248.6	212.6	189.2	172.8
70°	200.8	208.5	226.4	241.2	253.3	253.7	231.5	205.0	177.4	158.4	146.3
72.5°	172.4	179.9	193.5	203.6	212.8	209.8	189.5	168.6	146.3	131.9	122.9
75°	133.1	139.7	146.7	151.4	151.4	147.5	132.7	117.1	104.3	95.7	93.0
77.5°	96.7	102.2	104.5	103.8	102.4	96.3	87.0	76.8	72.2	68.2	66.1
80°	75.9	78.2	79.0	77.0	74.7	67.7	61.5	57.2	52.9	51.4	50.6
82.5°	56.3	58.3	56.3	56.8	51.7	45.9	42.5	41.0	39.2	38.6	37.8
85°	30.0	29.6	28.8	26.8	23.3	22.6	22.2	21.8	21.0	21.4	20.6
87.5°	11.1	10.5	9.6	9.7	10.0	9.6	10.2	10.5	10.7	10.6	11.4
90°	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3
92.5°	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6
95°	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4
97.5°	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4
100°	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2
102.5°	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4
105°	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6
107.5°	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0
110°	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5





TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1
115°	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8
117.5°	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7
120°	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4
122.5°	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6
125°	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9
127.5°	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2
130°	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9
132.5°	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8
135°	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6
137.5°	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1
140°	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8
142.5°	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0
145°	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9
147.5°	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2
150°	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2
155°	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7
157.5°	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7
160°	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2
162.5°	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0
165°	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3
167.5°	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8
170°	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1
172.5°	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3
175°	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0
177.5°	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1013.0	1014.3	1015.2	1018.3	1018.6	1021.4	1018.6
5°	1096.8	1102.3	1110.8	1119.4	1120.2	1125.6	1115.9
7.5°	1190.8	1203.4	1211.3	1225.1	1230.6	1234.0	1228.4
10°	1255.6	1267.2	1287.9	1298.0	1308.1	1309.6	1305.0
12.5°	1318.1	1336.6	1352.9	1372.1	1371.6	1385.3	1380.3
15°	1401.5	1420.5	1443.1	1464.5	1472.3	1472.3	1478.5
17.5°	1460.9	1495.9	1519.2	1536.0	1554.4	1557.6	1555.4
20°	1501.1	1538.8	1563.7	1585.5	1598.0	1601.5	1601.5
22.5°	1531.0	1563.1	1587.4	1607.0	1617.3	1621.4	1620.1
25°	1551.7	1579.3	1594.1	1599.9	1602.6	1601.8	1594.5
27.5°	1523.3	1522.1	1512.7	1494.8	1481.4	1473.2	1463.9
30°	1469.2	1448.9	1425.6	1399.9	1366.8	1341.5	1333.8
32.5°	1388.6	1343.1	1303.6	1260.8	1225.2	1199.9	1189.3
35°	1232.6	1160.6	1101.9	1050.5	1013.2	989.8	982.0
37.5°	1047.6	977.9	905.2	855.4	824.4	800.8	792.0
40°	929.9	854.0	790.6	743.9	712.0	689.1	688.7
42.5°	822.5	750.1	690.4	656.8	622.4	607.2	607.1
45°	673.5	615.5	564.9	538.5	517.9	505.4	501.9
47.5°	557.6	509.7	476.0	454.9	438.1	430.2	425.0
50°	492.6	450.6	423.7	405.4	396.1	386.0	385.2
52.5°	438.4	404.5	383.6	368.7	356.9	350.8	351.0
55°	368.5	341.6	326.8	315.5	306.2	301.5	299.6
57.5°	310.4	290.3	279.5	269.2	265.2	261.5	260.5
60°	274.3	260.7	250.6	242.4	236.6	235.4	235.0
62.5°	244.4	230.2	223.2	216.9	212.6	210.8	210.1
65°	201.5	191.0	184.8	179.8	178.2	175.5	175.1
67.5°	162.5	156.2	152.1	148.6	146.4	146.3	146.3
70°	138.5	135.0	131.5	129.6	128.4	127.6	127.6
72.5°	118.0	115.4	112.5	111.5	111.3	110.5	110.2
75°	89.9	87.2	87.5	85.6	84.0	82.1	80.9
77.5°	63.7	61.8	61.4	61.2	59.8	59.6	60.2
80°	49.4	47.5	47.1	47.5	47.1	45.9	45.9
82.5°	37.6	36.0	35.6	35.3	34.9	35.3	34.7
85°	20.2	19.5	19.5	19.5	20.2	19.8	19.5
87.5°	11.0	10.9	11.3	11.1	11.2	10.9	11.3
90°	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.2	245.8	245.9	246.4	246.9	247.4	247.9



TEST NUMBER: P333040

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)