

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332839-935

Luminaire Tested: **S124DIW-S1195D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332839-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D470U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6018.4 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	77	77	77	73		
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	65	65	65	65	65	65	62		
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	55	55	55	55	55	55	52		
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	47	47	47	47	44		
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	40	40	40	40	40	40	37		
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	35	35	35	35	35	35	33		
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	31	31	31	31	31	31	29		
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	28	28	28	25		
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	25	25	25	25	25	25	23		
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	22	22	22	22	20		
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	20	20	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.7
10°-20°	455.3	7.6
20°-30°	670.1	11.1
30°-40°	779.0	12.9
40°-50°	779.1	12.9
50°-60°	681.5	11.3
60°-70°	506.1	8.4
70°-80°	287.5	4.8
80°-90°	84.5	1.4
90°-100°	17.8	0.3
100°-110°	113.8	1.9
110°-120°	217.6	3.6
120°-130°	276.3	4.6
130°-140°	295.6	4.9
140°-150°	276.4	4.6
150°-160°	222.9	3.7
160°-170°	143.8	2.4
170°-180°	49.6	0.8
0°-30°	1287.0	21.4
0°-40°	2066.0	34.3
0°-60°	3526.5	58.6
0°-90°	4404.6	73.2
90°-120°	349.2	5.8
90°-150°	1197.5	19.9
90°-180°	1614.0	26.8
0°-180°	6018.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	1	5	9	11	12	5
95°	21	9	9	11	11	28
105°	117	120	122	124	111	123
115°	219	220	220	221	221	216
125°	308	310	309	310	311	275
135°	382	382	384	384	385	295
145°	441	442	442	443	443	275
155°	484	484	483	484	483	223
165°	510	508	508	511	508	144
175°	522	520	520	523	519	50
180°	522	522	522	522	522	



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	28.8	28.8	28.8	28.7	28.6	28.5	28.4	28.3	28.2	28.2	28.2
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	4.9	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8
95°	21.4	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1
97.5°	45.5	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3
100°	64.0	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7
102.5°	84.6	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8
105°	117.4	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5
107.5°	148.0	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1
110°	168.6	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.6	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7
115°	219.3	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2
117.5°	247.0	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3
120°	265.7	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1
122.5°	283.2	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8
125°	308.2	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3
127.5°	332.0	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2
130°	347.2	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0
132.5°	361.4	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6
135°	382.4	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7
137.5°	401.1	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1
140°	413.2	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1
142.5°	424.1	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2
145°	440.9	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2
147.5°	454.3	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2
150°	464.0	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1
152.5°	472.1	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8
155°	483.5	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0
157.5°	493.1	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0
160°	498.7	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7
162.5°	503.7	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3
165°	510.0	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8
167.5°	515.0	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5
170°	517.8	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5
172.5°	519.7	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4
175°	521.7	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6
177.5°	522.6	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	28.3	28.4	28.5	28.6	28.7	28.7	28.7	28.8
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.3	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	9.6	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	14.2	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	50.9	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	123.3	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.6	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.5	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P332839-935

CATALOG NUMBER: S124DIW-S1195D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.7	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.4	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	284.9	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.5	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.1	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.0	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.7	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	383.9	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.3	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.3	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.4	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.3	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	472.9	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.4	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	502.8	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	509.5	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	514.3	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.2	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.1	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	521.3	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.2	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)