

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769-935

Luminaire Tested: **S124DIW-S575D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332769-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7606.2 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6529	6529	6529	6529
5°	7688	6545	5777	6545
10°	9205	6517	5201	6517
15°	10891	6450	4776	6450
20°	12128	6383	4398	6383
25°	12324	6284	4136	6284
30°	10486	6190	4053	6190
35°	8062	6034	4054	6034
40°	6284	5853	4130	5853
45°	5239	5581	4199	5581
50°	4611	5247	4342	5247
55°	4224	4847	4517	4847
60°	3959	4489	4728	4489
65°	3687	4088	4902	4088
70°	3368	3692	5013	3692
75°	3010	3250	4953	3250
80°	2520	2664	4793	2664
85°	1862	1927	4594	1927



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.8	1.0
10°-20°	242.8	3.2
20°-30°	385.1	5.1
30°-40°	428.5	5.6
40°-50°	390.1	5.1
50°-60°	318.8	4.2
60°-70°	227.6	3.0
70°-80°	125.3	1.6
80°-90°	39.2	0.5
90°-100°	59.4	0.8
100°-110°	378.6	5.0
110°-120°	724.2	9.5
120°-130°	919.3	12.1
130°-140°	983.6	12.9
140°-150°	919.8	12.1
150°-160°	741.8	9.8
160°-170°	478.4	6.3
170°-180°	164.9	2.2
0°-30°	706.7	9.3
0°-40°	1135.2	14.9
0°-60°	1844.1	24.2
0°-90°	2236.2	29.4
90°-120°	1162.1	15.3
90°-150°	3984.9	52.4
90°-180°	5370.0	70.6
0°-180°	7606.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	809	809	809	809	809	
5°	949	808	713	808	949	96
15°	1303	772	572	772	1303	368
25°	1384	706	464	706	1384	610
35°	818	612	411	612	818	519
45°	459	489	368	489	459	362
55°	300	344	321	344	300	271
65°	193	214	257	214	193	191
75°	96	104	159	104	96	103
85°	20	21	50	21	20	26
90°	39	4	39	4	39	17
95°	38	71	38	71	38	30
105°	370	391	370	391	370	323
115°	735	730	735	730	735	727
125°	1034	1026	1034	1026	1034	920
135°	1282	1272	1282	1272	1282	986
145°	1475	1467	1475	1467	1475	922
155°	1608	1609	1608	1609	1608	741
165°	1689	1697	1689	1697	1689	477
175°	1726	1736	1726	1736	1726	164
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	860.7	860.4	857.7	857.2	855.3	852.9	852.4	848.1	839.5	835.5	834.4
5°	948.7	955.5	946.7	945.0	944.0	933.0	927.3	920.6	905.2	896.1	889.1
7.5°	1053.8	1054.6	1050.8	1047.7	1039.1	1029.5	1015.0	999.6	981.3	962.2	947.8
10°	1122.9	1125.6	1121.3	1120.6	1103.5	1092.8	1071.3	1053.3	1032.4	1009.4	988.3
12.5°	1195.8	1192.1	1189.8	1175.5	1172.3	1152.8	1127.9	1109.2	1077.2	1050.6	1022.5
15°	1303.1	1295.8	1291.1	1271.4	1261.6	1234.5	1208.0	1187.6	1145.7	1105.9	1075.6
17.5°	1366.1	1373.5	1362.6	1354.5	1329.4	1310.4	1283.3	1240.4	1207.6	1158.1	1120.1
20°	1411.7	1412.4	1406.4	1397.9	1378.2	1354.1	1324.6	1277.7	1238.5	1189.2	1137.0
22.5°	1424.0	1424.2	1421.6	1413.8	1398.8	1379.2	1349.5	1310.4	1262.9	1209.4	1157.1
25°	1383.5	1382.2	1385.3	1394.0	1388.3	1382.2	1365.1	1336.0	1291.8	1235.1	1178.9
27.5°	1233.2	1242.4	1259.5	1280.9	1301.6	1317.2	1321.7	1315.8	1288.3	1241.7	1182.8
30°	1124.9	1136.3	1149.0	1170.5	1212.0	1235.8	1262.0	1281.7	1270.7	1233.5	1178.5
32.5°	1005.9	1008.7	1027.6	1052.1	1090.1	1135.8	1177.2	1217.4	1230.7	1211.3	1165.4
35°	818.0	822.8	843.2	867.3	913.9	969.8	1032.2	1087.7	1133.7	1152.1	1128.6
37.5°	667.6	681.1	695.4	721.3	762.4	812.8	877.5	949.4	1017.9	1063.7	1071.4
40°	596.3	604.7	615.1	634.8	669.7	719.3	774.8	857.3	930.0	995.7	1017.1
42.5°	540.0	544.9	551.3	569.1	595.7	645.0	695.8	768.3	841.3	919.8	955.7
45°	458.9	464.0	474.7	485.1	505.1	539.3	586.6	646.2	719.5	795.3	861.6
47.5°	400.4	403.6	410.0	421.1	438.2	460.7	499.1	548.9	616.9	690.4	761.1
50°	367.1	369.8	374.9	385.0	398.0	418.1	449.5	496.1	549.4	623.5	692.8
52.5°	340.9	342.0	345.7	352.5	362.9	379.8	405.6	444.1	493.7	559.6	628.7
55°	300.1	301.5	304.9	309.9	318.9	329.7	349.4	378.2	421.5	478.7	538.6
57.5°	266.7	267.6	270.4	272.3	279.8	288.5	303.7	324.3	357.1	405.6	459.2
60°	245.2	244.5	247.9	249.6	254.6	262.0	273.7	293.4	321.9	361.1	410.4
62.5°	224.3	223.3	226.2	228.4	231.3	237.5	247.2	262.6	285.8	321.2	363.8
65°	193.0	191.7	193.3	196.0	198.6	202.0	209.1	222.7	241.2	266.7	299.1
67.5°	161.4	162.9	163.2	164.5	166.0	170.6	175.4	185.1	198.1	218.5	246.0
70°	142.7	143.0	144.4	144.4	145.4	149.4	153.4	159.1	171.9	190.6	213.1
72.5°	124.0	125.4	124.8	125.9	126.7	129.3	132.2	137.7	148.5	162.5	181.4
75°	96.5	97.5	97.5	97.8	98.8	99.8	102.2	106.2	113.9	124.2	137.3
77.5°	70.3	70.5	70.9	72.2	72.2	73.8	75.5	78.7	82.6	89.6	97.6
80°	54.2	54.9	54.6	55.3	55.3	56.7	57.3	61.3	62.9	67.7	74.0
82.5°	39.8	40.5	40.4	41.3	41.8	42.1	43.0	44.7	46.3	50.5	53.1
85°	20.1	20.8	20.1	20.8	21.8	22.1	23.1	23.4	24.8	25.8	28.2
87.5°	13.7	14.4	14.3	14.4	14.8	14.9	14.8	14.2	14.9	14.8	15.4
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0	29.3	27.6	25.2
95°	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0	30.3	28.6	28.2
97.5°	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6	34.4	34.3	66.5
100°	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4	52.3	57.2	96.9
102.5°	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4	222.3	275.3	280.4
105°	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3	407.7	405.1	403.6
107.5°	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6	506.4	505.1	503.1
110°	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8	573.2	572.6	570.8



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8	637.9	638.1	637.2
115°	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5	732.9	732.3	732.6
117.5°	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7	829.8	829.9	829.3
120°	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1	888.4
122.5°	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0	947.7	947.4	946.9
125°	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1	1029.2	1028.4	1028.9
127.5°	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6	1111.8	1112.0	1110.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4	1161.1	1160.8	1159.9
132.5°	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2	1209.9	1209.6	1208.5
135°	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5	1276.9	1276.3	1275.2
137.5°	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0	1341.4	1340.7	1339.5
140°	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0	1381.1	1380.2	1379.7
142.5°	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9	1418.2	1417.6	1417.3
145°	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7	1471.4	1471.1	1471.1
147.5°	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0	1517.9	1517.6	1517.9
150°	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7	1547.7	1547.7	1548.0
152.5°	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6	1573.1	1572.6	1573.1
155°	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4	1607.3	1606.1	1607.1
157.5°	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5	1636.5
160°	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2	1654.5
162.5°	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3	1671.5	1669.7	1670.1
165°	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1	1692.8	1690.6	1690.6
167.5°	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2	1708.7	1706.2	1706.3
170°	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1	1718.8	1716.5	1716.2
172.5°	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3	1725.0	1722.8	1722.4
175°	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7	1732.1	1729.5	1729.2
177.5°	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6	1735.8	1733.9	1733.5
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	834.7	831.0	828.3	826.1	820.2	816.7	814.1	810.3	806.0	801.4	795.8
5°	882.1	870.6	862.3	849.5	837.5	827.4	817.1	807.7	796.3	783.9	774.8
7.5°	931.9	914.9	893.2	874.3	853.2	834.7	818.3	801.4	783.9	766.8	751.2
10°	963.5	941.7	917.6	889.1	862.3	838.5	816.4	795.0	774.2	753.4	735.6
12.5°	997.5	970.3	934.7	901.4	871.4	839.6	812.9	786.6	761.6	739.8	719.0
15°	1043.2	1004.0	962.8	918.3	878.7	841.5	805.0	771.8	743.7	714.9	694.8
17.5°	1071.3	1022.8	975.7	929.1	881.2	834.3	795.0	756.7	721.4	692.8	667.5
20°	1089.8	1041.6	982.9	936.3	879.3	831.1	785.6	743.0	706.2	675.7	649.5
22.5°	1105.9	1050.1	991.4	930.1	873.5	822.3	772.4	729.6	692.0	659.9	634.8
25°	1114.6	1050.6	986.9	925.9	861.6	801.0	755.8	705.5	665.3	631.5	604.7
27.5°	1115.5	1047.1	975.1	907.3	840.9	784.5	727.4	682.4	640.8	604.9	579.2
30°	1112.5	1041.2	963.8	890.4	823.8	762.4	712.9	664.0	621.4	585.9	559.1
32.5°	1103.1	1028.8	949.3	871.7	802.6	742.6	691.5	645.0	603.5	568.5	540.4
35°	1076.0	1002.6	917.9	837.2	766.5	705.8	659.6	612.3	570.8	537.7	510.6
37.5°	1033.6	967.2	881.1	797.5	728.1	667.3	621.4	578.8	541.3	507.6	479.7
40°	996.6	938.3	851.9	770.5	695.4	637.5	594.6	555.4	518.2	486.4	459.9
42.5°	954.0	903.2	823.5	737.3	664.9	606.7	564.9	529.7	494.6	465.3	438.8
45°	878.0	844.6	769.5	689.7	614.4	559.5	519.6	488.8	459.3	430.5	408.4
47.5°	790.7	774.0	710.8	635.2	563.6	509.5	474.9	446.4	420.6	396.1	376.7
50°	731.9	723.9	669.3	596.3	528.0	477.1	442.2	417.8	395.6	374.2	355.8
52.5°	674.1	673.8	624.6	557.7	494.5	445.4	410.9	388.0	368.9	351.4	334.8
55°	585.6	595.0	556.5	496.8	440.2	396.0	364.8	344.4	331.0	316.6	304.2
57.5°	504.3	519.9	488.1	435.6	388.3	347.6	320.5	305.1	290.8	282.1	273.1
60°	451.3	466.0	441.2	397.0	352.4	317.5	291.8	278.0	265.6	259.6	253.2
62.5°	404.1	417.2	398.8	357.8	319.2	285.7	263.9	250.7	242.4	235.7	231.5
65°	336.7	347.8	332.0	302.2	269.0	242.2	224.5	214.0	206.0	203.4	198.6
67.5°	272.2	282.2	273.7	248.4	221.8	201.5	187.6	177.6	172.9	170.5	167.2
70°	233.8	243.9	234.8	212.8	192.3	175.2	162.1	156.4	151.4	150.4	145.8
72.5°	201.4	208.3	199.1	181.9	164.5	150.0	139.9	134.0	131.3	129.5	127.0
75°	151.1	157.1	151.1	137.7	125.3	115.2	106.5	104.2	101.2	100.1	98.5
77.5°	106.9	112.2	107.5	99.2	89.9	82.1	77.5	74.5	73.8	72.1	72.8
80°	81.7	85.1	80.8	75.1	67.7	62.3	59.0	57.3	55.3	54.6	56.0
82.5°	58.7	60.2	57.9	54.2	48.6	45.1	42.9	40.9	40.6	40.6	40.6
85°	30.5	30.1	29.8	26.4	24.8	22.5	21.1	20.8	20.4	21.1	21.8
87.5°	15.0	14.8	14.0	12.4	11.0	9.6	8.6	7.7	8.6	9.6	10.4
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4	61.6	51.8	42.0
97.5°	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6	157.7	163.8	170.0
100°	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9	218.2	223.3	228.5
102.5°	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5	285.3	289.1	292.9
105°	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8	392.5	394.3	396.1
107.5°	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3	493.3	494.1	495.0
110°	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9	561.8	562.7	563.5



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4	629.0	630.5	632.1
115°	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7	730.6	731.4	732.3
117.5°	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9	823.0	824.2	825.4
120°	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2	885.4	886.6	887.7
122.5°	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4	943.1	943.7	944.4
125°	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8	1026.9	1028.0	1029.2
127.5°	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7	1105.0	1105.3	1105.5
130°	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6	1155.9	1156.2	1156.5
132.5°	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3	1202.8	1203.4	1203.9
135°	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5	1272.1	1271.9	1271.6
137.5°	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6	1334.6	1334.7	1334.9
140°	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4	1412.4	1413.5	1414.5
145°	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2	1468.1	1469.0	1469.8
147.5°	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7	1513.2	1514.8	1516.5
150°	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9	1545.0	1546.1	1547.3
152.5°	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8	1571.8	1572.7	1573.6
155°	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8	1609.0	1609.3	1609.6
157.5°	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7	1640.5	1640.4	1640.2
160°	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4	1658.5	1657.7	1656.8
162.5°	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0	1674.9	1673.8	1672.8
165°	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0	1695.6	1694.2	1692.7
167.5°	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6	1712.2	1710.6	1709.2
170°	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0	1721.3	1719.5	1717.8
172.5°	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2	1727.5	1725.8	1724.1
175°	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9	1734.2	1732.5	1730.8
177.5°	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1	1737.5	1735.9	1734.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	793.2	790.7	787.2	782.4	778.4	774.1	773.0	771.5	774.6	772.0	771.2
5°	767.2	760.1	751.1	740.7	734.7	725.9	724.3	720.9	717.6	717.2	713.9
7.5°	739.6	729.3	717.5	706.9	697.1	687.6	681.3	680.0	675.0	672.2	668.8
10°	721.9	709.2	695.4	685.4	674.0	664.0	656.9	652.9	649.5	645.8	642.6
12.5°	701.0	687.5	676.1	665.3	651.8	644.1	632.6	625.6	624.9	625.0	616.3
15°	676.7	663.3	645.8	630.5	623.1	608.4	602.0	593.9	588.9	583.9	579.9
17.5°	648.9	632.2	618.6	600.9	586.9	575.1	566.7	561.9	554.4	547.3	542.1
20°	631.5	613.7	599.3	580.6	565.2	550.8	543.7	537.0	531.3	525.3	519.6
22.5°	613.8	595.2	577.6	559.4	545.0	529.9	523.1	513.9	508.5	505.1	499.5
25°	585.9	565.8	545.7	528.3	513.6	500.2	491.1	484.1	478.0	475.4	471.7
27.5°	555.6	535.6	516.3	496.5	479.7	470.0	462.8	457.4	454.0	450.5	448.8
30°	536.3	515.6	494.8	476.4	461.0	451.3	444.5	440.8	438.2	436.5	434.8
32.5°	516.8	496.3	474.4	457.6	443.8	435.1	430.1	426.4	425.1	424.5	423.9
35°	485.4	464.7	444.5	429.5	416.4	413.0	408.7	406.7	406.0	408.4	409.4
37.5°	455.0	435.8	417.2	402.7	394.1	389.2	387.7	387.8	390.2	392.3	394.7
40°	435.5	416.7	399.3	386.6	378.6	375.6	374.9	376.5	379.2	381.6	384.3
42.5°	416.5	398.0	382.2	370.2	364.6	361.9	362.3	363.9	367.7	370.6	374.6
45°	386.9	371.5	356.1	346.4	341.7	342.3	342.3	345.3	349.0	353.4	357.7
47.5°	359.1	343.5	330.9	322.7	320.3	319.7	321.6	325.5	330.9	336.2	342.3
50°	340.4	325.6	314.5	307.2	304.5	305.5	308.2	311.9	318.2	324.9	331.3
52.5°	321.3	307.9	297.6	290.8	289.0	290.8	293.4	299.3	304.9	312.1	319.8
55°	291.8	280.4	272.3	267.3	266.7	267.7	270.7	277.1	285.1	294.1	301.5
57.5°	262.3	252.9	245.5	242.0	242.4	243.3	248.2	255.8	264.4	274.1	283.5
60°	242.5	233.8	227.8	225.2	225.5	227.5	233.5	240.6	251.2	260.6	270.7
62.5°	223.8	216.1	210.3	207.9	207.5	211.9	217.7	225.0	235.7	246.2	257.0
65°	193.6	187.6	182.9	181.6	182.5	185.9	193.3	203.0	212.1	223.1	234.5
67.5°	164.1	159.2	156.0	156.6	157.8	162.7	168.9	177.3	187.5	199.0	210.3
70°	145.4	140.7	138.0	138.4	140.3	146.4	151.8	160.1	171.2	182.9	192.3
72.5°	126.1	123.0	120.6	122.0	124.0	128.2	134.8	143.3	153.0	163.8	173.8
75°	96.8	96.8	95.5	96.5	99.5	103.5	108.6	117.3	127.0	135.7	143.7
77.5°	71.8	71.1	72.0	73.2	74.9	79.6	85.4	91.7	98.9	107.7	114.3
80°	54.9	55.3	56.9	59.0	59.7	63.3	69.3	75.1	80.8	88.1	94.5
82.5°	41.2	41.6	42.4	45.0	45.7	49.7	53.6	59.2	64.4	69.3	74.6
85°	22.5	22.5	24.1	25.1	26.8	29.4	31.9	35.2	39.9	43.2	48.2
87.5°	11.9	12.5	13.9	15.0	16.3	18.1	18.9	22.2	23.7	25.3	28.0
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0	32.7	34.4	35.4
95°	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0	33.8	35.5	36.5
97.5°	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6	34.8	35.0	35.2
100°	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4	42.4	37.5	35.2
102.5°	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4	116.5	63.6	37.2
105°	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3	412.9	415.5	411.6
107.5°	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6	508.9	510.1	511.3
110°	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8	574.4	574.9	575.7



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8	637.7	637.6	638.1
115°	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5	734.0	734.6	734.9
117.5°	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7	829.6	829.5	829.4
120°	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2	889.8	890.4	890.4
122.5°	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0	948.4	948.7	948.6
125°	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1	1031.0	1031.8	1032.4
127.5°	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6	1111.5	1111.3	1111.0
130°	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4	1161.7	1161.9	1162.1
132.5°	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2	1210.5	1210.7	1210.8
135°	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5	1278.1	1278.7	1279.3
137.5°	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0	1342.6	1343.3	1343.5
140°	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0	1382.9	1383.7	1384.2
142.5°	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9	1419.5	1420.1	1420.5
145°	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7	1472.0	1472.2	1472.7
147.5°	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0	1518.3	1518.5	1518.8
150°	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7	1547.7	1547.7	1547.9
152.5°	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6	1574.0	1574.5	1574.6
155°	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4	1609.6	1610.8	1610.9
157.5°	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5
160°	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1
162.5°	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3	1675.0	1676.7	1676.5
165°	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1	1697.5	1699.8	1699.6
167.5°	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2	1713.7	1716.3	1716.1
170°	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1	1723.5	1725.8	1725.4
172.5°	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3	1729.7	1732.0	1731.6
175°	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7	1737.3	1739.9	1739.5
177.5°	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6	1739.5	1741.3	1740.9
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	770.6	770.1	768.2	767.9	768.2	770.1	770.6	771.2	772.0	774.6	771.5
5°	711.9	710.2	709.2	712.9	709.2	710.2	711.9	713.9	717.2	717.6	720.9
7.5°	667.6	666.2	663.3	662.4	663.3	666.2	667.6	668.8	672.2	675.0	680.0
10°	639.2	637.8	635.2	634.5	635.2	637.8	639.2	642.6	645.8	649.5	652.9
12.5°	611.8	609.2	608.6	609.3	608.6	609.2	611.8	616.3	625.0	624.9	625.6
15°	575.5	574.2	570.5	571.5	570.5	574.2	575.5	579.9	583.9	588.9	593.9
17.5°	539.8	538.1	533.6	537.6	533.6	538.1	539.8	542.1	547.3	554.4	561.9
20°	517.2	514.5	512.2	511.9	512.2	514.5	517.2	519.6	525.3	531.3	537.0
22.5°	495.8	493.4	493.2	490.9	493.2	493.4	495.8	499.5	505.1	508.5	513.9
25°	469.0	466.7	466.0	464.3	466.0	466.7	469.0	471.7	475.4	478.0	484.1
27.5°	448.4	447.3	446.1	446.6	446.1	447.3	448.4	448.8	450.5	454.0	457.4
30°	435.8	435.5	434.8	434.8	434.8	435.5	435.8	434.8	436.5	438.2	440.8
32.5°	425.4	425.3	425.7	425.7	425.7	425.3	425.4	423.9	424.5	425.1	426.4
35°	410.7	411.7	412.4	411.4	412.4	411.7	410.7	409.4	408.4	406.0	406.7
37.5°	397.4	398.5	399.4	400.5	399.4	398.5	397.4	394.7	392.3	390.2	387.8
40°	387.3	389.6	390.3	391.9	390.3	389.6	387.3	384.3	381.6	379.2	376.5
42.5°	377.6	380.2	381.9	382.3	381.9	380.2	377.6	374.6	370.6	367.7	363.9
45°	362.8	365.5	367.8	367.8	367.8	365.5	362.8	357.7	353.4	349.0	345.3
47.5°	347.5	351.4	353.7	354.3	353.7	351.4	347.5	342.3	336.2	330.9	325.5
50°	337.0	341.7	344.1	345.7	344.1	341.7	337.0	331.3	324.9	318.2	311.9
52.5°	326.8	331.5	334.7	335.5	334.7	331.5	326.8	319.8	312.1	304.9	299.3
55°	309.2	315.9	319.6	320.9	319.6	315.9	309.2	301.5	294.1	285.1	277.1
57.5°	292.6	298.8	303.1	304.0	303.1	298.8	292.6	283.5	274.1	264.4	255.8
60°	279.7	286.5	291.8	292.8	291.8	286.5	279.7	270.7	260.6	251.2	240.6
62.5°	266.6	273.5	278.4	281.0	278.4	273.5	266.6	257.0	246.2	235.7	225.0
65°	243.9	250.9	255.6	256.6	255.6	250.9	243.9	234.5	223.1	212.1	203.0
67.5°	219.1	226.1	229.2	231.2	229.2	226.1	219.1	210.3	199.0	187.5	177.3
70°	201.6	207.3	210.7	212.4	210.7	207.3	201.6	192.3	182.9	171.2	160.1
72.5°	181.8	187.8	191.7	192.0	191.7	187.8	181.8	173.8	163.8	153.0	143.3
75°	151.4	156.8	158.8	158.8	158.8	156.8	151.4	143.7	135.7	127.0	117.3
77.5°	119.9	122.6	125.2	125.7	125.2	122.6	119.9	114.3	107.7	98.9	91.7
80°	99.5	101.2	103.1	103.1	103.1	101.2	99.5	94.5	88.1	80.8	75.1
82.5°	78.6	80.0	82.0	81.7	82.0	80.0	78.6	74.6	69.3	64.4	59.2
85°	47.5	50.6	50.3	49.6	50.3	50.6	47.5	48.2	43.2	39.9	35.2
87.5°	28.8	29.3	30.2	30.8	30.2	29.3	28.8	28.0	25.3	23.7	22.2
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0
95°	36.8	37.1	37.4	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0
97.5°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6
100°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4
102.5°	37.2	37.3	37.4	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4
105°	401.2	390.8	380.5	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3
107.5°	512.5	513.5	514.6	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6
110°	576.5	577.4	578.2	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	639.2	640.2	641.4	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8
115°	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5
117.5°	829.2	829.1	829.1	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7
120°	889.8	889.2	888.7	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2
122.5°	948.0	947.4	946.8	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0
125°	1032.7	1032.9	1033.3	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1
127.5°	1110.9	1110.6	1110.3	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4
132.5°	1210.6	1210.3	1210.1	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2
135°	1279.8	1280.4	1281.0	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5
137.5°	1343.3	1343.2	1343.0	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0
140°	1384.6	1384.8	1385.1	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0
142.5°	1420.6	1420.6	1420.6	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9
145°	1473.3	1473.9	1474.5	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7
147.5°	1519.1	1519.3	1519.7	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0
150°	1548.2	1548.4	1548.8	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7
152.5°	1574.4	1574.3	1574.1	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6
155°	1610.1	1609.2	1608.3	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4
157.5°	1640.0	1638.5	1637.0	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5
160°	1659.4	1657.7	1656.0	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7
162.5°	1674.6	1672.7	1670.7	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3
165°	1697.0	1694.4	1691.9	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1
167.5°	1713.2	1710.4	1707.4	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2
170°	1722.6	1719.7	1716.8	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1
172.5°	1728.5	1725.4	1722.3	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3
175°	1735.9	1732.5	1729.1	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7
177.5°	1738.1	1735.3	1732.5	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	773.0	774.1	778.4	782.4	787.2	790.7	793.2	795.8	801.4	806.0	810.3
5°	724.3	725.9	734.7	740.7	751.1	760.1	767.2	774.8	783.9	796.3	807.7
7.5°	681.3	687.6	697.1	706.9	717.5	729.3	739.6	751.2	766.8	783.9	801.4
10°	656.9	664.0	674.0	685.4	695.4	709.2	721.9	735.6	753.4	774.2	795.0
12.5°	632.6	644.1	651.8	665.3	676.1	687.5	701.0	719.0	739.8	761.6	786.6
15°	602.0	608.4	623.1	630.5	645.8	663.3	676.7	694.8	714.9	743.7	771.8
17.5°	566.7	575.1	586.9	600.9	618.6	632.2	648.9	667.5	692.8	721.4	756.7
20°	543.7	550.8	565.2	580.6	599.3	613.7	631.5	649.5	675.7	706.2	743.0
22.5°	523.1	529.9	545.0	559.4	577.6	595.2	613.8	634.8	659.9	692.0	729.6
25°	491.1	500.2	513.6	528.3	545.7	565.8	585.9	604.7	631.5	665.3	705.5
27.5°	462.8	470.0	479.7	496.5	516.3	535.6	555.6	579.2	604.9	640.8	682.4
30°	444.5	451.3	461.0	476.4	494.8	515.6	536.3	559.1	585.9	621.4	664.0
32.5°	430.1	435.1	443.8	457.6	474.4	496.3	516.8	540.4	568.5	603.5	645.0
35°	408.7	413.0	416.4	429.5	444.5	464.7	485.4	510.6	537.7	570.8	612.3
37.5°	387.7	389.2	394.1	402.7	417.2	435.8	455.0	479.7	507.6	541.3	578.8
40°	374.9	375.6	378.6	386.6	399.3	416.7	435.5	459.9	486.4	518.2	555.4
42.5°	362.3	361.9	364.6	370.2	382.2	398.0	416.5	438.8	465.3	494.6	529.7
45°	342.3	342.3	341.7	346.4	356.1	371.5	386.9	408.4	430.5	459.3	488.8
47.5°	321.6	319.7	320.3	322.7	330.9	343.5	359.1	376.7	396.1	420.6	446.4
50°	308.2	305.5	304.5	307.2	314.5	325.6	340.4	355.8	374.2	395.6	417.8
52.5°	293.4	290.8	289.0	290.8	297.6	307.9	321.3	334.8	351.4	368.9	388.0
55°	270.7	267.7	266.7	267.3	272.3	280.4	291.8	304.2	316.6	331.0	344.4
57.5°	248.2	243.3	242.4	242.0	245.5	252.9	262.3	273.1	282.1	290.8	305.1
60°	233.5	227.5	225.5	225.2	227.8	233.8	242.5	253.2	259.6	265.6	278.0
62.5°	217.7	211.9	207.5	207.9	210.3	216.1	223.8	231.5	235.7	242.4	250.7
65°	193.3	185.9	182.5	181.6	182.9	187.6	193.6	198.6	203.4	206.0	214.0
67.5°	168.9	162.7	157.8	156.6	156.0	159.2	164.1	167.2	170.5	172.9	177.6
70°	151.8	146.4	140.3	138.4	138.0	140.7	145.4	145.8	150.4	151.4	156.4
72.5°	134.8	128.2	124.0	122.0	120.6	123.0	126.1	127.0	129.5	131.3	134.0
75°	108.6	103.5	99.5	96.5	95.5	96.8	96.8	98.5	100.1	101.2	104.2
77.5°	85.4	79.6	74.9	73.2	72.0	71.1	71.8	72.8	72.1	73.8	74.5
80°	69.3	63.3	59.7	59.0	56.9	55.3	54.9	56.0	54.6	55.3	57.3
82.5°	53.6	49.7	45.7	45.0	42.4	41.6	41.2	40.6	40.6	40.6	40.9
85°	31.9	29.4	26.8	25.1	24.1	22.5	22.5	21.8	21.1	20.4	20.8
87.5°	18.9	18.1	16.3	15.0	13.9	12.5	11.9	10.4	9.6	8.6	7.7
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	29.3	27.6	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4
95°	30.3	28.6	28.2	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4
97.5°	34.4	34.3	66.5	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6
100°	52.3	57.2	96.9	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9
102.5°	222.3	275.3	280.4	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5
105°	407.7	405.1	403.6	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8
107.5°	506.4	505.1	503.1	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3
110°	573.2	572.6	570.8	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.9	638.1	637.2	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4
115°	732.9	732.3	732.6	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7
117.5°	829.8	829.9	829.3	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9
120°	888.7	888.1	888.4	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2
122.5°	947.7	947.4	946.9	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4
125°	1029.2	1028.4	1028.9	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8
127.5°	1111.8	1112.0	1110.6	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7
130°	1161.1	1160.8	1159.9	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6
132.5°	1209.9	1209.6	1208.5	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3
135°	1276.9	1276.3	1275.2	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5
137.5°	1341.4	1340.7	1339.5	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6
140°	1381.1	1380.2	1379.7	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1418.2	1417.6	1417.3	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4
145°	1471.4	1471.1	1471.1	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2
147.5°	1517.9	1517.6	1517.9	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7
150°	1547.7	1547.7	1548.0	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9
152.5°	1573.1	1572.6	1573.1	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8
155°	1607.3	1606.1	1607.1	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8
157.5°	1637.0	1635.5	1636.5	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7
160°	1656.0	1654.2	1654.5	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4
162.5°	1671.5	1669.7	1670.1	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0
165°	1692.8	1690.6	1690.6	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0
167.5°	1708.7	1706.2	1706.3	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6
170°	1718.8	1716.5	1716.2	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0
172.5°	1725.0	1722.8	1722.4	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2
175°	1732.1	1729.5	1729.2	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9
177.5°	1735.8	1733.9	1733.5	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	814.1	816.7	820.2	826.1	828.3	831.0	834.7	834.4	835.5	839.5	848.1
5°	817.1	827.4	837.5	849.5	862.3	870.6	882.1	889.1	896.1	905.2	920.6
7.5°	818.3	834.7	853.2	874.3	893.2	914.9	931.9	947.8	962.2	981.3	999.6
10°	816.4	838.5	862.3	889.1	917.6	941.7	963.5	988.3	1009.4	1032.4	1053.3
12.5°	812.9	839.6	871.4	901.4	934.7	970.3	997.5	1022.5	1050.6	1077.2	1109.2
15°	805.0	841.5	878.7	918.3	962.8	1004.0	1043.2	1075.6	1105.9	1145.7	1187.6
17.5°	795.0	834.3	881.2	929.1	975.7	1022.8	1071.3	1120.1	1158.1	1207.6	1240.4
20°	785.6	831.1	879.3	936.3	982.9	1041.6	1089.8	1137.0	1189.2	1238.5	1277.7
22.5°	772.4	822.3	873.5	930.1	991.4	1050.1	1105.9	1157.1	1209.4	1262.9	1310.4
25°	755.8	801.0	861.6	925.9	986.9	1050.6	1114.6	1178.9	1235.1	1291.8	1336.0
27.5°	727.4	784.5	840.9	907.3	975.1	1047.1	1115.5	1182.8	1241.7	1288.3	1315.8
30°	712.9	762.4	823.8	890.4	963.8	1041.2	1112.5	1178.5	1233.5	1270.7	1281.7
32.5°	691.5	742.6	802.6	871.7	949.3	1028.8	1103.1	1165.4	1211.3	1230.7	1217.4
35°	659.6	705.8	766.5	837.2	917.9	1002.6	1076.0	1128.6	1152.1	1133.7	1087.7
37.5°	621.4	667.3	728.1	797.5	881.1	967.2	1033.6	1071.4	1063.7	1017.9	949.4
40°	594.6	637.5	695.4	770.5	851.9	938.3	996.6	1017.1	995.7	930.0	857.3
42.5°	564.9	606.7	664.9	737.3	823.5	903.2	954.0	955.7	919.8	841.3	768.3
45°	519.6	559.5	614.4	689.7	769.5	844.6	878.0	861.6	795.3	719.5	646.2
47.5°	474.9	509.5	563.6	635.2	710.8	774.0	790.7	761.1	690.4	616.9	548.9
50°	442.2	477.1	528.0	596.3	669.3	723.9	731.9	692.8	623.5	549.4	496.1
52.5°	410.9	445.4	494.5	557.7	624.6	673.8	674.1	628.7	559.6	493.7	444.1
55°	364.8	396.0	440.2	496.8	556.5	595.0	585.6	538.6	478.7	421.5	378.2
57.5°	320.5	347.6	388.3	435.6	488.1	519.9	504.3	459.2	405.6	357.1	324.3
60°	291.8	317.5	352.4	397.0	441.2	466.0	451.3	410.4	361.1	321.9	293.4
62.5°	263.9	285.7	319.2	357.8	398.8	417.2	404.1	363.8	321.2	285.8	262.6
65°	224.5	242.2	269.0	302.2	332.0	347.8	336.7	299.1	266.7	241.2	222.7
67.5°	187.6	201.5	221.8	248.4	273.7	282.2	272.2	246.0	218.5	198.1	185.1
70°	162.1	175.2	192.3	212.8	234.8	243.9	233.8	213.1	190.6	171.9	159.1
72.5°	139.9	150.0	164.5	181.9	199.1	208.3	201.4	181.4	162.5	148.5	137.7
75°	106.5	115.2	125.3	137.7	151.1	157.1	151.1	137.3	124.2	113.9	106.2
77.5°	77.5	82.1	89.9	99.2	107.5	112.2	106.9	97.6	89.6	82.6	78.7
80°	59.0	62.3	67.7	75.1	80.8	85.1	81.7	74.0	67.7	62.9	61.3
82.5°	42.9	45.1	48.6	54.2	57.9	60.2	58.7	53.1	50.5	46.3	44.7
85°	21.1	22.5	24.8	26.4	29.8	30.1	30.5	28.2	25.8	24.8	23.4
87.5°	8.6	9.6	11.0	12.4	14.0	14.8	15.0	15.4	14.8	14.9	14.2
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0
95°	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0
97.5°	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6
100°	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4
102.5°	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4
105°	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3
107.5°	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6
110°	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8
115°	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5
117.5°	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7
120°	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2
122.5°	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0
125°	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1
127.5°	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6
130°	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4
132.5°	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2
135°	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5
137.5°	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0
140°	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0
142.5°	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9
145°	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7
147.5°	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0
150°	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7
152.5°	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6
155°	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4
157.5°	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5
160°	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7
162.5°	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3
165°	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1
167.5°	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2
170°	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1
172.5°	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3
175°	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7
177.5°	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	808.7	808.7	808.7	808.7	808.7	808.7	808.7
2.5°	852.4	852.9	855.3	857.2	857.7	860.4	860.7
5°	927.3	933.0	944.0	945.0	946.7	955.5	948.7
7.5°	1015.0	1029.5	1039.1	1047.7	1050.8	1054.6	1053.8
10°	1071.3	1092.8	1103.5	1120.6	1121.3	1125.6	1122.9
12.5°	1127.9	1152.8	1172.3	1175.5	1189.8	1192.1	1195.8
15°	1208.0	1234.5	1261.6	1271.4	1291.1	1295.8	1303.1
17.5°	1283.3	1310.4	1329.4	1354.5	1362.6	1373.5	1366.1
20°	1324.6	1354.1	1378.2	1397.9	1406.4	1412.4	1411.7
22.5°	1349.5	1379.2	1398.8	1413.8	1421.6	1424.2	1424.0
25°	1365.1	1382.2	1388.3	1394.0	1385.3	1382.2	1383.5
27.5°	1321.7	1317.2	1301.6	1280.9	1259.5	1242.4	1233.2
30°	1262.0	1235.8	1212.0	1170.5	1149.0	1136.3	1124.9
32.5°	1177.2	1135.8	1090.1	1052.1	1027.6	1008.7	1005.9
35°	1032.2	969.8	913.9	867.3	843.2	822.8	818.0
37.5°	877.5	812.8	762.4	721.3	695.4	681.1	667.6
40°	774.8	719.3	669.7	634.8	615.1	604.7	596.3
42.5°	695.8	645.0	595.7	569.1	551.3	544.9	540.0
45°	586.6	539.3	505.1	485.1	474.7	464.0	458.9
47.5°	499.1	460.7	438.2	421.1	410.0	403.6	400.4
50°	449.5	418.1	398.0	385.0	374.9	369.8	367.1
52.5°	405.6	379.8	362.9	352.5	345.7	342.0	340.9
55°	349.4	329.7	318.9	309.9	304.9	301.5	300.1
57.5°	303.7	288.5	279.8	272.3	270.4	267.6	266.7
60°	273.7	262.0	254.6	249.6	247.9	244.5	245.2
62.5°	247.2	237.5	231.3	228.4	226.2	223.3	224.3
65°	209.1	202.0	198.6	196.0	193.3	191.7	193.0
67.5°	175.4	170.6	166.0	164.5	163.2	162.9	161.4
70°	153.4	149.4	145.4	144.4	144.4	143.0	142.7
72.5°	132.2	129.3	126.7	125.9	124.8	125.4	124.0
75°	102.2	99.8	98.8	97.8	97.5	97.5	96.5
77.5°	75.5	73.8	72.2	72.2	70.9	70.5	70.3
80°	57.3	56.7	55.3	55.3	54.6	54.9	54.2
82.5°	43.0	42.1	41.8	41.3	40.4	40.5	39.8
85°	23.1	22.1	21.8	20.8	20.1	20.8	20.1
87.5°	14.8	14.9	14.8	14.4	14.3	14.4	13.7
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P332769-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)