

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333031-935

Luminaire Tested: **S124RDIW-S350D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333031-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1560U935-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6653.4 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17
2	83	76	70	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	18	17	12
4	69	59	52	46	61	53	46	42	40	36	32	28	26	24	18	16	15	11
5	63	53	45	39	56	47	40	36	36	31	28	25	23	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	0.7
10°-20°	147.8	2.2
20°-30°	231.2	3.5
30°-40°	257.0	3.9
40°-50°	228.0	3.4
50°-60°	177.7	2.7
60°-70°	116.3	1.7
70°-80°	57.2	0.9
80°-90°	19.1	0.3
90°-100°	59.4	0.9
100°-110°	378.6	5.7
110°-120°	724.2	10.9
120°-130°	919.3	13.8
130°-140°	983.6	14.8
140°-150°	919.8	13.8
150°-160°	741.8	11.1
160°-170°	478.4	7.2
170°-180°	164.9	2.5
0°-30°	428.0	6.4
0°-40°	685.0	10.3
0°-60°	1090.8	16.4
0°-90°	1283.4	19.3
90°-120°	1162.1	17.5
90°-150°	3984.9	59.9
90°-180°	5370.0	80.7
0°-180°	6653.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	13
90°	39	4	39	4	39	17
95°	38	71	38	71	38	30
105°	370	391	370	391	370	323
115°	735	730	735	730	735	727
125°	1034	1026	1034	1026	1034	920
135°	1282	1272	1282	1272	1282	986
145°	1475	1467	1475	1467	1475	922
155°	1608	1609	1608	1609	1608	741
165°	1689	1697	1689	1697	1689	477
175°	1726	1736	1726	1736	1726	164
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	11.4	11.1	11.1	11.0	11.1	10.7	10.5	10.5	9.8	9.6	9.1
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0	29.3	27.6	25.2
95°	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0	30.3	28.6	28.2
97.5°	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6	34.4	34.3	66.5
100°	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4	52.3	57.2	96.9
102.5°	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4	222.3	275.3	280.4
105°	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3	407.7	405.1	403.6
107.5°	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6	506.4	505.1	503.1
110°	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8	573.2	572.6	570.8



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8	637.9	638.1	637.2
115°	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5	732.9	732.3	732.6
117.5°	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7	829.8	829.9	829.3
120°	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1	888.4
122.5°	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0	947.7	947.4	946.9
125°	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1	1029.2	1028.4	1028.9
127.5°	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6	1111.8	1112.0	1110.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4	1161.1	1160.8	1159.9
132.5°	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2	1209.9	1209.6	1208.5
135°	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5	1276.9	1276.3	1275.2
137.5°	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0	1341.4	1340.7	1339.5
140°	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0	1381.1	1380.2	1379.7
142.5°	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9	1418.2	1417.6	1417.3
145°	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7	1471.4	1471.1	1471.1
147.5°	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0	1517.9	1517.6	1517.9
150°	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7	1547.7	1547.7	1548.0
152.5°	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6	1573.1	1572.6	1573.1
155°	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4	1607.3	1606.1	1607.1
157.5°	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5	1636.5
160°	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2	1654.5
162.5°	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3	1671.5	1669.7	1670.1
165°	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1	1692.8	1690.6	1690.6
167.5°	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2	1708.7	1706.2	1706.3
170°	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1	1718.8	1716.5	1716.2
172.5°	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3	1725.0	1722.8	1722.4
175°	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7	1732.1	1729.5	1729.2
177.5°	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6	1735.8	1733.9	1733.5
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	8.7	8.1	7.9	7.4	6.9	7.0	6.8	6.3	6.5	6.6	6.7
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4	61.6	51.8	42.0
97.5°	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6	157.7	163.8	170.0
100°	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9	218.2	223.3	228.5
102.5°	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5	285.3	289.1	292.9
105°	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8	392.5	394.3	396.1
107.5°	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3	493.3	494.1	495.0
110°	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9	561.8	562.7	563.5





TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4	629.0	630.5	632.1
115°	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7	730.6	731.4	732.3
117.5°	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9	823.0	824.2	825.4
120°	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2	885.4	886.6	887.7
122.5°	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4	943.1	943.7	944.4
125°	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8	1026.9	1028.0	1029.2
127.5°	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7	1105.0	1105.3	1105.5
130°	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6	1155.9	1156.2	1156.5
132.5°	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3	1202.8	1203.4	1203.9
135°	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5	1272.1	1271.9	1271.6
137.5°	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6	1334.6	1334.7	1334.9
140°	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4	1412.4	1413.5	1414.5
145°	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2	1468.1	1469.0	1469.8
147.5°	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7	1513.2	1514.8	1516.5
150°	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9	1545.0	1546.1	1547.3
152.5°	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8	1571.8	1572.7	1573.6
155°	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8	1609.0	1609.3	1609.6
157.5°	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7	1640.5	1640.4	1640.2
160°	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4	1658.5	1657.7	1656.8
162.5°	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0	1674.9	1673.8	1672.8
165°	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0	1695.6	1694.2	1692.7
167.5°	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6	1712.2	1710.6	1709.2
170°	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0	1721.3	1719.5	1717.8
172.5°	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2	1727.5	1725.8	1724.1
175°	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9	1734.2	1732.5	1730.8
177.5°	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1	1737.5	1735.9	1734.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	7.4	7.7	8.3	8.4	9.0	9.5	9.6	10.0	10.5	10.5	10.8
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0	32.7	34.4	35.4
95°	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0	33.8	35.5	36.5
97.5°	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6	34.8	35.0	35.2
100°	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4	42.4	37.5	35.2
102.5°	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4	116.5	63.6	37.2
105°	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3	412.9	415.5	411.6
107.5°	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6	508.9	510.1	511.3
110°	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8	574.4	574.9	575.7



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8	637.7	637.6	638.1
115°	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5	734.0	734.6	734.9
117.5°	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7	829.6	829.5	829.4
120°	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2	889.8	890.4	890.4
122.5°	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0	948.4	948.7	948.6
125°	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1	1031.0	1031.8	1032.4
127.5°	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6	1111.5	1111.3	1111.0
130°	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4	1161.7	1161.9	1162.1
132.5°	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2	1210.5	1210.7	1210.8
135°	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5	1278.1	1278.7	1279.3
137.5°	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0	1342.6	1343.3	1343.5
140°	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0	1382.9	1383.7	1384.2
142.5°	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9	1419.5	1420.1	1420.5
145°	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7	1472.0	1472.2	1472.7
147.5°	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0	1518.3	1518.5	1518.8
150°	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7	1547.7	1547.7	1547.9
152.5°	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6	1574.0	1574.5	1574.6
155°	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4	1609.6	1610.8	1610.9
157.5°	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5
160°	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1
162.5°	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3	1675.0	1676.7	1676.5
165°	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1	1697.5	1699.8	1699.6
167.5°	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2	1713.7	1716.3	1716.1
170°	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1	1723.5	1725.8	1725.4
172.5°	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3	1729.7	1732.0	1731.6
175°	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7	1737.3	1739.9	1739.5
177.5°	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6	1739.5	1741.3	1740.9
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	11.2	11.1	11.1	11.4	11.1	11.1	11.2	10.8	10.5	10.5	10.0
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0
95°	36.8	37.1	37.4	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0
97.5°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6
100°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4
102.5°	37.2	37.3	37.4	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4
105°	401.2	390.8	380.5	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3
107.5°	512.5	513.5	514.6	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6
110°	576.5	577.4	578.2	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	639.2	640.2	641.4	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8
115°	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5
117.5°	829.2	829.1	829.1	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7
120°	889.8	889.2	888.7	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2
122.5°	948.0	947.4	946.8	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0
125°	1032.7	1032.9	1033.3	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1
127.5°	1110.9	1110.6	1110.3	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4
132.5°	1210.6	1210.3	1210.1	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2
135°	1279.8	1280.4	1281.0	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5
137.5°	1343.3	1343.2	1343.0	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0
140°	1384.6	1384.8	1385.1	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0
142.5°	1420.6	1420.6	1420.6	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9
145°	1473.3	1473.9	1474.5	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7
147.5°	1519.1	1519.3	1519.7	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0
150°	1548.2	1548.4	1548.8	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7
152.5°	1574.4	1574.3	1574.1	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6
155°	1610.1	1609.2	1608.3	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4
157.5°	1640.0	1638.5	1637.0	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5
160°	1659.4	1657.7	1656.0	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7
162.5°	1674.6	1672.7	1670.7	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3
165°	1697.0	1694.4	1691.9	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1
167.5°	1713.2	1710.4	1707.4	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2
170°	1722.6	1719.7	1716.8	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1
172.5°	1728.5	1725.4	1722.3	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3
175°	1735.9	1732.5	1729.1	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7
177.5°	1738.1	1735.3	1732.5	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	9.6	9.5	9.0	8.4	8.3	7.7	7.4	6.7	6.6	6.5	6.3
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	29.3	27.6	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4
95°	30.3	28.6	28.2	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4
97.5°	34.4	34.3	66.5	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6
100°	52.3	57.2	96.9	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9
102.5°	222.3	275.3	280.4	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5
105°	407.7	405.1	403.6	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8
107.5°	506.4	505.1	503.1	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3
110°	573.2	572.6	570.8	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.9	638.1	637.2	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4
115°	732.9	732.3	732.6	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7
117.5°	829.8	829.9	829.3	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9
120°	888.7	888.1	888.4	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2
122.5°	947.7	947.4	946.9	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4
125°	1029.2	1028.4	1028.9	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8
127.5°	1111.8	1112.0	1110.6	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7
130°	1161.1	1160.8	1159.9	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6
132.5°	1209.9	1209.6	1208.5	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3
135°	1276.9	1276.3	1275.2	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5
137.5°	1341.4	1340.7	1339.5	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6
140°	1381.1	1380.2	1379.7	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1418.2	1417.6	1417.3	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4
145°	1471.4	1471.1	1471.1	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2
147.5°	1517.9	1517.6	1517.9	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7
150°	1547.7	1547.7	1548.0	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9
152.5°	1573.1	1572.6	1573.1	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8
155°	1607.3	1606.1	1607.1	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8
157.5°	1637.0	1635.5	1636.5	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7
160°	1656.0	1654.2	1654.5	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4
162.5°	1671.5	1669.7	1670.1	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0
165°	1692.8	1690.6	1690.6	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0
167.5°	1708.7	1706.2	1706.3	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6
170°	1718.8	1716.5	1716.2	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0
172.5°	1725.0	1722.8	1722.4	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2
175°	1732.1	1729.5	1729.2	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9
177.5°	1735.8	1733.9	1733.5	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.8	7.0	6.9	7.4	7.9	8.1	8.7	9.1	9.6	9.8	10.5
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0
95°	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0
97.5°	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6
100°	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4
102.5°	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4
105°	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3
107.5°	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6
110°	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8





TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8
115°	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5
117.5°	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7
120°	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2
122.5°	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0
125°	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1
127.5°	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6
130°	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4
132.5°	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2
135°	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5
137.5°	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0
140°	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0
142.5°	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9
145°	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7
147.5°	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0
150°	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7
152.5°	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6
155°	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4
157.5°	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5
160°	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7
162.5°	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3
165°	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1
167.5°	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2
170°	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1
172.5°	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3
175°	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7
177.5°	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	10.5	10.7	11.1	11.0	11.1	11.1	11.4
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P333031-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)