

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333032-935

Luminaire Tested: **S124RDIW-S350D1560U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333032-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1560U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5940.7 lumens  
Efficiency: N/A  
Efficacy: 111.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	88	84	81	81	78	75	72	59	57	56	42	41	40	27	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	0.8
10°-20°	147.8	2.5
20°-30°	231.2	3.9
30°-40°	257.0	4.3
40°-50°	228.0	3.8
50°-60°	177.7	3.0
60°-70°	116.3	2.0
70°-80°	57.2	1.0
80°-90°	19.1	0.3
90°-100°	110.7	1.9
100°-110°	328.0	5.5
110°-120°	556.7	9.4
120°-130°	734.0	12.4
130°-140°	824.4	13.9
140°-150°	810.1	13.6
150°-160°	681.3	11.5
160°-170°	453.3	7.6
170°-180°	158.7	2.7
0°-30°	428.0	7.2
0°-40°	685.0	11.5
0°-60°	1090.8	18.4
0°-90°	1283.4	21.6
90°-120°	995.4	16.8
90°-150°	3363.9	56.6
90°-180°	4657.0	78.4
0°-180°	5940.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	13
90°	39	4	39	4	39	20
95°	102	78	102	78	102	107
105°	317	302	317	302	317	334
115°	561	566	561	566	561	554
125°	818	824	818	824	818	730
135°	1064	1063	1064	1063	1064	822
145°	1293	1292	1293	1292	1293	809
155°	1479	1480	1479	1480	1479	681
165°	1607	1611	1607	1611	1607	453
175°	1668	1676	1668	1676	1668	158
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	11.4	11.1	11.1	11.0	11.1	10.7	10.5	10.5	9.8	9.6	9.1
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	57.6	57.3	56.9	56.6	56.2	55.5	54.5	53.5	52.4	51.4	49.8
95°	102.5	102.5	102.5	102.5	102.5	102.1	101.3	100.4	99.5	98.7	96.7
97.5°	160.7	160.7	160.7	160.7	160.7	160.2	159.2	158.2	157.0	156.0	153.7
100°	201.2	201.2	201.2	201.2	201.2	201.0	200.4	199.8	199.2	198.6	196.0
102.5°	246.9	246.7	246.5	246.2	246.0	245.5	244.7	243.8	243.1	242.3	239.9
105°	316.8	315.9	315.0	314.2	313.3	312.5	311.6	310.7	309.9	309.0	307.8
107.5°	384.8	384.9	385.0	385.0	385.0	384.7	383.8	383.1	382.2	381.4	381.3
110°	433.6	432.7	431.9	431.0	430.2	430.0	430.6	431.2	431.7	432.3	432.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.5	483.3	483.1	482.9	482.8	482.8	482.8	482.9	483.1	483.2	483.7
115°	560.9	561.1	561.5	561.7	562.0	562.3	562.6	562.8	563.2	563.4	564.0
117.5°	634.6	635.2	635.8	636.3	636.9	637.7	638.7	639.6	640.6	641.6	642.0
120°	690.7	690.1	689.5	689.0	688.4	688.8	690.3	691.6	693.1	694.6	695.4
122.5°	737.4	738.5	739.5	740.5	741.6	742.6	743.6	744.5	745.5	746.5	746.9
125°	817.9	818.5	819.1	819.6	820.2	820.8	821.4	821.9	822.5	823.1	823.4
127.5°	892.4	892.9	893.4	893.8	894.2	894.8	895.4	896.0	896.5	897.1	897.6
130°	941.2	942.4	943.6	944.7	945.8	946.7	947.3	947.9	948.5	949.0	949.0
132.5°	993.2	993.6	994.1	994.5	995.0	995.5	996.1	996.7	997.3	997.8	998.1
135°	1064.5	1065.4	1066.3	1067.1	1068.0	1068.8	1069.4	1069.9	1070.5	1071.1	1071.1
137.5°	1139.6	1139.4	1139.3	1139.1	1138.9	1139.2	1140.0	1140.7	1141.4	1142.2	1141.8
140°	1185.3	1185.6	1185.9	1186.2	1186.5	1186.7	1187.1	1187.3	1187.6	1187.9	1187.9
142.5°	1231.0	1231.1	1231.1	1231.1	1231.2	1231.3	1231.3	1231.4	1231.5	1231.5	1231.7
145°	1293.0	1293.9	1294.8	1295.6	1296.5	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1355.9	1356.2	1356.5	1356.8	1357.0	1357.3	1357.5	1357.8	1358.0	1358.2	1358.5
150°	1394.3	1394.6	1394.9	1395.2	1395.5	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1429.6	1430.4	1431.2	1431.8	1432.6	1432.6	1431.9	1431.2	1430.6	1429.9	1429.7
155°	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7	1479.0
157.5°	1522.6	1523.5	1524.6	1525.5	1526.5	1526.6	1525.7	1524.8	1524.0	1523.1	1523.2
160°	1547.5	1548.9	1550.4	1551.9	1553.2	1553.6	1552.7	1551.9	1551.0	1550.1	1550.4
162.5°	1573.5	1574.9	1576.4	1577.8	1579.2	1579.2	1577.6	1576.1	1574.5	1573.0	1573.2
165°	1607.2	1608.3	1609.6	1610.7	1611.9	1611.5	1609.8	1608.1	1606.4	1604.6	1605.2
167.5°	1631.3	1633.1	1635.0	1636.8	1638.6	1638.6	1636.8	1635.1	1633.4	1631.7	1631.6
170°	1644.9	1646.9	1648.9	1651.0	1652.9	1653.1	1651.4	1649.7	1647.9	1646.1	1645.9
172.5°	1656.3	1658.3	1660.4	1662.3	1664.4	1664.4	1662.4	1660.5	1658.5	1656.6	1656.5
175°	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3	1668.5
177.5°	1674.5	1676.4	1678.2	1680.0	1681.9	1682.0	1680.3	1678.8	1677.1	1675.5	1675.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	8.7	8.1	7.9	7.4	6.9	7.0	6.8	6.3	6.5	6.6	6.7
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	48.2	46.6	44.9	42.4	38.7	35.0	31.4	27.8	31.4	35.0	38.7
95°	94.6	92.6	90.6	88.3	85.7	83.1	80.5	77.9	80.5	83.1	85.7
97.5°	151.3	149.0	146.6	144.4	142.3	140.2	138.1	136.0	138.1	140.2	142.3
100°	193.5	190.9	188.2	186.4	185.2	184.1	182.9	181.8	182.9	184.1	185.2
102.5°	237.5	235.1	232.8	231.4	230.9	230.5	230.0	229.5	230.0	230.5	230.9
105°	306.7	305.5	304.4	303.7	303.3	303.1	302.8	302.5	302.8	303.1	303.3
107.5°	381.1	380.9	380.7	380.5	380.1	379.8	379.4	379.1	379.4	379.8	380.1
110°	432.9	433.2	433.5	433.3	432.7	432.1	431.6	431.0	431.6	432.1	432.7





TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	484.2	484.7	485.3	485.5	485.3	485.3	485.2	485.0	485.2	485.3	485.3
115°	564.6	565.2	565.8	566.0	566.0	566.0	566.0	566.0	566.0	566.0	566.0
117.5°	642.4	642.8	643.3	643.3	643.1	642.8	642.6	642.4	642.6	642.8	643.1
120°	696.3	697.2	698.0	697.8	696.7	695.6	694.4	693.3	694.4	695.6	696.7
122.5°	747.3	747.7	748.1	748.0	747.6	747.2	746.7	746.2	746.7	747.2	747.6
125°	823.6	824.0	824.2	824.4	824.4	824.4	824.4	824.4	824.4	824.4	824.4
127.5°	898.0	898.5	899.0	898.7	897.9	897.0	896.1	895.3	896.1	897.0	897.9
130°	949.0	949.0	949.0	948.6	947.7	946.8	946.0	945.1	946.0	946.8	947.7
132.5°	998.3	998.5	998.8	998.6	997.9	997.3	996.7	996.0	996.7	997.3	997.9
135°	1071.1	1071.1	1071.1	1070.2	1068.5	1066.7	1065.0	1063.2	1065.0	1066.7	1068.5
137.5°	1141.3	1140.8	1140.4	1139.7	1138.9	1138.1	1137.3	1136.5	1137.3	1138.1	1138.9
140°	1187.9	1187.9	1187.9	1187.6	1187.1	1186.5	1185.9	1185.3	1185.9	1186.5	1187.1
142.5°	1232.0	1232.2	1232.4	1232.3	1231.7	1231.1	1230.5	1229.9	1230.5	1231.1	1231.7
145°	1297.7	1297.4	1297.1	1296.4	1295.2	1294.1	1292.9	1291.8	1292.9	1294.1	1295.2
147.5°	1358.7	1358.9	1359.2	1358.6	1357.2	1355.8	1354.4	1353.1	1354.4	1355.8	1357.2
150°	1395.6	1395.6	1395.6	1395.1	1393.9	1392.8	1391.5	1390.4	1391.5	1392.8	1393.9
152.5°	1429.4	1429.2	1429.0	1428.5	1427.8	1427.1	1426.4	1425.7	1426.4	1427.1	1427.8
155°	1479.3	1479.5	1479.9	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0
157.5°	1523.2	1523.3	1523.4	1523.6	1524.1	1524.7	1525.2	1525.7	1525.2	1524.7	1524.1
160°	1550.7	1551.0	1551.3	1551.5	1551.9	1552.1	1552.4	1552.7	1552.4	1552.1	1551.9
162.5°	1573.6	1573.8	1574.1	1574.6	1575.4	1576.1	1576.9	1577.6	1576.9	1576.1	1575.4
165°	1605.8	1606.4	1607.0	1607.7	1608.5	1609.4	1610.2	1611.1	1610.2	1609.4	1608.5
167.5°	1631.5	1631.5	1631.4	1632.0	1633.2	1634.4	1635.6	1636.8	1635.6	1634.4	1633.2
170°	1645.6	1645.3	1645.0	1645.6	1647.0	1648.5	1649.9	1651.4	1649.9	1648.5	1647.0
172.5°	1656.5	1656.4	1656.3	1656.9	1658.1	1659.3	1660.5	1661.7	1660.5	1659.3	1658.1
175°	1668.8	1669.1	1669.4	1670.3	1671.7	1673.2	1674.6	1676.0	1674.6	1673.2	1671.7
177.5°	1675.5	1675.5	1675.5	1676.1	1677.2	1678.4	1679.6	1680.7	1679.6	1678.4	1677.2
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	7.4	7.7	8.3	8.4	9.0	9.5	9.6	10.0	10.5	10.5	10.8
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	42.4	44.9	46.6	48.2	49.8	51.4	52.4	53.5	54.5	55.5	56.2
95°	88.3	90.6	92.6	94.6	96.7	98.7	99.5	100.4	101.3	102.1	102.5
97.5°	144.4	146.6	149.0	151.3	153.7	156.0	157.0	158.2	159.2	160.2	160.7
100°	186.4	188.2	190.9	193.5	196.0	198.6	199.2	199.8	200.4	201.0	201.2
102.5°	231.4	232.8	235.1	237.5	239.9	242.3	243.1	243.8	244.7	245.5	246.0
105°	303.7	304.4	305.5	306.7	307.8	309.0	309.9	310.7	311.6	312.5	313.3
107.5°	380.5	380.7	380.9	381.1	381.3	381.4	382.2	383.1	383.8	384.7	385.0
110°	433.3	433.5	433.2	432.9	432.6	432.3	431.7	431.2	430.6	430.0	430.2



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	485.5	485.3	484.7	484.2	483.7	483.2	483.1	482.9	482.8	482.8	482.8
115°	566.0	565.8	565.2	564.6	564.0	563.4	563.2	562.8	562.6	562.3	562.0
117.5°	643.3	643.3	642.8	642.4	642.0	641.6	640.6	639.6	638.7	637.7	636.9
120°	697.8	698.0	697.2	696.3	695.4	694.6	693.1	691.6	690.3	688.8	688.4
122.5°	748.0	748.1	747.7	747.3	746.9	746.5	745.5	744.5	743.6	742.6	741.6
125°	824.4	824.2	824.0	823.6	823.4	823.1	822.5	821.9	821.4	820.8	820.2
127.5°	898.7	899.0	898.5	898.0	897.6	897.1	896.5	896.0	895.4	894.8	894.2
130°	948.6	949.0	949.0	949.0	949.0	949.0	948.5	947.9	947.3	946.7	945.8
132.5°	998.6	998.8	998.5	998.3	998.1	997.8	997.3	996.7	996.1	995.5	995.0
135°	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5	1069.9	1069.4	1068.8	1068.0
137.5°	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4	1140.7	1140.0	1139.2	1138.9
140°	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.3	1187.1	1186.7	1186.5
142.5°	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5	1231.4	1231.3	1231.3	1231.2
145°	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0	1297.7	1297.4	1297.1	1296.5
147.5°	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0	1357.8	1357.5	1357.3	1357.0
150°	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.5
152.5°	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6	1431.2	1431.9	1432.6	1432.6
155°	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3
157.5°	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0	1524.8	1525.7	1526.6	1526.5
160°	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0	1551.9	1552.7	1553.6	1553.2
162.5°	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5	1576.1	1577.6	1579.2	1579.2
165°	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4	1608.1	1609.8	1611.5	1611.9
167.5°	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4	1635.1	1636.8	1638.6	1638.6
170°	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9	1649.7	1651.4	1653.1	1652.9
172.5°	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5	1660.5	1662.4	1664.4	1664.4
175°	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4
177.5°	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1	1678.8	1680.3	1682.0	1681.9
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	11.2	11.1	11.1	11.4	11.1	11.1	11.2	10.8	10.5	10.5	10.0
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	56.6	56.9	57.3	57.6	57.3	56.9	56.6	56.2	55.5	54.5	53.5
95°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.3	100.4
97.5°	160.7	160.7	160.7	160.7	160.7	160.7	160.7	160.7	160.2	159.2	158.2
100°	201.2	201.2	201.2	201.2	201.2	201.2	201.2	201.2	201.0	200.4	199.8
102.5°	246.2	246.5	246.7	246.9	246.7	246.5	246.2	246.0	245.5	244.7	243.8
105°	314.2	315.0	315.9	316.8	315.9	315.0	314.2	313.3	312.5	311.6	310.7
107.5°	385.0	385.0	384.9	384.8	384.9	385.0	385.0	385.0	384.7	383.8	383.1
110°	431.0	431.9	432.7	433.6	432.7	431.9	431.0	430.2	430.0	430.6	431.2



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.9	483.1	483.3	483.5	483.3	483.1	482.9	482.8	482.8	482.8	482.9
115°	561.7	561.5	561.1	560.9	561.1	561.5	561.7	562.0	562.3	562.6	562.8
117.5°	636.3	635.8	635.2	634.6	635.2	635.8	636.3	636.9	637.7	638.7	639.6
120°	689.0	689.5	690.1	690.7	690.1	689.5	689.0	688.4	688.8	690.3	691.6
122.5°	740.5	739.5	738.5	737.4	738.5	739.5	740.5	741.6	742.6	743.6	744.5
125°	819.6	819.1	818.5	817.9	818.5	819.1	819.6	820.2	820.8	821.4	821.9
127.5°	893.8	893.4	892.9	892.4	892.9	893.4	893.8	894.2	894.8	895.4	896.0
130°	944.7	943.6	942.4	941.2	942.4	943.6	944.7	945.8	946.7	947.3	947.9
132.5°	994.5	994.1	993.6	993.2	993.6	994.1	994.5	995.0	995.5	996.1	996.7
135°	1067.1	1066.3	1065.4	1064.5	1065.4	1066.3	1067.1	1068.0	1068.8	1069.4	1069.9
137.5°	1139.1	1139.3	1139.4	1139.6	1139.4	1139.3	1139.1	1138.9	1139.2	1140.0	1140.7
140°	1186.2	1185.9	1185.6	1185.3	1185.6	1185.9	1186.2	1186.5	1186.7	1187.1	1187.3
142.5°	1231.1	1231.1	1231.1	1231.0	1231.1	1231.1	1231.1	1231.2	1231.3	1231.3	1231.4
145°	1295.6	1294.8	1293.9	1293.0	1293.9	1294.8	1295.6	1296.5	1297.1	1297.4	1297.7
147.5°	1356.8	1356.5	1356.2	1355.9	1356.2	1356.5	1356.8	1357.0	1357.3	1357.5	1357.8
150°	1395.2	1394.9	1394.6	1394.3	1394.6	1394.9	1395.2	1395.5	1395.6	1395.6	1395.6
152.5°	1431.8	1431.2	1430.4	1429.6	1430.4	1431.2	1431.8	1432.6	1432.6	1431.9	1431.2
155°	1482.1	1481.0	1479.9	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0
157.5°	1525.5	1524.6	1523.5	1522.6	1523.5	1524.6	1525.5	1526.5	1526.6	1525.7	1524.8
160°	1551.9	1550.4	1548.9	1547.5	1548.9	1550.4	1551.9	1553.2	1553.6	1552.7	1551.9
162.5°	1577.8	1576.4	1574.9	1573.5	1574.9	1576.4	1577.8	1579.2	1579.2	1577.6	1576.1
165°	1610.7	1609.6	1608.3	1607.2	1608.3	1609.6	1610.7	1611.9	1611.5	1609.8	1608.1
167.5°	1636.8	1635.0	1633.1	1631.3	1633.1	1635.0	1636.8	1638.6	1638.6	1636.8	1635.1
170°	1651.0	1648.9	1646.9	1644.9	1646.9	1648.9	1651.0	1652.9	1653.1	1651.4	1649.7
172.5°	1662.3	1660.4	1658.3	1656.3	1658.3	1660.4	1662.3	1664.4	1664.4	1662.4	1660.5
175°	1674.3	1672.3	1670.3	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3
177.5°	1680.0	1678.2	1676.4	1674.5	1676.4	1678.2	1680.0	1681.9	1682.0	1680.3	1678.8
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	9.6	9.5	9.0	8.4	8.3	7.7	7.4	6.7	6.6	6.5	6.3
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	52.4	51.4	49.8	48.2	46.6	44.9	42.4	38.7	35.0	31.4	27.8
95°	99.5	98.7	96.7	94.6	92.6	90.6	88.3	85.7	83.1	80.5	77.9
97.5°	157.0	156.0	153.7	151.3	149.0	146.6	144.4	142.3	140.2	138.1	136.0
100°	199.2	198.6	196.0	193.5	190.9	188.2	186.4	185.2	184.1	182.9	181.8
102.5°	243.1	242.3	239.9	237.5	235.1	232.8	231.4	230.9	230.5	230.0	229.5
105°	309.9	309.0	307.8	306.7	305.5	304.4	303.7	303.3	303.1	302.8	302.5
107.5°	382.2	381.4	381.3	381.1	380.9	380.7	380.5	380.1	379.8	379.4	379.1
110°	431.7	432.3	432.6	432.9	433.2	433.5	433.3	432.7	432.1	431.6	431.0



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	483.1	483.2	483.7	484.2	484.7	485.3	485.5	485.3	485.3	485.2	485.0
115°	563.2	563.4	564.0	564.6	565.2	565.8	566.0	566.0	566.0	566.0	566.0
117.5°	640.6	641.6	642.0	642.4	642.8	643.3	643.3	643.1	642.8	642.6	642.4
120°	693.1	694.6	695.4	696.3	697.2	698.0	697.8	696.7	695.6	694.4	693.3
122.5°	745.5	746.5	746.9	747.3	747.7	748.1	748.0	747.6	747.2	746.7	746.2
125°	822.5	823.1	823.4	823.6	824.0	824.2	824.4	824.4	824.4	824.4	824.4
127.5°	896.5	897.1	897.6	898.0	898.5	899.0	898.7	897.9	897.0	896.1	895.3
130°	948.5	949.0	949.0	949.0	949.0	949.0	948.6	947.7	946.8	946.0	945.1
132.5°	997.3	997.8	998.1	998.3	998.5	998.8	998.6	997.9	997.3	996.7	996.0
135°	1070.5	1071.1	1071.1	1071.1	1071.1	1071.1	1070.2	1068.5	1066.7	1065.0	1063.2
137.5°	1141.4	1142.2	1141.8	1141.3	1140.8	1140.4	1139.7	1138.9	1138.1	1137.3	1136.5
140°	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.1	1186.5	1185.9	1185.3
142.5°	1231.5	1231.5	1231.7	1232.0	1232.2	1232.4	1232.3	1231.7	1231.1	1230.5	1229.9
145°	1298.0	1298.2	1298.0	1297.7	1297.4	1297.1	1296.4	1295.2	1294.1	1292.9	1291.8
147.5°	1358.0	1358.2	1358.5	1358.7	1358.9	1359.2	1358.6	1357.2	1355.8	1354.4	1353.1
150°	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.1	1393.9	1392.8	1391.5	1390.4
152.5°	1430.6	1429.9	1429.7	1429.4	1429.2	1429.0	1428.5	1427.8	1427.1	1426.4	1425.7
155°	1479.9	1478.7	1479.0	1479.3	1479.5	1479.9	1480.0	1480.0	1480.0	1480.0	1480.0
157.5°	1524.0	1523.1	1523.2	1523.2	1523.3	1523.4	1523.6	1524.1	1524.7	1525.2	1525.7
160°	1551.0	1550.1	1550.4	1550.7	1551.0	1551.3	1551.5	1551.9	1552.1	1552.4	1552.7
162.5°	1574.5	1573.0	1573.2	1573.6	1573.8	1574.1	1574.6	1575.4	1576.1	1576.9	1577.6
165°	1606.4	1604.6	1605.2	1605.8	1606.4	1607.0	1607.7	1608.5	1609.4	1610.2	1611.1
167.5°	1633.4	1631.7	1631.6	1631.5	1631.5	1631.4	1632.0	1633.2	1634.4	1635.6	1636.8
170°	1647.9	1646.1	1645.9	1645.6	1645.3	1645.0	1645.6	1647.0	1648.5	1649.9	1651.4
172.5°	1658.5	1656.6	1656.5	1656.5	1656.4	1656.3	1656.9	1658.1	1659.3	1660.5	1661.7
175°	1670.3	1668.3	1668.5	1668.8	1669.1	1669.4	1670.3	1671.7	1673.2	1674.6	1676.0
177.5°	1677.1	1675.5	1675.5	1675.5	1675.5	1675.5	1676.1	1677.2	1678.4	1679.6	1680.7
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.8	7.0	6.9	7.4	7.9	8.1	8.7	9.1	9.6	9.8	10.5
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4	53.5
95°	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5	100.4
97.5°	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0	158.2
100°	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2	199.8
102.5°	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1	243.8
105°	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9	310.7
107.5°	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2	383.1
110°	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7	431.2





TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1	482.9
115°	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2	562.8
117.5°	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6	639.6
120°	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1	691.6
122.5°	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5	744.5
125°	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5	821.9
127.5°	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5	896.0
130°	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5	947.9
132.5°	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3	996.7
135°	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5	1069.9
137.5°	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4	1140.7
140°	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.3
142.5°	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5	1231.4
145°	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0	1297.7
147.5°	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0	1357.8
150°	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6	1431.2
155°	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9	1481.0
157.5°	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0	1524.8
160°	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0	1551.9
162.5°	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5	1576.1
165°	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4	1608.1
167.5°	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4	1635.1
170°	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9	1649.7
172.5°	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5	1660.5
175°	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3	1672.3
177.5°	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1	1678.8
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	10.5	10.7	11.1	11.0	11.1	11.1	11.4
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	430.6	430.0	430.2	431.0	431.9	432.7	433.6



TEST NUMBER: P333032-935

CATALOG NUMBER: S124RDIW-S350D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)