

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333035-935

Luminaire Tested: **S124RDIW-S575D470U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333035-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3717.1 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36
4	77	66	58	52	71	62	55	50	54	49	45	47	43	39	40	37	35	31
5	71	59	51	45	66	56	48	43	49	43	39	42	38	35	36	33	30	27
6	65	53	45	40	61	50	43	38	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6713	6713	6713	6713
5°	7786	6733	5951	6733
10°	9211	6703	5311	6703
15°	10639	6641	4563	6641
20°	11846	6556	4127	6556
25°	12229	6472	3832	6472
30°	10705	6371	3653	6371
35°	8333	6220	3546	6220
40°	6249	6048	3488	6048
45°	4933	5771	3457	5771
50°	4166	5452	3357	5452
55°	3631	5102	3178	5102
60°	3266	4737	2813	4737
65°	2881	4346	2420	4346
70°	2594	3939	2183	3939
75°	2174	3490	1862	3490
80°	1836	2975	1743	2975
85°	1556	2325	1556	2325



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.6	2.2
10°-20°	243.0	6.5
20°-30°	380.1	10.2
30°-40°	422.5	11.4
40°-50°	374.9	10.1
50°-60°	292.1	7.9
60°-70°	191.3	5.1
70°-80°	94.1	2.5
80°-90°	24.7	0.7
90°-100°	17.8	0.5
100°-110°	113.8	3.1
110°-120°	217.6	5.9
120°-130°	276.3	7.4
130°-140°	295.6	8.0
140°-150°	276.4	7.4
150°-160°	222.9	6.0
160°-170°	143.8	3.9
170°-180°	49.6	1.3
0°-30°	703.7	18.9
0°-40°	1126.2	30.3
0°-60°	1793.2	48.2
0°-90°	2103.3	56.6
90°-120°	349.2	9.4
90°-150°	1197.5	32.2
90°-180°	1614.0	43.4
0°-180°	3717.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	832	832	832	832	832	
5°	961	831	734	831	961	97
15°	1273	795	546	795	1273	362
25°	1373	727	430	727	1373	609
35°	846	631	360	631	846	530
45°	432	506	303	506	432	342
55°	258	362	226	362	258	235
65°	151	228	127	228	151	152
75°	70	112	60	112	70	77
85°	17	25	17	25	17	19
90°	12	1	12	1	12	6
95°	11	21	11	21	11	9
105°	111	117	111	117	111	97
115°	221	219	221	219	221	219
125°	311	308	311	308	311	277
135°	385	382	385	382	385	296
145°	443	441	443	441	443	277
155°	483	484	483	484	483	223
165°	508	510	508	510	508	143
175°	519	522	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	877.0	879.4	877.0	876.8	874.1	873.3	872.2	868.7	862.3	858.5	859.4
5°	960.8	969.1	964.5	963.8	956.4	949.1	944.3	933.7	922.2	914.6	908.2
7.5°	1057.7	1062.5	1059.5	1054.8	1042.9	1036.1	1025.3	1011.2	990.8	975.1	960.9
10°	1123.6	1127.6	1126.3	1117.6	1108.9	1091.1	1081.1	1061.3	1035.4	1015.0	995.9
12.5°	1188.4	1192.7	1180.9	1181.4	1164.8	1150.8	1134.9	1110.1	1080.2	1053.9	1030.0
15°	1273.0	1267.7	1267.7	1260.9	1242.5	1223.1	1206.7	1180.5	1143.0	1111.6	1078.4
17.5°	1339.2	1341.1	1338.3	1322.5	1308.0	1288.0	1257.8	1227.4	1192.5	1150.2	1116.4
20°	1378.9	1378.9	1375.9	1365.1	1346.3	1324.9	1292.4	1259.3	1215.0	1172.5	1134.3
22.5°	1394.9	1396.0	1392.5	1383.6	1366.8	1345.8	1318.2	1284.4	1238.9	1191.0	1143.7
25°	1372.9	1379.1	1379.8	1377.5	1372.5	1359.8	1336.0	1301.5	1260.6	1208.7	1157.8
27.5°	1260.4	1268.4	1275.5	1287.0	1302.4	1310.5	1311.6	1294.0	1258.4	1208.4	1157.2
30°	1148.4	1155.0	1176.8	1205.3	1227.4	1247.5	1265.0	1269.6	1249.6	1204.6	1150.7
32.5°	1024.0	1033.1	1054.9	1085.5	1122.4	1156.4	1195.6	1215.5	1215.0	1188.0	1138.2
35°	845.5	852.2	872.4	904.5	948.7	999.3	1061.3	1109.5	1142.4	1140.0	1109.5
37.5°	681.9	689.5	709.8	736.5	779.4	842.0	902.0	968.5	1029.2	1063.2	1053.0
40°	593.0	593.3	613.0	640.5	680.7	735.3	800.6	874.3	942.0	997.3	1008.0
42.5°	522.7	522.8	535.9	565.5	594.4	645.8	708.2	781.4	860.6	924.4	952.8
45°	432.1	435.1	445.9	463.6	486.4	529.9	579.9	647.9	736.7	812.4	859.6
47.5°	365.9	370.4	377.2	391.7	409.8	438.9	480.1	541.2	613.5	696.7	764.0
50°	331.7	332.3	341.0	349.0	364.8	388.0	424.1	475.0	541.4	621.4	696.1
52.5°	302.2	302.0	307.3	317.5	330.3	348.3	377.5	423.9	482.7	554.4	631.5
55°	258.0	259.6	263.6	271.6	281.4	294.1	317.3	352.1	398.3	459.6	529.6
57.5°	224.3	225.2	228.3	231.8	240.6	249.9	267.3	291.4	330.5	380.6	445.9
60°	202.3	202.7	203.7	208.7	215.8	224.5	236.2	256.6	289.5	335.4	386.9
62.5°	180.9	181.5	183.0	186.8	192.2	198.2	210.4	226.9	254.1	293.3	339.8
65°	150.8	151.1	153.4	154.8	159.1	164.5	173.5	184.6	203.4	236.2	271.4
67.5°	126.0	126.0	126.1	127.9	131.0	134.5	139.9	148.8	162.9	183.0	214.0
70°	109.9	109.9	110.6	111.6	113.2	116.2	119.2	126.0	136.4	152.7	176.5
72.5°	94.9	95.1	95.8	96.0	96.9	99.4	101.6	105.8	113.6	126.0	145.2
75°	69.7	70.7	72.3	73.7	75.3	75.1	77.4	80.1	82.4	89.8	100.8
77.5°	51.8	51.3	51.5	52.7	52.9	53.2	54.8	56.9	58.7	62.2	66.1
80°	39.5	39.5	40.6	40.9	40.6	40.9	42.5	43.6	44.3	45.5	49.2
82.5°	29.9	30.4	30.0	30.4	30.7	31.0	32.4	32.5	33.2	33.8	35.3
85°	16.8	17.0	17.4	16.8	16.8	16.8	17.4	17.7	18.4	18.1	18.8
87.5°	8.3	7.9	8.2	8.1	8.4	8.0	8.2	8.6	8.0	8.2	8.0
90°	11.7	11.5	11.4	11.2	11.0	10.7	10.2	9.6	9.1	8.6	7.9
92.5°	10.8	10.8	10.7	10.7	10.6	10.3	9.8	9.3	8.8	8.3	7.6
95°	11.3	11.2	11.1	11.0	10.9	10.7	10.2	9.6	9.1	8.6	8.5
97.5°	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.4	10.3	10.3	20.0
100°	10.9	10.8	10.8	10.7	10.6	11.3	12.7	14.2	15.7	17.1	29.1
102.5°	11.3	11.2	11.2	11.2	11.2	19.1	35.0	50.9	66.8	82.7	84.3
105°	111.2	114.3	117.4	120.5	123.7	124.8	124.1	123.3	122.5	121.7	121.3
107.5°	155.0	154.6	154.3	154.0	153.7	153.3	152.9	152.6	152.1	151.8	151.2
110°	174.0	173.7	173.5	173.2	173.0	172.8	172.6	172.5	172.3	172.1	171.6



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	193.0	192.8	192.4	192.1	191.7	191.6	191.7	191.7	191.7	191.7	191.5
115°	220.8	220.8	220.8	220.8	220.8	220.8	220.6	220.4	220.2	220.1	220.2
117.5°	249.1	249.2	249.2	249.2	249.3	249.3	249.3	249.3	249.3	249.4	249.3
120°	266.9	267.1	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9	267.0
122.5°	284.4	284.6	284.7	284.9	285.1	285.1	285.0	284.9	284.8	284.7	284.6
125°	310.6	310.5	310.4	310.3	310.2	310.0	309.8	309.5	309.3	309.0	309.2
127.5°	333.6	333.7	333.7	333.8	333.9	334.0	334.0	334.1	334.2	334.2	333.8
130°	349.2	349.2	349.2	349.2	349.2	349.2	349.1	349.0	349.0	348.9	348.6
132.5°	363.6	363.7	363.8	363.8	363.9	363.9	363.8	363.7	363.6	363.5	363.2
135°	385.1	385.0	384.8	384.6	384.4	384.3	384.1	383.9	383.7	383.6	383.2
137.5°	403.6	403.6	403.6	403.7	403.7	403.7	403.5	403.3	403.1	402.9	402.5
140°	416.4	416.3	416.2	416.1	416.0	415.9	415.6	415.3	415.1	414.8	414.7
142.5°	427.0	427.0	427.0	426.9	426.9	426.8	426.6	426.4	426.2	426.0	425.9
145°	443.2	443.1	442.9	442.7	442.6	442.5	442.4	442.3	442.2	442.1	442.1
147.5°	456.8	456.7	456.6	456.5	456.4	456.3	456.2	456.2	456.2	456.1	456.2
150°	465.5	465.5	465.4	465.3	465.2	465.1	465.1	465.1	465.1	465.1	465.2
152.5°	473.0	473.0	473.1	473.2	473.2	473.2	473.0	472.9	472.8	472.6	472.8
155°	483.1	483.4	483.6	483.9	484.1	484.1	483.7	483.4	483.0	482.7	482.9
157.5°	491.5	492.0	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5	491.8
160°	497.1	497.7	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1	497.2
162.5°	501.5	502.0	502.7	503.3	503.9	503.9	503.3	502.8	502.3	501.8	501.9
165°	507.6	508.4	509.2	510.0	510.7	510.8	510.1	509.5	508.8	508.1	508.1
167.5°	512.3	513.2	514.0	514.9	515.7	515.8	515.1	514.3	513.5	512.7	512.8
170°	515.1	515.9	516.8	517.6	518.6	518.7	517.9	517.2	516.5	515.8	515.7
172.5°	516.6	517.5	518.5	519.4	520.4	520.5	519.8	519.1	518.4	517.7	517.6
175°	518.6	519.6	520.6	521.7	522.7	522.9	522.1	521.3	520.6	519.8	519.7
177.5°	519.9	520.6	521.5	522.4	523.1	523.3	522.7	522.2	521.6	521.1	520.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	856.7	852.9	851.0	846.7	841.6	839.0	836.5	833.1	828.5	823.7	820.2
5°	900.2	892.1	882.0	870.0	859.3	848.9	839.8	830.8	820.4	809.7	799.0
7.5°	944.8	928.9	911.9	892.1	872.9	855.4	839.3	823.9	806.5	790.8	776.6
10°	975.9	954.4	930.7	905.5	880.4	858.6	837.2	817.7	796.3	777.2	761.1
12.5°	1001.1	975.9	947.3	915.9	885.7	859.4	834.7	809.4	785.1	764.3	742.9
15°	1042.8	1008.3	969.8	932.3	893.1	857.3	824.1	794.6	766.8	737.7	717.2
17.5°	1071.6	1030.6	983.9	938.7	892.4	850.2	811.9	776.8	744.7	715.0	690.6
20°	1088.7	1043.5	991.6	940.3	888.4	843.2	802.0	763.1	730.0	697.8	672.7
22.5°	1098.4	1048.4	991.6	937.9	884.2	835.2	790.0	749.5	713.3	681.2	653.4
25°	1101.5	1047.8	989.9	928.2	869.4	817.4	770.5	726.6	686.4	654.3	624.7
27.5°	1097.2	1034.1	974.7	911.5	850.7	795.9	746.7	700.5	660.3	625.8	595.6
30°	1090.7	1023.1	959.4	893.8	832.2	779.5	727.6	683.4	641.5	605.7	575.2
32.5°	1076.9	1009.7	941.2	873.9	811.5	757.3	708.1	663.6	622.5	585.8	553.5
35°	1049.2	981.2	906.8	837.8	776.5	720.2	674.0	631.1	591.9	552.8	518.6
37.5°	1012.8	943.4	869.4	793.8	732.5	679.3	636.9	596.7	558.4	522.6	484.7
40°	978.5	915.2	838.9	763.8	700.9	649.5	610.4	573.9	535.4	499.8	461.9
42.5°	937.0	883.0	805.9	730.6	668.4	619.0	582.5	546.8	511.8	477.3	437.8
45°	867.6	826.8	754.4	682.1	619.4	570.5	537.0	505.5	474.7	441.9	404.7
47.5°	788.2	760.5	698.1	624.0	566.0	522.0	489.7	463.9	437.8	405.0	372.4
50°	733.0	715.2	655.0	587.3	532.0	491.5	458.3	434.1	412.4	380.9	351.7
52.5°	674.0	664.6	613.6	548.9	495.5	455.8	427.5	405.8	383.7	357.6	330.3
55°	584.3	589.3	546.0	490.1	439.9	406.4	380.6	362.5	343.7	321.6	300.5
57.5°	492.4	510.8	481.8	432.7	385.6	354.6	335.2	319.9	304.3	285.9	267.9
60°	437.5	452.9	436.5	393.3	352.1	323.3	305.2	293.4	277.7	261.0	247.2
62.5°	383.9	400.4	390.6	355.8	317.5	292.7	276.8	265.9	254.2	239.5	225.2
65°	316.6	327.3	322.6	298.5	271.4	250.2	235.5	227.5	216.7	206.0	193.3
67.5°	242.5	263.2	260.5	247.6	224.2	207.7	198.0	191.0	181.2	173.2	164.5
70°	199.3	218.4	218.1	207.7	194.9	179.5	172.9	166.9	158.1	150.4	143.4
72.5°	163.2	180.6	183.2	175.3	166.6	154.9	148.4	144.3	135.9	130.6	124.8
75°	114.3	127.0	130.4	130.4	126.3	120.3	114.6	111.9	105.8	101.2	97.8
77.5°	74.9	82.9	88.2	89.4	90.0	88.0	83.3	81.4	76.8	75.1	71.9
80°	53.0	58.3	64.3	66.3	68.0	67.3	65.3	64.0	59.7	57.9	56.7
82.5°	36.6	39.5	44.5	48.9	48.5	50.2	48.5	47.4	44.1	43.5	42.1
85°	19.1	19.5	20.1	23.1	24.8	25.5	25.8	25.1	24.1	24.1	21.8
87.5°	7.8	7.5	7.8	7.7	7.7	8.7	9.3	9.4	8.7	8.1	7.5
90°	7.2	6.5	5.8	5.0	4.0	3.1	2.2	1.2	2.2	3.1	4.0
92.5°	6.9	6.2	5.5	5.2	5.1	5.0	5.0	4.9	5.0	5.0	5.1
95°	8.4	8.4	8.3	9.6	12.7	15.6	18.5	21.4	18.5	15.6	12.7
97.5°	29.6	39.3	49.0	53.0	51.1	49.2	47.4	45.5	47.4	49.2	51.1
100°	41.1	53.0	65.0	70.3	68.7	67.2	65.5	64.0	65.5	67.2	68.7
102.5°	85.8	87.4	88.9	89.2	88.0	86.9	85.8	84.6	85.8	86.9	88.0
105°	120.9	120.5	120.0	119.5	119.0	118.5	118.0	117.4	118.0	118.5	119.0
107.5°	150.6	150.0	149.5	149.0	148.8	148.5	148.3	148.0	148.3	148.5	148.8
110°	171.1	170.5	170.0	169.6	169.4	169.1	168.8	168.6	168.8	169.1	169.4



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	191.2	191.1	190.8	190.5	189.9	189.5	189.0	188.6	189.0	189.5	189.9
115°	220.2	220.3	220.4	220.3	220.1	219.8	219.6	219.3	219.6	219.8	220.1
117.5°	249.0	248.8	248.7	248.4	248.1	247.7	247.4	247.0	247.4	247.7	248.1
120°	267.1	267.2	267.3	267.1	266.7	266.4	266.0	265.7	266.0	266.4	266.7
122.5°	284.5	284.3	284.2	284.0	283.9	283.6	283.4	283.2	283.4	283.6	283.9
125°	309.4	309.5	309.7	309.6	309.3	308.9	308.6	308.2	308.6	308.9	309.3
127.5°	333.4	332.9	332.6	332.3	332.3	332.2	332.1	332.0	332.1	332.2	332.3
130°	348.4	348.1	347.8	347.7	347.6	347.5	347.3	347.2	347.3	347.5	347.6
132.5°	362.8	362.6	362.2	362.0	361.8	361.6	361.4	361.4	361.4	361.6	361.8
135°	382.9	382.5	382.2	382.0	382.1	382.2	382.3	382.4	382.3	382.2	382.1
137.5°	402.2	401.7	401.4	401.2	401.1	401.1	401.1	401.1	401.1	401.1	401.1
140°	414.5	414.2	414.1	413.9	413.7	413.5	413.4	413.2	413.4	413.5	413.7
142.5°	425.9	425.7	425.6	425.4	425.1	424.8	424.5	424.1	424.5	424.8	425.1
145°	442.1	442.1	442.1	442.0	441.7	441.4	441.2	440.9	441.2	441.4	441.7
147.5°	456.2	456.3	456.4	456.2	455.7	455.2	454.8	454.3	454.8	455.2	455.7
150°	465.3	465.4	465.5	465.4	465.0	464.7	464.3	464.0	464.3	464.7	465.0
152.5°	472.9	473.1	473.2	473.2	472.9	472.6	472.3	472.1	472.3	472.6	472.9
155°	483.2	483.5	483.7	483.8	483.7	483.6	483.5	483.5	483.5	483.6	483.7
157.5°	492.1	492.4	492.7	492.8	492.9	492.9	493.0	493.1	493.0	492.9	492.9
160°	497.3	497.4	497.5	497.7	497.9	498.2	498.4	498.7	498.4	498.2	497.9
162.5°	502.0	502.0	502.1	502.4	502.7	503.0	503.3	503.7	503.3	503.0	502.7
165°	508.1	508.1	508.1	508.2	508.7	509.1	509.5	510.0	509.5	509.1	508.7
167.5°	512.8	512.9	512.9	513.2	513.7	514.1	514.5	515.0	514.5	514.1	513.7
170°	515.7	515.6	515.5	515.7	516.3	516.8	517.3	517.8	517.3	516.8	516.3
172.5°	517.5	517.5	517.4	517.6	518.1	518.7	519.2	519.7	519.2	518.7	518.1
175°	519.6	519.5	519.4	519.6	520.1	520.6	521.2	521.7	521.2	520.6	520.1
177.5°	520.8	520.6	520.6	520.7	521.2	521.7	522.2	522.6	522.2	521.7	521.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	816.5	813.8	810.3	806.2	801.4	797.2	795.3	796.9	797.7	795.6	795.3
5°	791.6	783.3	776.5	766.5	758.5	751.7	747.0	745.0	745.7	740.4	739.0
7.5°	763.6	753.7	742.8	730.8	719.7	709.9	704.7	701.9	696.2	693.8	689.7
10°	745.7	732.3	721.6	707.5	694.8	683.0	677.3	672.7	667.0	664.3	658.6
12.5°	727.2	711.7	699.9	685.3	672.3	658.1	652.7	644.0	635.1	629.5	622.2
15°	701.1	682.4	668.0	650.6	635.2	619.1	604.7	588.6	582.6	569.8	562.5
17.5°	670.6	651.6	633.8	610.4	586.7	566.7	551.3	536.0	526.7	518.6	514.8
20°	650.6	633.2	608.4	581.3	554.7	532.6	520.2	510.2	500.2	494.5	490.4
22.5°	631.5	609.3	580.5	551.2	524.8	507.5	497.0	486.6	478.5	473.0	467.7
25°	599.7	570.5	540.0	506.5	488.4	473.4	461.9	453.6	448.6	441.5	438.9
27.5°	566.9	531.6	497.9	475.4	456.6	442.8	432.9	426.6	420.3	415.7	412.2
30°	541.7	505.8	475.7	454.3	435.1	423.8	415.7	408.4	403.4	399.7	397.0
32.5°	516.8	481.0	455.6	432.6	417.5	406.4	397.8	392.3	388.3	383.6	381.9
35°	480.7	448.9	426.8	406.0	390.6	380.6	373.8	368.2	364.8	363.5	362.5
37.5°	446.1	420.0	396.2	379.2	365.5	357.6	349.7	346.9	344.6	342.2	343.3
40°	424.1	399.7	378.6	360.5	349.4	340.7	336.0	332.7	330.6	330.6	330.6
42.5°	405.1	381.2	360.6	344.4	333.3	326.0	320.7	317.9	317.3	316.9	318.6
45°	375.6	353.4	332.7	319.3	309.9	302.5	299.5	297.1	297.1	298.5	298.9
47.5°	346.3	325.5	308.8	293.9	285.2	280.7	278.0	276.8	277.0	278.3	279.8
50°	328.3	307.9	291.4	278.0	270.0	265.6	263.3	262.6	263.3	263.3	265.6
52.5°	308.8	290.4	274.3	263.0	253.9	249.9	248.6	247.6	248.1	249.1	250.1
55°	280.1	263.6	248.2	237.5	230.8	228.2	225.2	225.5	224.8	225.5	225.5
57.5°	251.3	236.6	222.2	213.7	207.8	204.0	200.7	201.6	200.6	200.4	199.9
60°	232.8	216.7	205.3	197.7	191.0	187.6	184.6	185.3	184.3	183.6	182.3
62.5°	212.8	199.3	188.5	181.1	175.6	171.8	168.8	168.1	165.7	163.5	160.5
65°	183.6	172.5	162.8	155.8	150.8	147.7	145.4	143.4	138.4	133.0	130.4
67.5°	155.2	147.2	138.2	132.2	128.2	124.2	119.8	116.3	111.6	108.7	107.0
70°	137.0	129.3	121.6	115.9	111.6	107.9	102.8	100.5	97.1	95.8	94.1
72.5°	119.6	112.4	105.2	100.1	95.5	92.6	88.7	86.3	84.8	84.3	82.6
75°	93.2	87.5	82.1	77.4	73.7	71.7	70.0	68.4	67.7	64.7	62.9
77.5°	67.9	64.1	60.9	57.5	54.8	53.6	50.3	48.4	47.3	45.8	45.5
80°	53.0	50.3	46.9	44.9	41.2	39.9	38.5	38.2	37.9	37.5	37.2
82.5°	39.8	37.1	33.8	32.5	31.6	30.7	30.0	29.6	29.3	29.4	29.4
85°	20.1	18.8	18.8	18.4	18.1	17.7	17.4	17.4	17.0	17.4	17.0
87.5°	7.7	7.6	7.7	7.3	7.7	7.9	7.7	7.8	8.2	7.7	7.8
90°	5.0	5.8	6.5	7.2	7.9	8.6	9.1	9.6	10.2	10.7	11.0
92.5°	5.2	5.5	6.2	6.9	7.6	8.3	8.8	9.3	9.8	10.3	10.6
95°	9.6	8.3	8.4	8.4	8.5	8.6	9.1	9.6	10.2	10.7	10.9
97.5°	53.0	49.0	39.3	29.6	20.0	10.3	10.3	10.4	10.4	10.5	10.6
100°	70.3	65.0	53.0	41.1	29.1	17.1	15.7	14.2	12.7	11.3	10.6
102.5°	89.2	88.9	87.4	85.8	84.3	82.7	66.8	50.9	35.0	19.1	11.2
105°	119.5	120.0	120.5	120.9	121.3	121.7	122.5	123.3	124.1	124.8	123.7
107.5°	149.0	149.5	150.0	150.6	151.2	151.8	152.1	152.6	152.9	153.3	153.7
110°	169.6	170.0	170.5	171.1	171.6	172.1	172.3	172.5	172.6	172.8	173.0



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	190.5	190.8	191.1	191.2	191.5	191.7	191.7	191.7	191.7	191.6	191.7
115°	220.3	220.4	220.3	220.2	220.2	220.1	220.2	220.4	220.6	220.8	220.8
117.5°	248.4	248.7	248.8	249.0	249.3	249.4	249.3	249.3	249.3	249.3	249.3
120°	267.1	267.3	267.2	267.1	267.0	266.9	267.1	267.3	267.4	267.6	267.6
122.5°	284.0	284.2	284.3	284.5	284.6	284.7	284.8	284.9	285.0	285.1	285.1
125°	309.6	309.7	309.5	309.4	309.2	309.0	309.3	309.5	309.8	310.0	310.2
127.5°	332.3	332.6	332.9	333.4	333.8	334.2	334.2	334.1	334.0	334.0	333.9
130°	347.7	347.8	348.1	348.4	348.6	348.9	349.0	349.0	349.1	349.2	349.2
132.5°	362.0	362.2	362.6	362.8	363.2	363.5	363.6	363.7	363.8	363.9	363.9
135°	382.0	382.2	382.5	382.9	383.2	383.6	383.7	383.9	384.1	384.3	384.4
137.5°	401.2	401.4	401.7	402.2	402.5	402.9	403.1	403.3	403.5	403.7	403.7
140°	413.9	414.1	414.2	414.5	414.7	414.8	415.1	415.3	415.6	415.9	416.0
142.5°	425.4	425.6	425.7	425.9	425.9	426.0	426.2	426.4	426.6	426.8	426.9
145°	442.0	442.1	442.1	442.1	442.1	442.1	442.2	442.3	442.4	442.5	442.6
147.5°	456.2	456.4	456.3	456.2	456.2	456.1	456.2	456.2	456.2	456.3	456.4
150°	465.4	465.5	465.4	465.3	465.2	465.1	465.1	465.1	465.1	465.1	465.2
152.5°	473.2	473.2	473.1	472.9	472.8	472.6	472.8	472.9	473.0	473.2	473.2
155°	483.8	483.7	483.5	483.2	482.9	482.7	483.0	483.4	483.7	484.1	484.1
157.5°	492.8	492.7	492.4	492.1	491.8	491.5	492.0	492.4	492.8	493.3	493.3
160°	497.7	497.5	497.4	497.3	497.2	497.1	497.7	498.2	498.7	499.2	499.2
162.5°	502.4	502.1	502.0	502.0	501.9	501.8	502.3	502.8	503.3	503.9	503.9
165°	508.2	508.1	508.1	508.1	508.1	508.1	508.8	509.5	510.1	510.8	510.7
167.5°	513.2	512.9	512.9	512.8	512.8	512.7	513.5	514.3	515.1	515.8	515.7
170°	515.7	515.5	515.6	515.7	515.7	515.8	516.5	517.2	517.9	518.7	518.6
172.5°	517.6	517.4	517.5	517.5	517.6	517.7	518.4	519.1	519.8	520.5	520.4
175°	519.6	519.4	519.5	519.6	519.7	519.8	520.6	521.3	522.1	522.9	522.7
177.5°	520.7	520.6	520.6	520.8	520.9	521.1	521.6	522.2	522.7	523.3	523.1
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	793.7	794.2	792.4	791.8	792.4	794.2	793.7	795.3	795.6	797.7	796.9
5°	736.3	735.6	734.0	734.3	734.0	735.6	736.3	739.0	740.4	745.7	745.0
7.5°	687.3	684.7	685.4	682.7	685.4	684.7	687.3	689.7	693.8	696.2	701.9
10°	657.3	653.6	650.6	647.9	650.6	653.6	657.3	658.6	664.3	667.0	672.7
12.5°	616.3	613.1	609.0	609.8	609.0	613.1	616.3	622.2	629.5	635.1	644.0
15°	558.1	553.1	545.0	546.0	545.0	553.1	558.1	562.5	569.8	582.6	588.6
17.5°	508.9	508.9	505.2	506.1	505.2	508.9	508.9	514.8	518.6	526.7	536.0
20°	483.4	481.0	481.4	480.4	481.4	481.0	483.4	490.4	494.5	500.2	510.2
22.5°	465.7	462.9	460.5	458.4	460.5	462.9	465.7	467.7	473.0	478.5	486.6
25°	435.8	433.9	430.8	430.2	430.8	433.9	435.8	438.9	441.5	448.6	453.6
27.5°	409.6	409.1	407.9	406.4	407.9	409.1	409.6	412.2	415.7	420.3	426.6
30°	394.3	393.6	393.0	391.9	393.0	393.6	394.3	397.0	399.7	403.4	408.4
32.5°	380.6	380.2	379.5	379.6	379.5	380.2	380.6	381.9	383.6	388.3	392.3
35°	361.1	360.8	360.2	359.8	360.2	360.8	361.1	362.5	363.5	364.8	368.2
37.5°	342.9	343.8	343.4	343.3	343.4	343.8	342.9	343.3	342.2	344.6	346.9
40°	330.3	330.6	331.3	331.0	331.3	330.6	330.3	330.6	330.6	330.6	332.7
42.5°	319.9	319.9	320.9	319.7	320.9	319.9	319.9	318.6	316.9	317.3	317.9
45°	301.2	303.2	302.8	302.8	302.8	303.2	301.2	298.9	298.5	297.1	297.1
47.5°	280.7	282.5	282.9	282.8	282.9	282.5	280.7	279.8	278.3	277.0	276.8
50°	267.3	266.7	267.7	267.3	267.7	266.7	267.3	265.6	263.3	263.3	262.6
52.5°	251.0	251.2	251.1	250.7	251.1	251.2	251.0	250.1	249.1	248.1	247.6
55°	225.8	226.1	225.5	225.8	225.5	226.1	225.8	225.5	225.5	224.8	225.5
57.5°	198.5	196.8	197.5	196.7	197.5	196.8	198.5	199.9	200.4	200.6	201.6
60°	178.9	176.2	175.6	174.2	175.6	176.2	178.9	182.3	183.6	184.3	185.3
62.5°	156.9	155.1	152.7	153.9	152.7	155.1	156.9	160.5	163.5	165.7	168.1
65°	127.6	126.3	125.3	126.7	125.3	126.3	127.6	130.4	133.0	138.4	143.4
67.5°	105.6	105.0	105.0	104.3	105.0	105.0	105.6	107.0	108.7	111.6	116.3
70°	94.1	93.2	93.2	92.5	93.2	93.2	94.1	94.1	95.8	97.1	100.5
72.5°	82.3	81.4	81.6	81.2	81.6	81.4	82.3	82.6	84.3	84.8	86.3
75°	61.0	59.3	59.3	59.7	59.3	59.3	61.0	62.9	64.7	67.7	68.4
77.5°	45.5	45.1	45.6	45.0	45.6	45.1	45.5	45.5	45.8	47.3	48.4
80°	37.2	36.9	36.5	37.5	36.5	36.9	37.2	37.2	37.5	37.9	38.2
82.5°	28.8	28.8	28.8	30.0	28.8	28.8	28.8	29.4	29.4	29.3	29.6
85°	17.4	16.8	17.4	16.8	17.4	16.8	17.4	17.0	17.4	17.0	17.4
87.5°	8.4	8.2	7.9	8.3	7.9	8.2	8.4	7.8	7.7	8.2	7.8
90°	11.2	11.4	11.5	11.7	11.5	11.4	11.2	11.0	10.7	10.2	9.6
92.5°	10.7	10.7	10.8	10.8	10.8	10.7	10.7	10.6	10.3	9.8	9.3
95°	11.0	11.1	11.2	11.3	11.2	11.1	11.0	10.9	10.7	10.2	9.6
97.5°	10.7	10.8	10.8	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.4
100°	10.7	10.8	10.8	10.9	10.8	10.8	10.7	10.6	11.3	12.7	14.2
102.5°	11.2	11.2	11.2	11.3	11.2	11.2	11.2	11.2	19.1	35.0	50.9
105°	120.5	117.4	114.3	111.2	114.3	117.4	120.5	123.7	124.8	124.1	123.3
107.5°	154.0	154.3	154.6	155.0	154.6	154.3	154.0	153.7	153.3	152.9	152.6
110°	173.2	173.5	173.7	174.0	173.7	173.5	173.2	173.0	172.8	172.6	172.5



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	192.1	192.4	192.8	193.0	192.8	192.4	192.1	191.7	191.6	191.7	191.7
115°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.6	220.4
117.5°	249.2	249.2	249.2	249.1	249.2	249.2	249.2	249.3	249.3	249.3	249.3
120°	267.4	267.3	267.1	266.9	267.1	267.3	267.4	267.6	267.6	267.4	267.3
122.5°	284.9	284.7	284.6	284.4	284.6	284.7	284.9	285.1	285.1	285.0	284.9
125°	310.3	310.4	310.5	310.6	310.5	310.4	310.3	310.2	310.0	309.8	309.5
127.5°	333.8	333.7	333.7	333.6	333.7	333.7	333.8	333.9	334.0	334.0	334.1
130°	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.1	349.0
132.5°	363.8	363.8	363.7	363.6	363.7	363.8	363.8	363.9	363.9	363.8	363.7
135°	384.6	384.8	385.0	385.1	385.0	384.8	384.6	384.4	384.3	384.1	383.9
137.5°	403.7	403.6	403.6	403.6	403.6	403.6	403.7	403.7	403.7	403.5	403.3
140°	416.1	416.2	416.3	416.4	416.3	416.2	416.1	416.0	415.9	415.6	415.3
142.5°	426.9	427.0	427.0	427.0	427.0	427.0	426.9	426.9	426.8	426.6	426.4
145°	442.7	442.9	443.1	443.2	443.1	442.9	442.7	442.6	442.5	442.4	442.3
147.5°	456.5	456.6	456.7	456.8	456.7	456.6	456.5	456.4	456.3	456.2	456.2
150°	465.3	465.4	465.5	465.5	465.5	465.4	465.3	465.2	465.1	465.1	465.1
152.5°	473.2	473.1	473.0	473.0	473.0	473.1	473.2	473.2	473.2	473.0	472.9
155°	483.9	483.6	483.4	483.1	483.4	483.6	483.9	484.1	484.1	483.7	483.4
157.5°	492.8	492.4	492.0	491.5	492.0	492.4	492.8	493.3	493.3	492.8	492.4
160°	498.7	498.2	497.7	497.1	497.7	498.2	498.7	499.2	499.2	498.7	498.2
162.5°	503.3	502.7	502.0	501.5	502.0	502.7	503.3	503.9	503.9	503.3	502.8
165°	510.0	509.2	508.4	507.6	508.4	509.2	510.0	510.7	510.8	510.1	509.5
167.5°	514.9	514.0	513.2	512.3	513.2	514.0	514.9	515.7	515.8	515.1	514.3
170°	517.6	516.8	515.9	515.1	515.9	516.8	517.6	518.6	518.7	517.9	517.2
172.5°	519.4	518.5	517.5	516.6	517.5	518.5	519.4	520.4	520.5	519.8	519.1
175°	521.7	520.6	519.6	518.6	519.6	520.6	521.7	522.7	522.9	522.1	521.3
177.5°	522.4	521.5	520.6	519.9	520.6	521.5	522.4	523.1	523.3	522.7	522.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	795.3	797.2	801.4	806.2	810.3	813.8	816.5	820.2	823.7	828.5	833.1
5°	747.0	751.7	758.5	766.5	776.5	783.3	791.6	799.0	809.7	820.4	830.8
7.5°	704.7	709.9	719.7	730.8	742.8	753.7	763.6	776.6	790.8	806.5	823.9
10°	677.3	683.0	694.8	707.5	721.6	732.3	745.7	761.1	777.2	796.3	817.7
12.5°	652.7	658.1	672.3	685.3	699.9	711.7	727.2	742.9	764.3	785.1	809.4
15°	604.7	619.1	635.2	650.6	668.0	682.4	701.1	717.2	737.7	766.8	794.6
17.5°	551.3	566.7	586.7	610.4	633.8	651.6	670.6	690.6	715.0	744.7	776.8
20°	520.2	532.6	554.7	581.3	608.4	633.2	650.6	672.7	697.8	730.0	763.1
22.5°	497.0	507.5	524.8	551.2	580.5	609.3	631.5	653.4	681.2	713.3	749.5
25°	461.9	473.4	488.4	506.5	540.0	570.5	599.7	624.7	654.3	686.4	726.6
27.5°	432.9	442.8	456.6	475.4	497.9	531.6	566.9	595.6	625.8	660.3	700.5
30°	415.7	423.8	435.1	454.3	475.7	505.8	541.7	575.2	605.7	641.5	683.4
32.5°	397.8	406.4	417.5	432.6	455.6	481.0	516.8	553.5	585.8	622.5	663.6
35°	373.8	380.6	390.6	406.0	426.8	448.9	480.7	518.6	552.8	591.9	631.1
37.5°	349.7	357.6	365.5	379.2	396.2	420.0	446.1	484.7	522.6	558.4	596.7
40°	336.0	340.7	349.4	360.5	378.6	399.7	424.1	461.9	499.8	535.4	573.9
42.5°	320.7	326.0	333.3	344.4	360.6	381.2	405.1	437.8	477.3	511.8	546.8
45°	299.5	302.5	309.9	319.3	332.7	353.4	375.6	404.7	441.9	474.7	505.5
47.5°	278.0	280.7	285.2	293.9	308.8	325.5	346.3	372.4	405.0	437.8	463.9
50°	263.3	265.6	270.0	278.0	291.4	307.9	328.3	351.7	380.9	412.4	434.1
52.5°	248.6	249.9	253.9	263.0	274.3	290.4	308.8	330.3	357.6	383.7	405.8
55°	225.2	228.2	230.8	237.5	248.2	263.6	280.1	300.5	321.6	343.7	362.5
57.5°	200.7	204.0	207.8	213.7	222.2	236.6	251.3	267.9	285.9	304.3	319.9
60°	184.6	187.6	191.0	197.7	205.3	216.7	232.8	247.2	261.0	277.7	293.4
62.5°	168.8	171.8	175.6	181.1	188.5	199.3	212.8	225.2	239.5	254.2	265.9
65°	145.4	147.7	150.8	155.8	162.8	172.5	183.6	193.3	206.0	216.7	227.5
67.5°	119.8	124.2	128.2	132.2	138.2	147.2	155.2	164.5	173.2	181.2	191.0
70°	102.8	107.9	111.6	115.9	121.6	129.3	137.0	143.4	150.4	158.1	166.9
72.5°	88.7	92.6	95.5	100.1	105.2	112.4	119.6	124.8	130.6	135.9	144.3
75°	70.0	71.7	73.7	77.4	82.1	87.5	93.2	97.8	101.2	105.8	111.9
77.5°	50.3	53.6	54.8	57.5	60.9	64.1	67.9	71.9	75.1	76.8	81.4
80°	38.5	39.9	41.2	44.9	46.9	50.3	53.0	56.7	57.9	59.7	64.0
82.5°	30.0	30.7	31.6	32.5	33.8	37.1	39.8	42.1	43.5	44.1	47.4
85°	17.4	17.7	18.1	18.4	18.8	18.8	20.1	21.8	24.1	24.1	25.1
87.5°	7.7	7.9	7.7	7.3	7.7	7.6	7.7	7.5	8.1	8.7	9.4
90°	9.1	8.6	7.9	7.2	6.5	5.8	5.0	4.0	3.1	2.2	1.2
92.5°	8.8	8.3	7.6	6.9	6.2	5.5	5.2	5.1	5.0	5.0	4.9
95°	9.1	8.6	8.5	8.4	8.4	8.3	9.6	12.7	15.6	18.5	21.4
97.5°	10.3	10.3	20.0	29.6	39.3	49.0	53.0	51.1	49.2	47.4	45.5
100°	15.7	17.1	29.1	41.1	53.0	65.0	70.3	68.7	67.2	65.5	64.0
102.5°	66.8	82.7	84.3	85.8	87.4	88.9	89.2	88.0	86.9	85.8	84.6
105°	122.5	121.7	121.3	120.9	120.5	120.0	119.5	119.0	118.5	118.0	117.4
107.5°	152.1	151.8	151.2	150.6	150.0	149.5	149.0	148.8	148.5	148.3	148.0
110°	172.3	172.1	171.6	171.1	170.5	170.0	169.6	169.4	169.1	168.8	168.6



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	191.7	191.7	191.5	191.2	191.1	190.8	190.5	189.9	189.5	189.0	188.6
115°	220.2	220.1	220.2	220.2	220.3	220.4	220.3	220.1	219.8	219.6	219.3
117.5°	249.3	249.4	249.3	249.0	248.8	248.7	248.4	248.1	247.7	247.4	247.0
120°	267.1	266.9	267.0	267.1	267.2	267.3	267.1	266.7	266.4	266.0	265.7
122.5°	284.8	284.7	284.6	284.5	284.3	284.2	284.0	283.9	283.6	283.4	283.2
125°	309.3	309.0	309.2	309.4	309.5	309.7	309.6	309.3	308.9	308.6	308.2
127.5°	334.2	334.2	333.8	333.4	332.9	332.6	332.3	332.3	332.2	332.1	332.0
130°	349.0	348.9	348.6	348.4	348.1	347.8	347.7	347.6	347.5	347.3	347.2
132.5°	363.6	363.5	363.2	362.8	362.6	362.2	362.0	361.8	361.6	361.4	361.4
135°	383.7	383.6	383.2	382.9	382.5	382.2	382.0	382.1	382.2	382.3	382.4
137.5°	403.1	402.9	402.5	402.2	401.7	401.4	401.2	401.1	401.1	401.1	401.1
140°	415.1	414.8	414.7	414.5	414.2	414.1	413.9	413.7	413.5	413.4	413.2
142.5°	426.2	426.0	425.9	425.9	425.7	425.6	425.4	425.1	424.8	424.5	424.1
145°	442.2	442.1	442.1	442.1	442.1	442.1	442.0	441.7	441.4	441.2	440.9
147.5°	456.2	456.1	456.2	456.2	456.3	456.4	456.2	455.7	455.2	454.8	454.3
150°	465.1	465.1	465.2	465.3	465.4	465.5	465.4	465.0	464.7	464.3	464.0
152.5°	472.8	472.6	472.8	472.9	473.1	473.2	473.2	472.9	472.6	472.3	472.1
155°	483.0	482.7	482.9	483.2	483.5	483.7	483.8	483.7	483.6	483.5	483.5
157.5°	492.0	491.5	491.8	492.1	492.4	492.7	492.8	492.9	492.9	493.0	493.1
160°	497.7	497.1	497.2	497.3	497.4	497.5	497.7	497.9	498.2	498.4	498.7
162.5°	502.3	501.8	501.9	502.0	502.0	502.1	502.4	502.7	503.0	503.3	503.7
165°	508.8	508.1	508.1	508.1	508.1	508.1	508.2	508.7	509.1	509.5	510.0
167.5°	513.5	512.7	512.8	512.8	512.9	512.9	513.2	513.7	514.1	514.5	515.0
170°	516.5	515.8	515.7	515.7	515.6	515.5	515.7	516.3	516.8	517.3	517.8
172.5°	518.4	517.7	517.6	517.5	517.5	517.4	517.6	518.1	518.7	519.2	519.7
175°	520.6	519.8	519.7	519.6	519.5	519.4	519.6	520.1	520.6	521.2	521.7
177.5°	521.6	521.1	520.9	520.8	520.6	520.6	520.7	521.2	521.7	522.2	522.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	836.5	839.0	841.6	846.7	851.0	852.9	856.7	859.4	858.5	862.3	868.7
5°	839.8	848.9	859.3	870.0	882.0	892.1	900.2	908.2	914.6	922.2	933.7
7.5°	839.3	855.4	872.9	892.1	911.9	928.9	944.8	960.9	975.1	990.8	1011.2
10°	837.2	858.6	880.4	905.5	930.7	954.4	975.9	995.9	1015.0	1035.4	1061.3
12.5°	834.7	859.4	885.7	915.9	947.3	975.9	1001.1	1030.0	1053.9	1080.2	1110.1
15°	824.1	857.3	893.1	932.3	969.8	1008.3	1042.8	1078.4	1111.6	1143.0	1180.5
17.5°	811.9	850.2	892.4	938.7	983.9	1030.6	1071.6	1116.4	1150.2	1192.5	1227.4
20°	802.0	843.2	888.4	940.3	991.6	1043.5	1088.7	1134.3	1172.5	1215.0	1259.3
22.5°	790.0	835.2	884.2	937.9	991.6	1048.4	1098.4	1143.7	1191.0	1238.9	1284.4
25°	770.5	817.4	869.4	928.2	989.9	1047.8	1101.5	1157.8	1208.7	1260.6	1301.5
27.5°	746.7	795.9	850.7	911.5	974.7	1034.1	1097.2	1157.2	1208.4	1258.4	1294.0
30°	727.6	779.5	832.2	893.8	959.4	1023.1	1090.7	1150.7	1204.6	1249.6	1269.6
32.5°	708.1	757.3	811.5	873.9	941.2	1009.7	1076.9	1138.2	1188.0	1215.0	1215.5
35°	674.0	720.2	776.5	837.8	906.8	981.2	1049.2	1109.5	1140.0	1142.4	1109.5
37.5°	636.9	679.3	732.5	793.8	869.4	943.4	1012.8	1053.0	1063.2	1029.2	968.5
40°	610.4	649.5	700.9	763.8	838.9	915.2	978.5	1008.0	997.3	942.0	874.3
42.5°	582.5	619.0	668.4	730.6	805.9	883.0	937.0	952.8	924.4	860.6	781.4
45°	537.0	570.5	619.4	682.1	754.4	826.8	867.6	859.6	812.4	736.7	647.9
47.5°	489.7	522.0	566.0	624.0	698.1	760.5	788.2	764.0	696.7	613.5	541.2
50°	458.3	491.5	532.0	587.3	655.0	715.2	733.0	696.1	621.4	541.4	475.0
52.5°	427.5	455.8	495.5	548.9	613.6	664.6	674.0	631.5	554.4	482.7	423.9
55°	380.6	406.4	439.9	490.1	546.0	589.3	584.3	529.6	459.6	398.3	352.1
57.5°	335.2	354.6	385.6	432.7	481.8	510.8	492.4	445.9	380.6	330.5	291.4
60°	305.2	323.3	352.1	393.3	436.5	452.9	437.5	386.9	335.4	289.5	256.6
62.5°	276.8	292.7	317.5	355.8	390.6	400.4	383.9	339.8	293.3	254.1	226.9
65°	235.5	250.2	271.4	298.5	322.6	327.3	316.6	271.4	236.2	203.4	184.6
67.5°	198.0	207.7	224.2	247.6	260.5	263.2	242.5	214.0	183.0	162.9	148.8
70°	172.9	179.5	194.9	207.7	218.1	218.4	199.3	176.5	152.7	136.4	126.0
72.5°	148.4	154.9	166.6	175.3	183.2	180.6	163.2	145.2	126.0	113.6	105.8
75°	114.6	120.3	126.3	130.4	130.4	127.0	114.3	100.8	89.8	82.4	80.1
77.5°	83.3	88.0	90.0	89.4	88.2	82.9	74.9	66.1	62.2	58.7	56.9
80°	65.3	67.3	68.0	66.3	64.3	58.3	53.0	49.2	45.5	44.3	43.6
82.5°	48.5	50.2	48.5	48.9	44.5	39.5	36.6	35.3	33.8	33.2	32.5
85°	25.8	25.5	24.8	23.1	20.1	19.5	19.1	18.8	18.1	18.4	17.7
87.5°	9.3	8.7	7.7	7.7	7.8	7.5	7.8	8.0	8.2	8.0	8.6
90°	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1	9.6
92.5°	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8	9.3
95°	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1	9.6
97.5°	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3	10.4
100°	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7	14.2
102.5°	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8	50.9
105°	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5	123.3
107.5°	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1	152.6
110°	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3	172.5



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7	191.7
115°	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2	220.4
117.5°	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3	249.3
120°	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1	267.3
122.5°	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8	284.9
125°	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3	309.5
127.5°	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2	334.1
130°	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0	349.0
132.5°	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6	363.7
135°	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7	383.9
137.5°	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1	403.3
140°	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1	415.3
142.5°	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2	426.4
145°	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2	442.3
147.5°	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2	456.2
150°	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1	465.1
152.5°	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8	472.9
155°	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0	483.4
157.5°	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0	492.4
160°	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7	498.2
162.5°	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3	502.8
165°	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8	509.5
167.5°	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5	514.3
170°	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5	517.2
172.5°	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4	519.1
175°	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6	521.3
177.5°	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6	522.2
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	872.2	873.3	874.1	876.8	877.0	879.4	877.0
5°	944.3	949.1	956.4	963.8	964.5	969.1	960.8
7.5°	1025.3	1036.1	1042.9	1054.8	1059.5	1062.5	1057.7
10°	1081.1	1091.1	1108.9	1117.6	1126.3	1127.6	1123.6
12.5°	1134.9	1150.8	1164.8	1181.4	1180.9	1192.7	1188.4
15°	1206.7	1223.1	1242.5	1260.9	1267.7	1267.7	1273.0
17.5°	1257.8	1288.0	1308.0	1322.5	1338.3	1341.1	1339.2
20°	1292.4	1324.9	1346.3	1365.1	1375.9	1378.9	1378.9
22.5°	1318.2	1345.8	1366.8	1383.6	1392.5	1396.0	1394.9
25°	1336.0	1359.8	1372.5	1377.5	1379.8	1379.1	1372.9
27.5°	1311.6	1310.5	1302.4	1287.0	1275.5	1268.4	1260.4
30°	1265.0	1247.5	1227.4	1205.3	1176.8	1155.0	1148.4
32.5°	1195.6	1156.4	1122.4	1085.5	1054.9	1033.1	1024.0
35°	1061.3	999.3	948.7	904.5	872.4	852.2	845.5
37.5°	902.0	842.0	779.4	736.5	709.8	689.5	681.9
40°	800.6	735.3	680.7	640.5	613.0	593.3	593.0
42.5°	708.2	645.8	594.4	565.5	535.9	522.8	522.7
45°	579.9	529.9	486.4	463.6	445.9	435.1	432.1
47.5°	480.1	438.9	409.8	391.7	377.2	370.4	365.9
50°	424.1	388.0	364.8	349.0	341.0	332.3	331.7
52.5°	377.5	348.3	330.3	317.5	307.3	302.0	302.2
55°	317.3	294.1	281.4	271.6	263.6	259.6	258.0
57.5°	267.3	249.9	240.6	231.8	228.3	225.2	224.3
60°	236.2	224.5	215.8	208.7	203.7	202.7	202.3
62.5°	210.4	198.2	192.2	186.8	183.0	181.5	180.9
65°	173.5	164.5	159.1	154.8	153.4	151.1	150.8
67.5°	139.9	134.5	131.0	127.9	126.1	126.0	126.0
70°	119.2	116.2	113.2	111.6	110.6	109.9	109.9
72.5°	101.6	99.4	96.9	96.0	95.8	95.1	94.9
75°	77.4	75.1	75.3	73.7	72.3	70.7	69.7
77.5°	54.8	53.2	52.9	52.7	51.5	51.3	51.8
80°	42.5	40.9	40.6	40.9	40.6	39.5	39.5
82.5°	32.4	31.0	30.7	30.4	30.0	30.4	29.9
85°	17.4	16.8	16.8	16.8	17.4	17.0	16.8
87.5°	8.2	8.0	8.4	8.1	8.2	7.9	8.3
90°	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P333035-935

CATALOG NUMBER: S124RDIW-S575D470U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)