

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333028-840

Luminaire Tested: **S124RDIW-S350D1340U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333028-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1340U840-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6202.8 lumens  
Efficiency: N/A  
Efficacy: 133.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	10
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4789	4789	4789	4789
5°	5555	4803	4246	4803
10°	6571	4782	3789	4782
15°	7590	4738	3256	4738
20°	8451	4677	2944	4677
25°	8725	4618	2734	4618
30°	7637	4545	2606	4545
35°	5945	4438	2530	4438
40°	4458	4314	2488	4314
45°	3520	4117	2466	4117
50°	2972	3890	2396	3890
55°	2590	3640	2267	3640
60°	2330	3379	2007	3379
65°	2055	3100	1727	3100
70°	1851	2811	1555	2811
75°	1550	2489	1326	2489
80°	1311	2120	1246	2120
85°	1102	1667	1102	1667



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.5	0.9
10°-20°	173.4	2.8
20°-30°	271.2	4.4
30°-40°	301.5	4.9
40°-50°	267.5	4.3
50°-60°	208.4	3.4
60°-70°	136.5	2.2
70°-80°	67.1	1.1
80°-90°	21.6	0.3
90°-100°	111.7	1.8
100°-110°	330.9	5.3
110°-120°	561.6	9.1
120°-130°	740.5	11.9
130°-140°	831.6	13.4
140°-150°	817.2	13.2
150°-160°	687.3	11.1
160°-170°	457.3	7.4
170°-180°	160.1	2.6
0°-30°	502.0	8.1
0°-40°	803.5	13.0
0°-60°	1279.4	20.6
0°-90°	1504.5	24.3
90°-120°	1004.2	16.2
90°-150°	3393.5	54.7
90°-180°	4698.0	75.7
0°-180°	6202.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	593	593	593	593	593	
5°	686	593	524	593	686	69
15°	908	567	390	567	908	258
25°	980	518	307	518	980	435
35°	603	450	257	450	603	378
45°	308	361	216	361	308	244
55°	184	259	161	259	184	167
65°	108	162	90	162	108	108
75°	50	80	42	80	50	55
85°	12	18	12	18	12	14
90°	39	4	39	4	39	20
95°	104	79	104	79	104	108
105°	320	305	320	305	320	337
115°	566	571	566	571	566	559
125°	825	832	825	832	825	736
135°	1074	1073	1074	1073	1074	829
145°	1304	1303	1304	1303	1304	816
155°	1492	1493	1492	1493	1492	687
165°	1621	1625	1621	1625	1621	457
175°	1683	1691	1683	1691	1683	160
180°	1693	1693	1693	1693	1693	



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	625.7	627.4	625.7	625.5	623.6	623.0	622.3	619.8	615.2	612.5	613.1
5°	685.5	691.5	688.1	687.6	682.4	677.1	673.8	666.1	657.9	652.5	647.9
7.5°	754.6	758.0	755.9	752.6	744.1	739.2	731.4	721.4	706.8	695.7	685.5
10°	801.6	804.5	803.5	797.3	791.1	778.4	771.2	757.2	738.7	724.2	710.5
12.5°	847.9	850.9	842.5	842.8	831.0	821.0	809.7	791.9	770.7	751.9	734.9
15°	908.2	904.3	904.3	899.6	886.5	872.6	860.9	842.2	815.5	793.0	769.3
17.5°	955.4	956.7	954.8	943.5	933.2	918.9	897.4	875.7	850.8	820.6	796.5
20°	983.7	983.7	981.6	973.9	960.6	945.2	922.1	898.4	866.9	836.5	809.3
22.5°	995.2	995.9	993.4	987.1	975.1	960.2	940.4	916.4	883.8	849.7	816.0
25°	979.5	984.0	984.4	982.8	979.2	970.1	953.1	928.6	899.4	862.3	826.0
27.5°	899.2	904.9	910.0	918.3	929.3	934.9	935.7	923.2	897.8	862.1	825.6
30°	819.3	824.0	839.6	859.9	875.7	890.0	902.5	905.8	891.5	859.5	821.0
32.5°	730.5	737.1	752.7	774.5	800.7	825.1	852.9	867.2	866.8	847.6	812.0
35°	603.2	608.0	622.4	645.3	676.8	713.0	757.2	791.5	815.0	813.3	791.5
37.5°	486.6	491.9	506.3	525.4	556.0	600.7	643.5	690.9	734.2	758.5	751.2
40°	423.0	423.2	437.4	457.0	485.6	524.6	571.2	623.8	672.1	711.6	719.1
42.5°	372.9	372.9	382.3	403.4	424.0	460.7	505.2	557.4	614.0	659.5	679.7
45°	308.3	310.4	318.1	330.7	347.0	378.1	413.7	462.2	525.5	579.6	613.3
47.5°	261.1	264.3	269.1	279.4	292.4	313.1	342.5	386.2	437.7	497.1	545.0
50°	236.6	237.1	243.3	249.0	260.2	276.8	302.6	338.9	386.3	443.3	496.7
52.5°	215.6	215.5	219.2	226.5	235.6	248.4	269.3	302.4	344.4	395.6	450.6
55°	184.0	185.2	188.1	193.8	200.8	209.8	226.3	251.2	284.2	327.9	377.9
57.5°	160.1	160.7	162.9	165.3	171.7	178.3	190.7	207.9	235.7	271.6	318.1
60°	144.3	144.6	145.3	148.9	153.9	160.2	168.5	183.1	206.5	239.2	276.1
62.5°	129.1	129.5	130.6	133.2	137.1	141.4	150.2	161.9	181.3	209.2	242.4
65°	107.6	107.8	109.5	110.4	113.5	117.3	123.8	131.7	145.1	168.5	193.6
67.5°	89.9	89.9	90.0	91.3	93.4	95.9	99.8	106.1	116.2	130.6	152.7
70°	78.4	78.4	78.9	79.6	80.8	82.9	85.1	89.9	97.3	109.0	125.9
72.5°	67.7	67.9	68.4	68.5	69.1	70.9	72.5	75.5	81.0	89.9	103.6
75°	49.7	50.4	51.6	52.6	53.8	53.5	55.2	57.2	58.8	64.0	71.9
77.5°	37.0	36.7	36.8	37.6	37.7	38.0	39.2	40.6	41.9	44.3	47.2
80°	28.2	28.2	28.9	29.2	28.9	29.2	30.4	31.1	31.5	32.5	35.1
82.5°	21.3	21.7	21.5	21.7	21.8	22.1	23.1	23.2	23.7	24.1	25.1
85°	11.9	12.2	12.4	11.9	11.9	11.9	12.4	12.6	13.1	12.9	13.4
87.5°	12.0	11.7	11.8	11.7	11.8	11.4	11.2	11.2	10.5	10.4	9.9
90°	39.3	38.7	38.2	37.6	37.0	35.7	34.0	32.3	30.6	28.8	26.5
92.5°	58.2	57.8	57.5	57.1	56.8	56.0	55.0	53.9	52.9	51.9	50.2
95°	103.5	103.5	103.5	103.5	103.5	103.0	102.2	101.3	100.4	99.6	97.5
97.5°	162.2	162.2	162.2	162.2	162.2	161.6	160.6	159.6	158.4	157.4	155.0
100°	203.0	203.0	203.0	203.0	203.0	202.7	202.2	201.6	201.0	200.4	197.7
102.5°	249.1	248.8	248.6	248.4	248.1	247.6	246.8	246.0	245.2	244.4	242.0
105°	319.5	318.7	317.8	316.9	316.1	315.2	314.4	313.5	312.6	311.7	310.5
107.5°	388.2	388.3	388.3	388.4	388.4	388.1	387.2	386.4	385.6	384.8	384.7
110°	437.5	436.6	435.7	434.8	433.9	433.8	434.3	434.9	435.6	436.2	436.5



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	487.6	487.4	487.2	487.1	487.0	487.2	487.3	487.4	487.5	488.0
115°	565.8	566.0	566.3	566.6	566.9	567.2	567.5	567.8	568.2	568.4	569.0
117.5°	640.2	640.8	641.4	641.9	642.5	643.3	644.3	645.3	646.2	647.2	647.6
120°	696.7	696.2	695.6	695.0	694.4	694.9	696.3	697.8	699.2	700.6	701.6
122.5°	743.9	745.0	746.0	747.0	748.1	749.1	750.1	751.0	752.0	753.1	753.5
125°	825.1	825.7	826.3	826.9	827.4	828.0	828.6	829.2	829.7	830.3	830.6
127.5°	900.3	900.7	901.2	901.7	902.1	902.6	903.2	903.8	904.4	904.9	905.4
130°	949.5	950.7	951.8	953.0	954.2	955.0	955.6	956.2	956.7	957.4	957.4
132.5°	1001.9	1002.4	1002.8	1003.3	1003.8	1004.3	1004.9	1005.4	1006.0	1006.6	1006.8
135°	1073.9	1074.8	1075.7	1076.5	1077.4	1078.1	1078.7	1079.3	1079.9	1080.5	1080.5
137.5°	1149.6	1149.4	1149.3	1149.1	1148.9	1149.2	1150.0	1150.7	1151.4	1152.3	1151.8
140°	1195.8	1196.0	1196.3	1196.6	1196.9	1197.2	1197.5	1197.8	1198.1	1198.3	1198.3
142.5°	1241.8	1241.9	1241.9	1242.0	1242.0	1242.1	1242.2	1242.2	1242.3	1242.3	1242.6
145°	1304.4	1305.4	1306.2	1307.1	1308.0	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4
147.5°	1367.9	1368.2	1368.4	1368.7	1369.0	1369.3	1369.5	1369.7	1370.0	1370.2	1370.4
150°	1406.6	1406.8	1407.1	1407.4	1407.8	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1442.2	1443.0	1443.7	1444.5	1445.2	1445.3	1444.6	1443.9	1443.2	1442.5	1442.3
155°	1491.8	1492.9	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8	1492.0
157.5°	1536.0	1537.0	1537.9	1538.9	1539.9	1540.0	1539.1	1538.2	1537.4	1536.5	1536.6
160°	1561.2	1562.6	1564.1	1565.5	1566.9	1567.2	1566.4	1565.5	1564.6	1563.8	1564.1
162.5°	1587.3	1588.8	1590.2	1591.6	1593.2	1593.1	1591.5	1589.9	1588.4	1586.8	1587.1
165°	1621.3	1622.6	1623.7	1624.9	1626.1	1625.8	1624.0	1622.2	1620.5	1618.7	1619.3
167.5°	1645.8	1647.6	1649.3	1651.1	1652.9	1652.9	1651.2	1649.5	1647.8	1646.0	1646.0
170°	1659.4	1661.4	1663.4	1665.5	1667.5	1667.7	1665.9	1664.2	1662.4	1660.6	1660.4
172.5°	1670.9	1672.9	1675.0	1677.0	1679.0	1679.1	1677.1	1675.1	1673.1	1671.1	1671.1
175°	1682.9	1685.0	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9	1683.2
177.5°	1689.2	1691.1	1692.9	1694.9	1696.7	1696.8	1695.2	1693.5	1691.9	1690.3	1690.3
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	611.2	608.5	607.1	604.1	600.5	598.5	596.8	594.3	591.1	587.6	585.2
5°	642.2	636.4	629.2	620.7	613.1	605.6	599.2	592.7	585.3	577.6	570.1
7.5°	674.0	662.8	650.6	636.4	622.8	610.3	598.7	587.8	575.4	564.2	554.1
10°	696.2	681.0	664.0	646.0	628.1	612.6	597.2	583.4	568.2	554.5	543.0
12.5°	714.2	696.2	675.8	653.5	631.9	613.1	595.5	577.4	560.1	545.3	530.0
15°	744.0	719.4	692.0	665.1	637.2	611.6	587.9	566.9	547.0	526.2	511.7
17.5°	764.6	735.3	701.9	669.7	636.7	606.5	579.3	554.2	531.3	510.1	492.7
20°	776.8	744.5	707.4	670.9	633.8	601.6	572.2	544.4	520.8	497.9	479.9
22.5°	783.7	747.9	707.4	669.1	630.8	595.8	563.6	534.7	509.0	485.9	466.2
25°	785.9	747.6	706.3	662.3	620.3	583.2	549.7	518.4	489.7	466.8	445.8
27.5°	782.7	737.7	695.4	650.3	606.8	567.8	532.7	499.8	471.1	446.5	424.9
30°	778.2	729.9	684.5	637.6	593.7	556.1	519.1	487.6	457.7	432.1	410.4
32.5°	768.2	720.3	671.5	623.5	579.0	540.3	505.1	473.4	444.1	418.0	394.9
35°	748.5	700.0	647.0	597.7	554.0	513.8	480.9	450.3	422.3	394.4	370.0
37.5°	722.6	673.1	620.3	566.3	522.5	484.6	454.4	425.7	398.4	372.8	345.9
40°	698.1	653.0	598.4	544.9	500.0	463.4	435.5	409.4	381.9	356.6	329.6
42.5°	668.5	630.1	574.9	521.2	476.9	441.6	415.6	390.1	365.1	340.5	312.4
45°	619.0	589.9	538.3	486.7	441.9	407.0	383.1	360.6	338.7	315.3	288.7
47.5°	562.3	542.6	498.1	445.1	403.8	372.4	349.3	330.9	312.4	288.9	265.7
50°	522.9	510.3	467.3	419.0	379.5	350.6	327.0	309.7	294.2	271.8	251.0
52.5°	480.9	474.1	437.8	391.6	353.6	325.2	305.0	289.5	273.8	255.1	235.7
55°	416.8	420.4	389.6	349.6	313.8	289.9	271.6	258.6	245.2	229.4	214.4
57.5°	351.3	364.5	343.8	308.7	275.1	253.0	239.1	228.3	217.0	204.0	191.1
60°	312.1	323.2	311.4	280.5	251.2	230.7	217.7	209.3	198.1	186.2	176.4
62.5°	273.9	285.7	278.7	253.8	226.5	208.8	197.4	189.7	181.3	170.9	160.7
65°	225.9	233.5	230.1	213.0	193.6	178.5	168.0	162.3	154.6	147.0	137.9
67.5°	173.0	187.7	185.8	176.6	160.0	148.1	141.3	136.2	129.3	123.6	117.4
70°	142.2	155.8	155.6	148.1	139.1	128.2	123.3	119.1	112.8	107.3	102.3
72.5°	116.4	128.9	130.8	125.0	118.9	110.5	105.9	103.0	96.9	93.2	89.1
75°	81.5	90.6	93.0	93.0	90.1	85.8	81.7	79.8	75.5	72.2	69.8
77.5°	53.4	59.2	62.9	63.7	64.2	62.7	59.4	58.1	54.7	53.6	51.3
80°	37.8	41.6	45.8	47.4	48.5	48.1	46.7	45.6	42.5	41.3	40.4
82.5°	26.1	28.2	31.7	34.9	34.5	35.9	34.5	33.8	31.4	31.0	30.1
85°	13.6	13.8	14.3	16.5	17.7	18.2	18.4	18.0	17.2	17.2	15.6
87.5°	9.4	8.8	8.7	8.1	7.7	7.8	7.8	7.3	7.4	7.4	7.5
90°	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9	7.2	10.3	13.5
92.5°	48.6	47.0	45.3	42.7	39.0	35.3	31.7	28.1	31.7	35.3	39.0
95°	95.4	93.4	91.4	89.1	86.4	83.8	81.2	78.6	81.2	83.8	86.4
97.5°	152.7	150.3	147.8	145.6	143.5	141.5	139.4	137.2	139.4	141.5	143.5
100°	195.1	192.5	189.9	188.0	186.8	185.7	184.5	183.4	184.5	185.7	186.8
102.5°	239.6	237.2	234.8	233.4	233.0	232.5	232.1	231.6	232.1	232.5	233.0
105°	309.4	308.2	307.0	306.3	306.0	305.8	305.5	305.2	305.5	305.8	306.0
107.5°	384.5	384.3	384.1	383.8	383.4	383.1	382.7	382.4	382.7	383.1	383.4
110°	436.7	437.0	437.3	437.2	436.6	436.0	435.4	434.8	435.4	436.0	436.6





TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	488.5	489.1	489.6	489.8	489.7	489.5	489.4	489.3	489.4	489.5	489.7
115°	569.6	570.2	570.8	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0
117.5°	648.0	648.4	648.8	648.9	648.7	648.5	648.2	648.0	648.2	648.5	648.7
120°	702.5	703.3	704.2	704.0	702.9	701.7	700.5	699.3	700.5	701.7	702.9
122.5°	753.9	754.3	754.7	754.7	754.2	753.8	753.3	752.8	753.3	753.8	754.2
125°	830.9	831.2	831.5	831.6	831.6	831.6	831.6	831.6	831.6	831.6	831.6
127.5°	905.9	906.4	906.9	906.7	905.7	904.9	904.0	903.1	904.0	904.9	905.7
130°	957.4	957.4	957.4	956.9	956.0	955.2	954.3	953.4	954.3	955.2	956.0
132.5°	1007.0	1007.3	1007.5	1007.3	1006.7	1006.0	1005.4	1004.8	1005.4	1006.0	1006.7
135°	1080.5	1080.5	1080.5	1079.6	1077.8	1076.1	1074.4	1072.6	1074.4	1076.1	1077.8
137.5°	1151.3	1150.8	1150.4	1149.7	1148.9	1148.1	1147.3	1146.5	1147.3	1148.1	1148.9
140°	1198.3	1198.3	1198.3	1198.1	1197.5	1196.9	1196.3	1195.8	1196.3	1196.9	1197.5
142.5°	1242.8	1243.0	1243.2	1243.1	1242.5	1241.9	1241.3	1240.8	1241.3	1241.9	1242.5
145°	1309.1	1308.8	1308.5	1307.8	1306.7	1305.5	1304.3	1303.1	1304.3	1305.5	1306.7
147.5°	1370.7	1370.9	1371.1	1370.5	1369.2	1367.8	1366.3	1364.9	1366.3	1367.8	1369.2
150°	1407.9	1407.9	1407.9	1407.3	1406.1	1405.0	1403.8	1402.7	1403.8	1405.0	1406.1
152.5°	1442.0	1441.8	1441.6	1441.1	1440.4	1439.7	1439.0	1438.2	1439.0	1439.7	1440.4
155°	1492.3	1492.6	1492.9	1493.0	1493.0	1493.0	1493.0	1493.0	1493.0	1493.0	1493.0
157.5°	1536.6	1536.7	1536.7	1537.0	1537.5	1538.1	1538.6	1539.1	1538.6	1538.1	1537.5
160°	1564.4	1564.6	1564.9	1565.2	1565.5	1565.8	1566.1	1566.4	1566.1	1565.8	1565.5
162.5°	1587.4	1587.7	1588.0	1588.5	1589.2	1590.0	1590.7	1591.5	1590.7	1590.0	1589.2
165°	1619.9	1620.5	1621.1	1621.8	1622.7	1623.6	1624.5	1625.3	1624.5	1623.6	1622.7
167.5°	1645.9	1645.9	1645.8	1646.4	1647.6	1648.8	1650.0	1651.2	1650.0	1648.8	1647.6
170°	1660.1	1659.8	1659.5	1660.1	1661.5	1663.0	1664.5	1665.9	1664.5	1663.0	1661.5
172.5°	1671.0	1671.0	1670.9	1671.5	1672.7	1674.0	1675.2	1676.4	1675.2	1674.0	1672.7
175°	1683.5	1683.8	1684.1	1685.0	1686.5	1687.9	1689.3	1690.8	1689.3	1687.9	1686.5
177.5°	1690.3	1690.3	1690.3	1690.8	1692.0	1693.1	1694.4	1695.5	1694.4	1693.1	1692.0
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	582.5	580.6	578.1	575.2	571.8	568.8	567.3	568.6	569.2	567.5	567.3
5°	564.7	558.8	554.0	546.8	541.1	536.3	533.0	531.5	532.0	528.2	527.3
7.5°	544.8	537.8	529.9	521.4	513.5	506.4	502.8	500.8	496.7	494.9	492.0
10°	532.0	522.5	514.8	504.7	495.6	487.4	483.2	479.9	475.8	473.9	469.9
12.5°	518.9	507.8	499.3	488.9	479.6	469.6	465.6	459.5	453.1	449.1	443.8
15°	500.2	486.9	476.6	464.1	453.1	441.7	431.4	419.9	415.7	406.6	401.3
17.5°	478.5	464.9	452.2	435.6	418.6	404.2	393.3	382.3	375.8	370.0	367.3
20°	464.1	451.7	434.0	414.7	395.8	380.0	371.1	364.0	356.8	352.7	349.9
22.5°	450.6	434.6	414.1	393.2	374.4	362.0	354.6	347.2	341.3	337.5	333.7
25°	427.8	407.0	385.3	361.3	348.5	337.7	329.6	323.6	320.0	315.0	313.1
27.5°	404.5	379.2	355.3	339.2	325.8	315.9	308.8	304.4	299.8	296.6	294.1
30°	386.5	360.9	339.4	324.1	310.4	302.4	296.6	291.3	287.7	285.1	283.3
32.5°	368.7	343.2	325.1	308.6	297.8	289.9	283.8	279.8	277.0	273.7	272.5
35°	343.0	320.2	304.5	289.6	278.7	271.6	266.7	262.7	260.2	259.3	258.6
37.5°	318.2	299.6	282.7	270.5	260.7	255.1	249.4	247.4	245.8	244.1	244.9
40°	302.6	285.1	270.0	257.2	249.2	243.1	239.7	237.3	235.9	235.9	235.9
42.5°	289.0	272.0	257.2	245.7	237.8	232.6	228.8	226.8	226.3	226.1	227.3
45°	267.9	252.2	237.3	227.7	221.1	215.8	213.7	212.0	212.0	213.0	213.2
47.5°	247.0	232.3	220.4	209.6	203.5	200.3	198.3	197.5	197.6	198.5	199.7
50°	234.2	219.6	207.9	198.3	192.7	189.6	187.8	187.3	187.8	187.8	189.6
52.5°	220.3	207.2	195.7	187.6	181.2	178.2	177.3	176.6	176.9	177.7	178.4
55°	199.9	188.1	177.1	169.5	164.7	162.8	160.6	160.9	160.4	160.9	160.9
57.5°	179.3	168.7	158.5	152.5	148.2	145.5	143.2	143.8	143.1	143.0	142.6
60°	166.1	154.6	146.5	141.0	136.2	133.8	131.7	132.2	131.5	131.0	130.0
62.5°	151.8	142.2	134.4	129.2	125.3	122.6	120.4	120.0	118.3	116.6	114.5
65°	131.0	123.1	116.1	111.2	107.6	105.4	103.7	102.3	98.7	94.9	93.0
67.5°	110.8	105.0	98.6	94.3	91.4	88.7	85.4	83.0	79.7	77.6	76.3
70°	97.8	92.3	86.7	82.7	79.6	77.0	73.4	71.7	69.3	68.4	67.2
72.5°	85.3	80.2	75.1	71.4	68.2	66.0	63.2	61.6	60.5	60.1	59.0
75°	66.4	62.4	58.6	55.2	52.6	51.1	50.0	48.8	48.3	46.2	44.9
77.5°	48.5	45.7	43.4	41.0	39.2	38.2	35.9	34.5	33.7	32.7	32.4
80°	37.8	35.9	33.4	32.0	29.4	28.5	27.5	27.3	27.0	26.8	26.6
82.5°	28.4	26.5	24.1	23.2	22.5	21.9	21.4	21.1	20.9	21.0	21.0
85°	14.3	13.4	13.4	13.1	12.9	12.6	12.4	12.4	12.2	12.4	12.2
87.5°	8.1	8.5	9.0	9.0	9.7	10.2	10.3	10.7	11.2	11.2	11.4
90°	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3	34.0	35.7	37.0
92.5°	42.7	45.3	47.0	48.6	50.2	51.9	52.9	53.9	55.0	56.0	56.8
95°	89.1	91.4	93.4	95.4	97.5	99.6	100.4	101.3	102.2	103.0	103.5
97.5°	145.6	147.8	150.3	152.7	155.0	157.4	158.4	159.6	160.6	161.6	162.2
100°	188.0	189.9	192.5	195.1	197.7	200.4	201.0	201.6	202.2	202.7	203.0
102.5°	233.4	234.8	237.2	239.6	242.0	244.4	245.2	246.0	246.8	247.6	248.1
105°	306.3	307.0	308.2	309.4	310.5	311.7	312.6	313.5	314.4	315.2	316.1
107.5°	383.8	384.1	384.3	384.5	384.7	384.8	385.6	386.4	387.2	388.1	388.4
110°	437.2	437.3	437.0	436.7	436.5	436.2	435.6	434.9	434.3	433.8	433.9



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	489.8	489.6	489.1	488.5	488.0	487.5	487.4	487.3	487.2	487.0	487.1
115°	571.0	570.8	570.2	569.6	569.0	568.4	568.2	567.8	567.5	567.2	566.9
117.5°	648.9	648.8	648.4	648.0	647.6	647.2	646.2	645.3	644.3	643.3	642.5
120°	704.0	704.2	703.3	702.5	701.6	700.6	699.2	697.8	696.3	694.9	694.4
122.5°	754.7	754.7	754.3	753.9	753.5	753.1	752.0	751.0	750.1	749.1	748.1
125°	831.6	831.5	831.2	830.9	830.6	830.3	829.7	829.2	828.6	828.0	827.4
127.5°	906.7	906.9	906.4	905.9	905.4	904.9	904.4	903.8	903.2	902.6	902.1
130°	956.9	957.4	957.4	957.4	957.4	957.4	956.7	956.2	955.6	955.0	954.2
132.5°	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0	1005.4	1004.9	1004.3	1003.8
135°	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9	1079.3	1078.7	1078.1	1077.4
137.5°	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4	1150.7	1150.0	1149.2	1148.9
140°	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1	1197.8	1197.5	1197.2	1196.9
142.5°	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3	1242.2	1242.2	1242.1	1242.0
145°	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4	1309.1	1308.8	1308.5	1308.0
147.5°	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0	1369.7	1369.5	1369.3	1369.0
150°	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.8
152.5°	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2	1443.9	1444.6	1445.3	1445.2
155°	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9	1494.1	1495.2	1496.4	1496.4
157.5°	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4	1538.2	1539.1	1540.0	1539.9
160°	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6	1565.5	1566.4	1567.2	1566.9
162.5°	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4	1589.9	1591.5	1593.1	1593.2
165°	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5	1622.2	1624.0	1625.8	1626.1
167.5°	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8	1649.5	1651.2	1652.9	1652.9
170°	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4	1664.2	1665.9	1667.7	1667.5
172.5°	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1	1675.1	1677.1	1679.1	1679.0
175°	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0	1687.0	1689.0	1691.1	1691.1
177.5°	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9	1693.5	1695.2	1696.8	1696.7
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	566.2	566.6	565.3	564.9	565.3	566.6	566.2	567.3	567.5	569.2	568.6
5°	525.3	524.8	523.6	523.9	523.6	524.8	525.3	527.3	528.2	532.0	531.5
7.5°	490.3	488.5	489.0	487.1	489.0	488.5	490.3	492.0	494.9	496.7	500.8
10°	468.9	466.3	464.1	462.2	464.1	466.3	468.9	469.9	473.9	475.8	479.9
12.5°	439.7	437.4	434.5	435.0	434.5	437.4	439.7	443.8	449.1	453.1	459.5
15°	398.2	394.6	388.9	389.6	388.9	394.6	398.2	401.3	406.6	415.7	419.9
17.5°	363.0	363.0	360.4	361.1	360.4	363.0	363.0	367.3	370.0	375.8	382.3
20°	344.9	343.3	343.5	342.7	343.5	343.3	344.9	349.9	352.7	356.8	364.0
22.5°	332.2	330.2	328.5	327.1	328.5	330.2	332.2	333.7	337.5	341.3	347.2
25°	310.9	309.5	307.4	306.9	307.4	309.5	310.9	313.1	315.0	320.0	323.6
27.5°	292.2	292.0	291.0	289.9	291.0	292.0	292.2	294.1	296.6	299.8	304.4
30°	281.3	280.8	280.3	279.6	280.3	280.8	281.3	283.3	285.1	287.7	291.3
32.5°	271.6	271.2	270.7	270.8	270.7	271.2	271.6	272.5	273.7	277.0	279.8
35°	257.6	257.4	256.9	256.7	256.9	257.4	257.6	258.6	259.3	260.2	262.7
37.5°	244.7	245.3	245.0	244.9	245.0	245.3	244.7	244.9	244.1	245.8	247.4
40°	235.7	235.9	236.4	236.1	236.4	235.9	235.7	235.9	235.9	235.9	237.3
42.5°	228.2	228.2	228.9	228.1	228.9	228.2	228.2	227.3	226.1	226.3	226.8
45°	214.9	216.3	216.0	216.0	216.0	216.3	214.9	213.2	213.0	212.0	212.0
47.5°	200.3	201.6	201.9	201.8	201.9	201.6	200.3	199.7	198.5	197.6	197.5
50°	190.8	190.3	191.0	190.8	191.0	190.3	190.8	189.6	187.8	187.8	187.3
52.5°	179.0	179.2	179.2	178.8	179.2	179.2	179.0	178.4	177.7	176.9	176.6
55°	161.1	161.4	160.9	161.1	160.9	161.4	161.1	160.9	160.9	160.4	160.9
57.5°	141.6	140.5	140.9	140.4	140.9	140.5	141.6	142.6	143.0	143.1	143.8
60°	127.6	125.7	125.2	124.3	125.2	125.7	127.6	130.0	131.0	131.5	132.2
62.5°	112.0	110.6	109.0	109.8	109.0	110.6	112.0	114.5	116.6	118.3	120.0
65°	91.1	90.1	89.4	90.4	89.4	90.1	91.1	93.0	94.9	98.7	102.3
67.5°	75.3	74.8	74.8	74.4	74.8	74.8	75.3	76.3	77.6	79.7	83.0
70°	67.2	66.4	66.4	65.9	66.4	66.4	67.2	67.2	68.4	69.3	71.7
72.5°	58.8	58.1	58.3	58.0	58.3	58.1	58.8	59.0	60.1	60.5	61.6
75°	43.5	42.3	42.3	42.5	42.3	42.3	43.5	44.9	46.2	48.3	48.8
77.5°	32.4	32.2	32.5	32.1	32.5	32.2	32.4	32.4	32.7	33.7	34.5
80°	26.6	26.3	26.1	26.8	26.1	26.3	26.6	26.6	26.8	27.0	27.3
82.5°	20.6	20.6	20.5	21.4	20.5	20.6	20.6	21.0	21.0	20.9	21.1
85°	12.4	11.9	12.4	11.9	12.4	11.9	12.4	12.2	12.4	12.2	12.4
87.5°	11.9	11.8	11.7	12.0	11.7	11.8	11.9	11.4	11.2	11.2	10.7
90°	37.6	38.2	38.7	39.3	38.7	38.2	37.6	37.0	35.7	34.0	32.3
92.5°	57.1	57.5	57.8	58.2	57.8	57.5	57.1	56.8	56.0	55.0	53.9
95°	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.0	102.2	101.3
97.5°	162.2	162.2	162.2	162.2	162.2	162.2	162.2	162.2	161.6	160.6	159.6
100°	203.0	203.0	203.0	203.0	203.0	203.0	203.0	203.0	202.7	202.2	201.6
102.5°	248.4	248.6	248.8	249.1	248.8	248.6	248.4	248.1	247.6	246.8	246.0
105°	316.9	317.8	318.7	319.5	318.7	317.8	316.9	316.1	315.2	314.4	313.5
107.5°	388.4	388.3	388.3	388.2	388.3	388.3	388.4	388.4	388.1	387.2	386.4
110°	434.8	435.7	436.6	437.5	436.6	435.7	434.8	433.9	433.8	434.3	434.9



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	487.2	487.4	487.6	487.8	487.6	487.4	487.2	487.1	487.0	487.2	487.3
115°	566.6	566.3	566.0	565.8	566.0	566.3	566.6	566.9	567.2	567.5	567.8
117.5°	641.9	641.4	640.8	640.2	640.8	641.4	641.9	642.5	643.3	644.3	645.3
120°	695.0	695.6	696.2	696.7	696.2	695.6	695.0	694.4	694.9	696.3	697.8
122.5°	747.0	746.0	745.0	743.9	745.0	746.0	747.0	748.1	749.1	750.1	751.0
125°	826.9	826.3	825.7	825.1	825.7	826.3	826.9	827.4	828.0	828.6	829.2
127.5°	901.7	901.2	900.7	900.3	900.7	901.2	901.7	902.1	902.6	903.2	903.8
130°	953.0	951.8	950.7	949.5	950.7	951.8	953.0	954.2	955.0	955.6	956.2
132.5°	1003.3	1002.8	1002.4	1001.9	1002.4	1002.8	1003.3	1003.8	1004.3	1004.9	1005.4
135°	1076.5	1075.7	1074.8	1073.9	1074.8	1075.7	1076.5	1077.4	1078.1	1078.7	1079.3
137.5°	1149.1	1149.3	1149.4	1149.6	1149.4	1149.3	1149.1	1148.9	1149.2	1150.0	1150.7
140°	1196.6	1196.3	1196.0	1195.8	1196.0	1196.3	1196.6	1196.9	1197.2	1197.5	1197.8
142.5°	1242.0	1241.9	1241.9	1241.8	1241.9	1241.9	1242.0	1242.0	1242.1	1242.2	1242.2
145°	1307.1	1306.2	1305.4	1304.4	1305.4	1306.2	1307.1	1308.0	1308.5	1308.8	1309.1
147.5°	1368.7	1368.4	1368.2	1367.9	1368.2	1368.4	1368.7	1369.0	1369.3	1369.5	1369.7
150°	1407.4	1407.1	1406.8	1406.6	1406.8	1407.1	1407.4	1407.8	1407.9	1407.9	1407.9
152.5°	1444.5	1443.7	1443.0	1442.2	1443.0	1443.7	1444.5	1445.2	1445.3	1444.6	1443.9
155°	1495.2	1494.1	1492.9	1491.8	1492.9	1494.1	1495.2	1496.4	1496.4	1495.2	1494.1
157.5°	1538.9	1537.9	1537.0	1536.0	1537.0	1537.9	1538.9	1539.9	1540.0	1539.1	1538.2
160°	1565.5	1564.1	1562.6	1561.2	1562.6	1564.1	1565.5	1566.9	1567.2	1566.4	1565.5
162.5°	1591.6	1590.2	1588.8	1587.3	1588.8	1590.2	1591.6	1593.2	1593.1	1591.5	1589.9
165°	1624.9	1623.7	1622.6	1621.3	1622.6	1623.7	1624.9	1626.1	1625.8	1624.0	1622.2
167.5°	1651.1	1649.3	1647.6	1645.8	1647.6	1649.3	1651.1	1652.9	1652.9	1651.2	1649.5
170°	1665.5	1663.4	1661.4	1659.4	1661.4	1663.4	1665.5	1667.5	1667.7	1665.9	1664.2
172.5°	1677.0	1675.0	1672.9	1670.9	1672.9	1675.0	1677.0	1679.0	1679.1	1677.1	1675.1
175°	1689.0	1687.0	1685.0	1682.9	1685.0	1687.0	1689.0	1691.1	1691.1	1689.0	1687.0
177.5°	1694.9	1692.9	1691.1	1689.2	1691.1	1692.9	1694.9	1696.7	1696.8	1695.2	1693.5
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	567.3	568.8	571.8	575.2	578.1	580.6	582.5	585.2	587.6	591.1	594.3
5°	533.0	536.3	541.1	546.8	554.0	558.8	564.7	570.1	577.6	585.3	592.7
7.5°	502.8	506.4	513.5	521.4	529.9	537.8	544.8	554.1	564.2	575.4	587.8
10°	483.2	487.4	495.6	504.7	514.8	522.5	532.0	543.0	554.5	568.2	583.4
12.5°	465.6	469.6	479.6	488.9	499.3	507.8	518.9	530.0	545.3	560.1	577.4
15°	431.4	441.7	453.1	464.1	476.6	486.9	500.2	511.7	526.2	547.0	566.9
17.5°	393.3	404.2	418.6	435.6	452.2	464.9	478.5	492.7	510.1	531.3	554.2
20°	371.1	380.0	395.8	414.7	434.0	451.7	464.1	479.9	497.9	520.8	544.4
22.5°	354.6	362.0	374.4	393.2	414.1	434.6	450.6	466.2	485.9	509.0	534.7
25°	329.6	337.7	348.5	361.3	385.3	407.0	427.8	445.8	466.8	489.7	518.4
27.5°	308.8	315.9	325.8	339.2	355.3	379.2	404.5	424.9	446.5	471.1	499.8
30°	296.6	302.4	310.4	324.1	339.4	360.9	386.5	410.4	432.1	457.7	487.6
32.5°	283.8	289.9	297.8	308.6	325.1	343.2	368.7	394.9	418.0	444.1	473.4
35°	266.7	271.6	278.7	289.6	304.5	320.2	343.0	370.0	394.4	422.3	450.3
37.5°	249.4	255.1	260.7	270.5	282.7	299.6	318.2	345.9	372.8	398.4	425.7
40°	239.7	243.1	249.2	257.2	270.0	285.1	302.6	329.6	356.6	381.9	409.4
42.5°	228.8	232.6	237.8	245.7	257.2	272.0	289.0	312.4	340.5	365.1	390.1
45°	213.7	215.8	221.1	227.7	237.3	252.2	267.9	288.7	315.3	338.7	360.6
47.5°	198.3	200.3	203.5	209.6	220.4	232.3	247.0	265.7	288.9	312.4	330.9
50°	187.8	189.6	192.7	198.3	207.9	219.6	234.2	251.0	271.8	294.2	309.7
52.5°	177.3	178.2	181.2	187.6	195.7	207.2	220.3	235.7	255.1	273.8	289.5
55°	160.6	162.8	164.7	169.5	177.1	188.1	199.9	214.4	229.4	245.2	258.6
57.5°	143.2	145.5	148.2	152.5	158.5	168.7	179.3	191.1	204.0	217.0	228.3
60°	131.7	133.8	136.2	141.0	146.5	154.6	166.1	176.4	186.2	198.1	209.3
62.5°	120.4	122.6	125.3	129.2	134.4	142.2	151.8	160.7	170.9	181.3	189.7
65°	103.7	105.4	107.6	111.2	116.1	123.1	131.0	137.9	147.0	154.6	162.3
67.5°	85.4	88.7	91.4	94.3	98.6	105.0	110.8	117.4	123.6	129.3	136.2
70°	73.4	77.0	79.6	82.7	86.7	92.3	97.8	102.3	107.3	112.8	119.1
72.5°	63.2	66.0	68.2	71.4	75.1	80.2	85.3	89.1	93.2	96.9	103.0
75°	50.0	51.1	52.6	55.2	58.6	62.4	66.4	69.8	72.2	75.5	79.8
77.5°	35.9	38.2	39.2	41.0	43.4	45.7	48.5	51.3	53.6	54.7	58.1
80°	27.5	28.5	29.4	32.0	33.4	35.9	37.8	40.4	41.3	42.5	45.6
82.5°	21.4	21.9	22.5	23.2	24.1	26.5	28.4	30.1	31.0	31.4	33.8
85°	12.4	12.6	12.9	13.1	13.4	13.4	14.3	15.6	17.2	17.2	18.0
87.5°	10.3	10.2	9.7	9.0	9.0	8.5	8.1	7.5	7.4	7.4	7.3
90°	30.6	28.8	26.5	24.1	21.8	19.5	16.8	13.5	10.3	7.2	3.9
92.5°	52.9	51.9	50.2	48.6	47.0	45.3	42.7	39.0	35.3	31.7	28.1
95°	100.4	99.6	97.5	95.4	93.4	91.4	89.1	86.4	83.8	81.2	78.6
97.5°	158.4	157.4	155.0	152.7	150.3	147.8	145.6	143.5	141.5	139.4	137.2
100°	201.0	200.4	197.7	195.1	192.5	189.9	188.0	186.8	185.7	184.5	183.4
102.5°	245.2	244.4	242.0	239.6	237.2	234.8	233.4	233.0	232.5	232.1	231.6
105°	312.6	311.7	310.5	309.4	308.2	307.0	306.3	306.0	305.8	305.5	305.2
107.5°	385.6	384.8	384.7	384.5	384.3	384.1	383.8	383.4	383.1	382.7	382.4
110°	435.6	436.2	436.5	436.7	437.0	437.3	437.2	436.6	436.0	435.4	434.8



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	487.4	487.5	488.0	488.5	489.1	489.6	489.8	489.7	489.5	489.4	489.3
115°	568.2	568.4	569.0	569.6	570.2	570.8	571.0	571.0	571.0	571.0	571.0
117.5°	646.2	647.2	647.6	648.0	648.4	648.8	648.9	648.7	648.5	648.2	648.0
120°	699.2	700.6	701.6	702.5	703.3	704.2	704.0	702.9	701.7	700.5	699.3
122.5°	752.0	753.1	753.5	753.9	754.3	754.7	754.7	754.2	753.8	753.3	752.8
125°	829.7	830.3	830.6	830.9	831.2	831.5	831.6	831.6	831.6	831.6	831.6
127.5°	904.4	904.9	905.4	905.9	906.4	906.9	906.7	905.7	904.9	904.0	903.1
130°	956.7	957.4	957.4	957.4	957.4	957.4	956.9	956.0	955.2	954.3	953.4
132.5°	1006.0	1006.6	1006.8	1007.0	1007.3	1007.5	1007.3	1006.7	1006.0	1005.4	1004.8
135°	1079.9	1080.5	1080.5	1080.5	1080.5	1080.5	1079.6	1077.8	1076.1	1074.4	1072.6
137.5°	1151.4	1152.3	1151.8	1151.3	1150.8	1150.4	1149.7	1148.9	1148.1	1147.3	1146.5
140°	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1	1197.5	1196.9	1196.3	1195.8
142.5°	1242.3	1242.3	1242.6	1242.8	1243.0	1243.2	1243.1	1242.5	1241.9	1241.3	1240.8
145°	1309.4	1309.7	1309.4	1309.1	1308.8	1308.5	1307.8	1306.7	1305.5	1304.3	1303.1
147.5°	1370.0	1370.2	1370.4	1370.7	1370.9	1371.1	1370.5	1369.2	1367.8	1366.3	1364.9
150°	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.3	1406.1	1405.0	1403.8	1402.7
152.5°	1443.2	1442.5	1442.3	1442.0	1441.8	1441.6	1441.1	1440.4	1439.7	1439.0	1438.2
155°	1492.9	1491.8	1492.0	1492.3	1492.6	1492.9	1493.0	1493.0	1493.0	1493.0	1493.0
157.5°	1537.4	1536.5	1536.6	1536.6	1536.7	1536.7	1537.0	1537.5	1538.1	1538.6	1539.1
160°	1564.6	1563.8	1564.1	1564.4	1564.6	1564.9	1565.2	1565.5	1565.8	1566.1	1566.4
162.5°	1588.4	1586.8	1587.1	1587.4	1587.7	1588.0	1588.5	1589.2	1590.0	1590.7	1591.5
165°	1620.5	1618.7	1619.3	1619.9	1620.5	1621.1	1621.8	1622.7	1623.6	1624.5	1625.3
167.5°	1647.8	1646.0	1646.0	1645.9	1645.9	1645.8	1646.4	1647.6	1648.8	1650.0	1651.2
170°	1662.4	1660.6	1660.4	1660.1	1659.8	1659.5	1660.1	1661.5	1663.0	1664.5	1665.9
172.5°	1673.1	1671.1	1671.1	1671.0	1671.0	1670.9	1671.5	1672.7	1674.0	1675.2	1676.4
175°	1685.0	1682.9	1683.2	1683.5	1683.8	1684.1	1685.0	1686.5	1687.9	1689.3	1690.8
177.5°	1691.9	1690.3	1690.3	1690.3	1690.3	1690.3	1690.8	1692.0	1693.1	1694.4	1695.5
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	596.8	598.5	600.5	604.1	607.1	608.5	611.2	613.1	612.5	615.2	619.8
5°	599.2	605.6	613.1	620.7	629.2	636.4	642.2	647.9	652.5	657.9	666.1
7.5°	598.7	610.3	622.8	636.4	650.6	662.8	674.0	685.5	695.7	706.8	721.4
10°	597.2	612.6	628.1	646.0	664.0	681.0	696.2	710.5	724.2	738.7	757.2
12.5°	595.5	613.1	631.9	653.5	675.8	696.2	714.2	734.9	751.9	770.7	791.9
15°	587.9	611.6	637.2	665.1	692.0	719.4	744.0	769.3	793.0	815.5	842.2
17.5°	579.3	606.5	636.7	669.7	701.9	735.3	764.6	796.5	820.6	850.8	875.7
20°	572.2	601.6	633.8	670.9	707.4	744.5	776.8	809.3	836.5	866.9	898.4
22.5°	563.6	595.8	630.8	669.1	707.4	747.9	783.7	816.0	849.7	883.8	916.4
25°	549.7	583.2	620.3	662.3	706.3	747.6	785.9	826.0	862.3	899.4	928.6
27.5°	532.7	567.8	606.8	650.3	695.4	737.7	782.7	825.6	862.1	897.8	923.2
30°	519.1	556.1	593.7	637.6	684.5	729.9	778.2	821.0	859.5	891.5	905.8
32.5°	505.1	540.3	579.0	623.5	671.5	720.3	768.2	812.0	847.6	866.8	867.2
35°	480.9	513.8	554.0	597.7	647.0	700.0	748.5	791.5	813.3	815.0	791.5
37.5°	454.4	484.6	522.5	566.3	620.3	673.1	722.6	751.2	758.5	734.2	690.9
40°	435.5	463.4	500.0	544.9	598.4	653.0	698.1	719.1	711.6	672.1	623.8
42.5°	415.6	441.6	476.9	521.2	574.9	630.1	668.5	679.7	659.5	614.0	557.4
45°	383.1	407.0	441.9	486.7	538.3	589.9	619.0	613.3	579.6	525.5	462.2
47.5°	349.3	372.4	403.8	445.1	498.1	542.6	562.3	545.0	497.1	437.7	386.2
50°	327.0	350.6	379.5	419.0	467.3	510.3	522.9	496.7	443.3	386.3	338.9
52.5°	305.0	325.2	353.6	391.6	437.8	474.1	480.9	450.6	395.6	344.4	302.4
55°	271.6	289.9	313.8	349.6	389.6	420.4	416.8	377.9	327.9	284.2	251.2
57.5°	239.1	253.0	275.1	308.7	343.8	364.5	351.3	318.1	271.6	235.7	207.9
60°	217.7	230.7	251.2	280.5	311.4	323.2	312.1	276.1	239.2	206.5	183.1
62.5°	197.4	208.8	226.5	253.8	278.7	285.7	273.9	242.4	209.2	181.3	161.9
65°	168.0	178.5	193.6	213.0	230.1	233.5	225.9	193.6	168.5	145.1	131.7
67.5°	141.3	148.1	160.0	176.6	185.8	187.7	173.0	152.7	130.6	116.2	106.1
70°	123.3	128.2	139.1	148.1	155.6	155.8	142.2	125.9	109.0	97.3	89.9
72.5°	105.9	110.5	118.9	125.0	130.8	128.9	116.4	103.6	89.9	81.0	75.5
75°	81.7	85.8	90.1	93.0	93.0	90.6	81.5	71.9	64.0	58.8	57.2
77.5°	59.4	62.7	64.2	63.7	62.9	59.2	53.4	47.2	44.3	41.9	40.6
80°	46.7	48.1	48.5	47.4	45.8	41.6	37.8	35.1	32.5	31.5	31.1
82.5°	34.5	35.9	34.5	34.9	31.7	28.2	26.1	25.1	24.1	23.7	23.2
85°	18.4	18.2	17.7	16.5	14.3	13.8	13.6	13.4	12.9	13.1	12.6
87.5°	7.8	7.8	7.7	8.1	8.7	8.8	9.4	9.9	10.4	10.5	11.2
90°	7.2	10.3	13.5	16.8	19.5	21.8	24.1	26.5	28.8	30.6	32.3
92.5°	31.7	35.3	39.0	42.7	45.3	47.0	48.6	50.2	51.9	52.9	53.9
95°	81.2	83.8	86.4	89.1	91.4	93.4	95.4	97.5	99.6	100.4	101.3
97.5°	139.4	141.5	143.5	145.6	147.8	150.3	152.7	155.0	157.4	158.4	159.6
100°	184.5	185.7	186.8	188.0	189.9	192.5	195.1	197.7	200.4	201.0	201.6
102.5°	232.1	232.5	233.0	233.4	234.8	237.2	239.6	242.0	244.4	245.2	246.0
105°	305.5	305.8	306.0	306.3	307.0	308.2	309.4	310.5	311.7	312.6	313.5
107.5°	382.7	383.1	383.4	383.8	384.1	384.3	384.5	384.7	384.8	385.6	386.4
110°	435.4	436.0	436.6	437.2	437.3	437.0	436.7	436.5	436.2	435.6	434.9





TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.4	489.5	489.7	489.8	489.6	489.1	488.5	488.0	487.5	487.4	487.3
115°	571.0	571.0	571.0	571.0	570.8	570.2	569.6	569.0	568.4	568.2	567.8
117.5°	648.2	648.5	648.7	648.9	648.8	648.4	648.0	647.6	647.2	646.2	645.3
120°	700.5	701.7	702.9	704.0	704.2	703.3	702.5	701.6	700.6	699.2	697.8
122.5°	753.3	753.8	754.2	754.7	754.7	754.3	753.9	753.5	753.1	752.0	751.0
125°	831.6	831.6	831.6	831.6	831.5	831.2	830.9	830.6	830.3	829.7	829.2
127.5°	904.0	904.9	905.7	906.7	906.9	906.4	905.9	905.4	904.9	904.4	903.8
130°	954.3	955.2	956.0	956.9	957.4	957.4	957.4	957.4	957.4	956.7	956.2
132.5°	1005.4	1006.0	1006.7	1007.3	1007.5	1007.3	1007.0	1006.8	1006.6	1006.0	1005.4
135°	1074.4	1076.1	1077.8	1079.6	1080.5	1080.5	1080.5	1080.5	1080.5	1079.9	1079.3
137.5°	1147.3	1148.1	1148.9	1149.7	1150.4	1150.8	1151.3	1151.8	1152.3	1151.4	1150.7
140°	1196.3	1196.9	1197.5	1198.1	1198.3	1198.3	1198.3	1198.3	1198.3	1198.1	1197.8
142.5°	1241.3	1241.9	1242.5	1243.1	1243.2	1243.0	1242.8	1242.6	1242.3	1242.3	1242.2
145°	1304.3	1305.5	1306.7	1307.8	1308.5	1308.8	1309.1	1309.4	1309.7	1309.4	1309.1
147.5°	1366.3	1367.8	1369.2	1370.5	1371.1	1370.9	1370.7	1370.4	1370.2	1370.0	1369.7
150°	1403.8	1405.0	1406.1	1407.3	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9	1407.9
152.5°	1439.0	1439.7	1440.4	1441.1	1441.6	1441.8	1442.0	1442.3	1442.5	1443.2	1443.9
155°	1493.0	1493.0	1493.0	1493.0	1492.9	1492.6	1492.3	1492.0	1491.8	1492.9	1494.1
157.5°	1538.6	1538.1	1537.5	1537.0	1536.7	1536.7	1536.6	1536.6	1536.5	1537.4	1538.2
160°	1566.1	1565.8	1565.5	1565.2	1564.9	1564.6	1564.4	1564.1	1563.8	1564.6	1565.5
162.5°	1590.7	1590.0	1589.2	1588.5	1588.0	1587.7	1587.4	1587.1	1586.8	1588.4	1589.9
165°	1624.5	1623.6	1622.7	1621.8	1621.1	1620.5	1619.9	1619.3	1618.7	1620.5	1622.2
167.5°	1650.0	1648.8	1647.6	1646.4	1645.8	1645.9	1645.9	1646.0	1646.0	1647.8	1649.5
170°	1664.5	1663.0	1661.5	1660.1	1659.5	1659.8	1660.1	1660.4	1660.6	1662.4	1664.2
172.5°	1675.2	1674.0	1672.7	1671.5	1670.9	1671.0	1671.0	1671.1	1671.1	1673.1	1675.1
175°	1689.3	1687.9	1686.5	1685.0	1684.1	1683.8	1683.5	1683.2	1682.9	1685.0	1687.0
177.5°	1694.4	1693.1	1692.0	1690.8	1690.3	1690.3	1690.3	1690.3	1690.3	1691.9	1693.5
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	622.3	623.0	623.6	625.5	625.7	627.4	625.7
5°	673.8	677.1	682.4	687.6	688.1	691.5	685.5
7.5°	731.4	739.2	744.1	752.6	755.9	758.0	754.6
10°	771.2	778.4	791.1	797.3	803.5	804.5	801.6
12.5°	809.7	821.0	831.0	842.8	842.5	850.9	847.9
15°	860.9	872.6	886.5	899.6	904.3	904.3	908.2
17.5°	897.4	918.9	933.2	943.5	954.8	956.7	955.4
20°	922.1	945.2	960.6	973.9	981.6	983.7	983.7
22.5°	940.4	960.2	975.1	987.1	993.4	995.9	995.2
25°	953.1	970.1	979.2	982.8	984.4	984.0	979.5
27.5°	935.7	934.9	929.3	918.3	910.0	904.9	899.2
30°	902.5	890.0	875.7	859.9	839.6	824.0	819.3
32.5°	852.9	825.1	800.7	774.5	752.7	737.1	730.5
35°	757.2	713.0	676.8	645.3	622.4	608.0	603.2
37.5°	643.5	600.7	556.0	525.4	506.3	491.9	486.6
40°	571.2	524.6	485.6	457.0	437.4	423.2	423.0
42.5°	505.2	460.7	424.0	403.4	382.3	372.9	372.9
45°	413.7	378.1	347.0	330.7	318.1	310.4	308.3
47.5°	342.5	313.1	292.4	279.4	269.1	264.3	261.1
50°	302.6	276.8	260.2	249.0	243.3	237.1	236.6
52.5°	269.3	248.4	235.6	226.5	219.2	215.5	215.6
55°	226.3	209.8	200.8	193.8	188.1	185.2	184.0
57.5°	190.7	178.3	171.7	165.3	162.9	160.7	160.1
60°	168.5	160.2	153.9	148.9	145.3	144.6	144.3
62.5°	150.2	141.4	137.1	133.2	130.6	129.5	129.1
65°	123.8	117.3	113.5	110.4	109.5	107.8	107.6
67.5°	99.8	95.9	93.4	91.3	90.0	89.9	89.9
70°	85.1	82.9	80.8	79.6	78.9	78.4	78.4
72.5°	72.5	70.9	69.1	68.5	68.4	67.9	67.7
75°	55.2	53.5	53.8	52.6	51.6	50.4	49.7
77.5°	39.2	38.0	37.7	37.6	36.8	36.7	37.0
80°	30.4	29.2	28.9	29.2	28.9	28.2	28.2
82.5°	23.1	22.1	21.8	21.7	21.5	21.7	21.3
85°	12.4	11.9	11.9	11.9	12.4	12.2	11.9
87.5°	11.2	11.4	11.8	11.7	11.8	11.7	12.0
90°	34.0	35.7	37.0	37.6	38.2	38.7	39.3
92.5°	55.0	56.0	56.8	57.1	57.5	57.8	58.2
95°	102.2	103.0	103.5	103.5	103.5	103.5	103.5
97.5°	160.6	161.6	162.2	162.2	162.2	162.2	162.2
100°	202.2	202.7	203.0	203.0	203.0	203.0	203.0
102.5°	246.8	247.6	248.1	248.4	248.6	248.8	249.1
105°	314.4	315.2	316.1	316.9	317.8	318.7	319.5
107.5°	387.2	388.1	388.4	388.4	388.3	388.3	388.2
110°	434.3	433.8	433.9	434.8	435.7	436.6	437.5



TEST NUMBER: P333028-840

CATALOG NUMBER: S124RDIW-S350D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	487.2	487.0	487.1	487.2	487.4	487.6	487.8
115°	567.5	567.2	566.9	566.6	566.3	566.0	565.8
117.5°	644.3	643.3	642.5	641.9	641.4	640.8	640.2
120°	696.3	694.9	694.4	695.0	695.6	696.2	696.7
122.5°	750.1	749.1	748.1	747.0	746.0	745.0	743.9
125°	828.6	828.0	827.4	826.9	826.3	825.7	825.1
127.5°	903.2	902.6	902.1	901.7	901.2	900.7	900.3
130°	955.6	955.0	954.2	953.0	951.8	950.7	949.5
132.5°	1004.9	1004.3	1003.8	1003.3	1002.8	1002.4	1001.9
135°	1078.7	1078.1	1077.4	1076.5	1075.7	1074.8	1073.9
137.5°	1150.0	1149.2	1148.9	1149.1	1149.3	1149.4	1149.6
140°	1197.5	1197.2	1196.9	1196.6	1196.3	1196.0	1195.8
142.5°	1242.2	1242.1	1242.0	1242.0	1241.9	1241.9	1241.8
145°	1308.8	1308.5	1308.0	1307.1	1306.2	1305.4	1304.4
147.5°	1369.5	1369.3	1369.0	1368.7	1368.4	1368.2	1367.9
150°	1407.9	1407.9	1407.8	1407.4	1407.1	1406.8	1406.6
152.5°	1444.6	1445.3	1445.2	1444.5	1443.7	1443.0	1442.2
155°	1495.2	1496.4	1496.4	1495.2	1494.1	1492.9	1491.8
157.5°	1539.1	1540.0	1539.9	1538.9	1537.9	1537.0	1536.0
160°	1566.4	1567.2	1566.9	1565.5	1564.1	1562.6	1561.2
162.5°	1591.5	1593.1	1593.2	1591.6	1590.2	1588.8	1587.3
165°	1624.0	1625.8	1626.1	1624.9	1623.7	1622.6	1621.3
167.5°	1651.2	1652.9	1652.9	1651.1	1649.3	1647.6	1645.8
170°	1665.9	1667.7	1667.5	1665.5	1663.4	1661.4	1659.4
172.5°	1677.1	1679.1	1679.0	1677.0	1675.0	1672.9	1670.9
175°	1689.0	1691.1	1691.1	1689.0	1687.0	1685.0	1682.9
177.5°	1695.2	1696.8	1696.7	1694.9	1692.9	1691.1	1689.2
180°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4

(END OF REPORT)