

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332769-940

Luminaire Tested: **S124DIW-S575D1560U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332769-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1560U940-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7877.5 lumens  
Efficiency: N/A  
Efficacy: 130.0 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.6	1.0
10°-20°	251.5	3.2
20°-30°	398.8	5.1
30°-40°	443.8	5.6
40°-50°	404.0	5.1
50°-60°	330.1	4.2
60°-70°	235.7	3.0
70°-80°	129.8	1.6
80°-90°	40.6	0.5
90°-100°	61.5	0.8
100°-110°	392.1	5.0
110°-120°	750.0	9.5
120°-130°	952.1	12.1
130°-140°	1018.7	12.9
140°-150°	952.6	12.1
150°-160°	768.2	9.8
160°-170°	495.5	6.3
170°-180°	170.8	2.2
0°-30°	731.9	9.3
0°-40°	1175.7	14.9
0°-60°	1909.9	24.2
0°-90°	2316.0	29.4
90°-120°	1203.6	15.3
90°-150°	4127.0	52.4
90°-180°	5561.0	70.6
0°-180°	7877.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	40	4	40	4	40	18
95°	39	74	39	74	39	31
105°	383	405	383	405	383	334
115°	761	756	761	756	761	753
125°	1070	1062	1070	1062	1070	953
135°	1327	1318	1327	1318	1327	1022
145°	1528	1520	1528	1520	1528	955
155°	1665	1666	1665	1666	1665	768
165°	1750	1758	1750	1758	1750	494
175°	1787	1798	1787	1798	1787	170
180°	1798	1798	1798	1798	1798	



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	14.2	14.9	14.8	14.9	15.3	15.4	15.3	14.7	15.4	15.3	16.0
90°	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2	31.4	29.6	27.2
92.5°	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1	30.3	28.5	26.1
95°	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2	31.4	29.6	29.2
97.5°	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8	35.7	35.5	68.8
100°	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0	54.1	59.2	100.4
102.5°	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5	230.2	285.1	290.4
105°	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9	422.2	419.5	418.0
107.5°	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8	524.4	523.1	521.0
110°	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2	593.6	593.0	591.2



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6	660.7	660.8	660.0
115°	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6	759.0	758.4	758.8
117.5°	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3	859.4	859.5	858.9
120°	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0	920.4	919.8	920.1
122.5°	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9	981.5	981.1	980.7
125°	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8	1066.0	1065.1	1065.6
127.5°	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3	1151.5	1151.6	1150.2
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8	1202.5	1202.2	1201.3
132.5°	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4	1253.0	1252.8	1251.6
135°	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0	1322.5	1321.9	1320.7
137.5°	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9	1389.2	1388.6	1387.2
140°	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3	1430.4	1429.4	1428.9
142.5°	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5	1468.8	1468.2	1467.8
145°	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2	1523.8	1523.6	1523.6
147.5°	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2	1572.0	1571.7	1572.0
150°	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9	1602.9	1602.9	1603.2
152.5°	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7	1629.2	1628.7	1629.2
155°	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8	1664.6	1663.4	1664.4
157.5°	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8	1694.9
160°	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2	1713.5
162.5°	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0	1731.1	1729.3	1729.7
165°	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6	1753.2	1750.9	1750.9
167.5°	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3	1769.6	1767.0	1767.2
170°	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5	1780.1	1777.7	1777.4
172.5°	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0	1786.5	1784.2	1783.9
175°	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5	1793.9	1791.2	1790.9
177.5°	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6	1797.7	1795.7	1795.3
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	15.5	15.3	14.5	12.8	11.4	9.9	8.9	8.0	8.9	9.9	10.8
90°	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0	7.3	10.6	13.9
92.5°	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9	17.1	17.3	17.5
95°	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9	63.8	53.7	43.5
97.5°	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0	163.4	169.7	176.1
100°	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5	226.0	231.3	236.7
102.5°	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5	295.5	299.4	303.4
105°	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7	406.5	408.3	410.2
107.5°	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9	510.9	511.8	512.6
110°	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9	581.8	582.7	583.6





TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8	651.4	653.0	654.6
115°	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7	756.6	757.5	758.4
117.5°	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2	852.4	853.6	854.8
120°	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8	916.9	918.2	919.4
122.5°	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0	976.7	977.4	978.1
125°	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4	1063.5	1064.7	1066.0
127.5°	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1	1144.4	1144.7	1145.0
130°	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9	1197.1	1197.4	1197.7
132.5°	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2	1245.7	1246.3	1246.9
135°	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9	1317.5	1317.2	1317.0
137.5°	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2	1382.2	1382.3	1382.5
140°	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1	1424.7	1425.3	1425.8
142.5°	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7	1462.8	1463.9	1465.0
145°	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6	1520.5	1521.3	1522.2
147.5°	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6	1567.2	1568.9	1570.6
150°	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9	1600.1	1601.2	1602.5
152.5°	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8	1627.8	1628.8	1629.7
155°	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2	1666.4	1666.7	1667.1
157.5°	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2	1699.1	1698.9	1698.7
160°	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6	1717.7	1716.8	1715.9
162.5°	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8	1734.6	1733.5	1732.4
165°	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6	1756.0	1754.6	1753.1
167.5°	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8	1773.3	1771.7	1770.1
170°	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5	1782.7	1780.8	1779.1
172.5°	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9	1789.1	1787.3	1785.6
175°	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9	1796.1	1794.3	1792.5
177.5°	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2	1799.5	1797.8	1796.1
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	12.3	12.9	14.4	15.5	16.9	18.7	19.6	23.0	24.5	26.2	29.0
90°	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2	35.0	36.7	38.0
92.5°	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1	33.9	35.7	36.6
95°	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2	35.0	36.7	37.8
97.5°	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8	36.0	36.2	36.5
100°	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0	44.0	38.9	36.5
102.5°	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5	120.6	65.9	38.5
105°	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9	427.7	430.3	426.2
107.5°	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8	527.1	528.3	529.6
110°	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2	594.9	595.4	596.2



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6	660.4	660.3	660.8
115°	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6	760.2	760.8	761.2
117.5°	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3	859.2	859.1	859.0
120°	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0	921.6	922.2	922.2
122.5°	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9	982.2	982.6	982.4
125°	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8	1067.7	1068.6	1069.3
127.5°	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3	1151.1	1150.9	1150.7
130°	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8	1203.1	1203.4	1203.5
132.5°	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4	1253.7	1253.9	1254.0
135°	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0	1323.7	1324.3	1324.9
137.5°	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9	1390.5	1391.2	1391.4
140°	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3	1432.2	1433.1	1433.6
142.5°	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5	1470.2	1470.8	1471.1
145°	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2	1524.5	1524.7	1525.3
147.5°	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2	1572.4	1572.7	1573.0
150°	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9	1602.9	1602.9	1603.1
152.5°	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7	1630.1	1630.7	1630.8
155°	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8	1667.1	1668.2	1668.4
157.5°	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0
160°	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4
162.5°	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0	1734.7	1736.5	1736.3
165°	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6	1758.0	1760.4	1760.2
167.5°	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3	1774.9	1777.5	1777.4
170°	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5	1784.9	1787.3	1787.0
172.5°	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0	1791.4	1793.8	1793.3
175°	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5	1799.3	1802.0	1801.5
177.5°	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6	1801.5	1803.4	1803.0
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	29.9	30.3	31.3	31.9	31.3	30.3	29.9	29.0	26.2	24.5	23.0
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2
92.5°	36.7	36.9	37.0	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1
95°	38.1	38.4	38.7	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2
97.5°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8
100°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0
102.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5
105°	415.5	404.7	394.0	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9
107.5°	530.7	531.8	533.0	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8
110°	597.1	598.0	598.9	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	662.0	663.1	664.2	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6
115°	761.2	761.2	761.2	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6
117.5°	858.8	858.7	858.6	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3
120°	921.6	921.0	920.4	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0
122.5°	981.9	981.2	980.6	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9
125°	1069.5	1069.8	1070.1	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8
127.5°	1150.5	1150.2	1150.0	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8
132.5°	1253.7	1253.5	1253.3	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4
135°	1325.4	1326.1	1326.7	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0
137.5°	1391.2	1391.1	1390.9	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9
140°	1434.0	1434.2	1434.5	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3
142.5°	1471.2	1471.3	1471.3	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5
145°	1525.8	1526.4	1527.1	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2
147.5°	1573.2	1573.5	1573.9	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2
150°	1603.4	1603.7	1604.0	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9
152.5°	1630.6	1630.4	1630.2	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7
155°	1667.5	1666.6	1665.7	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8
157.5°	1698.5	1696.9	1695.4	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9
160°	1718.6	1716.8	1715.0	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8
162.5°	1734.4	1732.3	1730.3	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0
165°	1757.6	1754.9	1752.2	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6
167.5°	1774.3	1771.4	1768.4	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3
170°	1784.0	1781.0	1778.1	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5
172.5°	1790.1	1786.9	1783.7	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0
175°	1797.9	1794.3	1790.7	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5
177.5°	1800.1	1797.2	1794.3	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	19.6	18.7	16.9	15.5	14.4	12.9	12.3	10.8	9.9	8.9	8.0
90°	31.4	29.6	27.2	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0
92.5°	30.3	28.5	26.1	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9
95°	31.4	29.6	29.2	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9
97.5°	35.7	35.5	68.8	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0
100°	54.1	59.2	100.4	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5
102.5°	230.2	285.1	290.4	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5
105°	422.2	419.5	418.0	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7
107.5°	524.4	523.1	521.0	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9
110°	593.6	593.0	591.2	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	660.7	660.8	660.0	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8
115°	759.0	758.4	758.8	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7
117.5°	859.4	859.5	858.9	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2
120°	920.4	919.8	920.1	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8
122.5°	981.5	981.1	980.7	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0
125°	1066.0	1065.1	1065.6	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4
127.5°	1151.5	1151.6	1150.2	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1
130°	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9
132.5°	1253.0	1252.8	1251.6	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2
135°	1322.5	1321.9	1320.7	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9
137.5°	1389.2	1388.6	1387.2	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2
140°	1430.4	1429.4	1428.9	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1
142.5°	1468.8	1468.2	1467.8	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7
145°	1523.8	1523.6	1523.6	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6
147.5°	1572.0	1571.7	1572.0	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6
150°	1602.9	1602.9	1603.2	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9
152.5°	1629.2	1628.7	1629.2	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8
155°	1664.6	1663.4	1664.4	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2
157.5°	1695.4	1693.8	1694.9	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2
160°	1715.0	1713.2	1713.5	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6
162.5°	1731.1	1729.3	1729.7	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8
165°	1753.2	1750.9	1750.9	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6
167.5°	1769.6	1767.0	1767.2	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8
170°	1780.1	1777.7	1777.4	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5
172.5°	1786.5	1784.2	1783.9	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9
175°	1793.9	1791.2	1790.9	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9
177.5°	1797.7	1795.7	1795.3	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	8.9	9.9	11.4	12.8	14.5	15.3	15.5	16.0	15.3	15.4	14.7
90°	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2
92.5°	17.1	17.3	17.5	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1
95°	63.8	53.7	43.5	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2
97.5°	163.4	169.7	176.1	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8
100°	226.0	231.3	236.7	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0
102.5°	295.5	299.4	303.4	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5
105°	406.5	408.3	410.2	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9
107.5°	510.9	511.8	512.6	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8
110°	581.8	582.7	583.6	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2





TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	651.4	653.0	654.6	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6
115°	756.6	757.5	758.4	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6
117.5°	852.4	853.6	854.8	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3
120°	916.9	918.2	919.4	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0
122.5°	976.7	977.4	978.1	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9
125°	1063.5	1064.7	1066.0	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8
127.5°	1144.4	1144.7	1145.0	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3
130°	1197.1	1197.4	1197.7	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8
132.5°	1245.7	1246.3	1246.9	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4
135°	1317.5	1317.2	1317.0	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0
137.5°	1382.2	1382.3	1382.5	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9
140°	1424.7	1425.3	1425.8	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3
142.5°	1462.8	1463.9	1465.0	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5
145°	1520.5	1521.3	1522.2	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2
147.5°	1567.2	1568.9	1570.6	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2
150°	1600.1	1601.2	1602.5	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9
152.5°	1627.8	1628.8	1629.7	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7
155°	1666.4	1666.7	1667.1	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8
157.5°	1699.1	1698.9	1698.7	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9
160°	1717.7	1716.8	1715.9	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8
162.5°	1734.6	1733.5	1732.4	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0
165°	1756.0	1754.6	1753.1	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6
167.5°	1773.3	1771.7	1770.1	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3
170°	1782.7	1780.8	1779.1	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5
172.5°	1789.1	1787.3	1785.6	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0
175°	1796.1	1794.3	1792.5	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5
177.5°	1799.5	1797.8	1796.1	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	15.3	15.4	15.3	14.9	14.8	14.9	14.2
90°	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	33.9	35.7	36.6	36.7	36.9	37.0	37.1
95°	35.0	36.7	37.8	38.1	38.4	38.7	39.0
97.5°	36.0	36.2	36.5	36.7	37.1	37.4	37.6
100°	44.0	38.9	36.5	36.7	37.1	37.4	37.6
102.5°	120.6	65.9	38.5	38.5	38.6	38.7	38.7
105°	427.7	430.3	426.2	415.5	404.7	394.0	383.3
107.5°	527.1	528.3	529.6	530.7	531.8	533.0	534.1
110°	594.9	595.4	596.2	597.1	598.0	598.9	599.8



TEST NUMBER: P332769-940

CATALOG NUMBER: S124DIW-S575D1560U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	660.4	660.3	660.8	662.0	663.1	664.2	665.4
115°	760.2	760.8	761.2	761.2	761.2	761.2	761.2
117.5°	859.2	859.1	859.0	858.8	858.7	858.6	858.4
120°	921.6	922.2	922.2	921.6	921.0	920.4	919.8
122.5°	982.2	982.6	982.4	981.9	981.2	980.6	980.1
125°	1067.7	1068.6	1069.3	1069.5	1069.8	1070.1	1070.4
127.5°	1151.1	1150.9	1150.7	1150.5	1150.2	1150.0	1149.8
130°	1203.1	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5
132.5°	1253.7	1253.9	1254.0	1253.7	1253.5	1253.3	1253.0
135°	1323.7	1324.3	1324.9	1325.4	1326.1	1326.7	1327.2
137.5°	1390.5	1391.2	1391.4	1391.2	1391.1	1390.9	1390.7
140°	1432.2	1433.1	1433.6	1434.0	1434.2	1434.5	1434.9
142.5°	1470.2	1470.8	1471.1	1471.2	1471.3	1471.3	1471.4
145°	1524.5	1524.7	1525.3	1525.8	1526.4	1527.1	1527.6
147.5°	1572.4	1572.7	1573.0	1573.2	1573.5	1573.9	1574.1
150°	1602.9	1602.9	1603.1	1603.4	1603.7	1604.0	1604.3
152.5°	1630.1	1630.7	1630.8	1630.6	1630.4	1630.2	1630.0
155°	1667.1	1668.2	1668.4	1667.5	1666.6	1665.7	1664.8
157.5°	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8
160°	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2
162.5°	1734.7	1736.5	1736.3	1734.4	1732.3	1730.3	1728.2
165°	1758.0	1760.4	1760.2	1757.6	1754.9	1752.2	1749.5
167.5°	1774.9	1777.5	1777.4	1774.3	1771.4	1768.4	1765.4
170°	1784.9	1787.3	1787.0	1784.0	1781.0	1778.1	1775.0
172.5°	1791.4	1793.8	1793.3	1790.1	1786.9	1783.7	1780.4
175°	1799.3	1802.0	1801.5	1797.9	1794.3	1790.7	1787.2
177.5°	1801.5	1803.4	1803.0	1800.1	1797.2	1794.3	1791.4
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9

(END OF REPORT)