

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332752-940

Luminaire Tested: **S124DIW-S575D770U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332752-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D770U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4687.5 lumens  
Efficiency: N/A  
Efficacy: 124.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	34	30
4	75	64	56	50	69	59	53	47	51	45	41	43	39	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	34	29	50	39	32	28	34	28	25	29	25	22	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.6	1.7
10°-20°	251.5	5.4
20°-30°	398.8	8.5
30°-40°	443.8	9.5
40°-50°	404.0	8.6
50°-60°	330.1	7.0
60°-70°	235.7	5.0
70°-80°	129.8	2.8
80°-90°	38.0	0.8
90°-100°	56.4	1.2
100°-110°	167.2	3.6
110°-120°	283.8	6.1
120°-130°	374.2	8.0
130°-140°	420.2	9.0
140°-150°	413.0	8.8
150°-160°	347.3	7.4
160°-170°	231.1	4.9
170°-180°	80.9	1.7
0°-30°	731.9	15.6
0°-40°	1175.7	25.1
0°-60°	1909.9	40.7
0°-90°	2313.3	49.4
90°-120°	507.4	10.8
90°-150°	1714.8	36.6
90°-180°	2374.0	50.6
0°-180°	4687.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	20	2	20	2	20	11
95°	52	40	52	40	52	54
105°	162	154	162	154	162	170
115°	286	289	286	289	286	283
125°	417	420	417	420	417	372
135°	543	542	543	542	543	419
145°	659	658	659	658	659	412
155°	754	754	754	754	754	347
165°	819	821	819	821	819	231
175°	850	854	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	10.1	10.9	10.8	11.0	11.5	11.7	11.8	11.3	12.2	12.3	13.2
90°	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3	15.4	14.5	13.4
92.5°	29.4	29.2	29.1	28.9	28.7	28.4	27.8	27.3	26.8	26.2	25.4
95°	52.3	52.3	52.3	52.3	52.3	52.1	51.6	51.2	50.7	50.3	49.3
97.5°	81.9	81.9	81.9	81.9	81.9	81.7	81.1	80.6	80.1	79.5	78.4
100°	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.8	101.6	101.3	100.0
102.5°	125.9	125.7	125.6	125.6	125.4	125.1	124.8	124.3	123.9	123.5	122.3
105°	161.5	161.0	160.6	160.2	159.7	159.3	158.8	158.4	157.9	157.5	156.9
107.5°	196.2	196.2	196.3	196.3	196.3	196.1	195.6	195.3	194.8	194.5	194.4
110°	221.1	220.6	220.2	219.7	219.3	219.2	219.5	219.8	220.1	220.3	220.5



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	246.5	246.4	246.3	246.2	246.1	246.1	246.1	246.2	246.3	246.3	246.6
115°	285.9	286.1	286.2	286.3	286.5	286.6	286.8	287.0	287.0	287.2	287.5
117.5°	323.5	323.8	324.0	324.4	324.7	325.0	325.6	326.1	326.5	327.1	327.3
120°	352.0	351.8	351.5	351.2	350.9	351.2	351.9	352.6	353.3	354.1	354.5
122.5°	375.9	376.5	376.9	377.5	378.0	378.5	379.1	379.5	380.0	380.6	380.8
125°	417.0	417.2	417.5	417.9	418.1	418.4	418.7	419.0	419.3	419.5	419.7
127.5°	455.0	455.1	455.4	455.7	455.8	456.1	456.5	456.7	457.0	457.4	457.5
130°	479.8	480.4	481.0	481.6	482.1	482.6	482.9	483.2	483.5	483.8	483.8
132.5°	506.3	506.5	506.8	507.0	507.2	507.5	507.8	508.1	508.4	508.6	508.8
135°	542.7	543.1	543.6	544.0	544.5	544.8	545.1	545.4	545.7	546.0	546.0
137.5°	580.9	580.9	580.8	580.7	580.6	580.8	581.1	581.5	581.8	582.3	582.0
140°	604.2	604.4	604.5	604.7	604.8	604.9	605.1	605.3	605.4	605.6	605.6
142.5°	627.5	627.6	627.6	627.6	627.7	627.7	627.7	627.8	627.8	627.8	627.9
145°	659.2	659.6	660.0	660.5	660.9	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	691.2	691.3	691.5	691.6	691.8	691.9	692.1	692.1	692.2	692.4	692.5
150°	710.8	711.0	711.1	711.2	711.4	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	728.8	729.2	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.9	728.8
155°	753.9	754.4	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9	753.9
157.5°	776.1	776.7	777.2	777.7	778.2	778.2	777.8	777.3	776.9	776.4	776.5
160°	788.9	789.6	790.3	791.1	791.8	792.0	791.6	791.1	790.7	790.2	790.3
162.5°	802.1	802.9	803.6	804.3	805.0	805.0	804.2	803.4	802.6	801.8	802.0
165°	819.3	819.9	820.5	821.1	821.7	821.5	820.6	819.7	818.9	818.0	818.3
167.5°	831.6	832.6	833.5	834.4	835.3	835.3	834.4	833.6	832.7	831.8	831.7
170°	838.6	839.5	840.6	841.6	842.7	842.8	841.9	841.0	840.1	839.2	839.0
172.5°	844.4	845.3	846.4	847.4	848.5	848.5	847.5	846.5	845.5	844.5	844.5
175°	850.4	851.5	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4	850.6
177.5°	853.6	854.5	855.5	856.4	857.4	857.5	856.6	855.8	855.0	854.2	854.2
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	13.0	13.0	12.5	11.1	10.0	8.8	8.2	7.6	8.2	8.8	9.5
90°	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0	3.6	5.3	6.9
92.5°	24.5	23.7	22.9	21.6	19.7	17.8	16.1	14.2	16.1	17.8	19.7
95°	48.2	47.2	46.2	45.0	43.7	42.4	41.0	39.7	41.0	42.4	43.7
97.5°	77.1	76.0	74.7	73.6	72.5	71.5	70.4	69.4	70.4	71.5	72.5
100°	98.6	97.3	95.9	95.0	94.4	93.8	93.3	92.6	93.3	93.8	94.4
102.5°	121.1	119.8	118.7	118.0	117.7	117.4	117.3	117.0	117.3	117.4	117.7
105°	156.3	155.8	155.2	154.8	154.6	154.5	154.4	154.2	154.4	154.5	154.6
107.5°	194.3	194.2	194.1	193.9	193.8	193.6	193.4	193.2	193.4	193.6	193.8
110°	220.7	220.8	221.0	220.9	220.6	220.3	220.0	219.7	220.0	220.3	220.6





TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.8	247.1	247.4	247.4	247.4	247.4	247.3	247.3	247.3	247.4	247.4
115°	287.8	288.1	288.4	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
117.5°	327.5	327.7	327.9	328.0	327.8	327.7	327.6	327.4	327.6	327.7	327.8
120°	355.0	355.4	355.8	355.8	355.2	354.5	354.0	353.4	354.0	354.5	355.2
122.5°	380.9	381.2	381.4	381.4	381.1	380.8	380.7	380.4	380.7	380.8	381.1
125°	419.9	420.0	420.2	420.3	420.3	420.3	420.3	420.3	420.3	420.3	420.3
127.5°	457.8	458.0	458.3	458.2	457.7	457.3	456.8	456.4	456.8	457.3	457.7
130°	483.8	483.8	483.8	483.6	483.1	482.7	482.2	481.8	482.2	482.7	483.1
132.5°	508.9	509.0	509.2	509.1	508.7	508.4	508.1	507.7	508.1	508.4	508.7
135°	546.0	546.0	546.0	545.5	544.7	543.8	542.9	542.1	542.9	543.8	544.7
137.5°	581.8	581.6	581.3	581.0	580.6	580.1	579.8	579.3	579.8	580.1	580.6
140°	605.6	605.6	605.6	605.4	605.1	604.8	604.5	604.2	604.5	604.8	605.1
142.5°	628.0	628.1	628.3	628.2	627.9	627.6	627.3	627.0	627.3	627.6	627.9
145°	661.6	661.4	661.2	660.8	660.3	659.7	659.1	658.5	659.1	659.7	660.3
147.5°	692.6	692.8	692.9	692.6	691.9	691.2	690.5	689.7	690.5	691.2	691.9
150°	711.5	711.5	711.5	711.1	710.6	710.0	709.4	708.8	709.4	710.0	710.6
152.5°	728.7	728.5	728.4	728.3	727.9	727.5	727.2	726.8	727.2	727.5	727.9
155°	754.1	754.2	754.4	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
157.5°	776.5	776.5	776.6	776.7	776.9	777.2	777.5	777.8	777.5	777.2	776.9
160°	790.5	790.7	790.8	790.9	791.1	791.2	791.4	791.6	791.4	791.2	791.1
162.5°	802.2	802.3	802.5	802.7	803.1	803.4	803.9	804.2	803.9	803.4	803.1
165°	818.6	818.9	819.2	819.6	820.0	820.5	820.9	821.4	820.9	820.5	820.0
167.5°	831.7	831.7	831.6	832.0	832.6	833.2	833.8	834.4	833.8	833.2	832.6
170°	838.9	838.7	838.6	838.9	839.6	840.3	841.1	841.9	841.1	840.3	839.6
172.5°	844.5	844.4	844.4	844.6	845.3	845.9	846.5	847.1	846.5	845.9	845.3
175°	850.7	850.9	851.0	851.5	852.2	852.9	853.6	854.4	853.6	852.9	852.2
177.5°	854.2	854.2	854.2	854.4	855.1	855.6	856.2	856.8	856.2	855.6	855.1
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	10.6	10.9	12.2	13.0	14.1	15.7	16.4	19.6	21.0	22.5	25.1
90°	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3	17.2	18.1	18.6
92.5°	21.6	22.9	23.7	24.5	25.4	26.2	26.8	27.3	27.8	28.4	28.7
95°	45.0	46.2	47.2	48.2	49.3	50.3	50.7	51.2	51.6	52.1	52.3
97.5°	73.6	74.7	76.0	77.1	78.4	79.5	80.1	80.6	81.1	81.7	81.9
100°	95.0	95.9	97.3	98.6	100.0	101.3	101.6	101.8	102.1	102.5	102.5
102.5°	118.0	118.7	119.8	121.1	122.3	123.5	123.9	124.3	124.8	125.1	125.4
105°	154.8	155.2	155.8	156.3	156.9	157.5	157.9	158.4	158.8	159.3	159.7
107.5°	193.9	194.1	194.2	194.3	194.4	194.5	194.8	195.3	195.6	196.1	196.3
110°	220.9	221.0	220.8	220.7	220.5	220.3	220.1	219.8	219.5	219.2	219.3



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	247.4	247.4	247.1	246.8	246.6	246.3	246.3	246.2	246.1	246.1	246.1
115°	288.6	288.4	288.1	287.8	287.5	287.2	287.0	287.0	286.8	286.6	286.5
117.5°	328.0	327.9	327.7	327.5	327.3	327.1	326.5	326.1	325.6	325.0	324.7
120°	355.8	355.8	355.4	355.0	354.5	354.1	353.3	352.6	351.9	351.2	350.9
122.5°	381.4	381.4	381.2	380.9	380.8	380.6	380.0	379.5	379.1	378.5	378.0
125°	420.3	420.2	420.0	419.9	419.7	419.5	419.3	419.0	418.7	418.4	418.1
127.5°	458.2	458.3	458.0	457.8	457.5	457.4	457.0	456.7	456.5	456.1	455.8
130°	483.6	483.8	483.8	483.8	483.8	483.8	483.5	483.2	482.9	482.6	482.1
132.5°	509.1	509.2	509.0	508.9	508.8	508.6	508.4	508.1	507.8	507.5	507.2
135°	545.5	546.0	546.0	546.0	546.0	546.0	545.7	545.4	545.1	544.8	544.5
137.5°	581.0	581.3	581.6	581.8	582.0	582.3	581.8	581.5	581.1	580.8	580.6
140°	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.3	605.1	604.9	604.8
142.5°	628.2	628.3	628.1	628.0	627.9	627.8	627.8	627.8	627.7	627.7	627.7
145°	660.8	661.2	661.4	661.6	661.6	661.8	661.6	661.6	661.4	661.2	660.9
147.5°	692.6	692.9	692.8	692.6	692.5	692.4	692.2	692.1	692.1	691.9	691.8
150°	711.1	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.4
152.5°	728.3	728.4	728.5	728.7	728.8	728.9	729.2	729.6	730.0	730.3	730.3
155°	754.5	754.4	754.2	754.1	753.9	753.9	754.4	755.0	755.5	756.2	756.2
157.5°	776.7	776.6	776.5	776.5	776.5	776.4	776.9	777.3	777.8	778.2	778.2
160°	790.9	790.8	790.7	790.5	790.3	790.2	790.7	791.1	791.6	792.0	791.8
162.5°	802.7	802.5	802.3	802.2	802.0	801.8	802.6	803.4	804.2	805.0	805.0
165°	819.6	819.2	818.9	818.6	818.3	818.0	818.9	819.7	820.6	821.5	821.7
167.5°	832.0	831.6	831.7	831.7	831.7	831.8	832.7	833.6	834.4	835.3	835.3
170°	838.9	838.6	838.7	838.9	839.0	839.2	840.1	841.0	841.9	842.8	842.7
172.5°	844.6	844.4	844.4	844.5	844.5	844.5	845.5	846.5	847.5	848.5	848.5
175°	851.5	851.0	850.9	850.7	850.6	850.4	851.5	852.5	853.5	854.5	854.5
177.5°	854.4	854.2	854.2	854.2	854.2	854.2	855.0	855.8	856.6	857.5	857.4
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	26.0	26.3	27.2	27.8	27.2	26.3	26.0	25.1	22.5	21.0	19.6
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3
92.5°	28.9	29.1	29.2	29.4	29.2	29.1	28.9	28.7	28.4	27.8	27.3
95°	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.1	51.6	51.2
97.5°	81.9	81.9	81.9	81.9	81.9	81.9	81.9	81.9	81.7	81.1	80.6
100°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.8
102.5°	125.6	125.6	125.7	125.9	125.7	125.6	125.6	125.4	125.1	124.8	124.3
105°	160.2	160.6	161.0	161.5	161.0	160.6	160.2	159.7	159.3	158.8	158.4
107.5°	196.3	196.3	196.2	196.2	196.2	196.3	196.3	196.3	196.1	195.6	195.3
110°	219.7	220.2	220.6	221.1	220.6	220.2	219.7	219.3	219.2	219.5	219.8



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	246.2	246.3	246.4	246.5	246.4	246.3	246.2	246.1	246.1	246.1	246.2
115°	286.3	286.2	286.1	285.9	286.1	286.2	286.3	286.5	286.6	286.8	287.0
117.5°	324.4	324.0	323.8	323.5	323.8	324.0	324.4	324.7	325.0	325.6	326.1
120°	351.2	351.5	351.8	352.0	351.8	351.5	351.2	350.9	351.2	351.9	352.6
122.5°	377.5	376.9	376.5	375.9	376.5	376.9	377.5	378.0	378.5	379.1	379.5
125°	417.9	417.5	417.2	417.0	417.2	417.5	417.9	418.1	418.4	418.7	419.0
127.5°	455.7	455.4	455.1	455.0	455.1	455.4	455.7	455.8	456.1	456.5	456.7
130°	481.6	481.0	480.4	479.8	480.4	481.0	481.6	482.1	482.6	482.9	483.2
132.5°	507.0	506.8	506.5	506.3	506.5	506.8	507.0	507.2	507.5	507.8	508.1
135°	544.0	543.6	543.1	542.7	543.1	543.6	544.0	544.5	544.8	545.1	545.4
137.5°	580.7	580.8	580.9	580.9	580.9	580.8	580.7	580.6	580.8	581.1	581.5
140°	604.7	604.5	604.4	604.2	604.4	604.5	604.7	604.8	604.9	605.1	605.3
142.5°	627.6	627.6	627.6	627.5	627.6	627.6	627.6	627.7	627.7	627.7	627.8
145°	660.5	660.0	659.6	659.2	659.6	660.0	660.5	660.9	661.2	661.4	661.6
147.5°	691.6	691.5	691.3	691.2	691.3	691.5	691.6	691.8	691.9	692.1	692.1
150°	711.2	711.1	711.0	710.8	711.0	711.1	711.2	711.4	711.5	711.5	711.5
152.5°	730.0	729.6	729.2	728.8	729.2	729.6	730.0	730.3	730.3	730.0	729.6
155°	755.5	755.0	754.4	753.9	754.4	755.0	755.5	756.2	756.2	755.5	755.0
157.5°	777.7	777.2	776.7	776.1	776.7	777.2	777.7	778.2	778.2	777.8	777.3
160°	791.1	790.3	789.6	788.9	789.6	790.3	791.1	791.8	792.0	791.6	791.1
162.5°	804.3	803.6	802.9	802.1	802.9	803.6	804.3	805.0	805.0	804.2	803.4
165°	821.1	820.5	819.9	819.3	819.9	820.5	821.1	821.7	821.5	820.6	819.7
167.5°	834.4	833.5	832.6	831.6	832.6	833.5	834.4	835.3	835.3	834.4	833.6
170°	841.6	840.6	839.5	838.6	839.5	840.6	841.6	842.7	842.8	841.9	841.0
172.5°	847.4	846.4	845.3	844.4	845.3	846.4	847.4	848.5	848.5	847.5	846.5
175°	853.5	852.5	851.5	850.4	851.5	852.5	853.5	854.5	854.5	853.5	852.5
177.5°	856.4	855.5	854.5	853.6	854.5	855.5	856.4	857.4	857.5	856.6	855.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	16.4	15.7	14.1	13.0	12.2	10.9	10.6	9.5	8.8	8.2	7.6
90°	15.4	14.5	13.4	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0
92.5°	26.8	26.2	25.4	24.5	23.7	22.9	21.6	19.7	17.8	16.1	14.2
95°	50.7	50.3	49.3	48.2	47.2	46.2	45.0	43.7	42.4	41.0	39.7
97.5°	80.1	79.5	78.4	77.1	76.0	74.7	73.6	72.5	71.5	70.4	69.4
100°	101.6	101.3	100.0	98.6	97.3	95.9	95.0	94.4	93.8	93.3	92.6
102.5°	123.9	123.5	122.3	121.1	119.8	118.7	118.0	117.7	117.4	117.3	117.0
105°	157.9	157.5	156.9	156.3	155.8	155.2	154.8	154.6	154.5	154.4	154.2
107.5°	194.8	194.5	194.4	194.3	194.2	194.1	193.9	193.8	193.6	193.4	193.2
110°	220.1	220.3	220.5	220.7	220.8	221.0	220.9	220.6	220.3	220.0	219.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	246.3	246.3	246.6	246.8	247.1	247.4	247.4	247.4	247.4	247.3	247.3
115°	287.0	287.2	287.5	287.8	288.1	288.4	288.6	288.6	288.6	288.6	288.6
117.5°	326.5	327.1	327.3	327.5	327.7	327.9	328.0	327.8	327.7	327.6	327.4
120°	353.3	354.1	354.5	355.0	355.4	355.8	355.8	355.2	354.5	354.0	353.4
122.5°	380.0	380.6	380.8	380.9	381.2	381.4	381.4	381.1	380.8	380.7	380.4
125°	419.3	419.5	419.7	419.9	420.0	420.2	420.3	420.3	420.3	420.3	420.3
127.5°	457.0	457.4	457.5	457.8	458.0	458.3	458.2	457.7	457.3	456.8	456.4
130°	483.5	483.8	483.8	483.8	483.8	483.8	483.6	483.1	482.7	482.2	481.8
132.5°	508.4	508.6	508.8	508.9	509.0	509.2	509.1	508.7	508.4	508.1	507.7
135°	545.7	546.0	546.0	546.0	546.0	546.0	545.5	544.7	543.8	542.9	542.1
137.5°	581.8	582.3	582.0	581.8	581.6	581.3	581.0	580.6	580.1	579.8	579.3
140°	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.1	604.8	604.5	604.2
142.5°	627.8	627.8	627.9	628.0	628.1	628.3	628.2	627.9	627.6	627.3	627.0
145°	661.6	661.8	661.6	661.6	661.4	661.2	660.8	660.3	659.7	659.1	658.5
147.5°	692.2	692.4	692.5	692.6	692.8	692.9	692.6	691.9	691.2	690.5	689.7
150°	711.5	711.5	711.5	711.5	711.5	711.5	711.1	710.6	710.0	709.4	708.8
152.5°	729.2	728.9	728.8	728.7	728.5	728.4	728.3	727.9	727.5	727.2	726.8
155°	754.4	753.9	753.9	754.1	754.2	754.4	754.5	754.5	754.5	754.5	754.5
157.5°	776.9	776.4	776.5	776.5	776.5	776.6	776.7	776.9	777.2	777.5	777.8
160°	790.7	790.2	790.3	790.5	790.7	790.8	790.9	791.1	791.2	791.4	791.6
162.5°	802.6	801.8	802.0	802.2	802.3	802.5	802.7	803.1	803.4	803.9	804.2
165°	818.9	818.0	818.3	818.6	818.9	819.2	819.6	820.0	820.5	820.9	821.4
167.5°	832.7	831.8	831.7	831.7	831.7	831.6	832.0	832.6	833.2	833.8	834.4
170°	840.1	839.2	839.0	838.9	838.7	838.6	838.9	839.6	840.3	841.1	841.9
172.5°	845.5	844.5	844.5	844.5	844.4	844.4	844.6	845.3	845.9	846.5	847.1
175°	851.5	850.4	850.6	850.7	850.9	851.0	851.5	852.2	852.9	853.6	854.4
177.5°	855.0	854.2	854.2	854.2	854.2	854.2	854.4	855.1	855.6	856.2	856.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	8.2	8.8	10.0	11.1	12.5	13.0	13.0	13.2	12.3	12.2	11.3
90°	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3
92.5°	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8	27.3
95°	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7	51.2
97.5°	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1	80.6
100°	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6	101.8
102.5°	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9	124.3
105°	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9	158.4
107.5°	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8	195.3
110°	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1	219.8





TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3	246.2
115°	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0	287.0
117.5°	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5	326.1
120°	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3	352.6
122.5°	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0	379.5
125°	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3	419.0
127.5°	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0	456.7
130°	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5	483.2
132.5°	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4	508.1
135°	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7	545.4
137.5°	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8	581.5
140°	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.3
142.5°	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8	627.8
145°	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6	661.6
147.5°	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2	692.1
150°	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2	729.6
155°	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4	755.0
157.5°	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9	777.3
160°	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7	791.1
162.5°	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6	803.4
165°	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9	819.7
167.5°	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7	833.6
170°	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1	841.0
172.5°	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5	846.5
175°	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5	852.5
177.5°	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0	855.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	11.8	11.7	11.5	11.0	10.8	10.9	10.1
90°	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.5	219.2	219.3	219.7	220.2	220.6	221.1



TEST NUMBER: P332752-940

CATALOG NUMBER: S124DIW-S575D770U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)