

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333016-940

Luminaire Tested: **S124RDIW-S350D470U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333016-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D470U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2775.1 lumens  
Efficiency: N/A  
Efficacy: 120.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	48	47	47	41
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4229	4229	4229	4229
5°	4905	4241	3749	4241
10°	5802	4223	3345	4223
15°	6702	4184	2875	4184
20°	7462	4130	2600	4130
25°	7704	4077	2414	4077
30°	6743	4013	2302	4013
35°	5249	3918	2234	3918
40°	3936	3810	2197	3810
45°	3108	3635	2177	3635
50°	2624	3435	2115	3435
55°	2287	3215	2001	3215
60°	2057	2985	1773	2985
65°	1815	2737	1524	2737
70°	1633	2481	1374	2481
75°	1369	2196	1170	2196
80°	1158	1874	1097	1874
85°	973	1473	973	1473



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.8	1.8
10°-20°	153.1	5.5
20°-30°	239.4	8.6
30°-40°	266.2	9.6
40°-50°	236.2	8.5
50°-60°	184.0	6.6
60°-70°	120.5	4.3
70°-80°	59.3	2.1
80°-90°	16.2	0.6
90°-100°	34.5	1.2
100°-110°	102.1	3.7
110°-120°	173.3	6.2
120°-130°	228.5	8.2
130°-140°	256.6	9.2
140°-150°	252.1	9.1
150°-160°	212.1	7.6
160°-170°	141.1	5.1
170°-180°	49.4	1.8
0°-30°	443.3	16.0
0°-40°	709.5	25.6
0°-60°	1129.7	40.7
0°-90°	1325.6	47.8
90°-120°	309.8	11.2
90°-150°	1047.0	37.7
90°-180°	1450.0	52.2
0°-180°	2775.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	524	524	524	524	524	
5°	605	523	463	523	605	61
15°	802	501	344	501	802	228
25°	865	458	271	458	865	384
35°	533	398	227	398	533	334
45°	272	318	191	318	272	216
55°	162	228	142	228	162	148
65°	95	143	80	143	95	96
75°	44	70	38	70	44	48
85°	10	16	10	16	10	12
90°	12	1	12	1	12	7
95°	32	24	32	24	32	33
105°	99	94	99	94	99	104
115°	175	176	175	176	175	173
125°	255	256	255	256	255	227
135°	331	331	331	331	331	256
145°	402	402	402	402	402	252
155°	460	461	460	461	460	212
165°	500	501	500	501	500	141
175°	519	522	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	552.5	554.0	552.5	552.3	550.6	550.1	549.5	547.2	543.2	540.8	541.4
5°	605.3	610.6	607.6	607.2	602.5	597.9	594.9	588.2	580.9	576.1	572.1
7.5°	666.3	669.3	667.4	664.5	657.0	652.7	645.9	637.0	624.1	614.3	605.3
10°	707.8	710.3	709.5	704.0	698.6	687.3	681.0	668.6	652.3	639.4	627.4
12.5°	748.7	751.4	744.0	744.2	733.8	725.0	715.0	699.3	680.6	664.0	648.9
15°	801.9	798.5	798.5	794.3	782.7	770.5	760.2	743.7	720.1	700.3	679.3
17.5°	843.6	844.8	843.1	833.1	824.0	811.4	792.4	773.2	751.3	724.6	703.3
20°	868.6	868.6	866.7	860.0	848.2	834.6	814.2	793.3	765.4	738.6	714.6
22.5°	878.8	879.4	877.2	871.6	861.0	847.8	830.4	809.1	780.4	750.3	720.5
25°	864.9	868.9	869.2	867.8	864.6	856.6	841.6	819.9	794.2	761.4	729.3
27.5°	794.0	799.1	803.5	810.8	820.6	825.5	826.3	815.2	792.7	761.3	729.0
30°	723.4	727.6	741.4	759.3	773.2	785.9	796.9	799.9	787.2	758.9	725.0
32.5°	645.1	650.9	664.6	683.9	707.0	728.5	753.1	765.7	765.4	748.4	717.0
35°	532.6	536.9	549.6	569.8	597.6	629.5	668.6	698.9	719.6	718.2	698.9
37.5°	429.6	434.4	447.1	464.0	491.0	530.4	568.2	610.1	648.3	669.8	663.3
40°	373.5	373.7	386.2	403.5	428.8	463.2	504.4	550.8	593.4	628.3	635.0
42.5°	329.3	329.3	337.6	356.2	374.4	406.8	446.1	492.2	542.2	582.4	600.2
45°	272.2	274.1	280.9	292.0	306.4	333.9	365.3	408.1	464.0	511.8	541.5
47.5°	230.5	233.4	237.6	246.7	258.2	276.4	302.5	341.0	386.5	438.9	481.3
50°	208.9	209.4	214.8	219.9	229.8	244.4	267.2	299.3	341.1	391.5	438.5
52.5°	190.4	190.3	193.6	200.0	208.0	219.4	237.8	267.0	304.1	349.3	397.9
55°	162.5	163.5	166.1	171.1	177.3	185.3	199.8	221.8	250.9	289.5	333.7
57.5°	141.3	141.9	143.8	146.0	151.6	157.5	168.4	183.6	208.1	239.8	280.9
60°	127.4	127.7	128.3	131.4	135.9	141.4	148.8	161.7	182.4	211.2	243.8
62.5°	114.0	114.3	115.3	117.6	121.1	124.8	132.6	142.9	160.1	184.8	214.0
65°	95.0	95.1	96.7	97.5	100.2	103.6	109.3	116.3	128.1	148.8	170.9
67.5°	79.4	79.4	79.5	80.6	82.5	84.7	88.1	93.7	102.6	115.3	134.8
70°	69.2	69.2	69.6	70.3	71.3	73.2	75.2	79.4	85.9	96.2	111.2
72.5°	59.7	59.9	60.4	60.5	61.0	62.6	64.0	66.7	71.5	79.4	91.5
75°	43.9	44.5	45.6	46.5	47.5	47.3	48.8	50.5	51.9	56.5	63.5
77.5°	32.6	32.4	32.5	33.2	33.3	33.5	34.6	35.8	37.0	39.1	41.6
80°	24.9	24.9	25.5	25.8	25.5	25.8	26.8	27.5	27.8	28.7	31.0
82.5°	18.8	19.2	19.0	19.2	19.3	19.5	20.4	20.5	21.0	21.3	22.2
85°	10.5	10.8	11.0	10.5	10.5	10.5	11.0	11.1	11.6	11.4	11.9
87.5°	6.2	6.0	6.1	6.1	6.2	5.9	6.0	6.2	5.8	5.8	5.7
90°	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0	9.5	8.9	8.2
92.5°	17.9	17.8	17.7	17.7	17.5	17.3	16.9	16.7	16.3	16.0	15.5
95°	31.9	31.9	31.9	31.9	31.9	31.7	31.5	31.2	30.9	30.7	30.1
97.5°	50.0	50.0	50.0	50.0	50.0	49.8	49.6	49.2	48.9	48.6	47.8
100°	62.6	62.6	62.6	62.6	62.6	62.5	62.3	62.2	62.0	61.8	61.0
102.5°	76.9	76.8	76.7	76.6	76.6	76.4	76.2	75.9	75.6	75.4	74.6
105°	98.6	98.4	98.1	97.8	97.6	97.3	97.0	96.8	96.4	96.1	95.8
107.5°	119.8	119.8	119.8	119.8	119.8	119.8	119.5	119.2	119.0	118.7	118.7
110°	134.9	134.6	134.4	134.1	133.8	133.8	134.0	134.2	134.4	134.6	134.6



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.4	150.4	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.4	150.5
115°	174.6	174.7	174.8	174.9	175.0	175.0	175.1	175.2	175.3	175.4	175.6
117.5°	197.5	197.7	197.9	198.0	198.2	198.5	198.8	199.1	199.4	199.7	199.8
120°	215.0	214.8	214.6	214.5	214.3	214.4	214.8	215.3	215.7	216.2	216.4
122.5°	229.5	229.8	230.2	230.5	230.8	231.1	231.4	231.8	232.0	232.4	232.5
125°	254.6	254.8	254.9	255.1	255.3	255.5	255.7	255.8	256.0	256.2	256.3
127.5°	277.8	277.9	278.0	278.2	278.3	278.5	278.7	278.8	279.0	279.2	279.4
130°	292.9	293.3	293.6	294.0	294.4	294.6	294.8	295.0	295.2	295.3	295.3
132.5°	309.2	309.2	309.4	309.5	309.7	309.9	310.0	310.2	310.4	310.6	310.7
135°	331.4	331.6	331.9	332.2	332.4	332.6	332.8	333.0	333.1	333.3	333.3
137.5°	354.7	354.6	354.5	354.5	354.5	354.5	354.8	355.0	355.3	355.5	355.3
140°	368.9	369.0	369.1	369.2	369.3	369.3	369.4	369.5	369.6	369.7	369.7
142.5°	383.2	383.2	383.2	383.2	383.2	383.3	383.3	383.3	383.3	383.3	383.3
145°	402.4	402.7	403.0	403.2	403.5	403.7	403.8	403.9	403.9	404.0	403.9
147.5°	422.0	422.1	422.2	422.3	422.4	422.5	422.5	422.6	422.7	422.8	422.8
150°	434.0	434.1	434.2	434.3	434.4	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	445.0	445.2	445.4	445.7	445.9	445.9	445.7	445.5	445.2	445.1	445.0
155°	460.2	460.6	460.9	461.3	461.6	461.6	461.3	460.9	460.6	460.2	460.3
157.5°	473.9	474.2	474.5	474.8	475.1	475.1	474.8	474.6	474.3	474.0	474.0
160°	481.6	482.1	482.6	483.0	483.5	483.6	483.3	483.0	482.8	482.5	482.6
162.5°	489.7	490.2	490.6	491.1	491.5	491.5	491.1	490.5	490.1	489.5	489.6
165°	500.2	500.6	501.0	501.3	501.7	501.6	501.1	500.5	500.0	499.4	499.6
167.5°	507.7	508.3	508.9	509.4	510.0	510.0	509.4	508.9	508.4	507.8	507.8
170°	511.9	512.6	513.2	513.8	514.4	514.5	514.0	513.4	512.9	512.4	512.3
172.5°	515.5	516.1	516.7	517.4	518.0	518.0	517.5	516.8	516.2	515.6	515.6
175°	519.2	519.9	520.5	521.1	521.7	521.7	521.1	520.5	519.9	519.2	519.3
177.5°	521.2	521.7	522.4	522.9	523.4	523.5	523.0	522.5	522.0	521.5	521.5
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	539.7	537.3	536.1	533.4	530.2	528.5	527.0	524.8	521.9	518.9	516.7
5°	567.0	562.0	555.6	548.0	541.4	534.8	529.1	523.3	516.8	510.1	503.4
7.5°	595.1	585.2	574.4	562.0	549.9	538.9	528.7	519.1	508.1	498.2	489.3
10°	614.7	601.3	586.3	570.4	554.6	540.9	527.4	515.1	501.7	489.6	479.5
12.5°	630.6	614.7	596.7	577.0	557.9	541.4	525.8	509.9	494.5	481.5	468.0
15°	656.9	635.3	611.0	587.3	562.7	540.0	519.2	500.6	483.0	464.7	451.8
17.5°	675.1	649.3	619.7	591.4	562.2	535.6	511.5	489.4	469.1	450.4	435.1
20°	685.9	657.4	624.6	592.4	559.6	531.2	505.2	480.7	459.9	439.6	423.7
22.5°	692.0	660.4	624.6	590.8	557.0	526.1	497.7	472.2	449.4	429.1	411.6
25°	693.9	660.1	623.7	584.8	547.7	515.0	485.4	457.7	432.4	412.1	393.6
27.5°	691.2	651.4	614.0	574.2	535.8	501.4	470.4	441.3	416.0	394.2	375.1
30°	687.2	644.5	604.4	563.0	524.2	491.1	458.3	430.5	404.1	381.6	362.4
32.5°	678.3	636.1	592.9	550.5	511.2	477.1	446.0	418.0	392.2	369.1	348.7
35°	660.9	618.1	571.3	527.8	489.2	453.7	424.6	397.6	372.9	348.2	326.7
37.5°	638.0	594.3	547.7	500.1	461.4	427.9	401.3	375.9	351.8	329.2	305.4
40°	616.4	576.6	528.4	481.2	441.5	409.2	384.5	361.5	337.2	314.9	291.1
42.5°	590.3	556.3	507.7	460.2	421.1	389.9	366.9	344.5	322.4	300.7	275.8
45°	546.6	520.8	475.3	429.7	390.2	359.4	338.3	318.4	299.1	278.4	254.9
47.5°	496.5	479.1	439.8	393.1	356.6	328.9	308.4	292.2	275.8	255.1	234.6
50°	461.7	450.6	412.6	370.0	335.1	309.6	288.7	273.5	259.8	240.0	221.6
52.5°	424.6	418.7	386.6	345.8	312.2	287.1	269.3	255.7	241.7	225.2	208.1
55°	368.0	371.2	344.0	308.7	277.1	256.0	239.8	228.4	216.5	202.6	189.3
57.5°	310.2	321.8	303.5	272.6	242.9	223.4	211.2	201.6	191.6	180.1	168.7
60°	275.6	285.3	275.0	247.7	221.8	203.7	192.3	184.9	175.0	164.4	155.8
62.5°	241.8	252.3	246.1	224.1	200.0	184.4	174.3	167.5	160.1	150.9	141.9
65°	199.5	206.2	203.2	188.1	170.9	157.7	148.4	143.3	136.5	129.8	121.8
67.5°	152.8	165.8	164.1	156.0	141.2	130.8	124.8	120.3	114.1	109.1	103.7
70°	125.6	137.6	137.4	130.8	122.8	113.2	108.9	105.1	99.6	94.8	90.3
72.5°	102.8	113.8	115.5	110.4	105.0	97.6	93.5	91.0	85.6	82.3	78.6
75°	72.0	80.0	82.1	82.1	79.5	75.8	72.1	70.4	66.7	63.8	61.6
77.5°	47.2	52.3	55.6	56.3	56.7	55.4	52.4	51.3	48.3	47.3	45.3
80°	33.3	36.7	40.5	41.8	42.8	42.4	41.2	40.3	37.5	36.5	35.7
82.5°	23.0	24.9	28.0	30.9	30.5	31.7	30.5	29.9	27.7	27.4	26.6
85°	12.0	12.2	12.7	14.5	15.6	16.1	16.2	15.9	15.2	15.2	13.7
87.5°	5.5	5.3	5.4	5.3	5.3	5.7	6.0	6.0	5.7	5.4	5.1
90°	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2	2.2	3.2	4.2
92.5°	15.0	14.5	14.0	13.2	12.0	10.9	9.8	8.6	9.8	10.9	12.0
95°	29.4	28.8	28.2	27.5	26.7	25.9	25.1	24.3	25.1	25.9	26.7
97.5°	47.1	46.4	45.7	44.9	44.3	43.6	43.0	42.4	43.0	43.6	44.3
100°	60.2	59.4	58.6	58.1	57.6	57.2	56.9	56.5	56.9	57.2	57.6
102.5°	73.9	73.2	72.5	72.1	71.9	71.7	71.6	71.4	71.6	71.7	71.9
105°	95.4	95.1	94.7	94.5	94.4	94.3	94.3	94.2	94.3	94.3	94.4
107.5°	118.6	118.6	118.5	118.4	118.3	118.2	118.1	118.0	118.1	118.2	118.3
110°	134.7	134.8	134.9	134.8	134.6	134.5	134.3	134.1	134.3	134.5	134.6





TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	150.7	150.9	151.1	151.1	151.1	151.1	151.0	151.0	151.0	151.1	151.1
115°	175.8	175.9	176.1	176.2	176.2	176.2	176.2	176.2	176.2	176.2	176.2
117.5°	199.9	200.1	200.2	200.2	200.2	200.1	200.0	199.9	200.0	200.1	200.2
120°	216.7	217.0	217.2	217.2	216.9	216.5	216.2	215.8	216.2	216.5	216.9
122.5°	232.6	232.7	232.8	232.8	232.6	232.6	232.4	232.3	232.4	232.6	232.6
125°	256.4	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.5
127.5°	279.5	279.6	279.8	279.7	279.5	279.2	278.9	278.7	278.9	279.2	279.5
130°	295.3	295.3	295.3	295.2	295.0	294.7	294.4	294.2	294.4	294.7	295.0
132.5°	310.7	310.8	310.9	310.8	310.6	310.4	310.2	310.0	310.2	310.4	310.6
135°	333.3	333.3	333.3	333.1	332.5	332.0	331.4	330.9	331.4	332.0	332.5
137.5°	355.3	355.1	354.9	354.7	354.5	354.2	354.0	353.7	354.0	354.2	354.5
140°	369.7	369.7	369.7	369.6	369.4	369.3	369.1	368.9	369.1	369.3	369.4
142.5°	383.4	383.5	383.6	383.5	383.3	383.2	383.0	382.8	383.0	383.2	383.3
145°	403.9	403.8	403.7	403.5	403.1	402.8	402.4	402.1	402.4	402.8	403.1
147.5°	422.8	422.9	423.0	422.8	422.4	422.0	421.5	421.2	421.5	422.0	422.4
150°	434.4	434.4	434.4	434.2	433.8	433.5	433.1	432.7	433.1	433.5	433.8
152.5°	444.9	444.8	444.8	444.6	444.4	444.2	444.0	443.7	444.0	444.2	444.4
155°	460.4	460.5	460.6	460.7	460.7	460.7	460.7	460.7	460.7	460.7	460.7
157.5°	474.1	474.1	474.1	474.2	474.4	474.6	474.7	474.8	474.7	474.6	474.4
160°	482.7	482.8	482.9	483.0	483.0	483.1	483.2	483.3	483.2	483.1	483.0
162.5°	489.7	489.8	489.9	490.1	490.4	490.5	490.8	491.1	490.8	490.5	490.4
165°	499.8	500.0	500.2	500.3	500.6	500.9	501.1	501.4	501.1	500.9	500.6
167.5°	507.8	507.7	507.7	507.9	508.4	508.7	509.1	509.4	509.1	508.7	508.4
170°	512.2	512.1	512.0	512.2	512.6	513.1	513.5	514.0	513.5	513.1	512.6
172.5°	515.6	515.5	515.5	515.7	516.1	516.5	516.8	517.2	516.8	516.5	516.1
175°	519.4	519.5	519.6	519.9	520.3	520.8	521.2	521.7	521.2	520.8	520.3
177.5°	521.5	521.5	521.5	521.7	522.0	522.4	522.7	523.1	522.7	522.4	522.0
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	514.3	512.6	510.5	507.9	504.9	502.2	501.0	502.0	502.6	501.1	501.0
5°	498.6	493.4	489.2	482.9	477.8	473.6	470.6	469.3	469.8	466.4	465.6
7.5°	481.1	474.8	467.9	460.4	453.4	447.2	444.0	442.2	438.5	437.0	434.4
10°	469.8	461.4	454.6	445.7	437.7	430.3	426.7	423.7	420.2	418.5	414.9
12.5°	458.2	448.4	440.9	431.7	423.5	414.6	411.2	405.7	400.1	396.5	391.9
15°	441.7	429.9	420.8	409.8	400.1	390.0	380.9	370.8	367.0	359.0	354.4
17.5°	422.5	410.5	399.3	384.6	369.6	357.0	347.3	337.6	331.8	326.7	324.3
20°	409.8	398.9	383.3	366.1	349.5	335.6	327.7	321.4	315.0	311.5	309.0
22.5°	397.9	383.8	365.7	347.2	330.6	319.7	313.1	306.6	301.4	298.0	294.6
25°	377.7	359.4	340.2	319.1	307.7	298.2	291.1	285.7	282.6	278.1	276.4
27.5°	357.1	334.8	313.7	299.5	287.7	278.9	272.7	268.8	264.7	261.9	259.7
30°	341.3	318.7	299.7	286.1	274.1	267.0	261.9	257.3	254.0	251.7	250.1
32.5°	325.6	303.0	287.0	272.5	263.0	256.0	250.6	247.1	244.6	241.7	240.6
35°	302.8	282.8	268.9	255.7	246.1	239.8	235.5	231.9	229.8	229.0	228.4
37.5°	281.0	264.6	249.6	238.9	230.2	225.2	220.3	218.5	217.0	215.5	216.2
40°	267.2	251.7	238.4	227.1	220.1	214.6	211.7	209.6	208.3	208.3	208.3
42.5°	255.2	240.1	227.1	217.0	210.0	205.4	202.1	200.3	199.8	199.7	200.7
45°	236.6	222.7	209.6	201.1	195.2	190.6	188.7	187.2	187.2	188.1	188.2
47.5°	218.1	205.1	194.6	185.1	179.7	176.8	175.1	174.4	174.5	175.3	176.3
50°	206.8	193.9	183.6	175.1	170.1	167.4	165.9	165.4	165.9	165.9	167.4
52.5°	194.5	183.0	172.8	165.7	160.0	157.4	156.6	156.0	156.2	156.9	157.6
55°	176.5	166.1	156.4	149.6	145.4	143.7	141.8	142.0	141.6	142.0	142.0
57.5°	158.3	149.0	140.0	134.6	130.9	128.5	126.4	127.0	126.4	126.3	125.9
60°	146.7	136.5	129.4	124.5	120.3	118.2	116.3	116.7	116.1	115.7	114.8
62.5°	134.0	125.6	118.7	114.0	110.7	108.3	106.3	105.9	104.4	103.0	101.1
65°	115.7	108.7	102.5	98.2	95.0	93.1	91.6	90.3	87.1	83.8	82.1
67.5°	97.8	92.7	87.0	83.3	80.7	78.3	75.4	73.3	70.4	68.5	67.4
70°	86.3	81.5	76.6	73.0	70.3	67.9	64.8	63.3	61.2	60.4	59.3
72.5°	75.3	70.8	66.3	63.0	60.2	58.3	55.8	54.4	53.4	53.1	52.1
75°	58.7	55.1	51.7	48.8	46.5	45.1	44.1	43.1	42.6	40.8	39.7
77.5°	42.8	40.4	38.3	36.2	34.6	33.7	31.7	30.5	29.8	28.9	28.6
80°	33.3	31.7	29.5	28.3	25.9	25.1	24.3	24.1	23.8	23.6	23.5
82.5°	25.1	23.4	21.3	20.5	19.9	19.4	18.9	18.6	18.5	18.5	18.5
85°	12.7	11.9	11.9	11.6	11.4	11.1	11.0	11.0	10.8	11.0	10.8
87.5°	5.3	5.3	5.4	5.2	5.5	5.6	5.6	5.7	6.0	5.8	5.8
90°	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0	10.5	11.1	11.4
92.5°	13.2	14.0	14.5	15.0	15.5	16.0	16.3	16.7	16.9	17.3	17.5
95°	27.5	28.2	28.8	29.4	30.1	30.7	30.9	31.2	31.5	31.7	31.9
97.5°	44.9	45.7	46.4	47.1	47.8	48.6	48.9	49.2	49.6	49.8	50.0
100°	58.1	58.6	59.4	60.2	61.0	61.8	62.0	62.2	62.3	62.5	62.6
102.5°	72.1	72.5	73.2	73.9	74.6	75.4	75.6	75.9	76.2	76.4	76.6
105°	94.5	94.7	95.1	95.4	95.8	96.1	96.4	96.8	97.0	97.3	97.6
107.5°	118.4	118.5	118.6	118.6	118.7	118.7	119.0	119.2	119.5	119.8	119.8
110°	134.8	134.9	134.8	134.7	134.6	134.6	134.4	134.2	134.0	133.8	133.8



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	151.1	151.1	150.9	150.7	150.5	150.4	150.3	150.3	150.3	150.3	150.3
115°	176.2	176.1	175.9	175.8	175.6	175.4	175.3	175.2	175.1	175.0	175.0
117.5°	200.2	200.2	200.1	199.9	199.8	199.7	199.4	199.1	198.8	198.5	198.2
120°	217.2	217.2	217.0	216.7	216.4	216.2	215.7	215.3	214.8	214.4	214.3
122.5°	232.8	232.8	232.7	232.6	232.5	232.4	232.0	231.8	231.4	231.1	230.8
125°	256.5	256.5	256.5	256.4	256.3	256.2	256.0	255.8	255.7	255.5	255.3
127.5°	279.7	279.8	279.6	279.5	279.4	279.2	279.0	278.8	278.7	278.5	278.3
130°	295.2	295.3	295.3	295.3	295.3	295.3	295.2	295.0	294.8	294.6	294.4
132.5°	310.8	310.9	310.8	310.7	310.7	310.6	310.4	310.2	310.0	309.9	309.7
135°	333.1	333.3	333.3	333.3	333.3	333.3	333.1	333.0	332.8	332.6	332.4
137.5°	354.7	354.9	355.1	355.3	355.3	355.5	355.3	355.0	354.8	354.5	354.5
140°	369.6	369.7	369.7	369.7	369.7	369.7	369.6	369.5	369.4	369.3	369.3
142.5°	383.5	383.6	383.5	383.4	383.3	383.3	383.3	383.3	383.3	383.3	383.2
145°	403.5	403.7	403.8	403.9	403.9	404.0	403.9	403.9	403.8	403.7	403.5
147.5°	422.8	423.0	422.9	422.8	422.8	422.8	422.7	422.6	422.5	422.5	422.4
150°	434.2	434.4	434.4	434.4	434.4	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	444.6	444.8	444.8	444.9	445.0	445.1	445.2	445.5	445.7	445.9	445.9
155°	460.7	460.6	460.5	460.4	460.3	460.2	460.6	460.9	461.3	461.6	461.6
157.5°	474.2	474.1	474.1	474.1	474.0	474.0	474.3	474.6	474.8	475.1	475.1
160°	483.0	482.9	482.8	482.7	482.6	482.5	482.8	483.0	483.3	483.6	483.5
162.5°	490.1	489.9	489.8	489.7	489.6	489.5	490.1	490.5	491.1	491.5	491.5
165°	500.3	500.2	500.0	499.8	499.6	499.4	500.0	500.5	501.1	501.6	501.7
167.5°	507.9	507.7	507.7	507.8	507.8	507.8	508.4	508.9	509.4	510.0	510.0
170°	512.2	512.0	512.1	512.2	512.3	512.4	512.9	513.4	514.0	514.5	514.4
172.5°	515.7	515.5	515.5	515.6	515.6	515.6	516.2	516.8	517.5	518.0	518.0
175°	519.9	519.6	519.5	519.4	519.3	519.2	519.9	520.5	521.1	521.7	521.7
177.5°	521.7	521.5	521.5	521.5	521.5	521.5	522.0	522.5	523.0	523.5	523.4
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	500.0	500.3	499.2	498.8	499.2	500.3	500.0	501.0	501.1	502.6	502.0
5°	463.9	463.4	462.4	462.6	462.4	463.4	463.9	465.6	466.4	469.8	469.3
7.5°	432.9	431.3	431.8	430.1	431.8	431.3	432.9	434.4	437.0	438.5	442.2
10°	414.0	411.7	409.8	408.1	409.8	411.7	414.0	414.9	418.5	420.2	423.7
12.5°	388.3	386.2	383.7	384.1	383.7	386.2	388.3	391.9	396.5	400.1	405.7
15°	351.6	348.4	343.4	344.0	343.4	348.4	351.6	354.4	359.0	367.0	370.8
17.5°	320.6	320.6	318.3	318.9	318.3	320.6	320.6	324.3	326.7	331.8	337.6
20°	304.5	303.1	303.3	302.6	303.3	303.1	304.5	309.0	311.5	315.0	321.4
22.5°	293.4	291.6	290.1	288.8	290.1	291.6	293.4	294.6	298.0	301.4	306.6
25°	274.6	273.3	271.4	271.0	271.4	273.3	274.6	276.4	278.1	282.6	285.7
27.5°	258.0	257.8	257.0	256.0	257.0	257.8	258.0	259.7	261.9	264.7	268.8
30°	248.4	248.0	247.5	246.9	247.5	248.0	248.4	250.1	251.7	254.0	257.3
32.5°	239.8	239.5	239.1	239.2	239.1	239.5	239.8	240.6	241.7	244.6	247.1
35°	227.5	227.3	226.9	226.7	226.9	227.3	227.5	228.4	229.0	229.8	231.9
37.5°	216.1	216.6	216.3	216.2	216.3	216.6	216.1	216.2	215.5	217.0	218.5
40°	208.1	208.3	208.7	208.5	208.7	208.3	208.1	208.3	208.3	208.3	209.6
42.5°	201.5	201.5	202.2	201.4	202.2	201.5	201.5	200.7	199.7	199.8	200.3
45°	189.8	191.0	190.7	190.7	190.7	191.0	189.8	188.2	188.1	187.2	187.2
47.5°	176.8	178.0	178.3	178.2	178.3	178.0	176.8	176.3	175.3	174.5	174.4
50°	168.4	168.0	168.6	168.4	168.6	168.0	168.4	167.4	165.9	165.9	165.4
52.5°	158.1	158.2	158.2	157.9	158.2	158.2	158.1	157.6	156.9	156.2	156.0
55°	142.2	142.5	142.0	142.2	142.0	142.5	142.2	142.0	142.0	141.6	142.0
57.5°	125.0	124.0	124.4	123.9	124.4	124.0	125.0	125.9	126.3	126.4	127.0
60°	112.7	111.0	110.6	109.8	110.6	111.0	112.7	114.8	115.7	116.1	116.7
62.5°	98.9	97.6	96.2	96.9	96.2	97.6	98.9	101.1	103.0	104.4	105.9
65°	80.4	79.5	78.9	79.8	78.9	79.5	80.4	82.1	83.8	87.1	90.3
67.5°	66.5	66.1	66.1	65.7	66.1	66.1	66.5	67.4	68.5	70.4	73.3
70°	59.3	58.7	58.7	58.2	58.7	58.7	59.3	59.3	60.4	61.2	63.3
72.5°	51.9	51.3	51.5	51.2	51.5	51.3	51.9	52.1	53.1	53.4	54.4
75°	38.4	37.4	37.4	37.5	37.4	37.4	38.4	39.7	40.8	42.6	43.1
77.5°	28.6	28.4	28.7	28.4	28.7	28.4	28.6	28.6	28.9	29.8	30.5
80°	23.5	23.2	23.0	23.6	23.0	23.2	23.5	23.5	23.6	23.8	24.1
82.5°	18.2	18.2	18.1	18.9	18.1	18.2	18.2	18.5	18.5	18.5	18.6
85°	11.0	10.5	11.0	10.5	11.0	10.5	11.0	10.8	11.0	10.8	11.0
87.5°	6.2	6.1	6.0	6.2	6.0	6.1	6.2	5.8	5.8	6.0	5.7
90°	11.6	11.8	11.9	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0
92.5°	17.7	17.7	17.8	17.9	17.8	17.7	17.7	17.5	17.3	16.9	16.7
95°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.7	31.5	31.2
97.5°	50.0	50.0	50.0	50.0	50.0	50.0	50.0	50.0	49.8	49.6	49.2
100°	62.6	62.6	62.6	62.6	62.6	62.6	62.6	62.6	62.5	62.3	62.2
102.5°	76.6	76.7	76.8	76.9	76.8	76.7	76.6	76.6	76.4	76.2	75.9
105°	97.8	98.1	98.4	98.6	98.4	98.1	97.8	97.6	97.3	97.0	96.8
107.5°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.5	119.2
110°	134.1	134.4	134.6	134.9	134.6	134.4	134.1	133.8	133.8	134.0	134.2



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	150.3	150.3	150.4	150.4	150.4	150.3	150.3	150.3	150.3	150.3	150.3
115°	174.9	174.8	174.7	174.6	174.7	174.8	174.9	175.0	175.0	175.1	175.2
117.5°	198.0	197.9	197.7	197.5	197.7	197.9	198.0	198.2	198.5	198.8	199.1
120°	214.5	214.6	214.8	215.0	214.8	214.6	214.5	214.3	214.4	214.8	215.3
122.5°	230.5	230.2	229.8	229.5	229.8	230.2	230.5	230.8	231.1	231.4	231.8
125°	255.1	254.9	254.8	254.6	254.8	254.9	255.1	255.3	255.5	255.7	255.8
127.5°	278.2	278.0	277.9	277.8	277.9	278.0	278.2	278.3	278.5	278.7	278.8
130°	294.0	293.6	293.3	292.9	293.3	293.6	294.0	294.4	294.6	294.8	295.0
132.5°	309.5	309.4	309.2	309.2	309.2	309.4	309.5	309.7	309.9	310.0	310.2
135°	332.2	331.9	331.6	331.4	331.6	331.9	332.2	332.4	332.6	332.8	333.0
137.5°	354.5	354.5	354.6	354.7	354.6	354.5	354.5	354.5	354.5	354.8	355.0
140°	369.2	369.1	369.0	368.9	369.0	369.1	369.2	369.3	369.3	369.4	369.5
142.5°	383.2	383.2	383.2	383.2	383.2	383.2	383.2	383.2	383.3	383.3	383.3
145°	403.2	403.0	402.7	402.4	402.7	403.0	403.2	403.5	403.7	403.8	403.9
147.5°	422.3	422.2	422.1	422.0	422.1	422.2	422.3	422.4	422.5	422.5	422.6
150°	434.3	434.2	434.1	434.0	434.1	434.2	434.3	434.4	434.4	434.4	434.4
152.5°	445.7	445.4	445.2	445.0	445.2	445.4	445.7	445.9	445.9	445.7	445.5
155°	461.3	460.9	460.6	460.2	460.6	460.9	461.3	461.6	461.6	461.3	460.9
157.5°	474.8	474.5	474.2	473.9	474.2	474.5	474.8	475.1	475.1	474.8	474.6
160°	483.0	482.6	482.1	481.6	482.1	482.6	483.0	483.5	483.6	483.3	483.0
162.5°	491.1	490.6	490.2	489.7	490.2	490.6	491.1	491.5	491.5	491.1	490.5
165°	501.3	501.0	500.6	500.2	500.6	501.0	501.3	501.7	501.6	501.1	500.5
167.5°	509.4	508.9	508.3	507.7	508.3	508.9	509.4	510.0	510.0	509.4	508.9
170°	513.8	513.2	512.6	511.9	512.6	513.2	513.8	514.4	514.5	514.0	513.4
172.5°	517.4	516.7	516.1	515.5	516.1	516.7	517.4	518.0	518.0	517.5	516.8
175°	521.1	520.5	519.9	519.2	519.9	520.5	521.1	521.7	521.7	521.1	520.5
177.5°	522.9	522.4	521.7	521.2	521.7	522.4	522.9	523.4	523.5	523.0	522.5
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	501.0	502.2	504.9	507.9	510.5	512.6	514.3	516.7	518.9	521.9	524.8
5°	470.6	473.6	477.8	482.9	489.2	493.4	498.6	503.4	510.1	516.8	523.3
7.5°	444.0	447.2	453.4	460.4	467.9	474.8	481.1	489.3	498.2	508.1	519.1
10°	426.7	430.3	437.7	445.7	454.6	461.4	469.8	479.5	489.6	501.7	515.1
12.5°	411.2	414.6	423.5	431.7	440.9	448.4	458.2	468.0	481.5	494.5	509.9
15°	380.9	390.0	400.1	409.8	420.8	429.9	441.7	451.8	464.7	483.0	500.6
17.5°	347.3	357.0	369.6	384.6	399.3	410.5	422.5	435.1	450.4	469.1	489.4
20°	327.7	335.6	349.5	366.1	383.3	398.9	409.8	423.7	439.6	459.9	480.7
22.5°	313.1	319.7	330.6	347.2	365.7	383.8	397.9	411.6	429.1	449.4	472.2
25°	291.1	298.2	307.7	319.1	340.2	359.4	377.7	393.6	412.1	432.4	457.7
27.5°	272.7	278.9	287.7	299.5	313.7	334.8	357.1	375.1	394.2	416.0	441.3
30°	261.9	267.0	274.1	286.1	299.7	318.7	341.3	362.4	381.6	404.1	430.5
32.5°	250.6	256.0	263.0	272.5	287.0	303.0	325.6	348.7	369.1	392.2	418.0
35°	235.5	239.8	246.1	255.7	268.9	282.8	302.8	326.7	348.2	372.9	397.6
37.5°	220.3	225.2	230.2	238.9	249.6	264.6	281.0	305.4	329.2	351.8	375.9
40°	211.7	214.6	220.1	227.1	238.4	251.7	267.2	291.1	314.9	337.2	361.5
42.5°	202.1	205.4	210.0	217.0	227.1	240.1	255.2	275.8	300.7	322.4	344.5
45°	188.7	190.6	195.2	201.1	209.6	222.7	236.6	254.9	278.4	299.1	318.4
47.5°	175.1	176.8	179.7	185.1	194.6	205.1	218.1	234.6	255.1	275.8	292.2
50°	165.9	167.4	170.1	175.1	183.6	193.9	206.8	221.6	240.0	259.8	273.5
52.5°	156.6	157.4	160.0	165.7	172.8	183.0	194.5	208.1	225.2	241.7	255.7
55°	141.8	143.7	145.4	149.6	156.4	166.1	176.5	189.3	202.6	216.5	228.4
57.5°	126.4	128.5	130.9	134.6	140.0	149.0	158.3	168.7	180.1	191.6	201.6
60°	116.3	118.2	120.3	124.5	129.4	136.5	146.7	155.8	164.4	175.0	184.9
62.5°	106.3	108.3	110.7	114.0	118.7	125.6	134.0	141.9	150.9	160.1	167.5
65°	91.6	93.1	95.0	98.2	102.5	108.7	115.7	121.8	129.8	136.5	143.3
67.5°	75.4	78.3	80.7	83.3	87.0	92.7	97.8	103.7	109.1	114.1	120.3
70°	64.8	67.9	70.3	73.0	76.6	81.5	86.3	90.3	94.8	99.6	105.1
72.5°	55.8	58.3	60.2	63.0	66.3	70.8	75.3	78.6	82.3	85.6	91.0
75°	44.1	45.1	46.5	48.8	51.7	55.1	58.7	61.6	63.8	66.7	70.4
77.5°	31.7	33.7	34.6	36.2	38.3	40.4	42.8	45.3	47.3	48.3	51.3
80°	24.3	25.1	25.9	28.3	29.5	31.7	33.3	35.7	36.5	37.5	40.3
82.5°	18.9	19.4	19.9	20.5	21.3	23.4	25.1	26.6	27.4	27.7	29.9
85°	11.0	11.1	11.4	11.6	11.9	11.9	12.7	13.7	15.2	15.2	15.9
87.5°	5.6	5.6	5.5	5.2	5.4	5.3	5.3	5.1	5.4	5.7	6.0
90°	9.5	8.9	8.2	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2
92.5°	16.3	16.0	15.5	15.0	14.5	14.0	13.2	12.0	10.9	9.8	8.6
95°	30.9	30.7	30.1	29.4	28.8	28.2	27.5	26.7	25.9	25.1	24.3
97.5°	48.9	48.6	47.8	47.1	46.4	45.7	44.9	44.3	43.6	43.0	42.4
100°	62.0	61.8	61.0	60.2	59.4	58.6	58.1	57.6	57.2	56.9	56.5
102.5°	75.6	75.4	74.6	73.9	73.2	72.5	72.1	71.9	71.7	71.6	71.4
105°	96.4	96.1	95.8	95.4	95.1	94.7	94.5	94.4	94.3	94.3	94.2
107.5°	119.0	118.7	118.7	118.6	118.6	118.5	118.4	118.3	118.2	118.1	118.0
110°	134.4	134.6	134.6	134.7	134.8	134.9	134.8	134.6	134.5	134.3	134.1



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	150.3	150.4	150.5	150.7	150.9	151.1	151.1	151.1	151.1	151.0	151.0
115°	175.3	175.4	175.6	175.8	175.9	176.1	176.2	176.2	176.2	176.2	176.2
117.5°	199.4	199.7	199.8	199.9	200.1	200.2	200.2	200.2	200.1	200.0	199.9
120°	215.7	216.2	216.4	216.7	217.0	217.2	217.2	216.9	216.5	216.2	215.8
122.5°	232.0	232.4	232.5	232.6	232.7	232.8	232.8	232.6	232.6	232.4	232.3
125°	256.0	256.2	256.3	256.4	256.5	256.5	256.5	256.5	256.5	256.5	256.5
127.5°	279.0	279.2	279.4	279.5	279.6	279.8	279.7	279.5	279.2	278.9	278.7
130°	295.2	295.3	295.3	295.3	295.3	295.3	295.2	295.0	294.7	294.4	294.2
132.5°	310.4	310.6	310.7	310.7	310.8	310.9	310.8	310.6	310.4	310.2	310.0
135°	333.1	333.3	333.3	333.3	333.3	333.3	333.1	332.5	332.0	331.4	330.9
137.5°	355.3	355.5	355.3	355.3	355.1	354.9	354.7	354.5	354.2	354.0	353.7
140°	369.6	369.7	369.7	369.7	369.7	369.7	369.6	369.4	369.3	369.1	368.9
142.5°	383.3	383.3	383.3	383.4	383.5	383.6	383.5	383.3	383.2	383.0	382.8
145°	403.9	404.0	403.9	403.9	403.8	403.7	403.5	403.1	402.8	402.4	402.1
147.5°	422.7	422.8	422.8	422.8	422.9	423.0	422.8	422.4	422.0	421.5	421.2
150°	434.4	434.4	434.4	434.4	434.4	434.4	434.2	433.8	433.5	433.1	432.7
152.5°	445.2	445.1	445.0	444.9	444.8	444.8	444.6	444.4	444.2	444.0	443.7
155°	460.6	460.2	460.3	460.4	460.5	460.6	460.7	460.7	460.7	460.7	460.7
157.5°	474.3	474.0	474.0	474.1	474.1	474.1	474.2	474.4	474.6	474.7	474.8
160°	482.8	482.5	482.6	482.7	482.8	482.9	483.0	483.0	483.1	483.2	483.3
162.5°	490.1	489.5	489.6	489.7	489.8	489.9	490.1	490.4	490.5	490.8	491.1
165°	500.0	499.4	499.6	499.8	500.0	500.2	500.3	500.6	500.9	501.1	501.4
167.5°	508.4	507.8	507.8	507.8	507.7	507.7	507.9	508.4	508.7	509.1	509.4
170°	512.9	512.4	512.3	512.2	512.1	512.0	512.2	512.6	513.1	513.5	514.0
172.5°	516.2	515.6	515.6	515.6	515.5	515.5	515.7	516.1	516.5	516.8	517.2
175°	519.9	519.2	519.3	519.4	519.5	519.6	519.9	520.3	520.8	521.2	521.7
177.5°	522.0	521.5	521.5	521.5	521.5	521.5	521.7	522.0	522.4	522.7	523.1
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	527.0	528.5	530.2	533.4	536.1	537.3	539.7	541.4	540.8	543.2	547.2
5°	529.1	534.8	541.4	548.0	555.6	562.0	567.0	572.1	576.1	580.9	588.2
7.5°	528.7	538.9	549.9	562.0	574.4	585.2	595.1	605.3	614.3	624.1	637.0
10°	527.4	540.9	554.6	570.4	586.3	601.3	614.7	627.4	639.4	652.3	668.6
12.5°	525.8	541.4	557.9	577.0	596.7	614.7	630.6	648.9	664.0	680.6	699.3
15°	519.2	540.0	562.7	587.3	611.0	635.3	656.9	679.3	700.3	720.1	743.7
17.5°	511.5	535.6	562.2	591.4	619.7	649.3	675.1	703.3	724.6	751.3	773.2
20°	505.2	531.2	559.6	592.4	624.6	657.4	685.9	714.6	738.6	765.4	793.3
22.5°	497.7	526.1	557.0	590.8	624.6	660.4	692.0	720.5	750.3	780.4	809.1
25°	485.4	515.0	547.7	584.8	623.7	660.1	693.9	729.3	761.4	794.2	819.9
27.5°	470.4	501.4	535.8	574.2	614.0	651.4	691.2	729.0	761.3	792.7	815.2
30°	458.3	491.1	524.2	563.0	604.4	644.5	687.2	725.0	758.9	787.2	799.9
32.5°	446.0	477.1	511.2	550.5	592.9	636.1	678.3	717.0	748.4	765.4	765.7
35°	424.6	453.7	489.2	527.8	571.3	618.1	660.9	698.9	718.2	719.6	698.9
37.5°	401.3	427.9	461.4	500.1	547.7	594.3	638.0	663.3	669.8	648.3	610.1
40°	384.5	409.2	441.5	481.2	528.4	576.6	616.4	635.0	628.3	593.4	550.8
42.5°	366.9	389.9	421.1	460.2	507.7	556.3	590.3	600.2	582.4	542.2	492.2
45°	338.3	359.4	390.2	429.7	475.3	520.8	546.6	541.5	511.8	464.0	408.1
47.5°	308.4	328.9	356.6	393.1	439.8	479.1	496.5	481.3	438.9	386.5	341.0
50°	288.7	309.6	335.1	370.0	412.6	450.6	461.7	438.5	391.5	341.1	299.3
52.5°	269.3	287.1	312.2	345.8	386.6	418.7	424.6	397.9	349.3	304.1	267.0
55°	239.8	256.0	277.1	308.7	344.0	371.2	368.0	333.7	289.5	250.9	221.8
57.5°	211.2	223.4	242.9	272.6	303.5	321.8	310.2	280.9	239.8	208.1	183.6
60°	192.3	203.7	221.8	247.7	275.0	285.3	275.6	243.8	211.2	182.4	161.7
62.5°	174.3	184.4	200.0	224.1	246.1	252.3	241.8	214.0	184.8	160.1	142.9
65°	148.4	157.7	170.9	188.1	203.2	206.2	199.5	170.9	148.8	128.1	116.3
67.5°	124.8	130.8	141.2	156.0	164.1	165.8	152.8	134.8	115.3	102.6	93.7
70°	108.9	113.2	122.8	130.8	137.4	137.6	125.6	111.2	96.2	85.9	79.4
72.5°	93.5	97.6	105.0	110.4	115.5	113.8	102.8	91.5	79.4	71.5	66.7
75°	72.1	75.8	79.5	82.1	82.1	80.0	72.0	63.5	56.5	51.9	50.5
77.5°	52.4	55.4	56.7	56.3	55.6	52.3	47.2	41.6	39.1	37.0	35.8
80°	41.2	42.4	42.8	41.8	40.5	36.7	33.3	31.0	28.7	27.8	27.5
82.5°	30.5	31.7	30.5	30.9	28.0	24.9	23.0	22.2	21.3	21.0	20.5
85°	16.2	16.1	15.6	14.5	12.7	12.2	12.0	11.9	11.4	11.6	11.1
87.5°	6.0	5.7	5.3	5.3	5.4	5.3	5.5	5.7	5.8	5.8	6.2
90°	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0
92.5°	9.8	10.9	12.0	13.2	14.0	14.5	15.0	15.5	16.0	16.3	16.7
95°	25.1	25.9	26.7	27.5	28.2	28.8	29.4	30.1	30.7	30.9	31.2
97.5°	43.0	43.6	44.3	44.9	45.7	46.4	47.1	47.8	48.6	48.9	49.2
100°	56.9	57.2	57.6	58.1	58.6	59.4	60.2	61.0	61.8	62.0	62.2
102.5°	71.6	71.7	71.9	72.1	72.5	73.2	73.9	74.6	75.4	75.6	75.9
105°	94.3	94.3	94.4	94.5	94.7	95.1	95.4	95.8	96.1	96.4	96.8
107.5°	118.1	118.2	118.3	118.4	118.5	118.6	118.6	118.7	118.7	119.0	119.2
110°	134.3	134.5	134.6	134.8	134.9	134.8	134.7	134.6	134.6	134.4	134.2





TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.0	151.1	151.1	151.1	151.1	150.9	150.7	150.5	150.4	150.3	150.3
115°	176.2	176.2	176.2	176.2	176.1	175.9	175.8	175.6	175.4	175.3	175.2
117.5°	200.0	200.1	200.2	200.2	200.2	200.1	199.9	199.8	199.7	199.4	199.1
120°	216.2	216.5	216.9	217.2	217.2	217.0	216.7	216.4	216.2	215.7	215.3
122.5°	232.4	232.6	232.6	232.8	232.8	232.7	232.6	232.5	232.4	232.0	231.8
125°	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.3	256.2	256.0	255.8
127.5°	278.9	279.2	279.5	279.7	279.8	279.6	279.5	279.4	279.2	279.0	278.8
130°	294.4	294.7	295.0	295.2	295.3	295.3	295.3	295.3	295.3	295.2	295.0
132.5°	310.2	310.4	310.6	310.8	310.9	310.8	310.7	310.7	310.6	310.4	310.2
135°	331.4	332.0	332.5	333.1	333.3	333.3	333.3	333.3	333.3	333.1	333.0
137.5°	354.0	354.2	354.5	354.7	354.9	355.1	355.3	355.3	355.5	355.3	355.0
140°	369.1	369.3	369.4	369.6	369.7	369.7	369.7	369.7	369.7	369.6	369.5
142.5°	383.0	383.2	383.3	383.5	383.6	383.5	383.4	383.3	383.3	383.3	383.3
145°	402.4	402.8	403.1	403.5	403.7	403.8	403.9	403.9	404.0	403.9	403.9
147.5°	421.5	422.0	422.4	422.8	423.0	422.9	422.8	422.8	422.8	422.7	422.6
150°	433.1	433.5	433.8	434.2	434.4	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	444.0	444.2	444.4	444.6	444.8	444.8	444.9	445.0	445.1	445.2	445.5
155°	460.7	460.7	460.7	460.7	460.6	460.5	460.4	460.3	460.2	460.6	460.9
157.5°	474.7	474.6	474.4	474.2	474.1	474.1	474.1	474.0	474.0	474.3	474.6
160°	483.2	483.1	483.0	483.0	482.9	482.8	482.7	482.6	482.5	482.8	483.0
162.5°	490.8	490.5	490.4	490.1	489.9	489.8	489.7	489.6	489.5	490.1	490.5
165°	501.1	500.9	500.6	500.3	500.2	500.0	499.8	499.6	499.4	500.0	500.5
167.5°	509.1	508.7	508.4	507.9	507.7	507.7	507.8	507.8	507.8	508.4	508.9
170°	513.5	513.1	512.6	512.2	512.0	512.1	512.2	512.3	512.4	512.9	513.4
172.5°	516.8	516.5	516.1	515.7	515.5	515.5	515.6	515.6	515.6	516.2	516.8
175°	521.2	520.8	520.3	519.9	519.6	519.5	519.4	519.3	519.2	519.9	520.5
177.5°	522.7	522.4	522.0	521.7	521.5	521.5	521.5	521.5	521.5	522.0	522.5
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	523.8	523.8	523.8	523.8	523.8	523.8	523.8
2.5°	549.5	550.1	550.6	552.3	552.5	554.0	552.5
5°	594.9	597.9	602.5	607.2	607.6	610.6	605.3
7.5°	645.9	652.7	657.0	664.5	667.4	669.3	666.3
10°	681.0	687.3	698.6	704.0	709.5	710.3	707.8
12.5°	715.0	725.0	733.8	744.2	744.0	751.4	748.7
15°	760.2	770.5	782.7	794.3	798.5	798.5	801.9
17.5°	792.4	811.4	824.0	833.1	843.1	844.8	843.6
20°	814.2	834.6	848.2	860.0	866.7	868.6	868.6
22.5°	830.4	847.8	861.0	871.6	877.2	879.4	878.8
25°	841.6	856.6	864.6	867.8	869.2	868.9	864.9
27.5°	826.3	825.5	820.6	810.8	803.5	799.1	794.0
30°	796.9	785.9	773.2	759.3	741.4	727.6	723.4
32.5°	753.1	728.5	707.0	683.9	664.6	650.9	645.1
35°	668.6	629.5	597.6	569.8	549.6	536.9	532.6
37.5°	568.2	530.4	491.0	464.0	447.1	434.4	429.6
40°	504.4	463.2	428.8	403.5	386.2	373.7	373.5
42.5°	446.1	406.8	374.4	356.2	337.6	329.3	329.3
45°	365.3	333.9	306.4	292.0	280.9	274.1	272.2
47.5°	302.5	276.4	258.2	246.7	237.6	233.4	230.5
50°	267.2	244.4	229.8	219.9	214.8	209.4	208.9
52.5°	237.8	219.4	208.0	200.0	193.6	190.3	190.4
55°	199.8	185.3	177.3	171.1	166.1	163.5	162.5
57.5°	168.4	157.5	151.6	146.0	143.8	141.9	141.3
60°	148.8	141.4	135.9	131.4	128.3	127.7	127.4
62.5°	132.6	124.8	121.1	117.6	115.3	114.3	114.0
65°	109.3	103.6	100.2	97.5	96.7	95.1	95.0
67.5°	88.1	84.7	82.5	80.6	79.5	79.4	79.4
70°	75.2	73.2	71.3	70.3	69.6	69.2	69.2
72.5°	64.0	62.6	61.0	60.5	60.4	59.9	59.7
75°	48.8	47.3	47.5	46.5	45.6	44.5	43.9
77.5°	34.6	33.5	33.3	33.2	32.5	32.4	32.6
80°	26.8	25.8	25.5	25.8	25.5	24.9	24.9
82.5°	20.4	19.5	19.3	19.2	19.0	19.2	18.8
85°	11.0	10.5	10.5	10.5	11.0	10.8	10.5
87.5°	6.0	5.9	6.2	6.1	6.1	6.0	6.2
90°	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.9	17.3	17.5	17.7	17.7	17.8	17.9
95°	31.5	31.7	31.9	31.9	31.9	31.9	31.9
97.5°	49.6	49.8	50.0	50.0	50.0	50.0	50.0
100°	62.3	62.5	62.6	62.6	62.6	62.6	62.6
102.5°	76.2	76.4	76.6	76.6	76.7	76.8	76.9
105°	97.0	97.3	97.6	97.8	98.1	98.4	98.6
107.5°	119.5	119.8	119.8	119.8	119.8	119.8	119.8
110°	134.0	133.8	133.8	134.1	134.4	134.6	134.9



TEST NUMBER: P333016-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	150.3	150.3	150.3	150.3	150.3	150.4	150.4
115°	175.1	175.0	175.0	174.9	174.8	174.7	174.6
117.5°	198.8	198.5	198.2	198.0	197.9	197.7	197.5
120°	214.8	214.4	214.3	214.5	214.6	214.8	215.0
122.5°	231.4	231.1	230.8	230.5	230.2	229.8	229.5
125°	255.7	255.5	255.3	255.1	254.9	254.8	254.6
127.5°	278.7	278.5	278.3	278.2	278.0	277.9	277.8
130°	294.8	294.6	294.4	294.0	293.6	293.3	292.9
132.5°	310.0	309.9	309.7	309.5	309.4	309.2	309.2
135°	332.8	332.6	332.4	332.2	331.9	331.6	331.4
137.5°	354.8	354.5	354.5	354.5	354.5	354.6	354.7
140°	369.4	369.3	369.3	369.2	369.1	369.0	368.9
142.5°	383.3	383.3	383.2	383.2	383.2	383.2	383.2
145°	403.8	403.7	403.5	403.2	403.0	402.7	402.4
147.5°	422.5	422.5	422.4	422.3	422.2	422.1	422.0
150°	434.4	434.4	434.4	434.3	434.2	434.1	434.0
152.5°	445.7	445.9	445.9	445.7	445.4	445.2	445.0
155°	461.3	461.6	461.6	461.3	460.9	460.6	460.2
157.5°	474.8	475.1	475.1	474.8	474.5	474.2	473.9
160°	483.3	483.6	483.5	483.0	482.6	482.1	481.6
162.5°	491.1	491.5	491.5	491.1	490.6	490.2	489.7
165°	501.1	501.6	501.7	501.3	501.0	500.6	500.2
167.5°	509.4	510.0	510.0	509.4	508.9	508.3	507.7
170°	514.0	514.5	514.4	513.8	513.2	512.6	511.9
172.5°	517.5	518.0	518.0	517.4	516.7	516.1	515.5
175°	521.1	521.7	521.7	521.1	520.5	519.9	519.2
177.5°	523.0	523.5	523.4	522.9	522.4	521.7	521.2
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5

(END OF REPORT)